

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331656-840

Luminaire Tested: **S122RDIP-S485D530U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331656-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S485D530U840-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3800.7 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331656-840

CATALOG NUMBER: S122RDIP-S485D530U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331656-840

CATALOG NUMBER: S122RDIP-S485D530U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33	29
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25
5	69	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	22	20
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	14
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13454	13454	13454
5°	13506	13287	13361
10°	13404	13070	12959
15°	13249	12682	12318
20°	13036	12129	11519
25°	12818	11501	10750
30°	12515	10856	9758
35°	12220	10153	8889
40°	11921	9428	7885
45°	11574	8611	6976
50°	11215	7784	6081
55°	10849	6899	5222
60°	10424	5968	4334
65°	9941	5012	3947
70°	9361	4131	3635
75°	8659	3762	3387
80°	7643	3366	3087
85°	6002	2649	2649



TEST NUMBER: P331656-840

CATALOG NUMBER: S122RDIP-S485D530U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	2.1
10°-20°	214.2	5.6
20°-30°	300.8	7.9
30°-40°	328.0	8.6
40°-50°	301.6	7.9
50°-60°	236.8	6.2
60°-70°	154.4	4.1
70°-80°	79.6	2.1
80°-90°	23.4	0.6
90°-100°	119.7	3.2
100°-110°	406.3	10.7
110°-120°	431.7	11.4
120°-130°	355.4	9.3
130°-140°	285.4	7.5
140°-150°	215.7	5.7
150°-160°	151.6	4.0
160°-170°	89.2	2.3
170°-180°	29.0	0.8
0°-30°	593.0	15.6
0°-40°	921.0	24.2
0°-60°	1459.4	38.4
0°-90°	1716.8	45.2
90°-120°	957.8	25.2
90°-150°	1814.1	47.7
90°-180°	2084.0	54.8
0°-180°	3800.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	833	833	833	833	833	
5°	833	829	820	826	824	79
15°	793	783	759	745	737	223
25°	720	694	646	616	603	331
35°	620	580	515	469	451	388
45°	507	455	377	326	306	391
55°	385	325	245	202	186	344
65°	260	199	131	107	103	258
75°	139	87	60	55	54	147
85°	32	17	14	14	14	38
90°	1	8	20	19	19	2
95°	20	50	226	85	66	21
105°	70	106	427	763	649	75
115°	124	156	357	737	854	123
125°	173	204	343	597	693	153
135°	203	242	339	502	574	157
145°	232	266	338	419	458	145
155°	263	284	328	371	385	121
165°	287	295	314	333	338	81
175°	299	299	302	306	305	28
180°	299	299	299	299	299	



TEST NUMBER: P331656-840

CATALOG NUMBER: S122RDIP-S485D530U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	836.4	835.8	835.1	834.4	833.7	832.6	831.2	829.7	828.2	826.8	828.1
5°	833.3	832.5	831.7	830.9	830.0	828.5	826.4	824.2	822.0	819.8	821.3
7.5°	824.8	823.7	822.7	821.6	820.6	818.8	816.3	813.7	811.2	808.7	809.1
10°	817.6	816.4	815.2	814.1	812.8	810.6	807.3	803.9	800.5	797.2	796.7
12.5°	808.5	807.1	805.6	804.2	802.7	799.9	795.6	791.3	787.0	782.7	781.8
15°	792.6	790.8	789.0	787.1	785.3	781.5	775.8	770.1	764.5	758.7	755.6
17.5°	773.3	770.4	767.6	764.8	761.9	756.9	749.6	742.3	735.0	727.6	723.9
20°	758.7	755.4	752.0	748.7	745.3	739.4	731.0	722.7	714.3	705.9	701.8
22.5°	743.1	739.3	735.5	731.7	728.0	721.4	712.0	702.5	693.1	683.6	678.2
25°	719.5	714.2	708.8	703.4	698.0	689.8	678.7	667.7	656.6	645.6	638.7
27.5°	691.2	685.3	679.4	673.7	667.8	658.6	646.2	633.7	621.3	608.7	600.8
30°	671.3	664.9	658.5	652.2	645.8	635.9	622.5	609.0	595.6	582.3	573.7
32.5°	652.0	644.5	637.0	629.7	622.2	611.6	597.9	584.2	570.6	556.9	547.1
35°	620.0	611.4	602.9	594.3	585.7	574.1	559.4	544.6	529.9	515.1	504.5
37.5°	587.9	578.6	569.2	559.8	550.5	537.9	522.2	506.4	490.7	475.0	463.3
40°	565.6	555.6	545.5	535.5	525.4	512.3	496.0	479.8	463.5	447.3	435.4
42.5°	542.7	532.1	521.5	511.0	500.4	486.7	469.9	453.0	436.3	419.5	407.2
45°	506.9	495.6	484.3	473.1	461.9	447.5	429.9	412.3	394.7	377.1	365.2
47.5°	471.8	459.9	448.1	436.2	424.2	409.2	391.0	372.8	354.7	336.5	324.7
50°	446.5	434.5	422.7	410.8	398.9	383.7	365.3	346.9	328.4	309.9	298.4
52.5°	421.7	409.3	396.9	384.5	372.0	356.8	338.7	320.7	302.7	284.7	273.5
55°	385.4	372.3	359.2	346.2	333.2	317.5	299.4	281.3	263.2	245.1	235.1
57.5°	348.1	334.8	321.3	307.9	294.5	279.1	261.8	244.3	226.9	209.5	200.3
60°	322.8	309.4	296.0	282.6	269.1	253.9	236.6	219.3	202.1	184.8	176.2
62.5°	298.0	284.7	271.2	257.8	244.4	229.5	213.1	196.6	180.2	163.7	155.5
65°	260.2	246.6	233.1	219.4	205.9	191.6	176.5	161.4	146.3	131.2	125.5
67.5°	223.7	210.3	196.7	183.3	169.8	156.2	142.7	129.2	115.5	102.0	99.4
70°	198.3	185.3	172.2	159.2	146.0	133.7	122.2	110.6	99.1	87.5	85.8
72.5°	174.2	161.7	149.2	136.6	124.1	113.2	103.9	94.6	85.3	76.0	74.6
75°	138.8	127.0	115.3	103.6	91.8	83.1	77.5	71.7	66.0	60.3	59.2
77.5°	103.9	93.6	83.3	73.0	62.8	56.2	53.5	50.8	48.0	45.2	44.5
80°	82.2	73.6	65.1	56.6	48.0	42.9	41.2	39.6	37.9	36.2	35.5
82.5°	62.3	55.6	49.0	42.3	35.6	31.7	30.6	29.4	28.3	27.2	26.8
85°	32.4	28.9	25.3	21.9	18.4	16.4	15.9	15.3	14.8	14.3	14.3
87.5°	9.8	9.1	8.4	7.6	6.8	6.6	7.2	8.0	8.6	8.8	8.5
90°	0.6	2.3	4.6	5.8	6.9	8.7	11.5	15.6	19.0	19.6	19.0
92.5°	7.1	10.1	14.2	16.9	20.7	26.2	39.2	57.5	73.8	74.8	63.2
95°	20.2	22.4	28.2	33.4	42.6	56.5	82.9	133.0	199.9	225.8	197.5
97.5°	32.8	36.0	42.0	49.9	60.5	76.1	109.5	179.3	290.2	385.4	404.2
100°	44.3	46.0	51.3	60.5	72.0	88.2	118.7	188.9	313.3	454.9	537.9
102.5°	54.9	56.2	61.4	70.6	82.6	98.7	126.9	189.3	304.6	457.3	587.6
105°	70.3	72.6	76.5	85.2	97.9	114.0	141.1	192.4	287.4	426.8	580.0
107.5°	86.8	88.7	92.6	100.6	113.1	129.4	155.6	200.3	278.8	394.0	529.4
110°	97.9	100.2	103.7	111.2	123.2	140.0	165.3	206.7	277.0	378.4	497.6



TEST NUMBER: P331656-840

CATALOG NUMBER: S122RDIP-S485D530U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	108.1	110.4	114.2	121.3	132.9	150.1	174.5	213.7	277.5	368.2	475.4
115°	123.8	126.7	130.2	137.0	148.6	164.1	188.9	224.0	279.9	357.1	448.1
117.5°	140.2	142.5	145.9	152.1	163.1	179.3	202.2	235.1	284.1	351.6	430.8
120°	150.3	152.6	156.0	161.3	172.8	188.9	211.4	242.5	286.8	348.4	421.6
122.5°	160.0	161.9	165.3	171.0	182.5	199.0	220.2	248.9	290.0	346.6	413.7
125°	172.8	174.5	177.9	184.9	196.4	212.5	233.3	259.1	294.9	343.3	402.5
127.5°	182.9	185.2	190.1	197.6	208.7	225.3	245.5	268.7	299.8	341.3	392.2
130°	188.9	191.2	196.9	205.0	216.5	232.7	252.9	274.7	303.5	340.3	385.3
132.5°	194.4	197.2	203.4	212.0	223.9	240.0	259.2	280.7	307.2	339.9	379.7
135°	202.7	205.0	212.0	220.6	233.8	249.9	268.4	288.5	311.5	339.2	372.0
137.5°	210.6	213.3	220.3	229.4	242.6	257.5	275.8	294.5	315.5	339.1	366.6
140°	216.5	218.8	225.8	235.0	247.6	262.7	279.9	297.7	317.3	338.6	363.5
142.5°	222.6	224.4	230.9	240.0	252.3	266.3	283.2	300.5	318.7	338.6	360.2
145°	231.6	233.8	239.5	248.2	259.7	272.4	287.9	304.1	320.2	337.5	355.9
147.5°	241.2	242.9	248.4	256.4	266.0	277.2	291.9	306.1	320.6	335.4	351.5
150°	247.6	249.3	254.0	261.5	270.1	280.4	293.7	307.0	320.2	334.1	347.9
152.5°	254.1	254.9	259.5	266.1	274.3	283.7	295.6	307.4	319.3	331.7	344.7
155°	263.2	263.8	267.2	273.6	279.9	288.5	298.3	308.1	317.9	327.7	338.6
157.5°	270.7	271.4	274.2	279.6	284.8	292.0	300.2	308.1	315.3	323.6	333.0
160°	275.9	276.4	278.7	283.4	287.9	294.3	301.2	308.1	313.9	320.8	328.8
162.5°	280.9	280.5	282.9	286.6	290.7	295.7	301.6	307.6	312.5	318.5	325.2
165°	286.8	286.2	287.4	290.8	293.7	297.2	302.4	306.4	309.8	313.9	319.0
167.5°	291.6	290.9	292.0	294.2	296.3	298.4	302.3	305.6	307.2	309.8	313.1
170°	294.9	293.7	294.3	296.0	297.2	298.9	301.7	304.7	305.8	307.5	309.8
172.5°	296.7	296.0	295.7	297.4	298.1	299.3	301.3	303.3	304.0	304.8	306.6
175°	298.9	298.3	297.7	298.9	298.9	299.4	300.6	301.7	301.2	301.7	302.4
177.5°	299.9	299.0	298.5	299.4	299.4	299.4	299.9	300.8	299.9	299.4	299.9
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4



TEST NUMBER: P331656-840

CATALOG NUMBER: S122RDIP-S485D530U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	829.4	830.8	832.1	832.6	832.4	832.1	831.8	831.6
5°	822.8	824.4	825.9	826.4	825.9	825.4	824.9	824.4
7.5°	809.5	809.9	810.4	810.2	809.3	808.4	807.6	806.7
10°	796.2	795.7	795.2	794.5	793.5	792.4	791.4	790.4
12.5°	780.9	780.0	779.1	777.8	776.1	774.5	772.7	771.1
15°	752.3	749.2	746.0	743.6	741.8	740.2	738.5	736.9
17.5°	720.0	716.3	712.5	709.1	706.3	703.4	700.5	697.6
20°	697.5	693.4	689.1	685.2	681.6	677.8	674.2	670.4
22.5°	672.8	667.4	662.1	657.9	655.2	652.5	649.7	646.9
25°	631.9	625.0	618.1	613.4	610.9	608.3	605.9	603.4
27.5°	592.8	584.7	576.7	570.8	566.7	562.8	558.8	554.8
30°	565.1	556.6	548.1	541.5	536.9	532.5	528.0	523.4
32.5°	537.3	527.7	517.9	510.9	506.6	502.4	498.1	493.8
35°	494.0	483.4	472.9	465.7	462.1	458.4	454.7	451.0
37.5°	451.7	440.1	428.5	420.5	416.4	412.1	407.9	403.6
40°	423.4	411.5	399.6	391.5	387.2	382.8	378.4	374.1
42.5°	394.9	382.5	370.3	362.0	357.8	353.6	349.3	345.1
45°	353.3	341.4	329.5	321.5	317.5	313.5	309.4	305.5
47.5°	312.9	301.0	289.2	281.4	277.8	274.2	270.4	266.8
50°	286.8	275.3	263.7	256.2	252.7	249.1	245.6	242.1
52.5°	262.3	251.2	239.9	232.8	229.5	226.3	223.0	219.7
55°	225.0	214.9	204.9	198.2	195.1	191.9	188.7	185.5
57.5°	191.1	181.9	172.7	166.7	164.0	161.4	158.6	155.9
60°	167.6	159.2	150.6	145.0	142.3	139.6	136.9	134.2
62.5°	147.3	139.3	131.1	126.2	124.6	123.0	121.4	119.8
65°	119.9	114.1	108.5	105.3	104.8	104.3	103.8	103.3
67.5°	96.7	94.1	91.5	90.0	89.4	88.9	88.4	87.8
70°	84.1	82.5	80.8	79.6	79.0	78.3	77.6	77.0
72.5°	73.2	71.8	70.4	69.5	69.1	68.7	68.3	67.9
75°	58.0	56.9	55.6	54.9	54.8	54.6	54.4	54.3
77.5°	43.9	43.2	42.6	42.1	41.8	41.6	41.3	41.0
80°	34.8	34.2	33.5	33.2	33.2	33.2	33.2	33.2
82.5°	26.4	26.0	25.5	25.3	25.3	25.3	25.3	25.3
85°	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3
87.5°	8.3	7.9	8.0	8.0	8.0	8.0	8.0	8.0
90°	18.4	17.3	18.4	19.0	19.0	19.0	19.0	19.0
92.5°	50.2	43.1	38.3	34.6	34.2	32.4	32.8	31.9
95°	150.9	115.7	91.6	78.9	71.4	66.9	65.0	65.6
97.5°	352.1	288.1	225.8	184.2	156.6	142.5	134.1	129.3
100°	525.8	454.4	375.5	305.8	258.0	233.3	216.5	206.2
102.5°	639.6	623.5	565.8	491.9	440.0	397.7	376.9	362.8
105°	699.7	764.8	772.3	753.3	717.6	681.9	657.1	649.0
107.5°	656.4	754.5	814.4	842.2	846.7	844.8	839.8	829.1
110°	619.1	722.2	795.9	843.1	867.9	878.9	884.0	883.4



TEST NUMBER: P331656-840

CATALOG NUMBER: S122RDIP-S485D530U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	585.0	684.0	762.8	816.9	851.3	869.6	879.4	882.5
115°	543.1	631.8	707.2	766.6	807.4	833.9	848.9	854.0
117.5°	511.5	589.4	657.8	713.5	755.2	783.2	798.9	803.2
120°	495.8	567.2	628.3	680.8	721.0	748.1	764.8	770.5
122.5°	483.4	548.9	606.6	654.0	690.1	716.8	731.6	736.5
125°	465.3	524.6	575.3	618.5	652.0	673.8	688.2	692.9
127.5°	447.5	501.2	549.0	588.9	617.9	638.4	650.9	654.6
130°	436.0	485.5	531.0	569.0	597.2	616.8	628.3	632.9
132.5°	425.0	470.8	512.6	548.3	576.0	595.6	606.2	610.4
135°	409.5	447.5	485.5	517.8	542.5	561.5	571.9	574.2
137.5°	397.2	429.0	459.1	487.3	509.8	526.1	535.2	538.7
140°	389.3	417.0	443.4	468.8	487.3	502.2	510.8	514.3
142.5°	382.8	406.4	429.2	450.4	467.9	481.5	489.2	489.9
145°	373.8	392.7	410.6	427.4	441.1	450.9	456.7	458.4
147.5°	366.8	381.7	395.7	407.9	419.3	427.1	431.0	432.0
150°	361.6	374.4	386.5	396.8	405.5	412.3	415.8	416.4
152.5°	356.6	368.4	378.6	387.6	394.4	400.4	402.9	403.0
155°	349.6	358.8	367.4	373.8	380.1	384.2	386.5	385.3
157.5°	341.4	349.1	356.4	361.3	365.8	369.2	370.2	370.2
160°	336.3	342.6	349.0	353.0	357.1	359.9	360.5	360.5
162.5°	331.2	336.7	342.1	345.2	349.2	351.2	351.7	351.3
165°	323.7	327.7	331.7	334.1	336.3	338.6	338.6	338.1
167.5°	316.4	319.5	322.2	324.4	325.4	326.7	326.6	325.9
170°	312.8	314.5	316.8	317.9	318.5	320.2	319.6	318.5
172.5°	308.6	309.8	311.6	312.4	313.0	313.8	313.2	312.5
175°	304.1	304.7	305.3	305.8	305.8	306.4	305.8	304.7
177.5°	300.8	300.8	301.3	301.3	301.3	301.3	300.8	299.9
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4

(END OF REPORT)