

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331690-840

Luminaire Tested: **S122RDIP-S675D725U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331690-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S675D725U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5271.1 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331690-840

CATALOG NUMBER: S122RDIP-S675D725U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331690-840

CATALOG NUMBER: S122RDIP-S675D725U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38				
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33				
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	34	33	28				
4	74	64	56	51	68	59	52	47	50	45	41	41	37	35	33	30	28	25				
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25	22				
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	24	22	19				
7	58	47	39	33	54	43	36	31	37	31	28	31	27	24	25	22	20	17				
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16				
9	51	39	31	27	46	36	29	25	31	26	22	26	22	19	21	18	16	14				
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18392	18392	18392
5°	18462	18162	18263
10°	18321	17864	17713
15°	18111	17336	16836
20°	17819	16579	15747
25°	17521	15720	14694
30°	17107	14838	13340
35°	16703	13878	12151
40°	16297	12886	10777
45°	15819	11768	9533
50°	15330	10643	8312
55°	14829	9433	7139
60°	14247	8157	5926
65°	13589	6854	5398
70°	12798	5646	4961
75°	11834	5147	4629
80°	10451	4603	4212
85°	8207	3631	3631



TEST NUMBER: P331690-840

CATALOG NUMBER: S122RDIP-S675D725U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.6	2.0
10°-20°	292.8	5.6
20°-30°	411.1	7.8
30°-40°	448.3	8.5
40°-50°	412.2	7.8
50°-60°	323.8	6.1
60°-70°	211.1	4.0
70°-80°	108.8	2.1
80°-90°	30.7	0.6
90°-100°	33.3	0.6
100°-110°	122.1	2.3
110°-120°	326.4	6.2
120°-130°	538.9	10.2
130°-140°	573.1	10.9
140°-150°	532.7	10.1
150°-160°	428.3	8.1
160°-170°	276.0	5.2
170°-180°	95.0	1.8
0°-30°	810.5	15.4
0°-40°	1258.9	23.9
0°-60°	1994.8	37.8
0°-90°	2345.4	44.5
90°-120°	481.9	9.1
90°-150°	2126.5	40.3
90°-180°	2926.0	55.5
0°-180°	5271.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1139	1139	1139	1139	1139	
5°	1139	1134	1121	1129	1127	108
15°	1084	1071	1037	1018	1007	305
25°	984	949	882	842	825	452
35°	847	793	704	642	616	530
45°	693	622	515	445	418	535
55°	527	445	335	276	254	471
65°	356	272	179	146	141	352
75°	190	120	82	76	74	201
85°	44	24	20	20	20	52
90°	1	9	14	18	20	4
95°	47	25	28	32	31	57
105°	220	229	44	52	55	235
115°	415	428	446	127	59	409
125°	587	597	610	615	618	523
135°	727	738	745	752	750	561
145°	843	843	854	859	856	527
155°	928	923	930	934	929	428
165°	978	974	976	980	976	276
175°	1000	996	997	1001	995	95
180°	998	998	998	998	998	



TEST NUMBER: P331690-840

CATALOG NUMBER: S122RDIP-S675D725U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1
2.5°	1143.3	1142.4	1141.5	1140.5	1139.6	1138.1	1136.1	1134.1	1132.2	1130.1	1132.0
5°	1139.1	1138.0	1136.9	1135.7	1134.6	1132.6	1129.5	1126.6	1123.6	1120.6	1122.7
7.5°	1127.4	1126.0	1124.6	1123.2	1121.8	1119.2	1115.8	1112.4	1108.8	1105.4	1105.9
10°	1117.5	1115.9	1114.3	1112.7	1111.1	1108.0	1103.4	1098.8	1094.3	1089.6	1089.0
12.5°	1105.1	1103.2	1101.2	1099.2	1097.2	1093.4	1087.5	1081.7	1075.7	1069.9	1068.6
15°	1083.5	1081.0	1078.4	1075.9	1073.4	1068.2	1060.5	1052.7	1044.9	1037.1	1032.8
17.5°	1056.9	1053.1	1049.2	1045.3	1041.5	1034.6	1024.6	1014.6	1004.6	994.6	989.5
20°	1037.1	1032.5	1027.9	1023.4	1018.8	1010.8	999.3	987.8	976.4	964.9	959.2
22.5°	1015.6	1010.6	1005.4	1000.3	995.1	986.1	973.2	960.3	947.4	934.4	927.1
25°	983.5	976.1	968.9	961.5	954.2	942.9	927.9	912.7	897.6	882.4	873.0
27.5°	944.7	936.8	928.8	920.8	912.8	900.3	883.3	866.3	849.2	832.1	821.2
30°	917.6	908.8	900.1	891.4	882.7	869.2	850.8	832.5	814.2	795.9	784.2
32.5°	891.1	880.9	870.8	860.6	850.4	836.0	817.3	798.6	779.9	761.2	747.9
35°	847.4	835.8	824.0	812.3	800.7	784.8	764.6	744.5	724.3	704.1	689.6
37.5°	803.8	790.8	778.0	765.2	752.3	735.2	713.8	692.3	670.8	649.2	633.4
40°	773.2	759.4	745.7	732.0	718.2	700.2	678.0	655.8	633.6	611.4	595.1
42.5°	741.8	727.4	712.9	698.4	684.0	665.2	642.3	619.4	596.3	573.4	556.5
45°	692.8	677.4	662.1	646.7	631.4	611.7	587.6	563.6	539.5	515.4	499.2
47.5°	644.9	628.6	612.4	596.1	579.9	559.4	534.5	509.7	484.8	460.0	443.8
50°	610.3	594.0	577.7	561.5	545.2	524.5	499.3	474.1	448.9	423.7	407.9
52.5°	576.5	559.5	542.5	525.5	508.5	487.7	463.0	438.4	413.7	389.1	373.9
55°	526.8	509.0	491.1	473.2	455.3	434.0	409.3	384.6	359.8	335.1	321.3
57.5°	475.8	457.6	439.2	420.9	402.5	381.5	357.7	334.0	310.1	286.4	273.8
60°	441.2	422.9	404.6	386.3	367.9	347.0	323.4	299.7	276.2	252.6	240.9
62.5°	407.4	389.1	370.7	352.4	334.1	313.7	291.2	268.7	246.2	223.7	212.6
65°	355.7	337.1	318.5	300.0	281.4	261.9	241.3	220.7	200.0	179.4	171.6
67.5°	305.8	287.3	268.9	250.5	232.1	213.6	195.0	176.5	157.9	139.4	135.8
70°	271.1	253.3	235.4	217.5	199.7	182.8	167.0	151.2	135.4	119.6	117.2
72.5°	238.1	221.0	203.9	186.7	169.6	154.7	142.0	129.3	116.6	103.9	102.0
75°	189.7	173.7	157.6	141.6	125.5	113.6	105.8	98.1	90.3	82.5	80.9
77.5°	142.1	127.9	113.9	99.9	85.8	76.9	73.1	69.4	65.6	61.9	60.9
80°	112.4	100.7	89.0	77.4	65.6	58.7	56.4	54.0	51.8	49.5	48.6
82.5°	85.1	76.0	67.0	57.8	48.7	43.3	41.8	40.2	38.7	37.2	36.6
85°	44.3	39.5	34.7	29.9	25.0	22.3	21.6	21.0	20.3	19.6	19.6
87.5°	13.3	12.2	11.1	10.0	8.9	8.5	8.7	9.0	9.2	9.5	9.5
90°	0.7	2.5	4.2	6.1	7.8	9.3	10.6	11.9	13.1	14.4	15.2
92.5°	14.5	14.4	14.2	14.1	13.9	14.2	14.8	15.5	16.2	16.8	17.2
95°	47.0	41.7	36.4	31.1	25.8	23.6	24.8	26.0	27.1	28.2	29.0
97.5°	93.2	78.3	63.3	48.4	33.4	27.3	29.9	32.5	35.1	37.7	38.4
100°	127.8	105.8	83.9	61.9	39.9	30.3	33.0	35.7	38.5	41.2	42.4
102.5°	166.0	161.4	156.7	152.1	147.3	133.6	110.8	88.0	65.1	42.3	44.0
105°	219.6	224.4	229.2	234.1	238.8	219.3	175.5	131.7	87.9	44.0	45.8
107.5°	280.7	284.6	288.5	292.4	296.3	272.0	219.3	166.8	114.2	61.7	59.9
110°	320.0	323.4	326.8	330.1	333.5	311.9	265.6	219.2	172.8	126.4	110.4



TEST NUMBER: P331690-840

CATALOG NUMBER: S122RDIP-S675D725U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	357.0	360.0	362.9	366.0	368.9	364.7	353.3	341.7	330.3	318.8	260.3
115°	415.4	418.1	420.8	423.5	426.3	429.7	433.6	437.7	441.7	445.8	371.4
117.5°	467.6	470.6	473.6	476.7	479.7	482.6	485.4	488.2	490.9	493.7	475.7
120°	505.6	508.1	510.5	512.9	515.3	518.0	520.9	523.7	526.6	529.5	531.4
122.5°	538.1	540.6	543.1	545.6	548.2	551.0	554.2	557.3	560.5	563.6	564.7
125°	587.3	589.4	591.5	593.6	595.6	598.2	601.3	604.3	607.3	610.5	611.6
127.5°	632.0	634.3	636.6	638.8	641.2	643.5	645.8	648.0	650.4	652.6	654.3
130°	660.2	662.9	665.4	667.9	670.6	672.7	674.5	676.2	678.0	679.7	681.6
132.5°	689.1	691.4	693.6	695.7	697.9	699.8	701.7	703.4	705.2	706.9	708.4
135°	726.7	729.3	731.8	734.5	737.0	739.0	740.4	741.8	743.4	744.8	746.4
137.5°	764.8	766.5	768.3	770.1	771.9	773.7	775.3	776.9	778.5	780.2	781.7
140°	789.6	790.8	792.1	793.5	794.7	796.3	798.0	799.8	801.5	803.3	804.8
142.5°	810.4	811.5	812.7	813.9	815.0	816.6	818.6	820.6	822.6	824.7	826.0
145°	843.0	842.8	842.7	842.5	842.4	843.6	846.4	849.1	851.8	854.5	855.8
147.5°	871.5	870.9	870.3	869.7	869.1	870.1	872.8	875.5	878.2	880.9	881.7
150°	890.0	888.9	887.8	886.7	885.4	886.3	888.8	891.3	893.9	896.5	897.5
152.5°	905.5	904.3	903.1	901.8	900.6	901.2	903.6	906.1	908.5	910.9	911.9
155°	928.3	926.9	925.3	923.9	922.5	922.7	924.6	926.6	928.5	930.4	931.4
157.5°	946.0	944.8	943.6	942.4	941.2	941.2	942.6	943.9	945.2	946.6	947.8
160°	956.4	955.4	954.5	953.5	952.6	952.6	953.5	954.5	955.4	956.4	957.5
162.5°	965.7	964.7	963.8	962.8	961.8	961.8	962.6	963.4	964.3	965.1	966.2
165°	978.2	977.1	976.2	975.2	974.2	974.0	974.5	975.0	975.4	975.9	977.0
167.5°	987.3	986.4	985.4	984.5	983.5	983.2	983.7	984.1	984.6	985.0	986.1
170°	992.6	991.6	990.7	989.7	988.8	988.4	988.8	989.1	989.4	989.7	990.8
172.5°	996.0	995.0	994.1	993.1	992.2	991.9	992.2	992.5	992.8	993.1	994.3
175°	1000.5	999.4	998.3	997.1	996.0	995.6	995.9	996.2	996.5	996.9	998.0
177.5°	1001.3	1000.4	999.5	998.6	997.6	997.2	997.3	997.5	997.6	997.7	998.7
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331690-840

CATALOG NUMBER: S122RDIP-S675D725U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1
2.5°	1133.8	1135.6	1137.4	1138.1	1137.8	1137.4	1137.1	1136.7
5°	1124.7	1126.8	1128.8	1129.5	1128.8	1128.1	1127.5	1126.8
7.5°	1106.5	1107.1	1107.7	1107.4	1106.2	1105.1	1103.9	1102.7
10°	1088.3	1087.6	1086.9	1085.9	1084.5	1083.2	1081.8	1080.4
12.5°	1067.4	1066.2	1064.9	1063.2	1060.9	1058.6	1056.3	1054.0
15°	1028.4	1024.0	1019.7	1016.3	1014.1	1011.8	1009.5	1007.2
17.5°	984.3	979.1	973.9	969.4	965.4	961.5	957.6	953.6
20°	953.5	947.8	942.0	936.6	931.6	926.6	921.5	916.5
22.5°	919.7	912.3	904.9	899.4	895.5	891.8	888.1	884.3
25°	863.6	854.2	844.9	838.5	835.1	831.6	828.2	824.8
27.5°	810.2	799.3	788.4	780.1	774.7	769.2	763.8	758.3
30°	772.5	760.8	749.1	740.2	734.0	727.8	721.6	715.5
32.5°	734.6	721.2	707.9	698.3	692.5	686.7	680.9	675.1
35°	675.3	660.9	646.4	636.6	631.6	626.5	621.6	616.5
37.5°	617.4	601.6	585.7	574.8	569.1	563.3	557.5	551.8
40°	578.8	562.5	546.2	535.1	529.2	523.2	517.3	511.3
42.5°	539.8	522.9	506.1	494.8	489.1	483.3	477.6	471.7
45°	482.9	466.7	450.4	439.5	434.0	428.5	423.0	417.5
47.5°	427.7	411.5	395.3	384.8	379.7	374.8	369.7	364.8
50°	392.1	376.3	360.5	350.1	345.4	340.5	335.8	330.9
52.5°	358.6	343.3	328.0	318.2	313.8	309.3	304.9	300.4
55°	307.6	293.8	280.0	271.0	266.7	262.3	257.9	253.6
57.5°	261.2	248.6	236.0	227.8	224.2	220.6	216.8	213.2
60°	229.2	217.5	205.8	198.1	194.5	190.9	187.1	183.5
62.5°	201.5	190.3	179.2	172.5	170.3	168.1	165.9	163.7
65°	163.8	156.0	148.2	144.0	143.3	142.6	141.9	141.3
67.5°	132.2	128.7	125.1	122.9	122.2	121.5	120.8	120.0
70°	115.0	112.7	110.4	108.9	107.9	106.9	106.0	105.1
72.5°	100.1	98.2	96.2	95.0	94.4	93.9	93.3	92.8
75°	79.3	77.7	76.0	75.1	74.9	74.7	74.4	74.2
77.5°	60.0	59.1	58.2	57.6	57.2	56.9	56.5	56.0
80°	47.7	46.8	45.8	45.3	45.3	45.3	45.3	45.3
82.5°	36.1	35.4	34.9	34.6	34.6	34.6	34.6	34.6
85°	19.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6
87.5°	9.4	9.4	9.4	9.4	9.5	9.6	9.6	9.7
90°	16.1	16.9	17.7	18.2	18.6	18.9	19.2	19.5
92.5°	17.6	18.0	18.4	18.8	18.9	19.1	19.3	19.5
95°	29.8	30.6	31.4	31.7	31.5	31.4	31.2	31.1
97.5°	39.0	39.6	40.3	40.7	40.9	41.1	41.3	41.5
100°	43.7	45.0	46.4	47.2	47.5	47.8	48.1	48.4
102.5°	45.6	47.4	49.0	50.1	50.5	51.0	51.4	51.9
105°	47.6	49.4	51.1	52.3	53.0	53.6	54.2	54.9
107.5°	58.1	56.2	54.5	53.9	54.5	55.2	55.8	56.5
110°	94.3	78.3	62.2	54.5	55.1	55.7	56.5	57.1



TEST NUMBER: P331690-840

CATALOG NUMBER: S122RDIP-S675D725U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	201.8	143.2	84.6	55.5	56.1	56.7	57.2	57.7
115°	297.1	222.8	148.5	105.4	93.9	82.3	70.8	59.3
117.5°	457.8	439.7	421.7	393.7	355.8	317.8	279.8	241.9
120°	533.4	535.3	537.2	527.4	505.6	484.0	462.3	440.7
122.5°	565.9	567.0	568.3	566.7	562.5	558.3	554.1	549.9
125°	612.7	613.8	614.9	615.7	616.2	616.7	617.1	617.6
127.5°	655.9	657.5	659.1	660.0	660.1	660.2	660.4	660.5
130°	683.3	685.1	686.8	687.6	687.5	687.3	687.1	687.0
132.5°	709.9	711.4	713.0	713.7	713.5	713.4	713.2	713.0
135°	748.0	749.6	751.2	751.8	751.5	751.2	750.8	750.5
137.5°	783.4	784.9	786.5	787.0	786.5	785.9	785.4	784.8
140°	806.2	807.6	809.1	809.4	808.6	807.8	807.0	806.2
142.5°	827.3	828.6	829.9	830.2	829.4	828.6	827.8	827.0
145°	856.9	858.0	859.1	859.2	858.5	857.7	856.9	856.1
147.5°	882.5	883.4	884.2	884.3	883.6	882.9	882.3	881.6
150°	898.4	899.4	900.3	900.4	899.6	898.8	898.0	897.2
152.5°	912.8	913.8	914.8	914.7	913.7	912.6	911.6	910.5
155°	932.4	933.3	934.3	934.1	932.8	931.6	930.3	929.0
157.5°	948.8	949.9	951.0	950.9	949.7	948.4	947.2	945.9
160°	958.4	959.4	960.3	960.2	959.1	958.0	956.8	955.7
162.5°	967.2	968.4	969.5	969.4	968.0	966.5	965.2	963.8
165°	978.2	979.4	980.5	980.5	979.4	978.2	977.0	975.9
167.5°	987.3	988.5	989.6	989.4	988.0	986.5	985.0	983.6
170°	991.9	993.0	994.2	994.0	992.6	991.1	989.7	988.3
172.5°	995.4	996.5	997.6	997.4	996.0	994.6	993.1	991.7
175°	999.2	1000.3	1001.4	1001.2	999.6	997.9	996.3	994.7
177.5°	999.6	1000.5	1001.4	1001.3	1000.1	999.0	997.7	996.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4

(END OF REPORT)