

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331734-840

Luminaire Tested: **S122RDIP-S865D1080U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331734-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S865D1080U840-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7296.0 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331734-840

CATALOG NUMBER: S122RDIP-S865D1080U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331734-840

CATALOG NUMBER: S122RDIP-S865D1080U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42																				
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36																				
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	31																				
3	81	71	64	59	73	66	60	55	55	50	46	44	41	39	35	33	31	27																				
4	74	63	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27	23																				
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24	20																				
6	63	51	43	38	57	47	40	35	39	34	30	32	29	26	26	23	21	18																				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	16																				
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17	15																				
9	50	38	31	26	46	35	29	25	30	25	22	25	21	18	20	17	15	13																				
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23909	23909	23909
5°	24000	23608	23738
10°	23815	23222	23023
15°	23542	22534	21884
20°	23163	21551	20469
25°	22775	20436	19099
30°	22236	19287	17339
35°	21711	18039	15794
40°	21182	16750	14010
45°	20562	15299	12392
50°	19926	13835	10803
55°	19277	12262	9278
60°	18519	10601	7702
65°	17662	8909	7014
70°	16636	7336	6449
75°	15384	6687	6014
80°	13575	5979	5486
85°	10689	4705	4705



TEST NUMBER: P331734-840

CATALOG NUMBER: S122RDIP-S865D1080U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.6	1.9
10°-20°	380.6	5.2
20°-30°	534.4	7.3
30°-40°	582.7	8.0
40°-50°	535.8	7.3
50°-60°	420.8	5.8
60°-70°	274.4	3.8
70°-80°	141.5	1.9
80°-90°	42.2	0.6
90°-100°	243.9	3.3
100°-110°	827.7	11.3
110°-120°	879.3	12.1
120°-130°	723.9	9.9
130°-140°	581.3	8.0
140°-150°	439.3	6.0
150°-160°	308.7	4.2
160°-170°	181.7	2.5
170°-180°	59.1	0.8
0°-30°	1053.6	14.4
0°-40°	1636.3	22.4
0°-60°	2593.0	35.5
0°-90°	3051.0	41.8
90°-120°	1951.0	26.7
90°-150°	3695.4	50.7
90°-180°	4245.0	58.2
0°-180°	7296.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1481	1481	1481	1481	1481	
5°	1481	1473	1457	1468	1465	140
15°	1408	1392	1348	1323	1309	397
25°	1278	1233	1147	1094	1072	588
35°	1102	1030	915	834	801	689
45°	900	808	670	578	543	695
55°	685	578	436	358	330	612
65°	462	353	233	190	184	458
75°	247	155	107	98	96	261
85°	58	31	25	25	25	68
90°	1	16	40	38	39	5
95°	41	101	460	174	134	44
105°	143	216	869	1554	1322	152
115°	252	319	727	1501	1740	250
125°	352	416	699	1216	1411	312
135°	413	493	691	1022	1170	319
145°	472	542	687	854	934	296
155°	536	579	668	755	785	247
165°	584	602	639	678	689	165
175°	609	609	615	622	621	58
180°	610	610	610	610	610	



TEST NUMBER: P331734-840

CATALOG NUMBER: S122RDIP-S865D1080U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8
2.5°	1486.1	1484.9	1483.7	1482.5	1481.4	1479.5	1476.8	1474.2	1471.6	1468.9	1471.4
5°	1480.8	1479.3	1477.7	1476.2	1474.8	1472.1	1468.2	1464.4	1460.5	1456.6	1459.3
7.5°	1465.4	1463.6	1461.8	1460.0	1458.0	1454.9	1450.4	1445.8	1441.3	1436.7	1437.5
10°	1452.6	1450.5	1448.4	1446.3	1444.2	1440.3	1434.3	1428.4	1422.4	1416.4	1415.5
12.5°	1436.5	1433.9	1431.4	1428.9	1426.2	1421.2	1413.5	1405.9	1398.3	1390.7	1389.1
15°	1408.4	1405.1	1401.8	1398.6	1395.2	1388.6	1378.5	1368.4	1358.2	1348.1	1342.4
17.5°	1373.8	1368.8	1363.8	1358.8	1353.8	1344.8	1331.8	1318.8	1305.9	1292.8	1286.2
20°	1348.1	1342.1	1336.2	1330.2	1324.2	1313.8	1298.9	1284.0	1269.2	1254.3	1246.8
22.5°	1320.2	1313.5	1306.9	1300.2	1293.5	1281.8	1265.0	1248.2	1231.4	1214.6	1205.0
25°	1278.4	1268.9	1259.3	1249.8	1240.3	1225.7	1206.0	1186.4	1166.7	1147.1	1134.9
27.5°	1228.0	1217.6	1207.3	1196.9	1186.6	1170.3	1148.1	1126.0	1103.8	1081.7	1067.4
30°	1192.7	1181.3	1170.0	1158.7	1147.4	1129.8	1106.0	1082.2	1058.3	1034.5	1019.4
32.5°	1158.3	1145.1	1131.9	1118.6	1105.4	1086.7	1062.4	1038.0	1013.8	989.5	972.2
35°	1101.5	1086.3	1071.2	1055.9	1040.8	1020.1	993.8	967.7	941.5	915.2	896.5
37.5°	1044.7	1028.0	1011.4	994.6	978.0	955.6	927.8	899.8	871.9	843.9	823.2
40°	1005.0	987.1	969.3	951.4	933.5	910.2	881.3	852.4	823.5	794.7	773.5
42.5°	964.3	945.4	926.7	907.9	889.0	864.6	834.9	805.0	775.2	745.3	723.5
45°	900.5	880.5	860.6	840.6	820.7	795.1	763.9	732.6	701.3	670.0	648.8
47.5°	838.3	817.2	796.1	774.9	753.8	727.0	694.8	662.5	630.2	597.9	576.9
50°	793.3	772.1	751.0	729.8	708.7	681.8	649.0	616.2	583.5	550.8	530.2
52.5°	749.3	727.2	705.2	683.1	661.0	633.9	601.9	569.8	537.8	505.7	485.8
55°	684.8	661.6	638.3	615.1	591.9	564.1	532.0	499.8	467.7	435.6	417.7
57.5°	618.5	594.7	570.9	547.0	523.3	495.9	464.9	434.0	403.1	372.2	355.9
60°	573.5	549.7	525.9	502.1	478.3	451.0	420.3	389.6	359.0	328.3	313.2
62.5°	529.6	505.7	481.9	458.1	434.2	407.8	378.5	349.3	320.0	290.7	276.3
65°	462.3	438.2	414.0	389.9	365.9	340.3	313.6	286.8	259.9	233.2	223.1
67.5°	397.5	373.5	349.6	325.6	301.6	277.6	253.6	229.4	205.3	181.2	176.5
70°	352.4	329.2	306.0	282.8	259.5	237.6	217.1	196.5	176.0	155.4	152.5
72.5°	309.5	287.3	265.0	242.8	220.5	201.1	184.6	168.0	151.6	135.1	132.6
75°	246.6	225.7	204.9	184.0	163.2	147.7	137.5	127.4	117.3	107.2	105.1
77.5°	184.7	166.3	148.0	129.8	111.5	100.0	95.0	90.2	85.3	80.4	79.2
80°	146.0	130.9	115.7	100.5	85.3	76.2	73.2	70.3	67.3	64.3	63.1
82.5°	110.7	98.9	86.9	75.1	63.3	56.4	54.3	52.3	50.3	48.3	47.6
85°	57.7	51.4	45.1	38.9	32.6	29.1	28.2	27.3	26.4	25.4	25.4
87.5°	17.4	16.2	15.2	13.7	12.3	12.1	13.2	14.9	16.4	16.6	16.1
90°	1.2	4.6	9.4	11.7	14.0	17.6	23.4	31.7	38.7	39.9	38.7
92.5°	14.3	20.6	29.1	34.2	42.2	53.2	79.8	117.0	150.4	152.5	128.9
95°	41.1	45.7	57.5	68.1	86.8	114.9	169.0	270.9	407.1	459.9	402.4
97.5°	66.9	73.2	85.6	101.6	123.2	155.1	222.9	365.1	591.3	785.1	823.5
100°	90.3	93.8	104.4	123.2	146.6	179.5	241.7	384.8	638.1	926.8	1095.7
102.5°	111.9	114.5	125.0	143.8	168.2	201.1	258.5	385.8	620.4	931.5	1197.1
105°	143.1	147.8	156.0	173.6	199.4	232.3	287.4	391.8	585.4	869.3	1181.3
107.5°	176.9	180.7	188.6	204.8	230.5	263.5	317.0	408.0	568.0	802.6	1078.3
110°	199.4	204.1	211.2	226.4	251.1	285.1	336.7	421.1	564.3	770.7	1013.6



TEST NUMBER: P331734-840

CATALOG NUMBER: S122RDIP-S865D1080U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	220.0	224.8	232.8	247.0	270.7	305.7	355.5	435.3	565.2	750.1	968.6
115°	252.3	258.1	265.1	279.2	302.7	334.4	384.8	456.4	570.2	727.3	912.7
117.5°	285.6	290.2	297.3	309.7	332.2	365.1	411.7	478.9	578.6	716.3	877.5
120°	306.2	310.8	317.9	328.5	351.9	384.8	430.5	493.9	584.2	709.7	858.7
122.5°	325.9	329.6	336.7	348.2	371.6	405.5	448.4	507.1	590.8	706.0	842.7
125°	351.9	355.5	362.5	376.6	400.0	432.9	475.1	528.0	600.7	699.2	820.0
127.5°	372.5	377.3	387.2	402.6	425.2	458.9	500.0	547.3	610.8	695.2	798.9
130°	384.8	389.5	401.2	417.7	441.1	473.9	515.0	559.6	618.2	693.3	784.9
132.5°	396.1	401.7	414.3	431.7	456.2	489.0	528.2	571.8	625.7	692.4	773.6
135°	412.9	417.7	431.7	449.3	476.3	509.2	546.6	587.7	634.7	690.9	757.8
137.5°	428.9	434.5	448.6	467.4	494.1	524.6	561.7	600.0	642.7	690.7	746.8
140°	441.1	445.8	459.9	478.7	504.4	534.9	570.2	606.5	646.4	689.8	740.2
142.5°	453.3	457.1	470.2	489.0	513.8	542.5	576.7	612.2	649.2	689.8	733.7
145°	471.6	476.3	488.1	505.6	529.1	554.9	586.5	619.5	652.3	687.4	725.0
147.5°	491.3	494.8	506.0	522.3	541.8	564.7	594.5	623.4	653.2	683.3	716.1
150°	504.4	508.0	517.4	532.6	550.2	571.3	598.3	625.3	652.3	680.4	708.5
152.5°	517.6	519.3	528.6	542.0	558.7	577.8	602.1	626.2	650.4	675.7	702.0
155°	536.1	537.2	544.3	557.2	570.2	587.7	607.6	627.6	647.5	667.5	689.8
157.5°	551.6	552.8	558.5	569.7	580.0	594.8	611.7	627.6	642.2	659.0	678.3
160°	561.9	563.1	567.7	577.1	586.5	599.5	613.6	627.6	639.3	653.5	669.8
162.5°	572.3	571.6	576.2	583.7	592.2	602.3	614.5	626.7	636.5	648.7	662.4
165°	584.2	583.1	585.4	592.4	598.3	605.3	615.9	624.1	631.2	639.3	649.9
167.5°	594.1	592.7	594.8	599.3	603.5	607.9	615.6	622.5	625.7	631.2	637.7
170°	600.7	598.3	599.5	603.0	605.3	608.8	614.7	620.6	622.9	626.4	631.2
172.5°	604.4	603.0	602.3	605.8	607.2	609.8	613.8	617.7	619.1	620.9	624.6
175°	608.8	607.6	606.5	608.8	608.8	610.1	612.4	614.7	613.6	614.7	615.9
177.5°	611.0	609.0	608.1	610.1	610.1	610.1	611.0	612.9	611.0	610.1	611.0
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1



TEST NUMBER: P331734-840

CATALOG NUMBER: S122RDIP-S865D1080U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8
2.5°	1473.7	1476.1	1478.4	1479.5	1478.9	1478.4	1478.0	1477.5
5°	1462.0	1464.6	1467.3	1468.2	1467.3	1466.4	1465.5	1464.6
7.5°	1438.4	1439.1	1439.9	1439.5	1437.9	1436.4	1434.8	1433.3
10°	1414.6	1413.7	1412.8	1411.5	1409.7	1408.0	1406.1	1404.3
12.5°	1387.5	1385.8	1384.2	1382.0	1379.0	1376.0	1373.0	1370.1
15°	1336.8	1331.1	1325.4	1321.1	1318.2	1315.1	1312.2	1309.2
17.5°	1279.4	1272.6	1266.0	1260.0	1254.9	1249.8	1244.7	1239.5
20°	1239.4	1231.9	1224.5	1217.5	1210.9	1204.4	1197.8	1191.3
22.5°	1195.5	1185.9	1176.3	1169.0	1164.2	1159.2	1154.4	1149.5
25°	1122.7	1110.4	1098.2	1089.8	1085.4	1081.0	1076.5	1072.1
27.5°	1053.2	1038.9	1024.7	1014.1	1007.0	999.9	992.8	985.7
30°	1004.1	989.0	973.7	962.1	954.1	946.0	938.1	930.0
32.5°	954.8	937.5	920.2	907.7	900.2	892.6	885.0	877.5
35°	877.7	859.0	840.2	827.6	821.0	814.5	807.9	801.3
37.5°	802.6	781.9	761.3	747.2	739.7	732.2	724.7	717.2
40°	752.3	731.2	710.0	695.6	687.9	680.1	672.4	664.7
42.5°	701.7	679.7	657.9	643.2	635.7	628.2	620.7	613.2
45°	627.7	606.6	585.4	571.3	564.1	557.0	549.9	542.7
47.5°	555.8	534.8	513.8	500.1	493.6	487.1	480.6	474.1
50°	509.7	489.1	468.6	455.1	448.9	442.6	436.4	430.1
52.5°	466.1	446.3	426.4	413.6	407.8	402.0	396.3	390.5
55°	399.8	381.9	364.1	352.2	346.6	340.9	335.3	329.6
57.5°	339.5	323.2	306.8	296.2	291.4	286.6	281.9	277.1
60°	297.9	282.8	267.5	257.6	252.8	248.0	243.3	238.5
62.5°	261.9	247.4	232.9	224.2	221.4	218.5	215.6	212.8
65°	212.9	202.8	192.7	187.1	186.2	185.4	184.5	183.6
67.5°	171.9	167.2	162.6	159.8	158.9	157.8	156.9	156.0
70°	149.5	146.5	143.5	141.5	140.3	139.1	137.8	136.6
72.5°	130.1	127.5	125.0	123.5	122.7	122.0	121.3	120.6
75°	103.0	101.0	98.9	97.7	97.4	97.0	96.7	96.4
77.5°	78.1	76.9	75.6	74.8	74.3	73.8	73.4	72.9
80°	61.9	60.8	59.6	59.0	59.0	59.0	59.0	59.0
82.5°	46.9	46.0	45.3	45.0	45.0	45.0	45.0	45.0
85°	25.4	25.4	25.4	25.4	25.4	25.4	25.4	25.4
87.5°	15.7	14.9	15.1	15.2	15.2	15.2	15.2	15.2
90°	37.6	35.2	37.6	38.7	38.7	38.7	38.7	38.7
92.5°	102.3	87.8	77.9	70.6	69.7	65.9	66.9	65.0
95°	307.4	235.8	186.5	160.7	145.4	136.1	132.6	133.7
97.5°	717.2	586.8	459.9	375.2	319.1	290.2	273.1	263.3
100°	1071.1	925.6	764.9	622.9	525.5	475.1	441.1	420.0
102.5°	1302.9	1270.0	1152.5	1002.1	896.3	810.2	767.7	739.1
105°	1425.3	1557.9	1573.2	1534.5	1461.7	1389.0	1338.6	1322.1
107.5°	1337.2	1536.8	1658.8	1715.6	1724.7	1720.7	1710.6	1688.8
110°	1261.1	1471.1	1621.2	1717.5	1767.9	1790.2	1800.8	1799.6



TEST NUMBER: P331734-840

CATALOG NUMBER: S122RDIP-S865D1080U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1191.6	1393.2	1553.7	1664.0	1734.1	1771.4	1791.4	1797.7
115°	1106.3	1287.0	1440.6	1561.5	1644.8	1698.7	1729.2	1739.8
117.5°	1042.0	1200.6	1340.0	1453.3	1538.2	1595.2	1627.4	1636.3
120°	1010.1	1155.5	1279.9	1386.6	1468.7	1523.9	1557.9	1569.6
122.5°	984.7	1118.0	1235.8	1332.2	1405.8	1460.1	1490.4	1500.2
125°	947.9	1068.7	1171.9	1259.9	1328.0	1372.6	1401.9	1411.3
127.5°	911.5	1020.9	1118.2	1199.4	1258.8	1300.5	1325.9	1333.4
130°	888.1	989.0	1081.7	1159.0	1216.6	1256.5	1279.9	1289.3
132.5°	865.6	959.0	1044.1	1116.8	1173.4	1213.3	1234.9	1243.2
135°	834.0	911.5	989.0	1054.6	1105.1	1143.8	1164.9	1169.6
137.5°	809.0	873.7	935.2	992.5	1038.4	1071.8	1090.4	1097.3
140°	793.0	849.4	903.3	954.9	992.5	1023.0	1040.6	1047.6
142.5°	779.9	827.8	874.2	917.4	953.0	980.8	996.4	997.8
145°	761.3	800.1	836.5	870.5	898.6	918.6	930.3	933.8
147.5°	747.1	777.6	806.0	830.8	854.0	870.0	878.0	880.1
150°	736.7	762.5	787.2	808.3	825.9	840.0	847.0	848.2
152.5°	726.4	750.3	771.2	789.5	803.3	815.6	820.7	820.9
155°	712.1	730.8	748.4	761.3	774.3	782.4	787.2	784.9
157.5°	695.4	711.1	725.9	736.0	745.2	751.9	754.1	754.1
160°	685.1	698.0	710.9	719.1	727.3	733.2	734.4	734.4
162.5°	674.8	685.8	696.8	703.2	711.3	715.4	716.5	715.6
165°	659.3	667.5	675.7	680.4	685.1	689.8	689.8	688.6
167.5°	644.5	650.9	656.5	660.8	662.8	665.4	665.2	663.8
170°	637.0	640.6	645.2	647.5	648.7	652.3	651.1	648.7
172.5°	628.5	631.2	634.9	636.3	637.5	639.1	637.9	636.5
175°	619.5	620.6	621.8	622.9	622.9	624.1	622.9	620.6
177.5°	612.9	612.9	613.8	613.8	613.8	613.8	612.9	611.0
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1

(END OF REPORT)