

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331705-840

Luminaire Tested: **S122RDIP-S865D330U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331705-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S865D330U840-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4656.2 lumens  
Efficiency: N/A  
Efficacy: 107.0 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331705-840

CATALOG NUMBER: S122RDIP-S865D330U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331705-840

CATALOG NUMBER: S122RDIP-S865D330U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	72
1	104	100	96	93	98	95	92	89	85	83	81	77	75	73	69	68	66	63
2	95	88	83	78	90	84	79	75	76	72	69	69	66	63	62	60	58	54
3	88	79	72	66	83	75	69	64	68	63	59	62	58	55	56	53	51	47
4	81	71	63	57	77	68	61	56	62	56	52	56	52	48	51	48	45	42
5	75	64	56	50	71	61	54	49	56	50	46	51	46	43	47	43	40	37
6	70	58	50	45	66	56	49	43	51	45	41	47	42	38	43	39	36	33
7	65	53	45	40	62	51	44	39	47	41	37	43	38	35	40	36	32	30
8	61	49	41	36	58	47	40	35	43	37	33	40	35	31	37	33	30	28
9	57	45	38	33	54	43	37	32	40	34	30	37	32	29	34	30	27	25
10	53	42	35	30	51	40	34	29	37	32	28	35	30	26	32	28	25	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	31136	31136	31136	31136
5°	34775	31331	27780	31331
10°	38581	31111	24079	31111
15°	40478	30654	18974	30654
20°	35093	29979	16417	29979
25°	23013	29054	14658	29054
30°	15491	27932	13267	27932
35°	12546	26518	11964	26518
40°	11158	24982	11072	24982
45°	10097	23178	9882	23178
50°	9191	21391	9156	21391
55°	8639	19409	8526	19409
60°	7227	17589	7143	17589
65°	6094	15973	6911	15973
70°	5632	14266	6515	14266
75°	5265	12414	6014	12414
80°	4863	10219	5365	10219
85°	4465	8058	4705	8058



TEST NUMBER: P331705-840

CATALOG NUMBER: S122RDIP-S865D330U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.8	3.9
10°-20°	509.4	10.9
20°-30°	656.4	14.1
30°-40°	623.8	13.4
40°-50°	534.4	11.5
50°-60°	406.9	8.7
60°-70°	257.2	5.5
70°-80°	128.5	2.8
80°-90°	34.5	0.7
90°-100°	15.1	0.3
100°-110°	55.2	1.2
110°-120°	147.6	3.2
120°-130°	243.6	5.2
130°-140°	259.0	5.6
140°-150°	240.8	5.2
150°-160°	193.6	4.2
160°-170°	124.7	2.7
170°-180°	42.9	0.9
0°-30°	1348.5	29.0
0°-40°	1972.3	42.4
0°-60°	2913.6	62.6
0°-90°	3333.8	71.6
90°-120°	217.8	4.7
90°-150°	961.2	20.6
90°-180°	1322.0	28.4
0°-180°	4656.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1928	1928	1928	1928	1928	
5°	2146	1933	1714	1933	2146	212
15°	2422	1834	1135	1834	2422	653
25°	1292	1631	823	1631	1292	613
35°	636	1345	607	1345	636	407
45°	442	1015	433	1015	442	342
55°	307	690	303	690	307	269
65°	160	418	181	418	160	162
75°	84	199	96	199	84	90
85°	24	44	25	44	24	26
90°	9	0	9	0	9	5
95°	14	21	14	21	14	13
105°	25	99	25	99	25	26
115°	27	188	27	188	27	67
125°	279	266	279	266	279	242
135°	339	328	339	328	339	261
145°	387	381	387	381	387	242
155°	420	420	420	420	420	194
165°	441	442	441	442	441	125
175°	450	452	450	452	450	43
180°	451	451	451	451	451	



TEST NUMBER: P331705-840

CATALOG NUMBER: S122RDIP-S865D330U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	2006.7	2008.3	2009.9	2006.1	2006.1	2003.0	1996.0	1990.6	1975.6	1973.5	1973.5
5°	2145.6	2144.1	2146.9	2138.2	2126.1	2123.4	2110.7	2094.0	2076.5	2057.1	2053.1
7.5°	2283.5	2281.5	2276.1	2274.7	2265.4	2245.2	2224.7	2202.9	2173.9	2145.7	2131.4
10°	2353.2	2375.3	2362.0	2338.4	2343.2	2311.7	2294.9	2266.1	2242.0	2199.8	2190.4
12.5°	2421.9	2430.5	2426.3	2413.0	2407.0	2385.1	2362.5	2337.4	2292.9	2255.0	2222.0
15°	2421.6	2434.3	2437.6	2433.7	2437.0	2435.7	2423.6	2402.8	2364.0	2322.4	2286.2
17.5°	2242.8	2251.7	2273.6	2288.5	2307.2	2346.9	2366.5	2374.1	2368.3	2344.6	2319.2
20°	2042.4	2027.6	2089.2	2120.7	2147.5	2214.5	2272.2	2294.3	2329.8	2329.2	2322.4
22.5°	1758.2	1761.7	1820.2	1857.5	1935.8	2002.8	2068.5	2151.7	2220.4	2265.8	2292.4
25°	1291.8	1317.4	1375.6	1426.5	1513.7	1638.3	1751.5	1882.9	2006.8	2104.7	2197.8
27.5°	970.3	972.1	1018.3	1065.4	1117.1	1219.2	1361.8	1518.6	1695.4	1841.2	2008.9
30°	830.9	826.9	846.3	875.0	919.3	998.4	1105.6	1259.7	1435.9	1655.7	1851.4
32.5°	732.3	732.5	747.1	768.4	805.2	858.5	931.9	1057.1	1223.7	1439.7	1669.1
35°	636.5	635.9	646.6	662.0	677.4	711.6	761.8	827.5	942.1	1143.8	1378.3
37.5°	567.9	570.9	576.1	585.7	602.8	621.8	652.0	696.1	777.7	897.0	1094.1
40°	529.4	530.7	538.1	546.1	556.1	570.9	595.7	631.2	690.8	786.0	930.0
42.5°	493.9	495.3	500.5	508.1	515.9	530.7	551.2	581.9	630.3	704.5	823.3
45°	442.2	442.2	447.0	450.3	459.0	472.4	489.2	514.6	548.1	603.1	682.2
47.5°	393.7	393.8	397.0	402.7	408.2	418.7	435.2	456.0	480.3	522.8	590.4
50°	365.9	366.5	368.5	373.2	376.6	386.0	398.7	416.8	442.2	475.0	531.4
52.5°	343.4	343.0	345.5	347.5	349.8	356.5	366.0	381.9	404.8	433.2	479.9
55°	306.9	304.2	308.2	311.5	313.6	316.3	321.6	331.6	351.1	375.3	410.1
57.5°	261.4	260.2	263.1	266.1	272.5	279.6	284.3	290.6	300.7	318.0	352.5
60°	223.8	223.8	229.8	231.9	239.2	248.6	258.0	263.4	273.4	284.8	310.2
62.5°	190.6	191.1	193.9	195.9	200.1	211.6	224.7	236.5	246.0	256.9	273.8
65°	159.5	160.8	160.8	162.2	164.8	167.5	172.9	182.3	199.0	214.4	227.1
67.5°	135.3	135.7	136.1	137.5	138.1	141.1	143.3	147.4	151.3	165.9	181.7
70°	119.3	121.3	120.6	122.0	122.6	123.9	126.6	128.7	134.7	138.0	147.4
72.5°	104.2	105.7	105.6	106.4	108.2	108.5	110.6	112.6	116.4	119.3	124.3
75°	84.4	83.7	84.4	85.7	86.4	87.2	87.2	89.8	91.8	94.5	97.9
77.5°	65.1	65.8	65.6	65.8	65.9	67.2	67.1	68.2	70.2	71.6	73.2
80°	52.3	52.9	52.3	52.9	53.6	54.2	53.6	54.2	56.2	57.7	57.7
82.5°	40.5	40.6	41.0	41.1	41.3	41.4	42.3	42.5	43.9	43.7	44.2
85°	24.1	23.4	23.4	23.4	24.1	24.7	24.1	24.1	24.7	24.7	24.7
87.5°	10.3	10.8	10.8	10.8	10.8	10.7	10.6	11.1	10.5	10.9	10.3
90°	8.8	8.7	8.5	8.4	8.3	8.0	7.6	7.3	6.9	6.6	6.0
92.5°	8.8	8.7	8.7	8.6	8.5	8.3	8.2	8.0	7.8	7.6	7.3
95°	14.0	14.1	14.1	14.2	14.3	14.1	13.8	13.4	13.1	12.7	12.2
97.5°	18.8	18.7	18.6	18.5	18.4	18.2	17.9	17.7	17.4	17.1	15.9
100°	21.9	21.7	21.6	21.4	21.3	20.9	20.4	19.8	19.2	18.6	17.4
102.5°	23.4	23.2	23.0	22.8	22.6	22.1	21.4	20.6	19.9	19.1	29.5
105°	24.8	24.5	24.2	23.9	23.6	23.1	22.3	21.5	20.7	19.9	39.7
107.5°	25.5	25.2	24.9	24.6	24.3	24.6	25.4	26.3	27.1	27.9	51.6
110°	25.8	25.5	25.2	24.9	24.6	28.1	35.3	42.6	49.9	57.2	78.1



TEST NUMBER: P331705-840

CATALOG NUMBER: S122RDIP-S865D330U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	26.1	25.9	25.5	25.3	25.1	38.3	64.7	91.2	117.6	144.1	149.3
115°	26.8	32.0	37.3	42.4	47.7	67.1	100.7	134.3	167.8	201.5	199.7
117.5°	109.4	126.5	143.7	160.9	178.0	190.7	198.7	206.9	215.0	223.2	221.9
120°	199.1	208.9	218.7	228.5	238.3	242.8	242.0	241.1	240.2	239.3	238.0
122.5°	248.5	250.4	252.4	254.3	256.1	256.8	256.3	255.8	255.3	254.8	253.4
125°	279.1	278.9	278.7	278.5	278.3	277.9	277.4	276.9	276.4	275.9	274.5
127.5°	298.5	298.4	298.4	298.4	298.3	297.9	297.2	296.5	295.7	295.0	294.0
130°	310.5	310.6	310.6	310.7	310.8	310.4	309.6	308.8	308.0	307.3	306.5
132.5°	322.2	322.3	322.4	322.4	322.6	322.2	321.5	320.9	320.2	319.5	318.7
135°	339.2	339.4	339.5	339.7	339.8	339.5	338.8	338.1	337.4	336.7	336.0
137.5°	354.8	355.0	355.3	355.5	355.7	355.5	354.8	354.1	353.4	352.6	351.9
140°	364.4	364.8	365.2	365.5	365.9	365.7	365.1	364.4	363.8	363.0	362.3
142.5°	373.8	374.2	374.6	374.9	375.3	375.2	374.6	374.0	373.3	372.7	371.8
145°	386.9	387.3	387.7	388.0	388.4	388.3	387.8	387.3	386.8	386.3	385.1
147.5°	398.5	398.8	399.1	399.4	399.7	399.7	399.3	398.9	398.5	398.2	397.0
150°	405.6	405.9	406.3	406.7	407.0	407.0	406.5	406.1	405.7	405.3	404.0
152.5°	411.5	412.0	412.5	412.9	413.4	413.4	413.0	412.6	412.1	411.7	410.6
155°	419.9	420.5	421.1	421.6	422.2	422.3	421.8	421.4	421.0	420.5	419.7
157.5°	427.6	428.1	428.7	429.2	429.8	429.8	429.4	428.9	428.4	427.9	427.3
160°	432.0	432.5	433.0	433.5	434.0	434.0	433.6	433.2	432.7	432.3	431.9
162.5°	435.7	436.3	436.9	437.5	438.2	438.2	437.7	437.2	436.8	436.3	435.9
165°	441.1	441.6	442.1	442.6	443.1	443.1	442.6	442.1	441.6	441.1	440.9
167.5°	444.5	445.2	445.9	446.6	447.2	447.3	446.8	446.3	445.8	445.2	445.0
170°	446.7	447.4	448.0	448.7	449.3	449.4	448.9	448.4	447.9	447.4	447.2
172.5°	448.3	448.9	449.6	450.2	450.9	450.9	450.4	449.9	449.4	448.9	448.8
175°	449.6	450.3	451.1	451.8	452.5	452.6	452.1	451.6	451.1	450.6	450.5
177.5°	450.5	451.0	451.5	452.0	452.5	452.6	452.2	451.8	451.4	451.0	450.9
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331705-840

CATALOG NUMBER: S122RDIP-S865D330U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1974.5	1970.2	1966.5	1956.8	1952.0	1941.3	1939.6	1939.1	1925.2	1911.8	1908.0
5°	2042.4	2031.6	2015.5	1996.8	1977.3	1957.2	1943.8	1933.1	1906.3	1880.9	1866.1
7.5°	2110.7	2087.6	2059.9	2024.4	1994.8	1961.6	1936.8	1914.7	1876.7	1840.3	1815.7
10°	2161.6	2124.0	2087.2	2038.3	2000.1	1962.6	1927.7	1897.6	1854.7	1806.4	1772.3
12.5°	2193.2	2151.9	2101.1	2053.4	2003.9	1956.1	1909.6	1870.8	1820.4	1770.6	1729.9
15°	2235.9	2191.7	2130.1	2061.7	1998.1	1935.8	1882.2	1833.9	1768.3	1708.6	1659.0
17.5°	2271.0	2210.1	2143.9	2064.9	1991.2	1912.0	1842.9	1781.3	1708.2	1636.3	1577.8
20°	2282.2	2221.9	2145.6	2066.5	1979.3	1886.2	1811.8	1744.8	1666.4	1588.0	1521.1
22.5°	2275.2	2228.4	2143.3	2048.7	1959.5	1862.1	1778.1	1700.3	1613.4	1533.4	1455.6
25°	2228.0	2211.8	2131.4	2028.2	1926.4	1813.2	1716.0	1630.9	1531.8	1446.0	1361.5
27.5°	2117.7	2152.3	2102.5	1992.6	1879.4	1758.0	1648.7	1551.9	1449.0	1352.4	1268.3
30°	2011.6	2091.2	2069.8	1967.9	1841.3	1722.0	1599.4	1498.2	1388.4	1289.2	1206.1
32.5°	1866.2	1997.9	2018.9	1933.7	1802.7	1671.6	1543.2	1442.5	1327.8	1223.2	1142.3
35°	1635.0	1831.9	1922.4	1868.1	1736.8	1595.4	1462.7	1345.4	1230.2	1127.0	1046.6
37.5°	1359.0	1627.3	1778.1	1781.9	1661.3	1514.3	1369.9	1253.4	1135.5	1034.2	947.2
40°	1179.9	1470.8	1667.1	1710.6	1608.8	1450.0	1303.9	1185.3	1070.1	970.9	871.1
42.5°	1019.2	1308.9	1550.2	1626.0	1545.0	1387.3	1240.7	1116.7	1004.7	910.9	808.9
45°	824.2	1077.4	1343.4	1478.8	1433.9	1287.9	1133.1	1015.1	909.9	828.9	731.0
47.5°	695.3	873.7	1131.1	1314.2	1313.4	1180.1	1027.8	914.9	817.3	741.3	662.2
50°	621.8	777.3	995.0	1202.7	1220.1	1108.2	963.5	851.6	760.5	680.8	617.1
52.5°	555.8	684.0	879.8	1078.9	1128.5	1031.6	891.2	787.9	699.4	626.1	571.6
55°	469.7	568.9	717.6	903.9	979.0	910.6	786.0	689.5	617.8	556.1	509.3
57.5°	397.4	471.7	591.1	741.0	828.5	785.5	682.7	604.3	542.9	487.2	450.1
60°	351.7	412.7	513.9	639.2	735.7	705.6	617.8	544.7	492.5	444.2	409.4
62.5°	308.9	361.3	448.0	549.7	638.1	625.7	554.0	492.7	447.0	402.9	373.4
65°	248.6	286.8	354.5	434.2	505.2	511.3	459.7	418.1	377.3	342.4	316.3
67.5°	197.9	222.9	270.5	337.7	390.9	409.9	378.4	346.7	314.3	287.3	264.7
70°	166.8	186.9	221.8	276.1	325.0	345.1	327.0	302.2	274.1	252.0	232.5
72.5°	135.2	154.8	180.5	220.4	262.3	284.0	277.7	259.8	237.0	218.7	200.4
75°	101.9	107.9	125.3	152.1	184.9	203.7	208.4	199.0	180.9	166.8	156.1
77.5°	75.3	79.0	87.3	101.3	122.8	139.5	146.3	145.2	132.8	124.6	114.6
80°	60.3	62.3	66.3	72.4	88.5	105.2	109.9	109.9	101.2	97.9	87.8
82.5°	45.8	47.3	49.7	53.0	60.6	75.1	80.4	81.5	75.9	71.6	63.6
85°	26.2	25.4	26.8	28.8	30.2	34.1	42.2	43.5	42.2	36.9	34.8
87.5°	10.2	10.6	10.5	9.8	10.2	10.6	13.1	15.7	13.6	12.2	11.3
90°	5.4	4.7	4.2	3.5	2.7	1.9	1.1	0.3	1.1	1.9	2.7
92.5°	7.0	6.7	6.5	6.3	6.4	6.5	6.6	6.6	6.6	6.5	6.4
95°	11.7	11.2	10.7	11.6	14.0	16.5	18.8	21.2	18.8	16.5	14.0
97.5°	14.6	13.5	12.3	15.1	21.9	28.6	35.3	42.1	35.3	28.6	21.9
100°	16.2	14.9	13.6	18.1	28.0	37.9	47.9	57.8	47.9	37.9	28.0
102.5°	39.8	50.1	60.4	66.7	68.8	70.8	72.9	75.0	72.9	70.8	68.8
105°	59.6	79.4	99.2	108.0	105.8	103.6	101.4	99.3	101.4	103.6	105.8
107.5°	75.4	99.2	122.9	133.9	132.2	130.4	128.7	126.8	128.7	130.4	132.2
110°	99.1	120.1	141.0	150.8	149.3	147.7	146.1	144.6	146.1	147.7	149.3





TEST NUMBER: P331705-840

CATALOG NUMBER: S122RDIP-S865D330U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	154.5	159.7	164.8	166.7	165.4	164.1	162.7	161.4	162.7	164.1	165.4
115°	197.8	196.0	194.2	192.7	191.5	190.3	188.9	187.7	188.9	190.3	191.5
117.5°	220.7	219.4	218.1	216.8	215.5	214.1	212.7	211.4	212.7	214.1	215.5
120°	236.7	235.4	234.1	232.9	231.9	230.8	229.6	228.5	229.6	230.8	231.9
122.5°	251.9	250.4	249.0	247.8	246.6	245.5	244.4	243.2	244.4	245.5	246.6
125°	273.2	271.8	270.4	269.2	268.3	267.3	266.4	265.5	266.4	267.3	268.3
127.5°	293.0	291.9	290.8	289.8	288.8	287.7	286.7	285.6	286.7	287.7	288.8
130°	305.7	304.9	304.1	303.1	301.9	300.7	299.6	298.4	299.6	300.7	301.9
132.5°	317.9	317.1	316.3	315.5	314.5	313.5	312.5	311.5	312.5	313.5	314.5
135°	335.4	334.7	334.1	333.2	331.9	330.8	329.6	328.5	329.6	330.8	331.9
137.5°	351.1	350.4	349.7	348.9	348.1	347.3	346.5	345.7	346.5	347.3	348.1
140°	361.5	360.7	359.9	359.2	358.6	358.0	357.5	356.9	357.5	358.0	358.6
142.5°	370.9	370.0	369.1	368.4	367.9	367.3	366.8	366.3	366.8	367.3	367.9
145°	383.8	382.5	381.3	380.7	380.8	380.9	381.0	381.0	381.0	380.9	380.8
147.5°	395.8	394.5	393.2	392.8	393.0	393.3	393.6	393.9	393.6	393.3	393.0
150°	402.9	401.7	400.6	400.2	400.7	401.2	401.7	402.2	401.7	401.2	400.7
152.5°	409.5	408.4	407.3	407.1	407.6	408.2	408.8	409.3	408.8	408.2	407.6
155°	418.8	418.0	417.1	417.0	417.6	418.3	418.9	419.6	418.9	418.3	417.6
157.5°	426.7	426.1	425.5	425.4	426.0	426.5	427.1	427.6	427.1	426.5	426.0
160°	431.4	431.0	430.6	430.6	431.0	431.4	431.9	432.3	431.9	431.4	431.0
162.5°	435.5	435.0	434.7	434.7	435.2	435.7	436.1	436.5	436.1	435.7	435.2
165°	440.7	440.5	440.3	440.4	440.8	441.2	441.7	442.1	441.7	441.2	440.8
167.5°	444.8	444.6	444.4	444.5	444.9	445.5	445.9	446.3	445.9	445.5	444.9
170°	447.1	446.9	446.8	446.9	447.4	447.8	448.2	448.7	448.2	447.8	447.4
172.5°	448.6	448.5	448.3	448.5	448.9	449.3	449.8	450.2	449.8	449.3	448.9
175°	450.3	450.2	450.0	450.2	450.7	451.2	451.7	452.2	451.7	451.2	450.7
177.5°	450.9	450.8	450.8	450.9	451.3	451.7	452.1	452.5	452.1	451.7	451.3
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331705-840

CATALOG NUMBER: S122RDIP-S865D330U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1901.1	1897.3	1890.4	1879.7	1873.2	1862.0	1854.4	1858.8	1859.8	1858.8	1857.6
5°	1850.0	1835.9	1816.5	1797.8	1780.3	1761.6	1750.8	1746.2	1736.8	1731.4	1728.8
7.5°	1788.3	1764.0	1736.5	1703.8	1676.1	1647.0	1632.1	1624.8	1605.6	1595.1	1586.0
10°	1742.1	1703.9	1676.5	1633.6	1607.5	1569.2	1543.2	1543.8	1517.6	1502.9	1492.2
12.5°	1691.2	1649.3	1603.6	1565.0	1528.6	1497.9	1466.5	1453.7	1426.0	1411.8	1382.8
15°	1606.8	1557.9	1509.6	1457.3	1420.5	1372.9	1327.4	1271.7	1226.9	1188.0	1177.3
17.5°	1514.6	1454.0	1405.6	1344.2	1281.1	1201.1	1148.3	1116.0	1088.9	1068.4	1053.2
20°	1451.4	1389.7	1338.1	1245.7	1160.5	1106.3	1067.4	1042.6	1014.5	992.4	980.3
22.5°	1384.8	1320.5	1250.2	1147.0	1080.7	1037.1	1002.5	974.0	954.9	937.7	926.7
25°	1290.5	1220.1	1104.3	1033.2	979.6	934.0	909.9	892.5	872.4	849.0	838.2
27.5°	1190.8	1078.9	995.7	942.9	891.7	862.1	840.4	814.4	796.4	785.9	774.7
30°	1116.3	1004.4	939.4	881.8	845.6	812.7	787.3	772.5	755.2	737.1	729.7
32.5°	1033.2	943.8	881.5	833.5	796.8	768.8	748.7	724.9	712.3	701.1	685.7
35°	930.0	862.3	805.4	766.6	731.7	708.9	685.5	671.4	648.6	639.2	633.2
37.5°	842.6	784.0	741.4	700.4	672.9	647.6	633.3	611.0	601.1	588.0	575.3
40°	793.3	735.7	694.9	661.4	630.6	611.8	593.7	575.6	560.9	554.8	539.4
42.5°	743.0	696.1	655.2	618.4	597.8	577.9	555.1	541.8	526.5	516.7	507.3
45°	673.4	631.9	597.0	566.8	544.1	523.3	508.6	486.5	477.8	458.3	450.3
47.5°	612.3	573.7	540.5	511.8	489.6	476.1	454.4	437.2	423.2	411.3	400.9
50°	568.9	536.7	504.5	479.1	459.0	439.6	417.5	408.7	387.3	381.2	375.3
52.5°	529.2	498.7	469.2	444.2	424.1	405.3	385.8	374.5	359.9	354.0	349.5
55°	473.7	444.2	416.1	393.9	373.9	354.5	342.4	328.3	321.6	316.9	311.5
57.5°	418.0	391.4	369.9	347.5	327.3	311.8	297.9	289.4	282.5	276.3	269.9
60°	382.6	357.1	337.7	316.9	296.2	283.5	272.7	262.7	254.6	245.2	242.6
62.5°	345.1	322.9	305.0	284.8	266.7	255.0	244.8	235.3	225.7	212.0	208.2
65°	293.5	276.1	257.3	240.5	224.5	213.1	198.3	187.6	183.6	182.3	181.6
67.5°	246.8	230.4	214.3	197.1	182.5	172.0	164.4	162.8	160.0	159.2	157.3
70°	215.7	200.4	184.3	168.1	154.1	152.1	149.5	146.7	143.4	142.1	140.7
72.5°	187.8	172.0	155.8	143.0	136.9	134.4	131.7	129.1	126.7	125.4	124.6
75°	144.1	129.4	118.6	113.9	110.6	108.6	104.5	102.5	101.2	99.2	98.5
77.5°	103.7	95.4	90.5	87.6	84.0	81.9	79.6	77.6	76.1	75.7	74.6
80°	79.1	75.0	71.7	67.7	66.3	63.6	63.0	61.0	61.6	59.7	59.7
82.5°	61.4	56.2	53.4	51.6	50.3	48.1	47.5	46.5	46.7	45.1	45.1
85°	31.5	30.2	28.8	27.5	27.5	25.4	26.2	25.4	25.4	24.1	23.4
87.5°	10.9	10.5	9.5	9.7	9.8	9.4	9.4	9.0	9.0	9.1	8.6
90°	3.5	4.2	4.7	5.4	6.0	6.6	6.9	7.3	7.6	8.0	8.3
92.5°	6.3	6.5	6.7	7.0	7.3	7.6	7.8	8.0	8.2	8.3	8.5
95°	11.6	10.7	11.2	11.7	12.2	12.7	13.1	13.4	13.8	14.1	14.3
97.5°	15.1	12.3	13.5	14.6	15.9	17.1	17.4	17.7	17.9	18.2	18.4
100°	18.1	13.6	14.9	16.2	17.4	18.6	19.2	19.8	20.4	20.9	21.3
102.5°	66.7	60.4	50.1	39.8	29.5	19.1	19.9	20.6	21.4	22.1	22.6
105°	108.0	99.2	79.4	59.6	39.7	19.9	20.7	21.5	22.3	23.1	23.6
107.5°	133.9	122.9	99.2	75.4	51.6	27.9	27.1	26.3	25.4	24.6	24.3
110°	150.8	141.0	120.1	99.1	78.1	57.2	49.9	42.6	35.3	28.1	24.6



TEST NUMBER: P331705-840

CATALOG NUMBER: S122RDIP-S865D330U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	166.7	164.8	159.7	154.5	149.3	144.1	117.6	91.2	64.7	38.3	25.1
115°	192.7	194.2	196.0	197.8	199.7	201.5	167.8	134.3	100.7	67.1	47.7
117.5°	216.8	218.1	219.4	220.7	221.9	223.2	215.0	206.9	198.7	190.7	178.0
120°	232.9	234.1	235.4	236.7	238.0	239.3	240.2	241.1	242.0	242.8	238.3
122.5°	247.8	249.0	250.4	251.9	253.4	254.8	255.3	255.8	256.3	256.8	256.1
125°	269.2	270.4	271.8	273.2	274.5	275.9	276.4	276.9	277.4	277.9	278.3
127.5°	289.8	290.8	291.9	293.0	294.0	295.0	295.7	296.5	297.2	297.9	298.3
130°	303.1	304.1	304.9	305.7	306.5	307.3	308.0	308.8	309.6	310.4	310.8
132.5°	315.5	316.3	317.1	317.9	318.7	319.5	320.2	320.9	321.5	322.2	322.6
135°	333.2	334.1	334.7	335.4	336.0	336.7	337.4	338.1	338.8	339.5	339.8
137.5°	348.9	349.7	350.4	351.1	351.9	352.6	353.4	354.1	354.8	355.5	355.7
140°	359.2	359.9	360.7	361.5	362.3	363.0	363.8	364.4	365.1	365.7	365.9
142.5°	368.4	369.1	370.0	370.9	371.8	372.7	373.3	374.0	374.6	375.2	375.3
145°	380.7	381.3	382.5	383.8	385.1	386.3	386.8	387.3	387.8	388.3	388.4
147.5°	392.8	393.2	394.5	395.8	397.0	398.2	398.5	398.9	399.3	399.7	399.7
150°	400.2	400.6	401.7	402.9	404.0	405.3	405.7	406.1	406.5	407.0	407.0
152.5°	407.1	407.3	408.4	409.5	410.6	411.7	412.1	412.6	413.0	413.4	413.4
155°	417.0	417.1	418.0	418.8	419.7	420.5	421.0	421.4	421.8	422.3	422.2
157.5°	425.4	425.5	426.1	426.7	427.3	427.9	428.4	428.9	429.4	429.8	429.8
160°	430.6	430.6	431.0	431.4	431.9	432.3	432.7	433.2	433.6	434.0	434.0
162.5°	434.7	434.7	435.0	435.5	435.9	436.3	436.8	437.2	437.7	438.2	438.2
165°	440.4	440.3	440.5	440.7	440.9	441.1	441.6	442.1	442.6	443.1	443.1
167.5°	444.5	444.4	444.6	444.8	445.0	445.2	445.8	446.3	446.8	447.3	447.2
170°	446.9	446.8	446.9	447.1	447.2	447.4	447.9	448.4	448.9	449.4	449.3
172.5°	448.5	448.3	448.5	448.6	448.8	448.9	449.4	449.9	450.4	450.9	450.9
175°	450.2	450.0	450.2	450.3	450.5	450.6	451.1	451.6	452.1	452.6	452.5
177.5°	450.9	450.8	450.8	450.9	450.9	451.0	451.4	451.8	452.2	452.6	452.5
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331705-840

CATALOG NUMBER: S122RDIP-S865D330U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1851.8	1852.8	1851.2	1852.3	1851.2	1852.8	1851.8	1857.6	1858.8	1859.8	1858.8
5°	1725.4	1717.4	1716.0	1714.0	1716.0	1717.4	1725.4	1728.8	1731.4	1736.8	1746.2
7.5°	1574.5	1573.3	1569.9	1565.3	1569.9	1573.3	1574.5	1586.0	1595.1	1605.6	1624.8
10°	1477.4	1474.1	1473.5	1468.7	1473.5	1474.1	1477.4	1492.2	1502.9	1517.6	1543.8
12.5°	1363.8	1342.2	1340.0	1328.3	1340.0	1342.2	1363.8	1382.8	1411.8	1426.0	1453.7
15°	1161.2	1157.2	1143.8	1135.1	1143.8	1157.2	1161.2	1177.3	1188.0	1226.9	1271.7
17.5°	1045.4	1032.3	1028.1	1026.2	1028.1	1032.3	1045.4	1053.2	1068.4	1088.9	1116.0
20°	970.9	958.9	956.8	955.5	956.8	958.9	970.9	980.3	992.4	1014.5	1042.6
22.5°	919.5	906.9	901.6	897.6	901.6	906.9	919.5	926.7	937.7	954.9	974.0
25°	831.5	826.9	824.2	822.8	824.2	826.9	831.5	838.2	849.0	872.4	892.5
27.5°	762.8	752.5	750.4	747.0	750.4	752.5	762.8	774.7	785.9	796.4	814.4
30°	723.7	720.3	715.6	711.6	715.6	720.3	723.7	729.7	737.1	755.2	772.5
32.5°	677.5	674.8	670.6	668.7	670.6	674.8	677.5	685.7	701.1	712.3	724.9
35°	626.5	617.1	613.1	607.0	613.1	617.1	626.5	633.2	639.2	648.6	671.4
37.5°	572.5	567.5	561.9	563.9	561.9	567.5	572.5	575.3	588.0	601.1	611.0
40°	530.7	527.4	526.0	525.3	526.0	527.4	530.7	539.4	554.8	560.9	575.6
42.5°	497.5	488.2	484.7	484.5	484.7	488.2	497.5	507.3	516.7	526.5	541.8
45°	447.0	438.2	432.2	432.8	432.2	438.2	447.0	450.3	458.3	477.8	486.5
47.5°	395.2	395.0	391.2	392.4	391.2	395.0	395.2	400.9	411.3	423.2	437.2
50°	370.5	366.5	363.9	364.5	363.9	366.5	370.5	375.3	381.2	387.3	408.7
52.5°	347.0	343.5	341.3	344.2	341.3	343.5	347.0	349.5	354.0	359.9	374.5
55°	308.2	304.2	303.6	302.9	303.6	304.2	308.2	311.5	316.9	321.6	328.3
57.5°	265.0	262.3	258.2	256.5	258.2	262.3	265.0	269.9	276.3	282.5	289.4
60°	233.9	228.5	221.8	221.2	221.8	228.5	233.9	242.6	245.2	254.6	262.7
62.5°	205.4	204.4	203.0	202.9	203.0	204.4	205.4	208.2	212.0	225.7	235.3
65°	180.3	179.6	180.3	180.9	180.3	179.6	180.3	181.6	182.3	183.6	187.6
67.5°	157.0	155.8	154.6	155.2	154.6	155.8	157.0	157.3	159.2	160.0	162.8
70°	139.4	138.7	138.0	138.0	138.0	138.7	139.4	140.7	142.1	143.4	146.7
72.5°	122.2	122.1	121.4	120.9	121.4	122.1	122.2	124.6	125.4	126.7	129.1
75°	97.9	96.4	96.4	96.4	96.4	96.4	97.9	98.5	99.2	101.2	102.5
77.5°	74.5	73.8	73.2	72.6	73.2	73.8	74.5	74.6	75.7	76.1	77.6
80°	59.0	58.3	57.7	57.7	57.7	58.3	59.0	59.7	59.7	61.6	61.0
82.5°	45.0	44.3	44.2	43.7	44.2	44.3	45.0	45.1	45.1	46.7	46.5
85°	24.1	24.7	24.1	25.4	24.1	24.7	24.1	23.4	24.1	25.4	25.4
87.5°	8.7	8.2	8.7	8.2	8.7	8.2	8.7	8.6	9.1	9.0	9.0
90°	8.4	8.5	8.7	8.8	8.7	8.5	8.4	8.3	8.0	7.6	7.3
92.5°	8.6	8.7	8.7	8.8	8.7	8.7	8.6	8.5	8.3	8.2	8.0
95°	14.2	14.1	14.1	14.0	14.1	14.1	14.2	14.3	14.1	13.8	13.4
97.5°	18.5	18.6	18.7	18.8	18.7	18.6	18.5	18.4	18.2	17.9	17.7
100°	21.4	21.6	21.7	21.9	21.7	21.6	21.4	21.3	20.9	20.4	19.8
102.5°	22.8	23.0	23.2	23.4	23.2	23.0	22.8	22.6	22.1	21.4	20.6
105°	23.9	24.2	24.5	24.8	24.5	24.2	23.9	23.6	23.1	22.3	21.5
107.5°	24.6	24.9	25.2	25.5	25.2	24.9	24.6	24.3	24.6	25.4	26.3
110°	24.9	25.2	25.5	25.8	25.5	25.2	24.9	24.6	28.1	35.3	42.6



TEST NUMBER: P331705-840

CATALOG NUMBER: S122RDIP-S865D330U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	25.3	25.5	25.9	26.1	25.9	25.5	25.3	25.1	38.3	64.7	91.2
115°	42.4	37.3	32.0	26.8	32.0	37.3	42.4	47.7	67.1	100.7	134.3
117.5°	160.9	143.7	126.5	109.4	126.5	143.7	160.9	178.0	190.7	198.7	206.9
120°	228.5	218.7	208.9	199.1	208.9	218.7	228.5	238.3	242.8	242.0	241.1
122.5°	254.3	252.4	250.4	248.5	250.4	252.4	254.3	256.1	256.8	256.3	255.8
125°	278.5	278.7	278.9	279.1	278.9	278.7	278.5	278.3	277.9	277.4	276.9
127.5°	298.4	298.4	298.4	298.5	298.4	298.4	298.4	298.3	297.9	297.2	296.5
130°	310.7	310.6	310.6	310.5	310.6	310.6	310.7	310.8	310.4	309.6	308.8
132.5°	322.4	322.4	322.3	322.2	322.3	322.4	322.4	322.6	322.2	321.5	320.9
135°	339.7	339.5	339.4	339.2	339.4	339.5	339.7	339.8	339.5	338.8	338.1
137.5°	355.5	355.3	355.0	354.8	355.0	355.3	355.5	355.7	355.5	354.8	354.1
140°	365.5	365.2	364.8	364.4	364.8	365.2	365.5	365.9	365.7	365.1	364.4
142.5°	374.9	374.6	374.2	373.8	374.2	374.6	374.9	375.3	375.2	374.6	374.0
145°	388.0	387.7	387.3	386.9	387.3	387.7	388.0	388.4	388.3	387.8	387.3
147.5°	399.4	399.1	398.8	398.5	398.8	399.1	399.4	399.7	399.7	399.3	398.9
150°	406.7	406.3	405.9	405.6	405.9	406.3	406.7	407.0	407.0	406.5	406.1
152.5°	412.9	412.5	412.0	411.5	412.0	412.5	412.9	413.4	413.4	413.0	412.6
155°	421.6	421.1	420.5	419.9	420.5	421.1	421.6	422.2	422.3	421.8	421.4
157.5°	429.2	428.7	428.1	427.6	428.1	428.7	429.2	429.8	429.8	429.4	428.9
160°	433.5	433.0	432.5	432.0	432.5	433.0	433.5	434.0	434.0	433.6	433.2
162.5°	437.5	436.9	436.3	435.7	436.3	436.9	437.5	438.2	438.2	437.7	437.2
165°	442.6	442.1	441.6	441.1	441.6	442.1	442.6	443.1	443.1	442.6	442.1
167.5°	446.6	445.9	445.2	444.5	445.2	445.9	446.6	447.2	447.3	446.8	446.3
170°	448.7	448.0	447.4	446.7	447.4	448.0	448.7	449.3	449.4	448.9	448.4
172.5°	450.2	449.6	448.9	448.3	448.9	449.6	450.2	450.9	450.9	450.4	449.9
175°	451.8	451.1	450.3	449.6	450.3	451.1	451.8	452.5	452.6	452.1	451.6
177.5°	452.0	451.5	451.0	450.5	451.0	451.5	452.0	452.5	452.6	452.2	451.8
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331705-840

CATALOG NUMBER: S122RDIP-S865D330U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1854.4	1862.0	1873.2	1879.7	1890.4	1897.3	1901.1	1908.0	1911.8	1925.2	1939.1
5°	1750.8	1761.6	1780.3	1797.8	1816.5	1835.9	1850.0	1866.1	1880.9	1906.3	1933.1
7.5°	1632.1	1647.0	1676.1	1703.8	1736.5	1764.0	1788.3	1815.7	1840.3	1876.7	1914.7
10°	1543.2	1569.2	1607.5	1633.6	1676.5	1703.9	1742.1	1772.3	1806.4	1854.7	1897.6
12.5°	1466.5	1497.9	1528.6	1565.0	1603.6	1649.3	1691.2	1729.9	1770.6	1820.4	1870.8
15°	1327.4	1372.9	1420.5	1457.3	1509.6	1557.9	1606.8	1659.0	1708.6	1768.3	1833.9
17.5°	1148.3	1201.1	1281.1	1344.2	1405.6	1454.0	1514.6	1577.8	1636.3	1708.2	1781.3
20°	1067.4	1106.3	1160.5	1245.7	1338.1	1389.7	1451.4	1521.1	1588.0	1666.4	1744.8
22.5°	1002.5	1037.1	1080.7	1147.0	1250.2	1320.5	1384.8	1455.6	1533.4	1613.4	1700.3
25°	909.9	934.0	979.6	1033.2	1104.3	1220.1	1290.5	1361.5	1446.0	1531.8	1630.9
27.5°	840.4	862.1	891.7	942.9	995.7	1078.9	1190.8	1268.3	1352.4	1449.0	1551.9
30°	787.3	812.7	845.6	881.8	939.4	1004.4	1116.3	1206.1	1289.2	1388.4	1498.2
32.5°	748.7	768.8	796.8	833.5	881.5	943.8	1033.2	1142.3	1223.2	1327.8	1442.5
35°	685.5	708.9	731.7	766.6	805.4	862.3	930.0	1046.6	1127.0	1230.2	1345.4
37.5°	633.3	647.6	672.9	700.4	741.4	784.0	842.6	947.2	1034.2	1135.5	1253.4
40°	593.7	611.8	630.6	661.4	694.9	735.7	793.3	871.1	970.9	1070.1	1185.3
42.5°	555.1	577.9	597.8	618.4	655.2	696.1	743.0	808.9	910.9	1004.7	1116.7
45°	508.6	523.3	544.1	566.8	597.0	631.9	673.4	731.0	828.9	909.9	1015.1
47.5°	454.4	476.1	489.6	511.8	540.5	573.7	612.3	662.2	741.3	817.3	914.9
50°	417.5	439.6	459.0	479.1	504.5	536.7	568.9	617.1	680.8	760.5	851.6
52.5°	385.8	405.3	424.1	444.2	469.2	498.7	529.2	571.6	626.1	699.4	787.9
55°	342.4	354.5	373.9	393.9	416.1	444.2	473.7	509.3	556.1	617.8	689.5
57.5°	297.9	311.8	327.3	347.5	369.9	391.4	418.0	450.1	487.2	542.9	604.3
60°	272.7	283.5	296.2	316.9	337.7	357.1	382.6	409.4	444.2	492.5	544.7
62.5°	244.8	255.0	266.7	284.8	305.0	322.9	345.1	373.4	402.9	447.0	492.7
65°	198.3	213.1	224.5	240.5	257.3	276.1	293.5	316.3	342.4	377.3	418.1
67.5°	164.4	172.0	182.5	197.1	214.3	230.4	246.8	264.7	287.3	314.3	346.7
70°	149.5	152.1	154.1	168.1	184.3	200.4	215.7	232.5	252.0	274.1	302.2
72.5°	131.7	134.4	136.9	143.0	155.8	172.0	187.8	200.4	218.7	237.0	259.8
75°	104.5	108.6	110.6	113.9	118.6	129.4	144.1	156.1	166.8	180.9	199.0
77.5°	79.6	81.9	84.0	87.6	90.5	95.4	103.7	114.6	124.6	132.8	145.2
80°	63.0	63.6	66.3	67.7	71.7	75.0	79.1	87.8	97.9	101.2	109.9
82.5°	47.5	48.1	50.3	51.6	53.4	56.2	61.4	63.6	71.6	75.9	81.5
85°	26.2	25.4	27.5	27.5	28.8	30.2	31.5	34.8	36.9	42.2	43.5
87.5°	9.4	9.4	9.8	9.7	9.5	10.5	10.9	11.3	12.2	13.6	15.7
90°	6.9	6.6	6.0	5.4	4.7	4.2	3.5	2.7	1.9	1.1	0.3
92.5°	7.8	7.6	7.3	7.0	6.7	6.5	6.3	6.4	6.5	6.6	6.6
95°	13.1	12.7	12.2	11.7	11.2	10.7	11.6	14.0	16.5	18.8	21.2
97.5°	17.4	17.1	15.9	14.6	13.5	12.3	15.1	21.9	28.6	35.3	42.1
100°	19.2	18.6	17.4	16.2	14.9	13.6	18.1	28.0	37.9	47.9	57.8
102.5°	19.9	19.1	29.5	39.8	50.1	60.4	66.7	68.8	70.8	72.9	75.0
105°	20.7	19.9	39.7	59.6	79.4	99.2	108.0	105.8	103.6	101.4	99.3
107.5°	27.1	27.9	51.6	75.4	99.2	122.9	133.9	132.2	130.4	128.7	126.8
110°	49.9	57.2	78.1	99.1	120.1	141.0	150.8	149.3	147.7	146.1	144.6



TEST NUMBER: P331705-840

CATALOG NUMBER: S122RDIP-S865D330U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	117.6	144.1	149.3	154.5	159.7	164.8	166.7	165.4	164.1	162.7	161.4
115°	167.8	201.5	199.7	197.8	196.0	194.2	192.7	191.5	190.3	188.9	187.7
117.5°	215.0	223.2	221.9	220.7	219.4	218.1	216.8	215.5	214.1	212.7	211.4
120°	240.2	239.3	238.0	236.7	235.4	234.1	232.9	231.9	230.8	229.6	228.5
122.5°	255.3	254.8	253.4	251.9	250.4	249.0	247.8	246.6	245.5	244.4	243.2
125°	276.4	275.9	274.5	273.2	271.8	270.4	269.2	268.3	267.3	266.4	265.5
127.5°	295.7	295.0	294.0	293.0	291.9	290.8	289.8	288.8	287.7	286.7	285.6
130°	308.0	307.3	306.5	305.7	304.9	304.1	303.1	301.9	300.7	299.6	298.4
132.5°	320.2	319.5	318.7	317.9	317.1	316.3	315.5	314.5	313.5	312.5	311.5
135°	337.4	336.7	336.0	335.4	334.7	334.1	333.2	331.9	330.8	329.6	328.5
137.5°	353.4	352.6	351.9	351.1	350.4	349.7	348.9	348.1	347.3	346.5	345.7
140°	363.8	363.0	362.3	361.5	360.7	359.9	359.2	358.6	358.0	357.5	356.9
142.5°	373.3	372.7	371.8	370.9	370.0	369.1	368.4	367.9	367.3	366.8	366.3
145°	386.8	386.3	385.1	383.8	382.5	381.3	380.7	380.8	380.9	381.0	381.0
147.5°	398.5	398.2	397.0	395.8	394.5	393.2	392.8	393.0	393.3	393.6	393.9
150°	405.7	405.3	404.0	402.9	401.7	400.6	400.2	400.7	401.2	401.7	402.2
152.5°	412.1	411.7	410.6	409.5	408.4	407.3	407.1	407.6	408.2	408.8	409.3
155°	421.0	420.5	419.7	418.8	418.0	417.1	417.0	417.6	418.3	418.9	419.6
157.5°	428.4	427.9	427.3	426.7	426.1	425.5	425.4	426.0	426.5	427.1	427.6
160°	432.7	432.3	431.9	431.4	431.0	430.6	430.6	431.0	431.4	431.9	432.3
162.5°	436.8	436.3	435.9	435.5	435.0	434.7	434.7	435.2	435.7	436.1	436.5
165°	441.6	441.1	440.9	440.7	440.5	440.3	440.4	440.8	441.2	441.7	442.1
167.5°	445.8	445.2	445.0	444.8	444.6	444.4	444.5	444.9	445.5	445.9	446.3
170°	447.9	447.4	447.2	447.1	446.9	446.8	446.9	447.4	447.8	448.2	448.7
172.5°	449.4	448.9	448.8	448.6	448.5	448.3	448.5	448.9	449.3	449.8	450.2
175°	451.1	450.6	450.5	450.3	450.2	450.0	450.2	450.7	451.2	451.7	452.2
177.5°	451.4	451.0	450.9	450.9	450.8	450.8	450.9	451.3	451.7	452.1	452.5
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331705-840

CATALOG NUMBER: S122RDIP-S865D330U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1939.6	1941.3	1952.0	1956.8	1966.5	1970.2	1974.5	1973.5	1973.5	1975.6	1990.6
5°	1943.8	1957.2	1977.3	1996.8	2015.5	2031.6	2042.4	2053.1	2057.1	2076.5	2094.0
7.5°	1936.8	1961.6	1994.8	2024.4	2059.9	2087.6	2110.7	2131.4	2145.7	2173.9	2202.9
10°	1927.7	1962.6	2000.1	2038.3	2087.2	2124.0	2161.6	2190.4	2199.8	2242.0	2266.1
12.5°	1909.6	1956.1	2003.9	2053.4	2101.1	2151.9	2193.2	2222.0	2255.0	2292.9	2337.4
15°	1882.2	1935.8	1998.1	2061.7	2130.1	2191.7	2235.9	2286.2	2322.4	2364.0	2402.8
17.5°	1842.9	1912.0	1991.2	2064.9	2143.9	2210.1	2271.0	2319.2	2344.6	2368.3	2374.1
20°	1811.8	1886.2	1979.3	2066.5	2145.6	2221.9	2282.2	2322.4	2329.2	2329.8	2294.3
22.5°	1778.1	1862.1	1959.5	2048.7	2143.3	2228.4	2275.2	2292.4	2265.8	2220.4	2151.7
25°	1716.0	1813.2	1926.4	2028.2	2131.4	2211.8	2228.0	2197.8	2104.7	2006.8	1882.9
27.5°	1648.7	1758.0	1879.4	1992.6	2102.5	2152.3	2117.7	2008.9	1841.2	1695.4	1518.6
30°	1599.4	1722.0	1841.3	1967.9	2069.8	2091.2	2011.6	1851.4	1655.7	1435.9	1259.7
32.5°	1543.2	1671.6	1802.7	1933.7	2018.9	1997.9	1866.2	1669.1	1439.7	1223.7	1057.1
35°	1462.7	1595.4	1736.8	1868.1	1922.4	1831.9	1635.0	1378.3	1143.8	942.1	827.5
37.5°	1369.9	1514.3	1661.3	1781.9	1778.1	1627.3	1359.0	1094.1	897.0	777.7	696.1
40°	1303.9	1450.0	1608.8	1710.6	1667.1	1470.8	1179.9	930.0	786.0	690.8	631.2
42.5°	1240.7	1387.3	1545.0	1626.0	1550.2	1308.9	1019.2	823.3	704.5	630.3	581.9
45°	1133.1	1287.9	1433.9	1478.8	1343.4	1077.4	824.2	682.2	603.1	548.1	514.6
47.5°	1027.8	1180.1	1313.4	1314.2	1131.1	873.7	695.3	590.4	522.8	480.3	456.0
50°	963.5	1108.2	1220.1	1202.7	995.0	777.3	621.8	531.4	475.0	442.2	416.8
52.5°	891.2	1031.6	1128.5	1078.9	879.8	684.0	555.8	479.9	433.2	404.8	381.9
55°	786.0	910.6	979.0	903.9	717.6	568.9	469.7	410.1	375.3	351.1	331.6
57.5°	682.7	785.5	828.5	741.0	591.1	471.7	397.4	352.5	318.0	300.7	290.6
60°	617.8	705.6	735.7	639.2	513.9	412.7	351.7	310.2	284.8	273.4	263.4
62.5°	554.0	625.7	638.1	549.7	448.0	361.3	308.9	273.8	256.9	246.0	236.5
65°	459.7	511.3	505.2	434.2	354.5	286.8	248.6	227.1	214.4	199.0	182.3
67.5°	378.4	409.9	390.9	337.7	270.5	222.9	197.9	181.7	165.9	151.3	147.4
70°	327.0	345.1	325.0	276.1	221.8	186.9	166.8	147.4	138.0	134.7	128.7
72.5°	277.7	284.0	262.3	220.4	180.5	154.8	135.2	124.3	119.3	116.4	112.6
75°	208.4	203.7	184.9	152.1	125.3	107.9	101.9	97.9	94.5	91.8	89.8
77.5°	146.3	139.5	122.8	101.3	87.3	79.0	75.3	73.2	71.6	70.2	68.2
80°	109.9	105.2	88.5	72.4	66.3	62.3	60.3	57.7	57.7	56.2	54.2
82.5°	80.4	75.1	60.6	53.0	49.7	47.3	45.8	44.2	43.7	43.9	42.5
85°	42.2	34.1	30.2	28.8	26.8	25.4	26.2	24.7	24.7	24.7	24.1
87.5°	13.1	10.6	10.2	9.8	10.5	10.6	10.2	10.3	10.9	10.5	11.1
90°	1.1	1.9	2.7	3.5	4.2	4.7	5.4	6.0	6.6	6.9	7.3
92.5°	6.6	6.5	6.4	6.3	6.5	6.7	7.0	7.3	7.6	7.8	8.0
95°	18.8	16.5	14.0	11.6	10.7	11.2	11.7	12.2	12.7	13.1	13.4
97.5°	35.3	28.6	21.9	15.1	12.3	13.5	14.6	15.9	17.1	17.4	17.7
100°	47.9	37.9	28.0	18.1	13.6	14.9	16.2	17.4	18.6	19.2	19.8
102.5°	72.9	70.8	68.8	66.7	60.4	50.1	39.8	29.5	19.1	19.9	20.6
105°	101.4	103.6	105.8	108.0	99.2	79.4	59.6	39.7	19.9	20.7	21.5
107.5°	128.7	130.4	132.2	133.9	122.9	99.2	75.4	51.6	27.9	27.1	26.3
110°	146.1	147.7	149.3	150.8	141.0	120.1	99.1	78.1	57.2	49.9	42.6





TEST NUMBER: P331705-840

CATALOG NUMBER: S122RDIP-S865D330U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	162.7	164.1	165.4	166.7	164.8	159.7	154.5	149.3	144.1	117.6	91.2
115°	188.9	190.3	191.5	192.7	194.2	196.0	197.8	199.7	201.5	167.8	134.3
117.5°	212.7	214.1	215.5	216.8	218.1	219.4	220.7	221.9	223.2	215.0	206.9
120°	229.6	230.8	231.9	232.9	234.1	235.4	236.7	238.0	239.3	240.2	241.1
122.5°	244.4	245.5	246.6	247.8	249.0	250.4	251.9	253.4	254.8	255.3	255.8
125°	266.4	267.3	268.3	269.2	270.4	271.8	273.2	274.5	275.9	276.4	276.9
127.5°	286.7	287.7	288.8	289.8	290.8	291.9	293.0	294.0	295.0	295.7	296.5
130°	299.6	300.7	301.9	303.1	304.1	304.9	305.7	306.5	307.3	308.0	308.8
132.5°	312.5	313.5	314.5	315.5	316.3	317.1	317.9	318.7	319.5	320.2	320.9
135°	329.6	330.8	331.9	333.2	334.1	334.7	335.4	336.0	336.7	337.4	338.1
137.5°	346.5	347.3	348.1	348.9	349.7	350.4	351.1	351.9	352.6	353.4	354.1
140°	357.5	358.0	358.6	359.2	359.9	360.7	361.5	362.3	363.0	363.8	364.4
142.5°	366.8	367.3	367.9	368.4	369.1	370.0	370.9	371.8	372.7	373.3	374.0
145°	381.0	380.9	380.8	380.7	381.3	382.5	383.8	385.1	386.3	386.8	387.3
147.5°	393.6	393.3	393.0	392.8	393.2	394.5	395.8	397.0	398.2	398.5	398.9
150°	401.7	401.2	400.7	400.2	400.6	401.7	402.9	404.0	405.3	405.7	406.1
152.5°	408.8	408.2	407.6	407.1	407.3	408.4	409.5	410.6	411.7	412.1	412.6
155°	418.9	418.3	417.6	417.0	417.1	418.0	418.8	419.7	420.5	421.0	421.4
157.5°	427.1	426.5	426.0	425.4	425.5	426.1	426.7	427.3	427.9	428.4	428.9
160°	431.9	431.4	431.0	430.6	430.6	431.0	431.4	431.9	432.3	432.7	433.2
162.5°	436.1	435.7	435.2	434.7	434.7	435.0	435.5	435.9	436.3	436.8	437.2
165°	441.7	441.2	440.8	440.4	440.3	440.5	440.7	440.9	441.1	441.6	442.1
167.5°	445.9	445.5	444.9	444.5	444.4	444.6	444.8	445.0	445.2	445.8	446.3
170°	448.2	447.8	447.4	446.9	446.8	446.9	447.1	447.2	447.4	447.9	448.4
172.5°	449.8	449.3	448.9	448.5	448.3	448.5	448.6	448.8	448.9	449.4	449.9
175°	451.7	451.2	450.7	450.2	450.0	450.2	450.3	450.5	450.6	451.1	451.6
177.5°	452.1	451.7	451.3	450.9	450.8	450.8	450.9	450.9	451.0	451.4	451.8
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331705-840

CATALOG NUMBER: S122RDIP-S865D330U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4	1928.4
2.5°	1996.0	2003.0	2006.1	2006.1	2009.9	2008.3	2006.7
5°	2110.7	2123.4	2126.1	2138.2	2146.9	2144.1	2145.6
7.5°	2224.7	2245.2	2265.4	2274.7	2276.1	2281.5	2283.5
10°	2294.9	2311.7	2343.2	2338.4	2362.0	2375.3	2353.2
12.5°	2362.5	2385.1	2407.0	2413.0	2426.3	2430.5	2421.9
15°	2423.6	2435.7	2437.0	2433.7	2437.6	2434.3	2421.6
17.5°	2366.5	2346.9	2307.2	2288.5	2273.6	2251.7	2242.8
20°	2272.2	2214.5	2147.5	2120.7	2089.2	2027.6	2042.4
22.5°	2068.5	2002.8	1935.8	1857.5	1820.2	1761.7	1758.2
25°	1751.5	1638.3	1513.7	1426.5	1375.6	1317.4	1291.8
27.5°	1361.8	1219.2	1117.1	1065.4	1018.3	972.1	970.3
30°	1105.6	998.4	919.3	875.0	846.3	826.9	830.9
32.5°	931.9	858.5	805.2	768.4	747.1	732.5	732.3
35°	761.8	711.6	677.4	662.0	646.6	635.9	636.5
37.5°	652.0	621.8	602.8	585.7	576.1	570.9	567.9
40°	595.7	570.9	556.1	546.1	538.1	530.7	529.4
42.5°	551.2	530.7	515.9	508.1	500.5	495.3	493.9
45°	489.2	472.4	459.0	450.3	447.0	442.2	442.2
47.5°	435.2	418.7	408.2	402.7	397.0	393.8	393.7
50°	398.7	386.0	376.6	373.2	368.5	366.5	365.9
52.5°	366.0	356.5	349.8	347.5	345.5	343.0	343.4
55°	321.6	316.3	313.6	311.5	308.2	304.2	306.9
57.5°	284.3	279.6	272.5	266.1	263.1	260.2	261.4
60°	258.0	248.6	239.2	231.9	229.8	223.8	223.8
62.5°	224.7	211.6	200.1	195.9	193.9	191.1	190.6
65°	172.9	167.5	164.8	162.2	160.8	160.8	159.5
67.5°	143.3	141.1	138.1	137.5	136.1	135.7	135.3
70°	126.6	123.9	122.6	122.0	120.6	121.3	119.3
72.5°	110.6	108.5	108.2	106.4	105.6	105.7	104.2
75°	87.2	87.2	86.4	85.7	84.4	83.7	84.4
77.5°	67.1	67.2	65.9	65.8	65.6	65.8	65.1
80°	53.6	54.2	53.6	52.9	52.3	52.9	52.3
82.5°	42.3	41.4	41.3	41.1	41.0	40.6	40.5
85°	24.1	24.7	24.1	23.4	23.4	23.4	24.1
87.5°	10.6	10.7	10.8	10.8	10.8	10.8	10.3
90°	7.6	8.0	8.3	8.4	8.5	8.7	8.8
92.5°	8.2	8.3	8.5	8.6	8.7	8.7	8.8
95°	13.8	14.1	14.3	14.2	14.1	14.1	14.0
97.5°	17.9	18.2	18.4	18.5	18.6	18.7	18.8
100°	20.4	20.9	21.3	21.4	21.6	21.7	21.9
102.5°	21.4	22.1	22.6	22.8	23.0	23.2	23.4
105°	22.3	23.1	23.6	23.9	24.2	24.5	24.8
107.5°	25.4	24.6	24.3	24.6	24.9	25.2	25.5
110°	35.3	28.1	24.6	24.9	25.2	25.5	25.8



TEST NUMBER: P331705-840

CATALOG NUMBER: S122RDIP-S865D330U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	64.7	38.3	25.1	25.3	25.5	25.9	26.1
115°	100.7	67.1	47.7	42.4	37.3	32.0	26.8
117.5°	198.7	190.7	178.0	160.9	143.7	126.5	109.4
120°	242.0	242.8	238.3	228.5	218.7	208.9	199.1
122.5°	256.3	256.8	256.1	254.3	252.4	250.4	248.5
125°	277.4	277.9	278.3	278.5	278.7	278.9	279.1
127.5°	297.2	297.9	298.3	298.4	298.4	298.4	298.5
130°	309.6	310.4	310.8	310.7	310.6	310.6	310.5
132.5°	321.5	322.2	322.6	322.4	322.4	322.3	322.2
135°	338.8	339.5	339.8	339.7	339.5	339.4	339.2
137.5°	354.8	355.5	355.7	355.5	355.3	355.0	354.8
140°	365.1	365.7	365.9	365.5	365.2	364.8	364.4
142.5°	374.6	375.2	375.3	374.9	374.6	374.2	373.8
145°	387.8	388.3	388.4	388.0	387.7	387.3	386.9
147.5°	399.3	399.7	399.7	399.4	399.1	398.8	398.5
150°	406.5	407.0	407.0	406.7	406.3	405.9	405.6
152.5°	413.0	413.4	413.4	412.9	412.5	412.0	411.5
155°	421.8	422.3	422.2	421.6	421.1	420.5	419.9
157.5°	429.4	429.8	429.8	429.2	428.7	428.1	427.6
160°	433.6	434.0	434.0	433.5	433.0	432.5	432.0
162.5°	437.7	438.2	438.2	437.5	436.9	436.3	435.7
165°	442.6	443.1	443.1	442.6	442.1	441.6	441.1
167.5°	446.8	447.3	447.2	446.6	445.9	445.2	444.5
170°	448.9	449.4	449.3	448.7	448.0	447.4	446.7
172.5°	450.4	450.9	450.9	450.2	449.6	448.9	448.3
175°	452.1	452.6	452.5	451.8	451.1	450.3	449.6
177.5°	452.2	452.6	452.5	452.0	451.5	451.0	450.5
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2

(END OF REPORT)