

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331630-927

Luminaire Tested: **S122RDIP-S290D725U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331630-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S290D725U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3114.8 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331630-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331630-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	34	34	34	26
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	29	23
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25	19
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	24	23	22	17
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17	13
6	60	48	41	35	53	44	37	32	34	30	26	26	23	20	18	16	15	11
7	55	44	36	31	49	39	33	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12	9
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11	8
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6421	6421	6421
5°	6446	6340	6374
10°	6396	6237	6184
15°	6322	6051	5877
20°	6220	5787	5498
25°	6116	5489	5129
30°	5972	5179	4657
35°	5830	4845	4242
40°	5689	4498	3762
45°	5523	4108	3329
50°	5350	3715	2901
55°	5177	3291	2494
60°	4973	2848	2070
65°	4741	2392	1883
70°	4471	1969	1733
75°	4130	1797	1616
80°	3645	1609	1469
85°	2853	1260	1260



TEST NUMBER: P331630-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.2	1.2
10°-20°	102.2	3.3
20°-30°	143.5	4.6
30°-40°	156.5	5.0
40°-50°	143.9	4.6
50°-60°	113.0	3.6
60°-70°	73.7	2.4
70°-80°	38.0	1.2
80°-90°	11.8	0.4
90°-100°	26.1	0.8
100°-110°	95.8	3.1
110°-120°	256.1	8.2
120°-130°	422.7	13.6
130°-140°	449.6	14.4
140°-150°	417.8	13.4
150°-160°	335.9	10.8
160°-170°	216.5	7.0
170°-180°	74.5	2.4
0°-30°	282.9	9.1
0°-40°	439.4	14.1
0°-60°	696.4	22.4
0°-90°	819.8	26.3
90°-120°	378.0	12.1
90°-150°	1668.1	53.6
90°-180°	2295.0	73.7
0°-180°	3114.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	398	398	398	398	398	
5°	398	396	391	394	393	38
15°	378	374	362	355	352	106
25°	343	331	308	294	288	158
35°	296	277	246	224	215	185
45°	242	217	180	155	146	187
55°	184	155	117	96	89	164
65°	124	95	63	51	49	123
75°	66	42	29	26	26	70
85°	15	8	7	7	7	18
90°	1	7	11	14	15	2
95°	37	19	22	25	24	45
105°	172	180	34	41	43	184
115°	326	336	350	100	46	321
125°	461	468	479	483	484	411
135°	570	579	584	590	589	440
145°	661	661	670	674	672	413
155°	728	724	730	733	729	335
165°	767	764	766	769	766	217
175°	785	781	782	785	780	75
180°	783	783	783	783	783	



TEST NUMBER: P331630-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	399.1	398.8	398.5	398.2	397.8	397.3	396.6	395.9	395.2	394.5	395.1
5°	397.7	397.3	396.9	396.5	396.1	395.3	394.3	393.2	392.2	391.2	391.9
7.5°	393.6	393.1	392.5	392.1	391.6	390.7	389.5	388.2	387.1	385.9	386.0
10°	390.1	389.5	389.0	388.4	387.9	386.7	385.2	383.6	382.0	380.4	380.2
12.5°	385.8	385.1	384.4	383.7	383.0	381.7	379.6	377.6	375.5	373.4	373.0
15°	378.2	377.3	376.4	375.6	374.7	372.9	370.2	367.5	364.7	362.0	360.5
17.5°	368.9	367.6	366.2	364.9	363.5	361.2	357.7	354.2	350.7	347.2	345.4
20°	362.0	360.4	358.9	357.2	355.6	352.8	348.8	344.8	340.9	336.8	334.9
22.5°	354.6	352.8	350.9	349.2	347.4	344.2	339.7	335.2	330.7	326.2	323.6
25°	343.3	340.7	338.2	335.6	333.1	329.2	323.8	318.6	313.3	308.1	304.8
27.5°	329.8	327.0	324.2	321.5	318.6	314.3	308.3	302.4	296.4	290.5	286.7
30°	320.3	317.3	314.2	311.2	308.2	303.4	297.0	290.7	284.2	277.8	273.8
32.5°	311.1	307.5	304.0	300.4	296.8	291.8	285.3	278.8	272.3	265.7	261.1
35°	295.8	291.8	287.6	283.6	279.5	273.9	266.9	259.8	252.9	245.8	240.7
37.5°	280.6	276.1	271.6	267.1	262.6	256.7	249.1	241.6	234.2	226.6	221.1
40°	269.9	265.1	260.3	255.5	250.7	244.5	236.7	228.9	221.2	213.4	207.7
42.5°	259.0	253.9	248.8	243.8	238.8	232.2	224.2	216.2	208.2	200.2	194.3
45°	241.9	236.5	231.1	225.8	220.4	213.5	205.1	196.7	188.3	179.9	174.3
47.5°	225.1	219.4	213.8	208.1	202.4	195.3	186.6	177.9	169.2	160.6	155.0
50°	213.0	207.4	201.7	196.0	190.4	183.1	174.3	165.5	156.7	147.9	142.4
52.5°	201.2	195.3	189.4	183.5	177.5	170.2	161.6	153.0	144.4	135.8	130.5
55°	183.9	177.7	171.4	165.2	158.9	151.5	142.8	134.2	125.6	116.9	112.2
57.5°	166.1	159.7	153.3	146.9	140.5	133.2	124.8	116.6	108.3	100.0	95.5
60°	154.0	147.7	141.2	134.8	128.4	121.1	112.9	104.6	96.4	88.2	84.1
62.5°	142.2	135.9	129.4	123.0	116.6	109.5	101.6	93.8	86.0	78.1	74.2
65°	124.1	117.6	111.2	104.7	98.2	91.4	84.2	77.0	69.8	62.6	59.9
67.5°	106.7	100.3	93.9	87.5	81.0	74.5	68.0	61.6	55.1	48.6	47.4
70°	94.7	88.4	82.1	76.0	69.7	63.8	58.3	52.8	47.3	41.7	41.0
72.5°	83.1	77.2	71.1	65.2	59.2	54.0	49.6	45.2	40.7	36.3	35.6
75°	66.2	60.6	55.1	49.4	43.8	39.7	36.9	34.2	31.5	28.8	28.2
77.5°	49.6	44.7	39.8	34.9	29.9	26.9	25.5	24.2	22.9	21.6	21.3
80°	39.2	35.2	31.1	27.0	22.9	20.4	19.6	18.9	18.1	17.3	17.0
82.5°	29.7	26.5	23.4	20.2	17.0	15.1	14.6	14.0	13.5	13.0	12.8
85°	15.4	13.8	12.1	10.5	8.8	7.8	7.5	7.3	7.1	6.8	6.8
87.5°	4.8	4.5	4.3	4.0	3.8	3.8	4.0	4.2	4.4	4.6	4.6
90°	0.6	2.0	3.3	4.8	6.1	7.3	8.3	9.3	10.3	11.3	12.0
92.5°	11.4	11.3	11.2	11.1	10.9	11.2	11.6	12.1	12.7	13.2	13.5
95°	36.8	32.7	28.5	24.4	20.2	18.5	19.5	20.4	21.2	22.1	22.7
97.5°	73.1	61.4	49.7	37.9	26.2	21.4	23.4	25.5	27.6	29.5	30.1
100°	100.3	83.0	65.8	48.6	31.3	23.8	25.9	28.0	30.2	32.3	33.3
102.5°	130.2	126.6	122.9	119.3	115.6	104.8	86.9	69.0	51.1	33.2	34.5
105°	172.3	176.0	179.8	183.6	187.4	172.1	137.7	103.3	68.9	34.5	36.0
107.5°	220.2	223.2	226.3	229.3	232.4	213.3	172.1	130.9	89.6	48.4	47.0
110°	251.0	253.7	256.4	259.0	261.6	244.7	208.3	172.0	135.5	99.2	86.6



TEST NUMBER: P331630-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	280.0	282.4	284.7	287.1	289.4	286.1	277.1	268.1	259.1	250.1	204.2
115°	325.8	328.0	330.1	332.2	334.4	337.1	340.2	343.3	346.5	349.7	291.4
117.5°	366.8	369.2	371.5	373.9	376.3	378.6	380.8	382.9	385.1	387.3	373.2
120°	396.6	398.5	400.4	402.3	404.3	406.3	408.6	410.8	413.1	415.3	416.8
122.5°	422.1	424.1	426.0	428.0	430.0	432.2	434.7	437.2	439.7	442.1	443.0
125°	460.7	462.3	464.0	465.6	467.2	469.3	471.7	474.0	476.4	478.9	479.7
127.5°	495.7	497.6	499.4	501.1	503.0	504.8	506.6	508.3	510.2	511.9	513.3
130°	517.9	520.0	522.0	523.9	526.0	527.7	529.1	530.4	531.9	533.2	534.6
132.5°	540.6	542.3	544.1	545.7	547.5	549.0	550.4	551.8	553.2	554.5	555.7
135°	570.1	572.1	574.1	576.2	578.1	579.7	580.8	581.9	583.1	584.2	585.5
137.5°	599.9	601.3	602.7	604.1	605.5	606.9	608.2	609.4	610.7	612.0	613.2
140°	619.4	620.4	621.4	622.4	623.4	624.6	626.0	627.4	628.8	630.2	631.3
142.5°	635.7	636.6	637.5	638.4	639.3	640.6	642.1	643.7	645.3	646.9	647.9
145°	661.3	661.2	661.1	660.9	660.8	661.8	663.9	666.1	668.2	670.3	671.3
147.5°	683.7	683.2	682.7	682.2	681.8	682.5	684.7	686.7	688.9	691.0	691.7
150°	698.2	697.3	696.4	695.5	694.6	695.2	697.2	699.2	701.2	703.2	704.0
152.5°	710.3	709.4	708.4	707.4	706.5	706.9	708.8	710.7	712.6	714.5	715.3
155°	728.2	727.1	725.9	724.8	723.7	723.8	725.3	726.8	728.3	729.8	730.6
157.5°	742.1	741.2	740.2	739.3	738.3	738.3	739.4	740.5	741.5	742.6	743.5
160°	750.3	749.5	748.8	748.0	747.3	747.3	748.0	748.8	749.5	750.3	751.1
162.5°	757.6	756.8	756.1	755.3	754.5	754.5	755.1	755.7	756.5	757.1	758.0
165°	767.3	766.5	765.8	765.0	764.2	764.1	764.5	764.9	765.2	765.6	766.4
167.5°	774.5	773.8	773.0	772.3	771.5	771.3	771.7	772.0	772.4	772.7	773.6
170°	778.6	777.8	777.1	776.3	775.6	775.3	775.6	775.9	776.1	776.3	777.2
172.5°	781.3	780.5	779.8	779.0	778.3	778.1	778.3	778.6	778.8	779.0	780.0
175°	784.8	783.9	783.1	782.2	781.3	781.0	781.3	781.5	781.7	782.0	782.9
177.5°	785.4	784.7	784.0	783.3	782.6	782.3	782.4	782.5	782.6	782.7	783.4
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331630-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	395.8	396.4	397.0	397.3	397.2	397.0	396.9	396.8
5°	392.6	393.3	394.0	394.3	394.0	393.8	393.6	393.3
7.5°	386.3	386.5	386.7	386.6	386.2	385.7	385.3	384.9
10°	379.9	379.7	379.5	379.1	378.6	378.1	377.6	377.2
12.5°	372.6	372.2	371.8	371.1	370.3	369.6	368.8	368.0
15°	359.0	357.4	355.9	354.8	354.0	353.2	352.4	351.6
17.5°	343.6	341.7	340.0	338.4	337.0	335.6	334.2	332.9
20°	332.9	330.8	328.8	326.9	325.2	323.4	321.7	320.0
22.5°	321.1	318.5	315.9	313.9	312.6	311.3	310.0	308.7
25°	301.5	298.2	294.9	292.7	291.5	290.3	289.1	287.9
27.5°	282.8	279.0	275.2	272.4	270.5	268.5	266.6	264.7
30°	269.7	265.6	261.5	258.4	256.2	254.1	251.9	249.8
32.5°	256.4	251.8	247.1	243.8	241.8	239.7	237.7	235.7
35°	235.8	230.7	225.6	222.2	220.5	218.7	217.0	215.2
37.5°	215.6	210.0	204.5	200.7	198.7	196.6	194.6	192.6
40°	202.1	196.4	190.7	186.8	184.7	182.7	180.5	178.5
42.5°	188.4	182.5	176.7	172.8	170.7	168.7	166.7	164.7
45°	168.6	162.9	157.2	153.4	151.5	149.6	147.7	145.8
47.5°	149.2	143.6	138.0	134.3	132.5	130.8	129.0	127.3
50°	136.9	131.3	125.8	122.2	120.6	118.9	117.2	115.5
52.5°	125.2	119.9	114.5	111.1	109.6	108.0	106.4	104.9
55°	107.3	102.6	97.8	94.6	93.1	91.6	90.1	88.6
57.5°	91.2	86.7	82.4	79.5	78.3	77.0	75.7	74.4
60°	80.0	76.0	71.9	69.2	67.9	66.6	65.4	64.1
62.5°	70.3	66.5	62.6	60.2	59.4	58.7	57.9	57.1
65°	57.2	54.4	51.7	50.2	50.0	49.7	49.5	49.3
67.5°	46.2	44.9	43.6	42.9	42.6	42.4	42.1	41.9
70°	40.2	39.4	38.6	38.0	37.6	37.3	37.0	36.7
72.5°	34.9	34.2	33.6	33.2	33.0	32.8	32.6	32.4
75°	27.6	27.1	26.5	26.2	26.1	26.1	26.0	25.9
77.5°	20.9	20.6	20.3	20.1	20.0	19.8	19.7	19.6
80°	16.6	16.3	16.0	15.8	15.8	15.8	15.8	15.8
82.5°	12.6	12.4	12.2	12.1	12.1	12.1	12.1	12.1
85°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
87.5°	4.7	4.8	4.8	4.9	4.9	5.0	5.0	5.1
90°	12.6	13.2	13.9	14.3	14.6	14.8	15.1	15.3
92.5°	13.8	14.1	14.4	14.7	14.8	15.0	15.1	15.3
95°	23.4	24.0	24.6	24.9	24.7	24.6	24.5	24.4
97.5°	30.6	31.1	31.6	31.9	32.1	32.2	32.4	32.6
100°	34.3	35.3	36.4	37.0	37.2	37.5	37.7	37.9
102.5°	35.8	37.2	38.4	39.3	39.6	40.0	40.3	40.7
105°	37.3	38.7	40.1	41.0	41.6	42.1	42.5	43.1
107.5°	45.6	44.1	42.8	42.3	42.8	43.3	43.8	44.3
110°	74.0	61.4	48.8	42.8	43.3	43.7	44.3	44.8



TEST NUMBER: P331630-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	158.3	112.3	66.4	43.6	44.0	44.4	44.8	45.2
115°	233.1	174.8	116.5	82.7	73.7	64.6	55.5	46.5
117.5°	359.1	344.9	330.8	308.9	279.1	249.3	219.5	189.7
120°	418.4	419.9	421.4	413.7	396.6	379.7	362.7	345.7
122.5°	443.9	444.8	445.8	444.6	441.2	437.9	434.7	431.3
125°	480.6	481.5	482.4	483.0	483.4	483.8	484.1	484.5
127.5°	514.5	515.8	517.1	517.8	517.8	517.9	518.0	518.1
130°	536.0	537.4	538.8	539.4	539.3	539.2	539.0	538.9
132.5°	556.9	558.1	559.3	559.8	559.7	559.6	559.4	559.3
135°	586.8	588.0	589.3	589.8	589.5	589.3	589.0	588.7
137.5°	614.5	615.7	617.0	617.3	617.0	616.5	616.1	615.6
140°	632.4	633.5	634.7	634.9	634.3	633.7	633.0	632.4
142.5°	649.0	650.0	651.0	651.3	650.6	650.0	649.4	648.7
145°	672.2	673.0	673.9	674.0	673.4	672.8	672.2	671.5
147.5°	692.3	693.0	693.6	693.7	693.2	692.6	692.1	691.6
150°	704.7	705.5	706.2	706.3	705.7	705.0	704.4	703.8
152.5°	716.1	716.8	717.6	717.6	716.8	715.9	715.1	714.2
155°	731.4	732.1	732.9	732.8	731.7	730.8	729.8	728.7
157.5°	744.3	745.1	746.0	745.9	745.0	743.9	743.0	742.0
160°	751.8	752.6	753.3	753.2	752.3	751.5	750.6	749.7
162.5°	758.8	759.6	760.5	760.4	759.3	758.2	757.2	756.1
165°	767.3	768.3	769.1	769.1	768.3	767.3	766.4	765.6
167.5°	774.5	775.4	776.3	776.1	775.0	773.9	772.7	771.6
170°	778.1	779.0	779.9	779.7	778.6	777.4	776.3	775.2
172.5°	780.9	781.7	782.6	782.4	781.3	780.2	779.0	777.9
175°	783.8	784.7	785.5	785.4	784.1	782.8	781.6	780.3
177.5°	784.1	784.8	785.5	785.4	784.5	783.6	782.7	781.8
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2

(END OF REPORT)