

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331678-927

Luminaire Tested: **S122RDIP-S675D330U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331678-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S675D330U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2876.2 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331678-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331678-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	102	97	94	90	95	92	88	85	81	78	76	71	69	68	62	61	59	55
2	93	86	80	75	87	81	76	71	72	68	64	63	60	57	55	53	51	47
3	85	76	69	63	80	72	65	60	64	59	55	56	53	49	49	47	44	41
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	45	41	39	35
5	72	61	53	47	68	58	50	45	51	46	41	46	41	38	41	37	34	31
6	67	55	47	41	63	52	45	39	47	41	36	42	37	33	37	33	30	28
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27	25
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	25	22
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22	20
10	50	38	31	26	48	37	30	26	33	28	24	30	25	22	27	23	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14428	14428	14428
5°	14483	14248	14326
10°	14372	14014	13895
15°	14206	13600	13207
20°	13979	13005	12352
25°	13744	12332	11526
30°	13420	11639	10465
35°	13102	10886	9532
40°	12783	10108	8454
45°	12408	9232	7478
50°	12024	8349	6521
55°	11634	7398	5599
60°	11176	6397	4647
65°	10659	5375	4233
70°	10041	4428	3895
75°	9283	4036	3631
80°	8201	3608	3310
85°	6447	2853	2853



TEST NUMBER: P331678-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	2.9
10°-20°	229.7	8.0
20°-30°	322.5	11.2
30°-40°	351.7	12.2
40°-50°	323.4	11.2
50°-60°	254.0	8.8
60°-70°	165.6	5.8
70°-80°	85.4	3.0
80°-90°	23.0	0.8
90°-100°	11.8	0.4
100°-110°	43.3	1.5
110°-120°	115.7	4.0
120°-130°	191.1	6.6
130°-140°	203.2	7.1
140°-150°	188.9	6.6
150°-160°	151.8	5.3
160°-170°	97.8	3.4
170°-180°	33.7	1.2
0°-30°	635.8	22.1
0°-40°	987.5	34.3
0°-60°	1564.8	54.4
0°-90°	1838.8	63.9
90°-120°	170.8	5.9
90°-150°	754.0	26.2
90°-180°	1037.0	36.1
0°-180°	2876.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	894	894	894	894	894	
5°	894	889	879	886	884	85
15°	850	840	814	799	790	239
25°	772	744	692	660	647	355
35°	665	622	552	503	484	416
45°	543	488	404	349	328	419
55°	413	349	263	216	199	369
65°	279	213	141	115	111	277
75°	149	94	65	59	58	158
85°	35	19	15	15	15	41
90°	0	3	5	6	7	2
95°	17	9	10	11	11	20
105°	78	81	16	18	20	83
115°	147	152	158	45	21	145
125°	208	212	216	218	219	186
135°	258	262	264	266	266	199
145°	299	299	303	305	304	187
155°	329	327	330	331	329	152
165°	347	345	346	348	346	98
175°	355	353	354	355	353	34
180°	354	354	354	354	354	



TEST NUMBER: P331678-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	896.8	896.1	895.4	894.7	894.0	892.8	891.2	889.6	888.1	886.5	888.0
5°	893.6	892.7	891.8	890.9	890.0	888.4	886.1	883.8	881.4	879.1	880.7
7.5°	884.4	883.3	882.2	881.1	880.0	878.0	875.3	872.6	869.8	867.1	867.5
10°	876.6	875.4	874.1	872.8	871.6	869.2	865.5	862.0	858.4	854.8	854.3
12.5°	866.9	865.4	863.8	862.3	860.7	857.7	853.1	848.5	843.8	839.2	838.3
15°	849.9	848.0	846.0	844.0	842.0	838.0	831.9	825.8	819.7	813.6	810.2
17.5°	829.1	826.1	823.1	820.0	817.0	811.6	803.7	795.9	788.1	780.2	776.2
20°	813.6	809.9	806.4	802.8	799.2	792.9	783.9	774.9	766.0	756.9	752.4
22.5°	796.7	792.7	788.7	784.7	780.6	773.6	763.4	753.3	743.1	733.0	727.2
25°	771.5	765.7	760.0	754.2	748.5	739.7	727.9	716.0	704.1	692.2	684.8
27.5°	741.1	734.8	728.6	722.3	716.1	706.2	692.9	679.5	666.1	652.8	644.2
30°	719.8	712.9	706.1	699.3	692.4	681.8	667.4	653.1	638.7	624.3	615.1
32.5°	699.0	691.0	683.1	675.1	667.1	655.8	641.1	626.5	611.8	597.1	586.7
35°	664.7	655.6	646.4	637.2	628.1	615.6	599.8	584.0	568.2	552.3	541.0
37.5°	630.5	620.4	610.3	600.2	590.2	576.7	559.9	543.0	526.2	509.3	496.9
40°	606.5	595.7	584.9	574.2	563.4	549.3	531.9	514.4	497.0	479.6	466.8
42.5°	581.9	570.6	559.2	547.9	536.5	521.8	503.8	485.8	467.8	449.8	436.6
45°	543.4	531.4	519.4	507.3	495.3	479.8	461.0	442.1	423.2	404.3	391.6
47.5°	505.9	493.1	480.4	467.6	454.9	438.8	419.3	399.8	380.3	360.8	348.2
50°	478.7	466.0	453.2	440.5	427.7	411.5	391.7	371.9	352.1	332.4	320.0
52.5°	452.3	438.9	425.6	412.3	398.9	382.5	363.2	343.9	324.6	305.2	293.3
55°	413.3	399.3	385.2	371.2	357.2	340.5	321.1	301.7	282.3	262.8	252.1
57.5°	373.3	358.9	344.5	330.2	315.8	299.3	280.6	262.0	243.3	224.7	214.8
60°	346.1	331.8	317.3	303.0	288.6	272.2	253.7	235.1	216.7	198.1	188.9
62.5°	319.6	305.2	290.8	276.5	262.1	246.1	228.5	210.8	193.1	175.5	166.8
65°	279.0	264.4	249.9	235.4	220.8	205.4	189.3	173.1	156.9	140.7	134.6
67.5°	239.9	225.4	211.0	196.5	182.0	167.5	153.0	138.5	123.9	109.3	106.5
70°	212.7	198.7	184.7	170.6	156.6	143.4	131.0	118.6	106.2	93.8	92.0
72.5°	186.8	173.3	159.9	146.5	133.0	121.4	111.4	101.4	91.5	81.5	80.0
75°	148.8	136.3	123.7	111.1	98.5	89.1	83.0	76.9	70.8	64.7	63.5
77.5°	111.5	100.4	89.4	78.3	67.3	60.3	57.4	54.4	51.5	48.6	47.8
80°	88.2	79.0	69.8	60.7	51.5	46.0	44.2	42.4	40.6	38.8	38.1
82.5°	66.8	59.7	52.5	45.3	38.2	34.0	32.8	31.5	30.3	29.2	28.7
85°	34.8	31.0	27.3	23.4	19.6	17.5	17.0	16.5	15.9	15.4	15.4
87.5°	10.4	9.3	8.3	7.4	6.3	5.9	5.9	6.0	6.1	6.2	6.1
90°	0.2	0.9	1.5	2.1	2.8	3.3	3.7	4.2	4.7	5.1	5.4
92.5°	5.1	5.1	5.1	5.0	4.9	5.1	5.2	5.5	5.7	5.9	6.1
95°	16.6	14.7	12.9	11.0	9.1	8.4	8.8	9.2	9.6	10.0	10.3
97.5°	33.0	27.7	22.4	17.2	11.9	9.7	10.6	11.5	12.4	13.4	13.6
100°	45.3	37.5	29.7	21.9	14.2	10.7	11.7	12.7	13.6	14.6	15.1
102.5°	58.9	57.2	55.5	53.9	52.3	47.4	39.3	31.2	23.1	15.0	15.6
105°	77.9	79.5	81.3	83.0	84.7	77.8	62.3	46.7	31.1	15.6	16.2
107.5°	99.5	100.9	102.3	103.7	105.0	96.4	77.8	59.2	40.5	21.9	21.2
110°	113.4	114.6	115.9	117.1	118.3	110.6	94.2	77.7	61.2	44.8	39.1



TEST NUMBER: P331678-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	126.6	127.6	128.7	129.8	130.8	129.3	125.2	121.2	117.1	113.0	92.3
115°	147.3	148.2	149.2	150.2	151.1	152.3	153.8	155.2	156.6	158.0	131.7
117.5°	165.8	166.8	167.9	169.1	170.1	171.1	172.1	173.1	174.0	175.1	168.7
120°	179.3	180.1	181.0	181.9	182.7	183.6	184.7	185.7	186.7	187.7	188.5
122.5°	190.8	191.7	192.6	193.5	194.4	195.4	196.5	197.6	198.8	199.9	200.3
125°	208.3	209.0	209.7	210.5	211.2	212.1	213.2	214.3	215.3	216.4	216.8
127.5°	224.0	224.9	225.7	226.6	227.4	228.1	228.9	229.8	230.6	231.4	232.0
130°	234.1	235.0	235.9	236.9	237.7	238.5	239.2	239.8	240.4	241.1	241.6
132.5°	244.4	245.1	245.9	246.7	247.5	248.1	248.7	249.4	250.0	250.6	251.2
135°	257.7	258.6	259.5	260.4	261.3	262.1	262.5	263.1	263.6	264.1	264.7
137.5°	271.2	271.8	272.4	273.1	273.7	274.3	274.9	275.4	276.1	276.6	277.2
140°	280.0	280.4	280.8	281.3	281.8	282.3	283.0	283.6	284.2	284.8	285.3
142.5°	287.3	287.7	288.1	288.6	289.0	289.5	290.3	291.0	291.7	292.4	292.9
145°	298.9	298.9	298.8	298.7	298.7	299.1	300.1	301.1	302.1	303.0	303.4
147.5°	309.0	308.8	308.6	308.3	308.2	308.5	309.4	310.5	311.4	312.4	312.6
150°	315.5	315.1	314.7	314.3	313.9	314.3	315.1	316.1	317.0	317.9	318.2
152.5°	321.1	320.7	320.2	319.7	319.3	319.5	320.4	321.2	322.1	323.0	323.3
155°	329.2	328.6	328.1	327.6	327.1	327.2	327.9	328.5	329.2	329.9	330.3
157.5°	335.4	335.0	334.5	334.1	333.7	333.7	334.2	334.7	335.2	335.6	336.0
160°	339.1	338.8	338.4	338.1	337.8	337.8	338.1	338.4	338.8	339.1	339.5
162.5°	342.4	342.1	341.7	341.4	341.0	341.0	341.3	341.6	341.9	342.2	342.6
165°	346.8	346.5	346.1	345.8	345.5	345.4	345.5	345.7	345.9	346.0	346.4
167.5°	350.1	349.7	349.4	349.0	348.7	348.6	348.8	349.0	349.1	349.3	349.7
170°	352.0	351.6	351.3	350.9	350.5	350.5	350.5	350.7	350.8	350.9	351.3
172.5°	353.2	352.8	352.4	352.1	351.8	351.6	351.8	351.9	352.0	352.1	352.5
175°	354.7	354.3	353.9	353.6	353.2	353.0	353.2	353.2	353.4	353.5	353.9
177.5°	355.0	354.7	354.3	354.0	353.7	353.6	353.6	353.7	353.7	353.8	354.1
180°	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9



TEST NUMBER: P331678-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	889.4	890.8	892.2	892.8	892.6	892.2	892.0	891.7
5°	882.3	883.9	885.5	886.1	885.5	884.9	884.5	883.9
7.5°	868.0	868.5	868.9	868.7	867.8	866.9	865.9	865.0
10°	853.7	853.2	852.6	851.8	850.7	849.7	848.6	847.5
12.5°	837.3	836.4	835.4	834.0	832.2	830.4	828.6	826.8
15°	806.8	803.3	799.9	797.3	795.5	793.7	791.9	790.1
17.5°	772.1	768.0	764.0	760.4	757.3	754.2	751.1	748.1
20°	748.0	743.5	738.9	734.7	730.8	726.8	722.9	718.9
22.5°	721.4	715.7	709.9	705.5	702.5	699.6	696.6	693.7
25°	677.5	670.1	662.7	657.7	655.1	652.4	649.7	647.0
27.5°	635.6	627.0	618.5	612.0	607.7	603.4	599.1	594.8
30°	606.0	596.8	587.6	580.7	575.8	570.9	566.1	561.3
32.5°	576.2	565.8	555.3	547.8	543.2	538.7	534.1	529.6
35°	529.7	518.4	507.1	499.4	495.4	491.5	487.6	483.6
37.5°	484.3	471.9	459.5	450.9	446.4	441.9	437.4	432.8
40°	454.0	441.2	428.5	419.8	415.1	410.4	405.8	401.1
42.5°	423.4	410.2	397.0	388.2	383.7	379.1	374.6	370.0
45°	378.8	366.1	353.3	344.8	340.5	336.1	331.8	327.5
47.5°	335.5	322.8	310.1	301.8	297.9	294.0	290.0	286.1
50°	307.6	295.2	282.8	274.6	270.9	267.1	263.4	259.6
52.5°	281.3	269.3	257.3	249.6	246.1	242.6	239.2	235.7
55°	241.3	230.4	219.7	212.6	209.2	205.7	202.3	198.9
57.5°	204.9	195.0	185.1	178.7	175.9	173.0	170.1	167.2
60°	179.8	170.6	161.4	155.4	152.6	149.7	146.8	143.9
62.5°	158.0	149.2	140.5	135.3	133.6	131.9	130.2	128.4
65°	128.5	122.4	116.3	113.0	112.4	111.9	111.3	110.8
67.5°	103.7	100.9	98.2	96.4	95.9	95.3	94.7	94.1
70°	90.2	88.4	86.6	85.4	84.6	83.9	83.2	82.5
72.5°	78.5	77.0	75.5	74.5	74.1	73.7	73.2	72.8
75°	62.2	60.9	59.7	58.9	58.8	58.6	58.4	58.2
77.5°	47.1	46.3	45.6	45.2	44.8	44.6	44.3	44.0
80°	37.4	36.7	36.0	35.6	35.6	35.6	35.6	35.6
82.5°	28.3	27.8	27.4	27.2	27.2	27.2	27.2	27.2
85°	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4
87.5°	6.0	5.9	5.9	5.8	5.9	5.9	5.9	5.9
90°	5.7	5.9	6.3	6.5	6.6	6.7	6.8	6.9
92.5°	6.3	6.4	6.5	6.7	6.7	6.8	6.8	6.9
95°	10.5	10.9	11.1	11.2	11.2	11.1	11.1	11.0
97.5°	13.9	14.0	14.3	14.4	14.5	14.6	14.7	14.7
100°	15.5	16.0	16.4	16.7	16.8	17.0	17.0	17.2
102.5°	16.2	16.8	17.3	17.7	17.9	18.1	18.2	18.4
105°	16.9	17.5	18.1	18.5	18.8	19.0	19.3	19.5
107.5°	20.6	20.0	19.3	19.1	19.3	19.6	19.8	20.0
110°	33.4	27.7	22.0	19.3	19.6	19.8	20.0	20.2



TEST NUMBER: P331678-927

CATALOG NUMBER: S122RDIP-S675D330U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	71.5	50.8	30.0	19.7	19.9	20.0	20.3	20.4
115°	105.4	79.0	52.6	37.4	33.3	29.2	25.1	21.0
117.5°	162.3	155.9	149.6	139.7	126.2	112.7	99.3	85.8
120°	189.1	189.8	190.4	187.0	179.3	171.6	163.9	156.2
122.5°	200.7	201.1	201.5	200.9	199.5	198.0	196.5	195.0
125°	217.2	217.6	218.0	218.3	218.5	218.6	218.8	219.0
127.5°	232.6	233.1	233.7	234.0	234.1	234.1	234.1	234.2
130°	242.2	242.9	243.5	243.8	243.8	243.7	243.7	243.6
132.5°	251.8	252.2	252.8	253.0	252.9	252.9	252.9	252.8
135°	265.2	265.8	266.3	266.6	266.5	266.3	266.3	266.1
137.5°	277.7	278.3	278.8	279.0	278.8	278.7	278.5	278.3
140°	285.8	286.4	286.8	287.0	286.7	286.5	286.1	285.8
142.5°	293.3	293.8	294.3	294.4	294.1	293.8	293.5	293.2
145°	303.8	304.2	304.6	304.7	304.4	304.1	303.8	303.5
147.5°	312.9	313.2	313.5	313.5	313.3	313.1	312.8	312.6
150°	318.5	318.9	319.2	319.2	319.0	318.7	318.4	318.1
152.5°	323.7	324.0	324.3	324.3	323.9	323.6	323.2	322.8
155°	330.6	330.9	331.3	331.2	330.7	330.3	329.9	329.4
157.5°	336.4	336.8	337.2	337.2	336.7	336.3	335.8	335.4
160°	339.8	340.2	340.5	340.5	340.1	339.7	339.3	338.9
162.5°	342.9	343.3	343.7	343.7	343.2	342.7	342.2	341.7
165°	346.8	347.2	347.6	347.6	347.2	346.8	346.4	346.0
167.5°	350.1	350.5	350.9	350.8	350.3	349.7	349.3	348.7
170°	351.7	352.1	352.5	352.4	352.0	351.4	350.9	350.4
172.5°	352.9	353.3	353.7	353.7	353.2	352.7	352.1	351.6
175°	354.3	354.7	355.1	355.0	354.4	353.9	353.2	352.7
177.5°	354.4	354.7	355.1	355.0	354.6	354.2	353.8	353.4
180°	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9

(END OF REPORT)