

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331684-927

Luminaire Tested: **S122RDIP-S675D530U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331684-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S675D530U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3513.7 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331684-927

CATALOG NUMBER: S122RDIP-S675D530U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331684-927

CATALOG NUMBER: S122RDIP-S675D530U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	47	45	43	39
3	83	74	67	61	76	69	62	57	59	54	50	50	47	44	42	39	37	33
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	32	29
5	70	59	51	45	65	55	48	42	47	42	38	41	36	33	34	31	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	25	23
7	60	48	40	35	55	45	38	33	39	34	29	34	29	26	29	25	23	20
8	56	44	36	31	52	41	34	29	36	30	26	31	27	23	26	23	21	18
9	52	40	33	28	48	37	31	26	33	28	24	29	24	21	24	21	19	17
10	49	37	30	25	45	35	28	24	30	25	22	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14428	14428	14428
5°	14483	14248	14326
10°	14372	14014	13895
15°	14206	13600	13207
20°	13979	13005	12352
25°	13744	12332	11526
30°	13420	11639	10465
35°	13102	10886	9532
40°	12783	10108	8454
45°	12408	9232	7478
50°	12024	8349	6521
55°	11634	7398	5599
60°	11176	6397	4647
65°	10659	5375	4233
70°	10041	4428	3895
75°	9283	4036	3631
80°	8201	3608	3310
85°	6447	2853	2853



TEST NUMBER: P331684-927

CATALOG NUMBER: S122RDIP-S675D530U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	2.4
10°-20°	229.7	6.5
20°-30°	322.5	9.2
30°-40°	351.7	10.0
40°-50°	323.4	9.2
50°-60°	254.0	7.2
60°-70°	165.6	4.7
70°-80°	85.4	2.4
80°-90°	23.6	0.7
90°-100°	19.1	0.5
100°-110°	69.9	2.0
110°-120°	186.8	5.3
120°-130°	308.4	8.8
130°-140°	328.0	9.3
140°-150°	304.8	8.7
150°-160°	245.1	7.0
160°-170°	157.9	4.5
170°-180°	54.4	1.5
0°-30°	635.8	18.1
0°-40°	987.5	28.1
0°-60°	1564.8	44.5
0°-90°	1839.4	52.3
90°-120°	275.8	7.8
90°-150°	1217.0	34.6
90°-180°	1674.0	47.6
0°-180°	3513.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	894	894	894	894	894	
5°	894	889	879	886	884	85
15°	850	840	814	799	790	239
25°	772	744	692	660	647	355
35°	665	622	552	503	484	416
45°	543	488	404	349	328	419
55°	413	349	263	216	199	369
65°	279	213	141	115	111	277
75°	149	94	65	59	58	158
85°	35	19	15	15	15	41
90°	0	5	8	10	11	3
95°	27	14	16	18	18	33
105°	126	131	25	30	31	134
115°	238	245	255	73	34	234
125°	336	342	349	352	354	300
135°	416	422	426	430	430	321
145°	482	482	489	492	490	302
155°	531	528	532	535	532	245
165°	560	558	558	561	558	158
175°	573	570	570	573	569	54
180°	571	571	571	571	571	



TEST NUMBER: P331684-927

CATALOG NUMBER: S122RDIP-S675D530U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	896.8	896.1	895.4	894.7	894.0	892.8	891.2	889.6	888.1	886.5	888.0
5°	893.6	892.7	891.8	890.9	890.0	888.4	886.1	883.8	881.4	879.1	880.7
7.5°	884.4	883.3	882.2	881.1	880.0	878.0	875.3	872.6	869.8	867.1	867.5
10°	876.6	875.4	874.1	872.8	871.6	869.2	865.5	862.0	858.4	854.8	854.3
12.5°	866.9	865.4	863.8	862.3	860.7	857.7	853.1	848.5	843.8	839.2	838.3
15°	849.9	848.0	846.0	844.0	842.0	838.0	831.9	825.8	819.7	813.6	810.2
17.5°	829.1	826.1	823.1	820.0	817.0	811.6	803.7	795.9	788.1	780.2	776.2
20°	813.6	809.9	806.4	802.8	799.2	792.9	783.9	774.9	766.0	756.9	752.4
22.5°	796.7	792.7	788.7	784.7	780.6	773.6	763.4	753.3	743.1	733.0	727.2
25°	771.5	765.7	760.0	754.2	748.5	739.7	727.9	716.0	704.1	692.2	684.8
27.5°	741.1	734.8	728.6	722.3	716.1	706.2	692.9	679.5	666.1	652.8	644.2
30°	719.8	712.9	706.1	699.3	692.4	681.8	667.4	653.1	638.7	624.3	615.1
32.5°	699.0	691.0	683.1	675.1	667.1	655.8	641.1	626.5	611.8	597.1	586.7
35°	664.7	655.6	646.4	637.2	628.1	615.6	599.8	584.0	568.2	552.3	541.0
37.5°	630.5	620.4	610.3	600.2	590.2	576.7	559.9	543.0	526.2	509.3	496.9
40°	606.5	595.7	584.9	574.2	563.4	549.3	531.9	514.4	497.0	479.6	466.8
42.5°	581.9	570.6	559.2	547.9	536.5	521.8	503.8	485.8	467.8	449.8	436.6
45°	543.4	531.4	519.4	507.3	495.3	479.8	461.0	442.1	423.2	404.3	391.6
47.5°	505.9	493.1	480.4	467.6	454.9	438.8	419.3	399.8	380.3	360.8	348.2
50°	478.7	466.0	453.2	440.5	427.7	411.5	391.7	371.9	352.1	332.4	320.0
52.5°	452.3	438.9	425.6	412.3	398.9	382.5	363.2	343.9	324.6	305.2	293.3
55°	413.3	399.3	385.2	371.2	357.2	340.5	321.1	301.7	282.3	262.8	252.1
57.5°	373.3	358.9	344.5	330.2	315.8	299.3	280.6	262.0	243.3	224.7	214.8
60°	346.1	331.8	317.3	303.0	288.6	272.2	253.7	235.1	216.7	198.1	188.9
62.5°	319.6	305.2	290.8	276.5	262.1	246.1	228.5	210.8	193.1	175.5	166.8
65°	279.0	264.4	249.9	235.4	220.8	205.4	189.3	173.1	156.9	140.7	134.6
67.5°	239.9	225.4	211.0	196.5	182.0	167.5	153.0	138.5	123.9	109.3	106.5
70°	212.7	198.7	184.7	170.6	156.6	143.4	131.0	118.6	106.2	93.8	92.0
72.5°	186.8	173.3	159.9	146.5	133.0	121.4	111.4	101.4	91.5	81.5	80.0
75°	148.8	136.3	123.7	111.1	98.5	89.1	83.0	76.9	70.8	64.7	63.5
77.5°	111.5	100.4	89.4	78.3	67.3	60.3	57.4	54.4	51.5	48.6	47.8
80°	88.2	79.0	69.8	60.7	51.5	46.0	44.2	42.4	40.6	38.8	38.1
82.5°	66.8	59.7	52.5	45.3	38.2	34.0	32.8	31.5	30.3	29.2	28.7
85°	34.8	31.0	27.3	23.4	19.6	17.5	17.0	16.5	15.9	15.4	15.4
87.5°	10.5	9.5	8.6	7.6	6.7	6.3	6.4	6.5	6.7	6.8	6.8
90°	0.4	1.4	2.5	3.4	4.4	5.3	6.1	6.8	7.5	8.2	8.7
92.5°	8.3	8.2	8.2	8.1	8.0	8.2	8.5	8.9	9.2	9.6	9.8
95°	26.9	23.8	20.8	17.7	14.7	13.5	14.2	14.8	15.4	16.2	16.6
97.5°	53.3	44.8	36.3	27.7	19.2	15.6	17.1	18.6	20.1	21.5	21.9
100°	73.2	60.6	48.0	35.4	22.8	17.3	18.9	20.4	22.0	23.5	24.3
102.5°	95.0	92.4	89.7	87.0	84.4	76.4	63.5	50.4	37.3	24.2	25.2
105°	125.6	128.4	131.2	134.0	136.7	125.6	100.4	75.4	50.3	25.2	26.2
107.5°	160.7	162.9	165.1	167.3	169.5	155.6	125.6	95.5	65.4	35.3	34.3
110°	183.2	185.1	187.0	188.9	190.8	178.6	152.0	125.5	98.9	72.3	63.1



TEST NUMBER: P331684-927

CATALOG NUMBER: S122RDIP-S675D530U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	204.3	206.0	207.7	209.5	211.1	208.7	202.2	195.6	189.0	182.5	148.9
115°	237.7	239.2	240.8	242.4	244.0	245.9	248.2	250.5	252.8	255.1	212.5
117.5°	267.6	269.3	271.1	272.8	274.6	276.2	277.8	279.4	281.0	282.5	272.3
120°	289.4	290.7	292.2	293.5	294.9	296.4	298.1	299.8	301.3	303.0	304.1
122.5°	307.9	309.3	310.9	312.3	313.7	315.4	317.1	318.9	320.8	322.6	323.2
125°	336.1	337.3	338.5	339.7	340.9	342.4	344.1	345.9	347.6	349.4	350.0
127.5°	361.6	363.0	364.3	365.6	366.9	368.3	369.6	370.9	372.2	373.5	374.4
130°	377.9	379.3	380.8	382.3	383.7	385.0	386.0	387.0	388.0	389.0	390.1
132.5°	394.4	395.6	396.9	398.2	399.4	400.5	401.6	402.6	403.5	404.6	405.4
135°	415.9	417.4	418.8	420.3	421.8	422.9	423.7	424.6	425.4	426.2	427.1
137.5°	437.7	438.6	439.7	440.7	441.7	442.8	443.7	444.7	445.5	446.5	447.4
140°	451.9	452.6	453.4	454.1	454.8	455.7	456.7	457.7	458.7	459.7	460.6
142.5°	463.7	464.5	465.1	465.7	466.4	467.3	468.5	469.6	470.8	472.0	472.7
145°	482.4	482.4	482.3	482.2	482.1	482.8	484.4	485.9	487.5	489.1	489.7
147.5°	498.8	498.4	498.0	497.7	497.3	498.0	499.5	501.1	502.6	504.1	504.6
150°	509.3	508.7	508.0	507.4	506.8	507.2	508.7	510.1	511.6	513.0	513.6
152.5°	518.2	517.5	516.8	516.1	515.4	515.7	517.1	518.6	519.9	521.3	521.9
155°	531.2	530.4	529.6	528.8	527.9	528.1	529.2	530.3	531.4	532.5	533.1
157.5°	541.4	540.7	540.0	539.3	538.6	538.7	539.4	540.2	541.0	541.8	542.3
160°	547.4	546.8	546.3	545.7	545.2	545.2	545.7	546.3	546.8	547.4	548.0
162.5°	552.6	552.1	551.5	551.0	550.5	550.4	550.9	551.4	551.8	552.3	552.9
165°	559.8	559.2	558.6	558.1	557.5	557.5	557.7	557.9	558.3	558.5	559.2
167.5°	565.1	564.5	564.0	563.4	562.8	562.7	562.9	563.2	563.5	563.7	564.4
170°	568.0	567.5	567.0	566.4	565.9	565.6	565.9	566.0	566.2	566.4	567.0
172.5°	570.1	569.5	568.9	568.4	567.8	567.6	567.8	568.0	568.2	568.4	569.0
175°	572.6	572.0	571.3	570.7	570.0	569.8	570.0	570.1	570.3	570.5	571.2
177.5°	573.0	572.5	572.0	571.5	570.9	570.7	570.8	570.8	570.9	571.0	571.6
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3



TEST NUMBER: P331684-927

CATALOG NUMBER: S122RDIP-S675D530U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	889.4	890.8	892.2	892.8	892.6	892.2	892.0	891.7
5°	882.3	883.9	885.5	886.1	885.5	884.9	884.5	883.9
7.5°	868.0	868.5	868.9	868.7	867.8	866.9	865.9	865.0
10°	853.7	853.2	852.6	851.8	850.7	849.7	848.6	847.5
12.5°	837.3	836.4	835.4	834.0	832.2	830.4	828.6	826.8
15°	806.8	803.3	799.9	797.3	795.5	793.7	791.9	790.1
17.5°	772.1	768.0	764.0	760.4	757.3	754.2	751.1	748.1
20°	748.0	743.5	738.9	734.7	730.8	726.8	722.9	718.9
22.5°	721.4	715.7	709.9	705.5	702.5	699.6	696.6	693.7
25°	677.5	670.1	662.7	657.7	655.1	652.4	649.7	647.0
27.5°	635.6	627.0	618.5	612.0	607.7	603.4	599.1	594.8
30°	606.0	596.8	587.6	580.7	575.8	570.9	566.1	561.3
32.5°	576.2	565.8	555.3	547.8	543.2	538.7	534.1	529.6
35°	529.7	518.4	507.1	499.4	495.4	491.5	487.6	483.6
37.5°	484.3	471.9	459.5	450.9	446.4	441.9	437.4	432.8
40°	454.0	441.2	428.5	419.8	415.1	410.4	405.8	401.1
42.5°	423.4	410.2	397.0	388.2	383.7	379.1	374.6	370.0
45°	378.8	366.1	353.3	344.8	340.5	336.1	331.8	327.5
47.5°	335.5	322.8	310.1	301.8	297.9	294.0	290.0	286.1
50°	307.6	295.2	282.8	274.6	270.9	267.1	263.4	259.6
52.5°	281.3	269.3	257.3	249.6	246.1	242.6	239.2	235.7
55°	241.3	230.4	219.7	212.6	209.2	205.7	202.3	198.9
57.5°	204.9	195.0	185.1	178.7	175.9	173.0	170.1	167.2
60°	179.8	170.6	161.4	155.4	152.6	149.7	146.8	143.9
62.5°	158.0	149.2	140.5	135.3	133.6	131.9	130.2	128.4
65°	128.5	122.4	116.3	113.0	112.4	111.9	111.3	110.8
67.5°	103.7	100.9	98.2	96.4	95.9	95.3	94.7	94.1
70°	90.2	88.4	86.6	85.4	84.6	83.9	83.2	82.5
72.5°	78.5	77.0	75.5	74.5	74.1	73.7	73.2	72.8
75°	62.2	60.9	59.7	58.9	58.8	58.6	58.4	58.2
77.5°	47.1	46.3	45.6	45.2	44.8	44.6	44.3	44.0
80°	37.4	36.7	36.0	35.6	35.6	35.6	35.6	35.6
82.5°	28.3	27.8	27.4	27.2	27.2	27.2	27.2	27.2
85°	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4
87.5°	6.7	6.7	6.7	6.6	6.7	6.7	6.7	6.7
90°	9.2	9.7	10.1	10.5	10.6	10.8	11.0	11.2
92.5°	10.1	10.3	10.5	10.7	10.9	10.9	11.1	11.2
95°	17.0	17.5	18.0	18.1	18.1	18.0	17.9	17.7
97.5°	22.3	22.7	23.1	23.3	23.4	23.5	23.6	23.8
100°	25.0	25.7	26.5	26.9	27.2	27.3	27.5	27.7
102.5°	26.1	27.1	28.0	28.7	28.9	29.2	29.4	29.7
105°	27.3	28.3	29.2	29.9	30.3	30.7	31.1	31.4
107.5°	33.3	32.2	31.2	30.9	31.2	31.6	31.9	32.3
110°	53.9	44.8	35.6	31.2	31.5	31.9	32.3	32.6



TEST NUMBER: P331684-927

CATALOG NUMBER: S122RDIP-S675D530U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	115.4	81.9	48.4	31.8	32.1	32.4	32.7	33.0
115°	170.0	127.5	84.9	60.4	53.7	47.1	40.5	33.9
117.5°	262.0	251.7	241.4	225.4	203.6	181.9	160.2	138.4
120°	305.2	306.3	307.4	301.8	289.4	277.0	264.6	252.2
122.5°	323.8	324.6	325.2	324.3	321.9	319.5	317.1	314.7
125°	350.6	351.3	351.9	352.4	352.7	352.9	353.2	353.5
127.5°	375.3	376.3	377.2	377.7	377.8	377.9	377.9	378.0
130°	391.0	392.1	393.1	393.6	393.4	393.3	393.2	393.2
132.5°	406.3	407.2	408.1	408.4	408.3	408.2	408.1	408.1
135°	428.1	429.0	429.9	430.3	430.1	429.9	429.8	429.5
137.5°	448.3	449.2	450.1	450.4	450.0	449.7	449.5	449.2
140°	461.4	462.2	463.0	463.2	462.7	462.3	461.8	461.4
142.5°	473.5	474.2	475.0	475.2	474.7	474.2	473.7	473.2
145°	490.4	491.0	491.6	491.7	491.3	490.8	490.4	489.9
147.5°	505.1	505.6	506.0	506.0	505.7	505.3	504.9	504.5
150°	514.1	514.7	515.2	515.3	514.8	514.4	513.9	513.5
152.5°	522.4	523.0	523.6	523.5	522.9	522.3	521.7	521.1
155°	533.6	534.2	534.7	534.6	533.9	533.1	532.4	531.6
157.5°	543.0	543.6	544.2	544.2	543.4	542.7	542.0	541.3
160°	548.4	549.0	549.5	549.5	548.9	548.3	547.6	546.9
162.5°	553.6	554.2	554.8	554.8	554.0	553.2	552.4	551.6
165°	559.8	560.5	561.1	561.1	560.5	559.8	559.2	558.5
167.5°	565.0	565.7	566.3	566.3	565.4	564.6	563.7	562.9
170°	567.7	568.3	568.9	568.9	568.0	567.2	566.4	565.5
172.5°	569.7	570.3	570.9	570.8	570.1	569.2	568.4	567.5
175°	571.8	572.4	573.1	573.0	572.0	571.1	570.2	569.3
177.5°	572.0	572.6	573.1	573.0	572.4	571.6	571.0	570.4
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3

(END OF REPORT)