

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331246-940

Luminaire Tested: **S122DIP-S290D330U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331246-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S290D330U940-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2240.4 lumens  
Efficiency: N/A  
Efficacy: 110.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331246-940

CATALOG NUMBER: S122DIP-S290D330U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331246-940

CATALOG NUMBER: S122DIP-S290D330U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46	40
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	39	34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	37	35	33	29
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28	25
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25	21
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19
7	58	46	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19	17
8	54	41	34	28	49	38	32	27	33	27	24	28	23	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	13
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6801	6801	6801
5°	6827	6729	6770
10°	6787	6661	6694
15°	6703	6574	6569
20°	6584	6445	6438
25°	6465	6285	6285
30°	6315	6139	6087
35°	6173	5964	5876
40°	5994	5788	5678
45°	5818	5613	5476
50°	5627	5433	5242
55°	5427	5225	5027
60°	5205	4970	4789
65°	4967	4722	4504
70°	4664	4414	4206
75°	4242	4067	3968
80°	3766	3654	3468
85°	3075	2927	2631



TEST NUMBER: P331246-940

CATALOG NUMBER: S122DIP-S290D330U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.6	1.8
10°-20°	111.5	5.0
20°-30°	163.8	7.3
30°-40°	190.3	8.5
40°-50°	190.1	8.5
50°-60°	165.8	7.4
60°-70°	122.6	5.5
70°-80°	69.4	3.1
80°-90°	19.7	0.9
90°-100°	13.3	0.6
100°-110°	48.7	2.2
110°-120°	130.3	5.8
120°-130°	215.1	9.6
130°-140°	228.7	10.2
140°-150°	212.6	9.5
150°-160°	170.9	7.6
160°-170°	110.1	4.9
170°-180°	37.9	1.7
0°-30°	314.9	14.1
0°-40°	505.2	22.6
0°-60°	861.1	38.4
0°-90°	1072.8	47.9
90°-120°	192.3	8.6
90°-150°	848.7	37.9
90°-180°	1168.0	52.1
0°-180°	2240.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	421	421	421	421	421	
5°	421	420	415	418	418	40
15°	401	398	393	395	393	113
25°	363	360	353	354	353	167
35°	313	309	303	300	298	195
45°	255	252	246	242	240	197
55°	193	190	186	181	179	172
65°	130	128	124	120	118	129
75°	68	67	65	63	64	73
85°	17	16	16	15	14	19
90°	0	3	6	7	8	2
95°	19	10	11	13	12	23
105°	88	91	18	21	22	94
115°	166	171	178	51	24	163
125°	234	238	244	246	246	209
135°	290	295	297	300	300	224
145°	336	336	341	343	342	210
155°	370	368	371	373	371	171
165°	390	389	390	391	390	110
175°	399	397	398	400	397	38
180°	398	398	398	398	398	



TEST NUMBER: P331246-940

CATALOG NUMBER: S122DIP-S290D330U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2
2.5°	423.2	422.8	422.5	422.1	421.8	421.2	420.4	419.6	418.8	418.0	418.7
5°	421.2	420.9	420.5	420.2	419.8	419.2	418.2	417.2	416.2	415.2	415.9
7.5°	417.6	417.0	416.4	415.9	415.4	414.6	413.6	412.5	411.5	410.5	411.3
10°	414.0	413.4	412.8	412.1	411.4	410.6	409.6	408.5	407.4	406.3	407.0
12.5°	409.1	408.6	408.0	407.4	406.9	406.1	405.0	403.9	402.9	401.8	402.3
15°	401.0	400.5	399.9	399.4	398.9	398.1	396.8	395.7	394.5	393.3	393.7
17.5°	390.7	390.1	389.6	389.1	388.5	387.6	386.5	385.2	384.1	382.9	383.3
20°	383.2	382.6	382.1	381.6	381.0	380.1	378.9	377.6	376.4	375.1	375.4
22.5°	375.8	375.0	374.3	373.4	372.7	371.8	370.6	369.3	368.2	367.0	367.0
25°	362.9	362.2	361.5	360.8	360.1	358.9	357.4	355.9	354.4	352.8	353.0
27.5°	348.4	347.8	347.1	346.4	345.8	344.8	343.7	342.4	341.3	340.0	339.7
30°	338.7	338.0	337.2	336.5	335.7	334.7	333.4	332.1	330.6	329.3	329.0
32.5°	328.2	327.7	327.2	326.5	326.0	324.9	323.5	322.2	320.7	319.3	318.8
35°	313.2	312.2	311.3	310.4	309.5	308.4	306.9	305.5	304.1	302.6	302.0
37.5°	296.0	295.2	294.4	293.6	292.8	291.8	290.3	288.9	287.4	286.0	285.3
40°	284.4	283.7	282.9	282.2	281.5	280.4	278.9	277.5	276.1	274.6	273.8
42.5°	273.0	272.3	271.6	270.9	270.2	269.0	267.6	266.2	264.7	263.3	262.4
45°	254.8	254.1	253.5	252.9	252.3	251.3	249.9	248.6	247.3	245.8	244.9
47.5°	236.7	236.0	235.5	234.9	234.3	233.3	231.8	230.5	229.1	227.7	226.6
50°	224.0	223.6	223.1	222.7	222.2	221.3	220.1	218.8	217.6	216.3	215.1
52.5°	211.7	211.1	210.5	209.9	209.3	208.4	207.2	206.1	204.8	203.7	202.6
55°	192.8	192.3	191.7	191.2	190.6	189.8	188.8	187.7	186.6	185.6	184.4
57.5°	173.9	173.4	173.0	172.5	172.1	171.3	170.1	169.0	167.7	166.6	165.5
60°	161.2	160.9	160.5	160.2	159.8	159.0	157.7	156.5	155.2	153.9	152.9
62.5°	148.9	148.3	147.8	147.2	146.6	145.8	144.8	143.9	142.9	142.0	141.0
65°	130.0	129.5	128.9	128.4	127.9	127.2	126.3	125.4	124.5	123.6	122.7
67.5°	110.8	110.4	109.9	109.5	109.1	108.5	107.6	106.8	106.0	105.2	104.6
70°	98.8	98.4	98.1	97.7	97.4	96.8	96.0	95.2	94.3	93.5	92.9
72.5°	86.5	86.1	85.8	85.4	85.1	84.6	84.1	83.6	83.1	82.6	81.9
75°	68.0	67.9	67.7	67.5	67.3	67.1	66.6	66.1	65.6	65.2	64.6
77.5°	51.5	51.2	50.9	50.6	50.3	50.0	49.8	49.7	49.5	49.3	49.0
80°	40.5	40.4	40.3	40.2	40.1	40.0	39.9	39.7	39.5	39.3	39.1
82.5°	30.1	30.1	30.1	30.1	30.1	30.0	29.9	29.8	29.7	29.6	29.2
85°	16.6	16.5	16.4	16.3	16.2	16.1	16.1	16.0	15.9	15.8	15.5
87.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.8	5.8	5.7	5.7	5.5
90°	0.3	1.0	1.7	2.4	3.1	3.7	4.2	4.7	5.3	5.8	6.1
92.5°	5.8	5.8	5.7	5.6	5.5	5.7	5.9	6.2	6.4	6.7	6.9
95°	18.7	16.6	14.5	12.4	10.3	9.5	9.9	10.3	10.8	11.2	11.6
97.5°	37.2	31.2	25.2	19.4	13.4	10.9	11.9	12.9	14.0	15.1	15.3
100°	51.0	42.3	33.4	24.7	16.0	12.0	13.2	14.3	15.3	16.4	16.9
102.5°	66.3	64.4	62.5	60.7	58.9	53.3	44.2	35.1	26.0	16.9	17.6
105°	87.7	89.5	91.5	93.5	95.3	87.6	70.1	52.6	35.0	17.6	18.3
107.5°	112.0	113.6	115.1	116.7	118.2	108.5	87.6	66.6	45.6	24.6	23.9
110°	127.7	129.0	130.5	131.8	133.1	124.5	106.0	87.5	68.9	50.5	44.1



TEST NUMBER: P331246-940

CATALOG NUMBER: S122DIP-S290D330U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	142.5	143.7	144.9	146.1	147.2	145.5	141.0	136.4	131.8	127.2	103.9
115°	165.8	166.8	168.0	169.1	170.1	171.5	173.1	174.7	176.3	177.9	148.2
117.5°	186.6	187.8	189.0	190.3	191.5	192.6	193.8	194.8	195.9	197.1	189.8
120°	201.8	202.8	203.8	204.7	205.6	206.7	207.9	209.0	210.2	211.3	212.1
122.5°	214.7	215.8	216.8	217.8	218.8	219.9	221.1	222.4	223.7	225.0	225.4
125°	234.4	235.2	236.0	236.9	237.7	238.8	240.0	241.2	242.4	243.6	244.1
127.5°	252.2	253.2	254.0	255.0	255.9	256.8	257.7	258.7	259.6	260.5	261.1
130°	263.5	264.6	265.6	266.6	267.6	268.5	269.2	269.9	270.6	271.3	272.0
132.5°	275.1	275.9	276.8	277.7	278.6	279.3	280.0	280.7	281.4	282.1	282.8
135°	290.1	291.1	292.1	293.1	294.2	295.0	295.5	296.1	296.7	297.3	297.9
137.5°	305.2	305.9	306.7	307.4	308.1	308.8	309.4	310.0	310.8	311.4	312.0
140°	315.1	315.7	316.1	316.6	317.2	317.8	318.5	319.2	319.9	320.6	321.2
142.5°	323.4	323.9	324.3	324.9	325.3	325.9	326.7	327.5	328.3	329.1	329.7
145°	336.4	336.4	336.4	336.3	336.2	336.7	337.8	338.9	340.0	341.1	341.5
147.5°	347.9	347.6	347.3	347.1	346.9	347.2	348.3	349.5	350.5	351.6	351.9
150°	355.2	354.7	354.3	353.8	353.4	353.7	354.7	355.8	356.8	357.8	358.2
152.5°	361.4	361.0	360.4	359.9	359.4	359.6	360.6	361.6	362.6	363.6	363.9
155°	370.5	369.9	369.3	368.7	368.2	368.3	369.1	369.8	370.6	371.3	371.8
157.5°	377.6	377.1	376.6	376.1	375.6	375.7	376.2	376.7	377.3	377.8	378.3
160°	381.7	381.4	380.9	380.6	380.2	380.2	380.6	380.9	381.4	381.7	382.1
162.5°	385.4	385.0	384.7	384.2	383.9	383.9	384.1	384.5	384.9	385.2	385.7
165°	390.4	390.0	389.6	389.2	388.9	388.8	389.0	389.1	389.3	389.5	389.9
167.5°	394.0	393.7	393.3	392.9	392.5	392.4	392.6	392.8	393.0	393.2	393.6
170°	396.2	395.7	395.4	395.0	394.6	394.5	394.6	394.8	394.8	395.0	395.5
172.5°	397.5	397.2	396.7	396.4	396.0	395.8	396.0	396.1	396.3	396.4	396.8
175°	399.3	398.9	398.4	398.0	397.5	397.3	397.5	397.6	397.8	397.9	398.3
177.5°	399.6	399.2	398.9	398.5	398.1	398.1	398.1	398.1	398.1	398.2	398.6
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4



TEST NUMBER: P331246-940

CATALOG NUMBER: S122DIP-S290D330U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2
2.5°	419.5	420.2	420.9	421.2	421.1	420.9	420.8	420.6
5°	416.7	417.4	418.1	418.4	418.2	418.0	417.9	417.7
7.5°	412.0	412.7	413.4	413.7	413.5	413.2	413.0	412.9
10°	407.8	408.5	409.2	409.4	409.1	408.8	408.6	408.3
12.5°	402.8	403.2	403.8	403.9	403.8	403.5	403.3	403.1
15°	394.0	394.4	394.8	394.8	394.3	393.9	393.4	393.0
17.5°	383.7	384.1	384.5	384.5	384.1	383.7	383.3	382.8
20°	375.7	375.9	376.2	376.1	375.8	375.4	375.1	374.7
22.5°	367.1	367.2	367.2	367.1	366.9	366.7	366.5	366.3
25°	353.2	353.4	353.6	353.6	353.4	353.2	353.0	352.8
27.5°	339.5	339.2	338.9	338.6	338.1	337.7	337.3	336.9
30°	328.8	328.5	328.2	328.0	327.6	327.3	326.9	326.5
32.5°	318.3	317.8	317.4	316.9	316.6	316.2	315.8	315.5
35°	301.5	301.0	300.4	300.0	299.5	299.1	298.6	298.1
37.5°	284.6	284.0	283.3	282.8	282.3	281.9	281.5	281.1
40°	273.0	272.2	271.4	270.8	270.5	270.1	269.7	269.4
42.5°	261.5	260.6	259.8	259.0	258.6	258.1	257.6	257.1
45°	243.9	242.9	241.9	241.2	240.9	240.5	240.1	239.8
47.5°	225.6	224.5	223.5	222.7	222.2	221.7	221.1	220.6
50°	213.8	212.5	211.2	210.4	210.0	209.6	209.1	208.7
52.5°	201.6	200.5	199.5	198.7	198.0	197.5	196.9	196.3
55°	183.3	182.3	181.2	180.5	180.0	179.5	179.1	178.6
57.5°	164.4	163.4	162.3	161.6	161.3	161.0	160.6	160.2
60°	151.9	151.0	150.0	149.4	149.1	148.8	148.6	148.3
62.5°	140.1	139.2	138.3	137.7	137.3	137.0	136.6	136.3
65°	121.9	121.1	120.3	119.7	119.2	118.8	118.3	117.9
67.5°	104.0	103.3	102.7	102.2	101.8	101.5	101.1	100.8
70°	92.3	91.7	91.0	90.6	90.2	89.8	89.4	89.1
72.5°	81.3	80.7	80.1	79.5	79.3	79.0	78.7	78.4
75°	64.1	63.6	63.0	62.9	63.0	63.2	63.4	63.6
77.5°	48.8	48.5	48.2	48.0	47.7	47.5	47.3	47.0
80°	38.8	38.5	38.3	38.0	37.8	37.6	37.5	37.3
82.5°	28.9	28.5	28.2	28.0	28.0	27.9	27.9	27.9
85°	15.2	15.0	14.7	14.5	14.4	14.4	14.3	14.2
87.5°	5.4	5.3	5.1	5.0	4.9	4.9	4.8	4.8
90°	6.4	6.7	7.0	7.3	7.4	7.5	7.7	7.8
92.5°	7.0	7.2	7.3	7.5	7.6	7.7	7.7	7.8
95°	11.9	12.2	12.5	12.7	12.6	12.5	12.5	12.4
97.5°	15.6	15.8	16.1	16.2	16.3	16.4	16.5	16.6
100°	17.5	18.0	18.5	18.8	18.9	19.1	19.2	19.4
102.5°	18.2	18.9	19.5	20.0	20.2	20.3	20.5	20.7
105°	19.0	19.7	20.4	20.9	21.1	21.4	21.7	21.9
107.5°	23.2	22.5	21.8	21.5	21.8	22.0	22.3	22.6
110°	37.6	31.2	24.8	21.8	22.0	22.3	22.6	22.7





TEST NUMBER: P331246-940

CATALOG NUMBER: S122DIP-S290D330U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	80.5	57.2	33.8	22.2	22.4	22.6	22.8	23.0
115°	118.6	88.9	59.2	42.1	37.5	32.9	28.3	23.6
117.5°	182.7	175.5	168.4	157.2	142.0	126.9	111.7	96.6
120°	212.9	213.7	214.4	210.4	201.8	193.1	184.5	175.8
122.5°	225.9	226.3	226.8	226.1	224.5	222.8	221.1	219.5
125°	244.5	245.0	245.4	245.8	245.9	246.1	246.3	246.5
127.5°	261.8	262.4	263.1	263.4	263.5	263.5	263.5	263.6
130°	272.7	273.4	274.1	274.5	274.4	274.3	274.3	274.2
132.5°	283.4	283.9	284.5	284.8	284.7	284.7	284.6	284.5
135°	298.5	299.2	299.8	300.1	300.0	299.8	299.7	299.5
137.5°	312.6	313.3	313.9	314.1	313.9	313.7	313.4	313.3
140°	321.7	322.4	322.9	323.1	322.7	322.4	322.1	321.7
142.5°	330.2	330.7	331.3	331.4	331.0	330.7	330.4	330.0
145°	342.0	342.4	342.9	343.0	342.6	342.3	342.0	341.6
147.5°	352.2	352.6	352.9	352.9	352.7	352.4	352.1	351.9
150°	358.6	358.9	359.4	359.4	359.1	358.7	358.4	358.1
152.5°	364.4	364.7	365.1	365.1	364.6	364.3	363.8	363.4
155°	372.1	372.5	372.9	372.8	372.3	371.8	371.3	370.8
157.5°	378.7	379.2	379.5	379.5	379.0	378.5	378.0	377.6
160°	382.5	382.9	383.3	383.3	382.8	382.4	381.9	381.5
162.5°	386.0	386.5	386.9	386.9	386.3	385.8	385.2	384.7
165°	390.4	390.8	391.3	391.3	390.8	390.4	389.9	389.5
167.5°	394.0	394.5	394.9	394.8	394.3	393.7	393.2	392.5
170°	395.9	396.4	396.8	396.7	396.2	395.6	395.0	394.4
172.5°	397.3	397.7	398.1	398.1	397.5	397.0	396.4	395.8
175°	398.8	399.2	399.7	399.6	399.0	398.3	397.6	397.0
177.5°	399.0	399.3	399.7	399.6	399.1	398.7	398.2	397.8
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4

(END OF REPORT)