

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331327-940

Luminaire Tested: **S122DIP-S485D1080U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331327-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S485D1080U940-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5604.4 lumens  
Efficiency: N/A  
Efficacy: 113.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331327-940

CATALOG NUMBER: S122DIP-S485D1080U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331327-940

CATALOG NUMBER: S122DIP-S485D1080U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	35	34	33	26
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28	22
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11183	11183	11183
5°	11225	11063	11128
10°	11158	10952	11006
15°	11020	10810	10798
20°	10825	10596	10584
25°	10630	10334	10334
30°	10381	10094	10006
35°	10147	9806	9662
40°	9853	9518	9333
45°	9565	9229	9001
50°	9251	8932	8616
55°	8923	8586	8267
60°	8557	8173	7869
65°	8164	7759	7404
70°	7671	7260	6916
75°	6981	6687	6525
80°	6192	6007	5700
85°	5057	4798	4316



TEST NUMBER: P331327-940

CATALOG NUMBER: S122DIP-S485D1080U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.1	1.2
10°-20°	183.3	3.3
20°-30°	269.4	4.8
30°-40°	312.9	5.6
40°-50°	312.5	5.6
50°-60°	272.6	4.9
60°-70°	201.5	3.6
70°-80°	114.1	2.0
80°-90°	33.9	0.6
90°-100°	43.7	0.8
100°-110°	160.2	2.9
110°-120°	428.4	7.6
120°-130°	707.1	12.6
130°-140°	752.0	13.4
140°-150°	699.0	12.5
150°-160°	562.0	10.0
160°-170°	362.1	6.5
170°-180°	124.6	2.2
0°-30°	517.7	9.2
0°-40°	830.6	14.8
0°-60°	1415.7	25.3
0°-90°	1765.3	31.5
90°-120°	632.3	11.3
90°-150°	2790.4	49.8
90°-180°	3839.0	68.5
0°-180°	5604.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	693	693	693	693	693	
5°	693	690	683	688	687	66
15°	659	655	647	649	646	186
25°	597	591	580	581	580	274
35°	515	508	498	494	490	321
45°	419	414	404	397	394	323
55°	317	313	305	297	294	283
65°	214	210	203	197	194	211
75°	112	110	107	104	105	120
85°	27	27	26	24	23	31
90°	1	11	19	24	26	4
95°	62	32	37	41	41	75
105°	288	301	58	68	72	308
115°	545	562	585	167	78	537
125°	771	783	801	807	810	687
135°	954	968	977	986	985	736
145°	1106	1106	1121	1127	1123	692
155°	1218	1211	1221	1226	1219	561
165°	1284	1278	1281	1287	1281	362
175°	1313	1307	1308	1314	1305	125
180°	1310	1310	1310	1310	1310	



TEST NUMBER: P331327-940

CATALOG NUMBER: S122DIP-S485D1080U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6
2.5°	695.8	695.2	694.6	694.0	693.4	692.5	691.2	689.9	688.6	687.2	688.5
5°	692.6	692.0	691.4	690.8	690.3	689.1	687.5	685.9	684.2	682.6	683.8
7.5°	686.4	685.5	684.7	683.7	682.8	681.5	679.8	678.2	676.5	674.8	676.1
10°	680.6	679.6	678.5	677.5	676.5	675.0	673.2	671.5	669.8	668.0	669.1
12.5°	672.6	671.7	670.7	669.9	669.0	667.6	665.8	664.1	662.3	660.5	661.3
15°	659.3	658.4	657.5	656.7	655.8	654.3	652.4	650.5	648.5	646.7	647.2
17.5°	642.2	641.4	640.5	639.6	638.7	637.3	635.3	633.4	631.4	629.5	630.2
20°	630.0	629.1	628.2	627.3	626.4	625.0	622.9	620.8	618.8	616.7	617.2
22.5°	617.8	616.5	615.3	614.0	612.8	611.2	609.2	607.3	605.3	603.3	603.4
25°	596.7	595.5	594.3	593.2	592.0	590.1	587.6	585.1	582.6	580.1	580.3
27.5°	572.7	571.7	570.6	569.5	568.5	566.9	565.0	562.9	561.0	559.0	558.6
30°	556.8	555.5	554.4	553.2	552.0	550.3	548.0	545.9	543.7	541.4	541.0
32.5°	539.7	538.8	537.8	536.8	535.9	534.2	531.9	529.6	527.3	525.0	524.1
35°	514.8	513.3	511.8	510.3	508.9	506.9	504.6	502.2	499.8	497.5	496.6
37.5°	486.7	485.4	484.1	482.8	481.4	479.7	477.2	474.9	472.5	470.2	469.0
40°	467.5	466.3	465.1	464.0	462.8	461.0	458.6	456.3	453.9	451.6	450.2
42.5°	448.9	447.6	446.5	445.3	444.2	442.4	440.0	437.7	435.2	432.8	431.4
45°	418.9	417.9	416.8	415.8	414.7	413.1	410.9	408.7	406.4	404.2	402.6
47.5°	389.1	388.1	387.1	386.1	385.1	383.5	381.2	378.9	376.6	374.3	372.6
50°	368.3	367.6	366.8	366.0	365.3	363.9	361.9	359.8	357.7	355.6	353.6
52.5°	348.0	347.1	346.1	345.1	344.1	342.7	340.7	338.8	336.8	334.8	333.1
55°	317.0	316.1	315.2	314.3	313.4	312.1	310.3	308.5	306.7	305.0	303.3
57.5°	285.8	285.1	284.4	283.7	283.0	281.7	279.7	277.8	275.8	273.8	272.1
60°	265.0	264.5	263.9	263.2	262.7	261.4	259.3	257.2	255.1	253.1	251.5
62.5°	244.8	243.9	242.9	241.9	241.0	239.8	238.2	236.6	235.0	233.4	231.8
65°	213.7	212.9	212.0	211.1	210.3	209.0	207.6	206.1	204.6	203.1	201.8
67.5°	182.2	181.5	180.7	180.0	179.3	178.3	177.0	175.7	174.3	173.0	172.0
70°	162.5	161.9	161.3	160.7	160.2	159.2	157.8	156.5	155.2	153.8	152.8
72.5°	142.2	141.7	141.1	140.4	139.9	139.2	138.3	137.4	136.6	135.7	134.6
75°	111.9	111.6	111.3	111.0	110.7	110.2	109.4	108.7	108.0	107.2	106.3
77.5°	84.7	84.2	83.7	83.2	82.7	82.3	82.0	81.7	81.4	81.1	80.7
80°	66.6	66.4	66.3	66.2	66.0	65.8	65.5	65.2	64.9	64.6	64.1
82.5°	49.6	49.5	49.5	49.5	49.4	49.3	49.1	49.0	48.8	48.6	48.1
85°	27.3	27.2	27.0	26.8	26.8	26.6	26.4	26.3	26.1	25.9	25.5
87.5°	9.8	10.0	10.3	10.4	10.7	10.9	11.0	11.1	11.1	11.2	11.1
90°	1.0	3.3	5.6	7.9	10.3	12.2	13.9	15.6	17.3	19.0	20.0
92.5°	19.2	18.9	18.7	18.5	18.3	18.6	19.4	20.3	21.1	22.0	22.6
95°	61.6	54.7	47.7	40.8	33.8	31.0	32.5	34.1	35.5	37.0	38.0
97.5°	122.3	102.7	83.1	63.5	44.0	35.8	39.2	42.6	46.1	49.5	50.3
100°	167.8	138.9	110.0	81.2	52.3	39.7	43.2	46.9	50.5	54.0	55.7
102.5°	217.8	211.7	205.6	199.5	193.4	175.4	145.4	115.5	85.5	55.6	57.8
105°	288.2	294.5	300.8	307.1	313.4	287.8	230.3	172.8	115.3	57.8	60.1
107.5°	368.4	373.4	378.5	383.6	388.8	356.9	287.8	218.9	149.9	81.0	78.6
110°	419.9	424.4	428.8	433.2	437.7	409.4	348.5	287.7	226.8	165.9	144.8



TEST NUMBER: P331327-940

CATALOG NUMBER: S122DIP-S485D1080U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	468.5	472.4	476.3	480.2	484.1	478.6	463.5	448.5	433.5	418.4	341.6
115°	545.1	548.7	552.2	555.8	559.4	563.8	569.1	574.4	579.6	584.9	487.3
117.5°	613.5	617.5	621.5	625.5	629.5	633.3	636.9	640.6	644.2	647.8	624.2
120°	663.5	666.7	669.9	673.1	676.2	679.7	683.5	687.2	691.1	694.8	697.3
122.5°	706.1	709.4	712.7	716.0	719.3	723.1	727.2	731.3	735.5	739.6	741.1
125°	770.7	773.4	776.1	778.9	781.6	785.0	789.0	793.0	797.0	801.0	802.5
127.5°	829.3	832.3	835.4	838.4	841.4	844.4	847.4	850.3	853.4	856.4	858.5
130°	866.4	869.8	873.2	876.6	879.9	882.7	885.0	887.3	889.7	892.0	894.3
132.5°	904.3	907.2	910.1	912.9	915.8	918.4	920.7	923.0	925.3	927.6	929.6
135°	953.6	957.0	960.4	963.8	967.1	969.7	971.6	973.5	975.4	977.3	979.5
137.5°	1003.4	1005.8	1008.2	1010.6	1012.9	1015.1	1017.4	1019.5	1021.6	1023.8	1025.8
140°	1036.1	1037.8	1039.5	1041.2	1042.9	1044.8	1047.1	1049.5	1051.8	1054.1	1056.0
142.5°	1063.4	1064.9	1066.4	1067.9	1069.4	1071.6	1074.2	1076.8	1079.5	1082.2	1083.9
145°	1106.3	1106.0	1105.8	1105.6	1105.4	1107.1	1110.6	1114.2	1117.8	1121.4	1122.8
147.5°	1143.6	1142.8	1142.0	1141.2	1140.4	1141.7	1145.3	1148.8	1152.4	1155.9	1157.0
150°	1167.9	1166.4	1164.9	1163.4	1162.0	1162.9	1166.3	1169.7	1173.0	1176.3	1177.7
152.5°	1188.3	1186.7	1185.0	1183.4	1181.8	1182.5	1185.7	1188.9	1192.1	1195.3	1196.6
155°	1218.1	1216.2	1214.3	1212.4	1210.5	1210.9	1213.4	1215.8	1218.4	1220.9	1222.2
157.5°	1241.4	1239.8	1238.2	1236.6	1235.0	1235.1	1236.9	1238.6	1240.4	1242.2	1243.6
160°	1255.1	1253.8	1252.5	1251.2	1250.0	1250.0	1251.2	1252.5	1253.8	1255.1	1256.3
162.5°	1267.2	1266.0	1264.6	1263.4	1262.1	1262.0	1263.1	1264.3	1265.3	1266.4	1267.8
165°	1283.5	1282.2	1280.9	1279.7	1278.4	1278.1	1278.7	1279.4	1280.1	1280.7	1282.1
167.5°	1295.7	1294.4	1293.1	1291.8	1290.6	1290.2	1290.8	1291.4	1292.0	1292.6	1294.1
170°	1302.4	1301.2	1299.9	1298.7	1297.4	1297.0	1297.4	1297.8	1298.2	1298.7	1300.1
172.5°	1307.0	1305.7	1304.5	1303.2	1302.0	1301.5	1302.0	1302.3	1302.8	1303.2	1304.7
175°	1312.9	1311.4	1309.9	1308.5	1307.0	1306.4	1306.9	1307.3	1307.7	1308.1	1309.7
177.5°	1313.8	1312.7	1311.4	1310.3	1309.1	1308.6	1308.8	1308.9	1309.1	1309.3	1310.5
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331327-940

CATALOG NUMBER: S122DIP-S485D1080U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6
2.5°	689.6	690.8	692.0	692.5	692.2	692.0	691.8	691.5
5°	685.0	686.2	687.3	687.8	687.5	687.2	686.9	686.6
7.5°	677.3	678.4	679.7	680.0	679.8	679.4	679.0	678.8
10°	670.3	671.5	672.7	673.1	672.6	672.2	671.7	671.3
12.5°	662.2	663.0	663.8	664.1	663.7	663.4	663.1	662.7
15°	647.8	648.5	649.0	648.9	648.2	647.5	646.8	646.0
17.5°	630.8	631.5	632.2	632.1	631.4	630.8	630.1	629.4
20°	617.6	618.0	618.5	618.4	617.8	617.2	616.6	616.0
22.5°	603.5	603.6	603.7	603.6	603.2	602.9	602.5	602.2
25°	580.7	580.9	581.2	581.2	580.9	580.7	580.3	580.1
27.5°	558.1	557.7	557.2	556.7	556.0	555.3	554.6	553.8
30°	540.6	540.1	539.7	539.1	538.5	538.0	537.3	536.7
32.5°	523.3	522.5	521.7	521.0	520.4	519.9	519.2	518.6
35°	495.7	494.8	493.9	493.1	492.4	491.6	490.9	490.2
37.5°	468.0	466.9	465.8	464.8	464.1	463.4	462.7	462.1
40°	448.9	447.5	446.2	445.2	444.6	444.1	443.4	442.8
42.5°	430.0	428.6	427.0	426.0	425.1	424.3	423.5	422.6
45°	401.0	399.4	397.7	396.6	396.0	395.5	394.8	394.2
47.5°	370.9	369.1	367.4	366.1	365.2	364.4	363.6	362.7
50°	351.5	349.4	347.3	345.9	345.2	344.5	343.7	343.0
52.5°	331.4	329.7	328.0	326.6	325.7	324.7	323.7	322.7
55°	301.5	299.7	297.9	296.7	295.9	295.2	294.4	293.7
57.5°	270.4	268.6	266.9	265.7	265.1	264.6	264.0	263.4
60°	249.8	248.2	246.6	245.5	245.0	244.6	244.2	243.7
62.5°	230.3	228.8	227.3	226.3	225.7	225.2	224.6	224.0
65°	200.5	199.1	197.8	196.7	196.0	195.3	194.6	193.8
67.5°	170.9	169.9	168.9	168.1	167.5	166.8	166.3	165.7
70°	151.8	150.7	149.7	148.9	148.3	147.7	147.1	146.5
72.5°	133.7	132.6	131.6	130.8	130.4	129.8	129.4	128.9
75°	105.4	104.6	103.7	103.3	103.7	104.0	104.2	104.6
77.5°	80.3	79.8	79.4	78.9	78.5	78.1	77.7	77.2
80°	63.7	63.2	62.9	62.4	62.2	61.9	61.5	61.3
82.5°	47.5	46.9	46.4	46.0	46.0	45.9	45.8	45.8
85°	25.1	24.6	24.2	23.9	23.7	23.6	23.5	23.3
87.5°	11.0	10.8	10.7	10.6	10.5	10.5	10.5	10.4
90°	21.0	22.1	23.2	23.9	24.3	24.8	25.1	25.6
92.5°	23.1	23.6	24.2	24.6	24.9	25.1	25.3	25.6
95°	39.1	40.1	41.2	41.6	41.4	41.2	40.9	40.8
97.5°	51.2	52.0	52.9	53.4	53.7	53.9	54.1	54.4
100°	57.4	59.1	60.8	61.8	62.2	62.7	63.1	63.5
102.5°	59.9	62.2	64.3	65.7	66.3	66.9	67.5	68.0
105°	62.4	64.7	67.1	68.7	69.6	70.4	71.2	72.1
107.5°	76.2	73.8	71.5	70.8	71.6	72.4	73.3	74.1
110°	123.8	102.7	81.6	71.5	72.3	73.2	74.0	74.9





TEST NUMBER: P331327-940

CATALOG NUMBER: S122DIP-S485D1080U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	264.7	187.9	111.0	72.9	73.7	74.3	75.0	75.6
115°	389.8	292.3	194.7	138.4	123.2	108.1	92.9	77.8
117.5°	600.7	577.0	553.5	516.7	466.9	417.1	367.2	317.4
120°	699.9	702.4	705.0	692.0	663.5	635.1	606.6	578.3
122.5°	742.6	744.1	745.6	743.6	738.2	732.6	727.1	721.6
125°	804.0	805.4	806.9	808.0	808.6	809.2	809.9	810.5
127.5°	860.7	862.8	865.0	866.1	866.2	866.4	866.5	866.6
130°	896.6	898.9	901.3	902.3	902.1	901.9	901.7	901.5
132.5°	931.6	933.6	935.6	936.5	936.2	936.0	935.9	935.6
135°	981.5	983.6	985.7	986.6	986.1	985.7	985.3	984.9
137.5°	1027.9	1029.9	1032.0	1032.7	1032.0	1031.3	1030.6	1029.8
140°	1057.9	1059.8	1061.7	1062.1	1061.0	1060.0	1058.9	1057.9
142.5°	1085.6	1087.4	1089.0	1089.4	1088.3	1087.3	1086.3	1085.2
145°	1124.4	1125.8	1127.3	1127.5	1126.5	1125.4	1124.4	1123.3
147.5°	1158.1	1159.2	1160.3	1160.4	1159.5	1158.6	1157.7	1156.8
150°	1178.9	1180.2	1181.4	1181.5	1180.4	1179.5	1178.4	1177.3
152.5°	1197.8	1199.2	1200.4	1200.3	1198.9	1197.6	1196.1	1194.8
155°	1223.4	1224.8	1226.0	1225.7	1224.1	1222.4	1220.8	1219.1
157.5°	1245.0	1246.4	1247.9	1247.8	1246.2	1244.5	1242.9	1241.2
160°	1257.6	1258.8	1260.1	1260.0	1258.6	1257.0	1255.6	1254.1
162.5°	1269.3	1270.7	1272.2	1271.9	1270.2	1268.4	1266.5	1264.7
165°	1283.6	1285.0	1286.6	1286.6	1285.0	1283.6	1282.1	1280.7
167.5°	1295.6	1297.0	1298.5	1298.2	1296.4	1294.5	1292.6	1290.7
170°	1301.6	1303.1	1304.6	1304.3	1302.4	1300.6	1298.7	1296.7
172.5°	1306.2	1307.6	1309.1	1308.9	1307.0	1305.1	1303.2	1301.3
175°	1311.1	1312.6	1314.0	1313.8	1311.6	1309.5	1307.4	1305.3
177.5°	1311.6	1312.8	1314.0	1313.8	1312.3	1310.8	1309.3	1307.8
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0

(END OF REPORT)