

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331728-927

Luminaire Tested: **S122RDIP-S865D925U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331728-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S865D925U927-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5253.6 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331728-927

CATALOG NUMBER: S122RDIP-S865D925U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331728-927

CATALOG NUMBER: S122RDIP-S865D925U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46
1	97	93	89	86	89	86	82	80	71	69	67	59	57	56	47	46	45	39
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	42	40	38	34
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	25
5	69	57	50	44	63	53	46	41	45	40	36	37	34	31	30	28	25	22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	25	23	20	18
8	54	42	35	30	50	40	33	28	34	29	25	28	24	22	23	21	18	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	14
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18755	18755	18755
5°	18827	18519	18621
10°	18682	18216	18061
15°	18467	17677	17167
20°	18170	16905	16057
25°	17865	16030	14982
30°	17443	15129	13601
35°	17030	14152	12390
40°	16617	13139	10989
45°	16130	12001	9720
50°	15631	10854	8475
55°	15122	9619	7279
60°	14528	8315	6042
65°	13857	6988	5501
70°	13053	5755	5061
75°	12071	5246	4722
80°	10646	4695	4305
85°	8373	3705	3705



TEST NUMBER: P331728-927

CATALOG NUMBER: S122RDIP-S865D925U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.7	2.1
10°-20°	298.5	5.7
20°-30°	419.2	8.0
30°-40°	457.1	8.7
40°-50°	420.3	8.0
50°-60°	330.1	6.3
60°-70°	215.2	4.1
70°-80°	111.0	2.1
80°-90°	32.5	0.6
90°-100°	164.4	3.1
100°-110°	557.8	10.6
110°-120°	592.6	11.3
120°-130°	487.8	9.3
130°-140°	391.8	7.5
140°-150°	296.0	5.6
150°-160°	208.1	4.0
160°-170°	122.5	2.3
170°-180°	39.9	0.8
0°-30°	826.5	15.7
0°-40°	1283.6	24.4
0°-60°	2034.0	38.7
0°-90°	2392.7	45.5
90°-120°	1314.8	25.0
90°-150°	2490.5	47.4
90°-180°	2861.0	54.5
0°-180°	5253.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1162	1162	1162	1162	1162	
5°	1162	1156	1143	1151	1149	110
15°	1105	1092	1058	1038	1027	311
25°	1003	967	900	858	841	461
35°	864	808	718	654	629	541
45°	706	634	526	454	426	545
55°	537	453	342	281	259	480
65°	363	277	183	149	144	359
75°	194	122	84	77	76	205
85°	45	24	20	20	20	53
90°	1	11	27	26	26	3
95°	28	68	310	117	90	29
105°	96	145	586	1047	891	102
115°	170	215	490	1012	1172	169
125°	237	281	471	819	951	211
135°	278	332	466	689	788	215
145°	318	365	463	575	629	199
155°	361	390	450	509	529	166
165°	394	406	431	457	464	111
175°	410	411	414	420	418	39
180°	411	411	411	411	411	



TEST NUMBER: P331728-927

CATALOG NUMBER: S122RDIP-S865D925U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6
2.5°	1165.8	1164.8	1163.9	1162.9	1162.1	1160.5	1158.5	1156.4	1154.4	1152.3	1154.2
5°	1161.6	1160.4	1159.2	1158.0	1156.9	1154.8	1151.8	1148.7	1145.7	1142.6	1144.7
7.5°	1149.5	1148.1	1146.7	1145.3	1143.8	1141.3	1137.7	1134.2	1130.6	1127.0	1127.7
10°	1139.5	1137.8	1136.2	1134.6	1132.9	1129.8	1125.1	1120.5	1115.8	1111.1	1110.4
12.5°	1126.9	1124.8	1122.8	1120.9	1118.8	1114.8	1108.8	1102.9	1096.9	1090.9	1089.6
15°	1104.8	1102.2	1099.6	1097.1	1094.5	1089.3	1081.3	1073.4	1065.4	1057.5	1053.0
17.5°	1077.7	1073.7	1069.8	1065.9	1062.0	1054.9	1044.7	1034.5	1024.4	1014.2	1008.9
20°	1057.5	1052.8	1048.1	1043.5	1038.8	1030.6	1018.9	1007.3	995.6	983.9	978.0
22.5°	1035.6	1030.4	1025.2	1019.9	1014.7	1005.5	992.3	979.1	966.0	952.8	945.2
25°	1002.8	995.4	987.9	980.4	973.0	961.5	946.0	930.7	915.2	899.8	890.3
27.5°	963.3	955.1	947.1	938.9	930.8	918.1	900.6	883.3	865.9	848.5	837.3
30°	935.6	926.7	917.8	908.9	900.1	886.3	867.6	848.9	830.2	811.5	799.6
32.5°	908.6	898.3	887.9	877.5	867.1	852.5	833.4	814.3	795.3	776.2	762.6
35°	864.0	852.2	840.3	828.3	816.4	800.2	779.6	759.1	738.6	718.0	703.2
37.5°	819.5	806.4	793.4	780.2	767.1	749.6	727.8	705.8	684.0	662.0	645.8
40°	788.4	774.4	760.3	746.3	732.3	714.0	691.3	668.7	646.0	623.4	606.7
42.5°	756.5	741.6	726.9	712.2	697.4	678.3	654.9	631.4	608.1	584.6	567.5
45°	706.4	690.7	675.1	659.4	643.8	623.7	599.2	574.6	550.1	525.6	509.0
47.5°	657.6	641.0	624.5	607.8	591.3	570.3	545.0	519.7	494.3	469.1	452.6
50°	622.3	605.7	589.1	572.5	556.0	534.8	509.1	483.4	457.7	432.1	415.9
52.5°	587.8	570.5	553.2	535.8	518.5	497.3	472.1	446.9	421.8	396.7	381.1
55°	537.2	519.0	500.7	482.5	464.3	442.5	417.3	392.1	366.9	341.7	327.6
57.5°	485.2	466.5	447.8	429.1	410.5	389.0	364.7	340.5	316.2	292.0	279.2
60°	449.9	431.2	412.6	393.9	375.2	353.8	329.7	305.6	281.6	257.5	245.7
62.5°	415.4	396.7	378.0	359.3	340.6	319.9	296.9	274.0	251.0	228.1	216.7
65°	362.7	343.7	324.8	305.9	287.0	267.0	246.0	225.0	203.9	182.9	175.0
67.5°	311.8	293.0	274.3	255.4	236.6	217.8	198.9	180.0	161.1	142.1	138.5
70°	276.5	258.3	240.0	221.8	203.6	186.4	170.3	154.2	138.1	121.9	119.6
72.5°	242.8	225.4	207.9	190.4	172.9	157.7	144.8	131.8	118.9	106.0	104.0
75°	193.5	177.1	160.7	144.3	128.0	115.9	107.9	100.0	92.1	84.1	82.5
77.5°	144.9	130.5	116.1	101.8	87.5	78.4	74.5	70.7	66.9	63.1	62.1
80°	114.5	102.7	90.8	78.8	66.9	59.8	57.4	55.1	52.8	50.5	49.5
82.5°	86.8	77.6	68.2	58.9	49.7	44.2	42.6	41.0	39.5	37.9	37.3
85°	45.2	40.3	35.4	30.5	25.6	22.8	22.1	21.4	20.7	20.0	20.0
87.5°	13.6	12.6	11.7	10.5	9.3	9.1	9.9	11.0	12.0	12.1	11.7
90°	0.8	3.2	6.3	7.9	9.5	11.9	15.8	21.3	26.1	26.9	26.1
92.5°	9.7	13.9	19.6	23.1	28.4	35.9	53.8	78.9	101.3	102.7	86.8
95°	27.6	30.8	38.7	45.9	58.5	77.5	113.8	182.6	274.3	309.9	271.2
97.5°	45.1	49.4	57.8	68.4	83.0	104.5	150.2	246.1	398.5	529.1	555.0
100°	60.8	63.2	70.3	83.0	98.9	121.0	162.9	259.4	430.1	624.6	738.5
102.5°	75.4	77.2	84.3	97.0	113.4	135.5	174.3	260.0	418.1	627.7	806.8
105°	96.5	99.7	105.1	117.0	134.4	156.5	193.7	264.0	394.5	585.8	796.1
107.5°	119.2	121.8	127.1	138.1	155.3	177.6	213.7	275.0	382.8	541.0	726.7
110°	134.4	137.6	142.3	152.6	169.2	192.1	226.9	283.8	380.3	519.4	683.1



TEST NUMBER: P331728-927

CATALOG NUMBER: S122RDIP-S865D925U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	148.3	151.5	156.9	166.5	182.4	206.0	239.6	293.3	380.9	505.5	652.8
115°	170.0	174.0	178.7	188.1	204.0	225.3	259.4	307.5	384.2	490.2	615.1
117.5°	192.4	195.6	200.3	208.7	223.9	246.1	277.5	322.7	389.9	482.8	591.4
120°	206.4	209.5	214.3	221.3	237.2	259.4	290.2	332.9	393.7	478.3	578.8
122.5°	219.7	222.1	226.9	234.6	250.5	273.2	302.1	341.7	398.2	475.8	568.0
125°	237.2	239.6	244.3	253.8	269.6	291.8	320.2	355.8	404.8	471.2	552.6
127.5°	251.1	254.3	260.9	271.3	286.5	309.3	337.0	368.9	411.6	468.5	538.4
130°	259.4	262.4	270.4	281.5	297.3	319.4	347.1	377.2	416.7	467.2	528.9
132.5°	266.9	270.7	279.2	291.0	307.4	329.5	355.9	385.3	421.7	466.6	521.3
135°	278.3	281.5	291.0	302.8	321.0	343.1	368.4	396.1	427.7	465.6	510.7
137.5°	289.1	292.9	302.3	315.0	333.0	353.6	378.6	404.3	433.1	465.5	503.3
140°	297.3	300.5	309.9	322.6	340.0	360.5	384.2	408.8	435.6	464.9	498.9
142.5°	305.5	308.0	316.9	329.5	346.3	365.6	388.6	412.6	437.5	464.9	494.5
145°	317.8	321.0	328.9	340.8	356.6	374.0	395.3	417.5	439.6	463.3	488.6
147.5°	331.1	333.5	341.0	352.0	365.1	380.6	400.7	420.2	440.2	460.5	482.6
150°	340.0	342.3	348.6	358.9	370.8	385.0	403.2	421.4	439.6	458.6	477.5
152.5°	348.8	349.9	356.2	365.3	376.5	389.4	405.8	422.0	438.3	455.4	473.1
155°	361.3	362.1	366.9	375.6	384.2	396.1	409.6	422.9	436.4	449.9	464.9
157.5°	371.8	372.6	376.4	383.9	390.9	400.8	412.3	422.9	432.8	444.2	457.2
160°	378.7	379.5	382.6	389.0	395.3	404.0	413.5	422.9	430.9	440.4	451.5
162.5°	385.6	385.2	388.3	393.4	399.1	405.9	414.2	422.3	429.0	437.2	446.4
165°	393.7	392.9	394.5	399.3	403.2	408.0	415.1	420.6	425.3	430.9	438.0
167.5°	400.4	399.4	400.8	403.9	406.7	409.7	414.9	419.5	421.7	425.3	429.8
170°	404.8	403.2	404.0	406.4	408.0	410.4	414.3	418.3	419.9	422.2	425.3
172.5°	407.3	406.4	405.9	408.3	409.2	411.0	413.7	416.4	417.3	418.4	421.0
175°	410.4	409.6	408.8	410.4	410.4	411.1	412.7	414.3	413.5	414.3	415.1
177.5°	411.8	410.5	409.9	411.1	411.1	411.1	411.8	413.0	411.8	411.1	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331728-927

CATALOG NUMBER: S122RDIP-S865D925U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6
2.5°	1156.0	1157.9	1159.8	1160.5	1160.2	1159.8	1159.4	1159.0
5°	1146.8	1148.9	1151.0	1151.8	1151.0	1150.3	1149.6	1148.9
7.5°	1128.3	1128.9	1129.5	1129.2	1128.0	1126.8	1125.5	1124.3
10°	1109.7	1109.0	1108.3	1107.2	1105.8	1104.5	1103.0	1101.6
12.5°	1088.4	1087.1	1085.8	1084.1	1081.7	1079.4	1077.1	1074.8
15°	1048.6	1044.2	1039.7	1036.3	1034.0	1031.7	1029.4	1027.0
17.5°	1003.6	998.3	993.1	988.4	984.4	980.4	976.4	972.3
20°	972.2	966.4	960.5	955.1	949.9	944.8	939.6	934.5
22.5°	937.8	930.3	922.7	917.0	913.2	909.3	905.5	901.7
25°	880.7	871.1	861.5	854.9	851.4	848.0	844.5	841.0
27.5°	826.2	815.0	803.8	795.5	790.0	784.3	778.8	773.2
30°	787.7	775.8	763.8	754.7	748.5	742.1	735.9	729.5
32.5°	749.0	735.4	721.8	712.0	706.2	700.2	694.3	688.3
35°	688.5	673.8	659.1	649.2	644.0	638.9	633.7	628.6
37.5°	629.6	613.4	597.2	586.1	580.3	574.3	568.5	562.6
40°	590.2	573.6	557.0	545.7	539.6	533.5	527.4	521.4
42.5°	550.4	533.2	516.1	504.5	498.7	492.8	486.9	481.0
45°	492.4	475.9	459.2	448.1	442.5	437.0	431.3	425.7
47.5°	436.0	419.5	403.1	392.3	387.2	382.1	377.0	371.9
50°	399.8	383.7	367.6	357.0	352.1	347.2	342.3	337.4
52.5°	365.6	350.1	334.5	324.5	319.9	315.4	310.9	306.3
55°	313.6	299.6	285.6	276.3	271.9	267.4	263.0	258.6
57.5°	266.3	253.5	240.7	232.3	228.6	224.8	221.1	217.4
60°	233.7	221.8	209.8	202.1	198.3	194.6	190.8	187.1
62.5°	205.4	194.1	182.7	175.9	173.6	171.4	169.1	166.9
65°	167.0	159.1	151.1	146.8	146.1	145.4	144.7	144.0
67.5°	134.8	131.2	127.5	125.3	124.6	123.8	123.1	122.4
70°	117.2	114.9	112.6	111.0	110.0	109.1	108.1	107.2
72.5°	102.0	100.1	98.1	96.9	96.3	95.7	95.1	94.6
75°	80.8	79.2	77.6	76.6	76.4	76.1	75.9	75.7
77.5°	61.2	60.3	59.3	58.7	58.3	57.9	57.6	57.2
80°	48.6	47.7	46.7	46.3	46.3	46.3	46.3	46.3
82.5°	36.8	36.1	35.6	35.3	35.3	35.3	35.3	35.3
85°	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0
87.5°	11.4	10.9	11.0	11.1	11.1	11.1	11.1	11.1
90°	25.3	23.7	25.3	26.1	26.1	26.1	26.1	26.1
92.5°	68.9	59.2	52.5	47.6	47.0	44.4	45.1	43.8
95°	207.2	158.9	125.7	108.3	98.1	91.7	89.4	90.2
97.5°	483.4	395.5	309.9	252.9	215.1	195.6	184.0	177.4
100°	721.8	623.8	515.5	419.9	354.2	320.2	297.3	283.0
102.5°	878.1	856.0	776.7	675.3	604.0	546.0	517.4	498.1
105°	960.6	1050.0	1060.3	1034.1	985.1	936.1	902.1	891.0
107.5°	901.2	1035.7	1117.9	1156.2	1162.4	1159.7	1152.9	1138.2
110°	849.9	991.4	1092.7	1157.5	1191.4	1206.5	1213.6	1212.8



TEST NUMBER: P331728-927

CATALOG NUMBER: S122RDIP-S865D925U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	803.1	939.0	1047.1	1121.4	1168.7	1193.8	1207.3	1211.6
115°	745.5	867.3	970.9	1052.3	1108.4	1144.8	1165.4	1172.5
117.5°	702.2	809.1	903.0	979.5	1036.6	1075.1	1096.8	1102.7
120°	680.7	778.8	862.5	934.5	989.8	1027.0	1050.0	1057.9
122.5°	663.6	753.4	832.8	897.9	947.5	984.0	1004.4	1011.1
125°	638.8	720.3	789.8	849.1	895.0	925.0	944.8	951.1
127.5°	614.3	688.0	753.6	808.3	848.3	876.5	893.6	898.7
130°	598.5	666.5	729.0	781.2	819.9	846.8	862.5	868.9
132.5°	583.3	646.3	703.6	752.7	790.8	817.7	832.2	837.9
135°	562.1	614.3	666.5	710.7	744.7	770.9	785.1	788.2
137.5°	545.2	588.8	630.3	668.8	699.9	722.3	734.8	739.6
140°	534.5	572.4	608.8	643.6	668.8	689.4	701.3	706.0
142.5°	525.6	557.9	589.1	618.3	642.3	661.0	671.5	672.5
145°	513.1	539.2	563.7	586.6	605.6	619.1	626.9	629.3
147.5°	503.4	524.0	543.1	559.9	575.6	586.3	591.7	593.1
150°	496.5	513.9	530.5	544.7	556.6	566.1	570.8	571.6
152.5°	489.6	505.6	519.8	532.1	541.4	549.6	553.1	553.3
155°	479.9	492.6	504.4	513.1	521.8	527.4	530.5	528.9
157.5°	468.7	479.3	489.3	496.1	502.2	506.8	508.2	508.2
160°	461.7	470.4	479.1	484.7	490.2	494.2	495.0	495.0
162.5°	454.8	462.2	469.6	473.9	479.4	482.1	482.9	482.3
165°	444.3	449.9	455.4	458.6	461.7	464.9	464.9	464.1
167.5°	434.4	438.6	442.4	445.3	446.7	448.5	448.3	447.3
170°	429.3	431.7	434.8	436.4	437.2	439.6	438.8	437.2
172.5°	423.6	425.3	427.9	428.8	429.6	430.7	429.9	429.0
175°	417.5	418.3	419.1	419.9	419.9	420.6	419.9	418.3
177.5°	413.0	413.0	413.7	413.7	413.7	413.7	413.0	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1

(END OF REPORT)