

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331309-940

Luminaire Tested: **S122DIP-S485D725U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331309-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S485D725U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4347.6 lumens
Efficiency: N/A
Efficacy: 113.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331309-940

CATALOG NUMBER: S122DIP-S485D725U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331309-940

CATALOG NUMBER: S122DIP-S485D725U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41
1	96	91	88	84	87	83	80	77	68	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	34	29
3	79	70	63	57	72	64	58	53	53	48	45	42	39	36	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	60	51	44	38	42	37	33	34	30	27	26	24	22	18
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	45	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	30	26	31	26	22	25	21	19	20	17	15	13
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11183	11183	11183
5°	11225	11063	11128
10°	11158	10952	11006
15°	11020	10810	10798
20°	10825	10596	10584
25°	10630	10334	10334
30°	10381	10094	10006
35°	10147	9806	9662
40°	9853	9518	9333
45°	9565	9229	9001
50°	9251	8932	8616
55°	8923	8586	8267
60°	8557	8173	7869
65°	8164	7759	7404
70°	7671	7260	6916
75°	6981	6687	6525
80°	6192	6007	5700
85°	5057	4798	4316



TEST NUMBER: P331309-940

CATALOG NUMBER: S122DIP-S485D725U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.1	1.5
10°-20°	183.3	4.2
20°-30°	269.4	6.2
30°-40°	312.9	7.2
40°-50°	312.5	7.2
50°-60°	272.6	6.3
60°-70°	201.5	4.6
70°-80°	114.1	2.6
80°-90°	32.9	0.8
90°-100°	29.4	0.7
100°-110°	107.8	2.5
110°-120°	288.3	6.6
120°-130°	475.8	10.9
130°-140°	506.0	11.6
140°-150°	470.3	10.8
150°-160°	378.1	8.7
160°-170°	243.7	5.6
170°-180°	83.9	1.9
0°-30°	517.7	11.9
0°-40°	830.6	19.1
0°-60°	1415.7	32.6
0°-90°	1764.2	40.6
90°-120°	425.5	9.8
90°-150°	1877.7	43.2
90°-180°	2583.0	59.4
0°-180°	4347.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	693	693	693	693	693	
5°	693	690	683	688	687	66
15°	659	655	647	649	646	186
25°	597	591	580	581	580	274
35°	515	508	498	494	490	321
45°	419	414	404	397	394	323
55°	317	313	305	297	294	283
65°	214	210	203	197	194	211
75°	112	110	107	104	105	120
85°	27	27	26	24	23	31
90°	1	8	13	16	17	3
95°	42	22	25	28	28	51
105°	194	202	39	46	48	207
115°	367	378	394	112	52	361
125°	519	527	539	543	545	462
135°	642	652	658	664	663	495
145°	744	744	755	759	756	465
155°	820	815	822	825	820	378
165°	864	860	862	866	862	244
175°	883	879	880	884	878	84
180°	882	882	882	882	882	



TEST NUMBER: P331309-940

CATALOG NUMBER: S122DIP-S485D725U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6
2.5°	695.8	695.2	694.6	694.0	693.4	692.5	691.2	689.9	688.6	687.2	688.5
5°	692.6	692.0	691.4	690.8	690.3	689.1	687.5	685.9	684.2	682.6	683.8
7.5°	686.4	685.5	684.7	683.7	682.8	681.5	679.8	678.2	676.5	674.8	676.1
10°	680.6	679.6	678.5	677.5	676.5	675.0	673.2	671.5	669.8	668.0	669.1
12.5°	672.6	671.7	670.7	669.9	669.0	667.6	665.8	664.1	662.3	660.5	661.3
15°	659.3	658.4	657.5	656.7	655.8	654.3	652.4	650.5	648.5	646.7	647.2
17.5°	642.2	641.4	640.5	639.6	638.7	637.3	635.3	633.4	631.4	629.5	630.2
20°	630.0	629.1	628.2	627.3	626.4	625.0	622.9	620.8	618.8	616.7	617.2
22.5°	617.8	616.5	615.3	614.0	612.8	611.2	609.2	607.3	605.3	603.3	603.4
25°	596.7	595.5	594.3	593.2	592.0	590.1	587.6	585.1	582.6	580.1	580.3
27.5°	572.7	571.7	570.6	569.5	568.5	566.9	565.0	562.9	561.0	559.0	558.6
30°	556.8	555.5	554.4	553.2	552.0	550.3	548.0	545.9	543.7	541.4	541.0
32.5°	539.7	538.8	537.8	536.8	535.9	534.2	531.9	529.6	527.3	525.0	524.1
35°	514.8	513.3	511.8	510.3	508.9	506.9	504.6	502.2	499.8	497.5	496.6
37.5°	486.7	485.4	484.1	482.8	481.4	479.7	477.2	474.9	472.5	470.2	469.0
40°	467.5	466.3	465.1	464.0	462.8	461.0	458.6	456.3	453.9	451.6	450.2
42.5°	448.9	447.6	446.5	445.3	444.2	442.4	440.0	437.7	435.2	432.8	431.4
45°	418.9	417.9	416.8	415.8	414.7	413.1	410.9	408.7	406.4	404.2	402.6
47.5°	389.1	388.1	387.1	386.1	385.1	383.5	381.2	378.9	376.6	374.3	372.6
50°	368.3	367.6	366.8	366.0	365.3	363.9	361.9	359.8	357.7	355.6	353.6
52.5°	348.0	347.1	346.1	345.1	344.1	342.7	340.7	338.8	336.8	334.8	333.1
55°	317.0	316.1	315.2	314.3	313.4	312.1	310.3	308.5	306.7	305.0	303.3
57.5°	285.8	285.1	284.4	283.7	283.0	281.7	279.7	277.8	275.8	273.8	272.1
60°	265.0	264.5	263.9	263.2	262.7	261.4	259.3	257.2	255.1	253.1	251.5
62.5°	244.8	243.9	242.9	241.9	241.0	239.8	238.2	236.6	235.0	233.4	231.8
65°	213.7	212.9	212.0	211.1	210.3	209.0	207.6	206.1	204.6	203.1	201.8
67.5°	182.2	181.5	180.7	180.0	179.3	178.3	177.0	175.7	174.3	173.0	172.0
70°	162.5	161.9	161.3	160.7	160.2	159.2	157.8	156.5	155.2	153.8	152.8
72.5°	142.2	141.7	141.1	140.4	139.9	139.2	138.3	137.4	136.6	135.7	134.6
75°	111.9	111.6	111.3	111.0	110.7	110.2	109.4	108.7	108.0	107.2	106.3
77.5°	84.7	84.2	83.7	83.2	82.7	82.3	82.0	81.7	81.4	81.1	80.7
80°	66.6	66.4	66.3	66.2	66.0	65.8	65.5	65.2	64.9	64.6	64.1
82.5°	49.6	49.5	49.5	49.5	49.4	49.3	49.1	49.0	48.8	48.6	48.1
85°	27.3	27.2	27.0	26.8	26.8	26.6	26.4	26.3	26.1	25.9	25.5
87.5°	9.7	9.8	9.9	10.0	10.0	10.1	10.1	10.0	10.0	10.0	9.8
90°	0.6	2.2	3.7	5.4	6.9	8.2	9.4	10.5	11.6	12.8	13.5
92.5°	12.8	12.8	12.6	12.5	12.3	12.6	13.1	13.6	14.3	14.8	15.2
95°	41.5	36.8	32.1	27.5	22.7	20.9	21.9	22.9	23.9	24.9	25.6
97.5°	82.3	69.1	55.9	42.7	29.5	24.1	26.4	28.7	31.0	33.3	33.9
100°	112.9	93.5	74.1	54.7	35.2	26.8	29.2	31.6	34.0	36.4	37.5
102.5°	146.6	142.5	138.4	134.3	130.1	118.0	97.8	77.7	57.5	37.4	38.9
105°	193.9	198.1	202.4	206.7	210.9	193.7	155.0	116.3	77.6	38.9	40.5
107.5°	247.9	251.3	254.8	258.2	261.6	240.1	193.7	147.3	100.9	54.5	52.9
110°	282.6	285.5	288.6	291.5	294.4	275.4	234.5	193.6	152.6	111.6	97.5



TEST NUMBER: P331309-940

CATALOG NUMBER: S122DIP-S485D725U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	315.2	317.9	320.5	323.2	325.7	322.0	311.9	301.8	291.7	281.5	229.9
115°	366.8	369.2	371.6	374.0	376.4	379.4	382.9	386.5	390.0	393.6	328.0
117.5°	412.9	415.5	418.2	420.9	423.6	426.1	428.6	431.1	433.5	436.0	420.1
120°	446.5	448.6	450.8	452.9	455.0	457.4	459.9	462.4	465.0	467.5	469.2
122.5°	475.1	477.3	479.6	481.8	484.0	486.5	489.4	492.1	494.9	497.7	498.6
125°	518.6	520.4	522.3	524.1	525.9	528.2	530.9	533.6	536.3	539.0	540.0
127.5°	558.0	560.1	562.1	564.1	566.1	568.2	570.2	572.2	574.3	576.2	577.7
130°	583.0	585.3	587.5	589.8	592.1	594.0	595.6	597.1	598.7	600.2	601.8
132.5°	608.5	610.5	612.4	614.3	616.3	618.0	619.6	621.1	622.7	624.2	625.5
135°	641.7	644.0	646.2	648.5	650.8	652.6	653.8	655.1	656.4	657.6	659.1
137.5°	675.3	676.8	678.4	680.0	681.6	683.1	684.6	686.0	687.4	688.9	690.3
140°	697.2	698.3	699.5	700.6	701.7	703.1	704.6	706.2	707.8	709.4	710.6
142.5°	715.6	716.6	717.6	718.6	719.6	721.0	722.8	724.6	726.4	728.2	729.3
145°	744.4	744.2	744.1	744.0	743.9	744.9	747.3	749.8	752.2	754.6	755.6
147.5°	769.5	769.0	768.5	767.9	767.4	768.3	770.7	773.0	775.4	777.8	778.6
150°	785.9	784.9	783.9	782.9	781.9	782.6	784.8	787.0	789.3	791.6	792.5
152.5°	799.6	798.5	797.5	796.3	795.2	795.8	797.9	800.0	802.2	804.3	805.2
155°	819.7	818.4	817.1	815.8	814.6	814.8	816.5	818.1	819.8	821.5	822.4
157.5°	835.4	834.3	833.2	832.1	831.1	831.1	832.3	833.5	834.6	835.9	836.9
160°	844.5	843.6	842.8	842.0	841.2	841.2	842.0	842.8	843.6	844.5	845.4
162.5°	852.7	851.9	851.0	850.2	849.3	849.3	850.0	850.7	851.5	852.2	853.2
165°	863.7	862.8	862.0	861.1	860.2	860.1	860.5	860.9	861.3	861.7	862.7
167.5°	871.8	871.0	870.1	869.3	868.4	868.2	868.6	869.0	869.4	869.8	870.8
170°	876.5	875.6	874.8	873.9	873.1	872.7	873.1	873.3	873.6	873.9	874.9
172.5°	879.5	878.6	877.8	876.9	876.1	875.8	876.1	876.4	876.6	876.9	878.0
175°	883.4	882.4	881.5	880.5	879.5	879.1	879.4	879.7	879.9	880.3	881.3
177.5°	884.1	883.3	882.5	881.7	880.9	880.6	880.7	880.8	880.9	881.0	881.8
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331309-940

CATALOG NUMBER: S122DIP-S485D725U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6
2.5°	689.6	690.8	692.0	692.5	692.2	692.0	691.8	691.5
5°	685.0	686.2	687.3	687.8	687.5	687.2	686.9	686.6
7.5°	677.3	678.4	679.7	680.0	679.8	679.4	679.0	678.8
10°	670.3	671.5	672.7	673.1	672.6	672.2	671.7	671.3
12.5°	662.2	663.0	663.8	664.1	663.7	663.4	663.1	662.7
15°	647.8	648.5	649.0	648.9	648.2	647.5	646.8	646.0
17.5°	630.8	631.5	632.2	632.1	631.4	630.8	630.1	629.4
20°	617.6	618.0	618.5	618.4	617.8	617.2	616.6	616.0
22.5°	603.5	603.6	603.7	603.6	603.2	602.9	602.5	602.2
25°	580.7	580.9	581.2	581.2	580.9	580.7	580.3	580.1
27.5°	558.1	557.7	557.2	556.7	556.0	555.3	554.6	553.8
30°	540.6	540.1	539.7	539.1	538.5	538.0	537.3	536.7
32.5°	523.3	522.5	521.7	521.0	520.4	519.9	519.2	518.6
35°	495.7	494.8	493.9	493.1	492.4	491.6	490.9	490.2
37.5°	468.0	466.9	465.8	464.8	464.1	463.4	462.7	462.1
40°	448.9	447.5	446.2	445.2	444.6	444.1	443.4	442.8
42.5°	430.0	428.6	427.0	426.0	425.1	424.3	423.5	422.6
45°	401.0	399.4	397.7	396.6	396.0	395.5	394.8	394.2
47.5°	370.9	369.1	367.4	366.1	365.2	364.4	363.6	362.7
50°	351.5	349.4	347.3	345.9	345.2	344.5	343.7	343.0
52.5°	331.4	329.7	328.0	326.6	325.7	324.7	323.7	322.7
55°	301.5	299.7	297.9	296.7	295.9	295.2	294.4	293.7
57.5°	270.4	268.6	266.9	265.7	265.1	264.6	264.0	263.4
60°	249.8	248.2	246.6	245.5	245.0	244.6	244.2	243.7
62.5°	230.3	228.8	227.3	226.3	225.7	225.2	224.6	224.0
65°	200.5	199.1	197.8	196.7	196.0	195.3	194.6	193.8
67.5°	170.9	169.9	168.9	168.1	167.5	166.8	166.3	165.7
70°	151.8	150.7	149.7	148.9	148.3	147.7	147.1	146.5
72.5°	133.7	132.6	131.6	130.8	130.4	129.8	129.4	128.9
75°	105.4	104.6	103.7	103.3	103.7	104.0	104.2	104.6
77.5°	80.3	79.8	79.4	78.9	78.5	78.1	77.7	77.2
80°	63.7	63.2	62.9	62.4	62.2	61.9	61.5	61.3
82.5°	47.5	46.9	46.4	46.0	46.0	45.9	45.8	45.8
85°	25.1	24.6	24.2	23.9	23.7	23.6	23.5	23.3
87.5°	9.5	9.4	9.2	9.0	8.9	8.9	8.8	8.7
90°	14.2	14.9	15.6	16.1	16.4	16.7	16.9	17.2
92.5°	15.5	15.9	16.2	16.6	16.7	16.9	17.0	17.2
95°	26.3	27.0	27.7	28.0	27.8	27.7	27.6	27.5
97.5°	34.4	35.0	35.6	35.9	36.1	36.3	36.5	36.6
100°	38.6	39.8	40.9	41.6	41.9	42.2	42.4	42.7
102.5°	40.3	41.8	43.2	44.2	44.6	45.0	45.4	45.8
105°	42.0	43.6	45.1	46.2	46.8	47.3	47.9	48.5
107.5°	51.3	49.7	48.2	47.6	48.2	48.8	49.3	49.8
110°	83.3	69.1	54.9	48.2	48.7	49.2	49.8	50.4



TEST NUMBER: P331309-940

CATALOG NUMBER: S122DIP-S485D725U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	178.2	126.4	74.7	49.0	49.6	50.0	50.5	50.9
115°	262.3	196.7	131.1	93.1	82.9	72.7	62.5	52.3
117.5°	404.2	388.3	372.4	347.7	314.1	280.6	247.1	213.6
120°	471.0	472.7	474.4	465.7	446.5	427.4	408.2	389.1
122.5°	499.7	500.7	501.8	500.4	496.7	492.9	489.3	485.5
125°	541.0	542.0	543.0	543.7	544.1	544.6	544.9	545.4
127.5°	579.2	580.6	582.0	582.8	582.9	583.0	583.1	583.2
130°	603.3	604.9	606.5	607.2	607.1	606.9	606.7	606.6
132.5°	626.9	628.2	629.5	630.2	630.0	629.9	629.7	629.5
135°	660.5	661.9	663.3	663.9	663.6	663.3	663.0	662.7
137.5°	691.7	693.0	694.5	694.9	694.5	693.9	693.5	692.9
140°	711.9	713.1	714.4	714.7	714.0	713.3	712.6	711.9
142.5°	730.5	731.6	732.8	733.1	732.4	731.6	730.9	730.2
145°	756.6	757.6	758.6	758.7	758.0	757.3	756.6	755.9
147.5°	779.3	780.1	780.8	780.9	780.2	779.6	779.1	778.5
150°	793.3	794.2	795.0	795.0	794.3	793.6	792.9	792.2
152.5°	806.0	806.9	807.8	807.7	806.8	805.8	804.9	804.0
155°	823.3	824.1	825.0	824.8	823.7	822.6	821.4	820.3
157.5°	837.8	838.7	839.7	839.6	838.6	837.4	836.3	835.3
160°	846.2	847.1	847.9	847.8	846.9	845.9	844.9	843.9
162.5°	854.1	855.1	856.0	856.0	854.7	853.5	852.3	851.0
165°	863.7	864.8	865.8	865.8	864.8	863.7	862.7	861.7
167.5°	871.8	872.8	873.8	873.6	872.4	871.1	869.8	868.5
170°	875.8	876.8	877.9	877.7	876.5	875.1	873.9	872.6
172.5°	879.0	879.9	880.9	880.7	879.5	878.2	876.9	875.7
175°	882.3	883.2	884.2	884.0	882.6	881.2	879.8	878.3
177.5°	882.6	883.4	884.2	884.1	883.1	882.1	881.0	880.0
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5

(END OF REPORT)