

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331341-940

Luminaire Tested: **S122DIP-S675D530U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331341-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S675D530U940-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4455.6 lumens  
Efficiency: N/A  
Efficacy: 110.6 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331341-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331341-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59				
1	100	96	92	89	93	90	87	84	78	76	74	67	66	64	58	56	55	51				
2	92	85	79	74	85	79	74	70	69	65	62	60	57	54	51	49	47	43				
3	84	75	68	62	78	70	64	59	62	57	53	53	50	47	46	43	41	37				
4	77	67	59	53	72	63	56	50	55	50	45	48	44	41	41	38	36	33				
5	71	60	52	46	66	56	49	44	50	44	40	43	39	36	38	34	32	29				
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	34	31	28	25				
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23				
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21				
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	23	21	19				
10	50	38	31	26	46	36	29	25	32	27	23	28	24	21	25	22	19	17				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	19125	19125	19125	19125
5°	21441	19248	17057	19248
10°	24568	19090	14762	19090
15°	27178	18740	13041	18740
20°	26764	18364	11888	18364
25°	24134	17865	11158	17865
30°	19943	17066	10625	17066
35°	14534	16232	10247	16232
40°	11609	15247	10037	15247
45°	10145	14104	9750	14104
50°	9535	12999	9560	12999
55°	8791	11879	9303	11879
60°	8054	10685	8909	10685
65°	7339	9616	8520	9616
70°	6661	8573	7950	8573
75°	5908	7411	7043	7411
80°	5086	6137	5672	6137
85°	4557	4557	3372	4557



TEST NUMBER: P331341-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	112.8	2.5
10°-20°	327.9	7.4
20°-30°	475.9	10.7
30°-40°	502.2	11.3
40°-50°	444.7	10.0
50°-60°	354.9	8.0
60°-70°	241.2	5.4
70°-80°	123.7	2.8
80°-90°	32.2	0.7
90°-100°	105.7	2.4
100°-110°	358.8	8.1
110°-120°	381.2	8.6
120°-130°	313.8	7.0
130°-140°	252.0	5.7
140°-150°	190.4	4.3
150°-160°	133.8	3.0
160°-170°	78.8	1.8
170°-180°	25.6	0.6
0°-30°	916.7	20.6
0°-40°	1418.9	31.8
0°-60°	2218.4	49.8
0°-90°	2615.5	58.7
90°-120°	845.7	19.0
90°-150°	1601.9	36.0
90°-180°	1840.0	41.3
0°-180°	4455.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1184	1184	1184	1184	1184	
5°	1323	1188	1052	1188	1323	132
15°	1626	1121	780	1121	1626	449
25°	1355	1003	626	1003	1355	612
35°	737	824	520	824	737	480
45°	444	618	427	618	444	349
55°	312	422	330	422	312	280
65°	192	252	223	252	192	191
75°	95	119	113	119	95	101
85°	25	25	18	25	25	27
90°	17	0	17	0	17	10
95°	58	18	58	18	58	75
105°	573	62	573	62	573	555
115°	754	109	754	109	754	738
125°	612	153	612	153	612	553
135°	507	179	507	179	507	394
145°	405	204	405	204	405	257
155°	340	232	340	232	340	159
165°	298	253	298	253	298	85
175°	269	264	269	264	269	26
180°	264	264	264	264	264	



TEST NUMBER: P331341-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1239.0	1239.4	1240.2	1234.3	1233.6	1233.6	1228.5	1224.1	1219.1	1212.1	1212.8
5°	1322.9	1327.8	1329.6	1324.2	1316.0	1315.1	1307.3	1294.6	1282.7	1273.2	1266.4
7.5°	1422.8	1424.8	1420.3	1413.1	1407.0	1396.2	1381.7	1367.6	1347.8	1329.7	1316.3
10°	1498.5	1501.3	1493.5	1483.1	1474.4	1461.7	1440.7	1419.3	1393.4	1368.3	1348.3
12.5°	1556.0	1562.8	1552.9	1551.5	1536.7	1519.2	1494.2	1483.5	1446.9	1412.0	1390.5
15°	1625.9	1625.5	1626.5	1617.8	1606.9	1604.1	1577.7	1549.1	1497.6	1477.1	1441.6
17.5°	1605.8	1612.7	1615.9	1615.8	1615.5	1613.8	1605.3	1587.2	1561.5	1528.2	1487.2
20°	1557.7	1566.8	1568.2	1578.7	1584.6	1592.3	1595.4	1590.5	1574.6	1546.8	1511.3
22.5°	1483.5	1485.9	1490.2	1506.5	1519.4	1538.7	1548.9	1565.8	1559.6	1546.0	1516.4
25°	1354.7	1350.1	1366.1	1374.2	1403.8	1434.8	1457.1	1481.7	1503.5	1516.7	1508.1
27.5°	1200.1	1193.3	1217.1	1238.9	1262.9	1296.5	1331.2	1372.3	1406.4	1449.1	1463.7
30°	1069.7	1073.8	1096.6	1119.8	1156.2	1203.5	1242.7	1287.8	1336.5	1384.3	1417.5
32.5°	929.2	944.9	959.3	994.9	1026.9	1079.8	1137.1	1193.5	1254.2	1308.5	1359.9
35°	737.4	755.6	775.7	801.6	846.7	899.0	955.0	1031.0	1113.9	1188.1	1249.1
37.5°	620.7	617.8	629.3	648.0	684.6	726.7	791.2	866.4	963.9	1051.1	1137.1
40°	550.8	548.9	557.1	574.4	602.3	633.2	689.6	755.6	846.2	952.7	1055.2
42.5°	502.7	503.8	508.4	520.6	539.6	565.1	607.3	663.5	746.5	846.8	956.8
45°	444.3	447.5	452.5	458.4	469.3	490.3	513.9	554.0	619.6	703.3	811.6
47.5°	402.3	402.3	407.4	412.6	419.1	430.9	450.2	475.3	521.6	589.8	682.9
50°	379.6	376.5	380.1	384.1	391.0	399.2	412.0	435.6	466.5	521.7	599.5
52.5°	352.0	352.0	355.3	356.9	363.0	371.1	382.8	399.2	427.2	470.3	534.3
55°	312.3	314.5	316.4	319.1	324.6	330.5	339.6	350.5	372.4	404.7	452.0
57.5°	274.9	275.6	277.5	282.7	286.1	291.6	300.2	310.1	324.4	348.3	383.9
60°	249.4	249.4	253.1	255.4	259.9	265.4	272.2	281.8	294.5	314.1	342.8
62.5°	226.1	225.8	227.2	231.0	234.4	239.5	246.4	254.5	266.4	283.8	307.5
65°	192.1	191.2	193.9	194.8	198.5	203.5	208.9	217.6	227.1	239.9	260.8
67.5°	159.3	160.4	161.8	163.6	165.6	170.9	174.5	180.7	188.7	199.3	213.5
70°	141.1	141.1	141.1	142.5	145.2	147.9	151.6	156.6	164.3	173.4	186.2
72.5°	120.7	122.2	123.6	122.8	126.3	127.9	132.2	135.1	142.5	148.3	159.6
75°	94.7	94.7	94.7	96.9	98.4	99.7	102.5	105.1	108.8	116.1	122.0
77.5°	70.6	70.4	70.9	71.4	72.9	74.5	75.3	77.8	81.2	84.5	89.6
80°	54.7	55.6	56.0	56.9	56.9	57.8	58.2	61.4	63.8	66.0	69.2
82.5°	42.3	42.4	42.5	42.7	43.1	43.6	44.8	45.8	46.6	48.5	51.0
85°	24.6	24.2	24.2	25.1	24.6	24.6	25.5	26.4	26.4	26.8	28.2
87.5°	12.8	12.8	13.2	12.8	12.8	13.1	12.8	12.8	13.2	13.6	13.9
90°	16.8	16.8	16.8	16.8	16.8	16.2	15.2	16.2	16.8	17.3	16.8
92.5°	28.2	29.0	28.6	30.2	30.6	33.8	38.1	44.3	55.8	66.1	65.2
95°	58.0	57.4	59.0	63.0	69.6	80.9	102.2	133.2	174.4	199.4	176.5
97.5°	114.1	118.4	125.8	138.3	162.6	199.4	254.4	310.9	357.0	340.3	256.3
100°	182.1	191.2	206.0	227.8	270.0	331.5	401.3	464.3	474.9	401.7	276.6
102.5°	320.4	332.8	351.2	388.5	434.4	499.6	550.5	564.8	518.9	403.8	268.9
105°	573.1	580.2	602.1	633.6	665.1	682.0	675.3	617.9	512.1	376.8	253.8
107.5°	732.1	741.5	745.9	747.6	743.7	719.1	666.2	579.6	467.4	347.9	246.2
110°	780.1	780.6	776.1	766.3	744.5	702.8	637.7	546.7	439.3	334.1	244.6



TEST NUMBER: P331341-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	779.3	776.5	767.9	751.7	721.3	673.5	604.0	516.6	419.8	325.1	245.0
115°	754.1	749.6	736.4	712.9	676.9	624.5	557.9	479.6	395.7	315.3	247.2
117.5°	709.3	705.4	691.5	666.8	630.0	580.9	520.4	451.7	380.4	310.5	250.8
120°	680.4	675.3	660.6	636.7	601.1	554.8	500.9	437.8	372.3	307.6	253.2
122.5°	650.3	646.0	632.9	609.4	577.5	535.7	484.6	426.9	365.3	306.0	256.1
125°	611.8	607.7	594.9	575.7	546.2	508.0	463.2	410.9	355.4	303.1	260.4
127.5°	578.0	574.7	563.7	545.6	520.0	484.7	442.6	395.1	346.3	301.4	264.7
130°	558.8	554.8	544.7	527.4	502.4	468.9	428.7	385.0	340.2	300.5	268.0
132.5°	539.0	535.3	525.9	508.6	484.1	452.6	415.7	375.2	335.3	300.1	271.3
135°	507.0	505.0	495.8	479.0	457.2	428.7	395.1	361.6	328.5	299.5	275.1
137.5°	475.6	472.6	464.6	450.1	430.3	405.4	378.8	350.7	323.7	299.4	278.6
140°	454.1	451.0	443.4	430.3	413.9	391.6	368.2	343.8	320.9	299.0	280.2
142.5°	432.6	431.9	425.2	413.1	397.7	379.0	358.8	338.0	318.1	299.0	281.4
145°	404.7	403.2	398.1	389.5	377.4	362.6	346.8	330.0	314.2	298.0	282.8
147.5°	381.5	380.6	377.1	370.2	360.2	349.4	337.1	323.9	310.4	296.1	283.1
150°	367.7	367.1	364.1	358.0	350.4	341.3	330.6	319.3	307.2	295.0	282.8
152.5°	355.9	355.8	353.6	348.2	342.2	334.3	325.3	314.9	304.3	292.9	282.0
155°	340.2	341.3	339.2	335.6	330.0	324.4	316.8	308.7	299.0	289.4	280.7
157.5°	326.9	326.9	326.0	323.0	319.1	314.7	308.3	301.5	294.0	285.7	278.4
160°	318.3	318.3	317.8	315.3	311.7	308.2	302.6	296.9	290.3	283.3	277.1
162.5°	310.2	310.6	310.1	308.4	304.8	302.1	297.3	292.5	287.1	281.2	275.9
165°	298.5	299.0	299.0	296.9	295.0	292.9	289.4	285.8	281.7	277.1	273.6
167.5°	287.8	288.4	288.5	287.3	286.4	284.5	282.1	279.4	276.4	273.6	271.3
170°	281.2	282.2	282.8	281.2	280.7	279.7	277.7	276.2	273.6	271.5	270.0
172.5°	275.9	276.5	277.1	276.3	275.8	275.2	273.6	272.5	270.7	269.1	268.4
175°	269.0	270.0	270.5	270.0	270.0	269.6	269.0	268.5	267.0	266.4	266.0
177.5°	264.8	265.6	266.1	266.1	266.1	266.1	265.6	265.6	264.8	264.4	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331341-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1215.4	1212.5	1210.7	1204.1	1198.3	1192.5	1190.6	1191.3	1183.4	1175.7	1172.4
5°	1262.8	1253.7	1245.0	1232.7	1218.2	1202.2	1194.0	1187.6	1171.7	1154.4	1144.4
7.5°	1305.2	1292.2	1275.5	1252.3	1231.2	1206.1	1190.2	1176.1	1152.7	1128.4	1113.4
10°	1331.1	1313.2	1291.8	1263.6	1237.7	1207.2	1185.8	1164.4	1137.1	1108.0	1089.8
12.5°	1353.3	1329.3	1308.2	1272.0	1241.4	1203.2	1177.8	1147.6	1118.9	1084.3	1066.5
15°	1406.1	1362.0	1321.9	1280.9	1243.1	1189.9	1161.7	1121.1	1083.3	1040.6	1020.1
17.5°	1447.0	1397.4	1334.3	1282.2	1238.1	1179.2	1137.7	1089.2	1044.6	995.6	967.8
20°	1470.3	1413.4	1345.6	1283.7	1230.8	1163.5	1118.5	1068.8	1016.5	961.4	931.3
22.5°	1484.2	1424.3	1357.3	1278.2	1216.3	1150.8	1094.0	1039.6	986.6	927.2	895.6
25°	1488.5	1433.9	1362.9	1273.6	1198.1	1123.9	1055.6	1002.8	938.6	883.1	837.1
27.5°	1466.9	1427.7	1359.4	1265.1	1177.1	1090.3	1014.2	954.4	886.6	826.3	780.2
30°	1440.3	1417.5	1351.0	1256.3	1160.3	1067.0	983.2	915.4	848.0	787.0	739.7
32.5°	1399.1	1394.2	1335.8	1243.9	1142.5	1037.5	950.8	882.3	807.6	747.7	702.6
35°	1318.3	1340.2	1303.2	1216.3	1108.8	995.5	901.8	823.5	746.1	688.8	646.4
37.5°	1210.0	1264.2	1254.5	1175.8	1063.5	949.9	846.3	764.5	690.7	632.8	591.3
40°	1135.2	1204.4	1214.5	1144.9	1031.5	914.5	804.8	723.4	651.4	598.6	556.7
42.5°	1055.2	1136.0	1163.5	1107.7	996.5	877.4	767.7	683.2	612.1	560.7	523.6
45°	920.9	1027.9	1077.5	1045.6	938.2	816.2	703.3	617.7	553.0	504.8	476.2
47.5°	795.3	912.2	978.9	967.7	873.3	752.4	640.9	558.7	495.8	457.3	431.6
50°	706.5	826.6	907.2	910.9	826.6	706.9	594.9	517.5	459.8	423.8	402.9
52.5°	629.3	744.0	831.9	851.1	774.5	659.6	553.8	476.8	425.9	392.8	374.1
55°	528.5	625.4	722.8	758.4	696.9	587.6	489.8	422.0	374.2	351.4	335.0
57.5°	439.3	520.2	610.2	649.4	611.5	518.0	426.2	367.4	328.6	308.6	296.0
60°	392.4	456.1	536.2	583.1	550.4	467.1	386.9	330.9	299.1	281.3	269.5
62.5°	348.7	405.1	472.9	515.8	497.9	419.4	347.6	298.2	270.6	254.0	245.5
65°	287.7	332.3	384.7	424.3	412.4	352.8	294.1	251.7	229.9	216.7	209.8
67.5°	236.9	269.1	305.4	340.1	330.6	288.3	241.2	208.2	191.9	180.6	176.5
70°	204.8	229.4	261.7	289.5	281.8	247.2	209.8	181.6	167.6	157.9	153.8
72.5°	174.2	194.5	219.1	241.8	236.6	207.9	176.7	155.4	144.5	135.7	132.3
75°	131.5	147.0	162.0	177.1	175.7	153.4	135.2	118.8	110.1	103.3	101.9
77.5°	97.1	105.8	116.0	124.9	122.4	109.7	95.4	86.1	79.6	75.1	74.4
80°	74.2	79.2	86.5	92.8	89.7	84.2	72.9	66.0	61.4	56.9	55.1
82.5°	53.8	58.9	63.2	66.6	64.2	59.1	52.1	47.4	44.7	41.6	40.8
85°	28.2	30.9	32.8	33.7	32.8	29.6	26.4	24.6	22.3	21.0	20.5
87.5°	13.6	12.9	12.5	12.8	11.6	11.4	9.5	8.1	8.0	8.1	7.6
90°	13.7	10.2	7.7	6.1	5.1	4.1	2.1	0.5	2.1	4.1	5.1
92.5°	50.7	34.6	23.1	18.3	14.9	12.6	8.9	6.2	8.9	12.6	14.9
95°	117.4	73.2	49.8	37.6	29.5	24.9	19.8	17.8	19.8	24.9	29.5
97.5°	158.3	96.7	67.2	53.4	44.1	37.1	31.7	29.0	31.7	37.1	44.1
100°	166.8	104.8	77.8	63.6	53.4	45.3	40.7	39.1	40.7	45.3	53.4
102.5°	167.2	112.1	87.1	72.9	62.3	54.2	49.7	48.5	49.7	54.2	62.3
105°	169.9	124.6	100.7	86.4	75.3	67.6	64.1	62.1	64.1	67.6	75.3
107.5°	176.8	137.4	114.2	99.9	88.8	81.8	78.3	76.7	78.3	81.8	88.8
110°	182.5	146.0	123.6	108.8	98.2	91.6	88.5	86.4	88.5	91.6	98.2





TEST NUMBER: P331341-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	188.7	154.1	132.5	117.3	107.1	100.9	97.5	95.4	97.5	100.9	107.1
115°	197.8	166.8	144.9	131.2	121.0	114.9	111.9	109.3	111.9	114.9	121.0
117.5°	207.6	178.5	158.3	144.0	134.3	128.9	125.8	123.8	125.8	128.9	134.3
120°	214.1	186.6	166.8	152.6	142.4	137.8	134.7	132.7	134.7	137.8	142.4
122.5°	219.8	194.4	175.8	161.1	151.0	146.0	142.9	141.2	142.9	146.0	151.0
125°	228.8	206.0	187.6	173.4	163.3	157.1	154.1	152.6	154.1	157.1	163.3
127.5°	237.3	216.8	198.9	184.3	174.5	167.8	163.5	161.5	163.5	167.8	174.5
130°	242.5	223.3	205.5	191.2	181.0	173.9	168.8	166.8	168.8	173.9	181.0
132.5°	247.9	228.9	212.0	197.7	187.2	179.6	174.2	171.7	174.2	179.6	187.2
135°	254.8	237.0	220.7	206.4	194.7	187.2	181.0	179.0	181.0	187.2	194.7
137.5°	260.0	243.5	227.4	214.2	202.6	194.5	188.3	185.9	188.3	194.5	202.6
140°	262.9	247.2	231.9	218.6	207.5	199.4	193.2	191.2	193.2	199.4	207.5
142.5°	265.4	250.0	235.1	222.7	212.0	203.8	198.1	196.5	198.1	203.8	212.0
145°	268.5	254.2	240.5	229.3	219.2	211.5	206.4	204.5	206.4	211.5	219.2
147.5°	270.3	257.7	244.8	234.9	226.4	219.4	214.5	212.9	214.5	219.4	226.4
150°	271.1	259.3	247.6	238.5	230.9	224.3	220.2	218.6	220.2	224.3	230.9
152.5°	271.4	261.0	250.5	242.2	235.0	229.2	225.1	224.4	225.1	229.2	235.0
155°	272.1	263.4	254.8	247.2	241.6	235.9	232.9	232.4	232.9	235.9	241.6
157.5°	272.1	265.1	257.8	251.5	246.9	242.1	239.6	239.1	239.6	242.1	246.9
160°	272.1	266.0	259.8	254.2	250.2	246.1	244.1	243.6	244.1	246.1	250.2
162.5°	271.6	266.4	261.1	256.7	253.1	249.8	247.7	248.1	247.7	249.8	253.1
165°	270.5	267.0	262.4	259.3	256.8	253.8	252.7	253.2	252.7	253.8	256.8
167.5°	269.8	266.9	263.5	261.6	259.8	257.8	256.9	257.5	256.9	257.8	259.8
170°	269.0	266.4	263.9	262.4	261.4	259.8	259.3	260.4	259.3	259.8	261.4
172.5°	267.8	266.1	264.3	263.2	262.6	261.1	261.4	262.0	261.4	261.1	262.6
175°	266.4	265.5	264.4	263.9	263.9	262.9	263.4	263.9	263.4	262.9	263.9
177.5°	265.6	264.8	264.4	264.4	264.4	263.6	264.0	264.8	264.0	263.6	264.4
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331341-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1168.8	1166.6	1159.0	1154.9	1148.3	1142.2	1138.2	1140.1	1141.5	1140.8	1139.6
5°	1135.2	1126.6	1113.4	1102.1	1093.9	1078.8	1072.5	1069.3	1066.6	1063.4	1060.2
7.5°	1095.4	1081.7	1062.8	1046.6	1031.3	1012.6	1002.0	995.6	989.1	981.9	975.5
10°	1067.0	1047.8	1027.9	1005.0	986.9	970.0	955.0	945.0	935.9	927.3	920.9
12.5°	1037.1	1015.1	990.3	959.2	939.1	915.1	912.8	895.1	880.9	875.6	868.1
15°	989.6	958.7	927.3	890.4	874.4	852.6	838.9	825.3	813.0	804.3	802.1
17.5°	935.6	895.5	864.3	837.9	811.7	789.3	776.8	765.8	755.7	744.1	742.6
20°	894.5	859.9	825.7	802.5	775.7	752.9	737.4	726.5	717.8	711.1	705.1
22.5°	855.5	817.6	786.4	761.0	734.5	716.1	703.9	693.4	686.2	678.6	673.1
25°	793.0	763.4	729.2	700.5	678.7	666.9	656.8	647.7	643.2	638.2	631.9
27.5°	738.2	705.3	673.4	651.2	632.0	621.5	614.4	608.2	604.0	601.0	597.4
30°	699.6	666.4	641.4	619.6	603.6	593.2	588.6	585.0	580.0	578.1	576.3
32.5°	662.5	632.6	611.2	592.2	577.0	570.2	566.0	562.8	558.8	557.0	553.3
35°	609.9	585.0	564.0	553.5	541.3	535.3	532.2	527.5	524.0	522.1	521.7
37.5°	560.5	538.8	525.0	511.6	506.4	502.7	498.4	495.3	494.2	493.9	493.5
40°	528.5	510.8	498.5	487.5	485.3	479.7	476.2	473.4	473.4	473.9	473.4
42.5°	499.4	483.4	472.6	463.2	460.5	457.2	453.5	453.3	454.1	455.7	454.1
45°	455.2	443.8	436.0	431.5	426.5	423.3	422.8	424.3	424.7	425.2	426.5
47.5°	414.6	407.1	400.0	395.0	392.8	392.3	391.7	394.1	396.3	397.1	399.2
50°	390.6	381.9	376.0	372.8	371.0	370.1	371.0	373.7	375.5	377.8	379.2
52.5°	363.6	357.5	353.4	351.0	350.3	350.8	351.0	354.1	357.0	357.8	358.5
55°	326.4	321.8	320.9	316.8	318.6	318.2	320.5	322.3	325.0	327.7	328.2
57.5°	289.3	285.6	283.1	283.5	284.0	286.1	287.9	291.1	294.1	296.9	297.2
60°	264.5	262.6	261.3	261.3	262.2	264.9	267.2	270.4	272.2	274.0	275.4
62.5°	241.9	240.0	238.7	239.4	241.8	243.4	246.1	247.8	249.6	251.5	252.1
65°	206.2	205.3	206.7	207.6	208.0	210.3	213.5	214.8	216.7	217.6	220.8
67.5°	173.3	173.5	173.3	174.6	177.3	177.8	180.8	184.0	184.3	186.1	188.2
70°	151.1	152.0	152.9	153.8	156.1	157.0	159.3	160.7	162.5	163.9	165.2
72.5°	130.7	130.9	131.8	131.6	133.6	135.5	137.5	138.8	140.6	142.4	143.7
75°	100.6	100.6	101.5	101.9	104.2	106.6	106.0	107.0	108.8	110.6	111.6
77.5°	73.5	72.5	73.5	73.9	74.6	76.6	77.0	78.2	80.3	79.6	80.7
80°	56.0	54.7	56.0	56.4	56.4	58.8	58.8	59.7	61.0	59.7	61.0
82.5°	39.9	39.3	40.3	40.4	41.1	41.2	42.0	42.2	43.5	42.9	43.5
85°	20.1	19.6	20.1	19.6	20.1	20.5	20.5	20.1	20.1	21.0	19.6
87.5°	7.4	7.3	7.5	8.2	8.5	8.2	7.8	7.7	7.4	6.9	7.0
90°	6.1	7.7	10.2	13.7	16.8	17.3	16.8	16.2	15.2	16.2	16.8
92.5°	18.3	23.1	34.6	50.7	65.2	66.1	55.8	44.3	38.1	33.8	30.6
95°	37.6	49.8	73.2	117.4	176.5	199.4	174.4	133.2	102.2	80.9	69.6
97.5°	53.4	67.2	96.7	158.3	256.3	340.3	357.0	310.9	254.4	199.4	162.6
100°	63.6	77.8	104.8	166.8	276.6	401.7	474.9	464.3	401.3	331.5	270.0
102.5°	72.9	87.1	112.1	167.2	268.9	403.8	518.9	564.8	550.5	499.6	434.4
105°	86.4	100.7	124.6	169.9	253.8	376.8	512.1	617.9	675.3	682.0	665.1
107.5°	99.9	114.2	137.4	176.8	246.2	347.9	467.4	579.6	666.2	719.1	743.7
110°	108.8	123.6	146.0	182.5	244.6	334.1	439.3	546.7	637.7	702.8	744.5



TEST NUMBER: P331341-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	117.3	132.5	154.1	188.7	245.0	325.1	419.8	516.6	604.0	673.5	721.3
115°	131.2	144.9	166.8	197.8	247.2	315.3	395.7	479.6	557.9	624.5	676.9
117.5°	144.0	158.3	178.5	207.6	250.8	310.5	380.4	451.7	520.4	580.9	630.0
120°	152.6	166.8	186.6	214.1	253.2	307.6	372.3	437.8	500.9	554.8	601.1
122.5°	161.1	175.8	194.4	219.8	256.1	306.0	365.3	426.9	484.6	535.7	577.5
125°	173.4	187.6	206.0	228.8	260.4	303.1	355.4	410.9	463.2	508.0	546.2
127.5°	184.3	198.9	216.8	237.3	264.7	301.4	346.3	395.1	442.6	484.7	520.0
130°	191.2	205.5	223.3	242.5	268.0	300.5	340.2	385.0	428.7	468.9	502.4
132.5°	197.7	212.0	228.9	247.9	271.3	300.1	335.3	375.2	415.7	452.6	484.1
135°	206.4	220.7	237.0	254.8	275.1	299.5	328.5	361.6	395.1	428.7	457.2
137.5°	214.2	227.4	243.5	260.0	278.6	299.4	323.7	350.7	378.8	405.4	430.3
140°	218.6	231.9	247.2	262.9	280.2	299.0	320.9	343.8	368.2	391.6	413.9
142.5°	222.7	235.1	250.0	265.4	281.4	299.0	318.1	338.0	358.8	379.0	397.7
145°	229.3	240.5	254.2	268.5	282.8	298.0	314.2	330.0	346.8	362.6	377.4
147.5°	234.9	244.8	257.7	270.3	283.1	296.1	310.4	323.9	337.1	349.4	360.2
150°	238.5	247.6	259.3	271.1	282.8	295.0	307.2	319.3	330.6	341.3	350.4
152.5°	242.2	250.5	261.0	271.4	282.0	292.9	304.3	314.9	325.3	334.3	342.2
155°	247.2	254.8	263.4	272.1	280.7	289.4	299.0	308.7	316.8	324.4	330.0
157.5°	251.5	257.8	265.1	272.1	278.4	285.7	294.0	301.5	308.3	314.7	319.1
160°	254.2	259.8	266.0	272.1	277.1	283.3	290.3	296.9	302.6	308.2	311.7
162.5°	256.7	261.1	266.4	271.6	275.9	281.2	287.1	292.5	297.3	302.1	304.8
165°	259.3	262.4	267.0	270.5	273.6	277.1	281.7	285.8	289.4	292.9	295.0
167.5°	261.6	263.5	266.9	269.8	271.3	273.6	276.4	279.4	282.1	284.5	286.4
170°	262.4	263.9	266.4	269.0	270.0	271.5	273.6	276.2	277.7	279.7	280.7
172.5°	263.2	264.3	266.1	267.8	268.4	269.1	270.7	272.5	273.6	275.2	275.8
175°	263.9	264.4	265.5	266.4	266.0	266.4	267.0	268.5	269.0	269.6	270.0
177.5°	264.4	264.4	264.8	265.6	264.8	264.4	264.8	265.6	265.6	266.1	266.1
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331341-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1136.0	1135.2	1135.2	1132.0	1135.2	1135.2	1136.0	1139.6	1140.8	1141.5	1140.1
5°	1053.8	1052.4	1050.2	1052.4	1050.2	1052.4	1053.8	1060.2	1063.4	1066.6	1069.3
7.5°	972.5	967.1	966.3	960.8	966.3	967.1	972.5	975.5	981.9	989.1	995.6
10°	913.1	909.5	909.0	900.4	909.0	909.5	913.1	920.9	927.3	935.9	945.0
12.5°	868.0	859.3	860.9	856.0	860.9	859.3	868.0	868.1	875.6	880.9	895.1
15°	789.8	789.8	787.9	780.2	787.9	789.8	789.8	802.1	804.3	813.0	825.3
17.5°	733.6	732.7	728.3	730.5	728.3	732.7	733.6	742.6	744.1	755.7	765.8
20°	700.1	697.4	691.9	691.9	691.9	697.4	700.1	705.1	711.1	717.8	726.5
22.5°	668.4	668.2	662.5	664.2	662.5	668.2	668.4	673.1	678.6	686.2	693.4
25°	631.3	627.8	625.0	626.3	625.0	627.8	631.3	631.9	638.2	643.2	647.7
27.5°	596.2	594.2	594.1	590.3	594.1	594.2	596.2	597.4	601.0	604.0	608.2
30°	575.9	571.3	572.2	569.9	572.2	571.3	575.9	576.3	578.1	580.0	585.0
32.5°	552.5	550.9	550.0	548.0	550.0	550.9	552.5	553.3	557.0	558.8	562.8
35°	520.8	521.2	519.0	519.9	519.0	521.2	520.8	521.7	522.1	524.0	527.5
37.5°	493.0	494.5	493.4	493.7	493.4	494.5	493.0	493.5	493.9	494.2	495.3
40°	474.7	474.7	474.7	476.2	474.7	474.7	474.7	473.4	473.9	473.4	473.4
42.5°	457.3	456.6	455.8	455.8	455.8	456.6	457.3	454.1	455.7	454.1	453.3
45°	427.4	428.8	429.3	427.0	429.3	428.8	427.4	426.5	425.2	424.7	424.3
47.5°	400.4	400.6	400.4	402.4	400.4	400.6	400.4	399.2	397.1	396.3	394.1
50°	381.5	380.6	381.5	380.6	381.5	380.6	381.5	379.2	377.8	375.5	373.7
52.5°	361.4	361.6	361.1	360.9	361.1	361.6	361.4	358.5	357.8	357.0	354.1
55°	330.0	330.9	330.5	330.5	330.5	330.9	330.0	328.2	327.7	325.0	322.3
57.5°	297.6	298.4	299.0	296.9	299.0	298.4	297.6	297.2	296.9	294.1	291.1
60°	274.9	277.2	276.8	275.9	276.8	277.2	274.9	275.4	274.0	272.2	270.4
62.5°	254.2	255.0	254.9	254.8	254.9	255.0	254.2	252.1	251.5	249.6	247.8
65°	222.1	223.0	221.7	223.0	221.7	223.0	222.1	220.8	217.6	216.7	214.8
67.5°	187.6	187.9	189.0	189.6	189.0	187.9	187.6	188.2	186.1	184.3	184.0
70°	166.1	165.7	167.0	168.4	167.0	165.7	166.1	165.2	163.9	162.5	160.7
72.5°	143.6	144.5	144.1	145.1	144.1	144.5	143.6	143.7	142.4	140.6	138.8
75°	110.6	112.0	111.6	112.9	111.6	112.0	110.6	111.6	110.6	108.8	107.0
77.5°	79.9	80.1	79.9	80.7	79.9	80.1	79.9	80.7	79.6	80.3	78.2
80°	61.0	60.1	59.2	61.0	59.2	60.1	61.0	61.0	59.7	61.0	59.7
82.5°	42.4	43.0	42.1	42.1	42.1	43.0	42.4	43.5	42.9	43.5	42.2
85°	19.6	19.1	18.2	18.2	18.2	19.1	19.6	19.6	21.0	20.1	20.1
87.5°	7.0	6.6	6.6	6.2	6.6	6.6	7.0	7.0	6.9	7.4	7.7
90°	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.2	15.2	16.2
92.5°	30.2	28.6	29.0	28.2	29.0	28.6	30.2	30.6	33.8	38.1	44.3
95°	63.0	59.0	57.4	58.0	57.4	59.0	63.0	69.6	80.9	102.2	133.2
97.5°	138.3	125.8	118.4	114.1	118.4	125.8	138.3	162.6	199.4	254.4	310.9
100°	227.8	206.0	191.2	182.1	191.2	206.0	227.8	270.0	331.5	401.3	464.3
102.5°	388.5	351.2	332.8	320.4	332.8	351.2	388.5	434.4	499.6	550.5	564.8
105°	633.6	602.1	580.2	573.1	580.2	602.1	633.6	665.1	682.0	675.3	617.9
107.5°	747.6	745.9	741.5	732.1	741.5	745.9	747.6	743.7	719.1	666.2	579.6
110°	766.3	776.1	780.6	780.1	780.6	776.1	766.3	744.5	702.8	637.7	546.7



TEST NUMBER: P331341-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	751.7	767.9	776.5	779.3	776.5	767.9	751.7	721.3	673.5	604.0	516.6
115°	712.9	736.4	749.6	754.1	749.6	736.4	712.9	676.9	624.5	557.9	479.6
117.5°	666.8	691.5	705.4	709.3	705.4	691.5	666.8	630.0	580.9	520.4	451.7
120°	636.7	660.6	675.3	680.4	675.3	660.6	636.7	601.1	554.8	500.9	437.8
122.5°	609.4	632.9	646.0	650.3	646.0	632.9	609.4	577.5	535.7	484.6	426.9
125°	575.7	594.9	607.7	611.8	607.7	594.9	575.7	546.2	508.0	463.2	410.9
127.5°	545.6	563.7	574.7	578.0	574.7	563.7	545.6	520.0	484.7	442.6	395.1
130°	527.4	544.7	554.8	558.8	554.8	544.7	527.4	502.4	468.9	428.7	385.0
132.5°	508.6	525.9	535.3	539.0	535.3	525.9	508.6	484.1	452.6	415.7	375.2
135°	479.0	495.8	505.0	507.0	505.0	495.8	479.0	457.2	428.7	395.1	361.6
137.5°	450.1	464.6	472.6	475.6	472.6	464.6	450.1	430.3	405.4	378.8	350.7
140°	430.3	443.4	451.0	454.1	451.0	443.4	430.3	413.9	391.6	368.2	343.8
142.5°	413.1	425.2	431.9	432.6	431.9	425.2	413.1	397.7	379.0	358.8	338.0
145°	389.5	398.1	403.2	404.7	403.2	398.1	389.5	377.4	362.6	346.8	330.0
147.5°	370.2	377.1	380.6	381.5	380.6	377.1	370.2	360.2	349.4	337.1	323.9
150°	358.0	364.1	367.1	367.7	367.1	364.1	358.0	350.4	341.3	330.6	319.3
152.5°	348.2	353.6	355.8	355.9	355.8	353.6	348.2	342.2	334.3	325.3	314.9
155°	335.6	339.2	341.3	340.2	341.3	339.2	335.6	330.0	324.4	316.8	308.7
157.5°	323.0	326.0	326.9	326.9	326.9	326.0	323.0	319.1	314.7	308.3	301.5
160°	315.3	317.8	318.3	318.3	318.3	317.8	315.3	311.7	308.2	302.6	296.9
162.5°	308.4	310.1	310.6	310.2	310.6	310.1	308.4	304.8	302.1	297.3	292.5
165°	296.9	299.0	299.0	298.5	299.0	299.0	296.9	295.0	292.9	289.4	285.8
167.5°	287.3	288.5	288.4	287.8	288.4	288.5	287.3	286.4	284.5	282.1	279.4
170°	281.2	282.8	282.2	281.2	282.2	282.8	281.2	280.7	279.7	277.7	276.2
172.5°	276.3	277.1	276.5	275.9	276.5	277.1	276.3	275.8	275.2	273.6	272.5
175°	270.0	270.5	270.0	269.0	270.0	270.5	270.0	270.0	269.6	269.0	268.5
177.5°	266.1	266.1	265.6	264.8	265.6	266.1	266.1	266.1	266.1	265.6	265.6
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331341-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1138.2	1142.2	1148.3	1154.9	1159.0	1166.6	1168.8	1172.4	1175.7	1183.4	1191.3
5°	1072.5	1078.8	1093.9	1102.1	1113.4	1126.6	1135.2	1144.4	1154.4	1171.7	1187.6
7.5°	1002.0	1012.6	1031.3	1046.6	1062.8	1081.7	1095.4	1113.4	1128.4	1152.7	1176.1
10°	955.0	970.0	986.9	1005.0	1027.9	1047.8	1067.0	1089.8	1108.0	1137.1	1164.4
12.5°	912.8	915.1	939.1	959.2	990.3	1015.1	1037.1	1066.5	1084.3	1118.9	1147.6
15°	838.9	852.6	874.4	890.4	927.3	958.7	989.6	1020.1	1040.6	1083.3	1121.1
17.5°	776.8	789.3	811.7	837.9	864.3	895.5	935.6	967.8	995.6	1044.6	1089.2
20°	737.4	752.9	775.7	802.5	825.7	859.9	894.5	931.3	961.4	1016.5	1068.8
22.5°	703.9	716.1	734.5	761.0	786.4	817.6	855.5	895.6	927.2	986.6	1039.6
25°	656.8	666.9	678.7	700.5	729.2	763.4	793.0	837.1	883.1	938.6	1002.8
27.5°	614.4	621.5	632.0	651.2	673.4	705.3	738.2	780.2	826.3	886.6	954.4
30°	588.6	593.2	603.6	619.6	641.4	666.4	699.6	739.7	787.0	848.0	915.4
32.5°	566.0	570.2	577.0	592.2	611.2	632.6	662.5	702.6	747.7	807.6	882.3
35°	532.2	535.3	541.3	553.5	564.0	585.0	609.9	646.4	688.8	746.1	823.5
37.5°	498.4	502.7	506.4	511.6	525.0	538.8	560.5	591.3	632.8	690.7	764.5
40°	476.2	479.7	485.3	487.5	498.5	510.8	528.5	556.7	598.6	651.4	723.4
42.5°	453.5	457.2	460.5	463.2	472.6	483.4	499.4	523.6	560.7	612.1	683.2
45°	422.8	423.3	426.5	431.5	436.0	443.8	455.2	476.2	504.8	553.0	617.7
47.5°	391.7	392.3	392.8	395.0	400.0	407.1	414.6	431.6	457.3	495.8	558.7
50°	371.0	370.1	371.0	372.8	376.0	381.9	390.6	402.9	423.8	459.8	517.5
52.5°	351.0	350.8	350.3	351.0	353.4	357.5	363.6	374.1	392.8	425.9	476.8
55°	320.5	318.2	318.6	316.8	320.9	321.8	326.4	335.0	351.4	374.2	422.0
57.5°	287.9	286.1	284.0	283.5	283.1	285.6	289.3	296.0	308.6	328.6	367.4
60°	267.2	264.9	262.2	261.3	261.3	262.6	264.5	269.5	281.3	299.1	330.9
62.5°	246.1	243.4	241.8	239.4	238.7	240.0	241.9	245.5	254.0	270.6	298.2
65°	213.5	210.3	208.0	207.6	206.7	205.3	206.2	209.8	216.7	229.9	251.7
67.5°	180.8	177.8	177.3	174.6	173.3	173.5	173.3	176.5	180.6	191.9	208.2
70°	159.3	157.0	156.1	153.8	152.9	152.0	151.1	153.8	157.9	167.6	181.6
72.5°	137.5	135.5	133.6	131.6	131.8	130.9	130.7	132.3	135.7	144.5	155.4
75°	106.0	106.6	104.2	101.9	101.5	100.6	100.6	101.9	103.3	110.1	118.8
77.5°	77.0	76.6	74.6	73.9	73.5	72.5	73.5	74.4	75.1	79.6	86.1
80°	58.8	58.8	56.4	56.4	56.0	54.7	56.0	55.1	56.9	61.4	66.0
82.5°	42.0	41.2	41.1	40.4	40.3	39.3	39.9	40.8	41.6	44.7	47.4
85°	20.5	20.5	20.1	19.6	20.1	19.6	20.1	20.5	21.0	22.3	24.6
87.5°	7.8	8.2	8.5	8.2	7.5	7.3	7.4	7.6	8.1	8.0	8.1
90°	16.8	17.3	16.8	13.7	10.2	7.7	6.1	5.1	4.1	2.1	0.5
92.5°	55.8	66.1	65.2	50.7	34.6	23.1	18.3	14.9	12.6	8.9	6.2
95°	174.4	199.4	176.5	117.4	73.2	49.8	37.6	29.5	24.9	19.8	17.8
97.5°	357.0	340.3	256.3	158.3	96.7	67.2	53.4	44.1	37.1	31.7	29.0
100°	474.9	401.7	276.6	166.8	104.8	77.8	63.6	53.4	45.3	40.7	39.1
102.5°	518.9	403.8	268.9	167.2	112.1	87.1	72.9	62.3	54.2	49.7	48.5
105°	512.1	376.8	253.8	169.9	124.6	100.7	86.4	75.3	67.6	64.1	62.1
107.5°	467.4	347.9	246.2	176.8	137.4	114.2	99.9	88.8	81.8	78.3	76.7
110°	439.3	334.1	244.6	182.5	146.0	123.6	108.8	98.2	91.6	88.5	86.4



TEST NUMBER: P331341-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	419.8	325.1	245.0	188.7	154.1	132.5	117.3	107.1	100.9	97.5	95.4
115°	395.7	315.3	247.2	197.8	166.8	144.9	131.2	121.0	114.9	111.9	109.3
117.5°	380.4	310.5	250.8	207.6	178.5	158.3	144.0	134.3	128.9	125.8	123.8
120°	372.3	307.6	253.2	214.1	186.6	166.8	152.6	142.4	137.8	134.7	132.7
122.5°	365.3	306.0	256.1	219.8	194.4	175.8	161.1	151.0	146.0	142.9	141.2
125°	355.4	303.1	260.4	228.8	206.0	187.6	173.4	163.3	157.1	154.1	152.6
127.5°	346.3	301.4	264.7	237.3	216.8	198.9	184.3	174.5	167.8	163.5	161.5
130°	340.2	300.5	268.0	242.5	223.3	205.5	191.2	181.0	173.9	168.8	166.8
132.5°	335.3	300.1	271.3	247.9	228.9	212.0	197.7	187.2	179.6	174.2	171.7
135°	328.5	299.5	275.1	254.8	237.0	220.7	206.4	194.7	187.2	181.0	179.0
137.5°	323.7	299.4	278.6	260.0	243.5	227.4	214.2	202.6	194.5	188.3	185.9
140°	320.9	299.0	280.2	262.9	247.2	231.9	218.6	207.5	199.4	193.2	191.2
142.5°	318.1	299.0	281.4	265.4	250.0	235.1	222.7	212.0	203.8	198.1	196.5
145°	314.2	298.0	282.8	268.5	254.2	240.5	229.3	219.2	211.5	206.4	204.5
147.5°	310.4	296.1	283.1	270.3	257.7	244.8	234.9	226.4	219.4	214.5	212.9
150°	307.2	295.0	282.8	271.1	259.3	247.6	238.5	230.9	224.3	220.2	218.6
152.5°	304.3	292.9	282.0	271.4	261.0	250.5	242.2	235.0	229.2	225.1	224.4
155°	299.0	289.4	280.7	272.1	263.4	254.8	247.2	241.6	235.9	232.9	232.4
157.5°	294.0	285.7	278.4	272.1	265.1	257.8	251.5	246.9	242.1	239.6	239.1
160°	290.3	283.3	277.1	272.1	266.0	259.8	254.2	250.2	246.1	244.1	243.6
162.5°	287.1	281.2	275.9	271.6	266.4	261.1	256.7	253.1	249.8	247.7	248.1
165°	281.7	277.1	273.6	270.5	267.0	262.4	259.3	256.8	253.8	252.7	253.2
167.5°	276.4	273.6	271.3	269.8	266.9	263.5	261.6	259.8	257.8	256.9	257.5
170°	273.6	271.5	270.0	269.0	266.4	263.9	262.4	261.4	259.8	259.3	260.4
172.5°	270.7	269.1	268.4	267.8	266.1	264.3	263.2	262.6	261.1	261.4	262.0
175°	267.0	266.4	266.0	266.4	265.5	264.4	263.9	263.9	262.9	263.4	263.9
177.5°	264.8	264.4	264.8	265.6	264.8	264.4	264.4	264.4	263.6	264.0	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331341-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1190.6	1192.5	1198.3	1204.1	1210.7	1212.5	1215.4	1212.8	1212.1	1219.1	1224.1
5°	1194.0	1202.2	1218.2	1232.7	1245.0	1253.7	1262.8	1266.4	1273.2	1282.7	1294.6
7.5°	1190.2	1206.1	1231.2	1252.3	1275.5	1292.2	1305.2	1316.3	1329.7	1347.8	1367.6
10°	1185.8	1207.2	1237.7	1263.6	1291.8	1313.2	1331.1	1348.3	1368.3	1393.4	1419.3
12.5°	1177.8	1203.2	1241.4	1272.0	1308.2	1329.3	1353.3	1390.5	1412.0	1446.9	1483.5
15°	1161.7	1189.9	1243.1	1280.9	1321.9	1362.0	1406.1	1441.6	1477.1	1497.6	1549.1
17.5°	1137.7	1179.2	1238.1	1282.2	1334.3	1397.4	1447.0	1487.2	1528.2	1561.5	1587.2
20°	1118.5	1163.5	1230.8	1283.7	1345.6	1413.4	1470.3	1511.3	1546.8	1574.6	1590.5
22.5°	1094.0	1150.8	1216.3	1278.2	1357.3	1424.3	1484.2	1516.4	1546.0	1559.6	1565.8
25°	1055.6	1123.9	1198.1	1273.6	1362.9	1433.9	1488.5	1508.1	1516.7	1503.5	1481.7
27.5°	1014.2	1090.3	1177.1	1265.1	1359.4	1427.7	1466.9	1463.7	1449.1	1406.4	1372.3
30°	983.2	1067.0	1160.3	1256.3	1351.0	1417.5	1440.3	1417.5	1384.3	1336.5	1287.8
32.5°	950.8	1037.5	1142.5	1243.9	1335.8	1394.2	1399.1	1359.9	1308.5	1254.2	1193.5
35°	901.8	995.5	1108.8	1216.3	1303.2	1340.2	1318.3	1249.1	1188.1	1113.9	1031.0
37.5°	846.3	949.9	1063.5	1175.8	1254.5	1264.2	1210.0	1137.1	1051.1	963.9	866.4
40°	804.8	914.5	1031.5	1144.9	1214.5	1204.4	1135.2	1055.2	952.7	846.2	755.6
42.5°	767.7	877.4	996.5	1107.7	1163.5	1136.0	1055.2	956.8	846.8	746.5	663.5
45°	703.3	816.2	938.2	1045.6	1077.5	1027.9	920.9	811.6	703.3	619.6	554.0
47.5°	640.9	752.4	873.3	967.7	978.9	912.2	795.3	682.9	589.8	521.6	475.3
50°	594.9	706.9	826.6	910.9	907.2	826.6	706.5	599.5	521.7	466.5	435.6
52.5°	553.8	659.6	774.5	851.1	831.9	744.0	629.3	534.3	470.3	427.2	399.2
55°	489.8	587.6	696.9	758.4	722.8	625.4	528.5	452.0	404.7	372.4	350.5
57.5°	426.2	518.0	611.5	649.4	610.2	520.2	439.3	383.9	348.3	324.4	310.1
60°	386.9	467.1	550.4	583.1	536.2	456.1	392.4	342.8	314.1	294.5	281.8
62.5°	347.6	419.4	497.9	515.8	472.9	405.1	348.7	307.5	283.8	266.4	254.5
65°	294.1	352.8	412.4	424.3	384.7	332.3	287.7	260.8	239.9	227.1	217.6
67.5°	241.2	288.3	330.6	340.1	305.4	269.1	236.9	213.5	199.3	188.7	180.7
70°	209.8	247.2	281.8	289.5	261.7	229.4	204.8	186.2	173.4	164.3	156.6
72.5°	176.7	207.9	236.6	241.8	219.1	194.5	174.2	159.6	148.3	142.5	135.1
75°	135.2	153.4	175.7	177.1	162.0	147.0	131.5	122.0	116.1	108.8	105.1
77.5°	95.4	109.7	122.4	124.9	116.0	105.8	97.1	89.6	84.5	81.2	77.8
80°	72.9	84.2	89.7	92.8	86.5	79.2	74.2	69.2	66.0	63.8	61.4
82.5°	52.1	59.1	64.2	66.6	63.2	58.9	53.8	51.0	48.5	46.6	45.8
85°	26.4	29.6	32.8	33.7	32.8	30.9	28.2	28.2	26.8	26.4	26.4
87.5°	9.5	11.4	11.6	12.8	12.5	12.9	13.6	13.9	13.6	13.2	12.8
90°	2.1	4.1	5.1	6.1	7.7	10.2	13.7	16.8	17.3	16.8	16.2
92.5°	8.9	12.6	14.9	18.3	23.1	34.6	50.7	65.2	66.1	55.8	44.3
95°	19.8	24.9	29.5	37.6	49.8	73.2	117.4	176.5	199.4	174.4	133.2
97.5°	31.7	37.1	44.1	53.4	67.2	96.7	158.3	256.3	340.3	357.0	310.9
100°	40.7	45.3	53.4	63.6	77.8	104.8	166.8	276.6	401.7	474.9	464.3
102.5°	49.7	54.2	62.3	72.9	87.1	112.1	167.2	268.9	403.8	518.9	564.8
105°	64.1	67.6	75.3	86.4	100.7	124.6	169.9	253.8	376.8	512.1	617.9
107.5°	78.3	81.8	88.8	99.9	114.2	137.4	176.8	246.2	347.9	467.4	579.6
110°	88.5	91.6	98.2	108.8	123.6	146.0	182.5	244.6	334.1	439.3	546.7





TEST NUMBER: P331341-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	97.5	100.9	107.1	117.3	132.5	154.1	188.7	245.0	325.1	419.8	516.6
115°	111.9	114.9	121.0	131.2	144.9	166.8	197.8	247.2	315.3	395.7	479.6
117.5°	125.8	128.9	134.3	144.0	158.3	178.5	207.6	250.8	310.5	380.4	451.7
120°	134.7	137.8	142.4	152.6	166.8	186.6	214.1	253.2	307.6	372.3	437.8
122.5°	142.9	146.0	151.0	161.1	175.8	194.4	219.8	256.1	306.0	365.3	426.9
125°	154.1	157.1	163.3	173.4	187.6	206.0	228.8	260.4	303.1	355.4	410.9
127.5°	163.5	167.8	174.5	184.3	198.9	216.8	237.3	264.7	301.4	346.3	395.1
130°	168.8	173.9	181.0	191.2	205.5	223.3	242.5	268.0	300.5	340.2	385.0
132.5°	174.2	179.6	187.2	197.7	212.0	228.9	247.9	271.3	300.1	335.3	375.2
135°	181.0	187.2	194.7	206.4	220.7	237.0	254.8	275.1	299.5	328.5	361.6
137.5°	188.3	194.5	202.6	214.2	227.4	243.5	260.0	278.6	299.4	323.7	350.7
140°	193.2	199.4	207.5	218.6	231.9	247.2	262.9	280.2	299.0	320.9	343.8
142.5°	198.1	203.8	212.0	222.7	235.1	250.0	265.4	281.4	299.0	318.1	338.0
145°	206.4	211.5	219.2	229.3	240.5	254.2	268.5	282.8	298.0	314.2	330.0
147.5°	214.5	219.4	226.4	234.9	244.8	257.7	270.3	283.1	296.1	310.4	323.9
150°	220.2	224.3	230.9	238.5	247.6	259.3	271.1	282.8	295.0	307.2	319.3
152.5°	225.1	229.2	235.0	242.2	250.5	261.0	271.4	282.0	292.9	304.3	314.9
155°	232.9	235.9	241.6	247.2	254.8	263.4	272.1	280.7	289.4	299.0	308.7
157.5°	239.6	242.1	246.9	251.5	257.8	265.1	272.1	278.4	285.7	294.0	301.5
160°	244.1	246.1	250.2	254.2	259.8	266.0	272.1	277.1	283.3	290.3	296.9
162.5°	247.7	249.8	253.1	256.7	261.1	266.4	271.6	275.9	281.2	287.1	292.5
165°	252.7	253.8	256.8	259.3	262.4	267.0	270.5	273.6	277.1	281.7	285.8
167.5°	256.9	257.8	259.8	261.6	263.5	266.9	269.8	271.3	273.6	276.4	279.4
170°	259.3	259.8	261.4	262.4	263.9	266.4	269.0	270.0	271.5	273.6	276.2
172.5°	261.4	261.1	262.6	263.2	264.3	266.1	267.8	268.4	269.1	270.7	272.5
175°	263.4	262.9	263.9	263.9	264.4	265.5	266.4	266.0	266.4	267.0	268.5
177.5°	264.0	263.6	264.4	264.4	264.4	264.8	265.6	264.8	264.4	264.8	265.6
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331341-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1228.5	1233.6	1233.6	1234.3	1240.2	1239.4	1239.0
5°	1307.3	1315.1	1316.0	1324.2	1329.6	1327.8	1322.9
7.5°	1381.7	1396.2	1407.0	1413.1	1420.3	1424.8	1422.8
10°	1440.7	1461.7	1474.4	1483.1	1493.5	1501.3	1498.5
12.5°	1494.2	1519.2	1536.7	1551.5	1552.9	1562.8	1556.0
15°	1577.7	1604.1	1606.9	1617.8	1626.5	1625.5	1625.9
17.5°	1605.3	1613.8	1615.5	1615.8	1615.9	1612.7	1605.8
20°	1595.4	1592.3	1584.6	1578.7	1568.2	1566.8	1557.7
22.5°	1548.9	1538.7	1519.4	1506.5	1490.2	1485.9	1483.5
25°	1457.1	1434.8	1403.8	1374.2	1366.1	1350.1	1354.7
27.5°	1331.2	1296.5	1262.9	1238.9	1217.1	1193.3	1200.1
30°	1242.7	1203.5	1156.2	1119.8	1096.6	1073.8	1069.7
32.5°	1137.1	1079.8	1026.9	994.9	959.3	944.9	929.2
35°	955.0	899.0	846.7	801.6	775.7	755.6	737.4
37.5°	791.2	726.7	684.6	648.0	629.3	617.8	620.7
40°	689.6	633.2	602.3	574.4	557.1	548.9	550.8
42.5°	607.3	565.1	539.6	520.6	508.4	503.8	502.7
45°	513.9	490.3	469.3	458.4	452.5	447.5	444.3
47.5°	450.2	430.9	419.1	412.6	407.4	402.3	402.3
50°	412.0	399.2	391.0	384.1	380.1	376.5	379.6
52.5°	382.8	371.1	363.0	356.9	355.3	352.0	352.0
55°	339.6	330.5	324.6	319.1	316.4	314.5	312.3
57.5°	300.2	291.6	286.1	282.7	277.5	275.6	274.9
60°	272.2	265.4	259.9	255.4	253.1	249.4	249.4
62.5°	246.4	239.5	234.4	231.0	227.2	225.8	226.1
65°	208.9	203.5	198.5	194.8	193.9	191.2	192.1
67.5°	174.5	170.9	165.6	163.6	161.8	160.4	159.3
70°	151.6	147.9	145.2	142.5	141.1	141.1	141.1
72.5°	132.2	127.9	126.3	122.8	123.6	122.2	120.7
75°	102.5	99.7	98.4	96.9	94.7	94.7	94.7
77.5°	75.3	74.5	72.9	71.4	70.9	70.4	70.6
80°	58.2	57.8	56.9	56.9	56.0	55.6	54.7
82.5°	44.8	43.6	43.1	42.7	42.5	42.4	42.3
85°	25.5	24.6	24.6	25.1	24.2	24.2	24.6
87.5°	12.8	13.1	12.8	12.8	13.2	12.8	12.8
90°	15.2	16.2	16.8	16.8	16.8	16.8	16.8
92.5°	38.1	33.8	30.6	30.2	28.6	29.0	28.2
95°	102.2	80.9	69.6	63.0	59.0	57.4	58.0
97.5°	254.4	199.4	162.6	138.3	125.8	118.4	114.1
100°	401.3	331.5	270.0	227.8	206.0	191.2	182.1
102.5°	550.5	499.6	434.4	388.5	351.2	332.8	320.4
105°	675.3	682.0	665.1	633.6	602.1	580.2	573.1
107.5°	666.2	719.1	743.7	747.6	745.9	741.5	732.1
110°	637.7	702.8	744.5	766.3	776.1	780.6	780.1



TEST NUMBER: P331341-940

CATALOG NUMBER: S122DIP-S675D530U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	604.0	673.5	721.3	751.7	767.9	776.5	779.3
115°	557.9	624.5	676.9	712.9	736.4	749.6	754.1
117.5°	520.4	580.9	630.0	666.8	691.5	705.4	709.3
120°	500.9	554.8	601.1	636.7	660.6	675.3	680.4
122.5°	484.6	535.7	577.5	609.4	632.9	646.0	650.3
125°	463.2	508.0	546.2	575.7	594.9	607.7	611.8
127.5°	442.6	484.7	520.0	545.6	563.7	574.7	578.0
130°	428.7	468.9	502.4	527.4	544.7	554.8	558.8
132.5°	415.7	452.6	484.1	508.6	525.9	535.3	539.0
135°	395.1	428.7	457.2	479.0	495.8	505.0	507.0
137.5°	378.8	405.4	430.3	450.1	464.6	472.6	475.6
140°	368.2	391.6	413.9	430.3	443.4	451.0	454.1
142.5°	358.8	379.0	397.7	413.1	425.2	431.9	432.6
145°	346.8	362.6	377.4	389.5	398.1	403.2	404.7
147.5°	337.1	349.4	360.2	370.2	377.1	380.6	381.5
150°	330.6	341.3	350.4	358.0	364.1	367.1	367.7
152.5°	325.3	334.3	342.2	348.2	353.6	355.8	355.9
155°	316.8	324.4	330.0	335.6	339.2	341.3	340.2
157.5°	308.3	314.7	319.1	323.0	326.0	326.9	326.9
160°	302.6	308.2	311.7	315.3	317.8	318.3	318.3
162.5°	297.3	302.1	304.8	308.4	310.1	310.6	310.2
165°	289.4	292.9	295.0	296.9	299.0	299.0	298.5
167.5°	282.1	284.5	286.4	287.3	288.5	288.4	287.8
170°	277.7	279.7	280.7	281.2	282.8	282.2	281.2
172.5°	273.6	275.2	275.8	276.3	277.1	276.5	275.9
175°	269.0	269.6	270.0	270.0	270.5	270.0	269.0
177.5°	265.6	266.1	266.1	266.1	266.1	265.6	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4

(END OF REPORT)