

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331329-830

Luminaire Tested: **S122DIP-S485D1080U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331329-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S485D1080U830-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5829.6 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331329-830

CATALOG NUMBER: S122DIP-S485D1080U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331329-830

CATALOG NUMBER: S122DIP-S485D1080U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32					32			
1	94	90	86	82	84	81	78	75	64	62	60	49	48	46	35	34	33	27					27			
2	85	78	72	67	77	70	65	61	56	53	50	43	41	39	31	29	28	23					23			
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	25	24	19					19			
4	71	61	53	47	64	55	48	43	44	39	35	34	31	28	24	22	21	16					16			
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14					14			
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16	13					13			
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14	11					11			
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	17	14	12	10					10			
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9					9			
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8					8			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11820	11820	11820
5°	11866	11694	11763
10°	11795	11576	11632
15°	11649	11425	11413
20°	11442	11201	11187
25°	11236	10922	10922
30°	10972	10670	10577
35°	10724	10364	10212
40°	10416	10060	9866
45°	10111	9757	9515
50°	9779	9442	9105
55°	9433	9073	8740
60°	9045	8638	8318
65°	8630	8202	7824
70°	8105	7676	7312
75°	7380	7068	6900
80°	6546	6341	6025
85°	5335	5076	4557



TEST NUMBER: P331329-830

CATALOG NUMBER: S122DIP-S485D1080U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	1.2
10°-20°	193.7	3.3
20°-30°	284.7	4.9
30°-40°	330.7	5.7
40°-50°	330.4	5.7
50°-60°	288.1	4.9
60°-70°	213.0	3.7
70°-80°	120.7	2.1
80°-90°	37.6	0.6
90°-100°	227.7	3.9
100°-110°	772.5	13.3
110°-120°	820.7	14.1
120°-130°	675.6	11.6
130°-140°	542.5	9.3
140°-150°	410.0	7.0
150°-160°	288.1	4.9
160°-170°	169.6	2.9
170°-180°	55.2	0.9
0°-30°	547.2	9.4
0°-40°	878.0	15.1
0°-60°	1496.4	25.7
0°-90°	1867.6	32.0
90°-120°	1820.9	31.2
90°-150°	3449.0	59.2
90°-180°	3962.0	68.0
0°-180°	5829.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	732	732	732	732	732	
5°	732	729	722	727	726	69
15°	697	692	684	686	683	196
25°	631	625	613	614	613	290
35°	544	537	526	522	518	340
45°	443	438	427	420	417	342
55°	335	331	322	314	310	299
65°	226	222	215	208	205	223
75°	118	117	113	109	111	126
85°	29	28	27	25	25	33
90°	1	15	37	36	36	4
95°	38	94	429	162	125	41
105°	134	202	811	1450	1234	142
115°	235	297	679	1401	1624	233
125°	328	389	653	1135	1317	292
135°	385	460	645	954	1092	298
145°	440	506	642	797	872	276
155°	500	540	623	705	732	230
165°	545	562	597	633	643	154
175°	568	569	574	581	579	54
180°	569	569	569	569	569	



TEST NUMBER: P331329-830

CATALOG NUMBER: S122DIP-S485D1080U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	735.5	734.8	734.2	733.6	732.9	732.0	730.6	729.2	727.8	726.4	727.7
5°	732.1	731.4	730.8	730.2	729.6	728.4	726.7	725.0	723.2	721.5	722.7
7.5°	725.6	724.6	723.7	722.6	721.7	720.4	718.6	716.9	715.1	713.3	714.6
10°	719.4	718.3	717.2	716.1	715.0	713.5	711.6	709.8	707.9	706.1	707.3
12.5°	711.0	710.0	709.0	708.0	707.1	705.7	703.8	701.9	700.0	698.1	699.0
15°	696.9	696.0	695.0	694.1	693.1	691.6	689.6	687.6	685.5	683.5	684.1
17.5°	678.8	678.0	677.0	676.1	675.1	673.6	671.6	669.5	667.4	665.3	666.1
20°	665.9	665.0	664.0	663.1	662.1	660.6	658.4	656.2	654.0	651.9	652.3
22.5°	653.0	651.7	650.4	649.0	647.7	646.0	643.9	641.9	639.8	637.7	637.8
25°	630.7	629.4	628.2	627.0	625.8	623.8	621.1	618.4	615.8	613.1	613.4
27.5°	605.4	604.3	603.1	602.0	600.9	599.3	597.2	595.0	593.0	590.9	590.4
30°	588.5	587.2	586.0	584.8	583.4	581.6	579.3	577.0	574.7	572.3	571.8
32.5°	570.4	569.5	568.4	567.4	566.5	564.7	562.2	559.8	557.3	554.9	554.0
35°	544.1	542.5	541.0	539.4	537.9	535.8	533.4	530.8	528.3	525.8	524.9
37.5°	514.4	513.0	511.7	510.3	508.9	507.0	504.4	502.0	499.5	497.0	495.8
40°	494.2	492.9	491.6	490.4	489.2	487.3	484.7	482.3	479.8	477.3	475.9
42.5°	474.5	473.2	471.9	470.7	469.5	467.6	465.1	462.6	460.1	457.5	456.0
45°	442.8	441.7	440.5	439.5	438.4	436.7	434.3	432.0	429.6	427.3	425.6
47.5°	411.2	410.2	409.2	408.1	407.1	405.4	402.9	400.5	398.0	395.6	393.8
50°	389.3	388.5	387.7	386.9	386.2	384.7	382.5	380.3	378.1	375.9	373.7
52.5°	367.9	366.8	365.8	364.8	363.7	362.2	360.1	358.1	356.0	353.9	352.1
55°	335.1	334.1	333.2	332.2	331.3	329.9	328.0	326.1	324.2	322.3	320.6
57.5°	302.1	301.3	300.6	299.9	299.2	297.7	295.7	293.6	291.5	289.5	287.6
60°	280.1	279.6	278.9	278.2	277.7	276.3	274.1	271.8	269.7	267.5	265.8
62.5°	258.7	257.8	256.7	255.7	254.8	253.4	251.8	250.1	248.4	246.7	245.1
65°	225.9	225.0	224.0	223.1	222.3	220.9	219.4	217.8	216.2	214.7	213.3
67.5°	192.6	191.8	191.1	190.3	189.5	188.5	187.1	185.7	184.3	182.9	181.8
70°	171.7	171.2	170.5	169.8	169.3	168.2	166.8	165.4	164.0	162.6	161.6
72.5°	150.3	149.8	149.1	148.5	147.9	147.1	146.2	145.2	144.4	143.5	142.3
75°	118.3	117.9	117.6	117.3	117.0	116.5	115.6	114.9	114.1	113.3	112.4
77.5°	89.5	89.0	88.5	87.9	87.4	87.0	86.7	86.3	86.1	85.8	85.3
80°	70.4	70.2	70.1	69.9	69.7	69.6	69.2	68.9	68.6	68.2	67.8
82.5°	52.4	52.3	52.3	52.3	52.2	52.1	51.9	51.7	51.6	51.4	50.8
85°	28.8	28.7	28.6	28.4	28.3	28.1	27.9	27.8	27.6	27.4	27.0
87.5°	10.4	10.7	11.4	11.6	11.8	12.2	13.0	14.3	15.4	15.4	14.7
90°	1.1	4.3	8.8	10.9	13.1	16.4	21.9	29.6	36.1	37.2	36.1
92.5°	13.4	19.2	27.1	32.0	39.4	49.7	74.5	109.2	140.3	142.3	120.3
95°	38.4	42.7	53.6	63.5	81.1	107.3	157.7	252.9	379.9	429.2	375.6
97.5°	62.4	68.3	79.9	94.8	115.0	144.8	208.0	340.7	551.9	732.7	768.6
100°	84.3	87.6	97.5	115.0	136.9	167.5	225.6	359.1	595.6	865.0	1022.7
102.5°	104.4	106.9	116.7	134.2	157.0	187.7	241.3	360.1	579.0	869.4	1117.3
105°	133.6	138.0	145.6	162.0	186.2	216.8	268.2	365.7	546.4	811.3	1102.6
107.5°	165.1	168.6	176.1	191.1	215.1	245.9	295.9	380.8	530.2	749.1	1006.4
110°	186.2	190.5	197.1	211.3	234.3	266.1	314.2	393.0	526.7	719.3	946.0



TEST NUMBER: P331329-830

CATALOG NUMBER: S122DIP-S485D1080U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	205.4	209.8	217.3	230.5	252.7	285.3	331.8	406.2	527.5	700.1	904.0
115°	235.4	240.9	247.4	260.6	282.5	312.1	359.1	425.9	532.2	678.8	851.9
117.5°	266.6	270.9	277.5	289.1	310.1	340.7	384.3	447.0	540.0	668.5	819.0
120°	285.8	290.1	296.7	306.6	328.5	359.1	401.8	461.0	545.3	662.4	801.4
122.5°	304.2	307.6	314.2	325.0	346.9	378.4	418.5	473.3	551.4	658.9	786.6
125°	328.5	331.8	338.4	351.5	373.3	404.1	443.5	492.8	560.6	652.6	765.3
127.5°	347.7	352.1	361.4	375.8	396.8	428.3	466.7	510.9	570.0	648.8	745.6
130°	359.1	363.5	374.5	389.8	411.7	442.3	480.7	522.3	577.0	647.1	732.5
132.5°	369.7	374.9	386.7	402.9	425.7	456.4	492.9	533.7	584.0	646.2	722.0
135°	385.4	389.8	402.9	419.3	444.5	475.2	510.2	548.6	592.4	644.9	707.3
137.5°	400.3	405.6	418.7	436.2	461.2	489.7	524.2	560.0	599.8	644.7	697.0
140°	411.7	416.0	429.2	446.8	470.8	499.3	532.2	566.1	603.3	643.9	690.9
142.5°	423.1	426.6	438.8	456.4	479.6	506.3	538.3	571.4	606.0	643.9	684.8
145°	440.2	444.5	455.5	471.9	493.8	517.9	547.4	578.2	608.8	641.6	676.7
147.5°	458.5	461.8	472.3	487.5	505.7	527.1	554.9	581.8	609.6	637.7	668.4
150°	470.8	474.1	482.9	497.1	513.5	533.2	558.5	583.6	608.8	635.1	661.3
152.5°	483.1	484.7	493.3	505.9	521.4	539.3	561.9	584.5	607.0	630.7	655.2
155°	500.4	501.4	508.0	520.1	532.2	548.6	567.1	585.8	604.4	623.0	643.9
157.5°	514.8	515.9	521.2	531.7	541.3	555.2	570.9	585.8	599.4	615.1	633.1
160°	524.4	525.6	529.9	538.7	547.4	559.5	572.7	585.8	596.7	609.9	625.2
162.5°	534.1	533.5	537.8	544.8	552.7	562.1	573.5	584.9	594.1	605.5	618.2
165°	545.3	544.2	546.4	552.9	558.5	565.0	574.9	582.5	589.1	596.7	606.6
167.5°	554.5	553.2	555.2	559.3	563.3	567.4	574.6	581.0	584.0	589.1	595.2
170°	560.6	558.5	559.5	562.8	565.0	568.3	573.7	579.2	581.4	584.7	589.1
172.5°	564.1	562.8	562.1	565.4	566.8	569.1	572.9	576.6	577.9	579.5	583.0
175°	568.3	567.1	566.1	568.3	568.3	569.4	571.6	573.7	572.7	573.7	574.9
177.5°	570.2	568.4	567.6	569.4	569.4	569.4	570.2	572.0	570.2	569.4	570.2
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4



TEST NUMBER: P331329-830

CATALOG NUMBER: S122DIP-S485D1080U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	729.0	730.2	731.4	732.0	731.7	731.4	731.2	730.9
5°	724.1	725.3	726.5	727.0	726.7	726.3	726.0	725.8
7.5°	715.9	717.1	718.4	718.8	718.5	718.1	717.7	717.5
10°	708.5	709.8	711.1	711.4	711.0	710.5	710.0	709.5
12.5°	699.9	700.8	701.6	701.9	701.5	701.3	700.9	700.5
15°	684.8	685.4	686.0	685.9	685.1	684.4	683.6	682.8
17.5°	666.8	667.5	668.3	668.2	667.4	666.8	666.0	665.2
20°	652.8	653.3	653.7	653.7	653.0	652.3	651.8	651.1
22.5°	637.9	638.0	638.1	638.0	637.6	637.3	636.9	636.5
25°	613.8	614.1	614.3	614.3	614.1	613.8	613.4	613.1
27.5°	589.9	589.5	589.0	588.4	587.7	586.9	586.2	585.4
30°	571.4	570.9	570.4	569.9	569.2	568.6	568.0	567.3
32.5°	553.2	552.3	551.5	550.7	550.1	549.5	548.8	548.2
35°	524.0	523.0	522.1	521.2	520.5	519.6	518.9	518.1
37.5°	494.6	493.5	492.4	491.3	490.6	489.8	489.1	488.4
40°	474.5	473.1	471.6	470.6	470.0	469.4	468.7	468.1
42.5°	454.5	453.0	451.4	450.3	449.3	448.5	447.6	446.7
45°	423.9	422.2	420.4	419.2	418.6	418.0	417.4	416.7
47.5°	392.0	390.1	388.3	387.0	386.1	385.2	384.3	383.3
50°	371.6	369.3	367.1	365.6	364.9	364.1	363.3	362.5
52.5°	350.3	348.5	346.7	345.3	344.2	343.2	342.1	341.1
55°	318.7	316.8	314.9	313.6	312.7	312.0	311.2	310.5
57.5°	285.8	283.9	282.1	280.9	280.2	279.7	279.1	278.4
60°	264.0	262.3	260.6	259.5	259.0	258.5	258.1	257.6
62.5°	243.5	241.9	240.3	239.2	238.6	238.0	237.4	236.8
65°	211.9	210.5	209.1	207.9	207.2	206.4	205.7	204.8
67.5°	180.7	179.6	178.5	177.7	177.0	176.3	175.8	175.1
70°	160.4	159.3	158.3	157.4	156.7	156.1	155.5	154.9
72.5°	141.3	140.2	139.1	138.3	137.8	137.2	136.8	136.3
75°	111.4	110.6	109.6	109.2	109.6	109.9	110.2	110.6
77.5°	84.8	84.4	83.9	83.4	82.9	82.6	82.1	81.6
80°	67.3	66.8	66.4	66.0	65.7	65.4	65.0	64.8
82.5°	50.2	49.6	49.0	48.6	48.6	48.5	48.4	48.4
85°	26.5	26.0	25.5	25.3	25.1	25.0	24.8	24.6
87.5°	14.1	13.3	13.4	13.4	13.2	13.1	13.0	12.8
90°	35.1	32.9	35.1	36.1	36.1	36.1	36.1	36.1
92.5°	95.5	81.9	72.7	65.9	65.0	61.5	62.4	60.7
95°	286.9	220.1	174.1	150.0	135.7	127.1	123.8	124.8
97.5°	669.4	547.7	429.2	350.2	297.8	270.9	254.9	245.7
100°	999.7	863.9	713.9	581.4	490.5	443.5	411.7	392.0
102.5°	1216.1	1185.3	1075.6	935.3	836.5	756.2	716.5	689.8
105°	1330.3	1454.1	1468.3	1432.2	1364.2	1296.4	1249.3	1234.0
107.5°	1248.0	1434.4	1548.2	1601.2	1609.8	1606.0	1596.6	1576.2
110°	1177.0	1373.0	1513.2	1603.0	1650.0	1670.8	1680.7	1679.6



TEST NUMBER: P331329-830

CATALOG NUMBER: S122DIP-S485D1080U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1112.2	1300.3	1450.1	1553.0	1618.5	1653.3	1672.0	1677.8
115°	1032.6	1201.2	1344.5	1457.4	1535.1	1585.5	1613.9	1623.8
117.5°	972.5	1120.6	1250.7	1356.4	1435.7	1488.8	1518.9	1527.2
120°	942.7	1078.5	1194.6	1294.2	1370.8	1422.3	1454.1	1465.0
122.5°	919.1	1043.5	1153.4	1243.4	1312.1	1362.7	1391.0	1400.1
125°	884.7	997.5	1093.8	1175.9	1239.4	1281.1	1308.4	1317.2
127.5°	850.7	952.8	1043.7	1119.5	1174.9	1213.8	1237.5	1244.5
130°	828.9	923.0	1009.6	1081.8	1135.5	1172.7	1194.6	1203.3
132.5°	807.9	895.0	974.5	1042.4	1095.1	1132.4	1152.5	1160.4
135°	778.4	850.7	923.0	984.3	1031.4	1067.5	1087.2	1091.7
137.5°	755.1	815.5	872.9	926.3	969.2	1000.3	1017.7	1024.2
140°	740.2	792.8	843.1	891.3	926.3	954.8	971.2	977.8
142.5°	727.9	772.6	816.0	856.2	889.5	915.4	930.0	931.3
145°	710.6	746.8	780.7	812.5	838.7	857.3	868.3	871.6
147.5°	697.3	725.8	752.2	775.4	797.1	812.0	819.4	821.4
150°	687.6	711.7	734.7	754.4	770.8	784.0	790.5	791.6
152.5°	678.0	700.3	719.8	736.9	749.8	761.2	766.0	766.2
155°	664.6	682.1	698.5	710.6	722.6	730.3	734.7	732.5
157.5°	649.0	663.7	677.5	686.9	695.5	701.8	703.8	703.8
160°	639.4	651.5	663.5	671.2	678.8	684.3	685.4	685.4
162.5°	629.8	640.1	650.4	656.3	663.9	667.7	668.7	667.9
165°	615.4	623.0	630.7	635.1	639.4	643.9	643.9	642.7
167.5°	601.5	607.5	612.7	616.7	618.6	621.0	620.9	619.5
170°	594.6	597.9	602.2	604.4	605.5	608.8	607.7	605.5
172.5°	586.6	589.1	592.6	593.9	595.0	596.5	595.4	594.1
175°	578.2	579.2	580.3	581.4	581.4	582.5	581.4	579.2
177.5°	572.0	572.0	572.9	572.9	572.9	572.9	572.0	570.2
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4

(END OF REPORT)