

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331292-830

Luminaire Tested: **S122DIP-S485D330U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331292-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S485D330U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2967.5 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331292-830

CATALOG NUMBER: S122DIP-S485D330U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331292-830

CATALOG NUMBER: S122DIP-S485D330U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57	53
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	50	48	44
3	84	74	66	60	78	70	63	58	61	56	52	54	50	46	47	44	41	38
4	77	66	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	28
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	40	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11820	11820	11820
5°	11866	11694	11763
10°	11795	11576	11632
15°	11649	11425	11413
20°	11442	11201	11187
25°	11236	10922	10922
30°	10972	10670	10577
35°	10724	10364	10212
40°	10416	10060	9866
45°	10111	9757	9515
50°	9779	9442	9105
55°	9433	9073	8740
60°	9045	8638	8318
65°	8630	8202	7824
70°	8105	7676	7312
75°	7380	7068	6900
80°	6546	6341	6025
85°	5335	5076	4557



TEST NUMBER: P331292-830

CATALOG NUMBER: S122DIP-S485D330U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	2.3
10°-20°	193.7	6.5
20°-30°	284.7	9.6
30°-40°	330.7	11.1
40°-50°	330.4	11.1
50°-60°	288.1	9.7
60°-70°	213.0	7.2
70°-80°	120.7	4.1
80°-90°	34.0	1.1
90°-100°	25.0	0.8
100°-110°	77.7	2.6
110°-120°	132.8	4.5
120°-130°	174.6	5.9
130°-140°	195.9	6.6
140°-150°	192.1	6.5
150°-160°	161.1	5.4
160°-170°	106.9	3.6
170°-180°	37.4	1.3
0°-30°	547.2	18.4
0°-40°	878.0	29.6
0°-60°	1496.4	50.4
0°-90°	1864.1	62.8
90°-120°	235.4	7.9
90°-150°	798.0	26.9
90°-180°	1103.0	37.2
0°-180°	2967.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	732	732	732	732	732	
5°	732	729	722	727	726	69
15°	697	692	684	686	683	196
25°	631	625	613	614	613	290
35°	544	537	526	522	518	340
45°	443	438	427	420	417	342
55°	335	331	322	314	310	299
65°	226	222	215	208	205	223
75°	118	117	113	109	111	126
85°	29	28	27	25	25	33
90°	0	5	12	11	11	2
95°	17	20	21	21	21	20
105°	72	73	73	74	74	76
115°	133	135	134	134	133	132
125°	194	197	196	195	194	173
135°	251	254	255	255	254	194
145°	304	307	309	309	308	190
155°	348	349	350	352	351	160
165°	379	378	378	380	379	107
175°	394	393	392	394	393	37
180°	395	395	395	395	395	



TEST NUMBER: P331292-830

CATALOG NUMBER: S122DIP-S485D330U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	735.5	734.8	734.2	733.6	732.9	732.0	730.6	729.2	727.8	726.4	727.7
5°	732.1	731.4	730.8	730.2	729.6	728.4	726.7	725.0	723.2	721.5	722.7
7.5°	725.6	724.6	723.7	722.6	721.7	720.4	718.6	716.9	715.1	713.3	714.6
10°	719.4	718.3	717.2	716.1	715.0	713.5	711.6	709.8	707.9	706.1	707.3
12.5°	711.0	710.0	709.0	708.0	707.1	705.7	703.8	701.9	700.0	698.1	699.0
15°	696.9	696.0	695.0	694.1	693.1	691.6	689.6	687.6	685.5	683.5	684.1
17.5°	678.8	678.0	677.0	676.1	675.1	673.6	671.6	669.5	667.4	665.3	666.1
20°	665.9	665.0	664.0	663.1	662.1	660.6	658.4	656.2	654.0	651.9	652.3
22.5°	653.0	651.7	650.4	649.0	647.7	646.0	643.9	641.9	639.8	637.7	637.8
25°	630.7	629.4	628.2	627.0	625.8	623.8	621.1	618.4	615.8	613.1	613.4
27.5°	605.4	604.3	603.1	602.0	600.9	599.3	597.2	595.0	593.0	590.9	590.4
30°	588.5	587.2	586.0	584.8	583.4	581.6	579.3	577.0	574.7	572.3	571.8
32.5°	570.4	569.5	568.4	567.4	566.5	564.7	562.2	559.8	557.3	554.9	554.0
35°	544.1	542.5	541.0	539.4	537.9	535.8	533.4	530.8	528.3	525.8	524.9
37.5°	514.4	513.0	511.7	510.3	508.9	507.0	504.4	502.0	499.5	497.0	495.8
40°	494.2	492.9	491.6	490.4	489.2	487.3	484.7	482.3	479.8	477.3	475.9
42.5°	474.5	473.2	471.9	470.7	469.5	467.6	465.1	462.6	460.1	457.5	456.0
45°	442.8	441.7	440.5	439.5	438.4	436.7	434.3	432.0	429.6	427.3	425.6
47.5°	411.2	410.2	409.2	408.1	407.1	405.4	402.9	400.5	398.0	395.6	393.8
50°	389.3	388.5	387.7	386.9	386.2	384.7	382.5	380.3	378.1	375.9	373.7
52.5°	367.9	366.8	365.8	364.8	363.7	362.2	360.1	358.1	356.0	353.9	352.1
55°	335.1	334.1	333.2	332.2	331.3	329.9	328.0	326.1	324.2	322.3	320.6
57.5°	302.1	301.3	300.6	299.9	299.2	297.7	295.7	293.6	291.5	289.5	287.6
60°	280.1	279.6	278.9	278.2	277.7	276.3	274.1	271.8	269.7	267.5	265.8
62.5°	258.7	257.8	256.7	255.7	254.8	253.4	251.8	250.1	248.4	246.7	245.1
65°	225.9	225.0	224.0	223.1	222.3	220.9	219.4	217.8	216.2	214.7	213.3
67.5°	192.6	191.8	191.1	190.3	189.5	188.5	187.1	185.7	184.3	182.9	181.8
70°	171.7	171.2	170.5	169.8	169.3	168.2	166.8	165.4	164.0	162.6	161.6
72.5°	150.3	149.8	149.1	148.5	147.9	147.1	146.2	145.2	144.4	143.5	142.3
75°	118.3	117.9	117.6	117.3	117.0	116.5	115.6	114.9	114.1	113.3	112.4
77.5°	89.5	89.0	88.5	87.9	87.4	87.0	86.7	86.3	86.1	85.8	85.3
80°	70.4	70.2	70.1	69.9	69.7	69.6	69.2	68.9	68.6	68.2	67.8
82.5°	52.4	52.3	52.3	52.3	52.2	52.1	51.9	51.7	51.6	51.4	50.8
85°	28.8	28.7	28.6	28.4	28.3	28.1	27.9	27.8	27.6	27.4	27.0
87.5°	10.2	10.1	10.1	10.0	9.9	9.9	10.0	10.1	10.2	10.2	9.8
90°	0.4	1.2	2.1	3.0	3.9	5.2	6.8	8.4	10.0	11.7	11.5
92.5°	5.9	6.6	7.3	7.9	8.6	9.0	9.4	9.8	10.2	10.6	10.7
95°	17.3	18.1	18.8	19.5	20.3	20.7	20.8	21.0	21.2	21.3	21.3
97.5°	31.7	32.3	32.9	33.6	34.2	34.7	35.0	35.3	35.5	35.8	35.8
100°	42.3	42.9	43.5	44.1	44.7	45.1	45.2	45.5	45.7	46.0	46.0
102.5°	53.4	53.9	54.4	54.9	55.3	55.8	56.0	56.3	56.6	56.8	56.9
105°	71.6	71.8	72.0	72.3	72.5	72.7	72.9	73.0	73.1	73.2	73.4
107.5°	89.8	90.2	90.5	90.9	91.1	91.3	91.3	91.3	91.3	91.3	91.3
110°	101.6	102.0	102.5	102.9	103.3	103.6	103.6	103.6	103.6	103.6	103.6



TEST NUMBER: P331292-830

CATALOG NUMBER: S122DIP-S485D330U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	114.3	114.8	115.3	115.6	116.1	116.3	116.2	116.2	116.1	116.1	115.9
115°	133.2	133.7	134.1	134.5	135.0	135.2	135.0	134.8	134.7	134.5	134.5
117.5°	151.9	152.6	153.2	153.7	154.4	154.5	154.0	153.6	153.2	152.8	152.6
120°	164.5	165.1	165.7	166.3	166.8	166.8	166.3	165.7	165.1	164.5	164.5
122.5°	176.0	176.6	177.4	178.0	178.8	179.0	178.5	178.1	177.7	177.3	177.1
125°	193.8	194.4	195.1	195.8	196.4	196.7	196.4	196.2	196.0	195.8	195.6
127.5°	211.2	212.1	212.9	213.7	214.5	214.8	214.6	214.3	214.1	213.8	213.5
130°	222.2	223.1	224.0	225.0	225.9	226.4	226.2	226.1	225.9	225.7	225.6
132.5°	234.4	235.2	235.9	236.7	237.5	237.9	237.9	238.0	238.0	238.0	237.7
135°	250.7	251.6	252.4	253.2	254.0	254.5	254.7	254.8	255.0	255.1	255.0
137.5°	268.0	268.6	269.3	270.0	270.7	271.1	271.3	271.5	271.6	271.8	271.8
140°	278.4	279.1	279.7	280.4	281.1	281.5	281.9	282.3	282.7	283.0	283.0
142.5°	289.1	289.7	290.4	291.1	291.7	292.2	292.4	292.7	292.9	293.1	293.2
145°	304.3	304.9	305.4	305.9	306.4	306.9	307.4	307.8	308.2	308.7	308.8
147.5°	318.0	318.7	319.2	319.9	320.5	320.9	321.2	321.6	321.9	322.2	322.3
150°	327.3	327.8	328.2	328.7	329.1	329.5	329.8	330.1	330.4	330.6	330.9
152.5°	335.6	336.0	336.5	337.0	337.3	337.8	338.1	338.5	338.8	339.2	339.5
155°	348.0	348.2	348.5	348.6	348.8	349.1	349.3	349.5	349.8	350.0	350.3
157.5°	358.5	358.7	358.8	359.0	359.2	359.3	359.5	359.6	359.7	359.9	360.3
160°	365.0	365.1	365.2	365.4	365.5	365.7	365.7	365.8	365.9	366.0	366.4
162.5°	370.8	370.9	370.9	370.9	371.0	371.0	371.1	371.2	371.3	371.3	371.8
165°	378.6	378.5	378.4	378.4	378.3	378.2	378.2	378.2	378.2	378.2	378.8
167.5°	385.1	384.9	384.7	384.5	384.3	384.2	384.1	384.1	384.1	384.1	384.6
170°	388.6	388.4	388.1	388.0	387.8	387.6	387.5	387.4	387.4	387.3	387.8
172.5°	391.0	390.8	390.6	390.3	390.1	389.9	389.9	389.8	389.7	389.6	390.2
175°	394.0	393.7	393.5	393.2	393.0	392.9	392.8	392.6	392.4	392.3	392.8
177.5°	395.1	394.9	394.7	394.6	394.5	394.3	394.2	394.1	393.9	393.8	394.2
180°	394.6	394.6	394.6	394.6	394.6	394.6	394.6	394.6	394.6	394.6	394.6



TEST NUMBER: P331292-830

CATALOG NUMBER: S122DIP-S485D330U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	729.0	730.2	731.4	732.0	731.7	731.4	731.2	730.9
5°	724.1	725.3	726.5	727.0	726.7	726.3	726.0	725.8
7.5°	715.9	717.1	718.4	718.8	718.5	718.1	717.7	717.5
10°	708.5	709.8	711.1	711.4	711.0	710.5	710.0	709.5
12.5°	699.9	700.8	701.6	701.9	701.5	701.3	700.9	700.5
15°	684.8	685.4	686.0	685.9	685.1	684.4	683.6	682.8
17.5°	666.8	667.5	668.3	668.2	667.4	666.8	666.0	665.2
20°	652.8	653.3	653.7	653.7	653.0	652.3	651.8	651.1
22.5°	637.9	638.0	638.1	638.0	637.6	637.3	636.9	636.5
25°	613.8	614.1	614.3	614.3	614.1	613.8	613.4	613.1
27.5°	589.9	589.5	589.0	588.4	587.7	586.9	586.2	585.4
30°	571.4	570.9	570.4	569.9	569.2	568.6	568.0	567.3
32.5°	553.2	552.3	551.5	550.7	550.1	549.5	548.8	548.2
35°	524.0	523.0	522.1	521.2	520.5	519.6	518.9	518.1
37.5°	494.6	493.5	492.4	491.3	490.6	489.8	489.1	488.4
40°	474.5	473.1	471.6	470.6	470.0	469.4	468.7	468.1
42.5°	454.5	453.0	451.4	450.3	449.3	448.5	447.6	446.7
45°	423.9	422.2	420.4	419.2	418.6	418.0	417.4	416.7
47.5°	392.0	390.1	388.3	387.0	386.1	385.2	384.3	383.3
50°	371.6	369.3	367.1	365.6	364.9	364.1	363.3	362.5
52.5°	350.3	348.5	346.7	345.3	344.2	343.2	342.1	341.1
55°	318.7	316.8	314.9	313.6	312.7	312.0	311.2	310.5
57.5°	285.8	283.9	282.1	280.9	280.2	279.7	279.1	278.4
60°	264.0	262.3	260.6	259.5	259.0	258.5	258.1	257.6
62.5°	243.5	241.9	240.3	239.2	238.6	238.0	237.4	236.8
65°	211.9	210.5	209.1	207.9	207.2	206.4	205.7	204.8
67.5°	180.7	179.6	178.5	177.7	177.0	176.3	175.8	175.1
70°	160.4	159.3	158.3	157.4	156.7	156.1	155.5	154.9
72.5°	141.3	140.2	139.1	138.3	137.8	137.2	136.8	136.3
75°	111.4	110.6	109.6	109.2	109.6	109.9	110.2	110.6
77.5°	84.8	84.4	83.9	83.4	82.9	82.6	82.1	81.6
80°	67.3	66.8	66.4	66.0	65.7	65.4	65.0	64.8
82.5°	50.2	49.6	49.0	48.6	48.6	48.5	48.4	48.4
85°	26.5	26.0	25.5	25.3	25.1	25.0	24.8	24.6
87.5°	9.4	9.0	8.6	8.3	8.2	8.1	8.0	7.9
90°	11.4	11.2	11.0	11.0	11.1	11.2	11.2	11.3
92.5°	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7
95°	21.3	21.3	21.3	21.2	21.1	20.9	20.8	20.6
97.5°	35.8	35.8	35.8	35.8	35.8	35.8	35.8	35.7
100°	46.0	46.0	46.0	45.9	45.8	45.8	45.7	45.6
102.5°	57.0	57.0	57.1	57.1	57.0	56.9	56.9	56.8
105°	73.5	73.7	73.9	73.9	73.9	73.9	73.9	73.9
107.5°	91.4	91.5	91.5	91.4	91.0	90.8	90.4	90.0
110°	103.6	103.6	103.6	103.5	103.2	103.0	102.8	102.5



TEST NUMBER: P331292-830

CATALOG NUMBER: S122DIP-S485D330U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	115.7	115.6	115.4	115.2	115.1	114.9	114.7	114.5
115°	134.4	134.3	134.2	134.1	133.8	133.7	133.5	133.2
117.5°	152.4	152.2	152.0	151.8	151.7	151.5	151.2	151.0
120°	164.5	164.5	164.5	164.4	164.2	163.9	163.7	163.5
122.5°	176.9	176.7	176.5	176.4	176.3	176.1	175.9	175.8
125°	195.4	195.1	194.9	194.7	194.7	194.6	194.5	194.4
127.5°	213.3	213.0	212.7	212.4	212.3	212.0	211.8	211.5
130°	225.5	225.4	225.2	225.0	224.7	224.3	224.0	223.8
132.5°	237.3	237.0	236.8	236.5	236.2	236.0	235.7	235.5
135°	255.0	254.9	254.8	254.7	254.4	254.2	254.0	253.7
137.5°	271.7	271.6	271.6	271.5	271.2	270.9	270.6	270.2
140°	283.0	283.0	283.0	282.9	282.6	282.3	282.0	281.7
142.5°	293.3	293.3	293.4	293.3	293.0	292.7	292.4	292.1
145°	308.9	308.9	309.0	308.9	308.6	308.3	308.0	307.6
147.5°	322.4	322.6	322.8	322.7	322.4	322.2	321.9	321.6
150°	331.1	331.3	331.6	331.6	331.3	331.1	330.9	330.6
152.5°	339.8	340.1	340.4	340.4	340.1	339.8	339.5	339.2
155°	350.7	351.1	351.5	351.6	351.3	351.1	350.9	350.6
157.5°	360.8	361.4	361.8	361.9	361.6	361.2	360.9	360.5
160°	366.8	367.3	367.8	367.8	367.5	367.2	366.9	366.6
162.5°	372.3	372.8	373.3	373.3	373.1	372.7	372.3	371.9
165°	379.3	379.8	380.3	380.4	380.0	379.7	379.3	379.0
167.5°	385.1	385.6	386.2	386.3	385.9	385.4	385.0	384.7
170°	388.3	388.8	389.4	389.4	389.0	388.5	388.0	387.6
172.5°	390.7	391.2	391.7	391.8	391.3	390.9	390.5	390.0
175°	393.3	393.8	394.4	394.4	394.0	393.5	393.0	392.6
177.5°	394.5	394.8	395.2	395.2	394.8	394.5	394.2	393.8
180°	394.6	394.6	394.6	394.6	394.6	394.6	394.6	394.6

(END OF REPORT)