

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331299-830

Luminaire Tested: **S122DIP-S485D530U830-4F0-1E-UDD-D4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331299-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S485D530U830-4F0-1E-UDD-D4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3800.5 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331299-830

CATALOG NUMBER: S122DIP-S485D530U830-4F0-1E-UDD-D4

Luminous Intensity Polar Plot





TEST NUMBER: P331299-830

CATALOG NUMBER: S122DIP-S485D530U830-4F0-1E-UDD-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	95	90	86	82	87	82	79	75	68	65	63	54	53	51	42	41	40	34
2	86	78	71	66	78	71	66	61	59	54	51	47	44	41	36	34	32	27
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	32	29	27	23
4	71	60	52	45	65	55	48	42	45	40	35	36	32	29	28	25	23	19
5	65	53	45	39	59	49	41	36	40	35	30	32	28	25	25	22	20	16
6	60	47	39	33	54	44	36	31	36	30	26	29	25	22	23	20	17	14
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	21	18	15	12
8	51	39	31	25	47	36	29	24	30	24	20	24	20	17	19	16	13	11
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12	10
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7842	7842	7842
5°	7880	7549	7520
10°	7831	7327	7244
15°	7723	7090	6952
20°	7587	6836	6671
25°	7453	6592	6417
30°	7262	6342	6160
35°	7069	6100	5981
40°	6869	5895	5801
45°	6677	5709	5648
50°	6471	5541	5495
55°	6254	5363	5341
60°	5990	5177	5178
65°	5716	4959	4983
70°	5407	4723	4775
75°	5013	4495	4582
80°	4391	4260	4385
85°	3800	4054	4232



TEST NUMBER: P331299-830

CATALOG NUMBER: S122DIP-S485D530U830-4F0-1E-UDD-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	1.2
10°-20°	132.0	3.5
20°-30°	200.0	5.3
30°-40°	243.6	6.4
40°-50°	262.1	6.9
50°-60°	254.5	6.7
60°-70°	222.2	5.8
70°-80°	171.1	4.5
80°-90°	117.3	3.1
90°-100°	190.9	5.0
100°-110°	437.0	11.5
110°-120°	441.0	11.6
120°-130°	353.0	9.3
130°-140°	275.3	7.2
140°-150°	202.8	5.3
150°-160°	141.4	3.7
160°-170°	83.3	2.2
170°-180°	27.1	0.7
0°-30°	378.0	9.9
0°-40°	621.6	16.4
0°-60°	1138.1	29.9
0°-90°	1648.8	43.4
90°-120°	1068.9	28.1
90°-150°	1900.0	50.0
90°-180°	2152.0	56.6
0°-180°	3800.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	486	486	486	486	486	
5°	487	485	481	485	484	46
15°	465	466	466	472	472	131
25°	422	427	434	442	444	194
35°	364	376	389	404	410	227
45°	298	318	342	363	371	230
55°	229	255	291	315	325	204
65°	156	191	232	260	270	155
75°	87	126	171	200	210	92
85°	25	69	114	142	153	27
90°	8	55	111	138	147	6
95°	24	85	292	186	177	24
105°	69	124	459	796	699	74
115°	118	158	376	750	868	117
125°	163	194	344	599	696	145
135°	190	227	324	490	564	147
145°	216	248	315	395	436	136
155°	246	265	306	346	360	113
165°	268	276	293	311	316	75
175°	279	279	282	285	284	26
180°	280	280	280	280	280	



TEST NUMBER: P331299-830

CATALOG NUMBER: S122DIP-S485D530U830-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.7	485.7	485.7	485.7	485.7	485.7	485.7	485.7	485.7	485.7	485.7
2.5°	488.5	488.1	487.8	487.4	487.0	486.4	485.5	484.7	483.8	482.9	483.5
5°	487.1	486.6	486.2	485.7	485.2	484.6	483.6	482.7	481.7	480.8	481.7
7.5°	482.8	482.4	482.1	481.8	481.5	481.0	480.2	479.6	478.8	478.1	479.2
10°	479.4	479.1	478.7	478.4	478.2	477.8	477.3	476.8	476.4	475.9	477.1
12.5°	473.7	473.8	473.9	473.9	474.0	473.8	473.5	473.2	472.8	472.5	473.7
15°	464.6	464.9	465.2	465.5	465.8	466.0	466.0	466.0	466.0	466.0	467.4
17.5°	452.8	453.5	454.1	454.8	455.4	456.0	456.5	456.9	457.5	458.0	459.4
20°	444.9	445.6	446.5	447.2	448.0	448.7	449.3	450.0	450.6	451.2	452.9
22.5°	436.4	437.3	438.3	439.1	440.1	440.9	441.9	442.7	443.6	444.5	446.2
25°	422.4	423.5	424.5	425.7	426.7	428.0	429.4	430.8	432.3	433.6	435.5
27.5°	405.5	407.3	409.1	410.9	412.6	414.3	415.9	417.6	419.2	420.9	423.3
30°	394.2	396.2	398.2	400.3	402.4	404.4	406.4	408.4	410.5	412.5	415.0
32.5°	381.8	384.1	386.3	388.7	391.0	393.3	395.7	398.1	400.5	402.9	405.8
35°	363.9	366.6	369.3	371.9	374.6	377.4	380.3	383.3	386.3	389.3	392.7
37.5°	344.5	347.6	350.6	353.7	356.8	360.2	364.1	367.9	371.7	375.6	379.5
40°	331.6	335.0	338.5	341.9	345.3	349.1	353.4	357.6	361.8	366.1	370.1
42.5°	319.1	322.6	326.0	329.5	332.9	337.1	342.0	346.8	351.7	356.5	360.9
45°	298.5	302.7	306.9	311.1	315.4	320.2	325.6	331.1	336.7	342.1	346.9
47.5°	278.1	282.7	287.3	291.8	296.4	302.0	308.4	314.8	321.2	327.6	332.7
50°	264.0	268.8	273.7	278.5	283.3	289.3	296.3	303.4	310.5	317.4	322.8
52.5°	250.4	255.5	260.6	265.8	270.9	277.1	284.6	291.9	299.4	306.8	312.2
55°	228.8	234.4	240.1	245.6	251.3	258.2	266.4	274.5	282.6	290.7	296.3
57.5°	207.4	213.8	220.1	226.4	232.8	240.1	248.4	256.7	264.9	273.2	279.4
60°	192.2	198.9	205.7	212.4	219.0	226.9	235.8	244.7	253.6	262.6	268.5
62.5°	178.6	185.6	192.7	199.6	206.6	214.5	223.4	232.3	241.3	250.2	256.5
65°	156.3	163.9	171.6	179.3	186.9	195.4	204.6	213.9	223.1	232.3	238.7
67.5°	135.7	143.7	151.7	159.8	167.8	176.4	186.0	195.4	204.8	214.2	220.7
70°	121.1	129.2	137.3	145.4	153.6	162.5	172.2	181.9	191.6	201.3	208.0
72.5°	107.5	115.9	124.3	132.7	141.1	150.2	160.0	169.8	179.6	189.5	196.1
75°	86.6	95.4	104.1	112.8	121.6	131.0	141.0	151.0	161.1	171.1	177.8
77.5°	66.4	75.5	84.6	93.8	103.0	112.6	122.8	133.0	143.2	153.4	160.0
80°	52.8	62.3	71.9	81.4	91.0	100.9	111.0	121.1	131.3	141.5	148.1
82.5°	41.6	51.0	60.3	69.7	79.2	89.1	99.3	109.6	119.9	130.3	136.8
85°	25.4	35.1	44.8	54.5	64.1	74.0	84.0	94.0	104.1	114.0	120.6
87.5°	13.9	23.6	33.3	42.9	52.4	62.4	73.0	83.7	94.3	104.4	110.7
90°	7.5	18.3	29.5	39.6	49.8	60.9	73.6	87.4	100.7	111.2	116.9
92.5°	13.0	24.4	36.7	47.5	59.6	73.7	95.5	122.2	147.1	157.7	153.0
95°	24.4	33.9	46.7	58.9	74.8	96.0	130.2	186.3	258.1	291.6	271.3
97.5°	35.5	45.1	57.2	71.1	87.6	109.9	150.0	224.1	336.8	434.6	458.0
100°	46.3	53.7	64.4	78.7	95.3	117.6	154.9	229.1	354.0	495.0	578.2
102.5°	55.6	62.1	72.2	86.1	102.5	124.5	159.4	226.2	342.1	493.2	620.6
105°	69.1	75.8	84.1	96.7	113.0	134.4	167.9	223.8	320.7	458.8	607.3
107.5°	84.5	89.8	97.1	108.1	123.5	144.3	176.6	226.1	307.3	422.5	554.1
110°	94.2	99.4	105.8	115.9	130.4	151.4	182.7	229.0	302.3	404.5	520.8



TEST NUMBER: P331299-830

CATALOG NUMBER: S122DIP-S485D530U830-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	103.7	108.4	114.7	123.9	137.4	158.3	188.4	232.2	299.2	391.2	496.2
115°	118.4	122.8	127.7	135.9	148.4	167.3	197.5	237.2	296.4	375.5	465.1
117.5°	132.9	136.2	140.5	147.4	158.8	177.7	205.6	242.9	295.0	364.7	443.2
120°	142.4	145.2	149.0	154.5	165.9	184.4	211.6	246.9	294.5	358.3	430.9
122.5°	151.5	153.4	156.8	162.4	173.4	191.9	217.5	250.2	294.5	353.2	420.1
125°	162.7	164.3	167.5	174.0	184.7	202.3	226.6	255.8	294.2	344.3	403.9
127.5°	172.1	174.1	178.5	185.4	195.6	213.0	235.8	261.6	294.6	337.4	388.8
130°	177.7	179.7	184.9	192.3	202.9	219.5	241.6	265.3	295.5	333.2	378.8
132.5°	182.9	185.3	191.0	198.8	209.8	226.0	246.5	269.0	296.2	329.3	370.1
135°	189.9	192.1	198.5	206.6	219.0	234.8	253.5	273.9	297.0	324.3	358.3
137.5°	197.2	199.7	206.2	214.7	227.0	241.3	258.9	277.2	297.5	320.2	348.7
140°	202.8	204.8	211.1	219.5	231.2	245.2	261.7	278.7	297.3	317.4	343.1
142.5°	208.4	210.0	215.8	224.2	235.5	248.5	264.4	280.6	297.7	316.3	338.5
145°	216.1	218.2	223.6	231.7	242.4	254.2	268.7	283.8	298.9	315.0	333.1
147.5°	225.1	226.7	231.9	239.3	248.3	258.7	272.4	285.7	299.3	313.0	328.2
150°	231.1	232.7	237.0	244.0	252.1	261.7	274.1	286.5	298.9	311.8	324.7
152.5°	237.1	237.9	242.2	248.4	256.0	264.8	275.9	286.9	298.0	309.6	321.7
155°	245.6	246.2	249.4	255.3	261.3	269.3	278.4	287.6	296.7	305.9	316.0
157.5°	252.7	253.3	255.9	261.0	265.8	272.5	280.2	287.6	294.3	302.0	310.8
160°	257.5	258.0	260.1	264.5	268.7	274.7	281.2	287.6	292.9	299.4	306.9
162.5°	262.2	261.8	264.0	267.5	271.4	276.0	281.5	287.1	291.6	297.3	303.5
165°	267.7	267.1	268.2	271.5	274.1	277.4	282.2	286.0	289.2	292.9	297.7
167.5°	272.2	271.5	272.5	274.6	276.5	278.5	282.1	285.2	286.7	289.2	292.2
170°	275.2	274.1	274.7	276.3	277.4	279.0	281.6	284.4	285.4	287.0	289.2
172.5°	276.9	276.3	276.0	277.6	278.2	279.4	281.3	283.0	283.7	284.5	286.2
175°	279.0	278.4	277.9	279.0	279.0	279.5	280.6	281.6	281.2	281.6	282.2
177.5°	279.9	279.1	278.6	279.5	279.5	279.5	279.9	280.8	279.9	279.5	279.9
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5



TEST NUMBER: P331299-830

CATALOG NUMBER: S122DIP-S485D530U830-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	485.7	485.7	485.7	485.7	485.7	485.7	485.7	485.7
2.5°	484.2	484.7	485.4	485.6	485.3	485.1	484.8	484.6
5°	482.7	483.6	484.6	484.9	484.7	484.7	484.5	484.3
7.5°	480.3	481.5	482.6	483.1	483.0	482.8	482.6	482.5
10°	478.3	479.6	480.9	481.5	481.3	481.1	481.0	480.8
12.5°	474.9	476.3	477.5	478.1	477.9	477.7	477.6	477.4
15°	468.8	470.2	471.6	472.2	472.1	471.9	471.7	471.6
17.5°	460.9	462.4	463.8	464.6	464.6	464.6	464.6	464.6
20°	454.7	456.4	458.1	458.9	458.9	458.9	458.9	458.9
22.5°	447.9	449.6	451.4	452.3	452.6	452.8	453.1	453.4
25°	437.3	439.2	441.1	442.3	442.8	443.3	443.7	444.2
27.5°	425.7	428.1	430.5	431.8	432.2	432.5	432.8	433.2
30°	417.5	420.0	422.5	424.0	424.4	424.9	425.4	425.8
32.5°	408.7	411.5	414.4	416.3	417.2	418.0	418.9	419.7
35°	396.2	399.6	403.0	405.3	406.4	407.5	408.6	409.7
37.5°	383.2	387.1	390.9	393.3	394.5	395.7	396.8	398.0
40°	374.2	378.2	382.3	385.0	386.4	387.9	389.3	390.7
42.5°	365.3	369.8	374.2	377.2	378.5	379.9	381.4	382.8
45°	351.9	356.7	361.5	364.7	366.3	367.9	369.4	371.0
47.5°	337.7	342.8	347.9	351.3	353.0	354.7	356.5	358.2
50°	328.1	333.4	338.7	342.2	344.0	345.7	347.4	349.1
52.5°	317.6	323.1	328.6	332.2	334.0	335.9	337.7	339.6
55°	302.0	307.6	313.2	317.1	319.1	321.1	323.2	325.2
57.5°	285.4	291.4	297.6	301.6	303.7	305.8	307.8	309.9
60°	274.5	280.4	286.3	290.4	292.6	294.8	297.0	299.2
62.5°	262.8	269.1	275.4	279.7	281.7	283.8	285.9	287.9
65°	245.2	251.6	258.0	262.2	264.2	266.3	268.2	270.3
67.5°	227.2	233.7	240.2	244.5	246.6	248.7	250.9	253.0
70°	214.8	221.5	228.2	232.5	234.4	236.3	238.2	240.1
72.5°	202.7	209.3	215.9	220.4	222.5	224.8	227.1	229.3
75°	184.5	191.2	197.9	202.4	204.3	206.4	208.4	210.5
77.5°	166.7	173.4	180.1	184.5	186.7	188.9	191.1	193.3
80°	154.7	161.2	167.8	172.1	174.4	176.5	178.7	180.9
82.5°	143.4	150.0	156.5	160.8	162.9	164.9	167.0	169.1
85°	127.1	133.7	140.3	144.7	146.8	149.1	151.3	153.4
87.5°	117.0	123.2	129.8	134.0	136.1	138.1	140.1	142.0
90°	122.6	127.8	135.2	139.8	141.7	143.5	145.3	147.2
92.5°	146.9	146.5	148.1	148.7	150.1	150.3	152.7	153.6
95°	233.7	206.8	190.2	182.3	177.2	174.7	175.0	177.4
97.5°	415.1	361.1	308.8	273.8	250.0	238.6	232.5	229.9
100°	572.7	511.9	444.0	382.8	339.8	318.4	304.5	296.6
102.5°	674.8	665.3	617.2	552.0	505.2	467.4	449.7	438.3
105°	724.5	790.8	803.2	789.1	757.5	725.9	704.6	698.7
107.5°	678.0	774.7	835.8	865.3	871.3	871.2	868.3	860.0
110°	639.2	740.5	814.3	861.7	886.6	898.4	905.0	906.3



TEST NUMBER: P331299-830

CATALOG NUMBER: S122DIP-S485D530U830-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	603.5	700.8	779.4	833.2	867.1	885.9	896.8	901.4
115°	558.5	646.0	721.0	779.7	819.5	846.0	861.7	868.3
117.5°	523.1	600.5	668.9	724.0	764.5	792.2	808.5	814.2
120°	504.6	575.7	637.1	689.0	728.4	755.4	772.6	779.8
122.5°	489.4	554.7	612.9	660.0	695.2	721.5	736.9	742.8
125°	466.7	526.3	577.8	620.9	653.6	675.3	690.2	695.9
127.5°	444.3	498.2	546.8	586.5	615.1	635.7	648.7	653.5
130°	429.9	479.8	526.1	564.1	591.6	611.2	623.2	628.8
132.5°	415.9	462.3	505.0	540.7	568.0	587.5	598.6	603.7
135°	396.5	435.3	474.0	506.4	530.7	549.7	560.6	564.1
137.5°	380.1	412.6	443.7	471.9	494.0	510.4	519.9	524.2
140°	369.8	398.0	425.3	450.7	468.8	483.7	492.8	496.9
142.5°	361.7	385.6	408.9	430.1	447.2	460.7	468.7	470.1
145°	350.7	369.4	387.0	403.4	417.2	427.1	433.2	435.6
147.5°	342.5	356.7	369.8	381.4	392.5	400.1	404.2	405.5
150°	337.5	349.4	360.7	370.3	378.4	384.8	388.0	388.6
152.5°	332.8	343.8	353.4	361.7	368.1	373.7	376.1	376.2
155°	326.3	334.9	342.9	348.8	354.8	358.5	360.7	359.6
157.5°	318.7	325.8	332.6	337.2	341.4	344.6	345.5	345.5
160°	313.9	319.8	325.7	329.5	333.3	335.9	336.5	336.5
162.5°	309.2	314.2	319.3	322.2	325.9	327.8	328.3	327.9
165°	302.1	305.9	309.6	311.8	313.9	316.0	316.0	315.6
167.5°	295.3	298.2	300.8	302.7	303.7	304.9	304.8	304.2
170°	291.9	293.5	295.7	296.7	297.3	298.9	298.3	297.3
172.5°	288.0	289.2	290.9	291.5	292.1	292.8	292.3	291.6
175°	283.8	284.4	284.9	285.4	285.4	286.0	285.4	284.4
177.5°	280.8	280.8	281.3	281.3	281.3	281.3	280.8	279.9
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5

(END OF REPORT)