

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331353-940

Luminaire Tested: **S122DIP-S675D725U940-4F0-1E-UDD-D4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331353-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S675D725U940-4F0-1E-UDD-D4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4921.8 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331353-940

CATALOG NUMBER: S122DIP-S675D725U940-4F0-1E-UDD-D4

Luminous Intensity Polar Plot





TEST NUMBER: P331353-940

CATALOG NUMBER: S122DIP-S675D725U940-4F0-1E-UDD-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	95	90	86	82	86	82	79	75	68	65	63	54	53	51	42	41	40	34
2	86	78	71	66	78	71	66	61	59	54	51	47	44	41	36	34	32	27
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	32	29	27	22
4	71	60	52	45	65	55	48	42	45	40	35	36	32	29	28	25	23	19
5	65	53	45	39	59	49	41	36	40	35	30	32	28	25	25	22	20	16
6	60	47	39	33	54	44	36	31	36	30	26	29	25	22	23	20	17	14
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	21	18	15	12
8	51	39	31	25	47	36	29	24	30	24	20	24	20	17	19	16	13	11
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12	10
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10141	10141	10141
5°	10191	9762	9724
10°	10126	9474	9367
15°	9987	9168	8990
20°	9810	8841	8627
25°	9637	8525	8298
30°	9392	8201	7967
35°	9142	7888	7735
40°	8880	7621	7501
45°	8632	7383	7302
50°	8365	7166	7106
55°	8089	6934	6906
60°	7745	6695	6695
65°	7391	6412	6445
70°	6992	6110	6173
75°	6483	5811	5925
80°	5680	5509	5672
85°	4908	5245	5473



TEST NUMBER: P331353-940

CATALOG NUMBER: S122DIP-S675D725U940-4F0-1E-UDD-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.5	1.2
10°-20°	170.7	3.5
20°-30°	258.6	5.3
30°-40°	315.0	6.4
40°-50°	338.9	6.9
50°-60°	329.1	6.7
60°-70°	287.4	5.8
70°-80°	221.2	4.5
80°-90°	151.7	3.1
90°-100°	247.2	5.0
100°-110°	566.5	11.5
110°-120°	571.8	11.6
120°-130°	457.6	9.3
130°-140°	356.9	7.3
140°-150°	263.0	5.3
150°-160°	183.4	3.7
160°-170°	108.0	2.2
170°-180°	35.1	0.7
0°-30°	488.8	9.9
0°-40°	803.8	16.3
0°-60°	1471.8	29.9
0°-90°	2132.1	43.3
90°-120°	1385.5	28.2
90°-150°	2463.1	50.0
90°-180°	2790.0	56.7
0°-180°	4921.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	628	628	628	628	628	
5°	630	627	622	627	626	60
15°	601	602	603	610	610	169
25°	546	553	561	571	574	251
35°	471	486	503	523	530	294
45°	386	411	442	470	480	298
55°	296	329	376	408	420	264
65°	202	247	300	336	350	201
75°	112	163	221	259	272	118
85°	33	89	148	184	198	35
90°	10	72	144	178	190	7
95°	32	111	378	241	230	32
105°	90	160	595	1032	906	96
115°	154	205	487	973	1126	152
125°	211	251	446	777	902	188
135°	246	294	421	636	731	190
145°	280	322	408	513	565	176
155°	318	344	397	449	466	147
165°	347	358	380	403	409	98
175°	362	362	365	370	369	34
180°	362	362	362	362	362	



TEST NUMBER: P331353-940

CATALOG NUMBER: S122DIP-S675D725U940-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	628.1	628.1	628.1	628.1	628.1	628.1	628.1	628.1	628.1	628.1	628.1
2.5°	631.8	631.2	630.8	630.3	629.8	629.0	627.9	626.7	625.6	624.5	625.3
5°	629.9	629.3	628.7	628.1	627.5	626.6	625.4	624.2	622.9	621.7	622.9
7.5°	624.3	623.8	623.5	623.0	622.7	622.0	621.1	620.1	619.2	618.3	619.7
10°	619.9	619.5	619.1	618.7	618.3	617.8	617.2	616.6	616.0	615.4	617.0
12.5°	612.6	612.7	612.8	612.9	613.0	612.8	612.3	611.9	611.4	611.0	612.6
15°	600.8	601.2	601.6	602.0	602.4	602.6	602.6	602.6	602.6	602.6	604.4
17.5°	585.5	586.4	587.2	588.1	588.9	589.7	590.3	590.9	591.6	592.3	594.1
20°	575.3	576.3	577.3	578.4	579.3	580.2	581.0	581.9	582.7	583.5	585.8
22.5°	564.4	565.5	566.8	567.9	569.1	570.2	571.4	572.5	573.6	574.8	577.0
25°	546.2	547.6	549.0	550.5	551.9	553.5	555.3	557.1	558.9	560.7	563.2
27.5°	524.3	526.6	529.0	531.3	533.6	535.8	538.0	540.1	542.2	544.4	547.4
30°	509.8	512.4	515.1	517.6	520.3	522.9	525.6	528.2	530.8	533.4	536.6
32.5°	493.7	496.7	499.6	502.6	505.6	508.6	511.8	514.8	517.9	521.0	524.8
35°	470.6	474.0	477.5	480.9	484.4	488.0	491.9	495.7	499.5	503.4	507.8
37.5°	445.5	449.5	453.4	457.4	461.4	465.8	470.8	475.8	480.7	485.7	490.7
40°	428.7	433.2	437.7	442.1	446.6	451.5	457.0	462.4	467.9	473.3	478.6
42.5°	412.8	417.1	421.6	426.1	430.5	435.9	442.2	448.4	454.7	461.0	466.7
45°	385.9	391.5	396.9	402.3	407.8	414.1	421.2	428.3	435.3	442.4	448.7
47.5°	359.5	365.5	371.5	377.4	383.3	390.5	398.8	407.1	415.4	423.7	430.3
50°	341.3	347.7	353.9	360.2	366.4	374.2	383.3	392.4	401.4	410.5	417.4
52.5°	323.9	330.5	337.1	343.7	350.3	358.4	367.9	377.6	387.1	396.7	403.8
55°	295.9	303.1	310.4	317.7	324.9	333.9	344.4	354.9	365.4	375.9	383.3
57.5°	268.1	276.4	284.6	292.8	301.0	310.5	321.2	331.9	342.7	353.4	361.2
60°	248.5	257.2	265.9	274.6	283.3	293.5	305.0	316.5	328.0	339.6	347.2
62.5°	231.0	240.0	249.1	258.1	267.2	277.4	288.9	300.4	312.0	323.5	331.7
65°	202.1	212.0	221.9	231.8	241.7	252.6	264.6	276.5	288.5	300.4	308.7
67.5°	175.5	185.8	196.3	206.6	217.0	228.2	240.4	252.6	264.8	277.1	285.4
70°	156.6	167.1	177.6	188.2	198.7	210.2	222.7	235.2	247.8	260.4	269.0
72.5°	139.1	149.9	160.8	171.7	182.4	194.2	207.0	219.6	232.4	245.0	253.6
75°	112.0	123.3	134.6	146.0	157.3	169.4	182.4	195.3	208.2	221.2	229.9
77.5°	85.8	97.6	109.5	121.3	133.1	145.7	158.8	172.0	185.1	198.2	207.0
80°	68.3	80.6	92.9	105.3	117.6	130.4	143.6	156.7	169.8	183.0	191.5
82.5°	53.7	65.9	78.0	90.2	102.5	115.1	128.5	141.8	155.1	168.4	176.9
85°	32.8	45.3	57.9	70.4	82.9	95.7	108.6	121.5	134.6	147.5	156.0
87.5°	18.0	30.5	43.1	55.4	67.8	80.7	94.3	108.3	122.0	135.1	143.2
90°	9.8	23.6	38.2	51.3	64.4	78.8	95.2	113.1	130.2	143.8	151.2
92.5°	16.9	31.6	47.5	61.5	77.1	95.4	123.6	158.3	190.5	204.2	198.0
95°	31.7	44.0	60.5	76.2	96.9	124.5	168.6	241.4	334.4	377.9	351.4
97.5°	46.1	58.3	74.2	92.1	113.4	142.4	194.3	290.5	436.5	563.3	593.7
100°	60.0	69.6	83.4	102.0	123.4	152.4	200.6	297.0	458.9	641.7	749.6
102.5°	72.1	80.5	93.6	111.6	133.0	161.4	206.5	293.1	443.5	639.4	804.5
105°	89.6	98.3	109.0	125.3	146.5	174.2	217.5	290.1	415.6	594.8	787.3
107.5°	109.5	116.4	125.8	140.2	160.1	187.1	228.9	293.1	398.2	547.8	718.4
110°	122.2	128.9	137.2	150.3	169.0	196.2	236.7	296.9	391.8	524.4	675.2



TEST NUMBER: P331353-940

CATALOG NUMBER: S122DIP-S675D725U940-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.4	140.6	148.7	160.6	178.1	205.3	244.2	301.1	387.8	507.0	643.3
115°	153.5	159.3	165.6	176.2	192.3	216.9	255.9	307.6	384.2	486.8	603.0
117.5°	172.4	176.6	182.3	191.1	206.0	230.4	266.5	314.9	382.5	472.8	574.5
120°	184.7	188.2	193.2	200.4	215.1	239.1	274.3	320.0	381.8	464.5	558.7
122.5°	196.4	198.9	203.4	210.6	224.9	248.9	282.0	324.5	381.8	457.9	544.7
125°	211.0	213.0	217.2	225.6	239.5	262.3	293.8	331.7	381.4	446.4	523.6
127.5°	223.2	225.8	231.4	240.4	253.6	276.2	305.9	339.2	382.1	437.5	504.1
130°	230.4	233.0	239.8	249.3	263.1	284.6	313.3	344.0	383.2	431.9	491.2
132.5°	237.1	240.3	247.6	257.7	272.1	293.1	319.7	348.8	384.1	427.0	480.0
135°	246.3	249.1	257.4	267.9	283.9	304.4	328.8	355.2	385.1	420.6	464.6
137.5°	255.7	259.0	267.4	278.5	294.4	312.9	335.8	359.4	385.7	415.2	452.2
140°	263.0	265.6	273.8	284.7	299.8	318.1	339.4	361.4	385.5	411.7	444.9
142.5°	270.3	272.2	279.9	290.9	305.4	322.4	342.8	363.9	386.0	410.2	438.9
145°	280.2	283.0	290.0	300.4	314.3	329.7	348.6	368.0	387.5	408.5	432.0
147.5°	291.9	294.0	300.7	310.3	321.9	335.6	353.3	370.4	388.2	406.0	425.6
150°	299.7	301.8	307.4	316.5	326.9	339.5	355.5	371.5	387.5	404.3	421.0
152.5°	307.6	308.5	314.1	322.0	331.9	343.4	357.8	372.1	386.5	401.5	417.1
155°	318.5	319.2	323.4	331.1	338.8	349.2	361.1	372.9	384.8	396.6	409.8
157.5°	327.8	328.4	331.8	338.5	344.6	353.4	363.5	372.9	381.6	391.6	403.1
160°	333.9	334.6	337.3	343.0	348.6	356.1	364.5	372.9	379.9	388.3	398.1
162.5°	340.0	339.6	342.4	346.9	351.9	357.8	365.2	372.4	378.3	385.5	393.5
165°	347.1	346.4	347.9	352.0	355.5	359.7	366.0	370.9	375.1	379.9	386.2
167.5°	353.0	352.1	353.4	356.1	358.6	361.2	365.8	369.9	371.8	375.1	378.9
170°	356.9	355.5	356.1	358.3	359.7	361.8	365.2	368.7	370.1	372.2	375.1
172.5°	359.1	358.3	357.8	360.0	360.8	362.3	364.7	367.0	367.9	368.9	371.1
175°	361.8	361.1	360.3	361.8	361.8	362.5	363.8	365.2	364.5	365.2	366.0
177.5°	363.0	361.9	361.3	362.5	362.5	362.5	363.0	364.2	363.0	362.5	363.0
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5



TEST NUMBER: P331353-940

CATALOG NUMBER: S122DIP-S675D725U940-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	628.1	628.1	628.1	628.1	628.1	628.1	628.1	628.1
2.5°	626.1	626.9	627.7	627.9	627.6	627.3	627.0	626.7
5°	624.2	625.4	626.6	627.1	626.9	626.7	626.5	626.2
7.5°	621.2	622.7	624.1	624.7	624.6	624.3	624.1	623.9
10°	618.6	620.2	621.9	622.5	622.3	622.1	622.0	621.7
12.5°	614.2	615.8	617.5	618.1	618.0	617.8	617.6	617.3
15°	606.3	608.1	609.9	610.7	610.6	610.3	610.1	609.9
17.5°	596.0	598.0	599.9	600.8	600.8	600.8	600.8	600.8
20°	588.0	590.2	592.4	593.5	593.5	593.5	593.5	593.5
22.5°	579.3	581.5	583.6	585.0	585.2	585.6	585.9	586.2
25°	565.6	568.0	570.4	571.9	572.6	573.2	573.8	574.4
27.5°	550.5	553.6	556.7	558.4	558.8	559.3	559.7	560.2
30°	539.9	543.1	546.4	548.3	548.9	549.6	550.1	550.7
32.5°	528.5	532.3	535.9	538.3	539.5	540.6	541.6	542.7
35°	512.3	516.7	521.2	524.1	525.6	527.0	528.3	529.8
37.5°	495.6	500.5	505.5	508.7	510.2	511.7	513.2	514.7
40°	483.8	489.1	494.4	497.9	499.7	501.6	503.4	505.2
42.5°	472.4	478.2	483.9	487.8	489.5	491.4	493.2	495.0
45°	455.0	461.2	467.5	471.6	473.7	475.7	477.7	479.7
47.5°	436.8	443.4	449.9	454.2	456.5	458.7	460.9	463.2
50°	424.3	431.1	438.1	442.6	444.9	447.1	449.2	451.5
52.5°	410.8	417.9	424.9	429.6	431.9	434.4	436.8	439.2
55°	390.5	397.8	405.1	410.0	412.7	415.3	417.9	420.5
57.5°	369.1	376.9	384.8	390.0	392.7	395.4	398.1	400.7
60°	354.9	362.6	370.3	375.6	378.4	381.2	384.1	386.9
62.5°	339.8	348.0	356.2	361.7	364.3	366.9	369.6	372.3
65°	317.0	325.3	333.6	339.0	341.7	344.3	347.0	349.6
67.5°	293.8	302.2	310.6	316.2	318.9	321.6	324.4	327.2
70°	277.8	286.4	295.2	300.7	303.1	305.6	308.0	310.4
72.5°	262.2	270.6	279.2	284.9	287.8	290.8	293.6	296.6
75°	238.6	247.3	256.0	261.6	264.3	266.9	269.6	272.2
77.5°	215.6	224.3	232.9	238.6	241.5	244.3	247.1	249.9
80°	199.9	208.5	217.0	222.7	225.4	228.3	231.1	234.0
82.5°	185.4	193.9	202.4	207.9	210.6	213.3	216.0	218.6
85°	164.4	173.0	181.5	187.1	189.9	192.8	195.6	198.4
87.5°	151.3	159.3	167.8	173.3	176.0	178.6	181.2	183.8
90°	158.6	165.3	174.9	180.7	183.2	185.7	188.1	190.5
92.5°	190.3	189.6	191.6	192.4	194.3	194.6	197.5	198.9
95°	302.6	267.9	246.3	235.9	229.3	226.2	226.6	229.7
97.5°	538.0	468.0	400.0	354.6	323.7	309.0	301.1	297.7
100°	742.4	663.4	575.4	496.0	440.3	412.6	394.6	384.2
102.5°	874.8	862.6	800.0	715.4	654.8	605.8	582.8	568.0
105°	939.3	1025.2	1041.3	1023.0	982.0	941.0	913.3	905.7
107.5°	879.0	1004.3	1083.6	1121.9	1129.5	1129.4	1125.6	1114.9
110°	828.8	960.0	1055.7	1117.1	1149.4	1164.8	1173.3	1174.8



TEST NUMBER: P331353-940

CATALOG NUMBER: S122DIP-S675D725U940-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	782.4	908.6	1010.4	1080.3	1124.2	1148.6	1162.7	1168.7
115°	724.1	837.5	934.9	1010.8	1062.6	1096.8	1117.1	1125.7
117.5°	678.2	778.5	867.3	938.6	991.1	1027.1	1048.3	1055.6
120°	654.2	746.4	825.9	893.3	944.3	979.3	1001.7	1010.9
122.5°	634.5	719.3	794.7	855.7	901.3	935.5	955.4	963.1
125°	605.1	682.3	749.1	805.0	847.3	875.7	894.9	902.2
127.5°	576.0	646.0	708.9	760.5	797.5	824.2	841.0	847.2
130°	557.4	622.2	682.2	731.4	767.1	792.5	808.0	815.2
132.5°	539.3	599.5	654.8	701.2	736.4	761.7	776.1	782.8
135°	514.1	564.4	614.7	656.6	688.2	712.8	726.9	731.4
137.5°	492.8	535.0	575.3	611.9	640.6	661.7	674.1	679.7
140°	479.5	516.2	551.5	584.4	607.9	627.2	638.9	644.4
142.5°	469.0	500.0	530.1	557.7	579.9	597.4	607.8	609.7
145°	454.8	479.0	501.9	523.2	540.9	553.8	561.8	564.9
147.5°	444.3	462.5	479.6	494.6	508.9	518.9	524.1	525.8
150°	437.7	453.1	467.7	480.3	490.7	499.1	503.3	504.0
152.5°	431.6	445.9	458.3	469.1	477.3	484.6	487.7	487.8
155°	423.1	434.3	444.7	452.4	460.0	464.9	467.7	466.4
157.5°	413.2	422.6	431.3	437.3	442.7	446.8	448.1	448.1
160°	407.1	414.7	422.4	427.3	432.2	435.7	436.3	436.3
162.5°	400.9	407.5	414.0	417.9	422.7	425.1	425.8	425.2
165°	391.7	396.6	401.5	404.3	407.1	409.8	409.8	409.2
167.5°	383.0	386.7	390.0	392.6	393.9	395.4	395.2	394.4
170°	378.5	380.6	383.3	384.8	385.5	387.5	386.8	385.5
172.5°	373.4	375.1	377.3	378.1	378.8	379.8	379.1	378.3
175°	368.0	368.7	369.4	370.1	370.1	370.9	370.1	368.7
177.5°	364.2	364.2	364.7	364.7	364.7	364.7	364.2	363.0
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5

(END OF REPORT)