

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331373-830

Luminaire Tested: **S122DIP-S675D1080U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331373-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S675D1080U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6178.8 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331373-830

CATALOG NUMBER: S122DIP-S675D1080U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331373-830

CATALOG NUMBER: S122DIP-S675D1080U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	92	88	84	87	84	80	77	69	66	64	55	54	52	42	41	41	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	39	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	27	23	29	23	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16157	16157	16157
5°	16219	15985	16078
10°	16123	15823	15901
15°	15921	15616	15600
20°	15639	15309	15292
25°	15358	14931	14931
30°	14997	14585	14458
35°	14661	14168	13957
40°	14235	13748	13487
45°	13819	13337	13006
50°	13366	12906	12446
55°	12892	12405	11944
60°	12368	11806	11370
65°	11801	11213	10697
70°	11084	10494	9994
75°	10081	9669	9426
80°	8945	8675	8229
85°	7317	6947	6224



TEST NUMBER: P331373-830

CATALOG NUMBER: S122DIP-S675D1080U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.1	1.5
10°-20°	264.8	4.3
20°-30°	389.2	6.3
30°-40°	452.1	7.3
40°-50°	451.6	7.3
50°-60°	393.8	6.4
60°-70°	291.2	4.7
70°-80°	164.9	2.7
80°-90°	49.5	0.8
90°-100°	82.2	1.3
100°-110°	255.3	4.1
110°-120°	436.4	7.1
120°-130°	573.9	9.3
130°-140°	644.2	10.4
140°-150°	631.6	10.2
150°-160°	529.8	8.6
160°-170°	351.4	5.7
170°-180°	122.8	2.0
0°-30°	748.0	12.1
0°-40°	1200.1	19.4
0°-60°	2045.4	33.1
0°-90°	2551.1	41.3
90°-120°	774.0	12.5
90°-150°	2623.7	42.5
90°-180°	3628.0	58.7
0°-180°	6178.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1001	1001	1001	1001	1001	
5°	1001	996	986	993	992	95
15°	952	946	934	938	933	268
25°	862	854	838	840	838	396
35°	744	734	719	713	708	464
45°	605	598	584	574	570	467
55°	458	452	441	430	424	409
65°	309	303	294	285	280	305
75°	162	160	155	150	151	173
85°	40	38	38	35	34	45
90°	1	15	38	36	37	5
95°	57	67	70	70	68	65
105°	235	239	241	243	243	249
115°	438	444	442	441	438	433
125°	637	646	644	641	639	569
135°	824	836	839	837	834	637
145°	1001	1008	1015	1016	1012	625
155°	1144	1147	1151	1156	1153	526
165°	1245	1244	1244	1251	1246	351
175°	1295	1292	1290	1297	1291	123
180°	1297	1297	1297	1297	1297	



TEST NUMBER: P331373-830

CATALOG NUMBER: S122DIP-S675D1080U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	1005.3	1004.5	1003.6	1002.8	1001.9	1000.5	998.6	996.7	994.9	993.0	994.7
5°	1000.7	999.8	999.0	998.2	997.3	995.7	993.3	991.0	988.6	986.3	988.0
7.5°	991.8	990.5	989.2	987.9	986.6	984.7	982.3	979.9	977.5	975.1	976.8
10°	983.4	981.8	980.3	978.8	977.4	975.3	972.8	970.3	967.6	965.1	966.8
12.5°	971.9	970.5	969.1	967.8	966.5	964.6	962.0	959.4	956.9	954.3	955.5
15°	952.5	951.3	950.0	948.8	947.4	945.4	942.6	939.8	937.1	934.2	935.2
17.5°	927.9	926.6	925.4	924.1	922.8	920.8	917.9	915.1	912.3	909.5	910.5
20°	910.2	909.0	907.7	906.3	905.1	903.0	899.9	897.0	894.0	891.0	891.6
22.5°	892.5	890.7	888.9	887.1	885.3	883.1	880.2	877.4	874.6	871.8	871.9
25°	862.1	860.4	858.8	857.0	855.3	852.6	848.9	845.4	841.7	838.1	838.5
27.5°	827.5	826.0	824.4	822.8	821.3	819.2	816.2	813.4	810.5	807.7	807.0
30°	804.4	802.7	801.0	799.3	797.6	795.1	791.9	788.7	785.5	782.3	781.7
32.5°	779.8	778.4	777.0	775.6	774.3	771.9	768.5	765.2	761.8	758.4	757.2
35°	743.8	741.7	739.5	737.4	735.2	732.4	729.1	725.6	722.2	718.8	717.5
37.5°	703.1	701.3	699.4	697.5	695.7	693.0	689.6	686.2	682.8	679.3	677.7
40°	675.4	673.7	672.0	670.3	668.6	666.1	662.6	659.2	655.8	652.3	650.4
42.5°	648.6	646.8	645.1	643.4	641.7	639.1	635.7	632.3	628.9	625.5	623.3
45°	605.2	603.7	602.2	600.8	599.3	596.9	593.7	590.5	587.3	584.1	581.7
47.5°	562.1	560.7	559.3	557.9	556.5	554.1	550.7	547.4	544.1	540.7	538.3
50°	532.1	531.0	530.0	528.9	527.8	525.8	522.8	519.8	516.8	513.8	510.9
52.5°	502.8	501.4	500.0	498.6	497.2	495.1	492.3	489.5	486.6	483.8	481.4
55°	458.0	456.8	455.4	454.1	452.9	450.9	448.4	445.8	443.3	440.7	438.1
57.5°	412.9	412.0	410.9	409.9	408.9	407.0	404.2	401.3	398.5	395.7	393.1
60°	383.0	382.1	381.3	380.4	379.6	377.6	374.7	371.6	368.6	365.6	363.3
62.5°	353.7	352.3	351.0	349.6	348.3	346.4	344.1	341.8	339.5	337.1	335.0
65°	308.9	307.6	306.3	305.0	303.7	302.0	299.9	297.7	295.6	293.5	291.5
67.5°	263.3	262.2	261.2	260.1	259.1	257.7	255.7	253.8	251.9	250.0	248.5
70°	234.8	233.9	233.1	232.2	231.4	230.0	228.0	226.1	224.2	222.3	220.7
72.5°	205.6	204.6	203.8	202.9	202.1	201.0	199.8	198.6	197.4	196.0	194.6
75°	161.6	161.2	160.8	160.3	159.9	159.2	158.2	157.0	156.0	155.0	153.6
77.5°	122.4	121.7	120.9	120.2	119.5	118.9	118.5	118.0	117.6	117.2	116.6
80°	96.2	96.0	95.8	95.6	95.4	95.0	94.6	94.2	93.8	93.3	92.7
82.5°	71.6	71.5	71.5	71.4	71.4	71.3	71.0	70.8	70.5	70.2	69.5
85°	39.5	39.2	39.0	38.8	38.5	38.4	38.2	38.0	37.7	37.5	36.9
87.5°	14.0	14.3	14.5	14.8	15.1	15.6	16.2	17.0	17.7	18.5	17.8
90°	1.1	4.1	7.0	9.9	12.8	16.9	22.2	27.6	33.0	38.4	37.8
92.5°	19.5	21.6	23.8	25.9	28.1	29.8	31.0	32.3	33.6	34.8	34.9
95°	56.9	59.4	61.8	64.2	66.6	68.1	68.6	69.1	69.6	70.0	70.0
97.5°	104.1	106.1	108.3	110.5	112.5	114.1	115.0	115.9	116.9	117.8	117.8
100°	139.0	141.0	143.0	144.9	146.8	148.2	148.9	149.6	150.3	151.1	151.1
102.5°	175.9	177.4	179.0	180.5	182.1	183.3	184.3	185.1	186.1	187.0	187.2
105°	235.4	236.1	236.9	237.6	238.3	238.9	239.4	239.9	240.3	240.8	241.4
107.5°	295.4	296.4	297.6	298.6	299.6	300.2	300.2	300.2	300.2	300.2	300.4
110°	333.9	335.4	336.9	338.3	339.8	340.5	340.5	340.5	340.5	340.5	340.5



TEST NUMBER: P331373-830

CATALOG NUMBER: S122DIP-S675D1080U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	376.0	377.4	378.9	380.3	381.8	382.5	382.2	382.0	381.8	381.6	381.1
115°	437.9	439.4	440.8	442.3	443.7	444.2	443.7	443.3	442.8	442.3	442.1
117.5°	499.6	501.6	503.6	505.5	507.5	507.7	506.4	505.0	503.7	502.3	501.7
120°	540.8	542.8	544.8	546.7	548.7	548.7	546.7	544.8	542.8	540.8	540.8
122.5°	578.5	580.9	583.2	585.5	587.9	588.3	587.0	585.6	584.3	582.9	582.3
125°	637.2	639.4	641.6	643.8	645.9	646.7	645.9	645.3	644.5	643.8	643.0
127.5°	694.4	697.1	699.9	702.7	705.4	706.4	705.5	704.6	703.8	702.9	702.0
130°	730.3	733.4	736.6	739.7	742.9	744.2	743.8	743.3	742.8	742.3	741.8
132.5°	770.5	773.2	775.7	778.3	780.9	782.2	782.3	782.4	782.5	782.6	781.6
135°	824.4	827.1	829.8	832.5	835.1	836.7	837.2	837.6	838.2	838.7	838.4
137.5°	881.1	883.4	885.5	887.7	889.9	891.3	891.9	892.6	893.2	893.8	893.6
140°	915.3	917.5	919.6	921.9	924.1	925.8	927.0	928.2	929.4	930.6	930.6
142.5°	950.4	952.5	954.7	956.9	959.0	960.5	961.4	962.2	963.1	963.9	964.1
145°	1000.7	1002.4	1004.1	1005.8	1007.5	1009.1	1010.5	1012.0	1013.4	1014.9	1015.1
147.5°	1045.6	1047.6	1049.6	1051.7	1053.8	1055.3	1056.2	1057.2	1058.2	1059.1	1059.7
150°	1076.2	1077.7	1079.1	1080.6	1082.0	1083.3	1084.3	1085.2	1086.2	1087.2	1087.9
152.5°	1103.3	1104.8	1106.3	1107.8	1109.2	1110.5	1111.7	1112.9	1114.1	1115.2	1116.2
155°	1144.2	1144.8	1145.6	1146.3	1147.1	1147.7	1148.5	1149.2	1150.0	1150.7	1151.9
157.5°	1178.9	1179.4	1179.9	1180.3	1180.9	1181.3	1181.8	1182.2	1182.6	1183.1	1184.8
160°	1200.0	1200.4	1200.9	1201.4	1201.9	1202.2	1202.5	1202.8	1203.0	1203.2	1204.7
162.5°	1219.2	1219.3	1219.4	1219.5	1219.7	1219.7	1220.0	1220.2	1220.5	1220.8	1222.4
165°	1244.8	1244.6	1244.3	1244.1	1243.9	1243.8	1243.8	1243.8	1243.8	1243.8	1245.5
167.5°	1266.3	1265.6	1264.8	1264.1	1263.4	1263.0	1262.9	1262.9	1262.8	1262.8	1264.5
170°	1277.7	1277.0	1276.2	1275.4	1274.8	1274.3	1274.0	1273.8	1273.6	1273.3	1275.0
172.5°	1285.5	1284.9	1284.1	1283.4	1282.6	1282.1	1282.0	1281.7	1281.4	1281.2	1282.9
175°	1295.2	1294.5	1293.7	1293.0	1292.3	1291.7	1291.2	1290.7	1290.2	1289.7	1291.5
177.5°	1299.1	1298.5	1298.0	1297.4	1296.8	1296.3	1295.9	1295.5	1295.1	1294.8	1295.9
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4



TEST NUMBER: P331373-830

CATALOG NUMBER: S122DIP-S675D1080U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	996.4	998.2	999.8	1000.5	1000.1	999.8	999.5	999.2
5°	989.7	991.4	993.1	993.7	993.3	992.9	992.5	992.0
7.5°	978.5	980.2	981.9	982.5	982.0	981.7	981.2	980.7
10°	968.5	970.3	971.9	972.4	971.9	971.2	970.5	969.9
12.5°	956.7	957.9	959.1	959.4	958.9	958.6	958.1	957.6
15°	936.0	936.9	937.7	937.6	936.5	935.5	934.4	933.3
17.5°	911.4	912.4	913.4	913.4	912.4	911.3	910.3	909.3
20°	892.3	893.0	893.5	893.4	892.6	891.7	890.9	890.0
22.5°	872.0	872.1	872.2	872.0	871.6	871.0	870.5	870.1
25°	839.0	839.3	839.8	839.8	839.3	839.0	838.5	838.1
27.5°	806.3	805.8	805.1	804.3	803.2	802.2	801.2	800.1
30°	781.0	780.3	779.7	778.9	778.1	777.2	776.4	775.5
32.5°	756.1	755.0	753.8	752.8	752.0	751.1	750.2	749.3
35°	716.2	714.9	713.6	712.5	711.4	710.3	709.3	708.1
37.5°	676.2	674.6	673.0	671.7	670.6	669.6	668.6	667.6
40°	648.6	646.6	644.7	643.3	642.4	641.6	640.7	639.9
42.5°	621.2	619.2	617.1	615.4	614.2	613.0	611.8	610.6
45°	579.4	577.0	574.7	573.1	572.2	571.4	570.5	569.6
47.5°	535.8	533.3	530.8	529.0	527.7	526.5	525.3	524.1
50°	507.8	504.8	501.8	499.8	498.7	497.7	496.6	495.5
52.5°	478.8	476.4	473.9	471.9	470.5	469.1	467.7	466.3
55°	435.5	433.0	430.5	428.6	427.5	426.5	425.4	424.3
57.5°	390.6	388.0	385.6	383.9	383.0	382.3	381.4	380.6
60°	360.9	358.5	356.2	354.8	354.1	353.5	352.8	352.1
62.5°	332.8	330.6	328.5	327.0	326.1	325.3	324.5	323.7
65°	289.6	287.7	285.8	284.3	283.2	282.1	281.1	280.0
67.5°	246.9	245.5	244.0	242.8	242.0	241.1	240.3	239.4
70°	219.2	217.8	216.3	215.1	214.2	213.4	212.5	211.7
72.5°	193.1	191.6	190.1	189.0	188.3	187.7	187.0	186.2
75°	152.3	151.1	149.8	149.4	149.8	150.2	150.6	151.1
77.5°	115.9	115.3	114.6	114.0	113.4	112.8	112.3	111.6
80°	92.1	91.4	90.8	90.2	89.8	89.4	89.0	88.5
82.5°	68.6	67.8	67.0	66.5	66.4	66.4	66.3	66.2
85°	36.3	35.6	35.0	34.5	34.3	34.1	33.9	33.6
87.5°	17.2	16.6	16.0	15.6	15.6	15.4	15.3	15.2
90°	37.3	36.9	36.4	36.3	36.5	36.8	36.9	37.2
92.5°	35.0	35.1	35.3	35.3	35.3	35.3	35.4	35.4
95°	70.0	70.0	70.0	69.8	69.4	68.9	68.3	67.9
97.5°	117.8	117.8	117.8	117.8	117.7	117.7	117.6	117.6
100°	151.1	151.1	151.1	151.0	150.7	150.5	150.2	150.0
102.5°	187.4	187.6	187.8	187.8	187.5	187.3	187.0	186.8
105°	241.9	242.3	242.8	243.1	243.1	243.1	243.1	243.1
107.5°	300.6	300.8	301.0	300.5	299.4	298.3	297.2	296.1
110°	340.5	340.5	340.5	340.2	339.4	338.7	337.9	337.2



TEST NUMBER: P331373-830

CATALOG NUMBER: S122DIP-S675D1080U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	380.5	379.9	379.4	378.8	378.2	377.7	377.2	376.6
115°	441.9	441.6	441.3	440.8	440.2	439.4	438.7	437.9
117.5°	501.1	500.6	500.0	499.4	498.6	497.9	497.1	496.4
120°	540.8	540.8	540.8	540.5	539.8	539.0	538.3	537.5
122.5°	581.7	581.2	580.5	580.0	579.5	578.9	578.4	577.9
125°	642.3	641.6	640.8	640.4	640.1	639.9	639.6	639.4
127.5°	701.2	700.2	699.4	698.5	697.8	697.0	696.3	695.4
130°	741.3	740.8	740.4	739.6	738.7	737.6	736.7	735.7
132.5°	780.4	779.4	778.4	777.4	776.7	775.8	775.1	774.3
135°	838.2	837.9	837.6	837.2	836.4	835.8	835.0	834.2
137.5°	893.4	893.2	893.1	892.5	891.5	890.5	889.6	888.5
140°	930.6	930.6	930.6	930.1	929.2	928.2	927.2	926.2
142.5°	964.3	964.5	964.7	964.3	963.3	962.3	961.4	960.4
145°	1015.4	1015.7	1015.9	1015.5	1014.6	1013.6	1012.6	1011.6
147.5°	1060.3	1060.7	1061.3	1061.1	1060.2	1059.2	1058.3	1057.4
150°	1088.6	1089.4	1090.1	1090.1	1089.4	1088.6	1087.9	1087.2
152.5°	1117.1	1117.9	1118.9	1118.9	1117.9	1117.1	1116.2	1115.2
155°	1153.1	1154.3	1155.6	1155.7	1155.1	1154.3	1153.6	1152.8
157.5°	1186.4	1188.1	1189.7	1190.0	1188.7	1187.6	1186.5	1185.2
160°	1206.2	1207.6	1209.1	1209.3	1208.3	1207.4	1206.4	1205.4
162.5°	1224.1	1225.7	1227.4	1227.6	1226.4	1225.3	1224.1	1222.9
165°	1247.2	1248.9	1250.6	1250.8	1249.6	1248.4	1247.2	1245.9
167.5°	1266.2	1267.9	1269.6	1269.8	1268.6	1267.2	1266.0	1264.8
170°	1276.7	1278.4	1280.1	1280.3	1278.7	1277.3	1275.8	1274.4
172.5°	1284.6	1286.3	1288.0	1288.1	1286.7	1285.2	1283.7	1282.2
175°	1293.2	1294.9	1296.6	1296.7	1295.2	1293.7	1292.3	1290.8
177.5°	1297.1	1298.3	1299.4	1299.4	1298.3	1297.1	1295.9	1294.8
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4

(END OF REPORT)