

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331750-940

Luminaire Tested: **S122RDIP-S1005D725U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331750-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S1005D725U940-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 725 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5691.4 lumens  
Efficiency: N/A  
Efficacy: 93.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331750-940

CATALOG NUMBER: S122RDIP-S1005D725U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331750-940

CATALOG NUMBER: S122RDIP-S1005D725U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	54	53	52	47
2	91	84	78	73	84	78	73	69	67	63	60	57	55	52	48	46	45	40
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39	35
4	76	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34	30
5	70	59	51	45	65	55	48	43	48	43	38	42	37	34	35	32	30	27
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21	19
9	52	40	33	28	49	38	31	27	33	28	24	29	25	22	25	22	19	17
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	24380	24380	24380
5°	24473	24076	24209
10°	24287	23682	23481
15°	24008	22980	22318
20°	23622	21978	20874
25°	23225	20838	19475
30°	22676	19669	17682
35°	22141	18398	16109
40°	21602	17081	14286
45°	20970	15602	12638
50°	20321	14109	11017
55°	19657	12504	9464
60°	18887	10811	7857
65°	18010	9085	7156
70°	16966	7482	6581
75°	15689	6818	6138
80°	13845	6100	5588
85°	10893	4798	4798



TEST NUMBER: P331750-940

CATALOG NUMBER: S122RDIP-S1005D725U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.3	2.5
10°-20°	388.1	6.8
20°-30°	545.0	9.6
30°-40°	594.3	10.4
40°-50°	546.4	9.6
50°-60°	429.2	7.5
60°-70°	279.8	4.9
70°-80°	144.3	2.5
80°-90°	39.6	0.7
90°-100°	29.4	0.5
100°-110°	107.8	1.9
110°-120°	288.3	5.1
120°-130°	475.8	8.4
130°-140°	506.0	8.9
140°-150°	470.3	8.3
150°-160°	378.1	6.6
160°-170°	243.7	4.3
170°-180°	83.9	1.5
0°-30°	1074.4	18.9
0°-40°	1668.7	29.3
0°-60°	2644.3	46.5
0°-90°	3108.0	54.6
90°-120°	425.5	7.5
90°-150°	1877.7	33.0
90°-180°	2583.0	45.4
0°-180°	5691.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1510	1510	1510	1510	1510	
5°	1510	1503	1486	1497	1494	143
15°	1436	1419	1375	1350	1335	404
25°	1304	1257	1170	1116	1093	599
35°	1123	1051	933	850	817	703
45°	918	824	683	590	554	709
55°	698	589	444	365	336	624
65°	471	360	238	194	187	467
75°	252	158	109	100	98	266
85°	59	31	26	26	26	69
90°	1	8	13	16	17	4
95°	42	22	25	28	28	51
105°	194	202	39	46	48	207
115°	367	378	394	112	52	361
125°	519	527	539	543	545	462
135°	642	652	658	664	663	495
145°	744	744	755	759	756	465
155°	820	815	822	825	820	378
165°	864	860	862	866	862	244
175°	883	879	880	884	878	84
180°	882	882	882	882	882	



TEST NUMBER: P331750-940

CATALOG NUMBER: S122RDIP-S1005D725U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0
2.5°	1515.6	1514.3	1513.1	1511.9	1510.6	1508.7	1506.0	1503.4	1500.7	1498.1	1500.5
5°	1510.0	1508.5	1507.0	1505.5	1504.0	1501.3	1497.3	1493.3	1489.4	1485.5	1488.2
7.5°	1494.5	1492.6	1490.8	1488.8	1486.9	1483.7	1479.1	1474.4	1469.9	1465.3	1466.1
10°	1481.4	1479.3	1477.1	1475.0	1472.8	1468.7	1462.7	1456.6	1450.5	1444.5	1443.6
12.5°	1465.0	1462.3	1459.7	1457.1	1454.6	1449.3	1441.5	1433.8	1426.0	1418.3	1416.6
15°	1436.3	1432.9	1429.6	1426.2	1422.9	1416.0	1405.8	1395.4	1385.1	1374.8	1369.0
17.5°	1401.0	1395.9	1390.8	1385.7	1380.6	1371.5	1358.2	1345.0	1331.7	1318.5	1311.6
20°	1374.8	1368.7	1362.6	1356.6	1350.5	1339.9	1324.6	1309.5	1294.3	1279.1	1271.5
22.5°	1346.3	1339.5	1332.8	1326.0	1319.1	1307.2	1290.0	1272.9	1255.8	1238.7	1228.9
25°	1303.7	1294.0	1284.2	1274.5	1264.8	1250.0	1229.9	1209.9	1189.8	1169.7	1157.4
27.5°	1252.3	1241.8	1231.2	1220.7	1210.1	1193.5	1170.9	1148.3	1125.7	1103.1	1088.6
30°	1216.3	1204.7	1193.2	1181.6	1170.1	1152.2	1127.8	1103.6	1079.3	1055.0	1039.5
32.5°	1181.2	1167.8	1154.3	1140.9	1127.3	1108.2	1083.4	1058.6	1033.8	1009.1	991.4
35°	1123.3	1107.9	1092.3	1076.8	1061.4	1040.3	1013.5	986.9	960.1	933.4	914.3
37.5°	1065.4	1048.4	1031.4	1014.3	997.4	974.6	946.1	917.7	889.1	860.7	839.6
40°	1024.9	1006.7	988.5	970.3	952.1	928.2	898.8	869.3	839.8	810.4	788.8
42.5°	983.4	964.2	945.0	925.8	906.6	881.8	851.4	820.9	790.5	760.1	737.8
45°	918.4	898.0	877.6	857.3	837.0	810.8	778.9	747.1	715.2	683.3	661.7
47.5°	854.9	833.4	811.8	790.2	768.7	741.5	708.6	675.6	642.7	609.8	588.4
50°	809.0	787.5	765.9	744.3	722.7	695.3	661.9	628.5	595.0	561.7	540.7
52.5°	764.2	741.6	719.2	696.6	674.0	646.5	613.8	581.1	548.4	515.8	495.5
55°	698.3	674.7	650.9	627.2	603.6	575.3	542.5	509.7	477.0	444.2	425.9
57.5°	630.8	606.5	582.2	557.9	533.6	505.7	474.2	442.6	411.2	379.6	362.9
60°	584.9	560.6	536.3	512.0	487.7	459.9	428.6	397.3	366.0	334.8	319.3
62.5°	540.1	515.8	491.5	467.2	442.9	415.8	386.0	356.1	326.4	296.6	281.8
65°	471.4	446.8	422.3	397.7	373.1	347.1	319.8	292.5	265.1	237.8	227.5
67.5°	405.3	380.9	356.5	332.1	307.6	283.1	258.6	234.0	209.4	184.8	180.0
70°	359.4	335.7	312.0	288.4	264.7	242.4	221.4	200.5	179.5	158.5	155.5
72.5°	315.7	292.9	270.3	247.5	224.8	205.0	188.2	171.4	154.5	137.8	135.2
75°	251.5	230.2	208.9	187.7	166.4	150.6	140.3	130.0	119.7	109.3	107.2
77.5°	188.3	169.7	151.1	132.4	113.7	101.9	96.9	91.9	86.9	82.0	80.8
80°	148.9	133.5	118.0	102.5	87.0	77.8	74.7	71.7	68.7	65.6	64.4
82.5°	112.9	100.8	88.7	76.6	64.6	57.4	55.4	53.3	51.3	49.2	48.5
85°	58.8	52.3	46.0	39.6	33.3	29.6	28.7	27.8	26.8	25.9	25.9
87.5°	17.7	16.0	14.4	12.8	11.1	10.4	10.6	10.9	11.1	11.3	11.2
90°	0.6	2.2	3.7	5.4	6.9	8.2	9.4	10.5	11.6	12.8	13.5
92.5°	12.8	12.8	12.6	12.5	12.3	12.6	13.1	13.6	14.3	14.8	15.2
95°	41.5	36.8	32.1	27.5	22.7	20.9	21.9	22.9	23.9	24.9	25.6
97.5°	82.3	69.1	55.9	42.7	29.5	24.1	26.4	28.7	31.0	33.3	33.9
100°	112.9	93.5	74.1	54.7	35.2	26.8	29.2	31.6	34.0	36.4	37.5
102.5°	146.6	142.5	138.4	134.3	130.1	118.0	97.8	77.7	57.5	37.4	38.9
105°	193.9	198.1	202.4	206.7	210.9	193.7	155.0	116.3	77.6	38.9	40.5
107.5°	247.9	251.3	254.8	258.2	261.6	240.1	193.7	147.3	100.9	54.5	52.9
110°	282.6	285.5	288.6	291.5	294.4	275.4	234.5	193.6	152.6	111.6	97.5



TEST NUMBER: P331750-940

CATALOG NUMBER: S122RDIP-S1005D725U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	315.2	317.9	320.5	323.2	325.7	322.0	311.9	301.8	291.7	281.5	229.9
115°	366.8	369.2	371.6	374.0	376.4	379.4	382.9	386.5	390.0	393.6	328.0
117.5°	412.9	415.5	418.2	420.9	423.6	426.1	428.6	431.1	433.5	436.0	420.1
120°	446.5	448.6	450.8	452.9	455.0	457.4	459.9	462.4	465.0	467.5	469.2
122.5°	475.1	477.3	479.6	481.8	484.0	486.5	489.4	492.1	494.9	497.7	498.6
125°	518.6	520.4	522.3	524.1	525.9	528.2	530.9	533.6	536.3	539.0	540.0
127.5°	558.0	560.1	562.1	564.1	566.1	568.2	570.2	572.2	574.3	576.2	577.7
130°	583.0	585.3	587.5	589.8	592.1	594.0	595.6	597.1	598.7	600.2	601.8
132.5°	608.5	610.5	612.4	614.3	616.3	618.0	619.6	621.1	622.7	624.2	625.5
135°	641.7	644.0	646.2	648.5	650.8	652.6	653.8	655.1	656.4	657.6	659.1
137.5°	675.3	676.8	678.4	680.0	681.6	683.1	684.6	686.0	687.4	688.9	690.3
140°	697.2	698.3	699.5	700.6	701.7	703.1	704.6	706.2	707.8	709.4	710.6
142.5°	715.6	716.6	717.6	718.6	719.6	721.0	722.8	724.6	726.4	728.2	729.3
145°	744.4	744.2	744.1	744.0	743.9	744.9	747.3	749.8	752.2	754.6	755.6
147.5°	769.5	769.0	768.5	767.9	767.4	768.3	770.7	773.0	775.4	777.8	778.6
150°	785.9	784.9	783.9	782.9	781.9	782.6	784.8	787.0	789.3	791.6	792.5
152.5°	799.6	798.5	797.5	796.3	795.2	795.8	797.9	800.0	802.2	804.3	805.2
155°	819.7	818.4	817.1	815.8	814.6	814.8	816.5	818.1	819.8	821.5	822.4
157.5°	835.4	834.3	833.2	832.1	831.1	831.1	832.3	833.5	834.6	835.9	836.9
160°	844.5	843.6	842.8	842.0	841.2	841.2	842.0	842.8	843.6	844.5	845.4
162.5°	852.7	851.9	851.0	850.2	849.3	849.3	850.0	850.7	851.5	852.2	853.2
165°	863.7	862.8	862.0	861.1	860.2	860.1	860.5	860.9	861.3	861.7	862.7
167.5°	871.8	871.0	870.1	869.3	868.4	868.2	868.6	869.0	869.4	869.8	870.8
170°	876.5	875.6	874.8	873.9	873.1	872.7	873.1	873.3	873.6	873.9	874.9
172.5°	879.5	878.6	877.8	876.9	876.1	875.8	876.1	876.4	876.6	876.9	878.0
175°	883.4	882.4	881.5	880.5	879.5	879.1	879.4	879.7	879.9	880.3	881.3
177.5°	884.1	883.3	882.5	881.7	880.9	880.6	880.7	880.8	880.9	881.0	881.8
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331750-940

CATALOG NUMBER: S122RDIP-S1005D725U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0
2.5°	1502.9	1505.3	1507.8	1508.7	1508.2	1507.8	1507.3	1506.8
5°	1490.9	1493.7	1496.4	1497.3	1496.4	1495.5	1494.6	1493.7
7.5°	1466.8	1467.6	1468.4	1468.0	1466.4	1464.8	1463.3	1461.7
10°	1442.6	1441.7	1440.8	1439.5	1437.6	1435.8	1434.0	1432.2
12.5°	1415.0	1413.3	1411.7	1409.3	1406.3	1403.3	1400.3	1397.2
15°	1363.2	1357.5	1351.7	1347.3	1344.3	1341.2	1338.2	1335.2
17.5°	1304.8	1297.9	1291.0	1285.0	1279.8	1274.5	1269.3	1264.1
20°	1263.9	1256.3	1248.8	1241.6	1234.9	1228.2	1221.6	1214.9
22.5°	1219.1	1209.3	1199.5	1192.1	1187.2	1182.2	1177.2	1172.2
25°	1144.9	1132.5	1120.0	1111.5	1106.9	1102.3	1097.8	1093.2
27.5°	1074.1	1059.5	1045.0	1034.1	1026.9	1019.7	1012.4	1005.2
30°	1024.0	1008.5	993.0	981.2	973.0	964.8	956.6	948.4
32.5°	973.7	956.1	938.3	925.7	918.0	910.3	902.5	894.8
35°	895.1	876.0	856.8	843.9	837.2	830.5	823.9	817.3
37.5°	818.5	797.5	776.3	762.0	754.4	746.7	739.0	731.4
40°	767.2	745.6	724.2	709.4	701.5	693.6	685.7	677.8
42.5°	715.5	693.2	670.9	655.9	648.3	640.6	633.0	625.4
45°	640.2	618.6	597.0	582.6	575.3	568.0	560.7	553.5
47.5°	566.9	545.5	524.0	510.0	503.4	496.8	490.1	483.5
50°	519.8	498.8	477.9	464.1	457.8	451.4	445.1	438.6
52.5°	475.3	455.0	434.9	421.8	415.9	410.0	404.1	398.2
55°	407.7	389.5	371.2	359.3	353.5	347.7	342.0	336.2
57.5°	346.3	329.5	312.8	302.0	297.2	292.3	287.5	282.6
60°	303.8	288.4	272.9	262.7	257.8	253.0	248.1	243.3
62.5°	267.1	252.3	237.6	228.6	225.8	222.8	219.9	217.0
65°	217.1	206.8	196.4	190.8	189.9	189.0	188.2	187.3
67.5°	175.3	170.6	165.8	162.9	162.0	161.0	160.1	159.1
70°	152.5	149.5	146.4	144.3	143.0	141.8	140.6	139.4
72.5°	132.7	130.1	127.5	125.9	125.2	124.5	123.7	123.0
75°	105.0	103.0	100.9	99.6	99.3	99.0	98.7	98.4
77.5°	79.5	78.4	77.1	76.2	75.8	75.3	74.8	74.4
80°	63.1	62.0	60.7	60.1	60.1	60.1	60.1	60.1
82.5°	47.7	47.0	46.3	45.9	45.9	45.9	45.9	45.9
85°	25.9	25.9	25.9	25.9	25.9	25.9	25.9	25.9
87.5°	11.1	11.0	10.9	10.9	11.0	11.0	11.1	11.1
90°	14.2	14.9	15.6	16.1	16.4	16.7	16.9	17.2
92.5°	15.5	15.9	16.2	16.6	16.7	16.9	17.0	17.2
95°	26.3	27.0	27.7	28.0	27.8	27.7	27.6	27.5
97.5°	34.4	35.0	35.6	35.9	36.1	36.3	36.5	36.6
100°	38.6	39.8	40.9	41.6	41.9	42.2	42.4	42.7
102.5°	40.3	41.8	43.2	44.2	44.6	45.0	45.4	45.8
105°	42.0	43.6	45.1	46.2	46.8	47.3	47.9	48.5
107.5°	51.3	49.7	48.2	47.6	48.2	48.8	49.3	49.8
110°	83.3	69.1	54.9	48.2	48.7	49.2	49.8	50.4





TEST NUMBER: P331750-940

CATALOG NUMBER: S122RDIP-S1005D725U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	178.2	126.4	74.7	49.0	49.6	50.0	50.5	50.9
115°	262.3	196.7	131.1	93.1	82.9	72.7	62.5	52.3
117.5°	404.2	388.3	372.4	347.7	314.1	280.6	247.1	213.6
120°	471.0	472.7	474.4	465.7	446.5	427.4	408.2	389.1
122.5°	499.7	500.7	501.8	500.4	496.7	492.9	489.3	485.5
125°	541.0	542.0	543.0	543.7	544.1	544.6	544.9	545.4
127.5°	579.2	580.6	582.0	582.8	582.9	583.0	583.1	583.2
130°	603.3	604.9	606.5	607.2	607.1	606.9	606.7	606.6
132.5°	626.9	628.2	629.5	630.2	630.0	629.9	629.7	629.5
135°	660.5	661.9	663.3	663.9	663.6	663.3	663.0	662.7
137.5°	691.7	693.0	694.5	694.9	694.5	693.9	693.5	692.9
140°	711.9	713.1	714.4	714.7	714.0	713.3	712.6	711.9
142.5°	730.5	731.6	732.8	733.1	732.4	731.6	730.9	730.2
145°	756.6	757.6	758.6	758.7	758.0	757.3	756.6	755.9
147.5°	779.3	780.1	780.8	780.9	780.2	779.6	779.1	778.5
150°	793.3	794.2	795.0	795.0	794.3	793.6	792.9	792.2
152.5°	806.0	806.9	807.8	807.7	806.8	805.8	804.9	804.0
155°	823.3	824.1	825.0	824.8	823.7	822.6	821.4	820.3
157.5°	837.8	838.7	839.7	839.6	838.6	837.4	836.3	835.3
160°	846.2	847.1	847.9	847.8	846.9	845.9	844.9	843.9
162.5°	854.1	855.1	856.0	856.0	854.7	853.5	852.3	851.0
165°	863.7	864.8	865.8	865.8	864.8	863.7	862.7	861.7
167.5°	871.8	872.8	873.8	873.6	872.4	871.1	869.8	868.5
170°	875.8	876.8	877.9	877.7	876.5	875.1	873.9	872.6
172.5°	879.0	879.9	880.9	880.7	879.5	878.2	876.9	875.7
175°	882.3	883.2	884.2	884.0	882.6	881.2	879.8	878.3
177.5°	882.6	883.4	884.2	884.1	883.1	882.1	881.0	880.0
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5

(END OF REPORT)