

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331377-830

Luminaire Tested: **S122DIP-S865D330U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331377-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S865D330U830-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4796.9 lumens  
Efficiency: N/A  
Efficacy: 110.3 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331377-830

CATALOG NUMBER: S122DIP-S865D330U830-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331377-830

CATALOG NUMBER: S122DIP-S865D330U830-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75
1	104	100	96	93	99	95	92	89	86	84	82	78	76	75	71	70	68	65
2	95	88	82	77	91	84	79	74	77	72	69	70	66	63	63	61	59	55
3	88	78	71	65	83	75	68	63	68	63	59	62	58	55	57	53	51	48
4	81	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44	41
5	74	63	55	49	71	60	53	47	55	49	44	51	46	42	47	42	39	37
6	69	57	49	43	65	54	47	42	50	44	39	46	41	37	43	38	35	32
7	64	52	44	38	61	50	42	37	46	40	35	42	37	33	39	35	31	29
8	60	47	39	34	57	45	38	33	42	36	32	39	34	30	36	32	28	26
9	56	43	36	31	53	42	35	30	39	33	29	36	31	27	33	29	26	24
10	52	40	33	28	50	39	32	27	36	30	26	34	28	25	31	27	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	26274	26274	26274	26274
5°	29457	26446	23436	26446
10°	33755	26230	20282	26230
15°	37342	25748	17919	25748
20°	36773	25232	16333	25232
25°	33157	24545	15330	24545
30°	27401	23448	14600	23448
35°	19969	22300	14079	22300
40°	15951	20946	13789	20946
45°	13938	19379	13394	19379
50°	13102	17862	13132	17862
55°	12076	16321	12780	16321
60°	11066	14683	12239	14683
65°	10082	13211	11706	13211
70°	9153	11783	10924	11783
75°	8116	10181	9676	10181
80°	6974	8433	7792	8433
85°	6243	6243	4631	6243



TEST NUMBER: P331377-830

CATALOG NUMBER: S122DIP-S865D330U830-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.0	3.2
10°-20°	450.6	9.4
20°-30°	653.9	13.6
30°-40°	690.0	14.4
40°-50°	611.0	12.7
50°-60°	487.6	10.2
60°-70°	331.4	6.9
70°-80°	169.9	3.5
80°-90°	42.5	0.9
90°-100°	69.2	1.4
100°-110°	235.0	4.9
110°-120°	249.6	5.2
120°-130°	205.5	4.3
130°-140°	165.0	3.4
140°-150°	124.7	2.6
150°-160°	87.6	1.8
160°-170°	51.6	1.1
170°-180°	16.8	0.4
0°-30°	1259.4	26.3
0°-40°	1949.5	40.6
0°-60°	3048.0	63.5
0°-90°	3591.8	74.9
90°-120°	553.8	11.5
90°-150°	1049.0	21.9
90°-180°	1205.0	25.1
0°-180°	4796.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1627	1627	1627	1627	1627	
5°	1818	1632	1446	1632	1818	181
15°	2234	1540	1072	1540	2234	616
25°	1861	1378	860	1378	1861	841
35°	1013	1131	714	1131	1013	659
45°	610	849	587	849	610	480
55°	429	580	454	580	429	385
65°	264	346	306	346	264	262
75°	130	163	155	163	130	139
85°	34	34	25	34	34	37
90°	11	0	11	0	11	8
95°	38	12	38	12	38	49
105°	375	41	375	41	375	363
115°	494	72	494	72	494	484
125°	401	100	401	100	401	362
135°	332	117	332	117	332	258
145°	265	134	265	134	265	168
155°	223	152	223	152	223	104
165°	196	166	196	166	196	56
175°	176	173	176	173	176	17
180°	173	173	173	173	173	



TEST NUMBER: P331377-830

CATALOG NUMBER: S122DIP-S865D330U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1702.4	1702.9	1703.9	1695.9	1694.9	1694.9	1687.9	1681.9	1674.9	1665.4	1666.4
5°	1817.5	1824.4	1826.8	1819.4	1808.1	1806.9	1796.2	1778.7	1762.5	1749.3	1739.9
7.5°	1954.8	1957.6	1951.4	1941.5	1933.2	1918.2	1898.4	1879.1	1851.9	1827.0	1808.5
10°	2058.9	2062.7	2052.0	2037.6	2025.7	2008.2	1979.4	1950.0	1914.4	1880.0	1852.5
12.5°	2138.0	2147.2	2133.5	2131.7	2111.3	2087.3	2053.0	2038.2	1988.0	1940.0	1910.5
15°	2234.0	2233.4	2234.7	2222.7	2207.7	2203.9	2167.8	2128.4	2057.7	2029.5	1980.8
17.5°	2206.2	2215.7	2220.2	2220.0	2219.6	2217.2	2205.6	2180.8	2145.3	2099.7	2043.3
20°	2140.2	2152.7	2154.6	2169.0	2177.1	2187.7	2192.1	2185.2	2163.3	2125.2	2076.4
22.5°	2038.2	2041.6	2047.5	2069.9	2087.5	2114.2	2128.1	2151.2	2142.8	2124.2	2083.4
25°	1861.2	1855.0	1876.9	1888.1	1928.8	1971.3	2002.0	2035.7	2065.8	2083.9	2072.0
27.5°	1648.9	1639.5	1672.3	1702.1	1735.1	1781.2	1829.0	1885.4	1932.3	1990.9	2011.1
30°	1469.7	1475.4	1506.7	1538.5	1588.6	1653.6	1707.4	1769.3	1836.3	1901.9	1947.6
32.5°	1276.6	1298.3	1318.1	1366.9	1411.0	1483.5	1562.3	1639.7	1723.2	1797.8	1868.5
35°	1013.1	1038.2	1065.7	1101.4	1163.3	1235.2	1312.1	1416.5	1530.4	1632.4	1716.2
37.5°	852.8	848.9	864.6	890.3	940.5	998.5	1087.1	1190.3	1324.3	1444.1	1562.3
40°	756.8	754.2	765.5	789.3	827.5	870.0	947.5	1038.2	1162.6	1309.0	1449.7
42.5°	690.7	692.2	698.4	715.2	741.4	776.4	834.4	911.6	1025.6	1163.4	1314.7
45°	610.4	614.8	621.7	629.8	644.8	673.5	706.1	761.1	851.2	966.3	1115.1
47.5°	552.6	552.7	559.8	566.8	575.8	592.0	618.5	653.1	716.6	810.3	938.3
50°	521.6	517.3	522.3	527.8	537.2	548.5	566.0	598.5	641.0	716.7	823.7
52.5°	483.6	483.7	488.2	490.3	498.7	510.0	525.9	548.5	587.0	646.2	734.1
55°	429.0	432.2	434.7	438.4	445.9	454.0	466.6	481.5	511.6	556.0	621.0
57.5°	377.8	378.7	381.3	388.4	393.1	400.7	412.6	426.1	445.6	478.5	527.4
60°	342.7	342.7	347.7	350.8	357.1	364.6	374.0	387.1	404.6	431.5	471.0
62.5°	310.8	310.2	312.2	317.4	322.1	329.1	338.5	349.6	366.1	390.0	422.4
65°	263.9	262.7	266.5	267.7	272.7	279.6	287.1	299.0	312.1	329.6	358.4
67.5°	218.9	220.4	222.4	224.8	227.5	234.8	239.8	248.2	259.3	273.8	293.3
70°	193.9	193.9	193.9	195.8	199.5	203.3	208.3	215.2	225.7	238.3	255.8
72.5°	165.9	167.9	169.8	168.7	173.5	175.8	181.7	185.6	195.8	203.8	219.2
75°	130.1	130.1	130.1	133.2	135.1	137.0	140.7	144.5	149.5	159.5	167.6
77.5°	97.1	96.8	97.5	98.2	100.2	102.5	103.6	107.0	111.6	116.2	123.1
80°	75.0	76.3	76.9	78.1	78.1	79.5	80.0	84.5	87.6	90.7	95.1
82.5°	58.1	58.2	58.4	58.6	59.2	59.9	61.5	63.0	64.0	66.6	70.0
85°	33.7	33.2	33.2	34.4	33.7	33.7	35.1	36.3	36.3	36.9	38.7
87.5°	15.2	15.2	15.7	15.2	15.2	15.6	15.6	15.2	15.7	16.3	16.7
90°	11.0	11.0	11.0	11.0	11.0	10.7	10.0	10.7	11.0	11.3	11.0
92.5°	18.5	18.9	18.8	19.8	20.1	22.1	24.9	29.0	36.6	43.3	42.7
95°	38.0	37.6	38.6	41.3	45.6	53.0	66.9	87.3	114.2	130.5	115.6
97.5°	74.7	77.6	82.4	90.6	106.5	130.5	166.5	203.6	233.8	222.8	167.9
100°	119.2	125.3	134.9	149.2	176.8	217.2	262.8	304.1	311.0	263.1	181.2
102.5°	209.8	217.9	230.0	254.4	284.5	327.2	360.5	369.9	339.8	264.4	176.1
105°	375.3	379.9	394.3	414.9	435.6	446.6	442.2	404.6	335.4	246.8	166.2
107.5°	479.5	485.6	488.5	489.7	487.0	470.9	436.3	379.6	306.1	227.8	161.3
110°	510.9	511.2	508.2	501.9	487.6	460.2	417.6	358.0	287.8	218.8	160.2



TEST NUMBER: P331377-830

CATALOG NUMBER: S122DIP-S865D330U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	510.3	508.5	502.8	492.3	472.4	441.0	395.5	338.3	274.9	212.9	160.4
115°	493.9	490.9	482.2	466.9	443.3	409.0	365.3	314.1	259.1	206.5	161.8
117.5°	464.5	461.9	452.9	436.7	412.6	380.4	340.8	295.8	249.1	203.3	164.3
120°	445.6	442.2	432.6	417.0	393.6	363.4	328.0	286.7	243.7	201.5	165.9
122.5°	425.8	423.1	414.5	399.1	378.1	350.8	317.4	279.6	239.2	200.4	167.7
125°	400.7	397.9	389.6	377.0	357.7	332.7	303.4	269.1	232.8	198.5	170.5
127.5°	378.5	376.4	369.2	357.3	340.4	317.4	289.8	258.7	226.8	197.4	173.3
130°	366.0	363.4	356.7	345.3	329.0	307.1	280.8	252.1	222.8	196.8	175.5
132.5°	353.0	350.5	344.4	333.1	317.1	296.4	272.2	245.7	219.6	196.5	177.7
135°	332.1	330.7	324.7	313.7	299.4	280.8	258.7	236.8	215.1	196.1	180.2
137.5°	311.5	309.5	304.3	294.8	281.7	265.5	248.1	229.7	212.0	196.0	182.5
140°	297.4	295.4	290.4	281.7	271.1	256.5	241.1	225.1	210.1	195.9	183.5
142.5°	283.2	282.9	278.4	270.5	260.4	248.2	235.0	221.4	208.3	195.9	184.3
145°	265.0	264.1	260.8	255.1	247.1	237.4	227.2	216.1	205.9	195.1	185.1
147.5°	249.9	249.2	246.9	242.4	235.8	228.8	220.7	212.1	203.3	194.0	185.4
150°	240.8	240.4	238.5	234.4	229.4	223.5	216.5	209.2	201.1	193.1	185.1
152.5°	233.1	233.0	231.5	228.1	224.1	219.0	213.0	206.2	199.3	191.8	184.6
155°	222.8	223.5	222.2	219.8	216.1	212.4	207.5	202.2	195.9	189.5	183.8
157.5°	214.1	214.1	213.5	211.5	209.0	206.0	201.9	197.5	192.6	187.1	182.3
160°	208.5	208.5	208.1	206.5	204.2	201.8	198.1	194.4	190.1	185.5	181.5
162.5°	203.1	203.4	203.1	202.0	199.6	197.8	194.7	191.5	188.0	184.2	180.7
165°	195.5	195.9	195.9	194.4	193.1	191.8	189.5	187.2	184.5	181.5	179.2
167.5°	188.4	188.8	188.9	188.1	187.6	186.3	184.7	182.9	181.1	179.2	177.7
170°	184.2	184.8	185.1	184.2	183.8	183.1	181.8	180.9	179.2	177.9	176.8
172.5°	180.7	181.1	181.4	181.0	180.6	180.2	179.2	178.4	177.3	176.3	175.8
175°	176.2	176.8	177.2	176.8	176.8	176.5	176.2	175.9	174.8	174.5	174.2
177.5°	173.4	174.0	174.3	174.3	174.3	174.3	174.0	174.0	173.4	173.1	173.4
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1



TEST NUMBER: P331377-830

CATALOG NUMBER: S122DIP-S865D330U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1669.9	1665.8	1663.4	1654.4	1646.3	1638.3	1635.9	1636.8	1625.9	1615.3	1610.8
5°	1734.9	1722.4	1710.5	1693.7	1673.7	1651.7	1640.5	1631.7	1609.9	1586.1	1572.3
7.5°	1793.2	1775.3	1752.5	1720.7	1691.5	1657.1	1635.2	1615.8	1583.8	1550.3	1529.7
10°	1828.7	1804.3	1774.9	1736.2	1700.5	1658.6	1629.2	1599.9	1562.3	1522.3	1497.2
12.5°	1859.3	1826.4	1797.4	1747.7	1705.5	1653.1	1618.3	1576.8	1537.3	1489.8	1465.3
15°	1931.9	1871.2	1816.2	1759.9	1708.0	1634.8	1596.1	1540.4	1488.5	1429.7	1401.6
17.5°	1988.1	1920.0	1833.2	1761.7	1701.1	1620.1	1563.2	1496.5	1435.1	1367.9	1329.6
20°	2020.2	1941.9	1848.7	1763.7	1691.1	1598.6	1536.6	1468.5	1396.6	1320.9	1279.6
22.5°	2039.1	1956.9	1864.7	1756.1	1671.1	1581.0	1503.2	1428.4	1355.6	1273.8	1230.6
25°	2045.1	1970.1	1872.5	1749.9	1646.2	1544.2	1450.4	1377.8	1289.6	1213.3	1150.2
27.5°	2015.3	1961.5	1867.7	1738.1	1617.2	1498.0	1393.5	1311.3	1218.2	1135.4	1071.9
30°	1978.9	1947.6	1856.2	1726.2	1594.2	1466.0	1350.9	1257.7	1165.2	1081.4	1016.3
32.5°	1922.3	1915.5	1835.2	1709.1	1569.7	1425.5	1306.4	1212.2	1109.7	1027.3	965.3
35°	1811.2	1841.3	1790.5	1671.1	1523.5	1367.8	1239.0	1131.4	1025.1	946.2	888.1
37.5°	1662.4	1736.9	1723.6	1615.4	1461.2	1305.0	1162.8	1050.4	949.0	869.5	812.4
40°	1559.8	1654.8	1668.6	1572.9	1417.2	1256.5	1105.8	993.8	894.9	822.5	764.9
42.5°	1449.7	1560.8	1598.6	1521.9	1369.1	1205.4	1054.7	938.8	840.9	770.4	719.3
45°	1265.3	1412.2	1480.4	1436.6	1289.0	1121.3	966.3	848.7	759.9	693.6	654.2
47.5°	1092.7	1253.3	1345.0	1329.6	1199.8	1033.8	880.4	767.6	681.2	628.3	593.0
50°	970.6	1135.8	1246.4	1251.5	1135.8	971.3	817.5	711.1	631.7	582.3	553.5
52.5°	864.6	1022.2	1142.9	1169.4	1064.2	906.3	760.9	655.1	585.1	539.7	514.0
55°	726.1	859.3	993.2	1042.0	957.5	807.4	673.0	579.8	514.1	482.9	460.3
57.5°	603.7	714.7	838.3	892.2	840.2	711.7	585.6	504.7	451.4	424.0	406.8
60°	539.1	626.7	736.8	801.2	756.1	641.7	531.6	454.7	410.9	386.5	370.2
62.5°	479.1	556.7	649.7	708.6	684.1	576.2	477.6	409.6	371.8	349.0	337.2
65°	395.3	456.6	528.5	582.9	566.7	484.7	404.1	345.8	315.8	297.7	288.3
67.5°	325.5	369.8	419.6	467.3	454.2	396.2	331.3	286.1	263.7	248.1	242.4
70°	281.4	315.2	359.6	397.8	387.1	339.6	288.3	249.6	230.2	217.1	211.4
72.5°	239.4	267.2	301.0	332.2	325.1	285.6	242.8	213.5	198.6	186.5	181.9
75°	180.8	202.0	222.6	243.3	241.4	210.8	185.8	163.2	151.4	141.9	140.1
77.5°	133.5	145.3	159.4	171.6	168.2	150.7	131.1	118.2	109.4	103.2	102.2
80°	102.0	108.9	118.9	127.6	123.2	115.7	100.1	90.7	84.5	78.1	75.7
82.5°	73.9	80.8	86.8	91.5	88.2	81.2	71.5	65.1	61.5	57.1	56.2
85°	38.7	42.5	45.1	46.3	45.1	40.6	36.3	33.7	30.6	28.7	28.2
87.5°	16.8	16.3	16.0	16.8	15.2	15.1	12.8	11.0	10.7	10.6	9.7
90°	9.0	6.7	5.0	4.0	3.3	2.6	1.3	0.4	1.3	2.6	3.3
92.5°	33.3	22.6	15.1	12.0	9.7	8.3	5.8	4.1	5.8	8.3	9.7
95°	76.9	48.0	32.6	24.6	19.3	16.3	13.0	11.7	13.0	16.3	19.3
97.5°	103.7	63.2	44.0	35.0	28.8	24.3	20.7	18.9	20.7	24.3	28.8
100°	109.2	68.6	51.0	41.7	35.0	29.6	26.7	25.6	26.7	29.6	35.0
102.5°	109.5	73.4	57.1	47.8	40.8	35.5	32.5	31.8	32.5	35.5	40.8
105°	111.2	81.6	66.0	56.6	49.3	44.3	41.9	40.6	41.9	44.3	49.3
107.5°	115.8	90.0	74.8	65.4	58.2	53.5	51.3	50.2	51.3	53.5	58.2
110°	119.5	95.6	81.0	71.3	64.3	59.9	58.0	56.6	58.0	59.9	64.3





TEST NUMBER: P331377-830

CATALOG NUMBER: S122DIP-S865D330U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	123.6	100.9	86.8	76.8	70.1	66.1	63.8	62.5	63.8	66.1	70.1
115°	129.5	109.2	94.9	86.0	79.3	75.3	73.2	71.6	73.2	75.3	79.3
117.5°	135.9	116.9	103.7	94.3	87.9	84.4	82.4	81.1	82.4	84.4	87.9
120°	140.3	122.2	109.2	99.9	93.2	90.3	88.2	86.9	88.2	90.3	93.2
122.5°	143.9	127.2	115.1	105.5	98.9	95.6	93.6	92.6	93.6	95.6	98.9
125°	149.9	134.9	122.9	113.6	106.9	102.9	100.9	99.9	100.9	102.9	106.9
127.5°	155.4	141.9	130.3	120.6	114.3	109.9	107.1	105.8	107.1	109.9	114.3
130°	158.8	146.2	134.5	125.3	118.6	113.9	110.6	109.2	110.6	113.9	118.6
132.5°	162.3	150.0	138.8	129.5	122.5	117.6	114.0	112.4	114.0	117.6	122.5
135°	166.8	155.2	144.5	135.3	127.5	122.5	118.6	117.3	118.6	122.5	127.5
137.5°	170.3	159.5	148.9	140.3	132.7	127.3	123.4	121.8	123.4	127.3	132.7
140°	172.2	161.8	151.8	143.2	135.9	130.5	126.6	125.3	126.6	130.5	135.9
142.5°	173.8	163.7	154.0	145.9	138.8	133.5	129.8	128.7	129.8	133.5	138.8
145°	175.9	166.5	157.5	150.2	143.5	138.6	135.3	133.8	135.3	138.6	143.5
147.5°	177.0	168.8	160.3	153.8	148.3	143.6	140.4	139.5	140.4	143.6	148.3
150°	177.5	169.8	162.2	156.2	151.2	146.8	144.2	143.2	144.2	146.8	151.2
152.5°	177.8	170.9	164.0	158.6	153.8	150.1	147.4	146.9	147.4	150.1	153.8
155°	178.1	172.5	166.8	161.8	158.2	154.5	152.5	152.2	152.5	154.5	158.2
157.5°	178.1	173.6	168.8	164.7	161.7	158.5	156.9	156.6	156.9	158.5	161.7
160°	178.1	174.2	170.2	166.5	163.8	161.2	159.9	159.5	159.9	161.2	163.8
162.5°	177.9	174.5	171.0	168.1	165.7	163.6	162.2	162.5	162.2	163.6	165.7
165°	177.2	174.8	171.8	169.8	168.1	166.2	165.5	165.9	165.5	166.2	168.1
167.5°	176.7	174.7	172.6	171.4	170.1	168.8	168.2	168.6	168.2	168.8	170.1
170°	176.2	174.5	172.9	171.8	171.2	170.2	169.8	170.5	169.8	170.2	171.2
172.5°	175.4	174.3	173.1	172.4	172.0	171.0	171.2	171.5	171.2	171.0	172.0
175°	174.5	173.8	173.1	172.9	172.9	172.2	172.5	172.9	172.5	172.2	172.9
177.5°	174.0	173.4	173.1	173.1	173.1	172.7	172.9	173.4	172.9	172.7	173.1
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1



TEST NUMBER: P331377-830

CATALOG NUMBER: S122DIP-S865D330U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1605.8	1602.8	1592.3	1586.9	1577.8	1569.3	1563.8	1566.3	1568.3	1567.3	1565.8
5°	1559.8	1547.9	1529.7	1514.1	1502.9	1482.2	1473.5	1469.1	1465.4	1460.9	1456.6
7.5°	1505.1	1486.3	1460.2	1437.9	1416.9	1391.3	1376.7	1367.9	1359.0	1349.1	1340.3
10°	1466.0	1439.7	1412.2	1380.9	1355.9	1332.8	1312.1	1298.4	1285.9	1273.9	1265.3
12.5°	1424.9	1394.7	1360.7	1317.9	1290.3	1257.3	1254.1	1229.8	1210.3	1203.0	1192.7
15°	1359.7	1317.1	1273.9	1223.3	1201.5	1171.4	1152.6	1133.9	1117.0	1105.1	1102.0
17.5°	1285.5	1230.5	1187.5	1151.1	1115.2	1084.5	1067.2	1052.3	1038.3	1022.5	1020.3
20°	1229.0	1181.4	1134.5	1102.6	1065.7	1034.4	1013.1	998.2	986.3	976.9	968.7
22.5°	1175.4	1123.4	1080.4	1045.6	1009.2	983.9	967.1	952.6	942.7	932.4	924.7
25°	1089.5	1048.9	1001.9	962.5	932.5	916.2	902.5	889.9	883.7	876.8	868.1
27.5°	1014.3	969.1	925.3	894.8	868.4	853.9	844.2	835.7	829.8	825.8	820.8
30°	961.3	915.6	881.2	851.2	829.3	814.9	808.7	803.7	796.8	794.3	791.8
32.5°	910.2	869.1	839.7	813.7	792.8	783.4	777.7	773.2	767.8	765.3	760.3
35°	838.1	803.7	774.9	760.5	743.7	735.5	731.1	724.9	719.8	717.4	716.7
37.5°	770.2	740.3	721.3	702.9	695.7	690.7	684.8	680.4	678.9	678.5	678.0
40°	726.1	701.7	684.9	669.9	666.7	659.2	654.2	650.4	650.4	651.1	650.4
42.5°	686.1	664.2	649.3	636.3	632.6	628.2	623.2	622.9	624.0	626.0	624.0
45°	625.4	609.8	599.2	592.9	586.0	581.6	581.0	582.9	583.5	584.2	586.0
47.5°	569.7	559.2	549.6	542.7	539.7	538.9	538.2	541.5	544.5	545.6	548.5
50°	536.6	524.7	516.6	512.2	509.7	508.5	509.7	513.5	515.9	519.1	520.9
52.5°	499.5	491.2	485.6	482.2	481.2	481.9	482.2	486.4	490.5	491.5	492.5
55°	448.5	442.1	440.9	435.3	437.8	437.2	440.3	442.8	446.6	450.3	450.9
57.5°	397.4	392.4	389.0	389.6	390.3	393.0	395.7	400.0	404.1	408.0	408.4
60°	363.4	360.9	359.0	359.0	360.2	364.0	367.1	371.5	374.0	376.5	378.3
62.5°	332.3	329.9	328.0	328.9	332.2	334.5	338.1	340.4	343.0	345.4	346.4
65°	283.3	282.1	284.0	285.2	285.8	289.0	293.3	295.2	297.7	299.0	303.3
67.5°	238.2	238.4	238.2	239.9	243.6	244.3	248.5	252.8	253.3	255.7	258.5
70°	207.6	208.9	210.2	211.4	214.5	215.7	218.9	220.7	223.3	225.2	227.1
72.5°	179.6	179.8	181.2	180.9	183.5	186.2	188.9	190.8	193.2	195.7	197.5
75°	138.2	138.2	139.5	140.1	143.3	146.4	145.7	146.9	149.5	151.9	153.3
77.5°	100.9	99.5	100.9	101.6	102.5	105.2	105.7	107.4	110.3	109.4	110.8
80°	76.9	75.0	76.9	77.6	77.6	80.7	80.7	81.9	83.8	81.9	83.8
82.5°	55.0	54.0	55.4	55.5	56.6	56.6	57.7	57.9	59.8	58.9	59.8
85°	27.5	26.9	27.5	26.9	27.5	28.2	28.2	27.5	27.5	28.7	26.9
87.5°	9.3	9.0	8.9	9.3	9.2	8.8	8.2	8.1	8.0	7.2	7.2
90°	4.0	5.0	6.7	9.0	11.0	11.3	11.0	10.7	10.0	10.7	11.0
92.5°	12.0	15.1	22.6	33.3	42.7	43.3	36.6	29.0	24.9	22.1	20.1
95°	24.6	32.6	48.0	76.9	115.6	130.5	114.2	87.3	66.9	53.0	45.6
97.5°	35.0	44.0	63.2	103.7	167.9	222.8	233.8	203.6	166.5	130.5	106.5
100°	41.7	51.0	68.6	109.2	181.2	263.1	311.0	304.1	262.8	217.2	176.8
102.5°	47.8	57.1	73.4	109.5	176.1	264.4	339.8	369.9	360.5	327.2	284.5
105°	56.6	66.0	81.6	111.2	166.2	246.8	335.4	404.6	442.2	446.6	435.6
107.5°	65.4	74.8	90.0	115.8	161.3	227.8	306.1	379.6	436.3	470.9	487.0
110°	71.3	81.0	95.6	119.5	160.2	218.8	287.8	358.0	417.6	460.2	487.6



TEST NUMBER: P331377-830

CATALOG NUMBER: S122DIP-S865D330U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	76.8	86.8	100.9	123.6	160.4	212.9	274.9	338.3	395.5	441.0	472.4
115°	86.0	94.9	109.2	129.5	161.8	206.5	259.1	314.1	365.3	409.0	443.3
117.5°	94.3	103.7	116.9	135.9	164.3	203.3	249.1	295.8	340.8	380.4	412.6
120°	99.9	109.2	122.2	140.3	165.9	201.5	243.7	286.7	328.0	363.4	393.6
122.5°	105.5	115.1	127.2	143.9	167.7	200.4	239.2	279.6	317.4	350.8	378.1
125°	113.6	122.9	134.9	149.9	170.5	198.5	232.8	269.1	303.4	332.7	357.7
127.5°	120.6	130.3	141.9	155.4	173.3	197.4	226.8	258.7	289.8	317.4	340.4
130°	125.3	134.5	146.2	158.8	175.5	196.8	222.8	252.1	280.8	307.1	329.0
132.5°	129.5	138.8	150.0	162.3	177.7	196.5	219.6	245.7	272.2	296.4	317.1
135°	135.3	144.5	155.2	166.8	180.2	196.1	215.1	236.8	258.7	280.8	299.4
137.5°	140.3	148.9	159.5	170.3	182.5	196.0	212.0	229.7	248.1	265.5	281.7
140°	143.2	151.8	161.8	172.2	183.5	195.9	210.1	225.1	241.1	256.5	271.1
142.5°	145.9	154.0	163.7	173.8	184.3	195.9	208.3	221.4	235.0	248.2	260.4
145°	150.2	157.5	166.5	175.9	185.1	195.1	205.9	216.1	227.2	237.4	247.1
147.5°	153.8	160.3	168.8	177.0	185.4	194.0	203.3	212.1	220.7	228.8	235.8
150°	156.2	162.2	169.8	177.5	185.1	193.1	201.1	209.2	216.5	223.5	229.4
152.5°	158.6	164.0	170.9	177.8	184.6	191.8	199.3	206.2	213.0	219.0	224.1
155°	161.8	166.8	172.5	178.1	183.8	189.5	195.9	202.2	207.5	212.4	216.1
157.5°	164.7	168.8	173.6	178.1	182.3	187.1	192.6	197.5	201.9	206.0	209.0
160°	166.5	170.2	174.2	178.1	181.5	185.5	190.1	194.4	198.1	201.8	204.2
162.5°	168.1	171.0	174.5	177.9	180.7	184.2	188.0	191.5	194.7	197.8	199.6
165°	169.8	171.8	174.8	177.2	179.2	181.5	184.5	187.2	189.5	191.8	193.1
167.5°	171.4	172.6	174.7	176.7	177.7	179.2	181.1	182.9	184.7	186.3	187.6
170°	171.8	172.9	174.5	176.2	176.8	177.9	179.2	180.9	181.8	183.1	183.8
172.5°	172.4	173.1	174.3	175.4	175.8	176.3	177.3	178.4	179.2	180.2	180.6
175°	172.9	173.1	173.8	174.5	174.2	174.5	174.8	175.9	176.2	176.5	176.8
177.5°	173.1	173.1	173.4	174.0	173.4	173.1	173.4	174.0	174.0	174.3	174.3
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1



TEST NUMBER: P331377-830

CATALOG NUMBER: S122DIP-S865D330U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1560.8	1559.8	1559.8	1555.3	1559.8	1559.8	1560.8	1565.8	1567.3	1568.3	1566.3
5°	1447.8	1446.0	1442.8	1446.0	1442.8	1446.0	1447.8	1456.6	1460.9	1465.4	1469.1
7.5°	1336.1	1328.6	1327.5	1320.1	1327.5	1328.6	1336.1	1340.3	1349.1	1359.0	1367.9
10°	1254.6	1249.6	1249.0	1237.1	1249.0	1249.6	1254.6	1265.3	1273.9	1285.9	1298.4
12.5°	1192.6	1180.5	1182.9	1176.0	1182.9	1180.5	1192.6	1192.7	1203.0	1210.3	1229.8
15°	1085.1	1085.1	1082.6	1072.0	1082.6	1085.1	1085.1	1102.0	1105.1	1117.0	1133.9
17.5°	1008.0	1006.6	1000.7	1003.7	1000.7	1006.6	1008.0	1020.3	1022.5	1038.3	1052.3
20°	961.9	958.2	950.6	950.6	950.6	958.2	961.9	968.7	976.9	986.3	998.2
22.5°	918.4	918.1	910.1	912.6	910.1	918.1	918.4	924.7	932.4	942.7	952.6
25°	867.4	862.4	858.8	860.5	858.8	862.4	867.4	868.1	876.8	883.7	889.9
27.5°	819.2	816.4	816.1	811.1	816.1	816.4	819.2	820.8	825.8	829.8	835.7
30°	791.2	784.9	786.2	783.1	786.2	784.9	791.2	791.8	794.3	796.8	803.7
32.5°	759.1	756.9	755.6	753.0	755.6	756.9	759.1	760.3	765.3	767.8	773.2
35°	715.5	716.1	712.9	714.3	712.9	716.1	715.5	716.7	717.4	719.8	724.9
37.5°	677.3	679.3	677.9	678.3	677.9	679.3	677.3	678.0	678.5	678.9	680.4
40°	652.3	652.3	652.3	654.2	652.3	652.3	652.3	650.4	651.1	650.4	650.4
42.5°	628.3	627.3	626.3	626.1	626.3	627.3	628.3	624.0	626.0	624.0	622.9
45°	587.3	589.2	589.7	586.6	589.7	589.2	587.3	586.0	584.2	583.5	582.9
47.5°	550.2	550.4	550.2	552.9	550.2	550.4	550.2	548.5	545.6	544.5	541.5
50°	524.1	522.8	524.1	522.8	524.1	522.8	524.1	520.9	519.1	515.9	513.5
52.5°	496.6	496.8	496.1	495.9	496.1	496.8	496.6	492.5	491.5	490.5	486.4
55°	453.5	454.7	454.0	454.0	454.0	454.7	453.5	450.9	450.3	446.6	442.8
57.5°	408.8	409.9	410.8	408.0	410.8	409.9	408.8	408.4	408.0	404.1	400.0
60°	377.8	380.9	380.2	379.0	380.2	380.9	377.8	378.3	376.5	374.0	371.5
62.5°	349.2	350.3	350.2	350.0	350.2	350.3	349.2	346.4	345.4	343.0	340.4
65°	305.2	306.4	304.5	306.4	304.5	306.4	305.2	303.3	299.0	297.7	295.2
67.5°	257.8	258.2	259.6	260.4	259.6	258.2	257.8	258.5	255.7	253.3	252.8
70°	228.3	227.6	229.5	231.4	229.5	227.6	228.3	227.1	225.2	223.3	220.7
72.5°	197.3	198.6	198.0	199.3	198.0	198.6	197.3	197.5	195.7	193.2	190.8
75°	151.9	153.8	153.3	155.1	153.3	153.8	151.9	153.3	151.9	149.5	146.9
77.5°	109.8	110.1	109.8	110.8	109.8	110.1	109.8	110.8	109.4	110.3	107.4
80°	83.8	82.6	81.3	83.8	81.3	82.6	83.8	83.8	81.9	83.8	81.9
82.5°	58.2	59.0	57.8	57.8	57.8	59.0	58.2	59.8	58.9	59.8	57.9
85°	26.9	26.3	25.0	25.0	25.0	26.3	26.9	26.9	28.7	27.5	27.5
87.5°	7.2	6.7	6.7	6.2	6.7	6.7	7.2	7.2	7.2	8.0	8.1
90°	11.0	11.0	11.0	11.0	11.0	11.0	11.0	11.0	10.7	10.0	10.7
92.5°	19.8	18.8	18.9	18.5	18.9	18.8	19.8	20.1	22.1	24.9	29.0
95°	41.3	38.6	37.6	38.0	37.6	38.6	41.3	45.6	53.0	66.9	87.3
97.5°	90.6	82.4	77.6	74.7	77.6	82.4	90.6	106.5	130.5	166.5	203.6
100°	149.2	134.9	125.3	119.2	125.3	134.9	149.2	176.8	217.2	262.8	304.1
102.5°	254.4	230.0	217.9	209.8	217.9	230.0	254.4	284.5	327.2	360.5	369.9
105°	414.9	394.3	379.9	375.3	379.9	394.3	414.9	435.6	446.6	442.2	404.6
107.5°	489.7	488.5	485.6	479.5	485.6	488.5	489.7	487.0	470.9	436.3	379.6
110°	501.9	508.2	511.2	510.9	511.2	508.2	501.9	487.6	460.2	417.6	358.0



TEST NUMBER: P331377-830

CATALOG NUMBER: S122DIP-S865D330U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	492.3	502.8	508.5	510.3	508.5	502.8	492.3	472.4	441.0	395.5	338.3
115°	466.9	482.2	490.9	493.9	490.9	482.2	466.9	443.3	409.0	365.3	314.1
117.5°	436.7	452.9	461.9	464.5	461.9	452.9	436.7	412.6	380.4	340.8	295.8
120°	417.0	432.6	442.2	445.6	442.2	432.6	417.0	393.6	363.4	328.0	286.7
122.5°	399.1	414.5	423.1	425.8	423.1	414.5	399.1	378.1	350.8	317.4	279.6
125°	377.0	389.6	397.9	400.7	397.9	389.6	377.0	357.7	332.7	303.4	269.1
127.5°	357.3	369.2	376.4	378.5	376.4	369.2	357.3	340.4	317.4	289.8	258.7
130°	345.3	356.7	363.4	366.0	363.4	356.7	345.3	329.0	307.1	280.8	252.1
132.5°	333.1	344.4	350.5	353.0	350.5	344.4	333.1	317.1	296.4	272.2	245.7
135°	313.7	324.7	330.7	332.1	330.7	324.7	313.7	299.4	280.8	258.7	236.8
137.5°	294.8	304.3	309.5	311.5	309.5	304.3	294.8	281.7	265.5	248.1	229.7
140°	281.7	290.4	295.4	297.4	295.4	290.4	281.7	271.1	256.5	241.1	225.1
142.5°	270.5	278.4	282.9	283.2	282.9	278.4	270.5	260.4	248.2	235.0	221.4
145°	255.1	260.8	264.1	265.0	264.1	260.8	255.1	247.1	237.4	227.2	216.1
147.5°	242.4	246.9	249.2	249.9	249.2	246.9	242.4	235.8	228.8	220.7	212.1
150°	234.4	238.5	240.4	240.8	240.4	238.5	234.4	229.4	223.5	216.5	209.2
152.5°	228.1	231.5	233.0	233.1	233.0	231.5	228.1	224.1	219.0	213.0	206.2
155°	219.8	222.2	223.5	222.8	223.5	222.2	219.8	216.1	212.4	207.5	202.2
157.5°	211.5	213.5	214.1	214.1	214.1	213.5	211.5	209.0	206.0	201.9	197.5
160°	206.5	208.1	208.5	208.5	208.5	208.1	206.5	204.2	201.8	198.1	194.4
162.5°	202.0	203.1	203.4	203.1	203.4	203.1	202.0	199.6	197.8	194.7	191.5
165°	194.4	195.9	195.9	195.5	195.9	195.9	194.4	193.1	191.8	189.5	187.2
167.5°	188.1	188.9	188.8	188.4	188.8	188.9	188.1	187.6	186.3	184.7	182.9
170°	184.2	185.1	184.8	184.2	184.8	185.1	184.2	183.8	183.1	181.8	180.9
172.5°	181.0	181.4	181.1	180.7	181.1	181.4	181.0	180.6	180.2	179.2	178.4
175°	176.8	177.2	176.8	176.2	176.8	177.2	176.8	176.8	176.5	176.2	175.9
177.5°	174.3	174.3	174.0	173.4	174.0	174.3	174.3	174.3	174.3	174.0	174.0
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1



TEST NUMBER: P331377-830

CATALOG NUMBER: S122DIP-S865D330U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1563.8	1569.3	1577.8	1586.9	1592.3	1602.8	1605.8	1610.8	1615.3	1625.9	1636.8
5°	1473.5	1482.2	1502.9	1514.1	1529.7	1547.9	1559.8	1572.3	1586.1	1609.9	1631.7
7.5°	1376.7	1391.3	1416.9	1437.9	1460.2	1486.3	1505.1	1529.7	1550.3	1583.8	1615.8
10°	1312.1	1332.8	1355.9	1380.9	1412.2	1439.7	1466.0	1497.2	1522.3	1562.3	1599.9
12.5°	1254.1	1257.3	1290.3	1317.9	1360.7	1394.7	1424.9	1465.3	1489.8	1537.3	1576.8
15°	1152.6	1171.4	1201.5	1223.3	1273.9	1317.1	1359.7	1401.6	1429.7	1488.5	1540.4
17.5°	1067.2	1084.5	1115.2	1151.1	1187.5	1230.5	1285.5	1329.6	1367.9	1435.1	1496.5
20°	1013.1	1034.4	1065.7	1102.6	1134.5	1181.4	1229.0	1279.6	1320.9	1396.6	1468.5
22.5°	967.1	983.9	1009.2	1045.6	1080.4	1123.4	1175.4	1230.6	1273.8	1355.6	1428.4
25°	902.5	916.2	932.5	962.5	1001.9	1048.9	1089.5	1150.2	1213.3	1289.6	1377.8
27.5°	844.2	853.9	868.4	894.8	925.3	969.1	1014.3	1071.9	1135.4	1218.2	1311.3
30°	808.7	814.9	829.3	851.2	881.2	915.6	961.3	1016.3	1081.4	1165.2	1257.7
32.5°	777.7	783.4	792.8	813.7	839.7	869.1	910.2	965.3	1027.3	1109.7	1212.2
35°	731.1	735.5	743.7	760.5	774.9	803.7	838.1	888.1	946.2	1025.1	1131.4
37.5°	684.8	690.7	695.7	702.9	721.3	740.3	770.2	812.4	869.5	949.0	1050.4
40°	654.2	659.2	666.7	669.9	684.9	701.7	726.1	764.9	822.5	894.9	993.8
42.5°	623.2	628.2	632.6	636.3	649.3	664.2	686.1	719.3	770.4	840.9	938.8
45°	581.0	581.6	586.0	592.9	599.2	609.8	625.4	654.2	693.6	759.9	848.7
47.5°	538.2	538.9	539.7	542.7	549.6	559.2	569.7	593.0	628.3	681.2	767.6
50°	509.7	508.5	509.7	512.2	516.6	524.7	536.6	553.5	582.3	631.7	711.1
52.5°	482.2	481.9	481.2	482.2	485.6	491.2	499.5	514.0	539.7	585.1	655.1
55°	440.3	437.2	437.8	435.3	440.9	442.1	448.5	460.3	482.9	514.1	579.8
57.5°	395.7	393.0	390.3	389.6	389.0	392.4	397.4	406.8	424.0	451.4	504.7
60°	367.1	364.0	360.2	359.0	359.0	360.9	363.4	370.2	386.5	410.9	454.7
62.5°	338.1	334.5	332.2	328.9	328.0	329.9	332.3	337.2	349.0	371.8	409.6
65°	293.3	289.0	285.8	285.2	284.0	282.1	283.3	288.3	297.7	315.8	345.8
67.5°	248.5	244.3	243.6	239.9	238.2	238.4	238.2	242.4	248.1	263.7	286.1
70°	218.9	215.7	214.5	211.4	210.2	208.9	207.6	211.4	217.1	230.2	249.6
72.5°	188.9	186.2	183.5	180.9	181.2	179.8	179.6	181.9	186.5	198.6	213.5
75°	145.7	146.4	143.3	140.1	139.5	138.2	138.2	140.1	141.9	151.4	163.2
77.5°	105.7	105.2	102.5	101.6	100.9	99.5	100.9	102.2	103.2	109.4	118.2
80°	80.7	80.7	77.6	77.6	76.9	75.0	76.9	75.7	78.1	84.5	90.7
82.5°	57.7	56.6	56.6	55.5	55.4	54.0	55.0	56.2	57.1	61.5	65.1
85°	28.2	28.2	27.5	26.9	27.5	26.9	27.5	28.2	28.7	30.6	33.7
87.5°	8.2	8.8	9.2	9.3	8.9	9.0	9.3	9.7	10.6	10.7	11.0
90°	11.0	11.3	11.0	9.0	6.7	5.0	4.0	3.3	2.6	1.3	0.4
92.5°	36.6	43.3	42.7	33.3	22.6	15.1	12.0	9.7	8.3	5.8	4.1
95°	114.2	130.5	115.6	76.9	48.0	32.6	24.6	19.3	16.3	13.0	11.7
97.5°	233.8	222.8	167.9	103.7	63.2	44.0	35.0	28.8	24.3	20.7	18.9
100°	311.0	263.1	181.2	109.2	68.6	51.0	41.7	35.0	29.6	26.7	25.6
102.5°	339.8	264.4	176.1	109.5	73.4	57.1	47.8	40.8	35.5	32.5	31.8
105°	335.4	246.8	166.2	111.2	81.6	66.0	56.6	49.3	44.3	41.9	40.6
107.5°	306.1	227.8	161.3	115.8	90.0	74.8	65.4	58.2	53.5	51.3	50.2
110°	287.8	218.8	160.2	119.5	95.6	81.0	71.3	64.3	59.9	58.0	56.6



TEST NUMBER: P331377-830

CATALOG NUMBER: S122DIP-S865D330U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	274.9	212.9	160.4	123.6	100.9	86.8	76.8	70.1	66.1	63.8	62.5
115°	259.1	206.5	161.8	129.5	109.2	94.9	86.0	79.3	75.3	73.2	71.6
117.5°	249.1	203.3	164.3	135.9	116.9	103.7	94.3	87.9	84.4	82.4	81.1
120°	243.7	201.5	165.9	140.3	122.2	109.2	99.9	93.2	90.3	88.2	86.9
122.5°	239.2	200.4	167.7	143.9	127.2	115.1	105.5	98.9	95.6	93.6	92.6
125°	232.8	198.5	170.5	149.9	134.9	122.9	113.6	106.9	102.9	100.9	99.9
127.5°	226.8	197.4	173.3	155.4	141.9	130.3	120.6	114.3	109.9	107.1	105.8
130°	222.8	196.8	175.5	158.8	146.2	134.5	125.3	118.6	113.9	110.6	109.2
132.5°	219.6	196.5	177.7	162.3	150.0	138.8	129.5	122.5	117.6	114.0	112.4
135°	215.1	196.1	180.2	166.8	155.2	144.5	135.3	127.5	122.5	118.6	117.3
137.5°	212.0	196.0	182.5	170.3	159.5	148.9	140.3	132.7	127.3	123.4	121.8
140°	210.1	195.9	183.5	172.2	161.8	151.8	143.2	135.9	130.5	126.6	125.3
142.5°	208.3	195.9	184.3	173.8	163.7	154.0	145.9	138.8	133.5	129.8	128.7
145°	205.9	195.1	185.1	175.9	166.5	157.5	150.2	143.5	138.6	135.3	133.8
147.5°	203.3	194.0	185.4	177.0	168.8	160.3	153.8	148.3	143.6	140.4	139.5
150°	201.1	193.1	185.1	177.5	169.8	162.2	156.2	151.2	146.8	144.2	143.2
152.5°	199.3	191.8	184.6	177.8	170.9	164.0	158.6	153.8	150.1	147.4	146.9
155°	195.9	189.5	183.8	178.1	172.5	166.8	161.8	158.2	154.5	152.5	152.2
157.5°	192.6	187.1	182.3	178.1	173.6	168.8	164.7	161.7	158.5	156.9	156.6
160°	190.1	185.5	181.5	178.1	174.2	170.2	166.5	163.8	161.2	159.9	159.5
162.5°	188.0	184.2	180.7	177.9	174.5	171.0	168.1	165.7	163.6	162.2	162.5
165°	184.5	181.5	179.2	177.2	174.8	171.8	169.8	168.1	166.2	165.5	165.9
167.5°	181.1	179.2	177.7	176.7	174.7	172.6	171.4	170.1	168.8	168.2	168.6
170°	179.2	177.9	176.8	176.2	174.5	172.9	171.8	171.2	170.2	169.8	170.5
172.5°	177.3	176.3	175.8	175.4	174.3	173.1	172.4	172.0	171.0	171.2	171.5
175°	174.8	174.5	174.2	174.5	173.8	173.1	172.9	172.9	172.2	172.5	172.9
177.5°	173.4	173.1	173.4	174.0	173.4	173.1	173.1	173.1	172.7	172.9	173.4
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1



TEST NUMBER: P331377-830

CATALOG NUMBER: S122DIP-S865D330U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1635.9	1638.3	1646.3	1654.4	1663.4	1665.8	1669.9	1666.4	1665.4	1674.9	1681.9
5°	1640.5	1651.7	1673.7	1693.7	1710.5	1722.4	1734.9	1739.9	1749.3	1762.5	1778.7
7.5°	1635.2	1657.1	1691.5	1720.7	1752.5	1775.3	1793.2	1808.5	1827.0	1851.9	1879.1
10°	1629.2	1658.6	1700.5	1736.2	1774.9	1804.3	1828.7	1852.5	1880.0	1914.4	1950.0
12.5°	1618.3	1653.1	1705.5	1747.7	1797.4	1826.4	1859.3	1910.5	1940.0	1988.0	2038.2
15°	1596.1	1634.8	1708.0	1759.9	1816.2	1871.2	1931.9	1980.8	2029.5	2057.7	2128.4
17.5°	1563.2	1620.1	1701.1	1761.7	1833.2	1920.0	1988.1	2043.3	2099.7	2145.3	2180.8
20°	1536.6	1598.6	1691.1	1763.7	1848.7	1941.9	2020.2	2076.4	2125.2	2163.3	2185.2
22.5°	1503.2	1581.0	1671.1	1756.1	1864.7	1956.9	2039.1	2083.4	2124.2	2142.8	2151.2
25°	1450.4	1544.2	1646.2	1749.9	1872.5	1970.1	2045.1	2072.0	2083.9	2065.8	2035.7
27.5°	1393.5	1498.0	1617.2	1738.1	1867.7	1961.5	2015.3	2011.1	1990.9	1932.3	1885.4
30°	1350.9	1466.0	1594.2	1726.2	1856.2	1947.6	1978.9	1947.6	1901.9	1836.3	1769.3
32.5°	1306.4	1425.5	1569.7	1709.1	1835.2	1915.5	1922.3	1868.5	1797.8	1723.2	1639.7
35°	1239.0	1367.8	1523.5	1671.1	1790.5	1841.3	1811.2	1716.2	1632.4	1530.4	1416.5
37.5°	1162.8	1305.0	1461.2	1615.4	1723.6	1736.9	1662.4	1562.3	1444.1	1324.3	1190.3
40°	1105.8	1256.5	1417.2	1572.9	1668.6	1654.8	1559.8	1449.7	1309.0	1162.6	1038.2
42.5°	1054.7	1205.4	1369.1	1521.9	1598.6	1560.8	1449.7	1314.7	1163.4	1025.6	911.6
45°	966.3	1121.3	1289.0	1436.6	1480.4	1412.2	1265.3	1115.1	966.3	851.2	761.1
47.5°	880.4	1033.8	1199.8	1329.6	1345.0	1253.3	1092.7	938.3	810.3	716.6	653.1
50°	817.5	971.3	1135.8	1251.5	1246.4	1135.8	970.6	823.7	716.7	641.0	598.5
52.5°	760.9	906.3	1064.2	1169.4	1142.9	1022.2	864.6	734.1	646.2	587.0	548.5
55°	673.0	807.4	957.5	1042.0	993.2	859.3	726.1	621.0	556.0	511.6	481.5
57.5°	585.6	711.7	840.2	892.2	838.3	714.7	603.7	527.4	478.5	445.6	426.1
60°	531.6	641.7	756.1	801.2	736.8	626.7	539.1	471.0	431.5	404.6	387.1
62.5°	477.6	576.2	684.1	708.6	649.7	556.7	479.1	422.4	390.0	366.1	349.6
65°	404.1	484.7	566.7	582.9	528.5	456.6	395.3	358.4	329.6	312.1	299.0
67.5°	331.3	396.2	454.2	467.3	419.6	369.8	325.5	293.3	273.8	259.3	248.2
70°	288.3	339.6	387.1	397.8	359.6	315.2	281.4	255.8	238.3	225.7	215.2
72.5°	242.8	285.6	325.1	332.2	301.0	267.2	239.4	219.2	203.8	195.8	185.6
75°	185.8	210.8	241.4	243.3	222.6	202.0	180.8	167.6	159.5	149.5	144.5
77.5°	131.1	150.7	168.2	171.6	159.4	145.3	133.5	123.1	116.2	111.6	107.0
80°	100.1	115.7	123.2	127.6	118.9	108.9	102.0	95.1	90.7	87.6	84.5
82.5°	71.5	81.2	88.2	91.5	86.8	80.8	73.9	70.0	66.6	64.0	63.0
85°	36.3	40.6	45.1	46.3	45.1	42.5	38.7	38.7	36.9	36.3	36.3
87.5°	12.8	15.1	15.2	16.8	16.0	16.3	16.8	16.7	16.3	15.7	15.2
90°	1.3	2.6	3.3	4.0	5.0	6.7	9.0	11.0	11.3	11.0	10.7
92.5°	5.8	8.3	9.7	12.0	15.1	22.6	33.3	42.7	43.3	36.6	29.0
95°	13.0	16.3	19.3	24.6	32.6	48.0	76.9	115.6	130.5	114.2	87.3
97.5°	20.7	24.3	28.8	35.0	44.0	63.2	103.7	167.9	222.8	233.8	203.6
100°	26.7	29.6	35.0	41.7	51.0	68.6	109.2	181.2	263.1	311.0	304.1
102.5°	32.5	35.5	40.8	47.8	57.1	73.4	109.5	176.1	264.4	339.8	369.9
105°	41.9	44.3	49.3	56.6	66.0	81.6	111.2	166.2	246.8	335.4	404.6
107.5°	51.3	53.5	58.2	65.4	74.8	90.0	115.8	161.3	227.8	306.1	379.6
110°	58.0	59.9	64.3	71.3	81.0	95.6	119.5	160.2	218.8	287.8	358.0





TEST NUMBER: P331377-830

CATALOG NUMBER: S122DIP-S865D330U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	63.8	66.1	70.1	76.8	86.8	100.9	123.6	160.4	212.9	274.9	338.3
115°	73.2	75.3	79.3	86.0	94.9	109.2	129.5	161.8	206.5	259.1	314.1
117.5°	82.4	84.4	87.9	94.3	103.7	116.9	135.9	164.3	203.3	249.1	295.8
120°	88.2	90.3	93.2	99.9	109.2	122.2	140.3	165.9	201.5	243.7	286.7
122.5°	93.6	95.6	98.9	105.5	115.1	127.2	143.9	167.7	200.4	239.2	279.6
125°	100.9	102.9	106.9	113.6	122.9	134.9	149.9	170.5	198.5	232.8	269.1
127.5°	107.1	109.9	114.3	120.6	130.3	141.9	155.4	173.3	197.4	226.8	258.7
130°	110.6	113.9	118.6	125.3	134.5	146.2	158.8	175.5	196.8	222.8	252.1
132.5°	114.0	117.6	122.5	129.5	138.8	150.0	162.3	177.7	196.5	219.6	245.7
135°	118.6	122.5	127.5	135.3	144.5	155.2	166.8	180.2	196.1	215.1	236.8
137.5°	123.4	127.3	132.7	140.3	148.9	159.5	170.3	182.5	196.0	212.0	229.7
140°	126.6	130.5	135.9	143.2	151.8	161.8	172.2	183.5	195.9	210.1	225.1
142.5°	129.8	133.5	138.8	145.9	154.0	163.7	173.8	184.3	195.9	208.3	221.4
145°	135.3	138.6	143.5	150.2	157.5	166.5	175.9	185.1	195.1	205.9	216.1
147.5°	140.4	143.6	148.3	153.8	160.3	168.8	177.0	185.4	194.0	203.3	212.1
150°	144.2	146.8	151.2	156.2	162.2	169.8	177.5	185.1	193.1	201.1	209.2
152.5°	147.4	150.1	153.8	158.6	164.0	170.9	177.8	184.6	191.8	199.3	206.2
155°	152.5	154.5	158.2	161.8	166.8	172.5	178.1	183.8	189.5	195.9	202.2
157.5°	156.9	158.5	161.7	164.7	168.8	173.6	178.1	182.3	187.1	192.6	197.5
160°	159.9	161.2	163.8	166.5	170.2	174.2	178.1	181.5	185.5	190.1	194.4
162.5°	162.2	163.6	165.7	168.1	171.0	174.5	177.9	180.7	184.2	188.0	191.5
165°	165.5	166.2	168.1	169.8	171.8	174.8	177.2	179.2	181.5	184.5	187.2
167.5°	168.2	168.8	170.1	171.4	172.6	174.7	176.7	177.7	179.2	181.1	182.9
170°	169.8	170.2	171.2	171.8	172.9	174.5	176.2	176.8	177.9	179.2	180.9
172.5°	171.2	171.0	172.0	172.4	173.1	174.3	175.4	175.8	176.3	177.3	178.4
175°	172.5	172.2	172.9	172.9	173.1	173.8	174.5	174.2	174.5	174.8	175.9
177.5°	172.9	172.7	173.1	173.1	173.1	173.4	174.0	173.4	173.1	173.4	174.0
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1



TEST NUMBER: P331377-830

CATALOG NUMBER: S122DIP-S865D330U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3	1627.3
2.5°	1687.9	1694.9	1694.9	1695.9	1703.9	1702.9	1702.4
5°	1796.2	1806.9	1808.1	1819.4	1826.8	1824.4	1817.5
7.5°	1898.4	1918.2	1933.2	1941.5	1951.4	1957.6	1954.8
10°	1979.4	2008.2	2025.7	2037.6	2052.0	2062.7	2058.9
12.5°	2053.0	2087.3	2111.3	2131.7	2133.5	2147.2	2138.0
15°	2167.8	2203.9	2207.7	2222.7	2234.7	2233.4	2234.0
17.5°	2205.6	2217.2	2219.6	2220.0	2220.2	2215.7	2206.2
20°	2192.1	2187.7	2177.1	2169.0	2154.6	2152.7	2140.2
22.5°	2128.1	2114.2	2087.5	2069.9	2047.5	2041.6	2038.2
25°	2002.0	1971.3	1928.8	1888.1	1876.9	1855.0	1861.2
27.5°	1829.0	1781.2	1735.1	1702.1	1672.3	1639.5	1648.9
30°	1707.4	1653.6	1588.6	1538.5	1506.7	1475.4	1469.7
32.5°	1562.3	1483.5	1411.0	1366.9	1318.1	1298.3	1276.6
35°	1312.1	1235.2	1163.3	1101.4	1065.7	1038.2	1013.1
37.5°	1087.1	998.5	940.5	890.3	864.6	848.9	852.8
40°	947.5	870.0	827.5	789.3	765.5	754.2	756.8
42.5°	834.4	776.4	741.4	715.2	698.4	692.2	690.7
45°	706.1	673.5	644.8	629.8	621.7	614.8	610.4
47.5°	618.5	592.0	575.8	566.8	559.8	552.7	552.6
50°	566.0	548.5	537.2	527.8	522.3	517.3	521.6
52.5°	525.9	510.0	498.7	490.3	488.2	483.7	483.6
55°	466.6	454.0	445.9	438.4	434.7	432.2	429.0
57.5°	412.6	400.7	393.1	388.4	381.3	378.7	377.8
60°	374.0	364.6	357.1	350.8	347.7	342.7	342.7
62.5°	338.5	329.1	322.1	317.4	312.2	310.2	310.8
65°	287.1	279.6	272.7	267.7	266.5	262.7	263.9
67.5°	239.8	234.8	227.5	224.8	222.4	220.4	218.9
70°	208.3	203.3	199.5	195.8	193.9	193.9	193.9
72.5°	181.7	175.8	173.5	168.7	169.8	167.9	165.9
75°	140.7	137.0	135.1	133.2	130.1	130.1	130.1
77.5°	103.6	102.5	100.2	98.2	97.5	96.8	97.1
80°	80.0	79.5	78.1	78.1	76.9	76.3	75.0
82.5°	61.5	59.9	59.2	58.6	58.4	58.2	58.1
85°	35.1	33.7	33.7	34.4	33.2	33.2	33.7
87.5°	15.6	15.6	15.2	15.2	15.7	15.2	15.2
90°	10.0	10.7	11.0	11.0	11.0	11.0	11.0
92.5°	24.9	22.1	20.1	19.8	18.8	18.9	18.5
95°	66.9	53.0	45.6	41.3	38.6	37.6	38.0
97.5°	166.5	130.5	106.5	90.6	82.4	77.6	74.7
100°	262.8	217.2	176.8	149.2	134.9	125.3	119.2
102.5°	360.5	327.2	284.5	254.4	230.0	217.9	209.8
105°	442.2	446.6	435.6	414.9	394.3	379.9	375.3
107.5°	436.3	470.9	487.0	489.7	488.5	485.6	479.5
110°	417.6	460.2	487.6	501.9	508.2	511.2	510.9



TEST NUMBER: P331377-830

CATALOG NUMBER: S122DIP-S865D330U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	395.5	441.0	472.4	492.3	502.8	508.5	510.3
115°	365.3	409.0	443.3	466.9	482.2	490.9	493.9
117.5°	340.8	380.4	412.6	436.7	452.9	461.9	464.5
120°	328.0	363.4	393.6	417.0	432.6	442.2	445.6
122.5°	317.4	350.8	378.1	399.1	414.5	423.1	425.8
125°	303.4	332.7	357.7	377.0	389.6	397.9	400.7
127.5°	289.8	317.4	340.4	357.3	369.2	376.4	378.5
130°	280.8	307.1	329.0	345.3	356.7	363.4	366.0
132.5°	272.2	296.4	317.1	333.1	344.4	350.5	353.0
135°	258.7	280.8	299.4	313.7	324.7	330.7	332.1
137.5°	248.1	265.5	281.7	294.8	304.3	309.5	311.5
140°	241.1	256.5	271.1	281.7	290.4	295.4	297.4
142.5°	235.0	248.2	260.4	270.5	278.4	282.9	283.2
145°	227.2	237.4	247.1	255.1	260.8	264.1	265.0
147.5°	220.7	228.8	235.8	242.4	246.9	249.2	249.9
150°	216.5	223.5	229.4	234.4	238.5	240.4	240.8
152.5°	213.0	219.0	224.1	228.1	231.5	233.0	233.1
155°	207.5	212.4	216.1	219.8	222.2	223.5	222.8
157.5°	201.9	206.0	209.0	211.5	213.5	214.1	214.1
160°	198.1	201.8	204.2	206.5	208.1	208.5	208.5
162.5°	194.7	197.8	199.6	202.0	203.1	203.4	203.1
165°	189.5	191.8	193.1	194.4	195.9	195.9	195.5
167.5°	184.7	186.3	187.6	188.1	188.9	188.8	188.4
170°	181.8	183.1	183.8	184.2	185.1	184.8	184.2
172.5°	179.2	180.2	180.6	181.0	181.4	181.1	180.7
175°	176.2	176.5	176.8	176.8	177.2	176.8	176.2
177.5°	174.0	174.3	174.3	174.3	174.3	174.0	173.4
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1

(END OF REPORT)