

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331618-940

Luminaire Tested: **S122RDIP-S290D330U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331618-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S290D330U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2089.3 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331618-940

CATALOG NUMBER: S122RDIP-S290D330U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331618-940

CATALOG NUMBER: S122RDIP-S290D330U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	45	44	44	38
2	89	81	76	71	81	75	70	66	62	59	56	51	49	46	41	39	37	32
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	36	34	32	28
4	74	64	56	51	68	59	52	47	50	45	41	41	37	34	33	30	28	24
5	68	57	49	44	62	53	46	41	45	39	35	37	33	30	30	27	25	21
6	63	51	44	38	58	48	41	36	40	35	31	33	29	26	27	24	22	19
7	58	46	39	33	53	43	36	31	37	31	27	31	27	24	25	22	20	17
8	54	42	35	30	50	39	33	28	33	28	24	28	24	21	23	20	18	15
9	51	39	31	26	46	36	29	25	31	26	22	26	22	19	21	18	16	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7227	7227	7227
5°	7254	7136	7175
10°	7199	7020	6960
15°	7116	6812	6614
20°	7002	6515	6189
25°	6885	6178	5772
30°	6721	5830	5243
35°	6564	5454	4776
40°	6403	5063	4234
45°	6215	4624	3747
50°	6023	4182	3265
55°	5827	3704	2806
60°	5596	3203	2328
65°	5337	2690	2120
70°	5032	2219	1950
75°	4648	2021	1822
80°	4100	1804	1655
85°	3223	1426	1426



TEST NUMBER: P331618-940

CATALOG NUMBER: S122RDIP-S290D330U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	2.0
10°-20°	115.0	5.5
20°-30°	161.6	7.7
30°-40°	176.2	8.4
40°-50°	162.0	7.8
50°-60°	127.2	6.1
60°-70°	82.9	4.0
70°-80°	42.8	2.0
80°-90°	12.1	0.6
90°-100°	13.3	0.6
100°-110°	48.7	2.3
110°-120°	130.3	6.2
120°-130°	215.1	10.3
130°-140°	228.7	10.9
140°-150°	212.6	10.2
150°-160°	170.9	8.2
160°-170°	110.1	5.3
170°-180°	37.9	1.8
0°-30°	318.5	15.2
0°-40°	494.7	23.7
0°-60°	783.8	37.5
0°-90°	921.6	44.1
90°-120°	192.3	9.2
90°-150°	848.7	40.6
90°-180°	1168.0	55.9
0°-180°	2089.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	448	448	448	448	448	
5°	448	445	440	444	443	42
15°	426	421	408	400	396	120
25°	386	373	347	331	324	178
35°	333	312	277	252	242	208
45°	272	244	202	175	164	210
55°	207	175	132	108	100	185
65°	140	107	70	57	56	138
75°	74	47	32	30	29	79
85°	17	9	8	8	8	21
90°	0	3	6	7	8	2
95°	19	10	11	13	12	23
105°	88	91	18	21	22	94
115°	166	171	178	51	24	163
125°	234	238	244	246	246	209
135°	290	295	297	300	300	224
145°	336	336	341	343	342	210
155°	370	368	371	373	371	171
165°	390	389	390	391	390	110
175°	399	397	398	400	397	38
180°	398	398	398	398	398	



TEST NUMBER: P331618-940

CATALOG NUMBER: S122RDIP-S290D330U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	449.2	448.9	448.5	448.2	447.8	447.2	446.4	445.7	444.9	444.1	444.8
5°	447.6	447.2	446.7	446.3	445.9	445.0	443.8	442.6	441.5	440.3	441.1
7.5°	443.0	442.5	441.8	441.3	440.8	439.8	438.5	437.0	435.7	434.4	434.5
10°	439.1	438.5	437.8	437.2	436.6	435.3	433.5	431.8	430.0	428.2	427.9
12.5°	434.3	433.5	432.7	431.9	431.1	429.6	427.3	425.0	422.7	420.4	419.9
15°	425.7	424.7	423.7	422.8	421.8	419.7	416.7	413.7	410.5	407.5	405.8
17.5°	415.3	413.8	412.2	410.7	409.2	406.5	402.6	398.7	394.8	390.8	388.8
20°	407.5	405.7	403.9	402.1	400.3	397.2	392.6	388.2	383.7	379.2	376.9
22.5°	399.1	397.1	395.0	393.1	391.0	387.4	382.4	377.3	372.3	367.2	364.3
25°	386.5	383.5	380.7	377.8	375.0	370.5	364.5	358.6	352.7	346.8	343.0
27.5°	371.2	368.1	365.0	361.9	358.6	353.7	347.1	340.4	333.7	327.0	322.7
30°	360.5	357.1	353.7	350.3	346.9	341.5	334.3	327.2	319.9	312.7	308.2
32.5°	350.2	346.2	342.1	338.1	334.1	328.5	321.2	313.8	306.5	299.1	293.9
35°	333.0	328.4	323.8	319.2	314.6	308.4	300.4	292.5	284.6	276.7	271.0
37.5°	315.8	310.8	305.7	300.7	295.6	288.9	280.4	272.0	263.6	255.1	248.9
40°	303.8	298.5	293.0	287.6	282.2	275.2	266.4	257.7	249.0	240.2	233.8
42.5°	291.5	285.8	280.1	274.5	268.8	261.4	252.4	243.3	234.3	225.3	218.7
45°	272.2	266.2	260.1	254.1	248.1	240.3	230.9	221.4	212.0	202.5	196.2
47.5°	253.4	247.0	240.7	234.3	227.8	219.8	210.0	200.3	190.5	180.7	174.4
50°	239.8	233.4	227.0	220.6	214.3	206.1	196.2	186.3	176.4	166.5	160.2
52.5°	226.5	219.8	213.2	206.5	199.8	191.6	181.9	172.3	162.6	152.8	146.9
55°	207.0	200.0	193.0	185.9	178.9	170.6	160.8	151.1	141.3	131.6	126.3
57.5°	187.0	179.8	172.5	165.4	158.2	149.9	140.5	131.3	121.9	112.5	107.5
60°	173.3	166.2	159.0	151.8	144.5	136.3	127.1	117.8	108.5	99.2	94.6
62.5°	160.1	152.9	145.7	138.5	131.3	123.2	114.4	105.6	96.8	87.9	83.6
65°	139.7	132.4	125.2	117.9	110.6	102.9	94.8	86.7	78.6	70.4	67.4
67.5°	120.1	112.9	105.7	98.4	91.2	83.9	76.6	69.4	62.1	54.8	53.3
70°	106.6	99.5	92.5	85.5	78.5	71.9	65.6	59.4	53.2	47.0	46.1
72.5°	93.5	86.9	80.1	73.4	66.6	60.8	55.8	50.8	45.8	40.8	40.0
75°	74.5	68.2	62.0	55.6	49.3	44.7	41.6	38.5	35.5	32.4	31.7
77.5°	55.8	50.3	44.8	39.2	33.7	30.2	28.7	27.3	25.8	24.3	24.0
80°	44.1	39.6	35.0	30.4	25.8	23.0	22.1	21.2	20.3	19.4	19.1
82.5°	33.4	29.9	26.3	22.7	19.2	17.0	16.4	15.8	15.2	14.6	14.4
85°	17.4	15.5	13.6	11.8	9.9	8.7	8.5	8.2	7.9	7.7	7.7
87.5°	5.3	4.8	4.4	3.9	3.5	3.3	3.5	3.6	3.7	3.7	3.7
90°	0.3	1.0	1.7	2.4	3.1	3.7	4.2	4.7	5.3	5.8	6.1
92.5°	5.8	5.8	5.7	5.6	5.5	5.7	5.9	6.2	6.4	6.7	6.9
95°	18.7	16.6	14.5	12.4	10.3	9.5	9.9	10.3	10.8	11.2	11.6
97.5°	37.2	31.2	25.2	19.4	13.4	10.9	11.9	12.9	14.0	15.1	15.3
100°	51.0	42.3	33.4	24.7	16.0	12.0	13.2	14.3	15.3	16.4	16.9
102.5°	66.3	64.4	62.5	60.7	58.9	53.3	44.2	35.1	26.0	16.9	17.6
105°	87.7	89.5	91.5	93.5	95.3	87.6	70.1	52.6	35.0	17.6	18.3
107.5°	112.0	113.6	115.1	116.7	118.2	108.5	87.6	66.6	45.6	24.6	23.9
110°	127.7	129.0	130.5	131.8	133.1	124.5	106.0	87.5	68.9	50.5	44.1



TEST NUMBER: P331618-940

CATALOG NUMBER: S122RDIP-S290D330U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	142.5	143.7	144.9	146.1	147.2	145.5	141.0	136.4	131.8	127.2	103.9
115°	165.8	166.8	168.0	169.1	170.1	171.5	173.1	174.7	176.3	177.9	148.2
117.5°	186.6	187.8	189.0	190.3	191.5	192.6	193.8	194.8	195.9	197.1	189.8
120°	201.8	202.8	203.8	204.7	205.6	206.7	207.9	209.0	210.2	211.3	212.1
122.5°	214.7	215.8	216.8	217.8	218.8	219.9	221.1	222.4	223.7	225.0	225.4
125°	234.4	235.2	236.0	236.9	237.7	238.8	240.0	241.2	242.4	243.6	244.1
127.5°	252.2	253.2	254.0	255.0	255.9	256.8	257.7	258.7	259.6	260.5	261.1
130°	263.5	264.6	265.6	266.6	267.6	268.5	269.2	269.9	270.6	271.3	272.0
132.5°	275.1	275.9	276.8	277.7	278.6	279.3	280.0	280.7	281.4	282.1	282.8
135°	290.1	291.1	292.1	293.1	294.2	295.0	295.5	296.1	296.7	297.3	297.9
137.5°	305.2	305.9	306.7	307.4	308.1	308.8	309.4	310.0	310.8	311.4	312.0
140°	315.1	315.7	316.1	316.6	317.2	317.8	318.5	319.2	319.9	320.6	321.2
142.5°	323.4	323.9	324.3	324.9	325.3	325.9	326.7	327.5	328.3	329.1	329.7
145°	336.4	336.4	336.4	336.3	336.2	336.7	337.8	338.9	340.0	341.1	341.5
147.5°	347.9	347.6	347.3	347.1	346.9	347.2	348.3	349.5	350.5	351.6	351.9
150°	355.2	354.7	354.3	353.8	353.4	353.7	354.7	355.8	356.8	357.8	358.2
152.5°	361.4	361.0	360.4	359.9	359.4	359.6	360.6	361.6	362.6	363.6	363.9
155°	370.5	369.9	369.3	368.7	368.2	368.3	369.1	369.8	370.6	371.3	371.8
157.5°	377.6	377.1	376.6	376.1	375.6	375.7	376.2	376.7	377.3	377.8	378.3
160°	381.7	381.4	380.9	380.6	380.2	380.2	380.6	380.9	381.4	381.7	382.1
162.5°	385.4	385.0	384.7	384.2	383.9	383.9	384.1	384.5	384.9	385.2	385.7
165°	390.4	390.0	389.6	389.2	388.9	388.8	389.0	389.1	389.3	389.5	389.9
167.5°	394.0	393.7	393.3	392.9	392.5	392.4	392.6	392.8	393.0	393.2	393.6
170°	396.2	395.7	395.4	395.0	394.6	394.5	394.6	394.8	394.8	395.0	395.5
172.5°	397.5	397.2	396.7	396.4	396.0	395.8	396.0	396.1	396.3	396.4	396.8
175°	399.3	398.9	398.4	398.0	397.5	397.3	397.5	397.6	397.8	397.9	398.3
177.5°	399.6	399.2	398.9	398.5	398.1	398.1	398.1	398.1	398.1	398.2	398.6
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4



TEST NUMBER: P331618-940

CATALOG NUMBER: S122RDIP-S290D330U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	445.5	446.2	446.9	447.2	447.1	446.9	446.7	446.7
5°	441.9	442.7	443.5	443.8	443.5	443.3	443.0	442.7
7.5°	434.8	435.1	435.2	435.2	434.7	434.2	433.7	433.3
10°	427.7	427.4	427.1	426.7	426.1	425.6	425.1	424.5
12.5°	419.5	418.9	418.5	417.8	416.9	416.0	415.1	414.2
15°	404.1	402.3	400.6	399.4	398.5	397.5	396.6	395.7
17.5°	386.7	384.7	382.7	380.9	379.3	377.8	376.2	374.7
20°	374.7	372.4	370.1	368.0	366.0	364.1	362.1	360.2
22.5°	361.4	358.5	355.6	353.4	351.9	350.4	348.9	347.5
25°	339.4	335.6	332.0	329.5	328.1	326.7	325.4	324.0
27.5°	318.3	314.1	309.8	306.6	304.4	302.3	300.1	298.0
30°	303.5	299.0	294.4	290.9	288.4	286.0	283.6	281.2
32.5°	288.6	283.4	278.1	274.4	272.2	269.8	267.5	265.3
35°	265.4	259.7	254.0	250.1	248.2	246.2	244.2	242.3
37.5°	242.6	236.4	230.2	225.9	223.6	221.3	219.1	216.8
40°	227.5	221.1	214.6	210.3	207.9	205.6	203.2	200.9
42.5°	212.0	205.5	198.9	194.5	192.2	189.9	187.6	185.4
45°	189.8	183.3	177.0	172.7	170.6	168.4	166.2	164.1
47.5°	168.0	161.7	155.3	151.1	149.2	147.2	145.3	143.3
50°	154.1	147.8	141.6	137.6	135.7	133.8	131.9	130.0
52.5°	140.9	134.9	128.9	125.0	123.3	121.5	119.8	118.1
55°	120.8	115.5	110.0	106.5	104.8	103.1	101.4	99.7
57.5°	102.6	97.6	92.7	89.5	88.1	86.7	85.2	83.7
60°	90.1	85.5	80.9	77.8	76.4	75.0	73.6	72.1
62.5°	79.2	74.8	70.4	67.8	66.9	66.1	65.2	64.3
65°	64.4	61.3	58.2	56.5	56.3	56.0	55.7	55.5
67.5°	52.0	50.6	49.1	48.3	48.0	47.7	47.4	47.2
70°	45.2	44.3	43.4	42.8	42.4	42.0	41.6	41.3
72.5°	39.3	38.5	37.8	37.4	37.1	36.9	36.6	36.5
75°	31.1	30.5	29.9	29.5	29.4	29.3	29.2	29.2
77.5°	23.5	23.2	22.8	22.6	22.5	22.3	22.2	22.0
80°	18.7	18.4	18.0	17.8	17.8	17.8	17.8	17.8
82.5°	14.2	13.9	13.7	13.6	13.6	13.6	13.6	13.6
85°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
87.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.8	3.8
90°	6.4	6.7	7.0	7.3	7.4	7.5	7.7	7.8
92.5°	7.0	7.2	7.3	7.5	7.6	7.7	7.7	7.8
95°	11.9	12.2	12.5	12.7	12.6	12.5	12.5	12.4
97.5°	15.6	15.8	16.1	16.2	16.3	16.4	16.5	16.6
100°	17.5	18.0	18.5	18.8	18.9	19.1	19.2	19.4
102.5°	18.2	18.9	19.5	20.0	20.2	20.3	20.5	20.7
105°	19.0	19.7	20.4	20.9	21.1	21.4	21.7	21.9
107.5°	23.2	22.5	21.8	21.5	21.8	22.0	22.3	22.6
110°	37.6	31.2	24.8	21.8	22.0	22.3	22.6	22.7



TEST NUMBER: P331618-940

CATALOG NUMBER: S122RDIP-S290D330U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	80.5	57.2	33.8	22.2	22.4	22.6	22.8	23.0
115°	118.6	88.9	59.2	42.1	37.5	32.9	28.3	23.6
117.5°	182.7	175.5	168.4	157.2	142.0	126.9	111.7	96.6
120°	212.9	213.7	214.4	210.4	201.8	193.1	184.5	175.8
122.5°	225.9	226.3	226.8	226.1	224.5	222.8	221.1	219.5
125°	244.5	245.0	245.4	245.8	245.9	246.1	246.3	246.5
127.5°	261.8	262.4	263.1	263.4	263.5	263.5	263.5	263.6
130°	272.7	273.4	274.1	274.5	274.4	274.3	274.3	274.2
132.5°	283.4	283.9	284.5	284.8	284.7	284.7	284.6	284.5
135°	298.5	299.2	299.8	300.1	300.0	299.8	299.7	299.5
137.5°	312.6	313.3	313.9	314.1	313.9	313.7	313.4	313.3
140°	321.7	322.4	322.9	323.1	322.7	322.4	322.1	321.7
142.5°	330.2	330.7	331.3	331.4	331.0	330.7	330.4	330.0
145°	342.0	342.4	342.9	343.0	342.6	342.3	342.0	341.6
147.5°	352.2	352.6	352.9	352.9	352.7	352.4	352.1	351.9
150°	358.6	358.9	359.4	359.4	359.1	358.7	358.4	358.1
152.5°	364.4	364.7	365.1	365.1	364.6	364.3	363.8	363.4
155°	372.1	372.5	372.9	372.8	372.3	371.8	371.3	370.8
157.5°	378.7	379.2	379.5	379.5	379.0	378.5	378.0	377.6
160°	382.5	382.9	383.3	383.3	382.8	382.4	381.9	381.5
162.5°	386.0	386.5	386.9	386.9	386.3	385.8	385.2	384.7
165°	390.4	390.8	391.3	391.3	390.8	390.4	389.9	389.5
167.5°	394.0	394.5	394.9	394.8	394.3	393.7	393.2	392.5
170°	395.9	396.4	396.8	396.7	396.2	395.6	395.0	394.4
172.5°	397.3	397.7	398.1	398.1	397.5	397.0	396.4	395.8
175°	398.8	399.2	399.7	399.6	399.0	398.3	397.6	397.0
177.5°	399.0	399.3	399.7	399.6	399.1	398.7	398.2	397.8
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4

(END OF REPORT)