

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331669-940

Luminaire Tested: **S122RDIP-S485D1080U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331669-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S485D1080U940-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5498.6 lumens  
Efficiency: N/A  
Efficacy: 111.3 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331669-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331669-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	33	33	26
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	29	28	23
3	79	70	63	58	70	63	57	53	50	46	43	39	36	34	28	26	25	20
4	72	62	55	49	65	56	50	45	45	41	37	35	32	29	25	23	22	18
5	66	55	48	42	59	50	44	39	40	36	32	31	28	26	23	21	19	16
6	61	50	42	37	55	45	39	34	37	32	28	28	25	23	21	19	17	14
7	57	45	38	32	51	41	34	30	33	29	25	26	23	20	19	17	16	13
8	52	41	34	29	47	37	31	27	30	26	22	24	21	18	18	16	14	12
9	49	37	30	26	44	34	28	24	28	23	20	22	19	16	17	14	13	11
10	46	34	27	23	41	31	25	21	26	21	18	20	17	15	15	13	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15474	15474	15474	15474
5°	17280	15571	13807	15571
10°	19174	15462	11968	15462
15°	20117	15234	9429	15234
20°	17438	14899	8158	14899
25°	11437	14439	7285	14439
30°	7700	13882	6594	13882
35°	6236	13180	5947	13180
40°	5545	12416	5503	12416
45°	5019	11520	4912	11520
50°	4567	10630	4549	10630
55°	4293	9647	4236	9647
60°	3591	8741	3549	8741
65°	3030	7939	3435	7939
70°	2799	7091	3238	7091
75°	2620	6170	2994	6170
80°	2408	5077	2659	5077
85°	2205	4020	2353	4020



TEST NUMBER: P331669-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.8	1.7
10°-20°	253.1	4.6
20°-30°	326.2	5.9
30°-40°	310.0	5.6
40°-50°	265.6	4.8
50°-60°	202.2	3.7
60°-70°	127.8	2.3
70°-80°	63.8	1.2
80°-90°	19.8	0.4
90°-100°	43.7	0.8
100°-110°	160.2	2.9
110°-120°	428.4	7.8
120°-130°	707.1	12.9
130°-140°	752.0	13.7
140°-150°	699.0	12.7
150°-160°	562.0	10.2
160°-170°	362.1	6.6
170°-180°	124.6	2.3
0°-30°	670.2	12.2
0°-40°	980.2	17.8
0°-60°	1448.0	26.3
0°-90°	1659.5	30.2
90°-120°	632.3	11.5
90°-150°	2790.4	50.7
90°-180°	3839.0	69.8
0°-180°	5498.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	958	958	958	958	958	
5°	1066	961	852	961	1066	105
15°	1204	911	564	911	1204	325
25°	642	810	409	810	642	305
35°	316	669	302	669	316	202
45°	220	504	215	504	220	170
55°	152	343	150	343	152	134
65°	79	208	90	208	79	81
75°	42	99	48	99	42	45
85°	12	22	13	22	12	14
90°	26	1	26	1	26	12
95°	41	62	41	62	41	38
105°	72	288	72	288	72	75
115°	78	545	78	545	78	195
125°	810	771	810	771	810	701
135°	985	954	985	954	985	759
145°	1123	1106	1123	1106	1123	702
155°	1219	1218	1219	1218	1219	563
165°	1281	1284	1281	1284	1281	362
175°	1305	1313	1305	1313	1305	124
180°	1310	1310	1310	1310	1310	



TEST NUMBER: P331669-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	997.3	998.1	998.9	997.0	997.0	995.4	991.9	989.3	981.8	980.7	980.7
5°	1066.2	1065.6	1066.9	1062.6	1056.6	1055.3	1048.9	1040.6	1032.0	1022.3	1020.3
7.5°	1134.9	1133.9	1131.2	1130.4	1125.9	1115.8	1105.6	1094.8	1080.4	1066.3	1059.3
10°	1169.5	1180.4	1173.8	1162.2	1164.5	1148.9	1140.5	1126.2	1114.2	1093.2	1088.6
12.5°	1203.5	1207.9	1205.8	1199.2	1196.2	1185.4	1174.1	1161.6	1139.5	1120.7	1104.3
15°	1203.5	1209.8	1211.5	1209.4	1211.1	1210.4	1204.4	1194.1	1174.8	1154.1	1136.2
17.5°	1114.6	1119.0	1129.9	1137.3	1146.7	1166.4	1176.1	1179.9	1177.0	1165.2	1152.5
20°	1014.9	1007.6	1038.3	1053.9	1067.3	1100.5	1129.2	1140.1	1157.8	1157.5	1154.1
22.5°	873.8	875.5	904.6	923.1	962.1	995.3	1028.0	1069.3	1103.5	1126.1	1139.2
25°	642.0	654.7	683.7	708.9	752.2	814.2	870.5	935.8	997.3	1046.0	1092.3
27.5°	482.1	483.1	506.0	529.5	555.2	605.9	676.8	754.7	842.6	915.0	998.4
30°	413.0	410.9	420.6	434.9	456.9	496.1	549.5	626.1	713.6	822.9	920.1
32.5°	363.9	364.0	371.3	381.9	400.1	426.6	463.2	525.3	608.1	715.5	829.5
35°	316.4	316.0	321.4	329.0	336.6	353.7	378.6	411.3	468.2	568.5	685.0
37.5°	282.2	283.7	286.3	291.1	299.5	309.0	324.0	345.9	386.5	445.8	543.7
40°	263.1	263.8	267.4	271.4	276.4	283.7	296.0	313.7	343.3	390.6	462.2
42.5°	245.5	246.1	248.8	252.4	256.4	263.8	273.9	289.2	313.3	350.1	409.2
45°	219.8	219.8	222.1	223.7	228.1	234.8	243.1	255.7	272.4	299.7	339.0
47.5°	195.6	195.7	197.2	200.1	202.9	208.0	216.2	226.6	238.7	259.8	293.4
50°	181.8	182.2	183.2	185.5	187.2	191.8	198.1	207.1	219.8	236.1	264.0
52.5°	170.6	170.4	171.7	172.7	173.8	177.2	181.9	189.8	201.2	215.3	238.5
55°	152.5	151.1	153.2	154.8	155.9	157.2	159.8	164.9	174.5	186.5	203.8
57.5°	129.8	129.3	130.7	132.2	135.4	139.0	141.2	144.5	149.5	158.0	175.2
60°	111.2	111.2	114.2	115.2	118.9	123.5	128.2	130.9	135.9	141.5	154.2
62.5°	94.7	95.0	96.4	97.4	99.4	105.1	111.7	117.5	122.3	127.7	136.1
65°	79.3	79.9	79.9	80.6	81.9	83.3	85.9	90.6	98.9	106.6	112.9
67.5°	67.2	67.5	67.7	68.3	68.7	70.1	71.2	73.3	75.2	82.5	90.3
70°	59.3	60.3	59.9	60.6	60.9	61.6	63.0	63.9	67.0	68.6	73.3
72.5°	51.8	52.5	52.5	52.9	53.8	53.9	54.9	55.9	57.9	59.3	61.8
75°	42.0	41.6	42.0	42.6	43.0	43.2	43.2	44.6	45.7	47.0	48.6
77.5°	32.4	32.7	32.6	32.7	32.7	33.3	33.3	33.9	34.9	35.6	36.4
80°	25.9	26.3	25.9	26.3	26.7	26.9	26.7	26.9	28.0	28.6	28.6
82.5°	20.2	20.2	20.4	20.4	20.5	20.6	21.0	21.1	21.8	21.7	21.9
85°	11.9	11.7	11.7	11.7	11.9	12.3	11.9	11.9	12.3	12.3	12.3
87.5°	9.4	9.5	9.5	9.4	9.3	9.2	8.9	9.0	8.6	8.6	8.0
90°	25.6	25.1	24.8	24.3	23.9	23.2	22.1	21.0	20.0	19.0	17.3
92.5°	25.6	25.3	25.1	24.9	24.6	24.2	23.6	23.1	22.6	22.0	21.1
95°	40.8	40.9	41.2	41.4	41.6	41.2	40.1	39.1	38.0	37.0	35.5
97.5°	54.4	54.1	53.9	53.7	53.4	52.9	52.0	51.2	50.3	49.5	46.1
100°	63.5	63.1	62.7	62.2	61.8	60.8	59.1	57.4	55.7	54.0	50.5
102.5°	68.0	67.5	66.9	66.3	65.7	64.3	62.2	59.9	57.8	55.6	85.5
105°	72.1	71.2	70.4	69.6	68.7	67.1	64.7	62.4	60.1	57.8	115.3
107.5°	74.1	73.3	72.4	71.6	70.8	71.5	73.8	76.2	78.6	81.0	149.9
110°	74.9	74.0	73.2	72.3	71.5	81.6	102.7	123.8	144.8	165.9	226.8



TEST NUMBER: P331669-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	75.6	75.0	74.3	73.7	72.9	111.0	187.9	264.7	341.6	418.4	433.5
115°	77.8	92.9	108.1	123.2	138.4	194.7	292.3	389.8	487.3	584.9	579.6
117.5°	317.4	367.2	417.1	466.9	516.7	553.5	577.0	600.7	624.2	647.8	644.2
120°	578.3	606.6	635.1	663.5	692.0	705.0	702.4	699.9	697.3	694.8	691.1
122.5°	721.6	727.1	732.6	738.2	743.6	745.6	744.1	742.6	741.1	739.6	735.5
125°	810.5	809.9	809.2	808.6	808.0	806.9	805.4	804.0	802.5	801.0	797.0
127.5°	866.6	866.5	866.4	866.2	866.1	865.0	862.8	860.7	858.5	856.4	853.4
130°	901.5	901.7	901.9	902.1	902.3	901.3	898.9	896.6	894.3	892.0	889.7
132.5°	935.6	935.9	936.0	936.2	936.5	935.6	933.6	931.6	929.6	927.6	925.3
135°	984.9	985.3	985.7	986.1	986.6	985.7	983.6	981.5	979.5	977.3	975.4
137.5°	1029.8	1030.6	1031.3	1032.0	1032.7	1032.0	1029.9	1027.9	1025.8	1023.8	1021.6
140°	1057.9	1058.9	1060.0	1061.0	1062.1	1061.7	1059.8	1057.9	1056.0	1054.1	1051.8
142.5°	1085.2	1086.3	1087.3	1088.3	1089.4	1089.0	1087.4	1085.6	1083.9	1082.2	1079.5
145°	1123.3	1124.4	1125.4	1126.5	1127.5	1127.3	1125.8	1124.4	1122.8	1121.4	1117.8
147.5°	1156.8	1157.7	1158.6	1159.5	1160.4	1160.3	1159.2	1158.1	1157.0	1155.9	1152.4
150°	1177.3	1178.4	1179.5	1180.4	1181.5	1181.4	1180.2	1178.9	1177.7	1176.3	1173.0
152.5°	1194.8	1196.1	1197.6	1198.9	1200.3	1200.4	1199.2	1197.8	1196.6	1195.3	1192.1
155°	1219.1	1220.8	1222.4	1224.1	1225.7	1226.0	1224.8	1223.4	1222.2	1220.9	1218.4
157.5°	1241.2	1242.9	1244.5	1246.2	1247.8	1247.9	1246.4	1245.0	1243.6	1242.2	1240.4
160°	1254.1	1255.6	1257.0	1258.6	1260.0	1260.1	1258.8	1257.6	1256.3	1255.1	1253.8
162.5°	1264.7	1266.5	1268.4	1270.2	1271.9	1272.2	1270.7	1269.3	1267.8	1266.4	1265.3
165°	1280.7	1282.1	1283.6	1285.0	1286.6	1286.6	1285.0	1283.6	1282.1	1280.7	1280.1
167.5°	1290.7	1292.6	1294.5	1296.4	1298.2	1298.5	1297.0	1295.6	1294.1	1292.6	1292.0
170°	1296.7	1298.7	1300.6	1302.4	1304.3	1304.6	1303.1	1301.6	1300.1	1298.7	1298.2
172.5°	1301.3	1303.2	1305.1	1307.0	1308.9	1309.1	1307.6	1306.2	1304.7	1303.2	1302.8
175°	1305.3	1307.4	1309.5	1311.6	1313.8	1314.0	1312.6	1311.1	1309.7	1308.1	1307.7
177.5°	1307.8	1309.3	1310.8	1312.3	1313.8	1314.0	1312.8	1311.6	1310.5	1309.3	1309.1
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331669-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	981.2	979.2	977.3	972.5	970.1	964.7	963.9	963.7	956.8	950.1	948.2
5°	1014.9	1009.7	1001.7	992.3	982.7	972.7	966.0	960.7	947.4	934.7	927.4
7.5°	1048.9	1037.5	1023.7	1006.0	991.3	974.8	962.6	951.5	932.6	914.5	902.3
10°	1074.2	1055.6	1037.3	1013.0	994.0	975.4	958.1	943.1	921.8	897.8	880.7
12.5°	1089.9	1069.4	1044.2	1020.5	995.9	972.1	949.0	929.7	904.7	879.9	859.7
15°	1111.3	1089.2	1058.6	1024.7	993.0	962.1	935.4	911.4	878.8	849.2	824.5
17.5°	1128.6	1098.3	1065.4	1026.2	989.5	950.2	915.9	885.2	848.9	813.2	784.2
20°	1134.2	1104.2	1066.2	1027.0	983.6	937.4	900.4	867.1	828.1	789.2	755.9
22.5°	1130.7	1107.4	1065.1	1018.2	973.8	925.4	883.7	845.0	801.8	762.1	723.4
25°	1107.2	1099.2	1059.3	1008.0	957.3	901.1	852.8	810.5	761.3	718.6	676.6
27.5°	1052.4	1069.7	1044.9	990.2	934.0	873.6	819.4	771.2	720.1	672.1	630.3
30°	999.7	1039.3	1028.6	978.0	915.1	855.8	794.9	744.6	690.0	640.7	599.4
32.5°	927.5	992.9	1003.4	961.0	895.9	830.7	766.9	716.8	659.9	607.9	567.7
35°	812.5	910.4	955.4	928.4	863.1	792.9	726.9	668.7	611.4	560.1	520.1
37.5°	675.4	808.7	883.7	885.6	825.6	752.6	680.8	622.9	564.3	514.0	470.7
40°	586.4	730.9	828.5	850.2	799.5	720.6	648.0	589.1	531.8	482.5	432.9
42.5°	506.5	650.5	770.4	808.1	767.9	689.5	616.6	555.0	499.3	452.6	402.0
45°	409.6	535.5	667.6	734.9	712.7	640.0	563.1	504.5	452.2	411.9	363.3
47.5°	345.5	434.3	562.1	653.2	652.7	586.5	510.9	454.7	406.2	368.5	329.0
50°	309.0	386.3	494.5	597.7	606.4	550.8	478.8	423.2	378.0	338.3	306.7
52.5°	276.3	339.9	437.2	536.2	560.8	512.6	442.9	391.6	347.6	311.1	284.0
55°	233.4	282.7	356.7	449.2	486.5	452.5	390.6	342.7	307.0	276.4	253.1
57.5°	197.4	234.4	293.7	368.3	411.7	390.3	339.3	300.3	269.8	242.1	223.7
60°	174.9	205.1	255.4	317.7	365.6	350.6	307.0	270.7	244.8	220.8	203.5
62.5°	153.6	179.6	222.7	273.2	317.2	310.9	275.4	244.9	222.1	200.3	185.7
65°	123.5	142.5	176.1	215.8	251.1	254.0	228.5	207.8	187.4	170.1	157.2
67.5°	98.4	110.8	134.5	167.8	194.3	203.8	188.1	172.3	156.1	142.8	131.5
70°	82.9	92.9	110.2	137.2	161.5	171.5	162.5	150.2	136.2	125.2	115.6
72.5°	67.2	77.0	89.7	109.5	130.4	141.2	138.0	129.1	117.8	108.7	99.6
75°	50.6	53.6	62.2	75.6	91.9	101.2	103.5	98.9	89.9	82.9	77.6
77.5°	37.5	39.2	43.3	50.4	61.0	69.3	72.8	72.2	66.0	62.0	57.0
80°	30.0	30.9	33.0	35.9	44.0	52.3	54.6	54.6	50.3	48.6	43.6
82.5°	22.7	23.5	24.7	26.4	30.1	37.4	39.9	40.5	37.7	35.6	31.7
85°	13.0	12.7	13.3	14.4	15.0	16.9	21.0	21.7	21.0	18.3	17.3
87.5°	7.7	7.6	7.2	6.6	6.3	6.2	7.0	7.9	7.3	7.0	6.9
90°	15.6	13.9	12.2	10.3	7.9	5.6	3.3	1.0	3.3	5.6	7.9
92.5°	20.3	19.4	18.6	18.3	18.5	18.7	18.9	19.2	18.9	18.7	18.5
95°	34.1	32.5	31.0	33.8	40.8	47.7	54.7	61.6	54.7	47.7	40.8
97.5°	42.6	39.2	35.8	44.0	63.5	83.1	102.7	122.3	102.7	83.1	63.5
100°	46.9	43.2	39.7	52.3	81.2	110.0	138.9	167.8	138.9	110.0	81.2
102.5°	115.5	145.4	175.4	193.4	199.5	205.6	211.7	217.8	211.7	205.6	199.5
105°	172.8	230.3	287.8	313.4	307.1	300.8	294.5	288.2	294.5	300.8	307.1
107.5°	218.9	287.8	356.9	388.8	383.6	378.5	373.4	368.4	373.4	378.5	383.6
110°	287.7	348.5	409.4	437.7	433.2	428.8	424.4	419.9	424.4	428.8	433.2





TEST NUMBER: P331669-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	448.5	463.5	478.6	484.1	480.2	476.3	472.4	468.5	472.4	476.3	480.2
115°	574.4	569.1	563.8	559.4	555.8	552.2	548.7	545.1	548.7	552.2	555.8
117.5°	640.6	636.9	633.3	629.5	625.5	621.5	617.5	613.5	617.5	621.5	625.5
120°	687.2	683.5	679.7	676.2	673.1	669.9	666.7	663.5	666.7	669.9	673.1
122.5°	731.3	727.2	723.1	719.3	716.0	712.7	709.4	706.1	709.4	712.7	716.0
125°	793.0	789.0	785.0	781.6	778.9	776.1	773.4	770.7	773.4	776.1	778.9
127.5°	850.3	847.4	844.4	841.4	838.4	835.4	832.3	829.3	832.3	835.4	838.4
130°	887.3	885.0	882.7	879.9	876.6	873.2	869.8	866.4	869.8	873.2	876.6
132.5°	923.0	920.7	918.4	915.8	912.9	910.1	907.2	904.3	907.2	910.1	912.9
135°	973.5	971.6	969.7	967.1	963.8	960.4	957.0	953.6	957.0	960.4	963.8
137.5°	1019.5	1017.4	1015.1	1012.9	1010.6	1008.2	1005.8	1003.4	1005.8	1008.2	1010.6
140°	1049.5	1047.1	1044.8	1042.9	1041.2	1039.5	1037.8	1036.1	1037.8	1039.5	1041.2
142.5°	1076.8	1074.2	1071.6	1069.4	1067.9	1066.4	1064.9	1063.4	1064.9	1066.4	1067.9
145°	1114.2	1110.6	1107.1	1105.4	1105.6	1105.8	1106.0	1106.3	1106.0	1105.8	1105.6
147.5°	1148.8	1145.3	1141.7	1140.4	1141.2	1142.0	1142.8	1143.6	1142.8	1142.0	1141.2
150°	1169.7	1166.3	1162.9	1162.0	1163.4	1164.9	1166.4	1167.9	1166.4	1164.9	1163.4
152.5°	1188.9	1185.7	1182.5	1181.8	1183.4	1185.0	1186.7	1188.3	1186.7	1185.0	1183.4
155°	1215.8	1213.4	1210.9	1210.5	1212.4	1214.3	1216.2	1218.1	1216.2	1214.3	1212.4
157.5°	1238.6	1236.9	1235.1	1235.0	1236.6	1238.2	1239.8	1241.4	1239.8	1238.2	1236.6
160°	1252.5	1251.2	1250.0	1250.0	1251.2	1252.5	1253.8	1255.1	1253.8	1252.5	1251.2
162.5°	1264.3	1263.1	1262.0	1262.1	1263.4	1264.6	1266.0	1267.2	1266.0	1264.6	1263.4
165°	1279.4	1278.7	1278.1	1278.4	1279.7	1280.9	1282.2	1283.5	1282.2	1280.9	1279.7
167.5°	1291.4	1290.8	1290.2	1290.6	1291.8	1293.1	1294.4	1295.7	1294.4	1293.1	1291.8
170°	1297.8	1297.4	1297.0	1297.4	1298.7	1299.9	1301.2	1302.4	1301.2	1299.9	1298.7
172.5°	1302.3	1302.0	1301.5	1302.0	1303.2	1304.5	1305.7	1307.0	1305.7	1304.5	1303.2
175°	1307.3	1306.9	1306.4	1307.0	1308.5	1309.9	1311.4	1312.9	1311.4	1309.9	1308.5
177.5°	1308.9	1308.8	1308.6	1309.1	1310.3	1311.4	1312.7	1313.8	1312.7	1311.4	1310.3
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331669-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	944.8	942.9	939.4	934.2	930.9	925.3	921.6	923.7	924.3	923.7	923.2
5°	919.4	912.4	902.8	893.4	884.8	875.5	870.1	867.8	863.1	860.5	859.2
7.5°	888.7	876.6	863.0	846.8	832.9	818.5	811.1	807.4	797.9	792.7	788.2
10°	865.8	846.8	833.1	811.8	798.9	779.9	766.9	767.2	754.2	746.9	741.5
12.5°	840.5	819.7	796.9	777.8	759.7	744.5	728.8	722.5	708.6	701.6	687.2
15°	798.5	774.2	750.3	724.2	706.0	682.3	659.7	632.0	609.8	590.4	585.1
17.5°	752.7	722.6	698.6	668.1	636.7	596.9	570.7	554.6	541.2	531.0	523.4
20°	721.3	690.6	665.0	619.0	576.8	549.7	530.5	518.2	504.2	493.2	487.1
22.5°	688.2	656.3	621.3	570.0	537.1	515.4	498.2	484.0	474.6	466.0	460.6
25°	641.3	606.4	548.8	513.4	486.9	464.2	452.2	443.5	433.5	421.9	416.6
27.5°	591.8	536.2	494.8	468.6	443.2	428.5	417.7	404.7	395.8	390.6	385.0
30°	554.7	499.2	466.9	438.2	420.3	403.9	391.3	384.0	375.3	366.3	362.7
32.5°	513.4	469.0	438.1	414.3	396.0	382.1	372.1	360.3	354.0	348.5	340.8
35°	462.2	428.6	400.3	380.9	363.6	352.3	340.6	333.7	322.4	317.7	314.7
37.5°	418.7	389.6	368.5	348.1	334.4	321.9	314.8	303.6	298.7	292.2	285.9
40°	394.2	365.6	345.4	328.7	313.3	304.0	295.1	286.1	278.7	275.7	268.0
42.5°	369.3	345.9	325.6	307.4	297.1	287.2	275.9	269.3	261.6	256.8	252.1
45°	334.7	314.1	296.7	281.7	270.4	260.1	252.7	241.7	237.5	227.7	223.7
47.5°	304.3	285.1	268.6	254.3	243.3	236.6	225.9	217.2	210.4	204.4	199.3
50°	282.7	266.7	250.7	238.1	228.1	218.5	207.5	203.1	192.4	189.5	186.5
52.5°	263.0	247.8	233.2	220.8	210.8	201.4	191.7	186.1	178.9	175.8	173.7
55°	235.4	220.8	206.8	195.8	185.8	176.1	170.1	163.2	159.8	157.5	154.8
57.5°	207.7	194.6	183.8	172.7	162.6	155.0	148.0	143.8	140.4	137.3	134.1
60°	190.1	177.5	167.8	157.5	147.2	140.9	135.5	130.5	126.5	121.9	120.6
62.5°	171.5	160.4	151.6	141.5	132.5	126.7	121.7	117.0	112.2	105.4	103.5
65°	145.9	137.2	127.9	119.6	111.6	105.9	98.5	93.3	91.2	90.6	90.2
67.5°	122.7	114.5	106.5	98.0	90.7	85.4	81.7	80.9	79.5	79.1	78.2
70°	107.2	99.6	91.6	83.6	76.6	75.6	74.3	72.9	71.2	70.6	69.9
72.5°	93.4	85.4	77.5	71.1	68.0	66.8	65.5	64.1	63.0	62.3	62.0
75°	71.6	64.3	58.9	56.6	54.9	53.9	52.0	50.9	50.3	49.3	49.0
77.5°	51.5	47.4	44.9	43.5	41.7	40.7	39.6	38.5	37.8	37.6	37.1
80°	39.3	37.3	35.7	33.6	33.0	31.7	31.3	30.3	30.7	29.6	29.6
82.5°	30.5	28.0	26.6	25.7	25.0	23.9	23.5	23.1	23.2	22.5	22.5
85°	15.7	15.0	14.4	13.6	13.6	12.7	13.0	12.7	12.7	11.9	11.7
87.5°	7.1	7.2	7.0	7.4	7.8	7.8	8.0	7.9	8.1	8.4	8.2
90°	10.3	12.2	13.9	15.6	17.3	19.0	20.0	21.0	22.1	23.2	23.9
92.5°	18.3	18.6	19.4	20.3	21.1	22.0	22.6	23.1	23.6	24.2	24.6
95°	33.8	31.0	32.5	34.1	35.5	37.0	38.0	39.1	40.1	41.2	41.6
97.5°	44.0	35.8	39.2	42.6	46.1	49.5	50.3	51.2	52.0	52.9	53.4
100°	52.3	39.7	43.2	46.9	50.5	54.0	55.7	57.4	59.1	60.8	61.8
102.5°	193.4	175.4	145.4	115.5	85.5	55.6	57.8	59.9	62.2	64.3	65.7
105°	313.4	287.8	230.3	172.8	115.3	57.8	60.1	62.4	64.7	67.1	68.7
107.5°	388.8	356.9	287.8	218.9	149.9	81.0	78.6	76.2	73.8	71.5	70.8
110°	437.7	409.4	348.5	287.7	226.8	165.9	144.8	123.8	102.7	81.6	71.5



TEST NUMBER: P331669-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	484.1	478.6	463.5	448.5	433.5	418.4	341.6	264.7	187.9	111.0	72.9
115°	559.4	563.8	569.1	574.4	579.6	584.9	487.3	389.8	292.3	194.7	138.4
117.5°	629.5	633.3	636.9	640.6	644.2	647.8	624.2	600.7	577.0	553.5	516.7
120°	676.2	679.7	683.5	687.2	691.1	694.8	697.3	699.9	702.4	705.0	692.0
122.5°	719.3	723.1	727.2	731.3	735.5	739.6	741.1	742.6	744.1	745.6	743.6
125°	781.6	785.0	789.0	793.0	797.0	801.0	802.5	804.0	805.4	806.9	808.0
127.5°	841.4	844.4	847.4	850.3	853.4	856.4	858.5	860.7	862.8	865.0	866.1
130°	879.9	882.7	885.0	887.3	889.7	892.0	894.3	896.6	898.9	901.3	902.3
132.5°	915.8	918.4	920.7	923.0	925.3	927.6	929.6	931.6	933.6	935.6	936.5
135°	967.1	969.7	971.6	973.5	975.4	977.3	979.5	981.5	983.6	985.7	986.6
137.5°	1012.9	1015.1	1017.4	1019.5	1021.6	1023.8	1025.8	1027.9	1029.9	1032.0	1032.7
140°	1042.9	1044.8	1047.1	1049.5	1051.8	1054.1	1056.0	1057.9	1059.8	1061.7	1062.1
142.5°	1069.4	1071.6	1074.2	1076.8	1079.5	1082.2	1083.9	1085.6	1087.4	1089.0	1089.4
145°	1105.4	1107.1	1110.6	1114.2	1117.8	1121.4	1122.8	1124.4	1125.8	1127.3	1127.5
147.5°	1140.4	1141.7	1145.3	1148.8	1152.4	1155.9	1157.0	1158.1	1159.2	1160.3	1160.4
150°	1162.0	1162.9	1166.3	1169.7	1173.0	1176.3	1177.7	1178.9	1180.2	1181.4	1181.5
152.5°	1181.8	1182.5	1185.7	1188.9	1192.1	1195.3	1196.6	1197.8	1199.2	1200.4	1200.3
155°	1210.5	1210.9	1213.4	1215.8	1218.4	1220.9	1222.2	1223.4	1224.8	1226.0	1225.7
157.5°	1235.0	1235.1	1236.9	1238.6	1240.4	1242.2	1243.6	1245.0	1246.4	1247.9	1247.8
160°	1250.0	1250.0	1251.2	1252.5	1253.8	1255.1	1256.3	1257.6	1258.8	1260.1	1260.0
162.5°	1262.1	1262.0	1263.1	1264.3	1265.3	1266.4	1267.8	1269.3	1270.7	1272.2	1271.9
165°	1278.4	1278.1	1278.7	1279.4	1280.1	1280.7	1282.1	1283.6	1285.0	1286.6	1286.6
167.5°	1290.6	1290.2	1290.8	1291.4	1292.0	1292.6	1294.1	1295.6	1297.0	1298.5	1298.2
170°	1297.4	1297.0	1297.4	1297.8	1298.2	1298.7	1300.1	1301.6	1303.1	1304.6	1304.3
172.5°	1302.0	1301.5	1302.0	1302.3	1302.8	1303.2	1304.7	1306.2	1307.6	1309.1	1308.9
175°	1307.0	1306.4	1306.9	1307.3	1307.7	1308.1	1309.7	1311.1	1312.6	1314.0	1313.8
177.5°	1309.1	1308.6	1308.8	1308.9	1309.1	1309.3	1310.5	1311.6	1312.8	1314.0	1313.8
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331669-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	920.2	920.8	920.0	920.5	920.0	920.8	920.2	923.2	923.7	924.3	923.7
5°	857.5	853.5	852.8	851.9	852.8	853.5	857.5	859.2	860.5	863.1	867.8
7.5°	782.5	781.9	780.2	777.8	780.2	781.9	782.5	788.2	792.7	797.9	807.4
10°	734.2	732.6	732.3	730.0	732.3	732.6	734.2	741.5	746.9	754.2	767.2
12.5°	677.8	667.1	665.9	660.1	665.9	667.1	677.8	687.2	701.6	708.6	722.5
15°	577.1	575.1	568.5	564.1	568.5	575.1	577.1	585.1	590.4	609.8	632.0
17.5°	519.5	513.0	511.0	510.1	511.0	513.0	519.5	523.4	531.0	541.2	554.6
20°	482.5	476.5	475.5	474.8	475.5	476.5	482.5	487.1	493.2	504.2	518.2
22.5°	456.9	450.7	448.1	446.1	448.1	450.7	456.9	460.6	466.0	474.6	484.0
25°	413.2	410.9	409.6	408.9	409.6	410.9	413.2	416.6	421.9	433.5	443.5
27.5°	379.1	374.0	372.9	371.2	372.9	374.0	379.1	385.0	390.6	395.8	404.7
30°	359.6	357.9	355.6	353.7	355.6	357.9	359.6	362.7	366.3	375.3	384.0
32.5°	336.7	335.4	333.2	332.3	333.2	335.4	336.7	340.8	348.5	354.0	360.3
35°	311.4	306.7	304.7	301.7	304.7	306.7	311.4	314.7	317.7	322.4	333.7
37.5°	284.5	282.0	279.3	280.3	279.3	282.0	284.5	285.9	292.2	298.7	303.6
40°	263.8	262.1	261.4	261.1	261.4	262.1	263.8	268.0	275.7	278.7	286.1
42.5°	247.2	242.6	240.9	240.9	240.9	242.6	247.2	252.1	256.8	261.6	269.3
45°	222.1	217.8	214.8	215.1	214.8	217.8	222.1	223.7	227.7	237.5	241.7
47.5°	196.4	196.3	194.4	195.0	194.4	196.3	196.4	199.3	204.4	210.4	217.2
50°	184.1	182.2	180.8	181.1	180.8	182.2	184.1	186.5	189.5	192.4	203.1
52.5°	172.5	170.7	169.6	171.0	169.6	170.7	172.5	173.7	175.8	178.9	186.1
55°	153.2	151.1	150.9	150.5	150.9	151.1	153.2	154.8	157.5	159.8	163.2
57.5°	131.7	130.4	128.3	127.5	128.3	130.4	131.7	134.1	137.3	140.4	143.8
60°	116.2	113.5	110.2	109.9	110.2	113.5	116.2	120.6	121.9	126.5	130.5
62.5°	102.1	101.6	100.9	100.9	100.9	101.6	102.1	103.5	105.4	112.2	117.0
65°	89.6	89.3	89.6	89.9	89.6	89.3	89.6	90.2	90.6	91.2	93.3
67.5°	78.0	77.5	76.9	77.1	76.9	77.5	78.0	78.2	79.1	79.5	80.9
70°	69.3	68.9	68.6	68.6	68.6	68.9	69.3	69.9	70.6	71.2	72.9
72.5°	60.7	60.6	60.4	60.1	60.4	60.6	60.7	62.0	62.3	63.0	64.1
75°	48.6	48.0	48.0	48.0	48.0	48.0	48.6	49.0	49.3	50.3	50.9
77.5°	37.0	36.7	36.4	36.1	36.4	36.7	37.0	37.1	37.6	37.8	38.5
80°	29.3	29.0	28.6	28.6	28.6	29.0	29.3	29.6	29.6	30.7	30.3
82.5°	22.4	22.0	21.9	21.7	21.9	22.0	22.4	22.5	22.5	23.2	23.1
85°	11.9	12.3	11.9	12.7	11.9	12.3	11.9	11.7	11.9	12.7	12.7
87.5°	8.3	8.1	8.5	8.3	8.5	8.1	8.3	8.2	8.4	8.1	7.9
90°	24.3	24.8	25.1	25.6	25.1	24.8	24.3	23.9	23.2	22.1	21.0
92.5°	24.9	25.1	25.3	25.6	25.3	25.1	24.9	24.6	24.2	23.6	23.1
95°	41.4	41.2	40.9	40.8	40.9	41.2	41.4	41.6	41.2	40.1	39.1
97.5°	53.7	53.9	54.1	54.4	54.1	53.9	53.7	53.4	52.9	52.0	51.2
100°	62.2	62.7	63.1	63.5	63.1	62.7	62.2	61.8	60.8	59.1	57.4
102.5°	66.3	66.9	67.5	68.0	67.5	66.9	66.3	65.7	64.3	62.2	59.9
105°	69.6	70.4	71.2	72.1	71.2	70.4	69.6	68.7	67.1	64.7	62.4
107.5°	71.6	72.4	73.3	74.1	73.3	72.4	71.6	70.8	71.5	73.8	76.2
110°	72.3	73.2	74.0	74.9	74.0	73.2	72.3	71.5	81.6	102.7	123.8



TEST NUMBER: P331669-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	73.7	74.3	75.0	75.6	75.0	74.3	73.7	72.9	111.0	187.9	264.7
115°	123.2	108.1	92.9	77.8	92.9	108.1	123.2	138.4	194.7	292.3	389.8
117.5°	466.9	417.1	367.2	317.4	367.2	417.1	466.9	516.7	553.5	577.0	600.7
120°	663.5	635.1	606.6	578.3	606.6	635.1	663.5	692.0	705.0	702.4	699.9
122.5°	738.2	732.6	727.1	721.6	727.1	732.6	738.2	743.6	745.6	744.1	742.6
125°	808.6	809.2	809.9	810.5	809.9	809.2	808.6	808.0	806.9	805.4	804.0
127.5°	866.2	866.4	866.5	866.6	866.5	866.4	866.2	866.1	865.0	862.8	860.7
130°	902.1	901.9	901.7	901.5	901.7	901.9	902.1	902.3	901.3	898.9	896.6
132.5°	936.2	936.0	935.9	935.6	935.9	936.0	936.2	936.5	935.6	933.6	931.6
135°	986.1	985.7	985.3	984.9	985.3	985.7	986.1	986.6	985.7	983.6	981.5
137.5°	1032.0	1031.3	1030.6	1029.8	1030.6	1031.3	1032.0	1032.7	1032.0	1029.9	1027.9
140°	1061.0	1060.0	1058.9	1057.9	1058.9	1060.0	1061.0	1062.1	1061.7	1059.8	1057.9
142.5°	1088.3	1087.3	1086.3	1085.2	1086.3	1087.3	1088.3	1089.4	1089.0	1087.4	1085.6
145°	1126.5	1125.4	1124.4	1123.3	1124.4	1125.4	1126.5	1127.5	1127.3	1125.8	1124.4
147.5°	1159.5	1158.6	1157.7	1156.8	1157.7	1158.6	1159.5	1160.4	1160.3	1159.2	1158.1
150°	1180.4	1179.5	1178.4	1177.3	1178.4	1179.5	1180.4	1181.5	1181.4	1180.2	1178.9
152.5°	1198.9	1197.6	1196.1	1194.8	1196.1	1197.6	1198.9	1200.3	1200.4	1199.2	1197.8
155°	1224.1	1222.4	1220.8	1219.1	1220.8	1222.4	1224.1	1225.7	1226.0	1224.8	1223.4
157.5°	1246.2	1244.5	1242.9	1241.2	1242.9	1244.5	1246.2	1247.8	1247.9	1246.4	1245.0
160°	1258.6	1257.0	1255.6	1254.1	1255.6	1257.0	1258.6	1260.0	1260.1	1258.8	1257.6
162.5°	1270.2	1268.4	1266.5	1264.7	1266.5	1268.4	1270.2	1271.9	1272.2	1270.7	1269.3
165°	1285.0	1283.6	1282.1	1280.7	1282.1	1283.6	1285.0	1286.6	1286.6	1285.0	1283.6
167.5°	1296.4	1294.5	1292.6	1290.7	1292.6	1294.5	1296.4	1298.2	1298.5	1297.0	1295.6
170°	1302.4	1300.6	1298.7	1296.7	1298.7	1300.6	1302.4	1304.3	1304.6	1303.1	1301.6
172.5°	1307.0	1305.1	1303.2	1301.3	1303.2	1305.1	1307.0	1308.9	1309.1	1307.6	1306.2
175°	1311.6	1309.5	1307.4	1305.3	1307.4	1309.5	1311.6	1313.8	1314.0	1312.6	1311.1
177.5°	1312.3	1310.8	1309.3	1307.8	1309.3	1310.8	1312.3	1313.8	1314.0	1312.8	1311.6
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331669-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	921.6	925.3	930.9	934.2	939.4	942.9	944.8	948.2	950.1	956.8	963.7
5°	870.1	875.5	884.8	893.4	902.8	912.4	919.4	927.4	934.7	947.4	960.7
7.5°	811.1	818.5	832.9	846.8	863.0	876.6	888.7	902.3	914.5	932.6	951.5
10°	766.9	779.9	798.9	811.8	833.1	846.8	865.8	880.7	897.8	921.8	943.1
12.5°	728.8	744.5	759.7	777.8	796.9	819.7	840.5	859.7	879.9	904.7	929.7
15°	659.7	682.3	706.0	724.2	750.3	774.2	798.5	824.5	849.2	878.8	911.4
17.5°	570.7	596.9	636.7	668.1	698.6	722.6	752.7	784.2	813.2	848.9	885.2
20°	530.5	549.7	576.8	619.0	665.0	690.6	721.3	755.9	789.2	828.1	867.1
22.5°	498.2	515.4	537.1	570.0	621.3	656.3	688.2	723.4	762.1	801.8	845.0
25°	452.2	464.2	486.9	513.4	548.8	606.4	641.3	676.6	718.6	761.3	810.5
27.5°	417.7	428.5	443.2	468.6	494.8	536.2	591.8	630.3	672.1	720.1	771.2
30°	391.3	403.9	420.3	438.2	466.9	499.2	554.7	599.4	640.7	690.0	744.6
32.5°	372.1	382.1	396.0	414.3	438.1	469.0	513.4	567.7	607.9	659.9	716.8
35°	340.6	352.3	363.6	380.9	400.3	428.6	462.2	520.1	560.1	611.4	668.7
37.5°	314.8	321.9	334.4	348.1	368.5	389.6	418.7	470.7	514.0	564.3	622.9
40°	295.1	304.0	313.3	328.7	345.4	365.6	394.2	432.9	482.5	531.8	589.1
42.5°	275.9	287.2	297.1	307.4	325.6	345.9	369.3	402.0	452.6	499.3	555.0
45°	252.7	260.1	270.4	281.7	296.7	314.1	334.7	363.3	411.9	452.2	504.5
47.5°	225.9	236.6	243.3	254.3	268.6	285.1	304.3	329.0	368.5	406.2	454.7
50°	207.5	218.5	228.1	238.1	250.7	266.7	282.7	306.7	338.3	378.0	423.2
52.5°	191.7	201.4	210.8	220.8	233.2	247.8	263.0	284.0	311.1	347.6	391.6
55°	170.1	176.1	185.8	195.8	206.8	220.8	235.4	253.1	276.4	307.0	342.7
57.5°	148.0	155.0	162.6	172.7	183.8	194.6	207.7	223.7	242.1	269.8	300.3
60°	135.5	140.9	147.2	157.5	167.8	177.5	190.1	203.5	220.8	244.8	270.7
62.5°	121.7	126.7	132.5	141.5	151.6	160.4	171.5	185.7	200.3	222.1	244.9
65°	98.5	105.9	111.6	119.6	127.9	137.2	145.9	157.2	170.1	187.4	207.8
67.5°	81.7	85.4	90.7	98.0	106.5	114.5	122.7	131.5	142.8	156.1	172.3
70°	74.3	75.6	76.6	83.6	91.6	99.6	107.2	115.6	125.2	136.2	150.2
72.5°	65.5	66.8	68.0	71.1	77.5	85.4	93.4	99.6	108.7	117.8	129.1
75°	52.0	53.9	54.9	56.6	58.9	64.3	71.6	77.6	82.9	89.9	98.9
77.5°	39.6	40.7	41.7	43.5	44.9	47.4	51.5	57.0	62.0	66.0	72.2
80°	31.3	31.7	33.0	33.6	35.7	37.3	39.3	43.6	48.6	50.3	54.6
82.5°	23.5	23.9	25.0	25.7	26.6	28.0	30.5	31.7	35.6	37.7	40.5
85°	13.0	12.7	13.6	13.6	14.4	15.0	15.7	17.3	18.3	21.0	21.7
87.5°	8.0	7.8	7.8	7.4	7.0	7.2	7.1	6.9	7.0	7.3	7.9
90°	20.0	19.0	17.3	15.6	13.9	12.2	10.3	7.9	5.6	3.3	1.0
92.5°	22.6	22.0	21.1	20.3	19.4	18.6	18.3	18.5	18.7	18.9	19.2
95°	38.0	37.0	35.5	34.1	32.5	31.0	33.8	40.8	47.7	54.7	61.6
97.5°	50.3	49.5	46.1	42.6	39.2	35.8	44.0	63.5	83.1	102.7	122.3
100°	55.7	54.0	50.5	46.9	43.2	39.7	52.3	81.2	110.0	138.9	167.8
102.5°	57.8	55.6	85.5	115.5	145.4	175.4	193.4	199.5	205.6	211.7	217.8
105°	60.1	57.8	115.3	172.8	230.3	287.8	313.4	307.1	300.8	294.5	288.2
107.5°	78.6	81.0	149.9	218.9	287.8	356.9	388.8	383.6	378.5	373.4	368.4
110°	144.8	165.9	226.8	287.7	348.5	409.4	437.7	433.2	428.8	424.4	419.9



TEST NUMBER: P331669-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	341.6	418.4	433.5	448.5	463.5	478.6	484.1	480.2	476.3	472.4	468.5
115°	487.3	584.9	579.6	574.4	569.1	563.8	559.4	555.8	552.2	548.7	545.1
117.5°	624.2	647.8	644.2	640.6	636.9	633.3	629.5	625.5	621.5	617.5	613.5
120°	697.3	694.8	691.1	687.2	683.5	679.7	676.2	673.1	669.9	666.7	663.5
122.5°	741.1	739.6	735.5	731.3	727.2	723.1	719.3	716.0	712.7	709.4	706.1
125°	802.5	801.0	797.0	793.0	789.0	785.0	781.6	778.9	776.1	773.4	770.7
127.5°	858.5	856.4	853.4	850.3	847.4	844.4	841.4	838.4	835.4	832.3	829.3
130°	894.3	892.0	889.7	887.3	885.0	882.7	879.9	876.6	873.2	869.8	866.4
132.5°	929.6	927.6	925.3	923.0	920.7	918.4	915.8	912.9	910.1	907.2	904.3
135°	979.5	977.3	975.4	973.5	971.6	969.7	967.1	963.8	960.4	957.0	953.6
137.5°	1025.8	1023.8	1021.6	1019.5	1017.4	1015.1	1012.9	1010.6	1008.2	1005.8	1003.4
140°	1056.0	1054.1	1051.8	1049.5	1047.1	1044.8	1042.9	1041.2	1039.5	1037.8	1036.1
142.5°	1083.9	1082.2	1079.5	1076.8	1074.2	1071.6	1069.4	1067.9	1066.4	1064.9	1063.4
145°	1122.8	1121.4	1117.8	1114.2	1110.6	1107.1	1105.4	1105.6	1105.8	1106.0	1106.3
147.5°	1157.0	1155.9	1152.4	1148.8	1145.3	1141.7	1140.4	1141.2	1142.0	1142.8	1143.6
150°	1177.7	1176.3	1173.0	1169.7	1166.3	1162.9	1162.0	1163.4	1164.9	1166.4	1167.9
152.5°	1196.6	1195.3	1192.1	1188.9	1185.7	1182.5	1181.8	1183.4	1185.0	1186.7	1188.3
155°	1222.2	1220.9	1218.4	1215.8	1213.4	1210.9	1210.5	1212.4	1214.3	1216.2	1218.1
157.5°	1243.6	1242.2	1240.4	1238.6	1236.9	1235.1	1235.0	1236.6	1238.2	1239.8	1241.4
160°	1256.3	1255.1	1253.8	1252.5	1251.2	1250.0	1250.0	1251.2	1252.5	1253.8	1255.1
162.5°	1267.8	1266.4	1265.3	1264.3	1263.1	1262.0	1262.1	1263.4	1264.6	1266.0	1267.2
165°	1282.1	1280.7	1280.1	1279.4	1278.7	1278.1	1278.4	1279.7	1280.9	1282.2	1283.5
167.5°	1294.1	1292.6	1292.0	1291.4	1290.8	1290.2	1290.6	1291.8	1293.1	1294.4	1295.7
170°	1300.1	1298.7	1298.2	1297.8	1297.4	1297.0	1297.4	1298.7	1299.9	1301.2	1302.4
172.5°	1304.7	1303.2	1302.8	1302.3	1302.0	1301.5	1302.0	1303.2	1304.5	1305.7	1307.0
175°	1309.7	1308.1	1307.7	1307.3	1306.9	1306.4	1307.0	1308.5	1309.9	1311.4	1312.9
177.5°	1310.5	1309.3	1309.1	1308.9	1308.8	1308.6	1309.1	1310.3	1311.4	1312.7	1313.8
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331669-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	963.9	964.7	970.1	972.5	977.3	979.2	981.2	980.7	980.7	981.8	989.3
5°	966.0	972.7	982.7	992.3	1001.7	1009.7	1014.9	1020.3	1022.3	1032.0	1040.6
7.5°	962.6	974.8	991.3	1006.0	1023.7	1037.5	1048.9	1059.3	1066.3	1080.4	1094.8
10°	958.1	975.4	994.0	1013.0	1037.3	1055.6	1074.2	1088.6	1093.2	1114.2	1126.2
12.5°	949.0	972.1	995.9	1020.5	1044.2	1069.4	1089.9	1104.3	1120.7	1139.5	1161.6
15°	935.4	962.1	993.0	1024.7	1058.6	1089.2	1111.3	1136.2	1154.1	1174.8	1194.1
17.5°	915.9	950.2	989.5	1026.2	1065.4	1098.3	1128.6	1152.5	1165.2	1177.0	1179.9
20°	900.4	937.4	983.6	1027.0	1066.2	1104.2	1134.2	1154.1	1157.5	1157.8	1140.1
22.5°	883.7	925.4	973.8	1018.2	1065.1	1107.4	1130.7	1139.2	1126.1	1103.5	1069.3
25°	852.8	901.1	957.3	1008.0	1059.3	1099.2	1107.2	1092.3	1046.0	997.3	935.8
27.5°	819.4	873.6	934.0	990.2	1044.9	1069.7	1052.4	998.4	915.0	842.6	754.7
30°	794.9	855.8	915.1	978.0	1028.6	1039.3	999.7	920.1	822.9	713.6	626.1
32.5°	766.9	830.7	895.9	961.0	1003.4	992.9	927.5	829.5	715.5	608.1	525.3
35°	726.9	792.9	863.1	928.4	955.4	910.4	812.5	685.0	568.5	468.2	411.3
37.5°	680.8	752.6	825.6	885.6	883.7	808.7	675.4	543.7	445.8	386.5	345.9
40°	648.0	720.6	799.5	850.2	828.5	730.9	586.4	462.2	390.6	343.3	313.7
42.5°	616.6	689.5	767.9	808.1	770.4	650.5	506.5	409.2	350.1	313.3	289.2
45°	563.1	640.0	712.7	734.9	667.6	535.5	409.6	339.0	299.7	272.4	255.7
47.5°	510.9	586.5	652.7	653.2	562.1	434.3	345.5	293.4	259.8	238.7	226.6
50°	478.8	550.8	606.4	597.7	494.5	386.3	309.0	264.0	236.1	219.8	207.1
52.5°	442.9	512.6	560.8	536.2	437.2	339.9	276.3	238.5	215.3	201.2	189.8
55°	390.6	452.5	486.5	449.2	356.7	282.7	233.4	203.8	186.5	174.5	164.9
57.5°	339.3	390.3	411.7	368.3	293.7	234.4	197.4	175.2	158.0	149.5	144.5
60°	307.0	350.6	365.6	317.7	255.4	205.1	174.9	154.2	141.5	135.9	130.9
62.5°	275.4	310.9	317.2	273.2	222.7	179.6	153.6	136.1	127.7	122.3	117.5
65°	228.5	254.0	251.1	215.8	176.1	142.5	123.5	112.9	106.6	98.9	90.6
67.5°	188.1	203.8	194.3	167.8	134.5	110.8	98.4	90.3	82.5	75.2	73.3
70°	162.5	171.5	161.5	137.2	110.2	92.9	82.9	73.3	68.6	67.0	63.9
72.5°	138.0	141.2	130.4	109.5	89.7	77.0	67.2	61.8	59.3	57.9	55.9
75°	103.5	101.2	91.9	75.6	62.2	53.6	50.6	48.6	47.0	45.7	44.6
77.5°	72.8	69.3	61.0	50.4	43.3	39.2	37.5	36.4	35.6	34.9	33.9
80°	54.6	52.3	44.0	35.9	33.0	30.9	30.0	28.6	28.6	28.0	26.9
82.5°	39.9	37.4	30.1	26.4	24.7	23.5	22.7	21.9	21.7	21.8	21.1
85°	21.0	16.9	15.0	14.4	13.3	12.7	13.0	12.3	12.3	12.3	11.9
87.5°	7.0	6.2	6.3	6.6	7.2	7.6	7.7	8.0	8.6	8.6	9.0
90°	3.3	5.6	7.9	10.3	12.2	13.9	15.6	17.3	19.0	20.0	21.0
92.5°	18.9	18.7	18.5	18.3	18.6	19.4	20.3	21.1	22.0	22.6	23.1
95°	54.7	47.7	40.8	33.8	31.0	32.5	34.1	35.5	37.0	38.0	39.1
97.5°	102.7	83.1	63.5	44.0	35.8	39.2	42.6	46.1	49.5	50.3	51.2
100°	138.9	110.0	81.2	52.3	39.7	43.2	46.9	50.5	54.0	55.7	57.4
102.5°	211.7	205.6	199.5	193.4	175.4	145.4	115.5	85.5	55.6	57.8	59.9
105°	294.5	300.8	307.1	313.4	287.8	230.3	172.8	115.3	57.8	60.1	62.4
107.5°	373.4	378.5	383.6	388.8	356.9	287.8	218.9	149.9	81.0	78.6	76.2
110°	424.4	428.8	433.2	437.7	409.4	348.5	287.7	226.8	165.9	144.8	123.8





TEST NUMBER: P331669-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	472.4	476.3	480.2	484.1	478.6	463.5	448.5	433.5	418.4	341.6	264.7
115°	548.7	552.2	555.8	559.4	563.8	569.1	574.4	579.6	584.9	487.3	389.8
117.5°	617.5	621.5	625.5	629.5	633.3	636.9	640.6	644.2	647.8	624.2	600.7
120°	666.7	669.9	673.1	676.2	679.7	683.5	687.2	691.1	694.8	697.3	699.9
122.5°	709.4	712.7	716.0	719.3	723.1	727.2	731.3	735.5	739.6	741.1	742.6
125°	773.4	776.1	778.9	781.6	785.0	789.0	793.0	797.0	801.0	802.5	804.0
127.5°	832.3	835.4	838.4	841.4	844.4	847.4	850.3	853.4	856.4	858.5	860.7
130°	869.8	873.2	876.6	879.9	882.7	885.0	887.3	889.7	892.0	894.3	896.6
132.5°	907.2	910.1	912.9	915.8	918.4	920.7	923.0	925.3	927.6	929.6	931.6
135°	957.0	960.4	963.8	967.1	969.7	971.6	973.5	975.4	977.3	979.5	981.5
137.5°	1005.8	1008.2	1010.6	1012.9	1015.1	1017.4	1019.5	1021.6	1023.8	1025.8	1027.9
140°	1037.8	1039.5	1041.2	1042.9	1044.8	1047.1	1049.5	1051.8	1054.1	1056.0	1057.9
142.5°	1064.9	1066.4	1067.9	1069.4	1071.6	1074.2	1076.8	1079.5	1082.2	1083.9	1085.6
145°	1106.0	1105.8	1105.6	1105.4	1107.1	1110.6	1114.2	1117.8	1121.4	1122.8	1124.4
147.5°	1142.8	1142.0	1141.2	1140.4	1141.7	1145.3	1148.8	1152.4	1155.9	1157.0	1158.1
150°	1166.4	1164.9	1163.4	1162.0	1162.9	1166.3	1169.7	1173.0	1176.3	1177.7	1178.9
152.5°	1186.7	1185.0	1183.4	1181.8	1182.5	1185.7	1188.9	1192.1	1195.3	1196.6	1197.8
155°	1216.2	1214.3	1212.4	1210.5	1210.9	1213.4	1215.8	1218.4	1220.9	1222.2	1223.4
157.5°	1239.8	1238.2	1236.6	1235.0	1235.1	1236.9	1238.6	1240.4	1242.2	1243.6	1245.0
160°	1253.8	1252.5	1251.2	1250.0	1250.0	1251.2	1252.5	1253.8	1255.1	1256.3	1257.6
162.5°	1266.0	1264.6	1263.4	1262.1	1262.0	1263.1	1264.3	1265.3	1266.4	1267.8	1269.3
165°	1282.2	1280.9	1279.7	1278.4	1278.1	1278.7	1279.4	1280.1	1280.7	1282.1	1283.6
167.5°	1294.4	1293.1	1291.8	1290.6	1290.2	1290.8	1291.4	1292.0	1292.6	1294.1	1295.6
170°	1301.2	1299.9	1298.7	1297.4	1297.0	1297.4	1297.8	1298.2	1298.7	1300.1	1301.6
172.5°	1305.7	1304.5	1303.2	1302.0	1301.5	1302.0	1302.3	1302.8	1303.2	1304.7	1306.2
175°	1311.4	1309.9	1308.5	1307.0	1306.4	1306.9	1307.3	1307.7	1308.1	1309.7	1311.1
177.5°	1312.7	1311.4	1310.3	1309.1	1308.6	1308.8	1308.9	1309.1	1309.3	1310.5	1311.6
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331669-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	991.9	995.4	997.0	997.0	998.9	998.1	997.3
5°	1048.9	1055.3	1056.6	1062.6	1066.9	1065.6	1066.2
7.5°	1105.6	1115.8	1125.9	1130.4	1131.2	1133.9	1134.9
10°	1140.5	1148.9	1164.5	1162.2	1173.8	1180.4	1169.5
12.5°	1174.1	1185.4	1196.2	1199.2	1205.8	1207.9	1203.5
15°	1204.4	1210.4	1211.1	1209.4	1211.5	1209.8	1203.5
17.5°	1176.1	1166.4	1146.7	1137.3	1129.9	1119.0	1114.6
20°	1129.2	1100.5	1067.3	1053.9	1038.3	1007.6	1014.9
22.5°	1028.0	995.3	962.1	923.1	904.6	875.5	873.8
25°	870.5	814.2	752.2	708.9	683.7	654.7	642.0
27.5°	676.8	605.9	555.2	529.5	506.0	483.1	482.1
30°	549.5	496.1	456.9	434.9	420.6	410.9	413.0
32.5°	463.2	426.6	400.1	381.9	371.3	364.0	363.9
35°	378.6	353.7	336.6	329.0	321.4	316.0	316.4
37.5°	324.0	309.0	299.5	291.1	286.3	283.7	282.2
40°	296.0	283.7	276.4	271.4	267.4	263.8	263.1
42.5°	273.9	263.8	256.4	252.4	248.8	246.1	245.5
45°	243.1	234.8	228.1	223.7	222.1	219.8	219.8
47.5°	216.2	208.0	202.9	200.1	197.2	195.7	195.6
50°	198.1	191.8	187.2	185.5	183.2	182.2	181.8
52.5°	181.9	177.2	173.8	172.7	171.7	170.4	170.6
55°	159.8	157.2	155.9	154.8	153.2	151.1	152.5
57.5°	141.2	139.0	135.4	132.2	130.7	129.3	129.8
60°	128.2	123.5	118.9	115.2	114.2	111.2	111.2
62.5°	111.7	105.1	99.4	97.4	96.4	95.0	94.7
65°	85.9	83.3	81.9	80.6	79.9	79.9	79.3
67.5°	71.2	70.1	68.7	68.3	67.7	67.5	67.2
70°	63.0	61.6	60.9	60.6	59.9	60.3	59.3
72.5°	54.9	53.9	53.8	52.9	52.5	52.5	51.8
75°	43.2	43.2	43.0	42.6	42.0	41.6	42.0
77.5°	33.3	33.3	32.7	32.7	32.6	32.7	32.4
80°	26.7	26.9	26.7	26.3	25.9	26.3	25.9
82.5°	21.0	20.6	20.5	20.4	20.4	20.2	20.2
85°	11.9	12.3	11.9	11.7	11.7	11.7	11.9
87.5°	8.9	9.2	9.3	9.4	9.5	9.5	9.4
90°	22.1	23.2	23.9	24.3	24.8	25.1	25.6
92.5°	23.6	24.2	24.6	24.9	25.1	25.3	25.6
95°	40.1	41.2	41.6	41.4	41.2	40.9	40.8
97.5°	52.0	52.9	53.4	53.7	53.9	54.1	54.4
100°	59.1	60.8	61.8	62.2	62.7	63.1	63.5
102.5°	62.2	64.3	65.7	66.3	66.9	67.5	68.0
105°	64.7	67.1	68.7	69.6	70.4	71.2	72.1
107.5°	73.8	71.5	70.8	71.6	72.4	73.3	74.1
110°	102.7	81.6	71.5	72.3	73.2	74.0	74.9



TEST NUMBER: P331669-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	187.9	111.0	72.9	73.7	74.3	75.0	75.6
115°	292.3	194.7	138.4	123.2	108.1	92.9	77.8
117.5°	577.0	553.5	516.7	466.9	417.1	367.2	317.4
120°	702.4	705.0	692.0	663.5	635.1	606.6	578.3
122.5°	744.1	745.6	743.6	738.2	732.6	727.1	721.6
125°	805.4	806.9	808.0	808.6	809.2	809.9	810.5
127.5°	862.8	865.0	866.1	866.2	866.4	866.5	866.6
130°	898.9	901.3	902.3	902.1	901.9	901.7	901.5
132.5°	933.6	935.6	936.5	936.2	936.0	935.9	935.6
135°	983.6	985.7	986.6	986.1	985.7	985.3	984.9
137.5°	1029.9	1032.0	1032.7	1032.0	1031.3	1030.6	1029.8
140°	1059.8	1061.7	1062.1	1061.0	1060.0	1058.9	1057.9
142.5°	1087.4	1089.0	1089.4	1088.3	1087.3	1086.3	1085.2
145°	1125.8	1127.3	1127.5	1126.5	1125.4	1124.4	1123.3
147.5°	1159.2	1160.3	1160.4	1159.5	1158.6	1157.7	1156.8
150°	1180.2	1181.4	1181.5	1180.4	1179.5	1178.4	1177.3
152.5°	1199.2	1200.4	1200.3	1198.9	1197.6	1196.1	1194.8
155°	1224.8	1226.0	1225.7	1224.1	1222.4	1220.8	1219.1
157.5°	1246.4	1247.9	1247.8	1246.2	1244.5	1242.9	1241.2
160°	1258.8	1260.1	1260.0	1258.6	1257.0	1255.6	1254.1
162.5°	1270.7	1272.2	1271.9	1270.2	1268.4	1266.5	1264.7
165°	1285.0	1286.6	1286.6	1285.0	1283.6	1282.1	1280.7
167.5°	1297.0	1298.5	1298.2	1296.4	1294.5	1292.6	1290.7
170°	1303.1	1304.6	1304.3	1302.4	1300.6	1298.7	1296.7
172.5°	1307.6	1309.1	1308.9	1307.0	1305.1	1303.2	1301.3
175°	1312.6	1314.0	1313.8	1311.6	1309.5	1307.4	1305.3
177.5°	1312.8	1314.0	1313.8	1312.3	1310.8	1309.3	1307.8
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0

(END OF REPORT)