

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331620-830

Luminaire Tested: **S122RDIP-S290D330U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331620-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S290D330U830-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2179.7 lumens  
Efficiency: N/A  
Efficacy: 107.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331620-830

CATALOG NUMBER: S122RDIP-S290D330U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331620-830

CATALOG NUMBER: S122RDIP-S290D330U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	34	33	28
4	74	64	56	51	68	59	52	47	50	45	41	41	38	35	33	31	28	25
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25	22
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	25	22	19
7	58	47	39	33	54	43	36	31	37	31	28	31	27	24	25	22	20	17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16
9	51	39	31	27	46	36	30	25	31	26	22	26	22	19	21	19	16	14
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7640	7640	7640
5°	7669	7543	7585
10°	7609	7420	7356
15°	7522	7199	6992
20°	7400	6887	6541
25°	7277	6531	6102
30°	7105	6162	5541
35°	6936	5765	5048
40°	6768	5351	4477
45°	6572	4889	3959
50°	6365	4421	3451
55°	6159	3916	2967
60°	5916	3387	2464
65°	5643	2846	2239
70°	5316	2346	2058
75°	4916	2133	1921
80°	4342	1906	1757
85°	3409	1501	1501



TEST NUMBER: P331620-830

CATALOG NUMBER: S122RDIP-S290D330U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.3	2.0
10°-20°	121.6	5.6
20°-30°	170.8	7.8
30°-40°	186.2	8.5
40°-50°	171.2	7.9
50°-60°	134.5	6.2
60°-70°	87.7	4.0
70°-80°	45.2	2.1
80°-90°	13.3	0.6
90°-100°	69.2	3.2
100°-110°	235.0	10.8
110°-120°	249.6	11.5
120°-130°	205.5	9.4
130°-140°	165.0	7.6
140°-150°	124.7	5.7
150°-160°	87.6	4.0
160°-170°	51.6	2.4
170°-180°	16.8	0.8
0°-30°	336.6	15.4
0°-40°	522.8	24.0
0°-60°	828.5	38.0
0°-90°	974.7	44.7
90°-120°	553.8	25.4
90°-150°	1049.0	48.1
90°-180°	1205.0	55.3
0°-180°	2179.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	473	473	473	473	473	
5°	473	471	465	469	468	45
15°	450	445	431	423	418	127
25°	408	394	367	350	342	188
35°	352	329	292	266	256	220
45°	288	258	214	185	173	222
55°	219	185	139	114	105	195
65°	148	113	74	61	59	146
75°	79	50	34	31	31	83
85°	18	10	8	8	8	22
90°	0	4	11	11	11	1
95°	12	29	130	49	38	12
105°	41	61	247	441	375	43
115°	72	90	206	426	494	71
125°	100	118	198	345	401	89
135°	117	140	196	290	332	91
145°	134	154	195	242	265	84
155°	152	164	190	214	223	70
165°	166	171	182	192	196	47
175°	173	173	174	177	176	16
180°	173	173	173	173	173	



TEST NUMBER: P331620-830

CATALOG NUMBER: S122RDIP-S290D330U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2
2.5°	474.9	474.5	474.1	473.7	473.3	472.7	471.8	471.1	470.2	469.4	470.1
5°	473.2	472.7	472.2	471.7	471.3	470.3	469.1	467.9	466.7	465.4	466.3
7.5°	468.3	467.7	467.0	466.5	465.9	464.9	463.4	461.9	460.5	459.1	459.3
10°	464.1	463.4	462.8	462.1	461.5	460.1	458.3	456.4	454.5	452.6	452.3
12.5°	459.0	458.2	457.3	456.6	455.7	454.1	451.7	449.2	446.8	444.3	443.8
15°	450.0	448.9	447.9	446.9	445.8	443.7	440.5	437.2	433.9	430.7	429.0
17.5°	438.9	437.3	435.7	434.1	432.5	429.7	425.6	421.4	417.3	413.1	410.9
20°	430.7	428.9	427.0	425.0	423.1	419.8	415.0	410.3	405.6	400.8	398.4
22.5°	421.9	419.7	417.5	415.5	413.3	409.5	404.2	398.8	393.5	388.1	385.0
25°	408.5	405.4	402.4	399.4	396.3	391.6	385.3	379.1	372.8	366.6	362.6
27.5°	392.4	389.1	385.8	382.5	379.1	373.9	366.8	359.8	352.7	345.6	341.1
30°	381.1	377.5	373.8	370.2	366.6	361.0	353.4	345.8	338.2	330.5	325.7
32.5°	370.1	365.9	361.7	357.4	353.2	347.2	339.5	331.7	324.0	316.1	310.7
35°	351.9	347.1	342.2	337.4	332.5	325.9	317.5	309.2	300.9	292.5	286.4
37.5°	333.8	328.5	323.1	317.8	312.5	305.4	296.4	287.5	278.6	269.7	263.1
40°	321.1	315.5	309.7	304.0	298.3	290.9	281.6	272.4	263.2	253.9	247.1
42.5°	308.1	302.1	296.1	290.1	284.1	276.3	266.7	257.2	247.7	238.2	231.2
45°	287.8	281.3	274.9	268.6	262.2	254.0	244.0	234.0	224.0	214.1	207.4
47.5°	267.9	261.1	254.4	247.6	240.8	232.3	222.0	211.7	201.3	191.1	184.4
50°	253.4	246.8	240.0	233.2	226.5	217.8	207.4	196.9	186.4	176.0	169.4
52.5°	239.4	232.3	225.4	218.3	211.2	202.6	192.3	182.1	171.8	161.6	155.2
55°	218.8	211.4	204.0	196.5	189.1	180.3	169.9	159.7	149.4	139.1	133.5
57.5°	197.7	190.0	182.4	174.8	167.2	158.4	148.5	138.7	128.8	118.9	113.7
60°	183.2	175.7	168.1	160.4	152.8	144.1	134.3	124.5	114.7	104.9	100.0
62.5°	169.2	161.6	154.0	146.4	138.7	130.3	120.9	111.6	102.3	92.9	88.3
65°	147.7	140.0	132.3	124.6	116.9	108.8	100.2	91.6	83.0	74.5	71.3
67.5°	127.0	119.3	111.7	104.1	96.4	88.7	81.0	73.3	65.6	57.9	56.4
70°	112.6	105.2	97.7	90.4	82.9	76.0	69.4	62.8	56.3	49.7	48.7
72.5°	98.9	91.8	84.6	77.6	70.4	64.3	59.0	53.7	48.4	43.2	42.3
75°	78.8	72.1	65.5	58.8	52.1	47.2	43.9	40.7	37.5	34.2	33.6
77.5°	59.0	53.2	47.3	41.5	35.6	32.0	30.3	28.8	27.2	25.7	25.4
80°	46.7	41.8	36.9	32.1	27.2	24.3	23.4	22.4	21.5	20.5	20.2
82.5°	35.3	31.6	27.8	24.0	20.3	18.0	17.3	16.7	16.0	15.5	15.2
85°	18.4	16.4	14.4	12.4	10.5	9.2	9.0	8.7	8.4	8.1	8.1
87.5°	5.6	5.2	4.8	4.3	3.9	3.8	4.1	4.5	4.9	5.0	4.9
90°	0.4	1.3	2.6	3.3	4.0	5.0	6.7	9.0	11.0	11.3	11.0
92.5°	4.1	5.8	8.3	9.7	12.0	15.1	22.6	33.3	42.7	43.3	36.6
95°	11.7	13.0	16.3	19.3	24.6	32.6	48.0	76.9	115.6	130.5	114.2
97.5°	18.9	20.7	24.3	28.8	35.0	44.0	63.2	103.7	167.9	222.8	233.8
100°	25.6	26.7	29.6	35.0	41.7	51.0	68.6	109.2	181.2	263.1	311.0
102.5°	31.8	32.5	35.5	40.8	47.8	57.1	73.4	109.5	176.1	264.4	339.8
105°	40.6	41.9	44.3	49.3	56.6	66.0	81.6	111.2	166.2	246.8	335.4
107.5°	50.2	51.3	53.5	58.2	65.4	74.8	90.0	115.8	161.3	227.8	306.1
110°	56.6	58.0	59.9	64.3	71.3	81.0	95.6	119.5	160.2	218.8	287.8



TEST NUMBER: P331620-830

CATALOG NUMBER: S122RDIP-S290D330U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.5	63.8	66.1	70.1	76.8	86.8	100.9	123.6	160.4	212.9	274.9
115°	71.6	73.2	75.3	79.3	86.0	94.9	109.2	129.5	161.8	206.5	259.1
117.5°	81.1	82.4	84.4	87.9	94.3	103.7	116.9	135.9	164.3	203.3	249.1
120°	86.9	88.2	90.3	93.2	99.9	109.2	122.2	140.3	165.9	201.5	243.7
122.5°	92.6	93.6	95.6	98.9	105.5	115.1	127.2	143.9	167.7	200.4	239.2
125°	99.9	100.9	102.9	106.9	113.6	122.9	134.9	149.9	170.5	198.5	232.8
127.5°	105.8	107.1	109.9	114.3	120.6	130.3	141.9	155.4	173.3	197.4	226.8
130°	109.2	110.6	113.9	118.6	125.3	134.5	146.2	158.8	175.5	196.8	222.8
132.5°	112.4	114.0	117.6	122.5	129.5	138.8	150.0	162.3	177.7	196.5	219.6
135°	117.3	118.6	122.5	127.5	135.3	144.5	155.2	166.8	180.2	196.1	215.1
137.5°	121.8	123.4	127.3	132.7	140.3	148.9	159.5	170.3	182.5	196.0	212.0
140°	125.3	126.6	130.5	135.9	143.2	151.8	161.8	172.2	183.5	195.9	210.1
142.5°	128.7	129.8	133.5	138.8	145.9	154.0	163.7	173.8	184.3	195.9	208.3
145°	133.8	135.3	138.6	143.5	150.2	157.5	166.5	175.9	185.1	195.1	205.9
147.5°	139.5	140.4	143.6	148.3	153.8	160.3	168.8	177.0	185.4	194.0	203.3
150°	143.2	144.2	146.8	151.2	156.2	162.2	169.8	177.5	185.1	193.1	201.1
152.5°	146.9	147.4	150.1	153.8	158.6	164.0	170.9	177.8	184.6	191.8	199.3
155°	152.2	152.5	154.5	158.2	161.8	166.8	172.5	178.1	183.8	189.5	195.9
157.5°	156.6	156.9	158.5	161.7	164.7	168.8	173.6	178.1	182.3	187.1	192.6
160°	159.5	159.9	161.2	163.8	166.5	170.2	174.2	178.1	181.5	185.5	190.1
162.5°	162.5	162.2	163.6	165.7	168.1	171.0	174.5	177.9	180.7	184.2	188.0
165°	165.9	165.5	166.2	168.1	169.8	171.8	174.8	177.2	179.2	181.5	184.5
167.5°	168.6	168.2	168.8	170.1	171.4	172.6	174.7	176.7	177.7	179.2	181.1
170°	170.5	169.8	170.2	171.2	171.8	172.9	174.5	176.2	176.8	177.9	179.2
172.5°	171.5	171.2	171.0	172.0	172.4	173.1	174.3	175.4	175.8	176.3	177.3
175°	172.9	172.5	172.2	172.9	172.9	173.1	173.8	174.5	174.2	174.5	174.8
177.5°	173.4	172.9	172.7	173.1	173.1	173.1	173.4	174.0	173.4	173.1	173.4
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1



TEST NUMBER: P331620-830

CATALOG NUMBER: S122RDIP-S290D330U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2
2.5°	470.9	471.6	472.4	472.7	472.6	472.4	472.2	472.1
5°	467.1	468.0	468.8	469.1	468.8	468.5	468.3	468.0
7.5°	459.6	459.9	460.1	460.0	459.5	458.9	458.5	458.0
10°	452.0	451.8	451.5	451.0	450.4	449.9	449.3	448.7
12.5°	443.4	442.8	442.3	441.6	440.6	439.7	438.8	437.8
15°	427.2	425.3	423.5	422.2	421.2	420.2	419.2	418.3
17.5°	408.8	406.6	404.5	402.7	401.0	399.4	397.7	396.1
20°	396.1	393.6	391.2	389.0	386.9	384.8	382.8	380.7
22.5°	382.0	378.9	375.9	373.5	371.9	370.4	368.8	367.3
25°	358.7	354.8	350.9	348.3	346.9	345.3	343.9	342.5
27.5°	336.5	332.0	327.4	324.0	321.8	319.5	317.3	315.0
30°	320.8	316.0	311.1	307.5	304.8	302.3	299.7	297.2
32.5°	305.1	299.5	294.0	290.0	287.7	285.2	282.8	280.4
35°	280.5	274.5	268.4	264.4	262.3	260.2	258.2	256.1
37.5°	256.5	249.9	243.3	238.7	236.4	233.9	231.6	229.1
40°	240.4	233.7	226.9	222.3	219.8	217.4	214.8	212.4
42.5°	224.1	217.2	210.2	205.6	203.1	200.8	198.3	196.0
45°	200.6	193.8	187.1	182.6	180.3	178.0	175.7	173.4
47.5°	177.6	170.9	164.2	159.8	157.7	155.6	153.5	151.5
50°	162.9	156.3	149.7	145.4	143.5	141.5	139.4	137.4
52.5°	148.9	142.6	136.3	132.1	130.4	128.5	126.6	124.8
55°	127.7	122.1	116.3	112.5	110.7	109.0	107.2	105.4
57.5°	108.5	103.2	98.0	94.6	93.1	91.6	90.1	88.5
60°	95.2	90.4	85.5	82.3	80.8	79.3	77.8	76.3
62.5°	83.7	79.1	74.5	71.6	70.7	69.8	68.9	68.0
65°	68.1	64.8	61.5	59.8	59.5	59.2	58.9	58.6
67.5°	55.0	53.4	51.9	51.1	50.7	50.4	50.1	49.9
70°	47.8	46.8	45.9	45.2	44.8	44.4	44.0	43.6
72.5°	41.6	40.7	40.0	39.5	39.2	39.0	38.7	38.5
75°	32.9	32.2	31.6	31.2	31.1	31.0	30.9	30.8
77.5°	24.9	24.5	24.1	23.9	23.8	23.6	23.5	23.3
80°	19.8	19.4	19.0	18.9	18.9	18.9	18.9	18.9
82.5°	15.0	14.7	14.5	14.4	14.4	14.4	14.4	14.4
85°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
87.5°	4.7	4.5	4.5	4.6	4.6	4.6	4.6	4.6
90°	10.7	10.0	10.7	11.0	11.0	11.0	11.0	11.0
92.5°	29.0	24.9	22.1	20.1	19.8	18.8	18.9	18.5
95°	87.3	66.9	53.0	45.6	41.3	38.6	37.6	38.0
97.5°	203.6	166.5	130.5	106.5	90.6	82.4	77.6	74.7
100°	304.1	262.8	217.2	176.8	149.2	134.9	125.3	119.2
102.5°	369.9	360.5	327.2	284.5	254.4	230.0	217.9	209.8
105°	404.6	442.2	446.6	435.6	414.9	394.3	379.9	375.3
107.5°	379.6	436.3	470.9	487.0	489.7	488.5	485.6	479.5
110°	358.0	417.6	460.2	487.6	501.9	508.2	511.2	510.9





TEST NUMBER: P331620-830

CATALOG NUMBER: S122RDIP-S290D330U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	338.3	395.5	441.0	472.4	492.3	502.8	508.5	510.3
115°	314.1	365.3	409.0	443.3	466.9	482.2	490.9	493.9
117.5°	295.8	340.8	380.4	412.6	436.7	452.9	461.9	464.5
120°	286.7	328.0	363.4	393.6	417.0	432.6	442.2	445.6
122.5°	279.6	317.4	350.8	378.1	399.1	414.5	423.1	425.8
125°	269.1	303.4	332.7	357.7	377.0	389.6	397.9	400.7
127.5°	258.7	289.8	317.4	340.4	357.3	369.2	376.4	378.5
130°	252.1	280.8	307.1	329.0	345.3	356.7	363.4	366.0
132.5°	245.7	272.2	296.4	317.1	333.1	344.4	350.5	353.0
135°	236.8	258.7	280.8	299.4	313.7	324.7	330.7	332.1
137.5°	229.7	248.1	265.5	281.7	294.8	304.3	309.5	311.5
140°	225.1	241.1	256.5	271.1	281.7	290.4	295.4	297.4
142.5°	221.4	235.0	248.2	260.4	270.5	278.4	282.9	283.2
145°	216.1	227.2	237.4	247.1	255.1	260.8	264.1	265.0
147.5°	212.1	220.7	228.8	235.8	242.4	246.9	249.2	249.9
150°	209.2	216.5	223.5	229.4	234.4	238.5	240.4	240.8
152.5°	206.2	213.0	219.0	224.1	228.1	231.5	233.0	233.1
155°	202.2	207.5	212.4	216.1	219.8	222.2	223.5	222.8
157.5°	197.5	201.9	206.0	209.0	211.5	213.5	214.1	214.1
160°	194.4	198.1	201.8	204.2	206.5	208.1	208.5	208.5
162.5°	191.5	194.7	197.8	199.6	202.0	203.1	203.4	203.1
165°	187.2	189.5	191.8	193.1	194.4	195.9	195.9	195.5
167.5°	182.9	184.7	186.3	187.6	188.1	188.9	188.8	188.4
170°	180.9	181.8	183.1	183.8	184.2	185.1	184.8	184.2
172.5°	178.4	179.2	180.2	180.6	181.0	181.4	181.1	180.7
175°	175.9	176.2	176.5	176.8	176.8	177.2	176.8	176.2
177.5°	174.0	174.0	174.3	174.3	174.3	174.3	174.0	173.4
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1

(END OF REPORT)