

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331660-830

Luminaire Tested: **S122RDIP-S485D725U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331660-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S485D725U830-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 725 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4332.8 lumens  
Efficiency: N/A  
Efficacy: 112.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331660-830

CATALOG NUMBER: S122RDIP-S485D725U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331660-830

CATALOG NUMBER: S122RDIP-S485D725U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37								
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	40	39	38	32								
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	32	27								
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	23								
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24	20								
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	23	22	18								
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16								
7	57	45	38	32	52	42	35	30	34	29	26	28	24	21	21	19	17	14								
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13								
9	49	38	30	25	45	35	28	24	29	24	20	23	20	17	18	16	14	12								
10	46	34	27	23	42	32	26	21	27	22	18	22	18	16	17	15	13	11								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12558	12558	12558
5°	12606	12402	12470
10°	12511	12198	12095
15°	12366	11836	11497
20°	12167	11320	10753
25°	11965	10735	10033
30°	11680	10133	9107
35°	11404	9477	8296
40°	11126	8800	7358
45°	10803	8035	6510
50°	10467	7267	5674
55°	10125	6441	4873
60°	9726	5570	4046
65°	9280	4676	3683
70°	8738	3852	3389
75°	8079	3512	3163
80°	7132	3133	2882
85°	5613	2482	2482



TEST NUMBER: P331660-830

CATALOG NUMBER: S122RDIP-S485D725U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.8	1.7
10°-20°	199.9	4.6
20°-30°	280.7	6.5
30°-40°	306.1	7.1
40°-50°	281.5	6.5
50°-60°	221.1	5.1
60°-70°	144.1	3.3
70°-80°	74.3	1.7
80°-90°	21.6	0.5
90°-100°	31.1	0.7
100°-110°	114.0	2.6
110°-120°	304.7	7.0
120°-130°	502.9	11.6
130°-140°	534.9	12.3
140°-150°	497.1	11.5
150°-160°	399.7	9.2
160°-170°	257.6	5.9
170°-180°	88.7	2.0
0°-30°	553.4	12.8
0°-40°	859.6	19.8
0°-60°	1362.1	31.4
0°-90°	1602.1	37.0
90°-120°	449.7	10.4
90°-150°	1984.7	45.8
90°-180°	2731.0	63.0
0°-180°	4332.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	778	778	778	778	778	
5°	778	774	765	771	769	74
15°	740	731	708	695	688	208
25°	672	648	603	575	563	309
35°	579	541	481	438	421	362
45°	473	424	352	304	285	365
55°	360	304	229	188	173	321
65°	243	186	122	100	96	241
75°	130	82	56	52	51	137
85°	30	16	13	13	13	36
90°	1	8	14	17	18	3
95°	44	23	26	29	29	54
105°	205	214	41	48	51	219
115°	388	399	416	118	55	382
125°	548	557	570	574	576	489
135°	678	689	695	701	700	524
145°	787	787	798	802	799	492
155°	866	861	868	872	867	399
165°	913	909	911	915	911	258
175°	934	929	930	934	928	89
180°	932	932	932	932	932	



TEST NUMBER: P331660-830

CATALOG NUMBER: S122RDIP-S485D725U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	780.6	780.0	779.4	778.7	778.2	777.1	775.8	774.4	773.0	771.7	772.9
5°	777.8	777.0	776.3	775.5	774.7	773.3	771.3	769.2	767.2	765.2	766.6
7.5°	769.8	768.8	767.9	766.9	765.9	764.2	761.9	759.5	757.1	754.8	755.2
10°	763.1	762.0	760.8	759.8	758.7	756.6	753.5	750.3	747.2	744.0	743.6
12.5°	754.6	753.3	751.9	750.5	749.2	746.6	742.5	738.6	734.5	730.6	729.7
15°	739.8	738.1	736.4	734.6	732.9	729.4	724.1	718.8	713.5	708.1	705.2
17.5°	721.7	719.1	716.4	713.8	711.1	706.4	699.6	692.8	686.0	679.1	675.6
20°	708.1	705.0	701.9	698.8	695.6	690.1	682.3	674.5	666.7	658.8	655.0
22.5°	693.5	690.0	686.5	683.0	679.5	673.4	664.5	655.6	646.9	638.0	633.0
25°	671.6	666.6	661.6	656.5	651.5	643.9	633.5	623.2	612.8	602.6	596.2
27.5°	645.1	639.6	634.1	628.8	623.3	614.7	603.1	591.4	579.9	568.2	560.7
30°	626.5	620.6	614.6	608.7	602.8	593.5	581.0	568.4	555.9	543.5	535.5
32.5°	608.5	601.5	594.6	587.7	580.7	570.8	558.1	545.3	532.5	519.8	510.7
35°	578.6	570.6	562.7	554.7	546.7	535.8	522.1	508.3	494.6	480.8	470.9
37.5°	548.7	540.0	531.2	522.5	513.8	502.0	487.4	472.7	458.0	443.4	432.4
40°	527.9	518.6	509.2	499.8	490.4	478.2	463.0	447.8	432.6	417.5	406.3
42.5°	506.5	496.6	486.7	476.9	467.0	454.2	438.6	422.8	407.2	391.5	380.0
45°	473.1	462.6	452.0	441.6	431.1	417.6	401.2	384.8	368.3	351.9	340.8
47.5°	440.4	429.2	418.2	407.1	396.0	381.9	365.0	348.0	331.0	314.1	303.0
50°	416.7	405.6	394.5	383.4	372.3	358.2	340.9	323.8	306.5	289.3	278.5
52.5°	393.6	382.0	370.4	358.8	347.2	333.0	316.1	299.4	282.5	265.7	255.2
55°	359.7	347.5	335.3	323.1	310.9	296.3	279.5	262.6	245.6	228.8	219.4
57.5°	324.9	312.5	299.9	287.4	274.8	260.5	244.3	228.0	211.8	195.6	186.9
60°	301.2	288.8	276.3	263.7	251.2	237.0	220.8	204.7	188.6	172.5	164.5
62.5°	278.1	265.7	253.2	240.6	228.1	214.2	198.9	183.5	168.1	152.8	145.2
65°	242.9	230.2	217.5	204.8	192.2	178.8	164.8	150.6	136.6	122.4	117.2
67.5°	208.8	196.2	183.6	171.1	158.4	145.8	133.2	120.6	107.8	95.2	92.7
70°	185.1	173.0	160.7	148.5	136.3	124.8	114.0	103.2	92.5	81.6	80.1
72.5°	162.6	150.9	139.2	127.5	115.8	105.7	97.0	88.3	79.6	71.0	69.7
75°	129.5	118.6	107.6	96.7	85.7	77.6	72.3	66.9	61.6	56.3	55.2
77.5°	97.0	87.4	77.8	68.1	58.6	52.5	50.0	47.4	44.8	42.2	41.6
80°	76.7	68.7	60.8	52.8	44.8	40.1	38.5	36.9	35.3	33.7	33.2
82.5°	58.2	51.9	45.7	39.5	33.3	29.6	28.6	27.4	26.4	25.4	25.0
85°	30.3	27.0	23.7	20.5	17.2	15.3	14.8	14.3	13.9	13.4	13.4
87.5°	9.1	8.5	7.8	7.2	6.5	6.2	6.5	6.7	7.0	7.2	7.3
90°	0.7	2.4	4.0	5.7	7.3	8.7	9.9	11.1	12.3	13.5	14.2
92.5°	13.6	13.5	13.3	13.2	13.0	13.3	13.9	14.4	15.1	15.6	16.0
95°	43.8	38.9	33.9	29.0	24.0	22.1	23.2	24.2	25.3	26.3	27.1
97.5°	87.0	73.0	59.1	45.1	31.2	25.4	27.9	30.3	32.8	35.2	35.8
100°	119.3	98.8	78.3	57.8	37.2	28.3	30.8	33.4	35.9	38.5	39.6
102.5°	155.0	150.6	146.3	141.9	137.5	124.7	103.4	82.1	60.8	39.5	41.1
105°	205.0	209.4	214.0	218.5	222.9	204.7	163.8	122.9	82.0	41.1	42.8
107.5°	262.0	265.6	269.3	272.9	276.5	253.8	204.7	155.7	106.6	57.6	55.9
110°	298.7	301.8	305.0	308.1	311.2	291.2	247.9	204.6	161.3	118.0	103.0



TEST NUMBER: P331660-830

CATALOG NUMBER: S122RDIP-S485D725U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	333.2	336.0	338.7	341.6	344.3	340.4	329.7	319.0	308.3	297.6	243.0
115°	387.7	390.2	392.8	395.3	397.8	401.1	404.7	408.5	412.3	416.0	346.7
117.5°	436.4	439.2	442.1	444.9	447.7	450.4	453.1	455.6	458.2	460.8	444.0
120°	471.9	474.2	476.5	478.7	481.0	483.4	486.2	488.8	491.5	494.2	496.0
122.5°	502.2	504.5	506.9	509.3	511.6	514.3	517.3	520.2	523.1	526.0	527.1
125°	548.2	550.1	552.0	554.0	555.9	558.4	561.2	564.0	566.8	569.8	570.8
127.5°	589.8	592.0	594.2	596.3	598.4	600.6	602.8	604.8	607.0	609.1	610.7
130°	616.2	618.7	621.0	623.4	625.8	627.8	629.5	631.1	632.8	634.4	636.1
132.5°	643.2	645.3	647.3	649.3	651.4	653.2	654.9	656.5	658.2	659.8	661.2
135°	678.3	680.7	683.1	685.5	687.9	689.8	691.1	692.4	693.8	695.1	696.6
137.5°	713.8	715.4	717.1	718.8	720.5	722.1	723.6	725.1	726.6	728.2	729.6
140°	737.0	738.1	739.3	740.6	741.7	743.2	744.8	746.5	748.1	749.8	751.1
142.5°	756.4	757.4	758.6	759.6	760.6	762.1	764.0	765.9	767.8	769.7	770.9
145°	786.8	786.6	786.6	786.4	786.3	787.4	789.9	792.5	795.0	797.6	798.7
147.5°	813.4	812.8	812.3	811.7	811.2	812.1	814.6	817.1	819.6	822.2	822.9
150°	830.7	829.6	828.6	827.6	826.4	827.2	829.5	831.9	834.3	836.7	837.6
152.5°	845.2	844.0	842.9	841.7	840.6	841.1	843.4	845.6	847.9	850.2	851.1
155°	866.4	865.1	863.7	862.3	861.0	861.2	863.0	864.8	866.6	868.4	869.3
157.5°	883.0	881.8	880.7	879.6	878.4	878.4	879.8	881.0	882.2	883.5	884.6
160°	892.7	891.7	890.9	889.9	889.1	889.1	889.9	890.9	891.7	892.7	893.6
162.5°	901.4	900.4	899.6	898.6	897.7	897.7	898.4	899.2	900.0	900.8	901.8
165°	912.9	912.0	911.2	910.2	909.3	909.1	909.6	910.0	910.4	910.9	911.9
167.5°	921.5	920.7	919.7	918.9	917.9	917.7	918.1	918.5	919.0	919.4	920.4
170°	926.4	925.5	924.6	923.7	922.8	922.5	922.8	923.1	923.4	923.7	924.7
172.5°	929.6	928.7	927.8	926.9	926.0	925.8	926.0	926.3	926.6	926.9	928.0
175°	933.8	932.7	931.7	930.7	929.6	929.3	929.5	929.8	930.1	930.5	931.5
177.5°	934.5	933.7	932.8	932.0	931.1	930.8	930.9	931.0	931.1	931.2	932.1
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8



TEST NUMBER: P331660-830

CATALOG NUMBER: S122RDIP-S485D725U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	774.1	775.4	776.7	777.1	776.9	776.7	776.4	776.2
5°	768.0	769.4	770.8	771.3	770.8	770.3	769.9	769.4
7.5°	755.5	755.9	756.4	756.2	755.4	754.5	753.8	752.9
10°	743.1	742.6	742.2	741.5	740.6	739.6	738.7	737.7
12.5°	728.9	728.0	727.2	725.9	724.3	722.8	721.2	719.7
15°	702.2	699.3	696.3	694.0	692.4	690.9	689.3	687.8
17.5°	672.0	668.5	665.0	661.9	659.2	656.5	653.8	651.1
20°	651.0	647.1	643.2	639.5	636.1	632.6	629.2	625.8
22.5°	627.9	622.9	617.9	614.1	611.5	609.0	606.4	603.8
25°	589.7	583.3	576.9	572.5	570.1	567.8	565.5	563.2
27.5°	553.3	545.7	538.3	532.7	529.0	525.3	521.5	517.8
30°	527.4	519.5	511.5	505.4	501.1	497.0	492.8	488.5
32.5°	501.5	492.5	483.3	476.8	472.9	468.9	464.9	460.9
35°	461.1	451.2	441.4	434.7	431.3	427.8	424.4	420.9
37.5°	421.6	410.8	399.9	392.5	388.6	384.7	380.7	376.7
40°	395.2	384.1	373.0	365.4	361.4	357.3	353.2	349.1
42.5°	368.5	357.0	345.6	337.9	333.9	330.0	326.0	322.1
45°	329.7	318.7	307.6	300.1	296.3	292.6	288.8	285.1
47.5°	292.0	281.0	269.9	262.7	259.3	255.9	252.4	249.0
50°	267.7	256.9	246.1	239.1	235.8	232.5	229.2	225.9
52.5°	244.8	234.4	223.9	217.3	214.2	211.2	208.1	205.1
55°	210.0	200.6	191.2	185.0	182.1	179.1	176.2	173.1
57.5°	178.3	169.8	161.2	155.6	153.1	150.6	148.1	145.5
60°	156.5	148.5	140.5	135.3	132.8	130.3	127.8	125.3
62.5°	137.5	130.0	122.3	117.8	116.3	114.8	113.3	111.8
65°	111.9	106.5	101.2	98.3	97.8	97.4	96.9	96.4
67.5°	90.3	87.8	85.4	84.0	83.4	82.9	82.5	81.9
70°	78.5	77.0	75.4	74.3	73.7	73.0	72.4	71.8
72.5°	68.3	67.0	65.7	64.8	64.5	64.1	63.7	63.3
75°	54.1	53.1	51.9	51.3	51.2	51.0	50.8	50.7
77.5°	41.0	40.3	39.8	39.3	39.0	38.8	38.5	38.3
80°	32.5	32.0	31.3	31.0	31.0	31.0	31.0	31.0
82.5°	24.6	24.2	23.8	23.7	23.7	23.7	23.7	23.7
85°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4
87.5°	7.3	7.3	7.3	7.4	7.4	7.4	7.5	7.5
90°	15.0	15.7	16.5	17.0	17.3	17.6	17.9	18.2
92.5°	16.4	16.8	17.2	17.5	17.6	17.8	18.0	18.2
95°	27.8	28.6	29.3	29.6	29.4	29.3	29.1	29.0
97.5°	36.4	36.9	37.6	38.0	38.2	38.4	38.5	38.7
100°	40.8	42.0	43.3	44.0	44.3	44.6	44.9	45.1
102.5°	42.6	44.2	45.7	46.8	47.1	47.6	48.0	48.4
105°	44.4	46.1	47.7	48.8	49.5	50.0	50.6	51.3
107.5°	54.2	52.5	50.9	50.3	50.9	51.6	52.1	52.7
110°	88.0	73.0	58.1	50.9	51.5	52.0	52.7	53.3





TEST NUMBER: P331660-830

CATALOG NUMBER: S122RDIP-S485D725U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	188.3	133.7	79.0	51.8	52.4	52.9	53.3	53.8
115°	277.3	207.9	138.6	98.4	87.7	76.8	66.1	55.3
117.5°	427.3	410.4	393.6	367.5	332.1	296.6	261.2	225.7
120°	497.9	499.6	501.4	492.2	471.9	451.8	431.5	411.3
122.5°	528.2	529.2	530.4	529.0	525.0	521.0	517.2	513.2
125°	571.8	572.9	573.9	574.7	575.1	575.6	576.0	576.5
127.5°	612.2	613.7	615.2	616.0	616.1	616.2	616.3	616.4
130°	637.7	639.4	641.0	641.8	641.7	641.5	641.3	641.2
132.5°	662.6	664.0	665.4	666.1	665.9	665.8	665.6	665.4
135°	698.1	699.6	701.2	701.7	701.4	701.2	700.8	700.5
137.5°	731.1	732.5	734.1	734.5	734.1	733.5	733.0	732.4
140°	752.4	753.8	755.2	755.4	754.7	753.9	753.2	752.4
142.5°	772.1	773.4	774.6	774.9	774.1	773.4	772.6	771.8
145°	799.7	800.8	801.8	801.9	801.3	800.5	799.7	799.0
147.5°	823.7	824.5	825.3	825.4	824.7	824.1	823.5	822.8
150°	838.5	839.4	840.3	840.4	839.6	838.9	838.1	837.4
152.5°	852.0	852.9	853.8	853.8	852.8	851.8	850.8	849.8
155°	870.2	871.1	872.0	871.9	870.6	869.5	868.3	867.0
157.5°	885.5	886.6	887.6	887.5	886.4	885.1	884.0	882.9
160°	894.5	895.4	896.3	896.2	895.1	894.1	893.1	892.0
162.5°	902.8	903.8	904.8	904.7	903.4	902.1	900.9	899.6
165°	912.9	914.1	915.1	915.1	914.1	912.9	911.9	910.9
167.5°	921.5	922.6	923.6	923.4	922.1	920.8	919.4	918.0
170°	925.8	926.8	927.9	927.7	926.4	925.0	923.7	922.4
172.5°	929.1	930.1	931.1	930.9	929.6	928.3	926.9	925.6
175°	932.6	933.6	934.6	934.4	932.9	931.4	929.9	928.4
177.5°	932.9	933.8	934.6	934.5	933.4	932.4	931.2	930.2
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8

(END OF REPORT)