

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331697-940

Luminaire Tested: **S122RDIP-S675D925U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331697-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S675D925U940-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5021.7 lumens  
Efficiency: N/A  
Efficacy: 96.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331697-940

CATALOG NUMBER: S122RDIP-S675D925U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331697-940

CATALOG NUMBER: S122RDIP-S675D925U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35	30
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	31	26
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27	23
5	68	57	49	43	62	52	45	40	44	38	34	36	32	29	28	26	23	20
6	63	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	33	53	42	36	31	36	31	27	29	26	23	23	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16239	16239	16239
5°	16302	16037	16126
10°	16179	15775	15641
15°	15992	15308	14867
20°	15735	14639	13904
25°	15471	13881	12975
30°	15105	13103	11779
35°	14747	12254	10730
40°	14389	11377	9516
45°	13967	10392	8416
50°	13536	9399	7340
55°	13095	8329	6303
60°	12581	7201	5231
65°	12000	6052	4768
70°	11301	4985	4381
75°	10449	4548	4086
80°	9224	4063	3719
85°	7243	3205	3205



TEST NUMBER: P331697-940

CATALOG NUMBER: S122RDIP-S675D925U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.2	1.9
10°-20°	258.5	5.1
20°-30°	363.0	7.2
30°-40°	395.9	7.9
40°-50°	364.0	7.2
50°-60°	285.9	5.7
60°-70°	186.4	3.7
70°-80°	96.1	1.9
80°-90°	29.1	0.6
90°-100°	66.8	1.3
100°-110°	207.5	4.1
110°-120°	354.7	7.1
120°-130°	466.5	9.3
130°-140°	523.6	10.4
140°-150°	513.4	10.2
150°-160°	430.6	8.6
160°-170°	285.6	5.7
170°-180°	99.8	2.0
0°-30°	715.7	14.3
0°-40°	1111.6	22.1
0°-60°	1761.4	35.1
0°-90°	2073.1	41.3
90°-120°	629.1	12.5
90°-150°	2132.6	42.5
90°-180°	2949.0	58.7
0°-180°	5021.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1006	1001	990	997	995	95
15°	957	946	916	899	889	269
25°	868	838	779	743	728	399
35°	748	700	622	566	544	468
45°	612	549	455	393	369	472
55°	465	393	296	243	224	416
65°	314	240	158	129	125	311
75°	168	106	73	67	66	177
85°	39	21	17	17	17	46
90°	1	12	31	30	30	4
95°	46	55	57	57	55	53
105°	191	194	196	197	198	202
115°	356	361	360	358	356	352
125°	518	525	523	521	520	463
135°	670	679	682	681	678	517
145°	813	820	825	826	822	508
155°	930	933	935	939	937	428
165°	1012	1011	1011	1017	1013	285
175°	1053	1050	1048	1054	1049	100
180°	1054	1054	1054	1054	1054	



TEST NUMBER: P331697-940

CATALOG NUMBER: S122RDIP-S675D925U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1009.5	1008.7	1007.9	1007.1	1006.3	1005.0	1003.2	1001.4	999.7	997.9	999.5
5°	1005.8	1004.9	1003.9	1002.8	1001.8	1000.1	997.4	994.8	992.1	989.5	991.3
7.5°	995.5	994.3	993.0	991.8	990.5	988.3	985.3	982.2	979.1	976.1	976.5
10°	986.8	985.3	983.9	982.5	981.1	978.4	974.3	970.3	966.3	962.2	961.6
12.5°	975.8	974.1	972.3	970.6	968.8	965.5	960.3	955.1	949.9	944.7	943.6
15°	956.7	954.5	952.3	950.0	947.8	943.3	936.4	929.5	922.7	915.8	912.0
17.5°	933.3	929.9	926.5	923.0	919.6	913.6	904.7	895.9	887.1	878.2	873.7
20°	915.8	911.7	907.7	903.7	899.6	892.5	882.3	872.3	862.2	852.0	846.9
22.5°	896.8	892.3	887.8	883.2	878.7	870.8	859.3	847.9	836.5	825.1	818.6
25°	868.4	861.9	855.5	849.0	842.6	832.6	819.3	805.9	792.6	779.2	770.9
27.5°	834.2	827.2	820.1	813.1	806.0	795.0	780.0	764.9	749.8	734.8	725.1
30°	810.2	802.5	794.8	787.1	779.4	767.5	751.3	735.1	718.9	702.8	692.4
32.5°	786.8	777.8	768.9	759.9	750.9	738.2	721.7	705.2	688.7	672.2	660.4
35°	748.2	738.0	727.6	717.3	707.0	692.9	675.1	657.4	639.5	621.7	608.9
37.5°	709.7	698.3	687.0	675.6	664.3	649.2	630.3	611.3	592.3	573.3	559.3
40°	682.7	670.6	658.4	646.3	634.2	618.3	598.7	579.1	559.5	539.8	525.5
42.5°	655.1	642.3	629.5	616.7	604.0	587.4	567.1	546.9	526.6	506.3	491.4
45°	611.7	598.2	584.6	571.1	557.5	540.1	518.9	497.7	476.4	455.1	440.8
47.5°	569.4	555.1	540.7	526.4	512.0	493.9	472.0	450.0	428.1	406.2	391.9
50°	538.9	524.5	510.1	495.8	481.4	463.2	440.9	418.7	396.4	374.2	360.2
52.5°	509.1	494.0	479.0	464.0	449.0	430.6	408.8	387.1	365.3	343.6	330.1
55°	465.2	449.4	433.6	417.9	402.1	383.3	361.4	339.6	317.7	295.9	283.7
57.5°	420.2	404.0	387.8	371.7	355.4	336.9	315.8	294.9	273.8	252.9	241.7
60°	389.6	373.4	357.2	341.1	324.9	306.4	285.5	264.7	243.9	223.0	212.7
62.5°	359.7	343.6	327.3	311.2	295.0	277.0	257.2	237.3	217.4	197.5	187.7
65°	314.1	297.7	281.2	264.9	248.5	231.2	213.0	194.8	176.6	158.4	151.5
67.5°	270.0	253.7	237.5	221.2	204.9	188.6	172.2	155.9	139.5	123.1	119.9
70°	239.4	223.6	207.9	192.1	176.3	161.4	147.5	133.5	119.6	105.6	103.5
72.5°	210.3	195.1	180.0	164.9	149.7	136.6	125.4	114.1	103.0	91.8	90.1
75°	167.5	153.4	139.2	125.0	110.8	100.3	93.5	86.6	79.7	72.9	71.4
77.5°	125.5	113.0	100.6	88.2	75.8	67.9	64.6	61.3	58.0	54.7	53.8
80°	99.2	88.9	78.6	68.3	58.0	51.8	49.8	47.7	45.7	43.7	42.9
82.5°	75.2	67.1	59.1	51.0	43.0	38.3	36.9	35.5	34.2	32.8	32.3
85°	39.1	34.9	30.7	26.4	22.1	19.7	19.1	18.5	17.9	17.3	17.3
87.5°	11.9	11.0	10.2	9.4	8.6	8.6	9.5	10.3	11.1	12.0	11.8
90°	0.9	3.3	5.6	8.0	10.3	13.7	18.1	22.5	26.8	31.1	30.8
92.5°	15.9	17.6	19.4	21.0	22.8	24.2	25.2	26.2	27.3	28.3	28.4
95°	46.3	48.2	50.2	52.2	54.2	55.4	55.7	56.2	56.5	57.0	57.0
97.5°	84.5	86.3	88.0	89.8	91.5	92.7	93.5	94.3	95.0	95.8	95.8
100°	113.0	114.6	116.2	117.8	119.3	120.5	121.0	121.6	122.3	122.8	122.8
102.5°	142.9	144.2	145.4	146.7	147.9	149.0	149.7	150.5	151.2	152.0	152.1
105°	191.4	191.9	192.5	193.1	193.7	194.2	194.6	195.0	195.4	195.7	196.2
107.5°	240.0	240.9	241.8	242.7	243.6	244.0	244.0	244.0	244.0	244.0	244.2
110°	271.4	272.6	273.8	275.0	276.2	276.8	276.8	276.8	276.8	276.8	276.8



TEST NUMBER: P331697-940

CATALOG NUMBER: S122RDIP-S675D925U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	305.6	306.7	308.0	309.2	310.3	310.9	310.7	310.5	310.4	310.2	309.8
115°	356.0	357.1	358.3	359.5	360.7	361.1	360.7	360.3	359.9	359.5	359.4
117.5°	406.2	407.7	409.3	410.9	412.5	412.7	411.6	410.5	409.4	408.3	407.8
120°	439.6	441.2	442.7	444.3	445.9	445.9	444.3	442.7	441.2	439.6	439.6
122.5°	470.2	472.1	474.0	475.9	477.8	478.2	477.1	476.0	474.9	473.8	473.3
125°	517.9	519.7	521.5	523.3	525.0	525.7	525.0	524.4	523.9	523.3	522.6
127.5°	564.4	566.6	568.9	571.1	573.4	574.2	573.5	572.7	572.0	571.3	570.6
130°	593.5	596.1	598.7	601.3	603.9	604.9	604.5	604.1	603.8	603.3	603.0
132.5°	626.3	628.4	630.5	632.6	634.7	635.8	635.9	636.0	636.0	636.1	635.3
135°	670.1	672.3	674.4	676.6	678.8	680.1	680.5	680.8	681.3	681.6	681.4
137.5°	716.2	717.9	719.7	721.5	723.3	724.4	725.0	725.5	726.0	726.5	726.4
140°	744.0	745.7	747.5	749.3	751.1	752.4	753.4	754.4	755.5	756.4	756.4
142.5°	772.4	774.2	776.0	777.8	779.5	780.8	781.4	782.1	782.7	783.5	783.6
145°	813.3	814.8	816.1	817.5	818.9	820.2	821.4	822.5	823.8	824.9	825.1
147.5°	849.8	851.5	853.2	854.8	856.5	857.7	858.5	859.3	860.1	860.9	861.3
150°	874.8	875.9	877.1	878.3	879.5	880.5	881.3	882.1	882.9	883.7	884.2
152.5°	896.8	898.0	899.2	900.4	901.6	902.7	903.6	904.6	905.4	906.4	907.2
155°	930.0	930.5	931.1	931.7	932.3	932.9	933.5	934.1	934.7	935.2	936.3
157.5°	958.2	958.6	959.0	959.4	959.8	960.2	960.6	960.9	961.3	961.6	963.0
160°	975.4	975.7	976.1	976.5	976.9	977.2	977.4	977.6	977.8	977.9	979.2
162.5°	991.0	991.0	991.1	991.2	991.3	991.4	991.7	991.8	992.0	992.2	993.5
165°	1011.8	1011.6	1011.4	1011.2	1011.0	1010.9	1010.9	1010.9	1010.9	1010.9	1012.3
167.5°	1029.2	1028.7	1028.1	1027.4	1026.9	1026.5	1026.5	1026.4	1026.4	1026.4	1027.8
170°	1038.5	1037.9	1037.3	1036.7	1036.1	1035.7	1035.5	1035.4	1035.1	1034.9	1036.3
172.5°	1044.9	1044.3	1043.7	1043.1	1042.5	1042.1	1042.0	1041.7	1041.5	1041.3	1042.8
175°	1052.8	1052.1	1051.5	1051.0	1050.3	1049.9	1049.5	1049.1	1048.7	1048.3	1049.6
177.5°	1056.0	1055.4	1055.0	1054.5	1054.0	1053.6	1053.3	1053.0	1052.7	1052.4	1053.3
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331697-940

CATALOG NUMBER: S122RDIP-S675D925U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1001.1	1002.7	1004.3	1005.0	1004.7	1004.3	1004.1	1003.7
5°	993.1	995.0	996.8	997.4	996.8	996.1	995.6	995.0
7.5°	977.0	977.6	978.1	977.9	976.8	975.8	974.7	973.7
10°	961.0	960.4	959.7	958.9	957.6	956.4	955.2	954.0
12.5°	942.5	941.5	940.3	938.8	936.7	934.8	932.7	930.7
15°	908.1	904.2	900.4	897.4	895.5	893.4	891.4	889.4
17.5°	869.2	864.5	860.0	856.0	852.5	849.0	845.5	842.0
20°	842.0	836.9	831.8	827.1	822.6	818.1	813.7	809.2
22.5°	812.1	805.6	799.1	794.2	790.8	787.5	784.2	780.9
25°	762.6	754.3	746.0	740.4	737.4	734.3	731.3	728.3
27.5°	715.4	705.8	696.2	688.8	684.0	679.2	674.4	669.6
30°	682.2	671.8	661.5	653.6	648.1	642.7	637.2	631.8
32.5°	648.6	636.9	625.1	616.6	611.4	606.4	601.2	596.1
35°	596.3	583.5	570.8	562.1	557.7	553.2	548.8	544.4
37.5°	545.2	531.2	517.2	507.6	502.5	497.4	492.3	487.2
40°	511.0	496.7	482.3	472.5	467.3	462.0	456.7	451.5
42.5°	476.6	461.7	446.9	436.9	431.9	426.8	421.7	416.5
45°	426.4	412.1	397.7	388.1	383.3	378.4	373.5	368.6
47.5°	377.6	363.4	349.0	339.7	335.3	330.9	326.5	322.1
50°	346.3	332.3	318.3	309.2	305.0	300.7	296.5	292.2
52.5°	316.6	303.1	289.6	281.0	277.1	273.1	269.2	265.3
55°	271.6	259.4	247.3	239.3	235.5	231.6	227.7	223.9
57.5°	230.6	219.5	208.4	201.2	198.0	194.7	191.5	188.2
60°	202.4	192.1	181.7	175.0	171.7	168.5	165.2	162.0
62.5°	177.9	168.0	158.2	152.3	150.3	148.5	146.5	144.5
65°	144.6	137.8	130.9	127.2	126.5	125.9	125.3	124.8
67.5°	116.7	113.6	110.5	108.5	107.9	107.3	106.6	105.9
70°	101.6	99.5	97.5	96.1	95.2	94.4	93.6	92.8
72.5°	88.4	86.7	85.0	83.9	83.4	82.9	82.4	81.9
75°	70.0	68.6	67.1	66.3	66.2	66.0	65.7	65.5
77.5°	53.0	52.2	51.4	50.8	50.5	50.2	49.8	49.5
80°	42.1	41.3	40.5	40.0	40.0	40.0	40.0	40.0
82.5°	31.8	31.3	30.9	30.6	30.6	30.6	30.6	30.6
85°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3
87.5°	11.6	11.3	11.1	11.0	11.1	11.1	11.1	11.1
90°	30.3	30.0	29.6	29.4	29.7	29.9	30.1	30.2
92.5°	28.4	28.5	28.6	28.7	28.7	28.7	28.8	28.8
95°	57.0	57.0	57.0	56.7	56.4	56.0	55.6	55.2
97.5°	95.8	95.8	95.8	95.8	95.7	95.7	95.6	95.6
100°	122.8	122.8	122.8	122.7	122.5	122.3	122.1	121.9
102.5°	152.3	152.5	152.7	152.6	152.4	152.2	152.0	151.9
105°	196.5	197.0	197.3	197.5	197.5	197.5	197.5	197.5
107.5°	244.3	244.5	244.6	244.2	243.3	242.5	241.6	240.6
110°	276.8	276.8	276.8	276.4	275.9	275.3	274.6	274.1





TEST NUMBER: P331697-940

CATALOG NUMBER: S122RDIP-S675D925U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	309.2	308.8	308.4	307.8	307.5	307.0	306.6	306.1
115°	359.1	358.9	358.7	358.3	357.8	357.1	356.5	356.0
117.5°	407.3	406.9	406.4	405.8	405.3	404.7	404.0	403.5
120°	439.6	439.6	439.6	439.3	438.7	438.1	437.6	436.9
122.5°	472.8	472.3	471.9	471.4	471.0	470.6	470.1	469.7
125°	522.1	521.5	520.8	520.5	520.3	520.0	519.9	519.7
127.5°	569.9	569.2	568.5	567.8	567.1	566.5	565.9	565.3
130°	602.5	602.2	601.7	601.2	600.4	599.6	598.8	598.0
132.5°	634.4	633.5	632.6	631.9	631.2	630.6	630.0	629.4
135°	681.3	681.1	680.8	680.5	679.8	679.3	678.7	678.1
137.5°	726.2	726.0	725.9	725.4	724.6	723.8	723.0	722.2
140°	756.4	756.4	756.4	756.0	755.2	754.4	753.7	752.9
142.5°	783.8	783.9	784.1	783.8	783.0	782.2	781.4	780.6
145°	825.3	825.5	825.7	825.5	824.7	823.9	823.0	822.2
147.5°	861.7	862.2	862.6	862.5	861.7	860.9	860.2	859.4
150°	884.8	885.5	886.0	886.0	885.5	884.8	884.2	883.7
152.5°	907.9	908.7	909.5	909.5	908.7	907.9	907.2	906.4
155°	937.3	938.3	939.2	939.4	938.8	938.3	937.6	937.0
157.5°	964.3	965.6	967.0	967.1	966.3	965.3	964.3	963.4
160°	980.3	981.5	982.8	982.9	982.1	981.3	980.5	979.7
162.5°	994.9	996.2	997.6	997.8	996.8	995.9	995.0	994.0
165°	1013.7	1015.0	1016.5	1016.6	1015.7	1014.7	1013.7	1012.7
167.5°	1029.1	1030.6	1031.9	1032.1	1031.1	1030.0	1029.0	1028.0
170°	1037.7	1039.1	1040.4	1040.5	1039.4	1038.2	1037.0	1035.8
172.5°	1044.1	1045.5	1046.9	1047.0	1045.8	1044.6	1043.4	1042.2
175°	1051.1	1052.4	1053.8	1053.9	1052.8	1051.5	1050.3	1049.2
177.5°	1054.3	1055.3	1056.1	1056.1	1055.3	1054.3	1053.3	1052.4
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5

(END OF REPORT)