

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331678-830

Luminaire Tested: **S122RDIP-S675D330U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331678-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S675D330U830-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3422.1 lumens  
Efficiency: N/A  
Efficacy: 97.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331678-830

CATALOG NUMBER: S122RDIP-S675D330U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331678-830

CATALOG NUMBER: S122RDIP-S675D330U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69	64								
1	102	97	94	90	95	92	88	85	81	78	76	71	69	68	62	61	59	55								
2	93	86	80	75	87	81	76	71	72	68	64	63	60	57	55	53	51	47								
3	85	76	69	63	80	72	65	60	64	59	55	56	53	49	49	47	44	41								
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	45	41	39	35								
5	72	61	53	47	68	58	50	45	51	46	41	46	41	38	41	37	34	31								
6	67	55	47	41	63	52	45	39	47	41	36	42	37	33	37	33	30	28								
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27	25								
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	25	22								
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22	20								
10	50	38	31	26	48	37	30	26	33	28	24	30	25	22	27	23	20	19								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17166	17166	17166
5°	17232	16951	17045
10°	17100	16674	16531
15°	16904	16181	15714
20°	16632	15474	14698
25°	16352	14672	13714
30°	15966	13848	12450
35°	15589	12952	11341
40°	15209	12026	10058
45°	14764	10985	8896
50°	14307	9934	7759
55°	13841	8802	6663
60°	13298	7611	5532
65°	12684	6395	5039
70°	11948	5268	4631
75°	11042	4803	4323
80°	9754	4296	3933
85°	7669	3390	3390



TEST NUMBER: P331678-830

CATALOG NUMBER: S122RDIP-S675D330U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.5	2.9
10°-20°	273.3	8.0
20°-30°	383.7	11.2
30°-40°	418.4	12.2
40°-50°	384.7	11.2
50°-60°	302.2	8.8
60°-70°	197.0	5.8
70°-80°	101.6	3.0
80°-90°	27.4	0.8
90°-100°	14.0	0.4
100°-110°	51.5	1.5
110°-120°	137.7	4.0
120°-130°	227.3	6.6
130°-140°	241.8	7.1
140°-150°	224.7	6.6
150°-160°	180.7	5.3
160°-170°	116.4	3.4
170°-180°	40.1	1.2
0°-30°	756.5	22.1
0°-40°	1174.9	34.3
0°-60°	1861.8	54.4
0°-90°	2187.8	63.9
90°-120°	203.3	5.9
90°-150°	897.1	26.2
90°-180°	1234.0	36.1
0°-180°	3422.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1063	1063	1063	1063	1063	
5°	1063	1058	1046	1054	1052	101
15°	1011	999	968	950	940	285
25°	918	885	824	786	770	422
35°	791	740	657	599	575	495
45°	647	580	481	415	390	499
55°	492	415	313	257	237	439
65°	332	254	167	136	132	329
75°	177	112	77	71	69	187
85°	41	22	18	18	18	49
90°	0	4	6	8	8	3
95°	20	10	12	13	13	24
105°	93	97	19	22	23	99
115°	175	181	188	54	25	172
125°	248	252	258	260	260	221
135°	307	311	314	317	317	237
145°	356	356	360	362	361	222
155°	392	389	392	394	392	180
165°	413	411	412	414	412	117
175°	422	420	421	422	420	40
180°	421	421	421	421	421	



TEST NUMBER: P331678-830

CATALOG NUMBER: S122RDIP-S675D330U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1067.1	1066.2	1065.4	1064.5	1063.7	1062.2	1060.4	1058.5	1056.7	1054.8	1056.5
5°	1063.2	1062.2	1061.1	1060.0	1058.9	1057.1	1054.2	1051.5	1048.7	1045.9	1047.8
7.5°	1052.3	1050.9	1049.6	1048.3	1047.0	1044.6	1041.4	1038.2	1034.9	1031.7	1032.2
10°	1043.0	1041.5	1040.0	1038.5	1037.0	1034.2	1029.8	1025.6	1021.3	1017.0	1016.4
12.5°	1031.4	1029.6	1027.7	1026.0	1024.1	1020.5	1015.0	1009.6	1004.0	998.5	997.4
15°	1011.3	1008.9	1006.5	1004.2	1001.8	997.0	989.8	982.5	975.2	968.0	963.9
17.5°	986.5	982.9	979.3	975.6	972.0	965.6	956.3	947.0	937.6	928.3	923.5
20°	968.0	963.7	959.4	955.2	950.8	943.4	932.6	922.0	911.3	900.6	895.2
22.5°	947.9	943.2	938.4	933.6	928.8	920.4	908.3	896.3	884.2	872.1	865.3
25°	917.9	911.1	904.3	897.4	890.6	880.1	866.0	851.9	837.7	823.6	814.8
27.5°	881.7	874.3	866.9	859.4	852.0	840.3	824.4	808.5	792.6	776.7	766.5
30°	856.4	848.2	840.1	832.0	823.9	811.2	794.1	777.0	759.9	742.8	731.9
32.5°	831.7	822.2	812.8	803.2	793.7	780.2	762.8	745.4	727.9	710.5	698.0
35°	790.9	780.0	769.1	758.2	747.3	732.4	713.6	694.8	676.0	657.1	643.7
37.5°	750.2	738.1	726.1	714.2	702.2	686.2	666.2	646.1	626.0	606.0	591.2
40°	721.6	708.8	696.0	683.2	670.3	653.6	632.8	612.1	591.4	570.6	555.4
42.5°	692.4	678.9	665.3	651.9	638.4	620.9	599.5	578.1	556.6	535.2	519.4
45°	646.6	632.3	617.9	603.6	589.3	570.9	548.5	526.0	503.5	481.1	465.9
47.5°	601.9	586.7	571.6	556.4	541.2	522.1	498.9	475.7	452.5	429.3	414.2
50°	569.6	554.4	539.2	524.1	508.9	489.6	466.0	442.5	419.0	395.5	380.7
52.5°	538.1	522.2	506.3	490.5	474.6	455.2	432.2	409.2	386.2	363.2	348.9
55°	491.7	475.0	458.4	441.7	425.0	405.1	382.0	358.9	335.8	312.7	299.9
57.5°	444.1	427.1	409.9	392.9	375.7	356.1	333.8	311.7	289.5	267.3	255.5
60°	411.8	394.7	377.6	360.5	343.4	323.9	301.8	279.7	257.8	235.7	224.8
62.5°	380.2	363.2	346.0	328.9	311.8	292.8	271.8	250.8	229.8	208.8	198.4
65°	332.0	314.6	297.3	280.0	262.7	244.4	225.2	205.9	186.6	167.4	160.1
67.5°	285.4	268.2	251.0	233.8	216.6	199.3	182.0	164.8	147.4	130.1	126.8
70°	253.1	236.4	219.7	203.0	186.3	170.6	155.9	141.1	126.4	111.6	109.4
72.5°	222.3	206.2	190.3	174.3	158.3	144.4	132.5	120.6	108.9	97.0	95.2
75°	177.0	162.1	147.1	132.1	117.2	106.0	98.8	91.5	84.3	77.0	75.5
77.5°	132.6	119.4	106.3	93.2	80.1	71.7	68.2	64.8	61.3	57.8	56.8
80°	104.9	94.0	83.0	72.2	61.3	54.8	52.6	50.4	48.4	46.2	45.3
82.5°	79.5	71.0	62.5	53.9	45.4	40.4	39.0	37.5	36.1	34.7	34.1
85°	41.4	36.9	32.4	27.9	23.4	20.8	20.2	19.6	18.9	18.3	18.3
87.5°	12.3	11.1	9.9	8.8	7.5	7.0	7.1	7.2	7.3	7.4	7.3
90°	0.3	1.0	1.8	2.5	3.3	4.0	4.4	5.0	5.6	6.1	6.4
92.5°	6.1	6.1	6.0	5.9	5.8	6.0	6.2	6.5	6.8	7.1	7.3
95°	19.8	17.5	15.4	13.1	10.8	10.0	10.5	10.9	11.4	11.9	12.3
97.5°	39.3	33.0	26.7	20.5	14.1	11.5	12.6	13.7	14.8	15.9	16.2
100°	53.9	44.7	35.3	26.1	16.9	12.7	13.9	15.1	16.2	17.3	17.9
102.5°	70.0	68.1	66.1	64.2	62.2	56.4	46.8	37.1	27.5	17.8	18.6
105°	92.7	94.6	96.7	98.8	100.8	92.6	74.1	55.6	37.0	18.6	19.3
107.5°	118.4	120.1	121.7	123.4	125.0	114.7	92.6	70.4	48.2	26.0	25.3
110°	135.0	136.4	137.9	139.3	140.7	131.6	112.1	92.5	72.9	53.3	46.6



TEST NUMBER: P331678-830

CATALOG NUMBER: S122RDIP-S675D330U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	150.6	151.8	153.2	154.4	155.6	153.8	149.0	144.2	139.3	134.5	109.8
115°	175.2	176.3	177.6	178.7	179.8	181.3	182.9	184.6	186.3	188.0	156.7
117.5°	197.3	198.5	199.8	201.1	202.4	203.6	204.8	205.9	207.1	208.3	200.7
120°	213.3	214.3	215.4	216.4	217.4	218.5	219.7	220.9	222.2	223.4	224.2
122.5°	227.0	228.1	229.1	230.2	231.3	232.4	233.8	235.1	236.5	237.8	238.3
125°	247.8	248.6	249.5	250.4	251.3	252.4	253.6	255.0	256.2	257.5	258.0
127.5°	266.6	267.6	268.5	269.6	270.5	271.5	272.4	273.4	274.4	275.3	276.0
130°	278.5	279.7	280.7	281.8	282.9	283.8	284.6	285.3	286.1	286.8	287.5
132.5°	290.8	291.6	292.6	293.5	294.5	295.2	296.0	296.7	297.5	298.2	298.9
135°	306.6	307.6	308.8	309.8	310.9	311.8	312.4	313.0	313.6	314.2	314.9
137.5°	322.6	323.4	324.1	324.9	325.6	326.4	327.1	327.7	328.5	329.1	329.8
140°	333.1	333.7	334.1	334.7	335.3	335.9	336.7	337.4	338.2	338.8	339.5
142.5°	341.9	342.3	342.8	343.4	343.8	344.5	345.3	346.2	347.0	347.9	348.5
145°	355.6	355.6	355.5	355.4	355.3	355.9	357.0	358.3	359.4	360.5	361.0
147.5°	367.7	367.4	367.1	366.8	366.6	367.0	368.2	369.4	370.5	371.6	371.9
150°	375.4	374.9	374.5	374.0	373.5	373.9	374.9	376.1	377.1	378.2	378.6
152.5°	382.0	381.5	381.0	380.4	379.9	380.1	381.2	382.2	383.2	384.3	384.7
155°	391.6	391.0	390.4	389.7	389.2	389.3	390.1	390.9	391.7	392.5	392.9
157.5°	399.1	398.6	398.0	397.6	397.0	397.1	397.7	398.2	398.8	399.4	399.8
160°	403.5	403.1	402.7	402.3	401.9	401.9	402.3	402.7	403.1	403.5	403.9
162.5°	407.4	407.0	406.6	406.1	405.8	405.8	406.0	406.4	406.8	407.2	407.6
165°	412.6	412.3	411.8	411.4	411.0	410.9	411.1	411.3	411.5	411.7	412.2
167.5°	416.5	416.1	415.8	415.3	414.9	414.8	415.0	415.2	415.4	415.6	416.0
170°	418.8	418.3	417.9	417.5	417.1	417.0	417.1	417.3	417.4	417.5	418.0
172.5°	420.2	419.8	419.3	419.0	418.6	418.4	418.6	418.7	418.9	419.0	419.4
175°	422.1	421.6	421.1	420.7	420.2	420.0	420.2	420.3	420.5	420.6	421.0
177.5°	422.4	422.0	421.6	421.2	420.8	420.8	420.8	420.8	420.8	420.9	421.3
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1



TEST NUMBER: P331678-830

CATALOG NUMBER: S122RDIP-S675D330U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1058.2	1059.9	1061.6	1062.2	1062.0	1061.6	1061.3	1060.9
5°	1049.7	1051.7	1053.6	1054.2	1053.6	1052.9	1052.3	1051.7
7.5°	1032.7	1033.3	1033.9	1033.6	1032.5	1031.4	1030.3	1029.2
10°	1015.8	1015.1	1014.5	1013.5	1012.2	1011.0	1009.7	1008.3
12.5°	996.3	995.1	993.9	992.3	990.1	988.1	985.9	983.7
15°	959.9	955.7	951.7	948.6	946.5	944.3	942.2	940.1
17.5°	918.7	913.8	909.0	904.7	901.1	897.4	893.7	890.0
20°	889.9	884.6	879.2	874.2	869.5	864.8	860.1	855.4
22.5°	858.4	851.5	844.6	839.4	835.8	832.4	828.9	825.4
25°	806.1	797.3	788.5	782.6	779.4	776.2	773.0	769.8
27.5°	756.2	746.0	735.8	728.1	723.0	717.9	712.8	707.8
30°	721.0	710.1	699.2	690.9	685.0	679.3	673.5	667.8
32.5°	685.6	673.2	660.7	651.8	646.3	640.9	635.5	630.1
35°	630.3	616.8	603.3	594.2	589.5	584.8	580.1	575.4
37.5°	576.3	561.5	546.7	536.5	531.1	525.8	520.4	515.0
40°	540.2	525.0	509.8	499.5	493.9	488.3	482.8	477.2
42.5°	503.8	488.0	472.4	461.8	456.5	451.1	445.7	440.3
45°	450.7	435.5	420.4	410.2	405.1	399.9	394.8	389.6
47.5°	399.2	384.1	368.9	359.1	354.4	349.8	345.1	340.4
50°	366.0	351.2	336.5	326.8	322.3	317.8	313.4	308.9
52.5°	334.7	320.4	306.1	297.0	292.8	288.7	284.6	280.4
55°	287.1	274.2	261.4	253.0	248.9	244.8	240.7	236.7
57.5°	243.7	232.1	220.3	212.6	209.2	205.9	202.4	199.0
60°	214.0	203.0	192.1	184.9	181.5	178.1	174.7	171.3
62.5°	188.0	177.6	167.2	161.0	158.9	156.9	154.9	152.8
65°	152.9	145.6	138.4	134.4	133.7	133.1	132.4	131.9
67.5°	123.4	120.1	116.8	114.7	114.0	113.4	112.7	112.0
70°	107.4	105.2	103.0	101.6	100.7	99.8	99.0	98.1
72.5°	93.4	91.6	89.8	88.7	88.1	87.7	87.1	86.6
75°	74.0	72.5	71.0	70.1	69.9	69.7	69.5	69.3
77.5°	56.0	55.1	54.3	53.7	53.3	53.1	52.7	52.3
80°	44.5	43.6	42.8	42.3	42.3	42.3	42.3	42.3
82.5°	33.6	33.1	32.6	32.3	32.3	32.3	32.3	32.3
85°	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	7.2	7.1	7.0	6.9	7.0	7.0	7.0	7.1
90°	6.8	7.1	7.4	7.7	7.8	7.9	8.1	8.2
92.5°	7.4	7.6	7.7	7.9	8.0	8.1	8.1	8.2
95°	12.5	12.9	13.2	13.4	13.3	13.2	13.2	13.1
97.5°	16.5	16.7	17.0	17.2	17.2	17.3	17.4	17.5
100°	18.5	19.0	19.5	19.9	20.0	20.2	20.3	20.5
102.5°	19.2	20.0	20.6	21.1	21.3	21.5	21.7	21.9
105°	20.1	20.8	21.6	22.1	22.3	22.6	22.9	23.2
107.5°	24.5	23.8	23.0	22.7	23.0	23.3	23.6	23.8
110°	39.8	33.0	26.2	23.0	23.3	23.6	23.8	24.0





TEST NUMBER: P331678-830

CATALOG NUMBER: S122RDIP-S675D330U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	85.1	60.4	35.7	23.5	23.7	23.8	24.1	24.3
115°	125.4	94.0	62.6	44.5	39.6	34.8	29.9	25.0
117.5°	193.1	185.5	178.0	166.2	150.1	134.1	118.1	102.1
120°	225.0	225.8	226.6	222.4	213.3	204.2	195.0	185.9
122.5°	238.7	239.2	239.7	239.0	237.3	235.5	233.8	232.0
125°	258.4	258.9	259.4	259.8	260.0	260.1	260.3	260.5
127.5°	276.7	277.4	278.1	278.4	278.5	278.5	278.5	278.6
130°	288.2	289.0	289.7	290.1	290.0	289.9	289.9	289.8
132.5°	299.5	300.1	300.8	301.0	301.0	301.0	300.9	300.8
135°	315.6	316.2	316.9	317.2	317.1	316.9	316.8	316.6
137.5°	330.5	331.1	331.8	332.0	331.8	331.6	331.3	331.1
140°	340.1	340.7	341.3	341.5	341.1	340.8	340.4	340.1
142.5°	349.0	349.6	350.2	350.2	349.9	349.6	349.2	348.8
145°	361.5	361.9	362.4	362.5	362.1	361.8	361.5	361.1
147.5°	372.3	372.7	373.1	373.1	372.8	372.5	372.2	371.9
150°	379.0	379.4	379.8	379.8	379.6	379.2	378.8	378.5
152.5°	385.1	385.5	385.9	385.9	385.4	385.0	384.6	384.1
155°	393.3	393.7	394.2	394.1	393.5	393.0	392.5	391.9
157.5°	400.3	400.8	401.1	401.1	400.6	400.1	399.5	399.1
160°	404.4	404.7	405.1	405.1	404.6	404.2	403.7	403.2
162.5°	408.0	408.5	409.0	409.0	408.3	407.7	407.2	406.6
165°	412.6	413.1	413.6	413.6	413.1	412.6	412.2	411.7
167.5°	416.5	417.0	417.5	417.4	416.8	416.1	415.6	414.9
170°	418.5	419.0	419.4	419.3	418.8	418.1	417.5	416.9
172.5°	419.9	420.4	420.8	420.8	420.2	419.6	419.0	418.4
175°	421.5	422.0	422.4	422.4	421.7	421.0	420.3	419.6
177.5°	421.7	422.1	422.4	422.4	421.9	421.4	420.9	420.5
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1

(END OF REPORT)