

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331463-930

Luminaire Tested: **S122DIP-S1005D1080U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331463-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S1005D1080U930-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6448.4 lumens  
Efficiency: N/A  
Efficacy: 89.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331463-930

CATALOG NUMBER: S122DIP-S1005D1080U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331463-930

CATALOG NUMBER: S122DIP-S1005D1080U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	47	36	29	24	31	25	22	27	22	19	22	19	17	14
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20980	20980	20980
5°	21060	20757	20879
10°	20935	20546	20649
15°	20677	20279	20259
20°	20309	19880	19859
25°	19946	19388	19388
30°	19475	18938	18776
35°	19036	18398	18126
40°	18487	17856	17513
45°	17945	17317	16890
50°	17357	16759	16164
55°	16743	16110	15510
60°	16059	15332	14767
65°	15320	14560	13891
70°	14389	13624	12977
75°	13094	12545	12239
80°	11623	11269	10693
85°	9485	9040	8096



TEST NUMBER: P331463-930

CATALOG NUMBER: S122DIP-S1005D1080U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.2	1.9
10°-20°	343.8	5.3
20°-30°	505.4	7.8
30°-40°	587.0	9.1
40°-50°	586.4	9.1
50°-60°	511.4	7.9
60°-70°	378.1	5.9
70°-80°	214.2	3.3
80°-90°	62.1	1.0
90°-100°	71.1	1.1
100°-110°	220.9	3.4
110°-120°	377.5	5.9
120°-130°	496.5	7.7
130°-140°	557.2	8.6
140°-150°	546.4	8.5
150°-160°	458.3	7.1
160°-170°	304.0	4.7
170°-180°	106.2	1.6
0°-30°	971.4	15.1
0°-40°	1558.4	24.2
0°-60°	2656.1	41.2
0°-90°	3310.5	51.3
90°-120°	669.5	10.4
90°-150°	2269.5	35.2
90°-180°	3138.0	48.7
0°-180°	6448.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1299	1299	1299	1299	1299	
5°	1299	1294	1281	1290	1288	123
15°	1237	1229	1213	1218	1212	348
25°	1120	1109	1088	1090	1088	515
35°	966	953	933	926	920	603
45°	786	777	758	745	740	606
55°	595	587	572	558	551	532
65°	401	393	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	1	13	33	31	32	5
95°	49	58	61	60	59	56
105°	204	206	208	210	210	215
115°	379	384	383	382	379	375
125°	551	559	557	554	553	492
135°	713	723	726	724	722	551
145°	866	872	878	879	875	541
155°	990	992	995	1000	997	455
165°	1077	1076	1076	1082	1078	304
175°	1120	1118	1116	1122	1117	106
180°	1122	1122	1122	1122	1122	



TEST NUMBER: P331463-930

CATALOG NUMBER: S122DIP-S1005D1080U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1305.5	1304.3	1303.3	1302.1	1301.0	1299.3	1296.8	1294.4	1291.9	1289.5	1291.7
5°	1299.4	1298.4	1297.2	1296.1	1295.0	1292.9	1289.9	1286.8	1283.8	1280.7	1283.0
7.5°	1287.9	1286.2	1284.5	1282.8	1281.1	1278.6	1275.5	1272.4	1269.3	1266.2	1268.4
10°	1276.9	1275.0	1273.1	1271.1	1269.2	1266.6	1263.2	1259.9	1256.5	1253.2	1255.5
12.5°	1262.0	1260.2	1258.5	1256.8	1255.1	1252.5	1249.2	1245.9	1242.6	1239.3	1240.8
15°	1237.0	1235.3	1233.6	1232.0	1230.3	1227.7	1224.1	1220.4	1216.8	1213.2	1214.4
17.5°	1205.0	1203.3	1201.7	1200.0	1198.3	1195.6	1192.0	1188.3	1184.6	1181.0	1182.3
20°	1182.0	1180.3	1178.7	1177.0	1175.3	1172.6	1168.7	1164.8	1160.9	1157.0	1157.8
22.5°	1159.0	1156.7	1154.4	1152.0	1149.7	1146.7	1143.0	1139.4	1135.7	1132.0	1132.2
25°	1119.6	1117.3	1115.1	1112.9	1110.7	1107.2	1102.4	1097.7	1093.0	1088.3	1088.8
27.5°	1074.6	1072.5	1070.6	1068.5	1066.6	1063.7	1060.0	1056.2	1052.6	1048.8	1048.0
30°	1044.6	1042.4	1040.1	1037.9	1035.7	1032.5	1028.3	1024.2	1020.0	1015.8	1015.0
32.5°	1012.6	1010.8	1009.0	1007.2	1005.4	1002.4	998.0	993.6	989.2	984.8	983.3
35°	965.8	963.0	960.3	957.5	954.7	951.1	946.6	942.2	937.8	933.4	931.7
37.5°	913.1	910.7	908.2	905.8	903.4	899.9	895.4	891.0	886.6	882.2	880.0
40°	877.1	874.9	872.7	870.5	868.2	865.0	860.5	856.1	851.6	847.2	844.7
42.5°	842.1	839.9	837.7	835.5	833.2	829.9	825.5	821.0	816.6	812.1	809.4
45°	785.9	784.0	782.0	780.1	778.1	775.1	770.9	766.8	762.6	758.4	755.4
47.5°	729.9	728.1	726.3	724.5	722.6	719.5	715.2	710.9	706.5	702.2	699.0
50°	691.0	689.6	688.2	686.8	685.4	682.7	678.9	675.0	671.1	667.2	663.3
52.5°	653.0	651.2	649.3	647.5	645.6	642.9	639.2	635.5	631.9	628.3	625.0
55°	594.8	593.0	591.4	589.8	588.1	585.5	582.3	578.9	575.6	572.3	568.9
57.5°	536.3	534.9	533.6	532.3	530.9	528.5	524.8	521.1	517.5	513.8	510.5
60°	497.3	496.2	495.0	494.0	492.8	490.3	486.5	482.6	478.7	474.8	471.7
62.5°	459.3	457.5	455.8	454.0	452.2	449.8	446.8	443.8	440.8	437.8	435.0
65°	401.0	399.4	397.8	396.1	394.4	392.2	389.4	386.6	383.8	381.1	378.6
67.5°	341.9	340.6	339.2	337.9	336.6	334.6	332.1	329.6	327.1	324.7	322.7
70°	304.8	303.8	302.6	301.6	300.4	298.6	296.1	293.6	291.1	288.6	286.7
72.5°	266.8	265.8	264.6	263.6	262.4	261.1	259.5	257.9	256.2	254.6	252.7
75°	209.9	209.4	208.8	208.2	207.7	206.7	205.3	203.9	202.5	201.1	199.5
77.5°	158.9	158.0	157.0	156.1	155.2	154.4	153.8	153.3	152.7	152.2	151.3
80°	125.0	124.7	124.4	124.1	123.8	123.4	122.9	122.3	121.7	121.2	120.3
82.5°	92.9	92.9	92.9	92.8	92.7	92.5	92.2	91.9	91.6	91.2	90.2
85°	51.2	51.0	50.7	50.4	50.1	49.8	49.6	49.2	49.0	48.8	47.9
87.5°	18.2	18.3	18.3	18.3	18.4	18.7	19.2	19.6	20.1	20.6	19.9
90°	1.0	3.5	6.0	8.6	11.1	14.6	19.2	23.9	28.5	33.2	32.7
92.5°	16.9	18.7	20.5	22.4	24.3	25.8	26.8	28.0	29.0	30.1	30.2
95°	49.2	51.4	53.5	55.5	57.6	58.9	59.4	59.8	60.2	60.6	60.6
97.5°	90.0	91.8	93.7	95.6	97.3	98.7	99.5	100.3	101.1	101.9	101.9
100°	120.3	122.0	123.7	125.3	127.0	128.2	128.8	129.4	130.0	130.7	130.7
102.5°	152.1	153.4	154.8	156.1	157.5	158.6	159.4	160.1	160.9	161.8	161.9
105°	203.6	204.2	204.9	205.5	206.1	206.7	207.1	207.5	207.9	208.3	208.8
107.5°	255.5	256.4	257.4	258.3	259.2	259.7	259.7	259.7	259.7	259.7	259.8
110°	288.9	290.1	291.4	292.6	293.9	294.6	294.6	294.6	294.6	294.6	294.6



TEST NUMBER: P331463-930

CATALOG NUMBER: S122DIP-S1005D1080U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	325.2	326.4	327.8	329.0	330.3	330.8	330.6	330.4	330.3	330.1	329.6
115°	378.8	380.1	381.3	382.6	383.8	384.3	383.8	383.4	383.0	382.6	382.4
117.5°	432.2	433.9	435.6	437.2	439.0	439.2	438.1	436.8	435.7	434.5	434.0
120°	467.8	469.5	471.2	472.9	474.6	474.6	472.9	471.2	469.5	467.8	467.8
122.5°	500.4	502.5	504.4	506.5	508.5	508.9	507.8	506.5	505.4	504.2	503.7
125°	551.1	553.1	555.0	556.8	558.7	559.4	558.7	558.2	557.5	556.8	556.2
127.5°	600.6	603.0	605.4	607.8	610.2	611.1	610.3	609.5	608.8	608.0	607.2
130°	631.7	634.4	637.2	639.8	642.6	643.8	643.4	642.9	642.5	642.1	641.6
132.5°	666.5	668.8	671.0	673.2	675.5	676.6	676.7	676.8	676.9	676.9	676.0
135°	713.1	715.4	717.8	720.1	722.4	723.7	724.1	724.6	725.0	725.5	725.2
137.5°	762.1	764.1	766.0	767.8	769.7	770.9	771.5	772.1	772.6	773.1	773.0
140°	791.7	793.6	795.5	797.4	799.3	800.8	801.8	802.9	804.0	804.9	804.9
142.5°	822.1	823.9	825.8	827.7	829.6	830.9	831.6	832.3	833.1	833.8	834.0
145°	865.6	867.1	868.5	870.0	871.5	872.9	874.1	875.4	876.6	877.9	878.1
147.5°	904.4	906.2	907.9	909.7	911.5	912.8	913.6	914.5	915.3	916.2	916.6
150°	930.9	932.2	933.4	934.7	936.0	937.0	937.9	938.7	939.6	940.4	941.0
152.5°	954.4	955.7	956.9	958.2	959.4	960.6	961.6	962.6	963.7	964.7	965.5
155°	989.7	990.3	990.9	991.6	992.2	992.8	993.4	994.1	994.7	995.3	996.4
157.5°	1019.8	1020.2	1020.6	1021.0	1021.5	1021.8	1022.2	1022.6	1023.0	1023.4	1024.8
160°	1038.0	1038.4	1038.8	1039.2	1039.7	1039.9	1040.2	1040.4	1040.6	1040.8	1042.0
162.5°	1054.6	1054.7	1054.8	1054.8	1055.0	1055.1	1055.3	1055.5	1055.7	1056.0	1057.4
165°	1076.8	1076.6	1076.4	1076.1	1076.0	1075.9	1075.9	1075.9	1075.9	1075.9	1077.3
167.5°	1095.4	1094.7	1094.1	1093.5	1092.8	1092.5	1092.4	1092.4	1092.3	1092.3	1093.8
170°	1105.2	1104.6	1103.9	1103.3	1102.7	1102.3	1102.0	1101.8	1101.6	1101.4	1102.9
172.5°	1112.0	1111.4	1110.8	1110.1	1109.5	1109.1	1108.9	1108.6	1108.4	1108.2	1109.7
175°	1120.4	1119.7	1119.1	1118.4	1117.9	1117.3	1116.9	1116.5	1116.1	1115.6	1117.1
177.5°	1123.7	1123.2	1122.7	1122.3	1121.8	1121.3	1121.0	1120.6	1120.3	1120.0	1121.0
180°	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3



TEST NUMBER: P331463-930

CATALOG NUMBER: S122DIP-S1005D1080U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1293.9	1296.1	1298.4	1299.3	1298.8	1298.4	1297.9	1297.5
5°	1285.2	1287.4	1289.6	1290.5	1289.9	1289.3	1288.7	1288.2
7.5°	1270.6	1272.8	1275.1	1275.9	1275.3	1274.7	1274.1	1273.5
10°	1257.7	1259.9	1262.1	1262.8	1262.0	1261.1	1260.3	1259.5
12.5°	1242.4	1243.9	1245.5	1245.9	1245.3	1244.7	1244.1	1243.5
15°	1215.4	1216.6	1217.6	1217.6	1216.2	1214.8	1213.4	1212.0
17.5°	1183.6	1184.9	1186.1	1186.1	1184.7	1183.4	1182.1	1180.7
20°	1158.7	1159.5	1160.3	1160.2	1159.1	1158.0	1156.9	1155.8
22.5°	1132.4	1132.5	1132.7	1132.5	1131.8	1131.1	1130.4	1129.8
25°	1089.4	1090.0	1090.5	1090.5	1090.0	1089.4	1088.8	1088.3
27.5°	1047.2	1046.3	1045.5	1044.4	1043.1	1041.7	1040.4	1039.1
30°	1014.2	1013.3	1012.5	1011.5	1010.4	1009.3	1008.2	1007.1
32.5°	981.9	980.3	978.8	977.5	976.4	975.3	974.2	973.1
35°	930.0	928.4	926.7	925.2	923.8	922.4	921.0	919.6
37.5°	878.0	876.0	873.9	872.2	870.9	869.5	868.2	866.9
40°	842.1	839.7	837.1	835.4	834.2	833.2	832.0	830.9
42.5°	806.7	804.0	801.3	799.2	797.6	796.1	794.5	792.9
45°	752.4	749.3	746.2	744.1	743.0	741.9	740.8	739.7
47.5°	695.8	692.5	689.3	686.9	685.3	683.7	682.1	680.4
50°	659.4	655.6	651.7	649.1	647.7	646.3	644.9	643.5
52.5°	621.8	618.6	615.4	612.9	611.0	609.2	607.3	605.5
55°	565.6	562.2	559.0	556.6	555.2	553.8	552.4	551.0
57.5°	507.2	503.9	500.7	498.5	497.5	496.4	495.4	494.3
60°	468.7	465.6	462.6	460.6	459.8	459.0	458.1	457.3
62.5°	432.2	429.3	426.5	424.5	423.5	422.4	421.3	420.3
65°	376.1	373.6	371.1	369.2	367.8	366.4	365.0	363.6
67.5°	320.7	318.8	316.8	315.3	314.2	313.1	312.0	310.9
70°	284.7	282.8	280.9	279.3	278.2	277.1	276.0	274.9
72.5°	250.8	248.8	246.9	245.5	244.6	243.7	242.8	241.9
75°	197.9	196.2	194.5	194.0	194.5	195.0	195.6	196.2
77.5°	150.5	149.7	148.9	148.1	147.2	146.5	145.7	145.0
80°	119.5	118.7	117.9	117.2	116.6	116.1	115.5	115.0
82.5°	89.1	88.1	87.0	86.4	86.3	86.2	86.1	85.9
85°	47.0	46.2	45.4	44.8	44.6	44.3	44.0	43.7
87.5°	19.2	18.3	17.6	17.1	17.0	16.8	16.6	16.5
90°	32.3	31.9	31.5	31.4	31.6	31.8	32.0	32.2
92.5°	30.2	30.3	30.5	30.5	30.6	30.6	30.7	30.7
95°	60.6	60.6	60.6	60.4	60.0	59.6	59.1	58.7
97.5°	101.9	101.9	101.9	101.9	101.8	101.8	101.7	101.7
100°	130.7	130.7	130.7	130.6	130.4	130.2	130.0	129.7
102.5°	162.1	162.2	162.4	162.4	162.2	162.0	161.8	161.6
105°	209.2	209.6	210.0	210.3	210.3	210.3	210.3	210.3
107.5°	260.0	260.2	260.3	259.9	259.0	258.0	257.1	256.1
110°	294.6	294.6	294.6	294.2	293.6	292.9	292.3	291.7





TEST NUMBER: P331463-930

CATALOG NUMBER: S122DIP-S1005D1080U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	329.1	328.6	328.2	327.7	327.2	326.7	326.3	325.8
115°	382.2	382.0	381.7	381.3	380.7	380.1	379.4	378.8
117.5°	433.5	433.0	432.5	431.9	431.3	430.6	430.0	429.4
120°	467.8	467.8	467.8	467.5	466.9	466.3	465.6	465.0
122.5°	503.2	502.7	502.1	501.7	501.2	500.8	500.3	499.9
125°	555.6	555.0	554.3	553.9	553.7	553.5	553.3	553.1
127.5°	606.5	605.7	605.0	604.2	603.6	602.9	602.3	601.5
130°	641.2	640.8	640.4	639.8	639.0	638.1	637.2	636.4
132.5°	675.1	674.2	673.3	672.5	671.8	671.1	670.4	669.8
135°	725.0	724.8	724.6	724.1	723.5	722.9	722.3	721.6
137.5°	772.8	772.7	772.5	772.0	771.1	770.3	769.5	768.6
140°	804.9	804.9	804.9	804.5	803.7	802.9	802.0	801.2
142.5°	834.1	834.3	834.5	834.1	833.2	832.4	831.6	830.7
145°	878.3	878.6	878.7	878.4	877.6	876.8	875.9	875.1
147.5°	917.1	917.5	918.0	917.9	917.0	916.2	915.4	914.7
150°	941.7	942.3	943.0	943.0	942.3	941.7	941.0	940.4
152.5°	966.3	967.0	967.8	967.8	967.0	966.3	965.5	964.7
155°	997.4	998.5	999.6	999.7	999.1	998.5	997.8	997.2
157.5°	1026.2	1027.7	1029.1	1029.3	1028.3	1027.3	1026.3	1025.2
160°	1043.3	1044.6	1045.9	1046.0	1045.2	1044.4	1043.5	1042.7
162.5°	1058.8	1060.2	1061.7	1061.8	1060.9	1059.9	1058.8	1057.9
165°	1078.8	1080.3	1081.7	1081.9	1080.9	1079.9	1078.8	1077.7
167.5°	1095.3	1096.7	1098.2	1098.4	1097.3	1096.2	1095.1	1094.1
170°	1104.3	1105.8	1107.3	1107.4	1106.1	1104.9	1103.6	1102.4
172.5°	1111.2	1112.6	1114.1	1114.2	1113.0	1111.7	1110.4	1109.1
175°	1118.6	1120.1	1121.5	1121.6	1120.4	1119.1	1117.9	1116.6
177.5°	1122.0	1123.0	1124.0	1124.0	1123.0	1122.0	1121.0	1120.0
180°	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3

(END OF REPORT)