

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331454-930

Luminaire Tested: **S122DIP-S1005D925U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331454-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S1005D925U930-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6005.8 lumens  
Efficiency: N/A  
Efficacy: 89.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331454-930

CATALOG NUMBER: S122DIP-S1005D925U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331454-930

CATALOG NUMBER: S122DIP-S1005D925U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	87	92	88	85	81	76	73	71	64	62	61	54	52	51	46
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	54	46	41	47	41	36	40	35	32	34	30	28	25
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	24	22
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	15
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20980	20980	20980
5°	21060	20757	20879
10°	20935	20546	20649
15°	20677	20279	20259
20°	20309	19880	19859
25°	19946	19388	19388
30°	19475	18938	18776
35°	19036	18398	18126
40°	18487	17856	17513
45°	17945	17317	16890
50°	17357	16759	16164
55°	16743	16110	15510
60°	16059	15332	14767
65°	15320	14560	13891
70°	14389	13624	12977
75°	13094	12545	12239
80°	11623	11269	10693
85°	9485	9040	8096



TEST NUMBER: P331454-930

CATALOG NUMBER: S122DIP-S1005D925U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.2	2.0
10°-20°	343.8	5.7
20°-30°	505.4	8.4
30°-40°	587.0	9.8
40°-50°	586.4	9.8
50°-60°	511.4	8.5
60°-70°	378.1	6.3
70°-80°	214.2	3.6
80°-90°	61.4	1.0
90°-100°	61.1	1.0
100°-110°	189.8	3.2
110°-120°	324.3	5.4
120°-130°	426.5	7.1
130°-140°	478.7	8.0
140°-150°	469.4	7.8
150°-160°	393.7	6.6
160°-170°	261.1	4.3
170°-180°	91.3	1.5
0°-30°	971.4	16.2
0°-40°	1558.4	25.9
0°-60°	2656.1	44.2
0°-90°	3309.8	55.1
90°-120°	575.2	9.6
90°-150°	1949.8	32.5
90°-180°	2696.0	44.9
0°-180°	6005.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1299	1299	1299	1299	1299	
5°	1299	1294	1281	1290	1288	123
15°	1237	1229	1213	1218	1212	348
25°	1120	1109	1088	1090	1088	515
35°	966	953	933	926	920	603
45°	786	777	758	745	740	606
55°	595	587	572	558	551	532
65°	401	393	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	1	11	28	27	28	5
95°	42	50	52	52	50	49
105°	175	177	179	180	181	185
115°	326	330	329	328	326	322
125°	474	480	478	476	475	423
135°	613	621	623	622	620	473
145°	744	749	754	755	752	464
155°	850	853	855	859	857	391
165°	925	924	924	929	926	261
175°	962	960	958	964	959	91
180°	964	964	964	964	964	



TEST NUMBER: P331454-930

CATALOG NUMBER: S122DIP-S1005D925U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1305.5	1304.3	1303.3	1302.1	1301.0	1299.3	1296.8	1294.4	1291.9	1289.5	1291.7
5°	1299.4	1298.4	1297.2	1296.1	1295.0	1292.9	1289.9	1286.8	1283.8	1280.7	1283.0
7.5°	1287.9	1286.2	1284.5	1282.8	1281.1	1278.6	1275.5	1272.4	1269.3	1266.2	1268.4
10°	1276.9	1275.0	1273.1	1271.1	1269.2	1266.6	1263.2	1259.9	1256.5	1253.2	1255.5
12.5°	1262.0	1260.2	1258.5	1256.8	1255.1	1252.5	1249.2	1245.9	1242.6	1239.3	1240.8
15°	1237.0	1235.3	1233.6	1232.0	1230.3	1227.7	1224.1	1220.4	1216.8	1213.2	1214.4
17.5°	1205.0	1203.3	1201.7	1200.0	1198.3	1195.6	1192.0	1188.3	1184.6	1181.0	1182.3
20°	1182.0	1180.3	1178.7	1177.0	1175.3	1172.6	1168.7	1164.8	1160.9	1157.0	1157.8
22.5°	1159.0	1156.7	1154.4	1152.0	1149.7	1146.7	1143.0	1139.4	1135.7	1132.0	1132.2
25°	1119.6	1117.3	1115.1	1112.9	1110.7	1107.2	1102.4	1097.7	1093.0	1088.3	1088.8
27.5°	1074.6	1072.5	1070.6	1068.5	1066.6	1063.7	1060.0	1056.2	1052.6	1048.8	1048.0
30°	1044.6	1042.4	1040.1	1037.9	1035.7	1032.5	1028.3	1024.2	1020.0	1015.8	1015.0
32.5°	1012.6	1010.8	1009.0	1007.2	1005.4	1002.4	998.0	993.6	989.2	984.8	983.3
35°	965.8	963.0	960.3	957.5	954.7	951.1	946.6	942.2	937.8	933.4	931.7
37.5°	913.1	910.7	908.2	905.8	903.4	899.9	895.4	891.0	886.6	882.2	880.0
40°	877.1	874.9	872.7	870.5	868.2	865.0	860.5	856.1	851.6	847.2	844.7
42.5°	842.1	839.9	837.7	835.5	833.2	829.9	825.5	821.0	816.6	812.1	809.4
45°	785.9	784.0	782.0	780.1	778.1	775.1	770.9	766.8	762.6	758.4	755.4
47.5°	729.9	728.1	726.3	724.5	722.6	719.5	715.2	710.9	706.5	702.2	699.0
50°	691.0	689.6	688.2	686.8	685.4	682.7	678.9	675.0	671.1	667.2	663.3
52.5°	653.0	651.2	649.3	647.5	645.6	642.9	639.2	635.5	631.9	628.3	625.0
55°	594.8	593.0	591.4	589.8	588.1	585.5	582.3	578.9	575.6	572.3	568.9
57.5°	536.3	534.9	533.6	532.3	530.9	528.5	524.8	521.1	517.5	513.8	510.5
60°	497.3	496.2	495.0	494.0	492.8	490.3	486.5	482.6	478.7	474.8	471.7
62.5°	459.3	457.5	455.8	454.0	452.2	449.8	446.8	443.8	440.8	437.8	435.0
65°	401.0	399.4	397.8	396.1	394.4	392.2	389.4	386.6	383.8	381.1	378.6
67.5°	341.9	340.6	339.2	337.9	336.6	334.6	332.1	329.6	327.1	324.7	322.7
70°	304.8	303.8	302.6	301.6	300.4	298.6	296.1	293.6	291.1	288.6	286.7
72.5°	266.8	265.8	264.6	263.6	262.4	261.1	259.5	257.9	256.2	254.6	252.7
75°	209.9	209.4	208.8	208.2	207.7	206.7	205.3	203.9	202.5	201.1	199.5
77.5°	158.9	158.0	157.0	156.1	155.2	154.4	153.8	153.3	152.7	152.2	151.3
80°	125.0	124.7	124.4	124.1	123.8	123.4	122.9	122.3	121.7	121.2	120.3
82.5°	92.9	92.9	92.9	92.8	92.7	92.5	92.2	91.9	91.6	91.2	90.2
85°	51.2	51.0	50.7	50.4	50.1	49.8	49.6	49.2	49.0	48.8	47.9
87.5°	18.2	18.2	18.1	18.1	18.1	18.3	18.7	19.0	19.3	19.7	18.9
90°	0.8	3.0	5.1	7.3	9.5	12.6	16.6	20.5	24.5	28.5	28.1
92.5°	14.5	16.1	17.7	19.2	20.9	22.1	23.1	24.0	24.9	25.8	25.9
95°	42.3	44.1	45.9	47.7	49.6	50.6	51.0	51.4	51.7	52.1	52.1
97.5°	77.3	78.9	80.5	82.1	83.6	84.8	85.5	86.2	86.8	87.6	87.6
100°	103.3	104.8	106.2	107.7	109.1	110.1	110.6	111.2	111.8	112.3	112.3
102.5°	130.7	131.8	133.0	134.1	135.3	136.2	136.9	137.6	138.3	139.0	139.1
105°	175.0	175.5	176.0	176.6	177.1	177.6	177.9	178.3	178.6	179.0	179.4
107.5°	219.5	220.3	221.1	221.9	222.7	223.1	223.1	223.1	223.1	223.1	223.2
110°	248.2	249.2	250.3	251.4	252.5	253.1	253.1	253.1	253.1	253.1	253.1



TEST NUMBER: P331454-930

CATALOG NUMBER: S122DIP-S1005D925U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	279.4	280.5	281.6	282.7	283.7	284.2	284.1	283.9	283.8	283.6	283.2
115°	325.5	326.5	327.6	328.7	329.8	330.1	329.8	329.5	329.1	328.7	328.6
117.5°	371.4	372.8	374.2	375.7	377.2	377.3	376.3	375.3	374.3	373.3	372.8
120°	401.9	403.4	404.8	406.3	407.7	407.7	406.3	404.8	403.4	401.9	401.9
122.5°	429.9	431.6	433.4	435.1	436.8	437.2	436.2	435.2	434.2	433.2	432.8
125°	473.5	475.2	476.8	478.4	480.0	480.6	480.0	479.5	479.0	478.4	477.8
127.5°	516.0	518.0	520.2	522.2	524.2	525.0	524.3	523.7	523.0	522.4	521.7
130°	542.7	545.0	547.4	549.8	552.1	553.1	552.7	552.4	552.0	551.6	551.3
132.5°	572.7	574.5	576.5	578.4	580.3	581.3	581.4	581.5	581.5	581.6	580.8
135°	612.7	614.7	616.6	618.6	620.6	621.8	622.2	622.5	622.9	623.2	623.1
137.5°	654.8	656.4	658.0	659.7	661.3	662.3	662.8	663.3	663.8	664.2	664.1
140°	680.2	681.8	683.5	685.1	686.7	687.9	688.8	689.7	690.7	691.6	691.6
142.5°	706.2	707.8	709.5	711.1	712.7	713.9	714.4	715.1	715.7	716.3	716.5
145°	743.6	744.9	746.2	747.5	748.7	749.9	751.0	752.0	753.2	754.2	754.4
147.5°	777.0	778.5	780.1	781.5	783.1	784.2	785.0	785.6	786.4	787.1	787.5
150°	799.8	800.9	801.9	803.1	804.1	805.0	805.8	806.5	807.2	808.0	808.5
152.5°	819.9	821.1	822.1	823.2	824.3	825.3	826.1	827.0	827.9	828.8	829.5
155°	850.3	850.8	851.3	851.9	852.4	853.0	853.5	854.0	854.6	855.1	856.1
157.5°	876.1	876.4	876.9	877.2	877.6	877.9	878.2	878.6	878.9	879.2	880.4
160°	891.8	892.1	892.4	892.8	893.2	893.5	893.6	893.8	894.0	894.1	895.3
162.5°	906.0	906.1	906.2	906.3	906.4	906.4	906.7	906.9	907.0	907.2	908.4
165°	925.1	925.0	924.7	924.5	924.4	924.3	924.3	924.3	924.3	924.3	925.5
167.5°	941.0	940.5	940.0	939.4	938.9	938.6	938.6	938.5	938.5	938.4	939.7
170°	949.5	948.9	948.4	947.9	947.3	947.0	946.8	946.6	946.4	946.2	947.5
172.5°	955.4	954.8	954.3	953.7	953.2	952.8	952.7	952.4	952.3	952.1	953.4
175°	962.5	962.0	961.4	960.9	960.3	959.9	959.5	959.2	958.8	958.5	959.7
177.5°	965.5	965.0	964.6	964.2	963.7	963.4	963.0	962.8	962.5	962.2	963.0
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331454-930

CATALOG NUMBER: S122DIP-S1005D925U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1293.9	1296.1	1298.4	1299.3	1298.8	1298.4	1297.9	1297.5
5°	1285.2	1287.4	1289.6	1290.5	1289.9	1289.3	1288.7	1288.2
7.5°	1270.6	1272.8	1275.1	1275.9	1275.3	1274.7	1274.1	1273.5
10°	1257.7	1259.9	1262.1	1262.8	1262.0	1261.1	1260.3	1259.5
12.5°	1242.4	1243.9	1245.5	1245.9	1245.3	1244.7	1244.1	1243.5
15°	1215.4	1216.6	1217.6	1217.6	1216.2	1214.8	1213.4	1212.0
17.5°	1183.6	1184.9	1186.1	1186.1	1184.7	1183.4	1182.1	1180.7
20°	1158.7	1159.5	1160.3	1160.2	1159.1	1158.0	1156.9	1155.8
22.5°	1132.4	1132.5	1132.7	1132.5	1131.8	1131.1	1130.4	1129.8
25°	1089.4	1090.0	1090.5	1090.5	1090.0	1089.4	1088.8	1088.3
27.5°	1047.2	1046.3	1045.5	1044.4	1043.1	1041.7	1040.4	1039.1
30°	1014.2	1013.3	1012.5	1011.5	1010.4	1009.3	1008.2	1007.1
32.5°	981.9	980.3	978.8	977.5	976.4	975.3	974.2	973.1
35°	930.0	928.4	926.7	925.2	923.8	922.4	921.0	919.6
37.5°	878.0	876.0	873.9	872.2	870.9	869.5	868.2	866.9
40°	842.1	839.7	837.1	835.4	834.2	833.2	832.0	830.9
42.5°	806.7	804.0	801.3	799.2	797.6	796.1	794.5	792.9
45°	752.4	749.3	746.2	744.1	743.0	741.9	740.8	739.7
47.5°	695.8	692.5	689.3	686.9	685.3	683.7	682.1	680.4
50°	659.4	655.6	651.7	649.1	647.7	646.3	644.9	643.5
52.5°	621.8	618.6	615.4	612.9	611.0	609.2	607.3	605.5
55°	565.6	562.2	559.0	556.6	555.2	553.8	552.4	551.0
57.5°	507.2	503.9	500.7	498.5	497.5	496.4	495.4	494.3
60°	468.7	465.6	462.6	460.6	459.8	459.0	458.1	457.3
62.5°	432.2	429.3	426.5	424.5	423.5	422.4	421.3	420.3
65°	376.1	373.6	371.1	369.2	367.8	366.4	365.0	363.6
67.5°	320.7	318.8	316.8	315.3	314.2	313.1	312.0	310.9
70°	284.7	282.8	280.9	279.3	278.2	277.1	276.0	274.9
72.5°	250.8	248.8	246.9	245.5	244.6	243.7	242.8	241.9
75°	197.9	196.2	194.5	194.0	194.5	195.0	195.6	196.2
77.5°	150.5	149.7	148.9	148.1	147.2	146.5	145.7	145.0
80°	119.5	118.7	117.9	117.2	116.6	116.1	115.5	115.0
82.5°	89.1	88.1	87.0	86.4	86.3	86.2	86.1	85.9
85°	47.0	46.2	45.4	44.8	44.6	44.3	44.0	43.7
87.5°	18.2	17.4	16.7	16.3	16.1	15.9	15.7	15.5
90°	27.7	27.4	27.1	26.9	27.1	27.3	27.5	27.6
92.5°	26.0	26.1	26.2	26.3	26.3	26.3	26.3	26.3
95°	52.1	52.1	52.1	51.9	51.5	51.2	50.8	50.5
97.5°	87.6	87.6	87.6	87.6	87.5	87.5	87.4	87.4
100°	112.3	112.3	112.3	112.2	112.0	111.9	111.6	111.5
102.5°	139.3	139.4	139.6	139.5	139.3	139.2	139.0	138.8
105°	179.7	180.1	180.4	180.6	180.6	180.6	180.6	180.6
107.5°	223.4	223.6	223.6	223.3	222.5	221.7	220.9	220.0
110°	253.1	253.1	253.1	252.7	252.3	251.7	251.1	250.6





TEST NUMBER: P331454-930

CATALOG NUMBER: S122DIP-S1005D925U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	282.7	282.3	281.9	281.4	281.1	280.7	280.3	279.9
115°	328.3	328.2	328.0	327.6	327.1	326.5	326.0	325.5
117.5°	372.4	372.0	371.5	371.0	370.6	370.0	369.4	368.9
120°	401.9	401.9	401.9	401.7	401.1	400.6	400.1	399.5
122.5°	432.3	431.9	431.5	431.0	430.6	430.2	429.8	429.4
125°	477.4	476.8	476.2	475.9	475.7	475.5	475.3	475.2
127.5°	521.1	520.4	519.8	519.1	518.5	518.0	517.4	516.8
130°	550.9	550.6	550.2	549.7	548.9	548.2	547.5	546.7
132.5°	580.0	579.2	578.4	577.7	577.2	576.6	576.0	575.4
135°	622.9	622.7	622.5	622.2	621.6	621.1	620.5	620.0
137.5°	664.0	663.8	663.7	663.2	662.5	661.8	661.0	660.3
140°	691.6	691.6	691.6	691.2	690.5	689.7	689.1	688.4
142.5°	716.6	716.7	716.9	716.6	715.9	715.2	714.4	713.7
145°	754.6	754.8	755.0	754.7	754.0	753.3	752.5	751.8
147.5°	787.9	788.3	788.7	788.6	787.9	787.2	786.5	785.8
150°	809.0	809.6	810.1	810.1	809.6	809.0	808.5	808.0
152.5°	830.1	830.8	831.5	831.5	830.8	830.1	829.5	828.8
155°	857.0	857.9	858.8	858.9	858.3	857.9	857.3	856.7
157.5°	881.7	882.9	884.1	884.3	883.5	882.6	881.7	880.8
160°	896.3	897.4	898.5	898.7	898.0	897.2	896.5	895.8
162.5°	909.6	910.9	912.1	912.3	911.4	910.5	909.7	908.8
165°	926.8	928.1	929.4	929.5	928.6	927.7	926.8	925.9
167.5°	940.9	942.2	943.5	943.6	942.7	941.8	940.9	939.9
170°	948.8	950.1	951.3	951.4	950.3	949.3	948.1	947.1
172.5°	954.6	955.9	957.2	957.2	956.2	955.1	954.0	952.9
175°	961.0	962.2	963.5	963.6	962.5	961.4	960.3	959.3
177.5°	963.9	964.8	965.6	965.6	964.8	963.9	963.0	962.2
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2

(END OF REPORT)