

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331257-930

Luminaire Tested: **S122DIP-S290D530U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331257-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S290D530U930-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2664.6 lumens  
Efficiency: N/A  
Efficacy: 104.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331257-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331257-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37								
1	95	91	87	83	86	82	79	76	67	64	62	52	51	49	39	38	37	31								
2	86	79	73	68	78	72	67	62	58	55	52	46	43	41	34	33	31	26								
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	27	22								
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19								
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16								
6	61	49	41	35	55	45	38	33	37	31	28	29	25	22	22	20	18	14								
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	18	16	13								
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	19	16	14	11								
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	13	10								
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	16	13	11	9								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6218	6218	6218
5°	6242	6152	6190
10°	6205	6091	6120
15°	6128	6011	6006
20°	6019	5893	5887
25°	5911	5747	5747
30°	5774	5614	5565
35°	5643	5452	5373
40°	5480	5292	5191
45°	5318	5133	5005
50°	5144	4968	4793
55°	4963	4777	4597
60°	4760	4543	4379
65°	4542	4317	4118
70°	4263	4036	3843
75°	3880	3718	3624
80°	3440	3347	3171
85°	2816	2668	2408



TEST NUMBER: P331257-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	36.2	1.4
10°-20°	101.9	3.8
20°-30°	149.8	5.6
30°-40°	174.0	6.5
40°-50°	173.8	6.5
50°-60°	151.6	5.7
60°-70°	112.1	4.2
70°-80°	63.5	2.4
80°-90°	19.2	0.7
90°-100°	96.7	3.6
100°-110°	328.1	12.3
110°-120°	348.5	13.1
120°-130°	286.9	10.8
130°-140°	230.4	8.6
140°-150°	174.1	6.5
150°-160°	122.4	4.6
160°-170°	72.0	2.7
170°-180°	23.4	0.9
0°-30°	287.9	10.8
0°-40°	461.9	17.3
0°-60°	787.3	29.5
0°-90°	982.1	36.9
90°-120°	773.2	29.0
90°-150°	1464.6	55.0
90°-180°	1682.0	63.1
0°-180°	2664.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	385	385	385	385	385	
5°	385	384	380	382	382	37
15°	367	364	360	361	359	103
25°	332	329	323	323	323	153
35°	286	282	277	274	273	179
45°	233	230	225	221	219	180
55°	176	174	170	165	163	158
65°	119	117	113	110	108	118
75°	62	61	60	58	58	66
85°	15	15	14	13	13	17
90°	0	6	16	15	15	2
95°	16	40	182	69	53	17
105°	57	86	344	616	524	60
115°	100	126	288	595	690	99
125°	140	165	277	482	559	124
135°	164	195	274	405	464	126
145°	187	215	272	338	370	117
155°	212	229	265	299	311	98
165°	232	238	253	269	273	65
175°	241	242	244	247	246	23
180°	242	242	242	242	242	



TEST NUMBER: P331257-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1
2.5°	386.9	386.6	386.3	386.0	385.6	385.1	384.4	383.7	382.9	382.2	382.9
5°	385.1	384.8	384.5	384.2	383.8	383.3	382.4	381.5	380.5	379.6	380.3
7.5°	381.8	381.2	380.7	380.3	379.8	379.0	378.1	377.2	376.3	375.4	376.0
10°	378.5	378.0	377.4	376.8	376.2	375.4	374.5	373.5	372.5	371.5	372.1
12.5°	374.1	373.6	373.1	372.5	372.0	371.3	370.3	369.3	368.4	367.4	367.8
15°	366.6	366.2	365.7	365.2	364.7	363.9	362.8	361.7	360.7	359.6	360.0
17.5°	357.2	356.7	356.2	355.7	355.2	354.4	353.4	352.2	351.1	350.1	350.4
20°	350.3	349.8	349.4	348.9	348.4	347.6	346.4	345.3	344.1	343.0	343.2
22.5°	343.6	342.8	342.2	341.4	340.8	339.9	338.8	337.7	336.6	335.6	335.6
25°	331.8	331.2	330.5	329.9	329.2	328.2	326.8	325.4	324.0	322.6	322.8
27.5°	318.5	318.0	317.3	316.7	316.2	315.3	314.2	313.1	312.0	310.9	310.6
30°	309.7	309.0	308.3	307.7	307.0	306.1	304.8	303.6	302.3	301.1	300.8
32.5°	300.1	299.6	299.1	298.6	298.1	297.1	295.8	294.6	293.3	292.0	291.5
35°	286.3	285.4	284.6	283.8	283.0	281.9	280.6	279.3	278.0	276.6	276.1
37.5°	270.7	269.9	269.2	268.5	267.7	266.8	265.5	264.2	262.8	261.5	260.9
40°	260.0	259.3	258.7	258.0	257.4	256.4	255.0	253.7	252.4	251.1	250.4
42.5°	249.6	249.0	248.3	247.7	247.0	246.0	244.7	243.4	242.1	240.8	239.9
45°	232.9	232.4	231.8	231.2	230.6	229.8	228.5	227.3	226.1	224.8	223.9
47.5°	216.4	215.8	215.3	214.7	214.2	213.3	212.0	210.8	209.5	208.1	207.2
50°	204.8	204.4	204.0	203.6	203.2	202.4	201.2	200.1	198.9	197.8	196.7
52.5°	193.6	193.0	192.5	191.9	191.4	190.5	189.5	188.4	187.3	186.2	185.2
55°	176.3	175.8	175.3	174.8	174.3	173.6	172.6	171.6	170.6	169.7	168.6
57.5°	159.0	158.6	158.2	157.8	157.4	156.6	155.6	154.5	153.4	152.3	151.3
60°	147.4	147.1	146.8	146.4	146.1	145.4	144.2	143.1	141.9	140.7	139.8
62.5°	136.2	135.6	135.1	134.6	134.0	133.3	132.4	131.6	130.7	129.8	128.9
65°	118.9	118.4	117.9	117.4	116.9	116.3	115.4	114.6	113.8	113.0	112.2
67.5°	101.3	100.9	100.5	100.1	99.8	99.2	98.4	97.7	96.9	96.2	95.6
70°	90.3	90.0	89.7	89.4	89.0	88.5	87.8	87.1	86.3	85.5	85.0
72.5°	79.1	78.8	78.4	78.1	77.8	77.4	76.9	76.5	76.0	75.5	74.9
75°	62.2	62.0	61.9	61.7	61.6	61.3	60.9	60.4	60.0	59.6	59.1
77.5°	47.1	46.8	46.6	46.3	46.0	45.7	45.6	45.4	45.2	45.1	44.8
80°	37.0	36.9	36.9	36.8	36.7	36.6	36.4	36.3	36.1	36.0	35.7
82.5°	27.6	27.6	27.6	27.5	27.5	27.4	27.3	27.2	27.1	27.1	26.7
85°	15.2	15.1	15.0	14.9	14.8	14.8	14.7	14.6	14.5	14.4	14.2
87.5°	5.5	5.5	5.8	5.9	6.0	6.0	6.4	6.9	7.3	7.3	7.0
90°	0.5	1.9	3.8	4.6	5.5	7.0	9.3	12.6	15.3	15.8	15.3
92.5°	5.7	8.2	11.5	13.6	16.7	21.1	31.6	46.4	59.6	60.4	51.0
95°	16.3	18.1	22.7	27.0	34.4	45.6	66.9	107.4	161.3	182.3	159.5
97.5°	26.5	29.0	33.9	40.3	48.8	61.5	88.4	144.7	234.3	311.1	326.4
100°	35.8	37.2	41.4	48.8	58.1	71.2	95.8	152.5	252.9	367.3	434.2
102.5°	44.4	45.4	49.6	57.0	66.7	79.7	102.5	152.9	245.9	369.2	474.4
105°	56.7	58.6	61.8	68.8	79.0	92.0	113.9	155.3	232.0	344.5	468.2
107.5°	70.1	71.6	74.8	81.2	91.3	104.4	125.6	161.7	225.1	318.1	427.4
110°	79.0	80.9	83.7	89.8	99.5	113.0	133.5	166.9	223.6	305.5	401.7



TEST NUMBER: P331257-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	87.2	89.1	92.2	97.9	107.3	121.2	140.9	172.5	224.0	297.3	383.8
115°	100.0	102.3	105.1	110.6	119.9	132.5	152.5	180.8	226.0	288.3	361.7
117.5°	113.2	115.0	117.8	122.8	131.7	144.7	163.2	189.8	229.3	283.9	347.8
120°	121.3	123.2	126.0	130.2	139.5	152.5	170.6	195.8	231.5	281.3	340.4
122.5°	129.1	130.7	133.5	138.0	147.3	160.7	177.7	201.0	234.2	279.8	334.0
125°	139.5	140.9	143.7	149.3	158.6	171.5	188.3	209.2	238.1	277.1	325.0
127.5°	147.7	149.5	153.4	159.6	168.5	181.9	198.2	217.0	242.1	275.6	316.7
130°	152.5	154.3	159.0	165.5	174.8	187.8	204.2	221.8	245.0	274.8	311.0
132.5°	156.9	159.2	164.2	171.1	180.8	193.8	209.3	226.7	248.0	274.4	306.6
135°	163.6	165.5	171.1	178.1	188.7	201.8	216.7	232.9	251.5	273.9	300.4
137.5°	170.0	172.2	177.8	185.2	195.8	207.9	222.7	237.7	254.7	273.8	296.0
140°	174.8	176.7	182.3	189.7	199.9	212.1	226.0	240.4	256.2	273.4	293.4
142.5°	179.7	181.2	186.4	193.8	203.7	215.0	228.6	242.6	257.3	273.4	290.8
145°	186.9	188.7	193.4	200.4	209.7	219.9	232.4	245.5	258.5	272.5	287.3
147.5°	194.7	196.1	200.6	207.0	214.7	223.8	235.6	247.1	258.9	270.8	283.8
150°	199.9	201.3	205.0	211.1	218.1	226.4	237.1	247.9	258.5	269.7	280.9
152.5°	205.1	205.8	209.5	214.8	221.4	229.0	238.6	248.2	257.8	267.8	278.3
155°	212.5	213.0	215.7	220.9	226.0	232.9	240.8	248.7	256.7	264.6	273.4
157.5°	218.6	219.1	221.4	225.8	229.9	235.7	242.4	248.7	254.5	261.2	268.8
160°	222.7	223.1	225.0	228.8	232.4	237.6	243.2	248.7	253.4	259.0	265.5
162.5°	226.8	226.5	228.4	231.4	234.7	238.7	243.5	248.3	252.3	257.1	262.5
165°	231.5	231.1	232.0	234.8	237.1	239.9	244.1	247.4	250.1	253.4	257.6
167.5°	235.5	234.9	235.7	237.5	239.2	240.9	244.0	246.7	248.0	250.1	252.7
170°	238.1	237.1	237.6	239.0	239.9	241.3	243.6	246.0	246.9	248.3	250.1
172.5°	239.5	239.0	238.7	240.1	240.7	241.7	243.3	244.8	245.4	246.1	247.5
175°	241.3	240.8	240.4	241.3	241.3	241.7	242.7	243.6	243.2	243.6	244.1
177.5°	242.1	241.4	241.0	241.7	241.7	241.7	242.1	242.9	242.1	241.7	242.1
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7



TEST NUMBER: P331257-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1
2.5°	383.5	384.2	384.8	385.1	385.0	384.8	384.7	384.6
5°	381.0	381.6	382.3	382.5	382.4	382.2	382.0	381.9
7.5°	376.7	377.3	378.0	378.2	378.1	377.8	377.6	377.5
10°	372.8	373.5	374.1	374.3	374.1	373.8	373.6	373.3
12.5°	368.3	368.7	369.2	369.3	369.2	368.9	368.8	368.6
15°	360.3	360.6	360.9	360.9	360.5	360.1	359.7	359.3
17.5°	350.8	351.2	351.6	351.6	351.1	350.8	350.4	350.0
20°	343.5	343.7	344.0	343.9	343.6	343.2	342.9	342.6
22.5°	335.7	335.7	335.7	335.7	335.5	335.3	335.1	334.9
25°	322.9	323.1	323.3	323.3	323.1	322.9	322.8	322.6
27.5°	310.4	310.1	309.9	309.6	309.2	308.8	308.4	308.0
30°	300.6	300.4	300.1	299.9	299.5	299.2	298.9	298.5
32.5°	291.1	290.6	290.2	289.8	289.4	289.1	288.8	288.5
35°	275.7	275.2	274.7	274.3	273.9	273.5	273.0	272.6
37.5°	260.2	259.7	259.0	258.5	258.1	257.7	257.4	257.0
40°	249.6	248.9	248.2	247.6	247.3	247.0	246.6	246.3
42.5°	239.1	238.3	237.5	236.8	236.4	235.9	235.5	235.1
45°	223.0	222.1	221.2	220.5	220.2	219.9	219.6	219.2
47.5°	206.3	205.3	204.3	203.6	203.2	202.7	202.2	201.7
50°	195.5	194.3	193.1	192.4	192.0	191.6	191.2	190.8
52.5°	184.3	183.4	182.4	181.6	181.1	180.6	180.0	179.4
55°	167.6	166.6	165.7	165.0	164.6	164.1	163.7	163.3
57.5°	150.3	149.4	148.4	147.7	147.5	147.2	146.8	146.5
60°	138.9	138.0	137.1	136.6	136.3	136.1	135.8	135.6
62.5°	128.1	127.3	126.5	125.9	125.6	125.2	124.9	124.6
65°	111.5	110.7	110.0	109.4	109.0	108.6	108.2	107.8
67.5°	95.1	94.5	93.9	93.4	93.1	92.8	92.5	92.1
70°	84.4	83.8	83.2	82.8	82.5	82.1	81.8	81.4
72.5°	74.4	73.8	73.2	72.7	72.5	72.2	72.0	71.7
75°	58.6	58.1	57.6	57.5	57.6	57.8	58.0	58.1
77.5°	44.6	44.4	44.1	43.9	43.6	43.5	43.2	43.0
80°	35.5	35.2	35.0	34.7	34.6	34.4	34.2	34.1
82.5°	26.4	26.1	25.8	25.6	25.6	25.5	25.5	25.5
85°	13.9	13.7	13.5	13.3	13.2	13.1	13.0	13.0
87.5°	6.8	6.4	6.4	6.3	6.2	6.2	6.1	6.0
90°	14.8	13.9	14.8	15.3	15.3	15.3	15.3	15.3
92.5°	40.5	34.8	30.9	28.0	27.6	26.2	26.5	25.8
95°	121.8	93.4	73.9	63.7	57.6	54.0	52.5	53.0
97.5°	284.3	232.6	182.3	148.7	126.5	115.0	108.3	104.4
100°	424.5	366.9	303.1	246.9	208.3	188.3	174.8	166.5
102.5°	516.4	503.4	456.8	397.1	355.2	321.1	304.3	292.9
105°	564.9	617.4	623.5	608.1	579.4	550.5	530.5	524.0
107.5°	529.9	609.1	657.5	680.0	683.5	682.0	678.0	669.4
110°	499.9	583.0	642.5	680.7	700.7	709.6	713.7	713.2





TEST NUMBER: P331257-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	472.3	552.2	615.8	659.5	687.3	702.1	710.0	712.5
115°	438.5	510.1	571.0	618.9	651.8	673.3	685.3	689.5
117.5°	412.9	475.8	531.1	576.0	609.7	632.3	645.0	648.5
120°	400.3	458.0	507.3	549.6	582.1	604.0	617.4	622.1
122.5°	390.3	443.1	489.8	528.0	557.2	578.7	590.7	594.6
125°	375.7	423.5	464.5	499.4	526.4	544.0	555.6	559.4
127.5°	361.3	404.6	443.2	475.4	498.9	515.4	525.5	528.5
130°	352.0	392.0	428.7	459.3	482.2	498.0	507.3	510.9
132.5°	343.1	380.1	413.8	442.6	465.0	480.9	489.4	492.8
135°	330.6	361.3	392.0	418.0	438.0	453.3	461.7	463.6
137.5°	320.7	346.3	370.6	393.4	411.6	424.8	432.1	434.9
140°	314.3	336.6	358.0	378.5	393.4	405.4	412.4	415.2
142.5°	309.1	328.1	346.5	363.6	377.7	388.7	394.9	395.5
145°	301.7	317.1	331.5	345.0	356.1	364.0	368.7	370.1
147.5°	296.1	308.2	319.4	329.3	338.5	344.8	348.0	348.8
150°	292.0	302.2	312.0	320.3	327.3	332.9	335.7	336.1
152.5°	287.9	297.4	305.7	312.9	318.4	323.3	325.3	325.4
155°	282.3	289.7	296.6	301.7	306.9	310.1	312.0	311.0
157.5°	275.7	281.8	287.7	291.7	295.3	298.1	298.9	298.9
160°	271.5	276.6	281.8	285.0	288.3	290.6	291.1	291.1
162.5°	267.4	271.8	276.2	278.7	281.9	283.6	284.0	283.6
165°	261.3	264.6	267.8	269.7	271.5	273.4	273.4	273.0
167.5°	255.4	258.0	260.2	261.9	262.7	263.7	263.7	263.1
170°	252.5	253.9	255.8	256.7	257.1	258.5	258.0	257.1
172.5°	249.2	250.1	251.6	252.2	252.7	253.3	252.8	252.3
175°	245.5	246.0	246.5	246.9	246.9	247.4	246.9	246.0
177.5°	242.9	242.9	243.3	243.3	243.3	243.3	242.9	242.1
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7

(END OF REPORT)