

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331266-930

Luminaire Tested: **S122DIP-S290D725U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331266-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S290D725U930-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3289.1 lumens  
Efficiency: N/A  
Efficacy: 105.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331266-930

CATALOG NUMBER: S122DIP-S290D725U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331266-930

CATALOG NUMBER: S122DIP-S290D725U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	93	89	85	82	84	80	77	74	63	61	59	48	46	45	33	32	32	25
2	85	78	72	67	76	70	65	61	55	52	49	42	39	37	29	28	27	21
3	77	68	61	56	69	61	55	51	49	44	41	37	34	32	26	24	23	18
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	20	15
5	65	54	46	40	58	48	42	37	39	34	30	29	26	23	21	19	17	13
6	60	48	40	34	53	43	37	32	35	30	26	26	23	20	19	17	15	12
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13	10
8	51	39	32	26	46	35	29	24	28	24	20	22	18	16	16	14	12	9
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	15	12	11	8
10	44	32	25	21	40	29	23	19	24	19	16	19	15	13	13	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6218	6218	6218
5°	6242	6152	6190
10°	6205	6091	6120
15°	6128	6011	6006
20°	6019	5893	5887
25°	5911	5747	5747
30°	5774	5614	5565
35°	5643	5452	5373
40°	5480	5292	5191
45°	5318	5133	5005
50°	5144	4968	4793
55°	4963	4777	4597
60°	4760	4543	4379
65°	4542	4317	4118
70°	4263	4036	3843
75°	3880	3718	3624
80°	3440	3347	3171
85°	2816	2668	2408



TEST NUMBER: P331266-930

CATALOG NUMBER: S122DIP-S290D725U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	36.2	1.1
10°-20°	101.9	3.1
20°-30°	149.8	4.6
30°-40°	174.0	5.3
40°-50°	173.8	5.3
50°-60°	151.6	4.6
60°-70°	112.1	3.4
70°-80°	63.5	1.9
80°-90°	20.1	0.6
90°-100°	132.5	4.0
100°-110°	449.7	13.7
110°-120°	477.7	14.5
120°-130°	393.2	12.0
130°-140°	315.8	9.6
140°-150°	238.6	7.3
150°-160°	167.7	5.1
160°-170°	98.7	3.0
170°-180°	32.1	1.0
0°-30°	287.9	8.8
0°-40°	461.9	14.0
0°-60°	787.3	23.9
0°-90°	982.9	29.9
90°-120°	1059.9	32.2
90°-150°	2007.6	61.0
90°-180°	2306.0	70.1
0°-180°	3289.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	385	385	385	385	385	
5°	385	384	380	382	382	37
15°	367	364	360	361	359	103
25°	332	329	323	323	323	153
35°	286	282	277	274	273	179
45°	233	230	225	221	219	180
55°	176	174	170	165	163	158
65°	119	117	113	110	108	118
75°	62	61	60	58	58	66
85°	15	15	14	13	13	17
90°	1	9	22	21	21	2
95°	22	55	250	94	73	24
105°	78	117	472	844	718	83
115°	137	173	395	815	945	136
125°	191	226	380	661	767	170
135°	224	268	375	555	635	173
145°	256	294	374	464	507	161
155°	291	314	363	410	426	134
165°	317	327	347	368	374	89
175°	331	331	334	338	337	31
180°	331	331	331	331	331	



TEST NUMBER: P331266-930

CATALOG NUMBER: S122DIP-S290D725U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1
2.5°	386.9	386.6	386.3	386.0	385.6	385.1	384.4	383.7	382.9	382.2	382.9
5°	385.1	384.8	384.5	384.2	383.8	383.3	382.4	381.5	380.5	379.6	380.3
7.5°	381.8	381.2	380.7	380.3	379.8	379.0	378.1	377.2	376.3	375.4	376.0
10°	378.5	378.0	377.4	376.8	376.2	375.4	374.5	373.5	372.5	371.5	372.1
12.5°	374.1	373.6	373.1	372.5	372.0	371.3	370.3	369.3	368.4	367.4	367.8
15°	366.6	366.2	365.7	365.2	364.7	363.9	362.8	361.7	360.7	359.6	360.0
17.5°	357.2	356.7	356.2	355.7	355.2	354.4	353.4	352.2	351.1	350.1	350.4
20°	350.3	349.8	349.4	348.9	348.4	347.6	346.4	345.3	344.1	343.0	343.2
22.5°	343.6	342.8	342.2	341.4	340.8	339.9	338.8	337.7	336.6	335.6	335.6
25°	331.8	331.2	330.5	329.9	329.2	328.2	326.8	325.4	324.0	322.6	322.8
27.5°	318.5	318.0	317.3	316.7	316.2	315.3	314.2	313.1	312.0	310.9	310.6
30°	309.7	309.0	308.3	307.7	307.0	306.1	304.8	303.6	302.3	301.1	300.8
32.5°	300.1	299.6	299.1	298.6	298.1	297.1	295.8	294.6	293.3	292.0	291.5
35°	286.3	285.4	284.6	283.8	283.0	281.9	280.6	279.3	278.0	276.6	276.1
37.5°	270.7	269.9	269.2	268.5	267.7	266.8	265.5	264.2	262.8	261.5	260.9
40°	260.0	259.3	258.7	258.0	257.4	256.4	255.0	253.7	252.4	251.1	250.4
42.5°	249.6	249.0	248.3	247.7	247.0	246.0	244.7	243.4	242.1	240.8	239.9
45°	232.9	232.4	231.8	231.2	230.6	229.8	228.5	227.3	226.1	224.8	223.9
47.5°	216.4	215.8	215.3	214.7	214.2	213.3	212.0	210.8	209.5	208.1	207.2
50°	204.8	204.4	204.0	203.6	203.2	202.4	201.2	200.1	198.9	197.8	196.7
52.5°	193.6	193.0	192.5	191.9	191.4	190.5	189.5	188.4	187.3	186.2	185.2
55°	176.3	175.8	175.3	174.8	174.3	173.6	172.6	171.6	170.6	169.7	168.6
57.5°	159.0	158.6	158.2	157.8	157.4	156.6	155.6	154.5	153.4	152.3	151.3
60°	147.4	147.1	146.8	146.4	146.1	145.4	144.2	143.1	141.9	140.7	139.8
62.5°	136.2	135.6	135.1	134.6	134.0	133.3	132.4	131.6	130.7	129.8	128.9
65°	118.9	118.4	117.9	117.4	116.9	116.3	115.4	114.6	113.8	113.0	112.2
67.5°	101.3	100.9	100.5	100.1	99.8	99.2	98.4	97.7	96.9	96.2	95.6
70°	90.3	90.0	89.7	89.4	89.0	88.5	87.8	87.1	86.3	85.5	85.0
72.5°	79.1	78.8	78.4	78.1	77.8	77.4	76.9	76.5	76.0	75.5	74.9
75°	62.2	62.0	61.9	61.7	61.6	61.3	60.9	60.4	60.0	59.6	59.1
77.5°	47.1	46.8	46.6	46.3	46.0	45.7	45.6	45.4	45.2	45.1	44.8
80°	37.0	36.9	36.9	36.8	36.7	36.6	36.4	36.3	36.1	36.0	35.7
82.5°	27.6	27.6	27.6	27.5	27.5	27.4	27.3	27.2	27.1	27.1	26.7
85°	15.2	15.1	15.0	14.9	14.8	14.8	14.7	14.6	14.5	14.4	14.2
87.5°	5.5	5.7	6.1	6.2	6.4	6.6	7.1	7.8	8.5	8.5	8.2
90°	0.7	2.5	5.1	6.4	7.7	9.5	12.7	17.2	21.0	21.7	21.0
92.5°	7.7	11.3	15.8	18.6	22.9	28.9	43.4	63.6	81.7	82.8	70.0
95°	22.3	24.9	31.2	36.9	47.1	62.5	91.8	147.2	221.2	249.8	218.6
97.5°	36.4	39.8	46.6	55.2	66.9	84.2	121.1	198.4	321.2	426.5	447.4
100°	49.1	51.0	56.7	66.9	79.7	97.5	131.3	209.0	346.7	503.4	595.3
102.5°	60.8	62.2	67.9	78.1	91.4	109.3	140.5	209.5	337.0	506.1	650.3
105°	77.8	80.3	84.8	94.3	108.4	126.2	156.1	212.9	318.0	472.2	641.8
107.5°	96.1	98.2	102.5	111.3	125.1	143.2	172.2	221.7	308.6	436.0	585.8
110°	108.4	110.9	114.7	123.0	136.4	154.9	182.9	228.8	306.6	418.7	550.7



TEST NUMBER: P331266-930

CATALOG NUMBER: S122DIP-S290D725U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	119.5	122.1	126.5	134.2	147.1	166.1	193.1	236.4	307.0	407.5	526.2
115°	137.1	140.2	144.1	151.6	164.4	181.6	209.0	247.9	309.7	395.2	495.9
117.5°	155.2	157.7	161.5	168.3	180.5	198.4	223.7	260.2	314.3	389.1	476.7
120°	166.3	168.9	172.7	178.5	191.2	209.0	233.9	268.3	317.4	385.6	466.5
122.5°	177.1	179.1	182.9	189.1	201.9	220.3	243.6	275.5	321.0	383.5	457.9
125°	191.2	193.1	196.9	204.6	217.4	235.1	258.1	286.8	326.3	379.8	445.5
127.5°	202.4	205.0	210.3	218.7	231.0	249.3	271.7	297.3	331.8	377.6	434.0
130°	209.0	211.6	217.9	226.9	239.6	257.5	279.8	304.0	335.9	376.7	426.4
132.5°	215.2	218.3	225.1	234.6	247.8	265.6	286.9	310.6	340.0	376.2	420.3
135°	224.4	226.9	234.6	244.1	258.8	276.6	297.0	319.3	344.8	375.4	411.7
137.5°	233.0	236.0	243.7	253.9	268.5	285.0	305.2	326.0	349.1	375.3	405.7
140°	239.6	242.1	249.8	260.0	274.0	290.7	309.7	329.5	351.1	374.7	402.2
142.5°	246.2	248.3	255.4	265.6	279.2	294.7	313.3	332.6	352.7	374.7	398.6
145°	256.2	258.8	265.1	274.7	287.4	301.4	318.7	336.5	354.3	373.5	393.9
147.5°	266.9	268.8	274.9	283.7	294.3	306.8	323.0	338.7	354.9	371.2	389.1
150°	274.0	276.0	281.0	289.3	298.9	310.4	325.1	339.7	354.3	369.7	384.9
152.5°	281.2	282.1	287.1	294.4	303.5	314.0	327.1	340.2	353.4	367.1	381.4
155°	291.2	291.9	295.7	302.7	309.7	319.3	330.1	341.0	351.8	362.6	374.7
157.5°	299.7	300.3	303.4	309.5	315.1	323.1	332.3	341.0	348.9	358.1	368.5
160°	305.2	305.9	308.4	313.6	318.7	325.6	333.3	341.0	347.3	355.0	363.9
162.5°	310.9	310.5	313.1	317.2	321.7	327.2	333.9	340.5	345.8	352.5	359.8
165°	317.4	316.7	318.0	321.9	325.1	328.9	334.6	339.1	342.9	347.3	353.1
167.5°	322.8	322.0	323.1	325.5	327.8	330.3	334.4	338.2	340.0	342.9	346.4
170°	326.3	325.1	325.6	327.6	328.9	330.8	333.9	337.1	338.4	340.3	342.9
172.5°	328.3	327.6	327.2	329.1	329.9	331.3	333.5	335.6	336.4	337.3	339.3
175°	330.8	330.1	329.5	330.8	330.8	331.4	332.6	333.9	333.3	333.9	334.6
177.5°	331.9	330.9	330.4	331.4	331.4	331.4	331.9	333.0	331.9	331.4	331.9
180°	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4



TEST NUMBER: P331266-930

CATALOG NUMBER: S122DIP-S290D725U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1
2.5°	383.5	384.2	384.8	385.1	385.0	384.8	384.7	384.6
5°	381.0	381.6	382.3	382.5	382.4	382.2	382.0	381.9
7.5°	376.7	377.3	378.0	378.2	378.1	377.8	377.6	377.5
10°	372.8	373.5	374.1	374.3	374.1	373.8	373.6	373.3
12.5°	368.3	368.7	369.2	369.3	369.2	368.9	368.8	368.6
15°	360.3	360.6	360.9	360.9	360.5	360.1	359.7	359.3
17.5°	350.8	351.2	351.6	351.6	351.1	350.8	350.4	350.0
20°	343.5	343.7	344.0	343.9	343.6	343.2	342.9	342.6
22.5°	335.7	335.7	335.7	335.7	335.5	335.3	335.1	334.9
25°	322.9	323.1	323.3	323.3	323.1	322.9	322.8	322.6
27.5°	310.4	310.1	309.9	309.6	309.2	308.8	308.4	308.0
30°	300.6	300.4	300.1	299.9	299.5	299.2	298.9	298.5
32.5°	291.1	290.6	290.2	289.8	289.4	289.1	288.8	288.5
35°	275.7	275.2	274.7	274.3	273.9	273.5	273.0	272.6
37.5°	260.2	259.7	259.0	258.5	258.1	257.7	257.4	257.0
40°	249.6	248.9	248.2	247.6	247.3	247.0	246.6	246.3
42.5°	239.1	238.3	237.5	236.8	236.4	235.9	235.5	235.1
45°	223.0	222.1	221.2	220.5	220.2	219.9	219.6	219.2
47.5°	206.3	205.3	204.3	203.6	203.2	202.7	202.2	201.7
50°	195.5	194.3	193.1	192.4	192.0	191.6	191.2	190.8
52.5°	184.3	183.4	182.4	181.6	181.1	180.6	180.0	179.4
55°	167.6	166.6	165.7	165.0	164.6	164.1	163.7	163.3
57.5°	150.3	149.4	148.4	147.7	147.5	147.2	146.8	146.5
60°	138.9	138.0	137.1	136.6	136.3	136.1	135.8	135.6
62.5°	128.1	127.3	126.5	125.9	125.6	125.2	124.9	124.6
65°	111.5	110.7	110.0	109.4	109.0	108.6	108.2	107.8
67.5°	95.1	94.5	93.9	93.4	93.1	92.8	92.5	92.1
70°	84.4	83.8	83.2	82.8	82.5	82.1	81.8	81.4
72.5°	74.4	73.8	73.2	72.7	72.5	72.2	72.0	71.7
75°	58.6	58.1	57.6	57.5	57.6	57.8	58.0	58.1
77.5°	44.6	44.4	44.1	43.9	43.6	43.5	43.2	43.0
80°	35.5	35.2	35.0	34.7	34.6	34.4	34.2	34.1
82.5°	26.4	26.1	25.8	25.6	25.6	25.5	25.5	25.5
85°	13.9	13.7	13.5	13.3	13.2	13.1	13.0	13.0
87.5°	7.8	7.4	7.4	7.4	7.3	7.3	7.3	7.2
90°	20.4	19.2	20.4	21.0	21.0	21.0	21.0	21.0
92.5°	55.6	47.7	42.3	38.4	37.8	35.8	36.4	35.3
95°	167.0	128.1	101.3	87.3	79.0	73.9	72.0	72.6
97.5°	389.6	318.8	249.8	203.8	173.3	157.7	148.4	143.0
100°	581.9	502.9	415.6	338.4	285.5	258.1	239.6	228.1
102.5°	707.8	690.0	626.1	544.4	486.9	440.1	417.0	401.5
105°	774.4	846.4	854.7	833.6	794.1	754.6	727.2	718.3
107.5°	726.4	834.9	901.2	932.1	937.0	934.8	929.4	917.5
110°	685.1	799.2	880.8	933.0	960.4	972.6	978.3	977.6





TEST NUMBER: P331266-930

CATALOG NUMBER: S122DIP-S290D725U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	647.4	756.8	844.1	904.0	942.1	962.4	973.2	976.6
115°	601.0	699.1	782.6	848.2	893.5	922.8	939.4	945.2
117.5°	566.1	652.2	728.0	789.5	835.7	866.7	884.1	888.9
120°	548.7	627.8	695.3	753.3	797.9	827.9	846.4	852.7
122.5°	535.0	607.4	671.3	723.7	763.8	793.2	809.7	815.0
125°	514.9	580.6	636.7	684.4	721.5	745.7	761.6	766.7
127.5°	495.2	554.6	607.5	651.6	683.9	706.5	720.3	724.4
130°	482.4	537.3	587.6	629.7	660.9	682.6	695.3	700.4
132.5°	470.2	521.0	567.2	606.7	637.5	659.1	670.8	675.4
135°	453.1	495.2	537.3	572.9	600.4	621.4	632.8	635.4
137.5°	439.5	474.7	508.1	539.2	564.2	582.3	592.3	596.1
140°	430.8	461.5	490.7	518.8	539.2	555.7	565.3	569.2
142.5°	423.7	449.7	474.9	498.4	517.8	532.8	541.4	542.1
145°	413.6	434.6	454.4	472.9	488.2	499.0	505.4	507.3
147.5°	405.9	422.4	437.8	451.3	464.0	472.6	477.0	478.1
150°	400.2	414.3	427.6	439.1	448.7	456.3	460.2	460.8
152.5°	394.6	407.6	419.0	428.9	436.4	443.0	445.9	446.0
155°	386.9	397.1	406.6	413.6	420.6	425.1	427.6	426.4
157.5°	377.8	386.4	394.4	399.8	404.8	408.5	409.7	409.7
160°	372.2	379.2	386.2	390.7	395.2	398.4	398.9	398.9
162.5°	366.6	372.6	378.5	382.0	386.5	388.7	389.3	388.7
165°	358.2	362.6	367.1	369.7	372.2	374.7	374.7	374.1
167.5°	350.2	353.6	356.6	359.0	360.1	361.5	361.3	360.6
170°	346.1	348.0	350.5	351.8	352.5	354.3	353.7	352.5
172.5°	341.4	342.9	345.0	345.7	346.3	347.2	346.6	345.8
175°	336.5	337.1	337.8	338.4	338.4	339.1	338.4	337.1
177.5°	333.0	333.0	333.5	333.5	333.5	333.5	333.0	331.9
180°	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4

(END OF REPORT)