

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331339-930

Luminaire Tested: **S122DIP-S675D530U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331339-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S675D530U930-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4113.9 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331339-930

CATALOG NUMBER: S122DIP-S675D530U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331339-930

CATALOG NUMBER: S122DIP-S675D530U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58																												
1	100	96	92	89	93	90	86	84	78	76	73	67	65	64	57	56	55	50																												
2	92	84	79	74	85	79	74	69	69	65	62	60	57	54	51	49	47	43																												
3	84	75	68	62	78	70	64	59	61	56	53	53	50	46	46	43	41	37																												
4	77	67	59	53	72	63	56	50	55	50	45	48	44	40	41	38	36	32																												
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28																												
6	66	54	46	40	61	51	44	38	45	39	35	39	35	31	34	31	28	25																												
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	28	25	23																												
8	57	45	37	32	53	42	35	30	37	32	28	33	28	25	29	25	23	20																												
9	53	41	33	28	49	39	32	27	34	29	25	31	26	23	27	23	21	19																												
10	50	38	30	26	46	36	29	25	32	26	23	28	24	21	25	21	19	17																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17486	17486	17486	17486
5°	19603	17598	15595	17598
10°	22463	17454	13496	17454
15°	24849	17135	11925	17135
20°	24471	16790	10869	16790
25°	22066	16335	10203	16335
30°	18233	15605	9715	15605
35°	13291	14840	9368	14840
40°	10614	13940	9177	13940
45°	9275	12896	8914	12896
50°	8719	11886	8741	11886
55°	8037	10860	8504	10860
60°	7363	9771	8147	9771
65°	6709	8795	7790	8795
70°	6090	7841	7270	7841
75°	5402	6775	6438	6775
80°	4649	5607	5188	5607
85°	4168	4168	3075	4168



TEST NUMBER: P331339-930

CATALOG NUMBER: S122DIP-S675D530U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.1	2.5
10°-20°	299.8	7.3
20°-30°	435.1	10.6
30°-40°	459.2	11.2
40°-50°	406.6	9.9
50°-60°	324.5	7.9
60°-70°	220.5	5.4
70°-80°	113.1	2.7
80°-90°	28.7	0.7
90°-100°	19.6	0.5
100°-110°	71.9	1.7
110°-120°	192.3	4.7
120°-130°	317.4	7.7
130°-140°	337.5	8.2
140°-150°	313.7	7.6
150°-160°	252.2	6.1
160°-170°	162.5	4.0
170°-180°	55.9	1.4
0°-30°	838.1	20.4
0°-40°	1297.3	31.5
0°-60°	2028.3	49.3
0°-90°	2390.6	58.1
90°-120°	283.8	6.9
90°-150°	1252.5	30.4
90°-180°	1723.0	41.9
0°-180°	4113.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1083	1083	1083	1083	1083	
5°	1210	1086	962	1086	1210	121
15°	1487	1025	713	1025	1487	410
25°	1239	917	573	917	1239	560
35°	674	753	475	753	674	439
45°	406	565	390	565	406	319
55°	286	386	302	386	286	256
65°	176	230	204	230	176	175
75°	87	109	103	109	87	93
85°	22	22	17	22	22	25
90°	12	0	12	0	12	6
95°	18	28	18	28	18	17
105°	32	129	32	129	32	34
115°	35	245	35	245	35	87
125°	364	346	364	346	364	315
135°	442	428	442	428	442	341
145°	504	496	504	496	504	315
155°	547	547	547	547	547	252
165°	575	576	575	576	575	162
175°	586	589	586	589	586	56
180°	588	588	588	588	588	



TEST NUMBER: P331339-930

CATALOG NUMBER: S122DIP-S675D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1132.9	1133.2	1133.9	1128.5	1127.9	1127.9	1123.2	1119.2	1114.6	1108.2	1108.9
5°	1209.5	1214.1	1215.7	1210.7	1203.2	1202.4	1195.3	1183.7	1172.8	1164.1	1157.9
7.5°	1300.9	1302.7	1298.6	1292.0	1286.5	1276.5	1263.3	1250.4	1232.3	1215.8	1203.5
10°	1370.1	1372.6	1365.5	1356.0	1348.1	1336.4	1317.3	1297.7	1274.0	1251.1	1232.7
12.5°	1422.7	1428.9	1419.8	1418.5	1405.0	1389.0	1366.2	1356.3	1322.9	1291.0	1271.4
15°	1486.6	1486.2	1487.1	1479.2	1469.2	1466.6	1442.5	1416.3	1369.3	1350.5	1318.1
17.5°	1468.2	1474.5	1477.4	1477.3	1477.1	1475.5	1467.8	1451.2	1427.7	1397.3	1359.8
20°	1424.2	1432.6	1433.8	1443.4	1448.8	1455.9	1458.7	1454.2	1439.7	1414.2	1381.8
22.5°	1356.3	1358.6	1362.5	1377.4	1389.2	1406.9	1416.2	1431.6	1426.0	1413.6	1386.4
25°	1238.6	1234.4	1249.0	1256.5	1283.5	1311.8	1332.3	1354.7	1374.7	1386.7	1378.8
27.5°	1097.2	1091.0	1112.8	1132.7	1154.7	1185.4	1217.2	1254.7	1285.9	1324.9	1338.3
30°	978.0	981.8	1002.7	1023.9	1057.1	1100.4	1136.2	1177.5	1222.0	1265.7	1296.0
32.5°	849.5	864.0	877.1	909.6	938.9	987.2	1039.7	1091.2	1146.7	1196.4	1243.4
35°	674.3	690.9	709.2	733.0	774.1	822.0	873.2	942.6	1018.5	1086.3	1142.1
37.5°	567.5	564.8	575.4	592.5	625.9	664.5	723.4	792.1	881.3	961.0	1039.7
40°	503.6	501.9	509.4	525.2	550.7	578.9	630.6	690.9	773.7	871.1	964.7
42.5°	459.7	460.6	464.8	476.0	493.3	516.7	555.3	606.7	682.5	774.2	874.8
45°	406.2	409.1	413.7	419.1	429.1	448.3	469.9	506.5	566.5	643.0	742.1
47.5°	367.8	367.9	372.5	377.2	383.2	394.0	411.6	434.6	476.9	539.2	624.4
50°	347.1	344.2	347.6	351.2	357.5	365.0	376.7	398.3	426.6	477.0	548.1
52.5°	321.8	321.9	324.9	326.3	331.9	339.3	350.0	365.0	390.6	430.0	488.5
55°	285.5	287.6	289.3	291.7	296.8	302.1	310.5	320.5	340.5	370.0	413.3
57.5°	251.4	252.0	253.7	258.4	261.6	266.6	274.5	283.6	296.6	318.5	351.0
60°	228.0	228.0	231.4	233.5	237.7	242.6	248.9	257.6	269.3	287.1	313.4
62.5°	206.8	206.4	207.7	211.2	214.3	219.0	225.3	232.7	243.6	259.5	281.1
65°	175.6	174.8	177.3	178.1	181.5	186.1	191.0	198.9	207.7	219.3	238.5
67.5°	145.7	146.7	148.0	149.6	151.4	156.2	159.6	165.2	172.5	182.2	195.2
70°	129.0	129.0	129.0	130.3	132.7	135.3	138.6	143.2	150.3	158.6	170.2
72.5°	110.4	111.7	113.0	112.3	115.4	116.9	120.9	123.5	130.3	135.6	145.9
75°	86.6	86.6	86.6	88.6	89.9	91.2	93.7	96.1	99.5	106.2	111.5
77.5°	64.6	64.4	64.8	65.3	66.7	68.2	68.9	71.2	74.3	77.3	81.9
80°	50.0	50.8	51.2	52.0	52.0	52.8	53.2	56.2	58.3	60.3	63.3
82.5°	38.6	38.8	38.9	39.1	39.4	39.9	40.9	41.9	42.6	44.4	46.6
85°	22.5	22.1	22.1	22.9	22.5	22.5	23.3	24.1	24.1	24.5	25.8
87.5°	10.9	10.9	11.3	10.8	10.8	11.1	11.0	10.5	10.8	11.0	11.2
90°	11.5	11.3	11.1	10.9	10.8	10.4	9.9	9.5	9.0	8.5	7.7
92.5°	11.5	11.4	11.3	11.2	11.0	10.8	10.6	10.4	10.1	9.9	9.5
95°	18.3	18.4	18.5	18.6	18.7	18.5	18.0	17.5	17.0	16.6	15.9
97.5°	24.5	24.3	24.2	24.1	24.0	23.7	23.3	23.0	22.6	22.2	20.7
100°	28.5	28.3	28.1	28.0	27.7	27.3	26.5	25.8	25.0	24.2	22.7
102.5°	30.6	30.2	30.0	29.8	29.5	28.9	27.9	26.9	25.9	24.9	38.4
105°	32.4	32.0	31.6	31.2	30.8	30.1	29.1	28.0	27.0	25.9	51.8
107.5°	33.3	32.9	32.5	32.1	31.8	32.1	33.2	34.2	35.3	36.4	67.3
110°	33.6	33.3	32.9	32.4	32.1	36.6	46.1	55.5	65.0	74.4	101.7



TEST NUMBER: P331339-930

CATALOG NUMBER: S122DIP-S675D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	33.9	33.7	33.3	33.0	32.8	49.8	84.3	118.8	153.3	187.8	194.5
115°	34.9	41.7	48.5	55.3	62.1	87.4	131.2	175.0	218.7	262.5	260.2
117.5°	142.4	164.9	187.2	209.5	232.0	248.4	259.0	269.6	280.2	290.7	289.2
120°	259.5	272.3	285.1	297.8	310.6	316.4	315.3	314.1	313.0	311.9	310.1
122.5°	323.8	326.4	328.8	331.3	333.8	334.7	334.0	333.3	332.6	332.0	330.1
125°	363.8	363.5	363.2	363.0	362.6	362.2	361.5	360.9	360.2	359.5	357.8
127.5°	389.0	388.9	388.9	388.8	388.7	388.2	387.3	386.3	385.3	384.4	383.0
130°	404.6	404.7	404.8	404.9	405.0	404.6	403.5	402.4	401.5	400.4	399.3
132.5°	420.0	420.0	420.1	420.2	420.3	420.0	419.1	418.2	417.3	416.4	415.3
135°	442.1	442.3	442.5	442.6	442.9	442.5	441.5	440.6	439.6	438.6	437.8
137.5°	462.3	462.6	462.8	463.2	463.5	463.3	462.3	461.4	460.5	459.5	458.5
140°	474.8	475.3	475.8	476.2	476.7	476.5	475.6	474.8	474.0	473.1	472.1
142.5°	487.1	487.5	488.0	488.5	489.0	488.9	488.0	487.3	486.5	485.8	484.5
145°	504.2	504.7	505.2	505.6	506.1	506.0	505.3	504.7	504.0	503.4	501.7
147.5°	519.3	519.7	520.1	520.5	520.8	520.8	520.3	519.8	519.3	518.9	517.2
150°	528.5	528.9	529.4	529.9	530.4	530.3	529.7	529.1	528.6	528.0	526.5
152.5°	536.3	536.9	537.5	538.2	538.7	538.8	538.3	537.7	537.1	536.5	535.1
155°	547.1	548.0	548.7	549.4	550.2	550.3	549.8	549.2	548.6	548.0	546.9
157.5°	557.1	557.8	558.6	559.3	560.1	560.1	559.5	558.8	558.2	557.6	556.8
160°	562.9	563.5	564.3	564.9	565.6	565.6	565.0	564.4	563.9	563.4	562.8
162.5°	567.7	568.5	569.3	570.1	571.0	571.0	570.4	569.7	569.1	568.4	567.9
165°	574.8	575.5	576.2	576.8	577.5	577.5	576.8	576.2	575.5	574.8	574.5
167.5°	579.4	580.2	581.1	581.9	582.8	582.9	582.2	581.5	580.8	580.2	579.9
170°	582.0	582.9	583.8	584.6	585.5	585.5	584.9	584.2	583.6	582.9	582.7
172.5°	584.1	585.0	585.8	586.7	587.5	587.6	586.9	586.3	585.6	585.0	584.7
175°	585.9	586.9	587.7	588.7	589.7	589.8	589.1	588.5	587.8	587.2	586.9
177.5°	587.0	587.7	588.3	589.1	589.7	589.8	589.3	588.7	588.2	587.7	587.6
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331339-930

CATALOG NUMBER: S122DIP-S675D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1111.3	1108.6	1106.9	1100.9	1095.6	1090.3	1088.6	1089.2	1082.0	1075.0	1072.0
5°	1154.5	1146.2	1138.3	1127.1	1113.8	1099.2	1091.7	1085.8	1071.3	1055.5	1046.4
7.5°	1193.4	1181.5	1166.2	1145.0	1125.7	1102.8	1088.2	1075.3	1053.9	1031.7	1018.0
10°	1217.0	1200.7	1181.1	1155.4	1131.6	1103.8	1084.2	1064.6	1039.7	1013.0	996.4
12.5°	1237.3	1215.4	1196.1	1163.0	1135.0	1100.1	1076.8	1049.3	1023.0	991.4	975.1
15°	1285.6	1245.3	1208.6	1171.2	1136.6	1087.9	1062.2	1025.1	990.5	951.5	932.7
17.5°	1323.0	1277.7	1219.9	1172.3	1132.0	1078.2	1040.2	995.9	955.0	910.3	884.8
20°	1344.3	1292.2	1230.3	1173.7	1125.4	1063.8	1022.6	977.2	929.4	879.0	851.5
22.5°	1357.0	1302.3	1241.0	1168.7	1112.1	1052.1	1000.3	950.6	902.0	847.7	818.9
25°	1361.0	1311.0	1246.1	1164.5	1095.4	1027.6	965.2	916.9	858.2	807.4	765.4
27.5°	1341.2	1305.4	1242.9	1156.7	1076.2	996.9	927.3	872.6	810.7	755.5	713.3
30°	1316.9	1296.0	1235.3	1148.7	1060.9	975.6	898.9	837.0	775.3	719.6	676.3
32.5°	1279.2	1274.7	1221.3	1137.3	1044.6	948.6	869.4	806.7	738.4	683.6	642.4
35°	1205.3	1225.3	1191.6	1112.1	1013.8	910.2	824.5	752.9	682.2	629.7	591.0
37.5°	1106.3	1155.8	1147.0	1075.1	972.4	868.5	773.8	699.0	631.5	578.6	540.6
40°	1038.0	1101.2	1110.4	1046.8	943.1	836.2	735.8	661.4	595.6	547.3	509.0
42.5°	964.7	1038.7	1063.8	1012.8	911.1	802.2	701.9	624.7	559.6	512.7	478.7
45°	842.0	939.8	985.1	956.0	857.8	746.2	643.0	564.8	505.6	461.5	435.4
47.5°	727.2	834.1	895.0	884.8	798.4	687.9	586.0	510.9	453.3	418.1	394.6
50°	646.0	755.8	829.5	832.8	755.8	646.4	544.0	473.2	420.4	387.5	368.4
52.5°	575.4	680.2	760.6	778.2	708.2	603.1	506.4	435.9	389.4	359.1	342.0
55°	483.2	571.9	660.9	693.4	637.2	537.3	447.8	385.8	342.1	321.3	306.3
57.5°	401.7	475.6	557.9	593.8	559.1	473.6	389.7	335.9	300.4	282.2	270.7
60°	358.7	417.0	490.2	533.1	503.2	427.1	353.8	302.6	273.5	257.2	246.4
62.5°	318.8	370.4	432.4	471.6	455.3	383.4	317.8	272.6	247.4	232.2	224.5
65°	263.0	303.9	351.7	387.9	377.1	322.5	268.9	230.2	210.2	198.1	191.8
67.5°	216.6	246.1	279.2	311.0	302.2	263.6	220.5	190.4	175.5	165.1	161.3
70°	187.3	209.8	239.3	264.7	257.6	226.0	191.8	166.1	153.2	144.4	140.6
72.5°	159.3	177.8	200.3	221.1	216.3	190.0	161.6	142.1	132.2	124.1	121.0
75°	120.3	134.4	148.1	161.9	160.6	140.2	123.6	108.6	100.7	94.5	93.2
77.5°	88.8	96.7	106.1	114.2	111.9	100.3	87.2	78.7	72.8	68.6	68.0
80°	67.8	72.4	79.1	84.9	82.0	77.0	66.6	60.3	56.2	52.0	50.4
82.5°	49.2	53.8	57.8	60.9	58.7	54.1	47.6	43.4	40.8	38.1	37.3
85°	25.8	28.3	30.0	30.8	30.0	27.1	24.1	22.5	20.4	19.2	18.8
87.5°	11.4	11.3	11.1	11.6	10.4	10.2	8.6	7.4	7.3	7.2	6.7
90°	7.0	6.3	5.5	4.6	3.5	2.5	1.5	0.4	1.5	2.5	3.5
92.5°	9.1	8.7	8.4	8.2	8.3	8.4	8.5	8.6	8.5	8.4	8.3
95°	15.2	14.6	13.9	15.2	18.3	21.4	24.5	27.6	24.5	21.4	18.3
97.5°	19.2	17.6	16.1	19.7	28.5	37.3	46.1	54.9	46.1	37.3	28.5
100°	21.0	19.4	17.9	23.5	36.4	49.4	62.4	75.3	62.4	49.4	36.4
102.5°	51.9	65.3	78.7	86.8	89.5	92.3	95.1	97.8	95.1	92.3	89.5
105°	77.6	103.4	129.2	140.7	137.9	135.0	132.2	129.3	132.2	135.0	137.9
107.5°	98.2	129.2	160.1	174.5	172.2	169.9	167.6	165.3	167.6	169.9	172.2
110°	129.1	156.5	183.8	196.4	194.4	192.5	190.5	188.5	190.5	192.5	194.4



TEST NUMBER: P331339-930

CATALOG NUMBER: S122DIP-S675D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	201.3	208.1	214.8	217.3	215.6	213.8	212.1	210.3	212.1	213.8	215.6
115°	257.8	255.4	253.1	251.1	249.5	247.9	246.2	244.7	246.2	247.9	249.5
117.5°	287.6	285.9	284.3	282.6	280.8	279.0	277.2	275.4	277.2	279.0	280.8
120°	308.5	306.8	305.1	303.5	302.1	300.7	299.2	297.8	299.2	300.7	302.1
122.5°	328.2	326.4	324.6	322.9	321.4	319.9	318.4	316.9	318.4	319.9	321.4
125°	356.0	354.2	352.4	350.8	349.6	348.4	347.2	345.9	347.2	348.4	349.6
127.5°	381.7	380.3	379.0	377.6	376.3	375.0	373.6	372.2	373.6	375.0	376.3
130°	398.3	397.3	396.2	394.9	393.5	391.9	390.4	388.9	390.4	391.9	393.5
132.5°	414.3	413.3	412.2	411.1	409.8	408.5	407.2	405.9	407.2	408.5	409.8
135°	437.0	436.1	435.3	434.1	432.6	431.0	429.6	428.0	429.6	431.0	432.6
137.5°	457.6	456.6	455.7	454.6	453.6	452.5	451.4	450.5	451.4	452.5	453.6
140°	471.1	470.0	469.0	468.1	467.3	466.6	465.8	465.0	465.8	466.6	467.3
142.5°	483.3	482.2	480.9	480.0	479.3	478.7	478.0	477.3	478.0	478.7	479.3
145°	500.1	498.6	496.9	496.2	496.3	496.4	496.4	496.5	496.4	496.4	496.3
147.5°	515.7	514.0	512.5	511.8	512.3	512.6	512.9	513.3	512.9	512.6	512.3
150°	525.0	523.5	522.0	521.5	522.2	522.9	523.5	524.2	523.5	522.9	522.2
152.5°	533.7	532.2	530.8	530.4	531.2	531.9	532.6	533.4	532.6	531.9	531.2
155°	545.8	544.6	543.5	543.3	544.2	545.0	545.9	546.7	545.9	545.0	544.2
157.5°	556.0	555.1	554.4	554.3	555.1	555.8	556.5	557.2	556.5	555.8	555.1
160°	562.2	561.7	561.1	561.1	561.7	562.2	562.8	563.4	562.8	562.2	561.7
162.5°	567.4	567.0	566.5	566.6	567.0	567.6	568.2	568.8	568.2	567.6	567.0
165°	574.2	574.0	573.7	573.8	574.4	574.9	575.5	576.1	575.5	574.9	574.4
167.5°	579.7	579.4	579.1	579.3	579.8	580.4	581.0	581.6	581.0	580.4	579.8
170°	582.5	582.4	582.1	582.4	582.9	583.5	584.1	584.6	584.1	583.5	582.9
172.5°	584.6	584.4	584.2	584.4	585.0	585.5	586.1	586.7	586.1	585.5	585.0
175°	586.8	586.6	586.4	586.6	587.3	588.0	588.6	589.3	588.6	588.0	587.3
177.5°	587.5	587.4	587.3	587.6	588.2	588.6	589.2	589.7	589.2	588.6	588.2
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331339-930

CATALOG NUMBER: S122DIP-S675D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1068.6	1066.7	1059.6	1056.0	1049.9	1044.3	1040.6	1042.4	1043.7	1043.0	1042.0
5°	1038.0	1030.0	1018.0	1007.6	1000.1	986.3	980.6	977.6	975.2	972.2	969.3
7.5°	1001.5	989.0	971.8	956.9	942.9	925.9	916.2	910.3	904.3	897.7	891.9
10°	975.6	958.1	939.8	918.9	902.3	886.9	873.2	864.1	855.7	847.8	842.0
12.5°	948.3	928.1	905.5	877.0	858.7	836.7	834.5	818.4	805.4	800.5	793.7
15°	904.8	876.5	847.8	814.1	799.5	779.5	767.0	754.6	743.3	735.4	733.4
17.5°	855.4	818.8	790.3	766.1	742.2	721.7	710.2	700.2	691.0	680.4	679.0
20°	817.8	786.2	755.0	733.8	709.2	688.4	674.3	664.2	656.3	650.1	644.7
22.5°	782.2	747.5	719.0	695.8	671.6	654.8	643.6	634.0	627.4	620.4	615.4
25°	725.0	698.0	666.8	640.5	620.5	609.8	600.5	592.2	588.1	583.5	577.7
27.5°	675.0	644.9	615.7	595.4	577.9	568.3	561.7	556.1	552.2	549.5	546.3
30°	639.7	609.3	586.4	566.5	551.9	542.3	538.2	534.8	530.3	528.6	526.9
32.5°	605.8	578.4	558.8	541.4	527.6	521.3	517.5	514.5	510.9	509.2	505.9
35°	557.7	534.8	515.7	506.1	494.9	489.4	486.6	482.3	479.1	477.4	477.0
37.5°	512.5	492.6	480.0	467.7	463.0	459.7	455.7	452.8	451.8	451.6	451.2
40°	483.2	467.0	455.8	445.7	443.7	438.6	435.4	432.8	432.8	433.3	432.8
42.5°	456.6	442.0	432.1	423.5	421.0	418.0	414.7	414.5	415.2	416.6	415.2
45°	416.2	405.8	398.7	394.5	390.0	387.0	386.6	387.9	388.3	388.7	390.0
47.5°	379.0	372.2	365.7	361.2	359.1	358.7	358.2	360.4	362.3	363.1	365.0
50°	357.1	349.2	343.8	340.9	339.2	338.3	339.2	341.7	343.3	345.4	346.7
52.5°	332.5	326.9	323.1	320.9	320.2	320.7	320.9	323.8	326.4	327.1	327.8
55°	298.4	294.2	293.4	289.7	291.3	290.9	293.0	294.6	297.2	299.6	300.1
57.5°	264.5	261.1	258.9	259.2	259.7	261.5	263.3	266.2	268.9	271.5	271.7
60°	241.8	240.1	238.9	238.9	239.7	242.2	244.3	247.2	248.9	250.5	251.8
62.5°	221.2	219.5	218.3	218.9	221.1	222.6	225.0	226.6	228.2	229.9	230.5
65°	188.5	187.7	189.0	189.8	190.2	192.2	195.2	196.4	198.1	198.9	201.9
67.5°	158.5	158.7	158.5	159.6	162.1	162.6	165.3	168.2	168.5	170.2	172.0
70°	138.2	139.0	139.8	140.6	142.8	143.6	145.7	146.9	148.5	149.9	151.1
72.5°	119.5	119.7	120.5	120.3	122.1	123.9	125.7	126.9	128.6	130.2	131.4
75°	92.0	92.0	92.8	93.2	95.3	97.4	96.9	97.8	99.5	101.1	102.0
77.5°	67.2	66.3	67.2	67.6	68.2	70.0	70.4	71.5	73.4	72.8	73.8
80°	51.2	50.0	51.2	51.6	51.6	53.7	53.7	54.5	55.8	54.5	55.8
82.5°	36.5	36.0	36.9	36.9	37.6	37.7	38.4	38.6	39.8	39.2	39.8
85°	18.3	17.9	18.3	17.9	18.3	18.8	18.8	18.3	18.3	19.2	17.9
87.5°	6.6	6.4	6.3	6.4	6.2	6.0	5.8	5.9	6.0	5.4	5.5
90°	4.6	5.5	6.3	7.0	7.7	8.5	9.0	9.5	9.9	10.4	10.8
92.5°	8.2	8.4	8.7	9.1	9.5	9.9	10.1	10.4	10.6	10.8	11.0
95°	15.2	13.9	14.6	15.2	15.9	16.6	17.0	17.5	18.0	18.5	18.7
97.5°	19.7	16.1	17.6	19.2	20.7	22.2	22.6	23.0	23.3	23.7	24.0
100°	23.5	17.9	19.4	21.0	22.7	24.2	25.0	25.8	26.5	27.3	27.7
102.5°	86.8	78.7	65.3	51.9	38.4	24.9	25.9	26.9	27.9	28.9	29.5
105°	140.7	129.2	103.4	77.6	51.8	25.9	27.0	28.0	29.1	30.1	30.8
107.5°	174.5	160.1	129.2	98.2	67.3	36.4	35.3	34.2	33.2	32.1	31.8
110°	196.4	183.8	156.5	129.1	101.7	74.4	65.0	55.5	46.1	36.6	32.1



TEST NUMBER: P331339-930

CATALOG NUMBER: S122DIP-S675D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	217.3	214.8	208.1	201.3	194.5	187.8	153.3	118.8	84.3	49.8	32.8
115°	251.1	253.1	255.4	257.8	260.2	262.5	218.7	175.0	131.2	87.4	62.1
117.5°	282.6	284.3	285.9	287.6	289.2	290.7	280.2	269.6	259.0	248.4	232.0
120°	303.5	305.1	306.8	308.5	310.1	311.9	313.0	314.1	315.3	316.4	310.6
122.5°	322.9	324.6	326.4	328.2	330.1	332.0	332.6	333.3	334.0	334.7	333.8
125°	350.8	352.4	354.2	356.0	357.8	359.5	360.2	360.9	361.5	362.2	362.6
127.5°	377.6	379.0	380.3	381.7	383.0	384.4	385.3	386.3	387.3	388.2	388.7
130°	394.9	396.2	397.3	398.3	399.3	400.4	401.5	402.4	403.5	404.6	405.0
132.5°	411.1	412.2	413.3	414.3	415.3	416.4	417.3	418.2	419.1	420.0	420.3
135°	434.1	435.3	436.1	437.0	437.8	438.6	439.6	440.6	441.5	442.5	442.9
137.5°	454.6	455.7	456.6	457.6	458.5	459.5	460.5	461.4	462.3	463.3	463.5
140°	468.1	469.0	470.0	471.1	472.1	473.1	474.0	474.8	475.6	476.5	476.7
142.5°	480.0	480.9	482.2	483.3	484.5	485.8	486.5	487.3	488.0	488.9	489.0
145°	496.2	496.9	498.6	500.1	501.7	503.4	504.0	504.7	505.3	506.0	506.1
147.5°	511.8	512.5	514.0	515.7	517.2	518.9	519.3	519.8	520.3	520.8	520.8
150°	521.5	522.0	523.5	525.0	526.5	528.0	528.6	529.1	529.7	530.3	530.4
152.5°	530.4	530.8	532.2	533.7	535.1	536.5	537.1	537.7	538.3	538.8	538.7
155°	543.3	543.5	544.6	545.8	546.9	548.0	548.6	549.2	549.8	550.3	550.2
157.5°	554.3	554.4	555.1	556.0	556.8	557.6	558.2	558.8	559.5	560.1	560.1
160°	561.1	561.1	561.7	562.2	562.8	563.4	563.9	564.4	565.0	565.6	565.6
162.5°	566.6	566.5	567.0	567.4	567.9	568.4	569.1	569.7	570.4	571.0	571.0
165°	573.8	573.7	574.0	574.2	574.5	574.8	575.5	576.2	576.8	577.5	577.5
167.5°	579.3	579.1	579.4	579.7	579.9	580.2	580.8	581.5	582.2	582.9	582.8
170°	582.4	582.1	582.4	582.5	582.7	582.9	583.6	584.2	584.9	585.5	585.5
172.5°	584.4	584.2	584.4	584.6	584.7	585.0	585.6	586.3	586.9	587.6	587.5
175°	586.6	586.4	586.6	586.8	586.9	587.2	587.8	588.5	589.1	589.8	589.7
177.5°	587.6	587.3	587.4	587.5	587.6	587.7	588.2	588.7	589.3	589.8	589.7
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331339-930

CATALOG NUMBER: S122DIP-S675D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1038.7	1038.0	1038.0	1035.0	1038.0	1038.0	1038.7	1042.0	1043.0	1043.7	1042.4
5°	963.5	962.2	960.2	962.2	960.2	962.2	963.5	969.3	972.2	975.2	977.6
7.5°	889.2	884.2	883.5	878.5	883.5	884.2	889.2	891.9	897.7	904.3	910.3
10°	834.9	831.5	831.1	823.2	831.1	831.5	834.9	842.0	847.8	855.7	864.1
12.5°	793.6	785.6	787.2	782.6	787.2	785.6	793.6	793.7	800.5	805.4	818.4
15°	722.1	722.1	720.4	713.4	720.4	722.1	722.1	733.4	735.4	743.3	754.6
17.5°	670.7	669.9	665.9	667.9	665.9	669.9	670.7	679.0	680.4	691.0	700.2
20°	640.1	637.6	632.6	632.6	632.6	637.6	640.1	644.7	650.1	656.3	664.2
22.5°	611.1	611.0	605.7	607.3	605.7	611.0	611.1	615.4	620.4	627.4	634.0
25°	577.2	574.0	571.4	572.7	571.4	574.0	577.2	577.7	583.5	588.1	592.2
27.5°	545.1	543.3	543.2	539.7	543.2	543.3	545.1	546.3	549.5	552.2	556.1
30°	526.5	522.4	523.2	521.1	523.2	522.4	526.5	526.9	528.6	530.3	534.8
32.5°	505.2	503.7	502.9	501.1	502.9	503.7	505.2	505.9	509.2	510.9	514.5
35°	476.1	476.5	474.5	475.3	474.5	476.5	476.1	477.0	477.4	479.1	482.3
37.5°	450.8	452.1	451.1	451.3	451.1	452.1	450.8	451.2	451.6	451.8	452.8
40°	434.1	434.1	434.1	435.4	434.1	434.1	434.1	432.8	433.3	432.8	432.8
42.5°	418.1	417.4	416.8	416.7	416.8	417.4	418.1	415.2	416.6	415.2	414.5
45°	390.8	392.1	392.5	390.4	392.5	392.1	390.8	390.0	388.7	388.3	387.9
47.5°	366.1	366.2	366.1	367.9	366.1	366.2	366.1	365.0	363.1	362.3	360.4
50°	348.8	348.0	348.8	348.0	348.8	348.0	348.8	346.7	345.4	343.3	341.7
52.5°	330.4	330.6	330.1	330.0	330.1	330.6	330.4	327.8	327.1	326.4	323.8
55°	301.7	302.6	302.1	302.1	302.1	302.6	301.7	300.1	299.6	297.2	294.6
57.5°	272.1	272.8	273.4	271.5	273.4	272.8	272.1	271.7	271.5	268.9	266.2
60°	251.4	253.5	253.1	252.3	253.1	253.5	251.4	251.8	250.5	248.9	247.2
62.5°	232.4	233.2	233.1	232.9	233.1	233.2	232.4	230.5	229.9	228.2	226.6
65°	203.1	203.9	202.7	203.9	202.7	203.9	203.1	201.9	198.9	198.1	196.4
67.5°	171.5	171.8	172.8	173.3	172.8	171.8	171.5	172.0	170.2	168.5	168.2
70°	151.9	151.5	152.7	154.0	152.7	151.5	151.9	151.1	149.9	148.5	146.9
72.5°	131.3	132.2	131.8	132.6	131.8	132.2	131.3	131.4	130.2	128.6	126.9
75°	101.1	102.4	102.0	103.2	102.0	102.4	101.1	102.0	101.1	99.5	97.8
77.5°	73.1	73.2	73.1	73.8	73.1	73.2	73.1	73.8	72.8	73.4	71.5
80°	55.8	55.0	54.1	55.8	54.1	55.0	55.8	55.8	54.5	55.8	54.5
82.5°	38.8	39.3	38.5	38.5	38.5	39.3	38.8	39.8	39.2	39.8	38.6
85°	17.9	17.4	16.6	16.6	16.6	17.4	17.9	17.9	19.2	18.3	18.3
87.5°	5.5	5.2	5.2	5.0	5.2	5.2	5.5	5.5	5.4	6.0	5.9
90°	10.9	11.1	11.3	11.5	11.3	11.1	10.9	10.8	10.4	9.9	9.5
92.5°	11.2	11.3	11.4	11.5	11.4	11.3	11.2	11.0	10.8	10.6	10.4
95°	18.6	18.5	18.4	18.3	18.4	18.5	18.6	18.7	18.5	18.0	17.5
97.5°	24.1	24.2	24.3	24.5	24.3	24.2	24.1	24.0	23.7	23.3	23.0
100°	28.0	28.1	28.3	28.5	28.3	28.1	28.0	27.7	27.3	26.5	25.8
102.5°	29.8	30.0	30.2	30.6	30.2	30.0	29.8	29.5	28.9	27.9	26.9
105°	31.2	31.6	32.0	32.4	32.0	31.6	31.2	30.8	30.1	29.1	28.0
107.5°	32.1	32.5	32.9	33.3	32.9	32.5	32.1	31.8	32.1	33.2	34.2
110°	32.4	32.9	33.3	33.6	33.3	32.9	32.4	32.1	36.6	46.1	55.5



TEST NUMBER: P331339-930

CATALOG NUMBER: S122DIP-S675D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	33.0	33.3	33.7	33.9	33.7	33.3	33.0	32.8	49.8	84.3	118.8
115°	55.3	48.5	41.7	34.9	41.7	48.5	55.3	62.1	87.4	131.2	175.0
117.5°	209.5	187.2	164.9	142.4	164.9	187.2	209.5	232.0	248.4	259.0	269.6
120°	297.8	285.1	272.3	259.5	272.3	285.1	297.8	310.6	316.4	315.3	314.1
122.5°	331.3	328.8	326.4	323.8	326.4	328.8	331.3	333.8	334.7	334.0	333.3
125°	363.0	363.2	363.5	363.8	363.5	363.2	363.0	362.6	362.2	361.5	360.9
127.5°	388.8	388.9	388.9	389.0	388.9	388.9	388.8	388.7	388.2	387.3	386.3
130°	404.9	404.8	404.7	404.6	404.7	404.8	404.9	405.0	404.6	403.5	402.4
132.5°	420.2	420.1	420.0	420.0	420.0	420.1	420.2	420.3	420.0	419.1	418.2
135°	442.6	442.5	442.3	442.1	442.3	442.5	442.6	442.9	442.5	441.5	440.6
137.5°	463.2	462.8	462.6	462.3	462.6	462.8	463.2	463.5	463.3	462.3	461.4
140°	476.2	475.8	475.3	474.8	475.3	475.8	476.2	476.7	476.5	475.6	474.8
142.5°	488.5	488.0	487.5	487.1	487.5	488.0	488.5	489.0	488.9	488.0	487.3
145°	505.6	505.2	504.7	504.2	504.7	505.2	505.6	506.1	506.0	505.3	504.7
147.5°	520.5	520.1	519.7	519.3	519.7	520.1	520.5	520.8	520.8	520.3	519.8
150°	529.9	529.4	528.9	528.5	528.9	529.4	529.9	530.4	530.3	529.7	529.1
152.5°	538.2	537.5	536.9	536.3	536.9	537.5	538.2	538.7	538.8	538.3	537.7
155°	549.4	548.7	548.0	547.1	548.0	548.7	549.4	550.2	550.3	549.8	549.2
157.5°	559.3	558.6	557.8	557.1	557.8	558.6	559.3	560.1	560.1	559.5	558.8
160°	564.9	564.3	563.5	562.9	563.5	564.3	564.9	565.6	565.6	565.0	564.4
162.5°	570.1	569.3	568.5	567.7	568.5	569.3	570.1	571.0	571.0	570.4	569.7
165°	576.8	576.2	575.5	574.8	575.5	576.2	576.8	577.5	577.5	576.8	576.2
167.5°	581.9	581.1	580.2	579.4	580.2	581.1	581.9	582.8	582.9	582.2	581.5
170°	584.6	583.8	582.9	582.0	582.9	583.8	584.6	585.5	585.5	584.9	584.2
172.5°	586.7	585.8	585.0	584.1	585.0	585.8	586.7	587.5	587.6	586.9	586.3
175°	588.7	587.7	586.9	585.9	586.9	587.7	588.7	589.7	589.8	589.1	588.5
177.5°	589.1	588.3	587.7	587.0	587.7	588.3	589.1	589.7	589.8	589.3	588.7
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331339-930

CATALOG NUMBER: S122DIP-S675D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1040.6	1044.3	1049.9	1056.0	1059.6	1066.7	1068.6	1072.0	1075.0	1082.0	1089.2
5°	980.6	986.3	1000.1	1007.6	1018.0	1030.0	1038.0	1046.4	1055.5	1071.3	1085.8
7.5°	916.2	925.9	942.9	956.9	971.8	989.0	1001.5	1018.0	1031.7	1053.9	1075.3
10°	873.2	886.9	902.3	918.9	939.8	958.1	975.6	996.4	1013.0	1039.7	1064.6
12.5°	834.5	836.7	858.7	877.0	905.5	928.1	948.3	975.1	991.4	1023.0	1049.3
15°	767.0	779.5	799.5	814.1	847.8	876.5	904.8	932.7	951.5	990.5	1025.1
17.5°	710.2	721.7	742.2	766.1	790.3	818.8	855.4	884.8	910.3	955.0	995.9
20°	674.3	688.4	709.2	733.8	755.0	786.2	817.8	851.5	879.0	929.4	977.2
22.5°	643.6	654.8	671.6	695.8	719.0	747.5	782.2	818.9	847.7	902.0	950.6
25°	600.5	609.8	620.5	640.5	666.8	698.0	725.0	765.4	807.4	858.2	916.9
27.5°	561.7	568.3	577.9	595.4	615.7	644.9	675.0	713.3	755.5	810.7	872.6
30°	538.2	542.3	551.9	566.5	586.4	609.3	639.7	676.3	719.6	775.3	837.0
32.5°	517.5	521.3	527.6	541.4	558.8	578.4	605.8	642.4	683.6	738.4	806.7
35°	486.6	489.4	494.9	506.1	515.7	534.8	557.7	591.0	629.7	682.2	752.9
37.5°	455.7	459.7	463.0	467.7	480.0	492.6	512.5	540.6	578.6	631.5	699.0
40°	435.4	438.6	443.7	445.7	455.8	467.0	483.2	509.0	547.3	595.6	661.4
42.5°	414.7	418.0	421.0	423.5	432.1	442.0	456.6	478.7	512.7	559.6	624.7
45°	386.6	387.0	390.0	394.5	398.7	405.8	416.2	435.4	461.5	505.6	564.8
47.5°	358.2	358.7	359.1	361.2	365.7	372.2	379.0	394.6	418.1	453.3	510.9
50°	339.2	338.3	339.2	340.9	343.8	349.2	357.1	368.4	387.5	420.4	473.2
52.5°	320.9	320.7	320.2	320.9	323.1	326.9	332.5	342.0	359.1	389.4	435.9
55°	293.0	290.9	291.3	289.7	293.4	294.2	298.4	306.3	321.3	342.1	385.8
57.5°	263.3	261.5	259.7	259.2	258.9	261.1	264.5	270.7	282.2	300.4	335.9
60°	244.3	242.2	239.7	238.9	238.9	240.1	241.8	246.4	257.2	273.5	302.6
62.5°	225.0	222.6	221.1	218.9	218.3	219.5	221.2	224.5	232.2	247.4	272.6
65°	195.2	192.2	190.2	189.8	189.0	187.7	188.5	191.8	198.1	210.2	230.2
67.5°	165.3	162.6	162.1	159.6	158.5	158.7	158.5	161.3	165.1	175.5	190.4
70°	145.7	143.6	142.8	140.6	139.8	139.0	138.2	140.6	144.4	153.2	166.1
72.5°	125.7	123.9	122.1	120.3	120.5	119.7	119.5	121.0	124.1	132.2	142.1
75°	96.9	97.4	95.3	93.2	92.8	92.0	92.0	93.2	94.5	100.7	108.6
77.5°	70.4	70.0	68.2	67.6	67.2	66.3	67.2	68.0	68.6	72.8	78.7
80°	53.7	53.7	51.6	51.6	51.2	50.0	51.2	50.4	52.0	56.2	60.3
82.5°	38.4	37.7	37.6	36.9	36.9	36.0	36.5	37.3	38.1	40.8	43.4
85°	18.8	18.8	18.3	17.9	18.3	17.9	18.3	18.8	19.2	20.4	22.5
87.5°	5.8	6.0	6.2	6.4	6.3	6.4	6.6	6.7	7.2	7.3	7.4
90°	9.0	8.5	7.7	7.0	6.3	5.5	4.6	3.5	2.5	1.5	0.4
92.5°	10.1	9.9	9.5	9.1	8.7	8.4	8.2	8.3	8.4	8.5	8.6
95°	17.0	16.6	15.9	15.2	14.6	13.9	15.2	18.3	21.4	24.5	27.6
97.5°	22.6	22.2	20.7	19.2	17.6	16.1	19.7	28.5	37.3	46.1	54.9
100°	25.0	24.2	22.7	21.0	19.4	17.9	23.5	36.4	49.4	62.4	75.3
102.5°	25.9	24.9	38.4	51.9	65.3	78.7	86.8	89.5	92.3	95.1	97.8
105°	27.0	25.9	51.8	77.6	103.4	129.2	140.7	137.9	135.0	132.2	129.3
107.5°	35.3	36.4	67.3	98.2	129.2	160.1	174.5	172.2	169.9	167.6	165.3
110°	65.0	74.4	101.7	129.1	156.5	183.8	196.4	194.4	192.5	190.5	188.5



TEST NUMBER: P331339-930

CATALOG NUMBER: S122DIP-S675D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	153.3	187.8	194.5	201.3	208.1	214.8	217.3	215.6	213.8	212.1	210.3
115°	218.7	262.5	260.2	257.8	255.4	253.1	251.1	249.5	247.9	246.2	244.7
117.5°	280.2	290.7	289.2	287.6	285.9	284.3	282.6	280.8	279.0	277.2	275.4
120°	313.0	311.9	310.1	308.5	306.8	305.1	303.5	302.1	300.7	299.2	297.8
122.5°	332.6	332.0	330.1	328.2	326.4	324.6	322.9	321.4	319.9	318.4	316.9
125°	360.2	359.5	357.8	356.0	354.2	352.4	350.8	349.6	348.4	347.2	345.9
127.5°	385.3	384.4	383.0	381.7	380.3	379.0	377.6	376.3	375.0	373.6	372.2
130°	401.5	400.4	399.3	398.3	397.3	396.2	394.9	393.5	391.9	390.4	388.9
132.5°	417.3	416.4	415.3	414.3	413.3	412.2	411.1	409.8	408.5	407.2	405.9
135°	439.6	438.6	437.8	437.0	436.1	435.3	434.1	432.6	431.0	429.6	428.0
137.5°	460.5	459.5	458.5	457.6	456.6	455.7	454.6	453.6	452.5	451.4	450.5
140°	474.0	473.1	472.1	471.1	470.0	469.0	468.1	467.3	466.6	465.8	465.0
142.5°	486.5	485.8	484.5	483.3	482.2	480.9	480.0	479.3	478.7	478.0	477.3
145°	504.0	503.4	501.7	500.1	498.6	496.9	496.2	496.3	496.4	496.4	496.5
147.5°	519.3	518.9	517.2	515.7	514.0	512.5	511.8	512.3	512.6	512.9	513.3
150°	528.6	528.0	526.5	525.0	523.5	522.0	521.5	522.2	522.9	523.5	524.2
152.5°	537.1	536.5	535.1	533.7	532.2	530.8	530.4	531.2	531.9	532.6	533.4
155°	548.6	548.0	546.9	545.8	544.6	543.5	543.3	544.2	545.0	545.9	546.7
157.5°	558.2	557.6	556.8	556.0	555.1	554.4	554.3	555.1	555.8	556.5	557.2
160°	563.9	563.4	562.8	562.2	561.7	561.1	561.1	561.7	562.2	562.8	563.4
162.5°	569.1	568.4	567.9	567.4	567.0	566.5	566.6	567.0	567.6	568.2	568.8
165°	575.5	574.8	574.5	574.2	574.0	573.7	573.8	574.4	574.9	575.5	576.1
167.5°	580.8	580.2	579.9	579.7	579.4	579.1	579.3	579.8	580.4	581.0	581.6
170°	583.6	582.9	582.7	582.5	582.4	582.1	582.4	582.9	583.5	584.1	584.6
172.5°	585.6	585.0	584.7	584.6	584.4	584.2	584.4	585.0	585.5	586.1	586.7
175°	587.8	587.2	586.9	586.8	586.6	586.4	586.6	587.3	588.0	588.6	589.3
177.5°	588.2	587.7	587.6	587.5	587.4	587.3	587.6	588.2	588.6	589.2	589.7
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331339-930

CATALOG NUMBER: S122DIP-S675D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1088.6	1090.3	1095.6	1100.9	1106.9	1108.6	1111.3	1108.9	1108.2	1114.6	1119.2
5°	1091.7	1099.2	1113.8	1127.1	1138.3	1146.2	1154.5	1157.9	1164.1	1172.8	1183.7
7.5°	1088.2	1102.8	1125.7	1145.0	1166.2	1181.5	1193.4	1203.5	1215.8	1232.3	1250.4
10°	1084.2	1103.8	1131.6	1155.4	1181.1	1200.7	1217.0	1232.7	1251.1	1274.0	1297.7
12.5°	1076.8	1100.1	1135.0	1163.0	1196.1	1215.4	1237.3	1271.4	1291.0	1322.9	1356.3
15°	1062.2	1087.9	1136.6	1171.2	1208.6	1245.3	1285.6	1318.1	1350.5	1369.3	1416.3
17.5°	1040.2	1078.2	1132.0	1172.3	1219.9	1277.7	1323.0	1359.8	1397.3	1427.7	1451.2
20°	1022.6	1063.8	1125.4	1173.7	1230.3	1292.2	1344.3	1381.8	1414.2	1439.7	1454.2
22.5°	1000.3	1052.1	1112.1	1168.7	1241.0	1302.3	1357.0	1386.4	1413.6	1426.0	1431.6
25°	965.2	1027.6	1095.4	1164.5	1246.1	1311.0	1361.0	1378.8	1386.7	1374.7	1354.7
27.5°	927.3	996.9	1076.2	1156.7	1242.9	1305.4	1341.2	1338.3	1324.9	1285.9	1254.7
30°	898.9	975.6	1060.9	1148.7	1235.3	1296.0	1316.9	1296.0	1265.7	1222.0	1177.5
32.5°	869.4	948.6	1044.6	1137.3	1221.3	1274.7	1279.2	1243.4	1196.4	1146.7	1091.2
35°	824.5	910.2	1013.8	1112.1	1191.6	1225.3	1205.3	1142.1	1086.3	1018.5	942.6
37.5°	773.8	868.5	972.4	1075.1	1147.0	1155.8	1106.3	1039.7	961.0	881.3	792.1
40°	735.8	836.2	943.1	1046.8	1110.4	1101.2	1038.0	964.7	871.1	773.7	690.9
42.5°	701.9	802.2	911.1	1012.8	1063.8	1038.7	964.7	874.8	774.2	682.5	606.7
45°	643.0	746.2	857.8	956.0	985.1	939.8	842.0	742.1	643.0	566.5	506.5
47.5°	586.0	687.9	798.4	884.8	895.0	834.1	727.2	624.4	539.2	476.9	434.6
50°	544.0	646.4	755.8	832.8	829.5	755.8	646.0	548.1	477.0	426.6	398.3
52.5°	506.4	603.1	708.2	778.2	760.6	680.2	575.4	488.5	430.0	390.6	365.0
55°	447.8	537.3	637.2	693.4	660.9	571.9	483.2	413.3	370.0	340.5	320.5
57.5°	389.7	473.6	559.1	593.8	557.9	475.6	401.7	351.0	318.5	296.6	283.6
60°	353.8	427.1	503.2	533.1	490.2	417.0	358.7	313.4	287.1	269.3	257.6
62.5°	317.8	383.4	455.3	471.6	432.4	370.4	318.8	281.1	259.5	243.6	232.7
65°	268.9	322.5	377.1	387.9	351.7	303.9	263.0	238.5	219.3	207.7	198.9
67.5°	220.5	263.6	302.2	311.0	279.2	246.1	216.6	195.2	182.2	172.5	165.2
70°	191.8	226.0	257.6	264.7	239.3	209.8	187.3	170.2	158.6	150.3	143.2
72.5°	161.6	190.0	216.3	221.1	200.3	177.8	159.3	145.9	135.6	130.3	123.5
75°	123.6	140.2	160.6	161.9	148.1	134.4	120.3	111.5	106.2	99.5	96.1
77.5°	87.2	100.3	111.9	114.2	106.1	96.7	88.8	81.9	77.3	74.3	71.2
80°	66.6	77.0	82.0	84.9	79.1	72.4	67.8	63.3	60.3	58.3	56.2
82.5°	47.6	54.1	58.7	60.9	57.8	53.8	49.2	46.6	44.4	42.6	41.9
85°	24.1	27.1	30.0	30.8	30.0	28.3	25.8	25.8	24.5	24.1	24.1
87.5°	8.6	10.2	10.4	11.6	11.1	11.3	11.4	11.2	11.0	10.8	10.5
90°	1.5	2.5	3.5	4.6	5.5	6.3	7.0	7.7	8.5	9.0	9.5
92.5°	8.5	8.4	8.3	8.2	8.4	8.7	9.1	9.5	9.9	10.1	10.4
95°	24.5	21.4	18.3	15.2	13.9	14.6	15.2	15.9	16.6	17.0	17.5
97.5°	46.1	37.3	28.5	19.7	16.1	17.6	19.2	20.7	22.2	22.6	23.0
100°	62.4	49.4	36.4	23.5	17.9	19.4	21.0	22.7	24.2	25.0	25.8
102.5°	95.1	92.3	89.5	86.8	78.7	65.3	51.9	38.4	24.9	25.9	26.9
105°	132.2	135.0	137.9	140.7	129.2	103.4	77.6	51.8	25.9	27.0	28.0
107.5°	167.6	169.9	172.2	174.5	160.1	129.2	98.2	67.3	36.4	35.3	34.2
110°	190.5	192.5	194.4	196.4	183.8	156.5	129.1	101.7	74.4	65.0	55.5



TEST NUMBER: P331339-930

CATALOG NUMBER: S122DIP-S675D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	212.1	213.8	215.6	217.3	214.8	208.1	201.3	194.5	187.8	153.3	118.8
115°	246.2	247.9	249.5	251.1	253.1	255.4	257.8	260.2	262.5	218.7	175.0
117.5°	277.2	279.0	280.8	282.6	284.3	285.9	287.6	289.2	290.7	280.2	269.6
120°	299.2	300.7	302.1	303.5	305.1	306.8	308.5	310.1	311.9	313.0	314.1
122.5°	318.4	319.9	321.4	322.9	324.6	326.4	328.2	330.1	332.0	332.6	333.3
125°	347.2	348.4	349.6	350.8	352.4	354.2	356.0	357.8	359.5	360.2	360.9
127.5°	373.6	375.0	376.3	377.6	379.0	380.3	381.7	383.0	384.4	385.3	386.3
130°	390.4	391.9	393.5	394.9	396.2	397.3	398.3	399.3	400.4	401.5	402.4
132.5°	407.2	408.5	409.8	411.1	412.2	413.3	414.3	415.3	416.4	417.3	418.2
135°	429.6	431.0	432.6	434.1	435.3	436.1	437.0	437.8	438.6	439.6	440.6
137.5°	451.4	452.5	453.6	454.6	455.7	456.6	457.6	458.5	459.5	460.5	461.4
140°	465.8	466.6	467.3	468.1	469.0	470.0	471.1	472.1	473.1	474.0	474.8
142.5°	478.0	478.7	479.3	480.0	480.9	482.2	483.3	484.5	485.8	486.5	487.3
145°	496.4	496.4	496.3	496.2	496.9	498.6	500.1	501.7	503.4	504.0	504.7
147.5°	512.9	512.6	512.3	511.8	512.5	514.0	515.7	517.2	518.9	519.3	519.8
150°	523.5	522.9	522.2	521.5	522.0	523.5	525.0	526.5	528.0	528.6	529.1
152.5°	532.6	531.9	531.2	530.4	530.8	532.2	533.7	535.1	536.5	537.1	537.7
155°	545.9	545.0	544.2	543.3	543.5	544.6	545.8	546.9	548.0	548.6	549.2
157.5°	556.5	555.8	555.1	554.3	554.4	555.1	556.0	556.8	557.6	558.2	558.8
160°	562.8	562.2	561.7	561.1	561.1	561.7	562.2	562.8	563.4	563.9	564.4
162.5°	568.2	567.6	567.0	566.6	566.5	567.0	567.4	567.9	568.4	569.1	569.7
165°	575.5	574.9	574.4	573.8	573.7	574.0	574.2	574.5	574.8	575.5	576.2
167.5°	581.0	580.4	579.8	579.3	579.1	579.4	579.7	579.9	580.2	580.8	581.5
170°	584.1	583.5	582.9	582.4	582.1	582.4	582.5	582.7	582.9	583.6	584.2
172.5°	586.1	585.5	585.0	584.4	584.2	584.4	584.6	584.7	585.0	585.6	586.3
175°	588.6	588.0	587.3	586.6	586.4	586.6	586.8	586.9	587.2	587.8	588.5
177.5°	589.2	588.6	588.2	587.6	587.3	587.4	587.5	587.6	587.7	588.2	588.7
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331339-930

CATALOG NUMBER: S122DIP-S675D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1123.2	1127.9	1127.9	1128.5	1133.9	1133.2	1132.9
5°	1195.3	1202.4	1203.2	1210.7	1215.7	1214.1	1209.5
7.5°	1263.3	1276.5	1286.5	1292.0	1298.6	1302.7	1300.9
10°	1317.3	1336.4	1348.1	1356.0	1365.5	1372.6	1370.1
12.5°	1366.2	1389.0	1405.0	1418.5	1419.8	1428.9	1422.7
15°	1442.5	1466.6	1469.2	1479.2	1487.1	1486.2	1486.6
17.5°	1467.8	1475.5	1477.1	1477.3	1477.4	1474.5	1468.2
20°	1458.7	1455.9	1448.8	1443.4	1433.8	1432.6	1424.2
22.5°	1416.2	1406.9	1389.2	1377.4	1362.5	1358.6	1356.3
25°	1332.3	1311.8	1283.5	1256.5	1249.0	1234.4	1238.6
27.5°	1217.2	1185.4	1154.7	1132.7	1112.8	1091.0	1097.2
30°	1136.2	1100.4	1057.1	1023.9	1002.7	981.8	978.0
32.5°	1039.7	987.2	938.9	909.6	877.1	864.0	849.5
35°	873.2	822.0	774.1	733.0	709.2	690.9	674.3
37.5°	723.4	664.5	625.9	592.5	575.4	564.8	567.5
40°	630.6	578.9	550.7	525.2	509.4	501.9	503.6
42.5°	555.3	516.7	493.3	476.0	464.8	460.6	459.7
45°	469.9	448.3	429.1	419.1	413.7	409.1	406.2
47.5°	411.6	394.0	383.2	377.2	372.5	367.9	367.8
50°	376.7	365.0	357.5	351.2	347.6	344.2	347.1
52.5°	350.0	339.3	331.9	326.3	324.9	321.9	321.8
55°	310.5	302.1	296.8	291.7	289.3	287.6	285.5
57.5°	274.5	266.6	261.6	258.4	253.7	252.0	251.4
60°	248.9	242.6	237.7	233.5	231.4	228.0	228.0
62.5°	225.3	219.0	214.3	211.2	207.7	206.4	206.8
65°	191.0	186.1	181.5	178.1	177.3	174.8	175.6
67.5°	159.6	156.2	151.4	149.6	148.0	146.7	145.7
70°	138.6	135.3	132.7	130.3	129.0	129.0	129.0
72.5°	120.9	116.9	115.4	112.3	113.0	111.7	110.4
75°	93.7	91.2	89.9	88.6	86.6	86.6	86.6
77.5°	68.9	68.2	66.7	65.3	64.8	64.4	64.6
80°	53.2	52.8	52.0	52.0	51.2	50.8	50.0
82.5°	40.9	39.9	39.4	39.1	38.9	38.8	38.6
85°	23.3	22.5	22.5	22.9	22.1	22.1	22.5
87.5°	11.0	11.1	10.8	10.8	11.3	10.9	10.9
90°	9.9	10.4	10.8	10.9	11.1	11.3	11.5
92.5°	10.6	10.8	11.0	11.2	11.3	11.4	11.5
95°	18.0	18.5	18.7	18.6	18.5	18.4	18.3
97.5°	23.3	23.7	24.0	24.1	24.2	24.3	24.5
100°	26.5	27.3	27.7	28.0	28.1	28.3	28.5
102.5°	27.9	28.9	29.5	29.8	30.0	30.2	30.6
105°	29.1	30.1	30.8	31.2	31.6	32.0	32.4
107.5°	33.2	32.1	31.8	32.1	32.5	32.9	33.3
110°	46.1	36.6	32.1	32.4	32.9	33.3	33.6



TEST NUMBER: P331339-930

CATALOG NUMBER: S122DIP-S675D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	84.3	49.8	32.8	33.0	33.3	33.7	33.9
115°	131.2	87.4	62.1	55.3	48.5	41.7	34.9
117.5°	259.0	248.4	232.0	209.5	187.2	164.9	142.4
120°	315.3	316.4	310.6	297.8	285.1	272.3	259.5
122.5°	334.0	334.7	333.8	331.3	328.8	326.4	323.8
125°	361.5	362.2	362.6	363.0	363.2	363.5	363.8
127.5°	387.3	388.2	388.7	388.8	388.9	388.9	389.0
130°	403.5	404.6	405.0	404.9	404.8	404.7	404.6
132.5°	419.1	420.0	420.3	420.2	420.1	420.0	420.0
135°	441.5	442.5	442.9	442.6	442.5	442.3	442.1
137.5°	462.3	463.3	463.5	463.2	462.8	462.6	462.3
140°	475.6	476.5	476.7	476.2	475.8	475.3	474.8
142.5°	488.0	488.9	489.0	488.5	488.0	487.5	487.1
145°	505.3	506.0	506.1	505.6	505.2	504.7	504.2
147.5°	520.3	520.8	520.8	520.5	520.1	519.7	519.3
150°	529.7	530.3	530.4	529.9	529.4	528.9	528.5
152.5°	538.3	538.8	538.7	538.2	537.5	536.9	536.3
155°	549.8	550.3	550.2	549.4	548.7	548.0	547.1
157.5°	559.5	560.1	560.1	559.3	558.6	557.8	557.1
160°	565.0	565.6	565.6	564.9	564.3	563.5	562.9
162.5°	570.4	571.0	571.0	570.1	569.3	568.5	567.7
165°	576.8	577.5	577.5	576.8	576.2	575.5	574.8
167.5°	582.2	582.9	582.8	581.9	581.1	580.2	579.4
170°	584.9	585.5	585.5	584.6	583.8	582.9	582.0
172.5°	586.9	587.6	587.5	586.7	585.8	585.0	584.1
175°	589.1	589.8	589.7	588.7	587.7	586.9	585.9
177.5°	589.3	589.8	589.7	589.1	588.3	587.7	587.0
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0

(END OF REPORT)