

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P334445

Luminaire Tested: **S122IP-S330U835-4F0-1E-UDD-4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P334445
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122IP-S330U835-4F0-1E-UDD-4
Description: DEFINE 2 INDIRECT LED LUMINAIRE, BATWING OPTIC
PENDANT MOUNT, 330 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1280.7 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 11.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P334445
CATALOG NUMBER: S122IP-S330U835-4F0-1E-UDD-4

Luminous Intensity Polar Plot





TEST NUMBER: P334445

CATALOG NUMBER: S122IP-S330U835-4F0-1E-UDD-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P334445

CATALOG NUMBER: S122IP-S330U835-4F0-1E-UDD-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.2	0.1
90°-100°	71.6	5.6
100°-110°	252.2	19.7
110°-120°	264.9	20.7
120°-130°	217.9	17.0
130°-140°	175.1	13.7
140°-150°	132.2	10.3
150°-160°	93.0	7.3
160°-170°	54.7	4.3
170°-180°	17.8	1.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.2	0.1
90°-120°	588.8	46.0
90°-150°	1114.0	87.0
90°-180°	1280.0	99.9
0°-180°	1280.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	5	12	12	12	1
95°	12	30	138	52	40	13
105°	43	65	262	468	398	46
115°	76	96	219	452	524	75
125°	106	125	211	366	425	94
135°	124	148	208	308	352	96
145°	142	163	207	257	281	89
155°	162	174	201	227	236	74
165°	176	181	193	204	207	50
175°	183	184	185	187	187	17
180°	184	184	184	184	184	



TEST NUMBER: P334445

CATALOG NUMBER: S122IP-S330U835-4F0-1E-UDD-4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.4	1.4	2.8	3.5	4.2	5.3	7.1	9.5	11.7	12.0	11.7
92.5°	5.3	7.4	10.2	12.0	14.8	18.7	28.3	41.7	53.7	54.4	45.6
95°	12.4	13.8	17.3	20.5	26.1	34.6	50.9	81.6	122.6	138.5	121.2
97.5°	18.4	20.5	24.4	29.0	35.3	44.9	65.7	108.5	174.5	225.8	227.5
100°	27.2	28.3	31.4	37.1	44.2	54.1	72.8	115.9	192.2	279.1	330.0
102.5°	35.3	36.0	39.2	44.9	52.3	62.2	79.1	116.2	185.5	280.9	368.2
105°	43.1	44.5	47.0	52.3	60.1	70.0	86.6	118.0	176.3	261.8	355.8
107.5°	51.6	52.6	55.1	60.1	67.8	77.7	94.0	121.9	171.4	244.1	329.7
110°	60.1	61.5	63.6	68.2	75.6	85.9	101.4	126.8	170.0	232.1	305.3



TEST NUMBER: P334445

CATALOG NUMBER: S122IP-S330U835-4F0-1E-UDD-4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	67.8	69.3	71.7	76.0	83.0	93.6	108.5	132.1	170.3	224.4	288.3
115°	76.0	77.7	79.9	84.1	91.2	100.7	115.9	137.4	171.7	219.1	274.9
117.5°	84.4	85.9	88.0	91.9	98.6	108.5	122.6	143.1	173.8	216.2	265.7
120°	92.2	93.6	95.8	98.9	106.0	115.9	129.7	148.8	176.0	213.8	258.6
122.5°	99.6	100.7	102.8	106.4	113.4	123.7	136.4	153.7	178.4	212.3	252.6
125°	106.0	107.1	109.2	113.4	120.5	130.4	143.1	159.0	180.9	210.6	247.0
127.5°	111.3	112.7	115.5	120.1	126.8	137.1	149.5	163.9	183.4	209.5	241.7
130°	115.9	117.3	120.8	125.8	132.9	142.7	155.1	168.5	186.2	208.8	236.4
132.5°	120.1	121.9	125.8	131.1	138.5	148.4	160.1	173.1	189.0	208.5	232.1
135°	124.4	125.8	130.0	135.3	143.5	153.3	164.7	177.0	191.2	208.1	228.2
137.5°	128.3	130.0	134.3	139.9	148.0	157.2	168.5	180.2	193.3	208.1	225.4
140°	132.9	134.3	138.5	144.2	151.9	161.1	171.7	182.7	194.7	207.8	222.9
142.5°	137.4	138.5	142.4	148.0	155.5	163.9	174.2	184.8	195.7	207.8	220.5
145°	142.0	143.5	147.0	152.3	159.4	167.1	176.7	186.6	196.4	207.0	218.4
147.5°	147.0	148.0	151.6	156.5	162.5	169.6	178.8	187.6	196.8	206.0	216.2
150°	151.9	153.0	155.8	160.4	165.7	172.1	180.2	188.3	196.4	204.9	213.4
152.5°	156.9	157.2	160.1	163.9	168.9	174.5	181.6	188.7	195.7	203.2	210.9
155°	161.5	161.8	163.9	167.8	171.7	177.0	183.0	189.0	195.0	201.0	207.8
157.5°	165.4	165.7	167.5	171.0	174.2	178.8	184.1	189.0	193.6	198.9	204.9
160°	169.2	169.6	171.0	173.8	176.7	180.6	184.8	189.0	192.6	196.8	201.7
162.5°	173.1	172.8	174.2	176.3	178.8	181.6	185.1	188.7	191.5	195.0	198.9
165°	176.0	175.6	176.3	178.4	180.2	182.3	185.5	188.0	190.1	192.6	195.7
167.5°	178.4	178.1	178.8	180.2	181.6	183.0	185.5	187.6	188.7	190.4	192.6
170°	180.9	180.2	180.6	181.6	182.3	183.4	185.1	186.9	187.6	188.7	190.1
172.5°	182.3	182.0	181.6	182.7	183.0	183.7	184.8	185.9	186.2	186.6	187.6
175°	183.4	183.0	182.7	183.4	183.4	183.7	184.4	185.1	184.8	185.1	185.5
177.5°	184.1	183.4	183.0	183.7	183.7	183.7	184.1	184.8	184.1	183.7	184.1
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P334445

CATALOG NUMBER: S122IP-S330U835-4F0-1E-UDD-4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	11.3	10.6	11.3	11.7	11.7	11.7	11.7	11.7
92.5°	35.7	30.4	26.5	23.7	23.3	21.9	22.3	21.6
95°	92.6	71.0	56.2	48.4	43.8	41.0	39.9	40.3
97.5°	189.4	151.2	115.5	94.3	80.6	73.5	69.6	67.5
100°	322.6	278.8	230.4	187.6	158.3	143.1	132.9	126.5
102.5°	409.9	408.4	376.3	330.4	297.9	269.2	255.8	246.6
105°	429.3	469.2	473.8	462.2	440.2	418.3	403.1	398.2
107.5°	408.4	467.8	502.4	516.6	516.2	513.0	508.4	500.3
110°	379.8	443.1	488.3	517.3	532.5	539.2	542.4	542.0



TEST NUMBER: P334445

CATALOG NUMBER: S122IP-S330U835-4F0-1E-UDD-4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	353.7	413.7	462.9	497.1	519.7	532.1	538.8	541.3
115°	333.2	387.6	433.9	470.3	495.4	511.6	520.8	524.0
117.5°	316.2	365.0	408.1	442.7	468.5	485.8	495.4	497.8
120°	304.2	348.0	385.5	417.6	442.4	459.0	469.2	472.8
122.5°	294.7	333.9	368.9	397.1	418.7	434.9	443.8	446.6
125°	285.5	321.9	353.0	379.5	400.0	413.4	422.2	425.1
127.5°	276.3	309.9	339.5	364.3	382.3	395.0	402.8	404.9
130°	267.5	297.9	325.8	349.1	366.4	378.4	385.5	388.3
132.5°	259.0	286.5	311.6	333.2	350.1	362.2	368.5	371.0
135°	251.2	274.5	297.9	317.6	332.8	344.5	350.9	352.3
137.5°	244.9	265.0	284.1	301.7	316.2	326.5	332.1	334.2
140°	238.8	255.8	272.1	287.6	298.9	308.1	313.4	315.5
142.5°	233.9	247.7	261.1	273.5	284.1	292.2	296.8	296.8
145°	229.3	241.0	251.9	262.2	270.6	276.7	280.2	281.2
147.5°	225.8	235.3	244.1	251.9	259.3	264.3	266.8	267.5
150°	221.9	229.7	237.1	243.4	248.7	253.0	255.1	255.5
152.5°	218.0	225.1	231.1	236.4	240.3	243.8	245.2	245.2
155°	214.5	220.1	225.4	229.3	233.2	235.7	237.1	236.4
157.5°	210.2	215.2	219.8	222.9	225.8	227.9	228.6	228.6
160°	206.3	210.2	214.1	216.6	219.1	220.8	221.2	221.2
162.5°	202.5	205.6	208.8	210.6	213.1	214.1	214.5	214.1
165°	198.6	201.0	203.5	204.9	206.3	207.8	207.8	207.4
167.5°	194.7	196.8	198.6	200.0	200.7	201.4	201.4	201.0
170°	191.9	192.9	194.3	195.0	195.4	196.4	196.1	195.4
172.5°	188.7	189.4	190.4	190.8	191.2	191.5	191.2	190.8
175°	186.6	186.9	187.3	187.6	187.6	188.0	187.6	186.9
177.5°	184.8	184.8	185.1	185.1	185.1	185.1	184.8	184.1
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7

(END OF REPORT)