

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P334550

Luminaire Tested: **S122IP-S330U835-4F0-1E-UDD**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P334550  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122IP-S330U835-4F0-1E-UDD  
Description: DEFINE 2 INDIRECT LED LUMINAIRE, NO LENS  
PENDANT MOUNT, 330 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1310.8 lumens  
Efficiency: N/A  
Efficacy: 115.0 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Indirect

Input Watts (W): 11.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P334550  
CATALOG NUMBER: S122IP-S330U835-4F0-1E-UDD

### Luminous Intensity Polar Plot





TEST NUMBER: P334550

CATALOG NUMBER: S122IP-S330U835-4F0-1E-UDD

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P334550

CATALOG NUMBER: S122IP-S330U835-4F0-1E-UDD

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.8	0.1
90°-100°	14.7	1.1
100°-110°	54.9	4.2
110°-120°	145.7	11.1
120°-130°	241.6	18.4
130°-140°	256.6	19.6
140°-150°	238.5	18.2
150°-160°	191.8	14.6
160°-170°	123.6	9.4
170°-180°	42.5	3.2
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.8	0.1
90°-120°	215.3	16.4
90°-150°	952.1	72.6
90°-180°	1310.0	99.9
0°-180°	1310.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	4	6	8	9	1
95°	21	10	13	14	14	25
105°	98	108	20	23	25	105
115°	186	191	200	50	26	183
125°	263	267	273	276	276	234
135°	325	330	333	337	336	251
145°	377	377	382	385	383	236
155°	416	413	416	418	416	191
165°	438	436	437	439	437	124
175°	448	446	446	448	445	43
180°	447	447	447	447	447	



TEST NUMBER: P334550

CATALOG NUMBER: S122IP-S330U835-4F0-1E-UDD

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.3	3.9	6.5	8.1	8.7
92.5°	8.1	6.8	7.8	8.4	8.7
95°	21.0	10.3	12.6	14.2	13.9
97.5°	37.8	11.3	16.5	17.5	17.8
100°	57.2	12.9	18.4	21.0	21.7
102.5°	78.6	77.9	19.1	22.6	23.6
105°	98.3	108.0	19.7	23.3	24.6
107.5°	121.2	129.3	20.4	23.9	25.2
110°	143.2	150.0	56.6	24.2	25.5



TEST NUMBER: P334550

CATALOG NUMBER: S122IP-S330U835-4F0-1E-UDD

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	163.9	169.7	164.3	24.9	25.9
115°	185.9	191.4	199.5	49.8	26.5
117.5°	205.0	211.5	217.0	170.7	86.0
120°	226.3	231.2	237.0	240.9	197.2
122.5°	244.4	249.6	256.1	258.0	258.3
125°	262.9	267.1	273.2	275.5	276.4
127.5°	279.7	284.2	289.1	292.3	292.6
130°	295.5	300.7	304.3	307.8	307.5
132.5°	311.7	315.9	319.4	322.4	322.0
135°	325.3	330.4	333.4	336.6	335.9
137.5°	339.5	343.4	346.6	349.8	348.9
140°	353.4	356.0	359.5	362.5	360.8
142.5°	365.0	367.3	371.5	374.1	372.5
145°	377.3	377.0	382.5	384.8	383.1
147.5°	388.0	387.0	392.5	394.1	392.8
150°	398.3	396.1	401.3	403.2	401.6
152.5°	407.1	404.5	409.3	411.3	409.0
155°	415.5	412.6	416.4	418.4	415.8
157.5°	422.3	419.7	422.6	424.9	422.3
160°	428.1	426.1	428.1	430.0	427.8
162.5°	433.3	431.3	432.9	435.2	432.3
165°	437.8	435.8	436.8	439.1	436.8
167.5°	441.3	439.4	440.4	442.6	439.7
170°	444.3	442.3	443.0	445.2	442.3
172.5°	446.2	444.3	444.9	447.2	444.3
175°	447.8	445.5	446.2	448.5	445.2
177.5°	448.5	446.2	446.5	448.8	445.9
180°	446.8	446.8	446.8	446.8	446.8

(END OF REPORT)