

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332033-927

Luminaire Tested: **S123DIP-S1000D1025U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332033-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1025U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6511.4 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332033-927

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332033-927

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	89	86	90	86	83	80	73	71	68	61	59	58	50	48	47	42
2	89	82	75	70	82	75	70	66	64	60	57	53	51	48	44	42	40	35
3	81	72	64	58	75	66	60	55	56	52	48	47	44	41	39	36	34	30
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	35	32	29	26
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20	17
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18	15
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13497	13497	13497
5°	13560	13374	13467
10°	13470	13258	13340
15°	13312	13108	13133
20°	13128	12893	12906
25°	12883	12638	12613
30°	12609	12356	12261
35°	12326	12056	11901
40°	12029	11726	11545
45°	11702	11423	11144
50°	11375	11050	10742
55°	10946	10663	10340
60°	10514	10213	9888
65°	10132	9722	9419
70°	9567	9161	8752
75°	8742	8430	8072
80°	7885	7550	7482
85°	6928	6657	6385



TEST NUMBER: P332033-927

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.1	1.8
10°-20°	333.5	5.1
20°-30°	492.7	7.6
30°-40°	575.5	8.8
40°-50°	578.6	8.9
50°-60°	508.2	7.8
60°-70°	378.6	5.8
70°-80°	215.7	3.3
80°-90°	64.9	1.0
90°-100°	38.7	0.6
100°-110°	184.4	2.8
110°-120°	443.0	6.8
120°-130°	564.1	8.7
130°-140°	602.7	9.3
140°-150°	563.6	8.7
150°-160°	454.6	7.0
160°-170°	293.4	4.5
170°-180°	101.1	1.6
0°-30°	944.3	14.5
0°-40°	1519.8	23.3
0°-60°	2606.6	40.0
0°-90°	3265.8	50.2
90°-120°	666.1	10.2
90°-150°	2396.5	36.8
90°-180°	3246.0	49.9
0°-180°	6511.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1254	1254	1254	1254	1254	
5°	1255	1249	1238	1248	1246	119
15°	1195	1190	1176	1184	1178	337
25°	1085	1078	1064	1065	1062	499
35°	938	931	918	911	906	587
45°	769	764	750	738	732	593
55°	583	582	568	557	551	522
65°	398	392	382	373	370	392
75°	210	206	203	197	194	225
85°	56	54	54	52	52	62
90°	1	9	19	22	24	5
95°	48	18	24	30	30	60
105°	236	240	173	41	35	250
115°	442	447	454	462	465	436
125°	623	629	633	634	636	556
135°	776	780	784	786	784	597
145°	895	900	902	904	904	560
155°	986	985	985	989	984	454
165°	1040	1038	1037	1042	1037	294
175°	1064	1061	1061	1066	1060	101
180°	1064	1064	1064	1064	1064	



TEST NUMBER: P332033-927

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1258.2	1257.5	1256.7	1255.9	1255.2	1253.7	1251.6	1249.5	1247.4	1245.3	1247.2
5°	1255.0	1253.8	1252.6	1251.4	1250.2	1248.3	1245.7	1243.0	1240.4	1237.8	1240.2
7.5°	1242.7	1241.5	1240.3	1239.1	1237.9	1236.0	1233.3	1230.5	1227.8	1225.0	1227.2
10°	1232.4	1231.2	1229.9	1228.8	1227.6	1225.4	1222.3	1219.2	1216.1	1213.0	1215.1
12.5°	1218.5	1217.6	1216.6	1215.5	1214.6	1212.6	1209.7	1206.7	1203.8	1200.9	1202.5
15°	1194.6	1193.7	1192.7	1191.8	1190.8	1188.7	1185.7	1182.6	1179.4	1176.3	1178.2
17.5°	1166.8	1165.5	1164.3	1163.1	1161.8	1159.7	1156.5	1153.4	1150.3	1147.2	1148.5
20°	1146.1	1144.7	1143.3	1141.8	1140.3	1138.0	1135.0	1131.9	1128.8	1125.6	1126.6
22.5°	1122.8	1121.4	1120.0	1118.5	1117.1	1114.8	1111.7	1108.6	1105.5	1102.3	1103.1
25°	1084.7	1083.2	1081.8	1080.4	1078.9	1076.7	1073.5	1070.4	1067.3	1064.1	1064.4
27.5°	1043.9	1042.5	1041.1	1039.7	1038.3	1035.9	1032.6	1029.3	1025.9	1022.5	1022.7
30°	1014.5	1013.4	1012.2	1011.0	1009.8	1007.5	1004.2	1000.8	997.4	994.1	994.1
32.5°	985.2	983.7	982.1	980.5	978.9	976.8	974.2	971.7	969.1	966.5	965.1
35°	938.0	936.6	935.2	933.7	932.2	930.0	926.9	923.8	920.7	917.5	916.1
37.5°	889.7	887.9	886.1	884.2	882.4	880.0	876.8	873.6	870.4	867.3	865.5
40°	856.1	854.6	853.2	851.8	850.3	848.0	844.5	841.2	837.9	834.5	832.6
42.5°	822.4	820.8	819.2	817.5	815.9	813.4	810.1	806.8	803.4	800.0	798.1
45°	768.7	767.8	766.8	765.9	764.9	762.9	759.8	756.6	753.5	750.4	747.6
47.5°	715.5	714.1	712.7	711.3	710.0	707.7	704.9	702.0	699.0	696.1	693.2
50°	679.3	678.0	676.8	675.7	674.5	672.3	669.2	666.1	663.0	659.9	657.2
52.5°	641.3	640.5	639.7	638.9	638.0	636.0	632.7	629.4	626.1	622.7	620.5
55°	583.3	583.0	582.8	582.6	582.3	580.7	577.6	574.4	571.3	568.2	565.5
57.5°	528.1	527.3	526.5	525.7	524.8	523.2	520.7	518.2	515.7	513.3	510.9
60°	488.4	488.1	487.9	487.7	487.4	485.9	483.0	480.1	477.3	474.4	472.2
62.5°	453.0	452.4	451.8	451.1	450.6	448.9	445.9	443.1	440.2	437.3	435.1
65°	397.8	396.6	395.5	394.3	393.1	391.3	388.9	386.5	384.0	381.7	379.8
67.5°	339.5	338.3	337.3	336.3	335.2	333.7	331.9	330.1	328.3	326.5	324.8
70°	304.0	302.6	301.2	299.8	298.3	296.8	295.4	294.0	292.6	291.1	289.5
72.5°	267.0	265.9	264.8	263.8	262.8	261.4	259.8	258.2	256.5	254.8	253.4
75°	210.2	209.3	208.3	207.4	206.4	205.6	204.9	204.1	203.4	202.7	201.5
77.5°	160.0	159.5	158.9	158.4	157.9	157.2	156.4	155.5	154.6	153.8	153.0
80°	127.2	126.5	125.8	125.1	124.4	123.7	123.3	122.8	122.3	121.8	121.6
82.5°	95.3	95.1	95.1	94.9	94.7	94.6	94.5	94.4	94.3	94.3	93.8
85°	56.1	55.6	55.1	54.7	54.2	53.9	53.9	53.9	53.9	53.9	53.4
87.5°	22.6	22.3	22.1	21.9	21.7	21.7	21.9	22.3	22.5	22.7	22.7
90°	0.8	2.5	4.3	6.1	7.8	9.8	12.1	14.4	16.7	19.0	19.6
92.5°	14.7	14.2	13.7	13.2	12.8	13.4	15.1	16.8	18.5	20.3	21.4
95°	48.2	41.0	33.8	26.6	19.4	16.8	18.7	20.7	22.6	24.5	25.7
97.5°	97.0	93.7	90.5	87.2	84.0	76.0	63.5	50.8	38.1	25.4	26.9
100°	133.6	137.1	140.7	144.2	147.7	135.7	108.3	80.9	53.5	26.1	27.5
102.5°	175.4	177.9	180.5	183.0	185.5	171.8	141.9	111.9	82.0	52.0	47.7
105°	235.6	237.6	239.5	241.5	243.4	236.4	220.6	204.8	189.0	173.2	142.0
107.5°	299.2	300.8	302.3	303.9	305.4	307.4	309.9	312.4	314.9	317.4	294.6
110°	341.6	343.0	344.4	345.8	347.2	348.9	350.8	352.8	354.7	356.6	350.8



TEST NUMBER: P332033-927

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	382.1	383.3	384.6	385.9	387.1	388.7	390.7	392.6	394.5	396.5	396.6
115°	442.0	443.1	444.1	445.2	446.2	447.6	449.1	450.7	452.3	453.8	455.7
117.5°	500.0	501.4	502.6	504.0	505.3	506.3	507.1	507.9	508.7	509.5	511.0
120°	536.1	537.7	539.2	540.8	542.4	543.5	544.0	544.5	545.1	545.6	547.0
122.5°	572.8	574.1	575.4	576.7	578.0	579.0	579.6	580.4	581.0	581.6	582.7
125°	623.1	624.5	625.9	627.3	628.7	629.8	630.5	631.1	631.8	632.6	633.0
127.5°	671.8	673.2	674.6	676.0	677.4	678.5	679.4	680.2	681.0	681.9	682.5
130°	702.2	703.5	705.0	706.4	707.8	708.8	709.6	710.3	710.9	711.6	712.3
132.5°	731.3	732.7	734.0	735.5	736.9	737.8	738.4	738.9	739.6	740.1	740.8
135°	775.7	776.7	777.8	778.9	779.9	780.8	781.5	782.2	782.9	783.6	784.1
137.5°	813.7	815.0	816.3	817.7	819.0	819.8	820.2	820.6	821.0	821.4	822.2
140°	838.9	840.0	841.1	842.1	843.2	844.0	844.5	845.0	845.6	846.1	846.8
142.5°	862.4	863.4	864.4	865.5	866.6	867.4	867.9	868.4	868.9	869.5	870.1
145°	895.1	896.4	897.5	898.8	900.0	900.8	901.2	901.5	901.8	902.2	902.5
147.5°	925.9	926.8	927.6	928.4	929.2	929.7	930.1	930.4	930.8	931.1	931.5
150°	944.9	945.5	945.9	946.5	947.0	947.5	947.8	948.2	948.5	948.9	949.2
152.5°	961.9	962.3	962.5	962.7	963.0	963.2	963.4	963.6	963.8	964.0	964.6
155°	986.0	985.6	985.3	985.0	984.6	984.5	984.7	984.8	985.1	985.2	986.1
157.5°	1004.6	1004.6	1004.6	1004.6	1004.6	1004.4	1004.2	1004.1	1003.9	1003.7	1004.8
160°	1016.1	1015.9	1015.7	1015.6	1015.3	1015.2	1015.0	1014.9	1014.6	1014.5	1015.6
162.5°	1026.8	1026.4	1025.9	1025.5	1025.0	1024.7	1024.5	1024.3	1024.1	1024.0	1025.2
165°	1039.8	1039.3	1038.7	1038.2	1037.7	1037.4	1037.1	1037.0	1036.8	1036.6	1038.0
167.5°	1049.9	1049.2	1048.5	1047.8	1047.1	1046.7	1046.7	1046.7	1046.7	1046.7	1048.1
170°	1055.6	1054.9	1054.2	1053.5	1052.8	1052.4	1052.4	1052.4	1052.4	1052.4	1053.8
172.5°	1059.4	1058.6	1057.7	1056.9	1056.1	1055.7	1055.8	1056.0	1056.1	1056.2	1057.6
175°	1064.3	1063.4	1062.6	1061.7	1060.8	1060.4	1060.6	1060.8	1061.0	1061.1	1062.4
177.5°	1065.6	1064.9	1064.1	1063.4	1062.8	1062.5	1062.6	1062.8	1062.9	1063.0	1064.1
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3



TEST NUMBER: P332033-927

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1249.1	1251.1	1253.0	1253.9	1253.6	1253.5	1253.2	1253.1
5°	1242.5	1244.9	1247.4	1248.3	1247.8	1247.4	1246.9	1246.4
7.5°	1229.4	1231.5	1233.7	1234.6	1234.3	1234.1	1233.7	1233.4
10°	1217.3	1219.4	1221.6	1222.4	1221.9	1221.5	1221.0	1220.5
12.5°	1204.0	1205.6	1207.2	1207.8	1207.6	1207.3	1207.0	1206.7
15°	1180.1	1182.0	1184.0	1184.2	1182.8	1181.3	1179.9	1178.5
17.5°	1149.9	1151.2	1152.5	1152.9	1152.5	1151.9	1151.4	1150.9
20°	1127.5	1128.5	1129.5	1129.6	1128.9	1128.1	1127.4	1126.7
22.5°	1103.9	1104.6	1105.4	1105.3	1104.5	1103.5	1102.6	1101.7
25°	1064.6	1064.9	1065.2	1064.9	1064.1	1063.4	1062.7	1062.0
27.5°	1022.9	1023.1	1023.3	1022.9	1022.1	1021.1	1020.3	1019.3
30°	994.1	994.1	994.1	993.2	991.6	989.9	988.2	986.5
32.5°	963.8	962.5	961.2	960.0	959.1	958.1	957.3	956.3
35°	914.7	913.2	911.8	910.5	909.3	908.1	906.9	905.7
37.5°	863.9	862.1	860.4	859.1	858.4	857.6	856.8	856.1
40°	830.7	828.8	826.9	825.4	824.4	823.5	822.5	821.6
42.5°	796.1	794.2	792.3	790.9	790.0	789.0	788.1	787.1
45°	744.7	741.8	738.9	736.9	735.7	734.5	733.3	732.1
47.5°	690.4	687.6	684.8	682.9	681.8	680.7	679.7	678.6
50°	654.6	652.0	649.3	647.3	645.9	644.4	642.9	641.5
52.5°	618.2	616.0	613.8	611.9	610.5	609.0	607.6	606.2
55°	562.9	560.3	557.7	555.7	554.5	553.3	552.2	551.0
57.5°	508.5	506.2	503.8	501.9	500.6	499.2	497.8	496.4
60°	470.1	467.9	465.8	464.1	462.9	461.7	460.5	459.3
62.5°	433.0	430.9	428.6	427.2	426.4	425.6	424.8	424.0
65°	377.9	375.9	374.0	372.7	372.0	371.3	370.5	369.8
67.5°	323.1	321.5	319.8	318.5	317.4	316.4	315.4	314.4
70°	287.7	286.1	284.4	283.0	281.8	280.6	279.4	278.1
72.5°	251.9	250.4	248.9	247.9	247.2	246.6	246.1	245.4
75°	200.3	199.1	197.9	196.9	196.2	195.5	194.8	194.1
77.5°	152.1	151.3	150.5	150.1	150.1	150.1	150.1	150.1
80°	121.4	121.1	120.9	120.7	120.7	120.7	120.7	120.7
82.5°	93.4	92.9	92.5	92.2	92.0	91.8	91.7	91.4
85°	52.9	52.4	52.0	51.7	51.7	51.7	51.7	51.7
87.5°	22.7	22.7	22.6	22.6	22.7	22.7	22.8	22.9
90°	20.4	21.1	21.8	22.3	22.7	23.1	23.4	23.7
92.5°	22.5	23.6	24.7	25.4	25.6	25.8	26.1	26.2
95°	26.9	28.2	29.5	30.0	30.0	30.0	30.0	30.0
97.5°	28.3	29.7	31.1	31.8	32.1	32.2	32.4	32.6
100°	28.9	30.3	31.7	32.5	32.7	32.9	33.0	33.2
102.5°	43.3	39.0	34.6	32.6	32.9	33.2	33.5	33.8
105°	111.0	79.9	48.8	33.4	33.7	34.1	34.5	34.8
107.5°	271.8	249.0	226.2	203.0	179.6	156.1	132.7	109.2
110°	345.0	339.2	333.4	318.0	292.8	267.7	242.6	217.5



TEST NUMBER: P332033-927

CATALOG NUMBER: S123DIP-S1000D1025U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	396.6	396.8	396.9	394.3	389.0	383.7	378.3	373.0
115°	457.4	459.1	460.9	462.2	462.8	463.5	464.2	464.9
117.5°	512.4	513.7	515.2	515.9	516.1	516.2	516.3	516.5
120°	548.4	549.8	551.2	551.9	551.9	551.9	551.9	551.9
122.5°	583.6	584.6	585.6	586.1	586.3	586.5	586.5	586.7
125°	633.3	633.6	634.0	634.3	634.7	635.0	635.4	635.7
127.5°	683.0	683.6	684.1	684.3	683.9	683.6	683.2	682.9
130°	713.0	713.8	714.5	714.6	714.3	713.9	713.6	713.2
132.5°	741.5	742.2	742.9	743.0	742.5	742.0	741.6	741.1
135°	784.7	785.2	785.7	785.7	785.2	784.7	784.1	783.6
137.5°	823.1	823.9	824.7	825.0	824.7	824.3	823.9	823.6
140°	847.5	848.2	848.9	849.1	848.7	848.3	848.0	847.6
142.5°	870.6	871.2	871.7	871.7	871.2	870.8	870.3	869.8
145°	902.9	903.2	903.6	903.8	903.8	903.8	903.8	903.8
147.5°	931.8	932.2	932.6	932.3	931.5	930.7	929.9	929.1
150°	949.6	949.9	950.3	950.1	949.7	949.1	948.6	948.1
152.5°	965.3	965.9	966.5	966.5	965.7	964.9	964.1	963.2
155°	987.0	987.9	988.7	988.6	987.6	986.6	985.5	984.4
157.5°	1005.8	1006.9	1008.0	1007.8	1006.4	1005.0	1003.7	1002.3
160°	1016.6	1017.6	1018.7	1018.6	1017.4	1016.1	1014.9	1013.7
162.5°	1026.4	1027.5	1028.7	1028.8	1027.7	1026.6	1025.6	1024.5
165°	1039.4	1040.8	1042.3	1042.4	1041.1	1039.9	1038.6	1037.4
167.5°	1049.6	1051.0	1052.3	1052.3	1051.0	1049.6	1048.1	1046.7
170°	1055.3	1056.7	1058.0	1058.0	1056.7	1055.3	1053.8	1052.4
172.5°	1059.1	1060.4	1061.8	1061.8	1060.3	1058.7	1057.2	1055.6
175°	1063.6	1064.9	1066.0	1066.0	1064.5	1063.2	1061.8	1060.3
177.5°	1065.2	1066.4	1067.5	1067.4	1066.0	1064.6	1063.2	1061.8
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3

(END OF REPORT)