

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331400-930

Luminaire Tested: **S122DIP-S865D725U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331400-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S865D725U930-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4977.1 lumens  
Efficiency: N/A  
Efficacy: 91.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331400-930

CATALOG NUMBER: S122DIP-S865D725U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331400-930

CATALOG NUMBER: S122DIP-S865D725U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63	58
1	99	95	91	88	92	89	85	82	77	74	72	66	64	62	56	54	53	48
2	91	83	77	72	84	78	72	67	67	63	60	58	55	52	49	47	45	41
3	83	73	66	60	77	68	62	56	59	54	50	51	47	44	43	41	38	34
4	76	65	57	51	70	61	53	48	53	47	43	46	41	38	39	36	33	30
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	32	29	26
6	64	52	44	38	59	49	41	36	43	37	32	37	32	29	32	28	25	23
7	59	47	39	33	55	44	37	32	39	33	28	34	29	25	29	25	23	20
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18	16
10	48	36	28	24	45	34	27	23	30	24	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18166	18166	18166
5°	18235	17973	18078
10°	18126	17790	17879
15°	17904	17560	17541
20°	17584	17213	17194
25°	17268	16787	16787
30°	16861	16397	16257
35°	16484	15928	15693
40°	16008	15460	15163
45°	15536	14995	14625
50°	15028	14511	13996
55°	14494	13948	13430
60°	13905	13275	12788
65°	13268	12607	12027
70°	12463	11797	11235
75°	11335	10861	10593
80°	10060	9754	9252
85°	8225	7818	7003



TEST NUMBER: P331400-930

CATALOG NUMBER: S122DIP-S865D725U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.8	2.1
10°-20°	297.7	6.0
20°-30°	437.6	8.8
30°-40°	508.3	10.2
40°-50°	507.7	10.2
50°-60°	442.8	8.9
60°-70°	327.4	6.6
70°-80°	185.4	3.7
80°-90°	52.9	1.1
90°-100°	47.9	1.0
100°-110°	148.6	3.0
110°-120°	254.0	5.1
120°-130°	334.1	6.7
130°-140°	375.0	7.5
140°-150°	367.7	7.4
150°-160°	308.4	6.2
160°-170°	204.5	4.1
170°-180°	71.5	1.4
0°-30°	841.1	16.9
0°-40°	1349.3	27.1
0°-60°	2299.8	46.2
0°-90°	2865.5	57.6
90°-120°	450.5	9.1
90°-150°	1527.2	30.7
90°-180°	2112.0	42.4
0°-180°	4977.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1125	1125	1125	1125	1125	
5°	1125	1120	1109	1117	1115	107
15°	1071	1064	1050	1054	1049	301
25°	969	960	942	944	942	446
35°	836	825	808	802	796	522
45°	680	672	657	645	640	525
55°	515	508	496	483	477	460
65°	347	341	330	320	315	343
75°	182	179	174	168	170	194
85°	44	43	42	39	38	51
90°	1	9	22	21	22	4
95°	33	39	41	41	40	38
105°	137	139	140	141	142	145
115°	255	258	258	257	255	252
125°	371	376	375	373	372	331
135°	480	487	488	487	486	371
145°	582	587	591	591	589	364
155°	666	668	670	673	671	306
165°	725	724	724	728	725	204
175°	754	752	751	755	751	72
180°	755	755	755	755	755	



TEST NUMBER: P331400-930

CATALOG NUMBER: S122DIP-S865D725U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1130.3	1129.4	1128.4	1127.5	1126.5	1124.9	1122.8	1120.7	1118.6	1116.5	1118.4
5°	1125.1	1124.1	1123.2	1122.3	1121.3	1119.5	1116.9	1114.2	1111.6	1108.9	1110.8
7.5°	1115.2	1113.7	1112.2	1110.7	1109.2	1107.1	1104.4	1101.7	1099.0	1096.3	1098.3
10°	1105.6	1104.0	1102.3	1100.6	1098.9	1096.7	1093.7	1090.9	1088.0	1085.1	1087.0
12.5°	1092.7	1091.2	1089.7	1088.2	1086.7	1084.5	1081.7	1078.7	1075.9	1073.0	1074.3
15°	1071.1	1069.6	1068.1	1066.7	1065.3	1063.0	1059.9	1056.7	1053.6	1050.5	1051.4
17.5°	1043.3	1041.9	1040.5	1039.0	1037.5	1035.3	1032.1	1028.9	1025.7	1022.5	1023.7
20°	1023.4	1022.0	1020.6	1019.1	1017.7	1015.3	1011.9	1008.5	1005.2	1001.8	1002.5
22.5°	1003.6	1001.5	999.5	997.4	995.5	992.9	989.7	986.5	983.3	980.2	980.3
25°	969.3	967.4	965.5	963.6	961.6	958.6	954.6	950.5	946.4	942.3	942.8
27.5°	930.4	928.7	926.9	925.2	923.5	921.0	917.8	914.5	911.3	908.1	907.4
30°	904.4	902.5	900.6	898.7	896.7	894.0	890.4	886.8	883.1	879.5	878.8
32.5°	876.8	875.2	873.7	872.1	870.6	867.9	864.1	860.3	856.6	852.7	851.4
35°	836.3	833.9	831.4	829.1	826.6	823.5	819.7	815.9	812.0	808.1	806.7
37.5°	790.6	788.5	786.4	784.2	782.2	779.2	775.3	771.5	767.6	763.8	762.0
40°	759.5	757.6	755.6	753.7	751.8	748.9	745.0	741.2	737.4	733.5	731.3
42.5°	729.2	727.2	725.3	723.4	721.5	718.6	714.8	710.9	707.0	703.2	700.8
45°	680.4	678.8	677.1	675.5	673.8	671.1	667.5	663.9	660.3	656.7	654.0
47.5°	632.0	630.5	628.8	627.3	625.7	623.0	619.2	615.5	611.7	608.0	605.2
50°	598.3	597.0	595.9	594.7	593.5	591.2	587.8	584.4	581.1	577.7	574.4
52.5°	565.4	563.8	562.2	560.6	559.1	556.7	553.5	550.3	547.1	544.0	541.2
55°	514.9	513.6	512.1	510.6	509.2	507.0	504.2	501.2	498.4	495.5	492.6
57.5°	464.3	463.2	462.0	460.9	459.7	457.5	454.4	451.2	448.0	444.8	442.1
60°	430.6	429.6	428.7	427.7	426.7	424.6	421.2	417.8	414.5	411.1	408.5
62.5°	397.7	396.2	394.6	393.1	391.5	389.5	386.9	384.3	381.6	379.1	376.7
65°	347.3	345.8	344.4	342.9	341.5	339.6	337.2	334.8	332.4	330.0	327.8
67.5°	296.0	294.8	293.7	292.5	291.4	289.8	287.6	285.4	283.2	281.0	279.4
70°	264.0	263.0	262.0	261.1	260.2	258.5	256.4	254.2	252.1	249.9	248.3
72.5°	231.1	230.2	229.2	228.2	227.2	226.1	224.7	223.3	221.8	220.5	218.8
75°	181.7	181.2	180.8	180.3	179.9	179.0	177.8	176.6	175.4	174.1	172.8
77.5°	137.6	136.8	136.0	135.2	134.4	133.7	133.2	132.7	132.2	131.8	131.0
80°	108.2	107.9	107.7	107.5	107.2	106.9	106.4	105.9	105.4	104.9	104.2
82.5°	80.5	80.5	80.4	80.3	80.3	80.1	79.8	79.6	79.2	79.0	78.0
85°	44.4	44.1	43.9	43.6	43.4	43.1	42.9	42.6	42.4	42.2	41.5
87.5°	15.7	15.7	15.7	15.6	15.5	15.7	15.9	16.1	16.3	16.6	16.0
90°	0.7	2.4	4.1	5.7	7.4	9.9	13.0	16.1	19.2	22.3	22.0
92.5°	11.3	12.6	13.9	15.1	16.3	17.3	18.0	18.8	19.6	20.3	20.3
95°	33.1	34.6	36.0	37.4	38.8	39.6	39.9	40.2	40.5	40.8	40.8
97.5°	60.6	61.8	63.0	64.2	65.6	66.4	66.9	67.5	68.0	68.6	68.6
100°	81.0	82.1	83.2	84.3	85.4	86.3	86.7	87.1	87.5	88.0	88.0
102.5°	102.3	103.2	104.2	105.1	106.0	106.7	107.2	107.8	108.3	108.8	108.9
105°	137.1	137.5	137.9	138.3	138.7	139.1	139.3	139.7	139.9	140.2	140.5
107.5°	171.9	172.6	173.2	173.8	174.4	174.7	174.7	174.7	174.7	174.7	174.9
110°	194.4	195.2	196.1	196.9	197.8	198.2	198.2	198.2	198.2	198.2	198.2



TEST NUMBER: P331400-930

CATALOG NUMBER: S122DIP-S865D725U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	218.8	219.7	220.5	221.4	222.3	222.6	222.5	222.4	222.3	222.2	221.8
115°	254.9	255.8	256.6	257.5	258.3	258.6	258.3	258.0	257.7	257.5	257.3
117.5°	290.8	292.0	293.1	294.2	295.4	295.5	294.7	294.0	293.2	292.4	292.0
120°	314.8	315.9	317.1	318.2	319.4	319.4	318.2	317.1	315.9	314.8	314.8
122.5°	336.7	338.1	339.5	340.8	342.2	342.4	341.7	340.9	340.1	339.2	338.9
125°	370.9	372.2	373.4	374.7	376.0	376.4	376.0	375.5	375.1	374.7	374.3
127.5°	404.1	405.8	407.4	409.0	410.6	411.2	410.7	410.2	409.6	409.1	408.6
130°	425.1	426.9	428.8	430.6	432.4	433.2	432.9	432.6	432.4	432.1	431.8
132.5°	448.5	450.0	451.5	453.0	454.5	455.3	455.3	455.4	455.4	455.5	454.9
135°	479.9	481.4	483.0	484.5	486.1	487.0	487.3	487.5	487.9	488.1	488.0
137.5°	512.9	514.1	515.4	516.7	518.0	518.8	519.2	519.5	519.9	520.2	520.2
140°	532.8	534.0	535.3	536.5	537.9	538.8	539.6	540.3	541.0	541.7	541.7
142.5°	553.2	554.4	555.7	557.0	558.2	559.1	559.6	560.1	560.6	561.1	561.2
145°	582.4	583.4	584.5	585.5	586.4	587.3	588.2	589.1	589.9	590.8	590.9
147.5°	608.6	609.8	611.0	612.1	613.3	614.2	614.8	615.4	616.0	616.5	616.8
150°	626.5	627.3	628.1	629.0	629.8	630.6	631.1	631.7	632.3	632.8	633.2
152.5°	642.2	643.1	643.9	644.8	645.6	646.4	647.1	647.8	648.4	649.1	649.6
155°	665.9	666.3	666.8	667.2	667.6	668.1	668.5	669.0	669.4	669.8	670.5
157.5°	686.2	686.5	686.8	687.1	687.4	687.6	687.9	688.1	688.4	688.6	689.6
160°	698.5	698.7	699.0	699.3	699.6	699.8	699.9	700.1	700.3	700.3	701.2
162.5°	709.6	709.7	709.8	709.8	709.9	710.0	710.1	710.3	710.5	710.5	711.5
165°	724.6	724.5	724.3	724.1	724.0	723.9	723.9	723.9	723.9	723.9	725.0
167.5°	737.0	736.6	736.2	735.8	735.4	735.2	735.2	735.1	735.1	735.0	736.1
170°	743.7	743.3	742.8	742.4	742.0	741.7	741.6	741.4	741.3	741.1	742.2
172.5°	748.3	747.9	747.5	747.0	746.6	746.3	746.2	746.0	745.9	745.8	746.7
175°	753.9	753.5	753.0	752.6	752.2	751.9	751.5	751.3	751.0	750.7	751.7
177.5°	756.2	755.9	755.5	755.1	754.8	754.6	754.3	754.1	753.8	753.7	754.3
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331400-930

CATALOG NUMBER: S122DIP-S865D725U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1120.3	1122.3	1124.1	1124.9	1124.5	1124.1	1123.8	1123.4
5°	1112.7	1114.7	1116.6	1117.3	1116.9	1116.4	1115.9	1115.4
7.5°	1100.2	1102.1	1104.1	1104.7	1104.2	1103.7	1103.2	1102.6
10°	1088.9	1090.9	1092.8	1093.4	1092.7	1091.9	1091.2	1090.5
12.5°	1075.7	1077.0	1078.4	1078.8	1078.2	1077.7	1077.2	1076.7
15°	1052.4	1053.4	1054.3	1054.2	1053.0	1051.8	1050.6	1049.4
17.5°	1024.7	1025.9	1027.0	1027.0	1025.8	1024.7	1023.5	1022.4
20°	1003.2	1004.0	1004.7	1004.5	1003.6	1002.7	1001.7	1000.7
22.5°	980.5	980.6	980.7	980.6	979.9	979.3	978.8	978.2
25°	943.3	943.7	944.2	944.2	943.7	943.3	942.8	942.3
27.5°	906.7	906.0	905.2	904.3	903.1	902.0	900.8	899.7
30°	878.1	877.4	876.7	875.8	874.9	873.9	872.9	872.0
32.5°	850.1	848.8	847.5	846.4	845.5	844.5	843.5	842.5
35°	805.3	803.8	802.4	801.0	799.9	798.7	797.4	796.2
37.5°	760.3	758.5	756.7	755.2	754.1	752.9	751.8	750.6
40°	729.2	727.0	724.9	723.3	722.4	721.4	720.4	719.4
42.5°	698.5	696.1	693.8	691.9	690.6	689.3	687.9	686.6
45°	651.4	648.7	646.1	644.3	643.4	642.4	641.4	640.5
47.5°	602.4	599.7	596.9	594.8	593.4	592.0	590.6	589.2
50°	571.0	567.6	564.3	562.0	560.8	559.5	558.4	557.2
52.5°	538.3	535.6	532.8	530.6	529.0	527.4	525.9	524.2
55°	489.8	486.8	484.0	481.9	480.7	479.5	478.3	477.1
57.5°	439.2	436.3	433.5	431.6	430.7	429.8	428.9	428.0
60°	405.9	403.2	400.6	398.8	398.1	397.4	396.6	396.0
62.5°	374.1	371.7	369.2	367.6	366.6	365.7	364.8	363.9
65°	325.6	323.5	321.3	319.6	318.5	317.2	316.0	314.8
67.5°	277.7	276.0	274.3	273.0	272.1	271.1	270.1	269.1
70°	246.5	244.8	243.2	241.8	240.9	239.9	239.0	238.0
72.5°	217.1	215.4	213.8	212.5	211.7	211.0	210.2	209.5
75°	171.3	169.8	168.4	168.0	168.4	168.9	169.3	169.8
77.5°	130.4	129.6	128.9	128.2	127.5	126.9	126.2	125.5
80°	103.5	102.8	102.1	101.4	100.9	100.5	100.0	99.5
82.5°	77.1	76.2	75.3	74.8	74.7	74.6	74.5	74.4
85°	40.8	40.0	39.3	38.8	38.6	38.3	38.1	37.8
87.5°	15.3	14.7	14.0	13.6	13.5	13.3	13.1	13.0
90°	21.8	21.4	21.2	21.1	21.3	21.4	21.5	21.7
92.5°	20.4	20.5	20.5	20.5	20.5	20.6	20.6	20.6
95°	40.8	40.8	40.8	40.7	40.4	40.1	39.8	39.5
97.5°	68.6	68.6	68.6	68.6	68.6	68.5	68.5	68.4
100°	88.0	88.0	88.0	87.9	87.7	87.6	87.5	87.3
102.5°	109.1	109.2	109.3	109.3	109.2	109.0	108.8	108.7
105°	140.8	141.0	141.4	141.5	141.5	141.5	141.5	141.5
107.5°	175.0	175.0	175.2	175.0	174.3	173.7	173.0	172.4
110°	198.2	198.2	198.2	198.0	197.5	197.1	196.7	196.2





TEST NUMBER: P331400-930

CATALOG NUMBER: S122DIP-S865D725U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	221.4	221.1	220.8	220.5	220.1	219.8	219.6	219.2
115°	257.1	257.1	256.9	256.6	256.2	255.8	255.4	254.9
117.5°	291.7	291.4	291.0	290.7	290.2	289.8	289.3	288.9
120°	314.8	314.8	314.8	314.6	314.1	313.7	313.3	312.9
122.5°	338.6	338.3	337.9	337.6	337.3	337.0	336.6	336.4
125°	373.9	373.4	373.0	372.8	372.6	372.4	372.3	372.2
127.5°	408.1	407.6	407.1	406.6	406.2	405.7	405.3	404.8
130°	431.5	431.2	431.0	430.5	429.9	429.4	428.8	428.3
132.5°	454.3	453.6	453.1	452.5	452.0	451.6	451.1	450.7
135°	487.9	487.7	487.5	487.3	486.9	486.5	486.0	485.6
137.5°	520.1	519.9	519.8	519.5	518.9	518.4	517.8	517.2
140°	541.7	541.7	541.7	541.4	540.9	540.3	539.7	539.2
142.5°	561.3	561.4	561.5	561.3	560.7	560.1	559.6	559.1
145°	591.0	591.2	591.3	591.1	590.5	590.0	589.4	588.8
147.5°	617.1	617.4	617.8	617.7	617.1	616.5	616.0	615.5
150°	633.7	634.1	634.5	634.5	634.1	633.7	633.2	632.8
152.5°	650.2	650.8	651.3	651.3	650.8	650.2	649.6	649.1
155°	671.2	671.9	672.6	672.8	672.3	671.9	671.5	671.1
157.5°	690.6	691.5	692.5	692.6	691.9	691.3	690.6	689.9
160°	702.1	703.0	703.8	703.9	703.4	702.8	702.2	701.6
162.5°	712.5	713.5	714.4	714.5	713.9	713.2	712.5	711.8
165°	725.9	726.9	727.9	728.1	727.3	726.6	725.9	725.2
167.5°	737.0	738.0	739.0	739.2	738.4	737.7	736.9	736.2
170°	743.1	744.1	745.1	745.2	744.4	743.5	742.7	741.8
172.5°	747.7	748.7	749.7	749.7	748.9	748.0	747.2	746.4
175°	752.7	753.7	754.6	754.7	753.9	753.0	752.2	751.4
177.5°	755.0	755.7	756.4	756.4	755.7	755.0	754.3	753.7
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1

(END OF REPORT)