

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331759-930

Luminaire Tested: **S122RDIP-S1005D1080U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331759-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S1005D1080U930-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6620.6 lumens  
Efficiency: N/A  
Efficacy: 92.3 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331759-930

CATALOG NUMBER: S122RDIP-S1005D1080U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331759-930

CATALOG NUMBER: S122RDIP-S1005D1080U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	94	90	87	90	86	83	81	73	70	68	60	58	57	48	47	46	41
2	90	83	77	72	82	76	72	67	65	61	58	54	51	49	43	42	40	36
3	82	73	67	61	76	68	62	57	58	53	50	48	45	42	39	37	35	31
4	76	66	58	52	70	61	54	49	52	47	43	43	40	37	36	33	31	27
5	70	59	51	46	64	55	48	43	47	42	38	39	36	33	33	30	28	24
6	65	53	45	40	59	49	43	38	42	37	33	36	32	29	30	27	25	22
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	28	25	22	20
8	56	44	37	32	51	41	35	30	36	30	27	30	26	24	26	23	20	18
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	24	21	19	17
10	49	37	30	26	45	35	29	25	30	25	22	26	22	20	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	29032	29032	29032	29032
5°	32423	29214	25901	29214
10°	35974	29009	22453	29009
15°	37742	28583	17690	28583
20°	32720	27953	15309	27953
25°	21458	27091	13668	27091
30°	14443	26045	12370	26045
35°	11698	24727	11158	24727
40°	10404	23294	10323	23294
45°	9417	21614	9216	21614
50°	8568	19947	8538	19947
55°	8056	18097	7949	18097
60°	6736	16401	6659	16401
65°	5681	14896	6445	14896
70°	5249	13303	6076	13303
75°	4916	11578	5608	11578
80°	4537	9530	4993	9530
85°	4168	7521	4390	7521



TEST NUMBER: P331759-930

CATALOG NUMBER: S122RDIP-S1005D1080U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	170.4	2.6
10°-20°	474.9	7.2
20°-30°	612.0	9.2
30°-40°	581.6	8.8
40°-50°	498.2	7.5
50°-60°	379.4	5.7
60°-70°	239.9	3.6
70°-80°	119.8	1.8
80°-90°	34.1	0.5
90°-100°	40.0	0.6
100°-110°	146.5	2.2
110°-120°	391.7	5.9
120°-130°	646.5	9.8
130°-140°	687.6	10.4
140°-150°	639.1	9.7
150°-160°	513.8	7.8
160°-170°	331.1	5.0
170°-180°	114.0	1.7
0°-30°	1257.4	19.0
0°-40°	1839.0	27.8
0°-60°	2716.7	41.0
0°-90°	3110.5	47.0
90°-120°	578.1	8.7
90°-150°	2551.3	38.5
90°-180°	3510.0	53.0
0°-180°	6620.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1798	1798	1798	1798	1798	
5°	2000	1802	1598	1802	2000	197
15°	2258	1710	1058	1710	2258	609
25°	1204	1521	767	1521	1204	572
35°	594	1254	566	1254	594	380
45°	412	947	404	947	412	319
55°	286	643	282	643	286	251
65°	149	390	169	390	149	151
75°	79	186	90	186	79	84
85°	22	41	24	41	22	25
90°	23	1	23	1	23	11
95°	37	56	37	56	37	35
105°	66	264	66	264	66	68
115°	71	498	71	498	71	178
125°	741	705	741	705	741	641
135°	900	872	900	872	900	694
145°	1027	1012	1027	1012	1027	642
155°	1115	1114	1115	1114	1115	514
165°	1171	1174	1171	1174	1171	331
175°	1193	1200	1193	1200	1193	114
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P331759-930

CATALOG NUMBER: S122RDIP-S1005D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1871.0	1872.6	1874.0	1870.5	1870.5	1867.5	1861.1	1856.0	1842.1	1840.0	1840.0
5°	2000.5	1999.3	2001.7	1993.7	1982.4	1979.9	1968.1	1952.4	1936.2	1918.1	1914.3
7.5°	2129.2	2127.4	2122.3	2121.0	2112.4	2093.4	2074.4	2054.0	2027.0	2000.7	1987.4
10°	2194.2	2214.8	2202.3	2180.4	2184.8	2155.5	2139.8	2113.0	2090.5	2051.1	2042.4
12.5°	2258.1	2266.3	2262.3	2249.9	2244.3	2223.9	2202.8	2179.5	2138.0	2102.6	2071.8
15°	2257.9	2269.8	2272.9	2269.1	2272.3	2271.0	2259.8	2240.4	2204.2	2165.4	2131.7
17.5°	2091.2	2099.5	2119.9	2133.8	2151.3	2188.3	2206.5	2213.7	2208.3	2186.2	2162.4
20°	1904.3	1890.5	1948.0	1977.4	2002.4	2064.8	2118.6	2139.2	2172.3	2171.7	2165.4
22.5°	1639.4	1642.7	1697.1	1732.0	1805.0	1867.4	1928.7	2006.3	2070.4	2112.7	2137.5
25°	1204.5	1228.3	1282.6	1330.2	1411.4	1527.5	1633.1	1755.6	1871.2	1962.4	2049.3
27.5°	904.7	906.4	949.5	993.4	1041.6	1136.9	1269.7	1416.0	1580.8	1716.8	1873.2
30°	774.7	770.9	789.0	816.0	857.2	930.9	1030.9	1174.6	1338.9	1543.8	1726.2
32.5°	682.7	683.0	696.6	716.5	750.7	800.5	868.9	985.6	1140.9	1342.4	1556.3
35°	593.5	592.9	602.9	617.3	631.6	663.5	710.4	771.6	878.4	1066.5	1285.2
37.5°	529.5	532.3	537.2	546.2	562.1	579.8	607.9	649.0	725.1	836.3	1020.1
40°	493.6	494.8	501.7	509.2	518.5	532.3	555.4	588.6	644.2	732.9	867.2
42.5°	460.6	461.9	466.7	473.7	481.1	494.8	514.0	542.6	587.7	656.9	767.7
45°	412.4	412.4	416.7	419.9	428.0	440.4	456.1	479.8	511.0	562.3	636.0
47.5°	367.1	367.2	370.1	375.5	380.6	390.4	405.7	425.1	447.8	487.5	550.4
50°	341.1	341.8	343.6	348.0	351.1	359.9	371.8	388.6	412.4	443.0	495.5
52.5°	320.2	319.8	322.1	324.0	326.1	332.4	341.3	356.1	377.3	404.0	447.4
55°	286.2	283.6	287.4	290.5	292.4	294.9	299.9	309.2	327.3	349.8	382.4
57.5°	243.7	242.6	245.3	248.2	254.0	260.8	265.1	271.0	280.4	296.5	328.7
60°	208.6	208.6	214.3	216.1	223.1	231.8	240.5	245.6	254.9	265.5	289.3
62.5°	177.7	178.2	180.8	182.7	186.5	197.3	209.5	220.5	229.4	239.5	255.3
65°	148.7	149.9	149.9	151.2	153.7	156.2	161.2	169.9	185.6	199.9	211.8
67.5°	126.2	126.6	126.9	128.2	128.8	131.6	133.5	137.5	141.0	154.7	169.4
70°	111.2	113.1	112.4	113.7	114.3	115.6	118.1	119.9	125.6	128.7	137.5
72.5°	97.2	98.6	98.5	99.2	100.9	101.1	103.1	104.9	108.6	111.2	115.9
75°	78.8	78.1	78.8	80.0	80.6	81.2	81.2	83.7	85.6	88.1	91.2
77.5°	60.7	61.4	61.2	61.4	61.5	62.6	62.5	63.6	65.5	66.7	68.2
80°	48.8	49.3	48.8	49.3	50.0	50.6	50.0	50.6	52.5	53.7	53.7
82.5°	37.7	37.8	38.2	38.4	38.5	38.6	39.5	39.6	41.0	40.8	41.3
85°	22.5	21.9	21.9	21.9	22.5	23.2	22.5	22.5	23.2	23.2	23.2
87.5°	12.6	13.1	13.0	13.0	12.9	12.7	12.6	12.9	12.1	12.5	11.7
90°	23.4	23.0	22.7	22.3	21.9	21.2	20.2	19.2	18.3	17.4	15.8
92.5°	23.4	23.2	22.9	22.7	22.5	22.1	21.6	21.1	20.6	20.1	19.3
95°	37.3	37.4	37.7	37.8	38.1	37.7	36.7	35.7	34.7	33.8	32.4
97.5°	49.7	49.5	49.3	49.1	48.8	48.3	47.5	46.8	46.0	45.2	42.2
100°	58.0	57.7	57.3	56.9	56.5	55.6	54.1	52.5	51.0	49.4	46.1
102.5°	62.2	61.7	61.1	60.6	60.1	58.8	56.8	54.8	52.8	50.8	48.2
105°	65.9	65.1	64.3	63.6	62.8	61.3	59.2	57.1	55.0	52.8	50.4
107.5°	67.8	67.0	66.2	65.5	64.7	65.4	67.5	69.7	71.8	74.0	78.1
110°	68.5	67.7	66.9	66.1	65.4	74.6	93.9	113.2	132.4	151.6	207.3



TEST NUMBER: P331759-930

CATALOG NUMBER: S122RDIP-S1005D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	69.1	68.6	67.9	67.3	66.7	101.5	171.8	242.1	312.3	382.5	396.3
115°	71.1	85.0	98.8	112.7	126.5	178.1	267.3	356.4	445.6	534.8	529.9
117.5°	290.2	335.7	381.3	426.9	472.5	506.1	527.6	549.2	570.7	592.3	589.0
120°	528.7	554.6	580.7	606.7	632.7	644.6	642.2	639.9	637.6	635.3	631.9
122.5°	659.7	664.8	669.8	674.9	679.9	681.8	680.4	679.0	677.6	676.2	672.5
125°	741.0	740.5	739.9	739.3	738.7	737.8	736.4	735.1	733.7	732.4	728.7
127.5°	792.3	792.2	792.1	792.0	791.9	790.8	788.9	786.9	785.0	783.0	780.2
130°	824.3	824.4	824.6	824.8	825.0	824.0	821.9	819.8	817.7	815.5	813.4
132.5°	855.4	855.7	855.8	856.0	856.2	855.4	853.6	851.7	849.9	848.2	846.0
135°	900.5	900.9	901.2	901.6	902.0	901.2	899.4	897.4	895.5	893.6	891.9
137.5°	941.6	942.2	942.9	943.5	944.2	943.5	941.7	939.8	937.9	936.0	934.1
140°	967.3	968.2	969.1	970.1	971.1	970.7	969.0	967.3	965.5	963.8	961.6
142.5°	992.2	993.2	994.1	995.1	996.1	995.7	994.2	992.5	991.0	989.4	987.0
145°	1027.0	1028.0	1029.0	1030.0	1030.9	1030.7	1029.3	1028.0	1026.6	1025.3	1022.1
147.5°	1057.7	1058.5	1059.3	1060.1	1060.9	1060.9	1059.9	1058.8	1057.9	1056.9	1053.6
150°	1076.4	1077.4	1078.4	1079.3	1080.3	1080.2	1079.0	1077.9	1076.8	1075.5	1072.5
152.5°	1092.4	1093.6	1094.9	1096.2	1097.5	1097.6	1096.4	1095.2	1094.1	1092.9	1090.0
155°	1114.6	1116.1	1117.7	1119.2	1120.7	1121.0	1119.8	1118.6	1117.4	1116.3	1114.0
157.5°	1134.8	1136.4	1137.8	1139.4	1140.8	1140.9	1139.6	1138.3	1137.0	1135.7	1134.1
160°	1146.6	1148.0	1149.3	1150.7	1152.0	1152.1	1151.0	1149.8	1148.7	1147.5	1146.4
162.5°	1156.3	1158.0	1159.7	1161.3	1162.9	1163.2	1161.8	1160.5	1159.2	1157.9	1156.9
165°	1170.9	1172.2	1173.6	1174.9	1176.3	1176.3	1174.9	1173.6	1172.2	1170.9	1170.4
167.5°	1180.1	1181.9	1183.6	1185.3	1187.0	1187.2	1185.9	1184.5	1183.2	1181.9	1181.3
170°	1185.6	1187.4	1189.1	1190.8	1192.5	1192.8	1191.4	1190.1	1188.7	1187.4	1187.0
172.5°	1189.8	1191.6	1193.3	1195.0	1196.8	1196.9	1195.6	1194.3	1192.9	1191.6	1191.2
175°	1193.4	1195.4	1197.3	1199.2	1201.2	1201.4	1200.1	1198.7	1197.4	1196.0	1195.6
177.5°	1195.7	1197.1	1198.5	1199.9	1201.3	1201.4	1200.3	1199.2	1198.2	1197.1	1196.9
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331759-930

CATALOG NUMBER: S122RDIP-S1005D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1841.1	1837.0	1833.6	1824.6	1820.1	1810.0	1808.6	1808.1	1795.1	1782.6	1779.1
5°	1904.3	1894.3	1879.3	1861.8	1843.7	1825.0	1812.5	1802.5	1777.4	1753.7	1740.0
7.5°	1968.1	1946.5	1920.7	1887.6	1859.9	1829.0	1806.0	1785.3	1749.9	1715.9	1693.0
10°	2015.5	1980.5	1946.1	1900.5	1864.9	1829.9	1797.5	1769.4	1729.3	1684.4	1652.5
12.5°	2045.0	2006.5	1959.2	1914.6	1868.4	1824.0	1780.5	1744.3	1697.4	1650.9	1613.1
15°	2084.9	2043.6	1986.2	1922.4	1863.0	1805.0	1755.0	1710.0	1648.8	1593.2	1546.9
17.5°	2117.5	2060.8	1999.0	1925.3	1856.6	1782.7	1718.4	1660.9	1592.8	1525.7	1471.2
20°	2127.9	2071.8	2000.5	1926.8	1845.6	1758.8	1689.4	1626.9	1553.8	1480.7	1418.2
22.5°	2121.5	2077.7	1998.5	1910.3	1827.1	1736.3	1657.9	1585.4	1504.3	1429.7	1357.2
25°	2077.4	2062.4	1987.4	1891.2	1796.2	1690.6	1600.0	1520.7	1428.2	1348.3	1269.5
27.5°	1974.5	2006.9	1960.4	1857.9	1752.3	1639.2	1537.3	1447.0	1351.0	1261.0	1182.6
30°	1875.6	1949.9	1929.9	1834.9	1716.9	1605.7	1491.3	1397.0	1294.5	1202.1	1124.6
32.5°	1740.1	1863.0	1882.4	1803.0	1680.9	1558.7	1438.8	1345.0	1238.0	1140.6	1065.1
35°	1524.4	1708.1	1792.4	1741.9	1619.4	1487.6	1363.8	1254.5	1147.0	1050.8	975.9
37.5°	1267.1	1517.4	1657.9	1661.5	1549.1	1412.0	1277.2	1168.7	1058.7	964.3	883.2
40°	1100.2	1371.3	1554.4	1595.1	1500.1	1352.0	1215.8	1105.2	997.8	905.3	812.2
42.5°	950.3	1220.4	1445.4	1516.0	1440.6	1293.6	1156.8	1041.2	936.8	849.3	754.2
45°	768.5	1004.6	1252.6	1378.8	1337.0	1200.8	1056.5	946.6	848.4	772.8	681.6
47.5°	648.2	814.7	1054.8	1225.4	1224.7	1100.3	958.4	853.0	762.1	691.2	617.4
50°	579.8	724.7	927.8	1121.4	1137.7	1033.4	898.4	794.1	709.1	634.8	575.4
52.5°	518.3	637.7	820.4	1006.0	1052.2	961.9	831.0	734.6	652.2	583.8	533.0
55°	438.0	530.4	669.1	842.8	912.8	849.1	732.9	642.9	576.0	518.5	474.8
57.5°	370.5	439.9	551.1	691.0	772.5	732.4	636.5	563.5	506.2	454.2	419.7
60°	328.0	384.8	479.2	596.1	686.0	657.9	576.0	507.9	459.2	414.3	381.7
62.5°	288.0	336.9	417.8	512.6	595.0	583.4	516.6	459.4	416.7	375.8	348.2
65°	231.8	267.4	330.5	404.9	471.1	476.7	428.6	389.9	351.7	319.3	294.9
67.5°	184.6	207.8	252.3	314.9	364.5	382.2	352.9	323.3	293.0	267.9	246.8
70°	155.6	174.3	206.8	257.4	303.0	321.7	304.9	281.8	255.5	234.9	216.8
72.5°	126.0	144.3	168.3	205.5	244.5	264.8	258.9	242.3	221.0	203.9	186.8
75°	95.0	100.6	116.8	141.9	172.4	190.0	194.3	185.6	168.7	155.6	145.5
77.5°	70.2	73.6	81.4	94.5	114.5	130.0	136.5	135.4	123.8	116.2	106.8
80°	56.3	58.1	61.9	67.5	82.5	98.1	102.5	102.5	94.3	91.2	81.9
82.5°	42.7	44.1	46.4	49.5	56.5	70.1	75.0	76.0	70.8	66.7	59.4
85°	24.4	23.7	25.0	26.9	28.1	31.9	39.4	40.6	39.4	34.3	32.4
87.5°	11.3	11.6	11.3	10.4	10.4	10.5	12.6	14.7	13.1	12.0	11.4
90°	14.3	12.7	11.2	9.4	7.3	5.1	3.0	0.9	3.0	5.1	7.3
92.5°	18.6	17.8	17.0	16.7	17.0	17.1	17.3	17.5	17.3	17.1	17.0
95°	31.1	29.8	28.4	30.9	37.3	43.6	50.0	56.3	50.0	43.6	37.3
97.5°	39.0	35.9	32.8	40.2	58.0	76.0	93.9	111.8	93.9	76.0	58.0
100°	42.9	39.5	36.3	47.9	74.3	100.6	127.0	153.4	127.0	100.6	74.3
102.5°	105.6	133.0	160.4	176.8	182.4	188.0	193.6	199.2	193.6	188.0	182.4
105°	158.0	210.6	263.2	286.6	280.8	275.0	269.3	263.5	269.3	275.0	280.8
107.5°	200.2	263.2	326.3	355.5	350.7	346.1	341.4	336.8	341.4	346.1	350.7
110°	263.0	318.6	374.3	400.1	396.1	392.1	388.0	383.9	388.0	392.1	396.1





TEST NUMBER: P331759-930

CATALOG NUMBER: S122RDIP-S1005D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	410.1	423.8	437.6	442.6	439.0	435.5	431.9	428.4	431.9	435.5	439.0
115°	525.1	520.3	515.5	511.4	508.2	504.9	501.7	498.4	501.7	504.9	508.2
117.5°	585.7	582.4	579.0	575.6	571.9	568.3	564.6	560.9	564.6	568.3	571.9
120°	628.4	624.9	621.4	618.2	615.4	612.5	609.6	606.7	609.6	612.5	615.4
122.5°	668.6	664.9	661.1	657.7	654.7	651.6	648.6	645.6	648.6	651.6	654.7
125°	725.0	721.4	717.7	714.6	712.2	709.6	707.1	704.7	707.1	709.6	712.2
127.5°	777.5	774.8	772.0	769.3	766.5	763.8	761.0	758.2	761.0	763.8	766.5
130°	811.3	809.2	807.1	804.5	801.4	798.3	795.2	792.1	795.2	798.3	801.4
132.5°	843.9	841.8	839.7	837.3	834.7	832.1	829.5	826.8	829.5	832.1	834.7
135°	890.1	888.4	886.6	884.2	881.2	878.1	875.0	871.9	875.0	878.1	881.2
137.5°	932.1	930.2	928.1	926.1	924.0	921.8	919.7	917.5	919.7	921.8	924.0
140°	959.5	957.4	955.3	953.5	951.9	950.4	948.8	947.3	948.8	950.4	951.9
142.5°	984.6	982.1	979.7	977.8	976.4	975.0	973.6	972.2	973.6	975.0	976.4
145°	1018.7	1015.5	1012.2	1010.6	1010.9	1011.1	1011.2	1011.5	1011.2	1011.1	1010.9
147.5°	1050.4	1047.2	1043.9	1042.7	1043.4	1044.2	1044.9	1045.6	1044.9	1044.2	1043.4
150°	1069.4	1066.3	1063.2	1062.4	1063.7	1065.1	1066.4	1067.8	1066.4	1065.1	1063.7
152.5°	1087.0	1084.1	1081.2	1080.5	1082.0	1083.5	1085.0	1086.5	1085.0	1083.5	1082.0
155°	1111.7	1109.4	1107.1	1106.8	1108.5	1110.3	1112.0	1113.7	1112.0	1110.3	1108.5
157.5°	1132.5	1130.9	1129.3	1129.2	1130.7	1132.1	1133.6	1135.1	1133.6	1132.1	1130.7
160°	1145.2	1144.0	1142.9	1142.9	1144.0	1145.2	1146.4	1147.5	1146.4	1145.2	1144.0
162.5°	1155.9	1154.9	1153.9	1154.0	1155.1	1156.3	1157.5	1158.6	1157.5	1156.3	1155.1
165°	1169.8	1169.1	1168.6	1168.9	1170.0	1171.2	1172.3	1173.5	1172.3	1171.2	1170.0
167.5°	1180.7	1180.2	1179.7	1180.0	1181.1	1182.3	1183.5	1184.6	1183.5	1182.3	1181.1
170°	1186.6	1186.3	1185.9	1186.3	1187.4	1188.5	1189.7	1190.8	1189.7	1188.5	1187.4
172.5°	1190.7	1190.4	1190.0	1190.4	1191.6	1192.7	1193.8	1195.0	1193.8	1192.7	1191.6
175°	1195.3	1194.9	1194.5	1195.0	1196.4	1197.7	1199.1	1200.4	1199.1	1197.7	1196.4
177.5°	1196.8	1196.6	1196.5	1196.9	1198.0	1199.1	1200.2	1201.3	1200.2	1199.1	1198.0
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331759-930

CATALOG NUMBER: S122RDIP-S1005D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1772.6	1769.1	1762.6	1752.6	1746.6	1736.1	1729.1	1733.1	1734.1	1733.1	1732.1
5°	1725.0	1711.9	1693.8	1676.3	1660.0	1642.5	1632.6	1628.2	1619.4	1614.4	1611.9
7.5°	1667.4	1644.8	1619.2	1588.7	1562.8	1535.7	1521.8	1514.9	1497.1	1487.4	1478.8
10°	1624.4	1588.8	1563.2	1523.2	1498.8	1463.2	1438.8	1439.5	1415.1	1401.3	1391.4
12.5°	1577.0	1537.8	1495.2	1459.2	1425.4	1396.8	1367.3	1355.5	1329.7	1316.4	1289.4
15°	1498.2	1452.6	1407.6	1358.9	1324.5	1280.2	1237.7	1185.9	1143.9	1107.7	1097.7
17.5°	1412.3	1355.8	1310.7	1253.4	1194.6	1120.0	1070.7	1040.6	1015.4	996.3	982.0
20°	1353.2	1295.8	1247.7	1161.5	1082.1	1031.5	995.2	972.2	945.9	925.3	914.0
22.5°	1291.3	1231.3	1165.7	1069.5	1007.6	967.0	934.7	908.2	890.4	874.3	864.1
25°	1203.3	1137.7	1029.6	963.4	913.4	870.9	848.4	832.2	813.4	791.6	781.6
27.5°	1110.4	1006.0	928.4	879.1	831.4	803.8	783.6	759.4	742.6	732.7	722.4
30°	1040.9	936.5	876.0	822.2	788.5	757.8	734.1	720.4	704.1	687.2	680.4
32.5°	963.4	880.0	822.0	777.2	743.0	716.9	698.1	675.9	664.1	653.8	639.4
35°	867.2	804.0	751.0	714.8	682.2	661.0	639.1	626.0	604.8	596.1	590.4
37.5°	785.7	731.0	691.4	653.1	627.4	603.9	590.5	569.6	560.4	548.3	536.5
40°	739.7	686.0	647.9	616.6	587.9	570.4	553.5	536.7	522.9	517.3	503.0
42.5°	692.8	649.0	610.9	576.7	557.4	538.9	517.6	505.2	491.0	481.8	473.0
45°	627.9	589.1	556.7	528.6	507.3	488.0	474.2	453.6	445.5	427.4	419.9
47.5°	571.0	534.9	503.9	477.2	456.5	443.8	423.7	407.6	394.6	383.5	373.9
50°	530.4	500.4	470.4	446.7	428.0	409.9	389.2	381.1	361.1	355.5	349.8
52.5°	493.4	465.0	437.5	414.3	395.5	377.9	359.7	349.1	335.7	330.0	325.9
55°	441.7	414.3	388.0	367.4	348.6	330.5	319.3	306.1	299.9	295.5	290.5
57.5°	389.7	365.0	344.9	324.0	305.2	290.7	277.8	269.9	263.4	257.6	251.7
60°	356.8	333.0	314.9	295.5	276.1	264.2	254.3	244.9	237.4	228.7	226.2
62.5°	321.7	301.0	284.4	265.5	248.7	237.8	228.3	219.4	210.4	197.7	194.2
65°	273.6	257.4	239.9	224.3	209.3	198.7	184.9	175.0	171.2	169.9	169.3
67.5°	230.2	214.8	199.8	183.8	170.2	160.3	153.4	151.8	149.2	148.5	146.7
70°	201.2	186.8	171.8	156.8	143.7	141.9	139.3	136.8	133.7	132.5	131.2
72.5°	175.2	160.3	145.3	133.3	127.7	125.3	122.9	120.3	118.2	117.0	116.2
75°	134.4	120.6	110.6	106.2	103.1	101.2	97.4	95.6	94.3	92.5	91.8
77.5°	96.7	88.9	84.4	81.6	78.4	76.3	74.2	72.3	71.0	70.6	69.6
80°	73.7	70.0	66.9	63.1	61.9	59.4	58.7	56.8	57.5	55.6	55.6
82.5°	57.2	52.5	49.9	48.1	46.9	44.8	44.3	43.4	43.5	42.1	42.1
85°	29.4	28.1	26.9	25.6	25.6	23.7	24.4	23.7	23.7	22.5	21.9
87.5°	11.3	11.3	10.5	10.8	11.2	10.9	11.2	10.8	11.0	11.3	10.8
90°	9.4	11.2	12.7	14.3	15.8	17.4	18.3	19.2	20.2	21.2	21.9
92.5°	16.7	17.0	17.8	18.6	19.3	20.1	20.6	21.1	21.6	22.1	22.5
95°	30.9	28.4	29.8	31.1	32.4	33.8	34.7	35.7	36.7	37.7	38.1
97.5°	40.2	32.8	35.9	39.0	42.2	45.2	46.0	46.8	47.5	48.3	48.8
100°	47.9	36.3	39.5	42.9	46.1	49.4	51.0	52.5	54.1	55.6	56.5
102.5°	176.8	160.4	133.0	105.6	78.2	50.8	52.8	54.8	56.8	58.8	60.1
105°	286.6	263.2	210.6	158.0	105.4	52.8	55.0	57.1	59.2	61.3	62.8
107.5°	355.5	326.3	263.2	200.2	137.1	74.0	71.8	69.7	67.5	65.4	64.7
110°	400.1	374.3	318.6	263.0	207.3	151.6	132.4	113.2	93.9	74.6	65.4



TEST NUMBER: P331759-930

CATALOG NUMBER: S122RDIP-S1005D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	442.6	437.6	423.8	410.1	396.3	382.5	312.3	242.1	171.8	101.5	66.7
115°	511.4	515.5	520.3	525.1	529.9	534.8	445.6	356.4	267.3	178.1	126.5
117.5°	575.6	579.0	582.4	585.7	589.0	592.3	570.7	549.2	527.6	506.1	472.5
120°	618.2	621.4	624.9	628.4	631.9	635.3	637.6	639.9	642.2	644.6	632.7
122.5°	657.7	661.1	664.9	668.6	672.5	676.2	677.6	679.0	680.4	681.8	679.9
125°	714.6	717.7	721.4	725.0	728.7	732.4	733.7	735.1	736.4	737.8	738.7
127.5°	769.3	772.0	774.8	777.5	780.2	783.0	785.0	786.9	788.9	790.8	791.9
130°	804.5	807.1	809.2	811.3	813.4	815.5	817.7	819.8	821.9	824.0	825.0
132.5°	837.3	839.7	841.8	843.9	846.0	848.2	849.9	851.7	853.6	855.4	856.2
135°	884.2	886.6	888.4	890.1	891.9	893.6	895.5	897.4	899.4	901.2	902.0
137.5°	926.1	928.1	930.2	932.1	934.1	936.0	937.9	939.8	941.7	943.5	944.2
140°	953.5	955.3	957.4	959.5	961.6	963.8	965.5	967.3	969.0	970.7	971.1
142.5°	977.8	979.7	982.1	984.6	987.0	989.4	991.0	992.5	994.2	995.7	996.1
145°	1010.6	1012.2	1015.5	1018.7	1022.1	1025.3	1026.6	1028.0	1029.3	1030.7	1030.9
147.5°	1042.7	1043.9	1047.2	1050.4	1053.6	1056.9	1057.9	1058.8	1059.9	1060.9	1060.9
150°	1062.4	1063.2	1066.3	1069.4	1072.5	1075.5	1076.8	1077.9	1079.0	1080.2	1080.3
152.5°	1080.5	1081.2	1084.1	1087.0	1090.0	1092.9	1094.1	1095.2	1096.4	1097.6	1097.5
155°	1106.8	1107.1	1109.4	1111.7	1114.0	1116.3	1117.4	1118.6	1119.8	1121.0	1120.7
157.5°	1129.2	1129.3	1130.9	1132.5	1134.1	1135.7	1137.0	1138.3	1139.6	1140.9	1140.8
160°	1142.9	1142.9	1144.0	1145.2	1146.4	1147.5	1148.7	1149.8	1151.0	1152.1	1152.0
162.5°	1154.0	1153.9	1154.9	1155.9	1156.9	1157.9	1159.2	1160.5	1161.8	1163.2	1162.9
165°	1168.9	1168.6	1169.1	1169.8	1170.4	1170.9	1172.2	1173.6	1174.9	1176.3	1176.3
167.5°	1180.0	1179.7	1180.2	1180.7	1181.3	1181.9	1183.2	1184.5	1185.9	1187.2	1187.0
170°	1186.3	1185.9	1186.3	1186.6	1187.0	1187.4	1188.7	1190.1	1191.4	1192.8	1192.5
172.5°	1190.4	1190.0	1190.4	1190.7	1191.2	1191.6	1192.9	1194.3	1195.6	1196.9	1196.8
175°	1195.0	1194.5	1194.9	1195.3	1195.6	1196.0	1197.4	1198.7	1200.1	1201.4	1201.2
177.5°	1196.9	1196.5	1196.6	1196.8	1196.9	1197.1	1198.2	1199.2	1200.3	1201.4	1201.3
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331759-930

CATALOG NUMBER: S122RDIP-S1005D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1726.6	1727.6	1726.2	1727.1	1726.2	1727.6	1726.6	1732.1	1733.1	1734.1	1733.1
5°	1608.7	1601.2	1600.0	1598.1	1600.0	1601.2	1608.7	1611.9	1614.4	1619.4	1628.2
7.5°	1468.1	1467.0	1463.9	1459.5	1463.9	1467.0	1468.1	1478.8	1487.4	1497.1	1514.9
10°	1377.6	1374.5	1373.9	1369.5	1373.9	1374.5	1377.6	1391.4	1401.3	1415.1	1439.5
12.5°	1271.6	1251.6	1249.4	1238.5	1249.4	1251.6	1271.6	1289.4	1316.4	1329.7	1355.5
15°	1082.7	1079.0	1066.5	1058.3	1066.5	1079.0	1082.7	1097.7	1107.7	1143.9	1185.9
17.5°	974.8	962.5	958.6	956.9	958.6	962.5	974.8	982.0	996.3	1015.4	1040.6
20°	905.3	894.1	892.2	891.0	892.2	894.1	905.3	914.0	925.3	945.9	972.2
22.5°	857.3	845.5	840.7	836.9	840.7	845.5	857.3	864.1	874.3	890.4	908.2
25°	775.3	770.9	768.5	767.2	768.5	770.9	775.3	781.6	791.6	813.4	832.2
27.5°	711.3	701.6	699.8	696.5	699.8	701.6	711.3	722.4	732.7	742.6	759.4
30°	674.7	671.6	667.2	663.5	667.2	671.6	674.7	680.4	687.2	704.1	720.4
32.5°	631.8	629.2	625.3	623.5	625.3	629.2	631.8	639.4	653.8	664.1	675.9
35°	584.2	575.4	571.7	566.1	571.7	575.4	584.2	590.4	596.1	604.8	626.0
37.5°	533.8	529.2	523.9	525.8	523.9	529.2	533.8	536.5	548.3	560.4	569.6
40°	494.8	491.7	490.5	489.8	490.5	491.7	494.8	503.0	517.3	522.9	536.7
42.5°	463.8	455.2	451.9	451.8	451.9	455.2	463.8	473.0	481.8	491.0	505.2
45°	416.7	408.6	403.0	403.6	403.0	408.6	416.7	419.9	427.4	445.5	453.6
47.5°	368.5	368.3	364.8	365.8	364.8	368.3	368.5	373.9	383.5	394.6	407.6
50°	345.5	341.8	339.2	339.9	339.2	341.8	345.5	349.8	355.5	361.1	381.1
52.5°	323.5	320.2	318.3	320.9	318.3	320.2	323.5	325.9	330.0	335.7	349.1
55°	287.4	283.6	283.0	282.4	283.0	283.6	287.4	290.5	295.5	299.9	306.1
57.5°	247.0	244.5	240.8	239.1	240.8	244.5	247.0	251.7	257.6	263.4	269.9
60°	218.0	213.0	206.8	206.2	206.8	213.0	218.0	226.2	228.7	237.4	244.9
62.5°	191.5	190.5	189.3	189.1	189.3	190.5	191.5	194.2	197.7	210.4	219.4
65°	168.0	167.5	168.0	168.7	168.0	167.5	168.0	169.3	169.9	171.2	175.0
67.5°	146.4	145.3	144.2	144.7	144.2	145.3	146.4	146.7	148.5	149.2	151.8
70°	130.0	129.3	128.7	128.7	128.7	129.3	130.0	131.2	132.5	133.7	136.8
72.5°	114.0	113.8	113.2	112.7	113.2	113.8	114.0	116.2	117.0	118.2	120.3
75°	91.2	89.9	89.9	89.9	89.9	89.9	91.2	91.8	92.5	94.3	95.6
77.5°	69.5	68.8	68.2	67.8	68.2	68.8	69.5	69.6	70.6	71.0	72.3
80°	55.0	54.4	53.7	53.7	53.7	54.4	55.0	55.6	55.6	57.5	56.8
82.5°	42.0	41.3	41.3	40.8	41.3	41.3	42.0	42.1	42.1	43.5	43.4
85°	22.5	23.2	22.5	23.7	22.5	23.2	22.5	21.9	22.5	23.7	23.7
87.5°	10.9	10.5	11.1	10.7	11.1	10.5	10.9	10.8	11.3	11.0	10.8
90°	22.3	22.7	23.0	23.4	23.0	22.7	22.3	21.9	21.2	20.2	19.2
92.5°	22.7	22.9	23.2	23.4	23.2	22.9	22.7	22.5	22.1	21.6	21.1
95°	37.8	37.7	37.4	37.3	37.4	37.7	37.8	38.1	37.7	36.7	35.7
97.5°	49.1	49.3	49.5	49.7	49.5	49.3	49.1	48.8	48.3	47.5	46.8
100°	56.9	57.3	57.7	58.0	57.7	57.3	56.9	56.5	55.6	54.1	52.5
102.5°	60.6	61.1	61.7	62.2	61.7	61.1	60.6	60.1	58.8	56.8	54.8
105°	63.6	64.3	65.1	65.9	65.1	64.3	63.6	62.8	61.3	59.2	57.1
107.5°	65.5	66.2	67.0	67.8	67.0	66.2	65.5	64.7	65.4	67.5	69.7
110°	66.1	66.9	67.7	68.5	67.7	66.9	66.1	65.4	74.6	93.9	113.2



TEST NUMBER: P331759-930

CATALOG NUMBER: S122RDIP-S1005D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	67.3	67.9	68.6	69.1	68.6	67.9	67.3	66.7	101.5	171.8	242.1
115°	112.7	98.8	85.0	71.1	85.0	98.8	112.7	126.5	178.1	267.3	356.4
117.5°	426.9	381.3	335.7	290.2	335.7	381.3	426.9	472.5	506.1	527.6	549.2
120°	606.7	580.7	554.6	528.7	554.6	580.7	606.7	632.7	644.6	642.2	639.9
122.5°	674.9	669.8	664.8	659.7	664.8	669.8	674.9	679.9	681.8	680.4	679.0
125°	739.3	739.9	740.5	741.0	740.5	739.9	739.3	738.7	737.8	736.4	735.1
127.5°	792.0	792.1	792.2	792.3	792.2	792.1	792.0	791.9	790.8	788.9	786.9
130°	824.8	824.6	824.4	824.3	824.4	824.6	824.8	825.0	824.0	821.9	819.8
132.5°	856.0	855.8	855.7	855.4	855.7	855.8	856.0	856.2	855.4	853.6	851.7
135°	901.6	901.2	900.9	900.5	900.9	901.2	901.6	902.0	901.2	899.4	897.4
137.5°	943.5	942.9	942.2	941.6	942.2	942.9	943.5	944.2	943.5	941.7	939.8
140°	970.1	969.1	968.2	967.3	968.2	969.1	970.1	971.1	970.7	969.0	967.3
142.5°	995.1	994.1	993.2	992.2	993.2	994.1	995.1	996.1	995.7	994.2	992.5
145°	1030.0	1029.0	1028.0	1027.0	1028.0	1029.0	1030.0	1030.9	1030.7	1029.3	1028.0
147.5°	1060.1	1059.3	1058.5	1057.7	1058.5	1059.3	1060.1	1060.9	1060.9	1059.9	1058.8
150°	1079.3	1078.4	1077.4	1076.4	1077.4	1078.4	1079.3	1080.3	1080.2	1079.0	1077.9
152.5°	1096.2	1094.9	1093.6	1092.4	1093.6	1094.9	1096.2	1097.5	1097.6	1096.4	1095.2
155°	1119.2	1117.7	1116.1	1114.6	1116.1	1117.7	1119.2	1120.7	1121.0	1119.8	1118.6
157.5°	1139.4	1137.8	1136.4	1134.8	1136.4	1137.8	1139.4	1140.8	1140.9	1139.6	1138.3
160°	1150.7	1149.3	1148.0	1146.6	1148.0	1149.3	1150.7	1152.0	1152.1	1151.0	1149.8
162.5°	1161.3	1159.7	1158.0	1156.3	1158.0	1159.7	1161.3	1162.9	1163.2	1161.8	1160.5
165°	1174.9	1173.6	1172.2	1170.9	1172.2	1173.6	1174.9	1176.3	1176.3	1174.9	1173.6
167.5°	1185.3	1183.6	1181.9	1180.1	1181.9	1183.6	1185.3	1187.0	1187.2	1185.9	1184.5
170°	1190.8	1189.1	1187.4	1185.6	1187.4	1189.1	1190.8	1192.5	1192.8	1191.4	1190.1
172.5°	1195.0	1193.3	1191.6	1189.8	1191.6	1193.3	1195.0	1196.8	1196.9	1195.6	1194.3
175°	1199.2	1197.3	1195.4	1193.4	1195.4	1197.3	1199.2	1201.2	1201.4	1200.1	1198.7
177.5°	1199.9	1198.5	1197.1	1195.7	1197.1	1198.5	1199.9	1201.3	1201.4	1200.3	1199.2
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331759-930

CATALOG NUMBER: S122RDIP-S1005D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1729.1	1736.1	1746.6	1752.6	1762.6	1769.1	1772.6	1779.1	1782.6	1795.1	1808.1
5°	1632.6	1642.5	1660.0	1676.3	1693.8	1711.9	1725.0	1740.0	1753.7	1777.4	1802.5
7.5°	1521.8	1535.7	1562.8	1588.7	1619.2	1644.8	1667.4	1693.0	1715.9	1749.9	1785.3
10°	1438.8	1463.2	1498.8	1523.2	1563.2	1588.8	1624.4	1652.5	1684.4	1729.3	1769.4
12.5°	1367.3	1396.8	1425.4	1459.2	1495.2	1537.8	1577.0	1613.1	1650.9	1697.4	1744.3
15°	1237.7	1280.2	1324.5	1358.9	1407.6	1452.6	1498.2	1546.9	1593.2	1648.8	1710.0
17.5°	1070.7	1120.0	1194.6	1253.4	1310.7	1355.8	1412.3	1471.2	1525.7	1592.8	1660.9
20°	995.2	1031.5	1082.1	1161.5	1247.7	1295.8	1353.2	1418.2	1480.7	1553.8	1626.9
22.5°	934.7	967.0	1007.6	1069.5	1165.7	1231.3	1291.3	1357.2	1429.7	1504.3	1585.4
25°	848.4	870.9	913.4	963.4	1029.6	1137.7	1203.3	1269.5	1348.3	1428.2	1520.7
27.5°	783.6	803.8	831.4	879.1	928.4	1006.0	1110.4	1182.6	1261.0	1351.0	1447.0
30°	734.1	757.8	788.5	822.2	876.0	936.5	1040.9	1124.6	1202.1	1294.5	1397.0
32.5°	698.1	716.9	743.0	777.2	822.0	880.0	963.4	1065.1	1140.6	1238.0	1345.0
35°	639.1	661.0	682.2	714.8	751.0	804.0	867.2	975.9	1050.8	1147.0	1254.5
37.5°	590.5	603.9	627.4	653.1	691.4	731.0	785.7	883.2	964.3	1058.7	1168.7
40°	553.5	570.4	587.9	616.6	647.9	686.0	739.7	812.2	905.3	997.8	1105.2
42.5°	517.6	538.9	557.4	576.7	610.9	649.0	692.8	754.2	849.3	936.8	1041.2
45°	474.2	488.0	507.3	528.6	556.7	589.1	627.9	681.6	772.8	848.4	946.6
47.5°	423.7	443.8	456.5	477.2	503.9	534.9	571.0	617.4	691.2	762.1	853.0
50°	389.2	409.9	428.0	446.7	470.4	500.4	530.4	575.4	634.8	709.1	794.1
52.5°	359.7	377.9	395.5	414.3	437.5	465.0	493.4	533.0	583.8	652.2	734.6
55°	319.3	330.5	348.6	367.4	388.0	414.3	441.7	474.8	518.5	576.0	642.9
57.5°	277.8	290.7	305.2	324.0	344.9	365.0	389.7	419.7	454.2	506.2	563.5
60°	254.3	264.2	276.1	295.5	314.9	333.0	356.8	381.7	414.3	459.2	507.9
62.5°	228.3	237.8	248.7	265.5	284.4	301.0	321.7	348.2	375.8	416.7	459.4
65°	184.9	198.7	209.3	224.3	239.9	257.4	273.6	294.9	319.3	351.7	389.9
67.5°	153.4	160.3	170.2	183.8	199.8	214.8	230.2	246.8	267.9	293.0	323.3
70°	139.3	141.9	143.7	156.8	171.8	186.8	201.2	216.8	234.9	255.5	281.8
72.5°	122.9	125.3	127.7	133.3	145.3	160.3	175.2	186.8	203.9	221.0	242.3
75°	97.4	101.2	103.1	106.2	110.6	120.6	134.4	145.5	155.6	168.7	185.6
77.5°	74.2	76.3	78.4	81.6	84.4	88.9	96.7	106.8	116.2	123.8	135.4
80°	58.7	59.4	61.9	63.1	66.9	70.0	73.7	81.9	91.2	94.3	102.5
82.5°	44.3	44.8	46.9	48.1	49.9	52.5	57.2	59.4	66.7	70.8	76.0
85°	24.4	23.7	25.6	25.6	26.9	28.1	29.4	32.4	34.3	39.4	40.6
87.5°	11.2	10.9	11.2	10.8	10.5	11.3	11.3	11.4	12.0	13.1	14.7
90°	18.3	17.4	15.8	14.3	12.7	11.2	9.4	7.3	5.1	3.0	0.9
92.5°	20.6	20.1	19.3	18.6	17.8	17.0	16.7	17.0	17.1	17.3	17.5
95°	34.7	33.8	32.4	31.1	29.8	28.4	30.9	37.3	43.6	50.0	56.3
97.5°	46.0	45.2	42.2	39.0	35.9	32.8	40.2	58.0	76.0	93.9	111.8
100°	51.0	49.4	46.1	42.9	39.5	36.3	47.9	74.3	100.6	127.0	153.4
102.5°	52.8	50.8	78.2	105.6	133.0	160.4	176.8	182.4	188.0	193.6	199.2
105°	55.0	52.8	105.4	158.0	210.6	263.2	286.6	280.8	275.0	269.3	263.5
107.5°	71.8	74.0	137.1	200.2	263.2	326.3	355.5	350.7	346.1	341.4	336.8
110°	132.4	151.6	207.3	263.0	318.6	374.3	400.1	396.1	392.1	388.0	383.9



TEST NUMBER: P331759-930

CATALOG NUMBER: S122RDIP-S1005D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	312.3	382.5	396.3	410.1	423.8	437.6	442.6	439.0	435.5	431.9	428.4
115°	445.6	534.8	529.9	525.1	520.3	515.5	511.4	508.2	504.9	501.7	498.4
117.5°	570.7	592.3	589.0	585.7	582.4	579.0	575.6	571.9	568.3	564.6	560.9
120°	637.6	635.3	631.9	628.4	624.9	621.4	618.2	615.4	612.5	609.6	606.7
122.5°	677.6	676.2	672.5	668.6	664.9	661.1	657.7	654.7	651.6	648.6	645.6
125°	733.7	732.4	728.7	725.0	721.4	717.7	714.6	712.2	709.6	707.1	704.7
127.5°	785.0	783.0	780.2	777.5	774.8	772.0	769.3	766.5	763.8	761.0	758.2
130°	817.7	815.5	813.4	811.3	809.2	807.1	804.5	801.4	798.3	795.2	792.1
132.5°	849.9	848.2	846.0	843.9	841.8	839.7	837.3	834.7	832.1	829.5	826.8
135°	895.5	893.6	891.9	890.1	888.4	886.6	884.2	881.2	878.1	875.0	871.9
137.5°	937.9	936.0	934.1	932.1	930.2	928.1	926.1	924.0	921.8	919.7	917.5
140°	965.5	963.8	961.6	959.5	957.4	955.3	953.5	951.9	950.4	948.8	947.3
142.5°	991.0	989.4	987.0	984.6	982.1	979.7	977.8	976.4	975.0	973.6	972.2
145°	1026.6	1025.3	1022.1	1018.7	1015.5	1012.2	1010.6	1010.9	1011.1	1011.2	1011.5
147.5°	1057.9	1056.9	1053.6	1050.4	1047.2	1043.9	1042.7	1043.4	1044.2	1044.9	1045.6
150°	1076.8	1075.5	1072.5	1069.4	1066.3	1063.2	1062.4	1063.7	1065.1	1066.4	1067.8
152.5°	1094.1	1092.9	1090.0	1087.0	1084.1	1081.2	1080.5	1082.0	1083.5	1085.0	1086.5
155°	1117.4	1116.3	1114.0	1111.7	1109.4	1107.1	1106.8	1108.5	1110.3	1112.0	1113.7
157.5°	1137.0	1135.7	1134.1	1132.5	1130.9	1129.3	1129.2	1130.7	1132.1	1133.6	1135.1
160°	1148.7	1147.5	1146.4	1145.2	1144.0	1142.9	1142.9	1144.0	1145.2	1146.4	1147.5
162.5°	1159.2	1157.9	1156.9	1155.9	1154.9	1153.9	1154.0	1155.1	1156.3	1157.5	1158.6
165°	1172.2	1170.9	1170.4	1169.8	1169.1	1168.6	1168.9	1170.0	1171.2	1172.3	1173.5
167.5°	1183.2	1181.9	1181.3	1180.7	1180.2	1179.7	1180.0	1181.1	1182.3	1183.5	1184.6
170°	1188.7	1187.4	1187.0	1186.6	1186.3	1185.9	1186.3	1187.4	1188.5	1189.7	1190.8
172.5°	1192.9	1191.6	1191.2	1190.7	1190.4	1190.0	1190.4	1191.6	1192.7	1193.8	1195.0
175°	1197.4	1196.0	1195.6	1195.3	1194.9	1194.5	1195.0	1196.4	1197.7	1199.1	1200.4
177.5°	1198.2	1197.1	1196.9	1196.8	1196.6	1196.5	1196.9	1198.0	1199.1	1200.2	1201.3
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331759-930

CATALOG NUMBER: S122RDIP-S1005D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1808.6	1810.0	1820.1	1824.6	1833.6	1837.0	1841.1	1840.0	1840.0	1842.1	1856.0
5°	1812.5	1825.0	1843.7	1861.8	1879.3	1894.3	1904.3	1914.3	1918.1	1936.2	1952.4
7.5°	1806.0	1829.0	1859.9	1887.6	1920.7	1946.5	1968.1	1987.4	2000.7	2027.0	2054.0
10°	1797.5	1829.9	1864.9	1900.5	1946.1	1980.5	2015.5	2042.4	2051.1	2090.5	2113.0
12.5°	1780.5	1824.0	1868.4	1914.6	1959.2	2006.5	2045.0	2071.8	2102.6	2138.0	2179.5
15°	1755.0	1805.0	1863.0	1922.4	1986.2	2043.6	2084.9	2131.7	2165.4	2204.2	2240.4
17.5°	1718.4	1782.7	1856.6	1925.3	1999.0	2060.8	2117.5	2162.4	2186.2	2208.3	2213.7
20°	1689.4	1758.8	1845.6	1926.8	2000.5	2071.8	2127.9	2165.4	2171.7	2172.3	2139.2
22.5°	1657.9	1736.3	1827.1	1910.3	1998.5	2077.7	2121.5	2137.5	2112.7	2070.4	2006.3
25°	1600.0	1690.6	1796.2	1891.2	1987.4	2062.4	2077.4	2049.3	1962.4	1871.2	1755.6
27.5°	1537.3	1639.2	1752.3	1857.9	1960.4	2006.9	1974.5	1873.2	1716.8	1580.8	1416.0
30°	1491.3	1605.7	1716.9	1834.9	1929.9	1949.9	1875.6	1726.2	1543.8	1338.9	1174.6
32.5°	1438.8	1558.7	1680.9	1803.0	1882.4	1863.0	1740.1	1556.3	1342.4	1140.9	985.6
35°	1363.8	1487.6	1619.4	1741.9	1792.4	1708.1	1524.4	1285.2	1066.5	878.4	771.6
37.5°	1277.2	1412.0	1549.1	1661.5	1657.9	1517.4	1267.1	1020.1	836.3	725.1	649.0
40°	1215.8	1352.0	1500.1	1595.1	1554.4	1371.3	1100.2	867.2	732.9	644.2	588.6
42.5°	1156.8	1293.6	1440.6	1516.0	1445.4	1220.4	950.3	767.7	656.9	587.7	542.6
45°	1056.5	1200.8	1337.0	1378.8	1252.6	1004.6	768.5	636.0	562.3	511.0	479.8
47.5°	958.4	1100.3	1224.7	1225.4	1054.8	814.7	648.2	550.4	487.5	447.8	425.1
50°	898.4	1033.4	1137.7	1121.4	927.8	724.7	579.8	495.5	443.0	412.4	388.6
52.5°	831.0	961.9	1052.2	1006.0	820.4	637.7	518.3	447.4	404.0	377.3	356.1
55°	732.9	849.1	912.8	842.8	669.1	530.4	438.0	382.4	349.8	327.3	309.2
57.5°	636.5	732.4	772.5	691.0	551.1	439.9	370.5	328.7	296.5	280.4	271.0
60°	576.0	657.9	686.0	596.1	479.2	384.8	328.0	289.3	265.5	254.9	245.6
62.5°	516.6	583.4	595.0	512.6	417.8	336.9	288.0	255.3	239.5	229.4	220.5
65°	428.6	476.7	471.1	404.9	330.5	267.4	231.8	211.8	199.9	185.6	169.9
67.5°	352.9	382.2	364.5	314.9	252.3	207.8	184.6	169.4	154.7	141.0	137.5
70°	304.9	321.7	303.0	257.4	206.8	174.3	155.6	137.5	128.7	125.6	119.9
72.5°	258.9	264.8	244.5	205.5	168.3	144.3	126.0	115.9	111.2	108.6	104.9
75°	194.3	190.0	172.4	141.9	116.8	100.6	95.0	91.2	88.1	85.6	83.7
77.5°	136.5	130.0	114.5	94.5	81.4	73.6	70.2	68.2	66.7	65.5	63.6
80°	102.5	98.1	82.5	67.5	61.9	58.1	56.3	53.7	53.7	52.5	50.6
82.5°	75.0	70.1	56.5	49.5	46.4	44.1	42.7	41.3	40.8	41.0	39.6
85°	39.4	31.9	28.1	26.9	25.0	23.7	24.4	23.2	23.2	23.2	22.5
87.5°	12.6	10.5	10.4	10.4	11.3	11.6	11.3	11.7	12.5	12.1	12.9
90°	3.0	5.1	7.3	9.4	11.2	12.7	14.3	15.8	17.4	18.3	19.2
92.5°	17.3	17.1	17.0	16.7	17.0	17.8	18.6	19.3	20.1	20.6	21.1
95°	50.0	43.6	37.3	30.9	28.4	29.8	31.1	32.4	33.8	34.7	35.7
97.5°	93.9	76.0	58.0	40.2	32.8	35.9	39.0	42.2	45.2	46.0	46.8
100°	127.0	100.6	74.3	47.9	36.3	39.5	42.9	46.1	49.4	51.0	52.5
102.5°	193.6	188.0	182.4	176.8	160.4	133.0	105.6	78.2	50.8	52.8	54.8
105°	269.3	275.0	280.8	286.6	263.2	210.6	158.0	105.4	52.8	55.0	57.1
107.5°	341.4	346.1	350.7	355.5	326.3	263.2	200.2	137.1	74.0	71.8	69.7
110°	388.0	392.1	396.1	400.1	374.3	318.6	263.0	207.3	151.6	132.4	113.2





TEST NUMBER: P331759-930

CATALOG NUMBER: S122RDIP-S1005D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	431.9	435.5	439.0	442.6	437.6	423.8	410.1	396.3	382.5	312.3	242.1
115°	501.7	504.9	508.2	511.4	515.5	520.3	525.1	529.9	534.8	445.6	356.4
117.5°	564.6	568.3	571.9	575.6	579.0	582.4	585.7	589.0	592.3	570.7	549.2
120°	609.6	612.5	615.4	618.2	621.4	624.9	628.4	631.9	635.3	637.6	639.9
122.5°	648.6	651.6	654.7	657.7	661.1	664.9	668.6	672.5	676.2	677.6	679.0
125°	707.1	709.6	712.2	714.6	717.7	721.4	725.0	728.7	732.4	733.7	735.1
127.5°	761.0	763.8	766.5	769.3	772.0	774.8	777.5	780.2	783.0	785.0	786.9
130°	795.2	798.3	801.4	804.5	807.1	809.2	811.3	813.4	815.5	817.7	819.8
132.5°	829.5	832.1	834.7	837.3	839.7	841.8	843.9	846.0	848.2	849.9	851.7
135°	875.0	878.1	881.2	884.2	886.6	888.4	890.1	891.9	893.6	895.5	897.4
137.5°	919.7	921.8	924.0	926.1	928.1	930.2	932.1	934.1	936.0	937.9	939.8
140°	948.8	950.4	951.9	953.5	955.3	957.4	959.5	961.6	963.8	965.5	967.3
142.5°	973.6	975.0	976.4	977.8	979.7	982.1	984.6	987.0	989.4	991.0	992.5
145°	1011.2	1011.1	1010.9	1010.6	1012.2	1015.5	1018.7	1022.1	1025.3	1026.6	1028.0
147.5°	1044.9	1044.2	1043.4	1042.7	1043.9	1047.2	1050.4	1053.6	1056.9	1057.9	1058.8
150°	1066.4	1065.1	1063.7	1062.4	1063.2	1066.3	1069.4	1072.5	1075.5	1076.8	1077.9
152.5°	1085.0	1083.5	1082.0	1080.5	1081.2	1084.1	1087.0	1090.0	1092.9	1094.1	1095.2
155°	1112.0	1110.3	1108.5	1106.8	1107.1	1109.4	1111.7	1114.0	1116.3	1117.4	1118.6
157.5°	1133.6	1132.1	1130.7	1129.2	1129.3	1130.9	1132.5	1134.1	1135.7	1137.0	1138.3
160°	1146.4	1145.2	1144.0	1142.9	1142.9	1144.0	1145.2	1146.4	1147.5	1148.7	1149.8
162.5°	1157.5	1156.3	1155.1	1154.0	1153.9	1154.9	1155.9	1156.9	1157.9	1159.2	1160.5
165°	1172.3	1171.2	1170.0	1168.9	1168.6	1169.1	1169.8	1170.4	1170.9	1172.2	1173.6
167.5°	1183.5	1182.3	1181.1	1180.0	1179.7	1180.2	1180.7	1181.3	1181.9	1183.2	1184.5
170°	1189.7	1188.5	1187.4	1186.3	1185.9	1186.3	1186.6	1187.0	1187.4	1188.7	1190.1
172.5°	1193.8	1192.7	1191.6	1190.4	1190.0	1190.4	1190.7	1191.2	1191.6	1192.9	1194.3
175°	1199.1	1197.7	1196.4	1195.0	1194.5	1194.9	1195.3	1195.6	1196.0	1197.4	1198.7
177.5°	1200.2	1199.1	1198.0	1196.9	1196.5	1196.6	1196.8	1196.9	1197.1	1198.2	1199.2
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331759-930

CATALOG NUMBER: S122RDIP-S1005D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1861.1	1867.5	1870.5	1870.5	1874.0	1872.6	1871.0
5°	1968.1	1979.9	1982.4	1993.7	2001.7	1999.3	2000.5
7.5°	2074.4	2093.4	2112.4	2121.0	2122.3	2127.4	2129.2
10°	2139.8	2155.5	2184.8	2180.4	2202.3	2214.8	2194.2
12.5°	2202.8	2223.9	2244.3	2249.9	2262.3	2266.3	2258.1
15°	2259.8	2271.0	2272.3	2269.1	2272.9	2269.8	2257.9
17.5°	2206.5	2188.3	2151.3	2133.8	2119.9	2099.5	2091.2
20°	2118.6	2064.8	2002.4	1977.4	1948.0	1890.5	1904.3
22.5°	1928.7	1867.4	1805.0	1732.0	1697.1	1642.7	1639.4
25°	1633.1	1527.5	1411.4	1330.2	1282.6	1228.3	1204.5
27.5°	1269.7	1136.9	1041.6	993.4	949.5	906.4	904.7
30°	1030.9	930.9	857.2	816.0	789.0	770.9	774.7
32.5°	868.9	800.5	750.7	716.5	696.6	683.0	682.7
35°	710.4	663.5	631.6	617.3	602.9	592.9	593.5
37.5°	607.9	579.8	562.1	546.2	537.2	532.3	529.5
40°	555.4	532.3	518.5	509.2	501.7	494.8	493.6
42.5°	514.0	494.8	481.1	473.7	466.7	461.9	460.6
45°	456.1	440.4	428.0	419.9	416.7	412.4	412.4
47.5°	405.7	390.4	380.6	375.5	370.1	367.2	367.1
50°	371.8	359.9	351.1	348.0	343.6	341.8	341.1
52.5°	341.3	332.4	326.1	324.0	322.1	319.8	320.2
55°	299.9	294.9	292.4	290.5	287.4	283.6	286.2
57.5°	265.1	260.8	254.0	248.2	245.3	242.6	243.7
60°	240.5	231.8	223.1	216.1	214.3	208.6	208.6
62.5°	209.5	197.3	186.5	182.7	180.8	178.2	177.7
65°	161.2	156.2	153.7	151.2	149.9	149.9	148.7
67.5°	133.5	131.6	128.8	128.2	126.9	126.6	126.2
70°	118.1	115.6	114.3	113.7	112.4	113.1	111.2
72.5°	103.1	101.1	100.9	99.2	98.5	98.6	97.2
75°	81.2	81.2	80.6	80.0	78.8	78.1	78.8
77.5°	62.5	62.6	61.5	61.4	61.2	61.4	60.7
80°	50.0	50.6	50.0	49.3	48.8	49.3	48.8
82.5°	39.5	38.6	38.5	38.4	38.2	37.8	37.7
85°	22.5	23.2	22.5	21.9	21.9	21.9	22.5
87.5°	12.6	12.7	12.9	13.0	13.0	13.1	12.6
90°	20.2	21.2	21.9	22.3	22.7	23.0	23.4
92.5°	21.6	22.1	22.5	22.7	22.9	23.2	23.4
95°	36.7	37.7	38.1	37.8	37.7	37.4	37.3
97.5°	47.5	48.3	48.8	49.1	49.3	49.5	49.7
100°	54.1	55.6	56.5	56.9	57.3	57.7	58.0
102.5°	56.8	58.8	60.1	60.6	61.1	61.7	62.2
105°	59.2	61.3	62.8	63.6	64.3	65.1	65.9
107.5°	67.5	65.4	64.7	65.5	66.2	67.0	67.8
110°	93.9	74.6	65.4	66.1	66.9	67.7	68.5



TEST NUMBER: P331759-930

CATALOG NUMBER: S122RDIP-S1005D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	171.8	101.5	66.7	67.3	67.9	68.6	69.1
115°	267.3	178.1	126.5	112.7	98.8	85.0	71.1
117.5°	527.6	506.1	472.5	426.9	381.3	335.7	290.2
120°	642.2	644.6	632.7	606.7	580.7	554.6	528.7
122.5°	680.4	681.8	679.9	674.9	669.8	664.8	659.7
125°	736.4	737.8	738.7	739.3	739.9	740.5	741.0
127.5°	788.9	790.8	791.9	792.0	792.1	792.2	792.3
130°	821.9	824.0	825.0	824.8	824.6	824.4	824.3
132.5°	853.6	855.4	856.2	856.0	855.8	855.7	855.4
135°	899.4	901.2	902.0	901.6	901.2	900.9	900.5
137.5°	941.7	943.5	944.2	943.5	942.9	942.2	941.6
140°	969.0	970.7	971.1	970.1	969.1	968.2	967.3
142.5°	994.2	995.7	996.1	995.1	994.1	993.2	992.2
145°	1029.3	1030.7	1030.9	1030.0	1029.0	1028.0	1027.0
147.5°	1059.9	1060.9	1060.9	1060.1	1059.3	1058.5	1057.7
150°	1079.0	1080.2	1080.3	1079.3	1078.4	1077.4	1076.4
152.5°	1096.4	1097.6	1097.5	1096.2	1094.9	1093.6	1092.4
155°	1119.8	1121.0	1120.7	1119.2	1117.7	1116.1	1114.6
157.5°	1139.6	1140.9	1140.8	1139.4	1137.8	1136.4	1134.8
160°	1151.0	1152.1	1152.0	1150.7	1149.3	1148.0	1146.6
162.5°	1161.8	1163.2	1162.9	1161.3	1159.7	1158.0	1156.3
165°	1174.9	1176.3	1176.3	1174.9	1173.6	1172.2	1170.9
167.5°	1185.9	1187.2	1187.0	1185.3	1183.6	1181.9	1180.1
170°	1191.4	1192.8	1192.5	1190.8	1189.1	1187.4	1185.6
172.5°	1195.6	1196.9	1196.8	1195.0	1193.3	1191.6	1189.8
175°	1200.1	1201.4	1201.2	1199.2	1197.3	1195.4	1193.4
177.5°	1200.3	1201.4	1201.3	1199.9	1198.5	1197.1	1195.7
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8

(END OF REPORT)