

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332000-927

Luminaire Tested: **S123DIP-S1000D365U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332000-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D365U927-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4508.3 lumens  
Efficiency: N/A  
Efficacy: 103.6 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332000-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332000-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	79	79	79	75
1	104	99	95	92	98	95	91	88	86	83	81	78	76	74	70	69	67	64
2	95	87	81	76	90	83	78	73	76	71	68	69	65	62	62	60	57	54
3	87	77	70	64	82	74	67	61	67	62	57	61	57	53	55	52	49	46
4	80	69	60	54	75	66	58	53	60	54	49	55	50	46	50	46	43	40
5	73	61	53	47	69	59	51	45	54	48	43	49	44	40	45	41	37	35
6	68	55	47	41	64	53	45	40	49	42	37	45	39	35	41	36	33	31
7	63	50	42	36	60	48	41	35	44	38	33	41	35	31	37	33	29	27
8	58	46	38	32	55	44	36	31	41	34	30	37	32	28	34	30	26	24
9	54	42	34	29	52	40	33	28	37	31	27	34	29	25	32	27	24	22
10	51	38	31	26	48	37	30	25	34	28	24	32	27	23	29	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11976	11976	11976	11976
5°	14282	12028	10659	12028
10°	17876	11967	9627	11967
15°	21926	11870	8963	11870
20°	26120	11720	8534	11720
25°	27736	11537	8438	11537
30°	23772	11404	8483	11404
35°	16533	11213	8571	11213
40°	12452	10991	8545	10991
45°	10339	10660	8435	10660
50°	9262	9984	8359	9984
55°	8659	9256	8255	9256
60°	8122	8495	8170	8495
65°	7636	7743	7908	7743
70°	7160	6889	7531	6889
75°	6413	6030	6904	6030
80°	5610	4947	5945	4947
85°	4397	3594	3989	3594



TEST NUMBER: P332000-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	109.6	2.4
10°-20°	351.5	7.8
20°-30°	589.8	13.1
30°-40°	667.9	14.8
40°-50°	598.9	13.3
50°-60°	483.3	10.7
60°-70°	336.8	7.5
70°-80°	177.0	3.9
80°-90°	44.3	1.0
90°-100°	13.7	0.3
100°-110°	65.3	1.4
110°-120°	156.8	3.5
120°-130°	199.7	4.4
130°-140°	213.4	4.7
140°-150°	199.5	4.4
150°-160°	160.9	3.6
160°-170°	103.9	2.3
170°-180°	35.8	0.8
0°-30°	1050.9	23.3
0°-40°	1718.8	38.1
0°-60°	2801.1	62.1
0°-90°	3359.2	74.5
90°-120°	235.8	5.2
90°-150°	848.4	18.8
90°-180°	1149.0	25.5
0°-180°	4508.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1113	1113	1113	1113	1113	
5°	1322	1113	986	1113	1322	137
15°	1968	1065	804	1065	1968	568
25°	2335	971	710	971	2335	1024
35°	1258	853	652	853	1258	817
45°	679	700	554	700	679	537
55°	461	493	440	493	461	414
65°	300	304	310	304	300	298
75°	154	145	166	145	154	165
85°	36	29	32	29	36	42
90°	8	0	8	0	8	6
95°	11	17	11	17	11	9
105°	12	83	12	83	12	28
115°	165	156	165	156	165	152
125°	225	221	225	221	225	201
135°	277	275	277	275	277	214
145°	320	317	320	317	320	200
155°	348	349	348	349	348	161
165°	367	368	367	368	367	104
175°	375	377	375	377	375	36
180°	377	377	377	377	377	



TEST NUMBER: P332000-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1180.7	1180.0	1177.7	1179.5	1176.1	1171.3	1170.8	1166.6	1154.1	1153.2	1149.8
5°	1321.8	1317.5	1316.9	1316.4	1308.8	1298.6	1279.2	1277.6	1251.7	1238.8	1223.1
7.5°	1504.4	1506.7	1498.8	1491.9	1468.9	1453.7	1432.8	1406.2	1374.4	1342.2	1320.7
10°	1635.5	1653.4	1631.3	1616.1	1602.1	1575.7	1545.0	1506.7	1468.5	1423.7	1389.7
12.5°	1776.2	1784.9	1780.4	1766.2	1744.5	1704.2	1649.8	1607.7	1572.4	1497.9	1467.8
15°	1967.6	2000.5	1979.5	1930.9	1932.1	1893.8	1822.6	1744.5	1703.0	1637.7	1548.8
17.5°	2171.6	2175.7	2166.8	2126.3	2099.4	2046.8	1981.1	1906.1	1822.1	1743.1	1648.8
20°	2280.3	2277.0	2258.2	2237.1	2190.8	2149.8	2078.1	1994.6	1886.7	1809.1	1706.2
22.5°	2340.7	2335.3	2326.3	2308.7	2270.2	2226.2	2161.8	2070.4	1967.9	1860.9	1741.9
25°	2335.3	2342.2	2343.4	2338.5	2325.1	2298.6	2247.9	2175.2	2072.7	1935.3	1811.3
27.5°	2123.9	2133.9	2162.7	2188.2	2216.8	2245.9	2242.0	2205.9	2130.1	2011.4	1859.8
30°	1912.6	1891.1	1944.4	2011.8	2057.6	2138.5	2183.8	2186.5	2143.9	2042.0	1894.3
32.5°	1619.4	1643.1	1666.7	1749.6	1849.7	1940.5	2030.7	2103.2	2111.6	2043.8	1914.5
35°	1258.2	1287.9	1330.9	1374.1	1481.9	1574.6	1733.1	1871.1	1981.1	1995.7	1916.4
37.5°	1013.9	1028.6	1055.8	1099.1	1169.6	1279.5	1402.2	1576.6	1735.9	1854.4	1859.6
40°	886.2	890.6	921.3	954.2	1011.3	1101.8	1212.4	1366.5	1557.4	1722.9	1791.9
42.5°	790.5	799.9	813.0	844.6	890.1	958.2	1061.0	1188.4	1363.3	1553.8	1688.8
45°	679.2	690.0	698.1	719.1	751.5	797.3	869.0	985.4	1118.6	1315.3	1497.0
47.5°	605.7	606.6	612.6	628.4	650.5	684.8	735.5	810.3	932.6	1092.2	1278.7
50°	553.1	561.7	563.9	576.2	593.5	618.9	660.9	724.5	824.8	965.0	1136.4
52.5°	516.0	518.6	524.7	533.6	548.7	568.4	604.8	654.7	733.3	852.8	1010.4
55°	461.4	461.4	467.4	474.4	483.0	500.8	525.1	561.7	621.5	714.3	844.7
57.5°	411.0	413.7	417.9	420.0	427.4	439.1	459.4	487.2	531.9	603.2	706.9
60°	377.3	382.2	381.7	386.0	392.4	401.6	418.8	441.5	481.4	538.5	625.9
62.5°	348.0	347.7	347.6	352.8	359.3	368.0	379.2	398.8	432.7	483.3	557.7
65°	299.8	298.7	302.5	305.6	307.8	314.3	322.9	340.2	362.8	400.5	458.2
67.5°	256.8	253.7	255.7	256.8	260.5	265.5	273.6	284.3	302.3	332.6	376.0
70°	227.5	224.8	224.3	225.3	228.5	232.3	238.3	248.5	265.2	289.5	321.3
72.5°	197.3	195.4	195.4	197.7	199.2	201.7	205.9	215.3	228.5	246.8	276.5
75°	154.2	154.2	154.2	154.7	156.3	158.5	161.7	166.6	176.8	189.7	209.7
77.5°	115.6	115.5	114.8	114.7	117.1	118.0	118.8	123.3	129.0	137.8	152.3
80°	90.5	87.9	89.0	90.5	91.7	92.2	93.8	94.9	99.7	104.6	114.8
82.5°	67.3	65.0	65.2	67.7	67.9	68.4	70.1	71.6	73.4	77.9	83.3
85°	35.6	35.6	36.1	36.1	36.7	36.1	37.7	38.3	38.3	41.0	44.2
87.5°	14.7	13.7	14.1	14.6	14.1	14.5	14.9	15.2	15.6	16.0	16.2
90°	8.4	8.2	8.2	8.0	7.9	7.7	7.4	7.2	7.0	6.7	5.9
92.5°	9.3	9.2	9.1	9.0	9.0	8.8	8.4	8.0	7.5	7.1	6.6
95°	10.6	10.6	10.6	10.6	10.6	10.5	10.0	9.6	9.1	8.7	8.0
97.5°	11.6	11.5	11.4	11.3	11.2	11.0	10.5	10.0	9.5	9.0	13.5
100°	11.7	11.7	11.6	11.6	11.5	11.2	10.7	10.2	9.7	9.3	18.9
102.5°	12.0	11.9	11.7	11.6	11.6	12.3	13.8	15.4	16.9	18.5	29.0
105°	12.3	12.2	12.0	12.0	11.8	17.3	28.3	39.3	50.3	61.3	66.9
107.5°	38.7	47.0	55.3	63.6	71.9	80.1	88.2	96.3	104.3	112.3	111.5
110°	77.0	85.9	94.7	103.7	112.6	118.0	120.1	122.2	124.2	126.3	125.6



TEST NUMBER: P332000-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	132.1	134.0	135.9	137.7	139.6	140.5	140.5	140.5	140.4	140.4	139.7
115°	164.6	164.4	164.1	163.8	163.6	163.2	162.6	161.9	161.3	160.7	160.1
117.5°	182.8	182.8	182.8	182.7	182.7	182.4	181.9	181.4	180.9	180.4	180.1
120°	195.4	195.4	195.4	195.4	195.4	195.1	194.6	194.2	193.7	193.1	193.0
122.5°	207.7	207.6	207.6	207.6	207.5	207.3	207.0	206.6	206.3	205.9	205.7
125°	225.1	225.0	224.8	224.7	224.6	224.4	224.3	224.2	224.1	223.9	223.7
127.5°	241.8	241.9	242.0	242.1	242.2	242.2	242.0	241.8	241.6	241.4	241.1
130°	252.5	252.6	252.8	252.9	253.0	252.9	252.7	252.5	252.2	251.9	251.7
132.5°	262.4	262.5	262.7	262.8	263.1	263.0	262.8	262.5	262.3	262.1	261.8
135°	277.4	277.6	277.8	278.0	278.1	278.1	278.0	277.8	277.6	277.4	277.2
137.5°	291.6	291.7	291.8	291.9	292.1	292.0	291.7	291.4	291.1	290.8	290.7
140°	300.1	300.2	300.3	300.5	300.6	300.6	300.2	300.0	299.8	299.5	299.4
142.5°	307.9	308.1	308.2	308.5	308.6	308.6	308.4	308.2	308.0	307.8	307.6
145°	320.0	320.0	320.0	320.0	320.0	319.9	319.8	319.6	319.6	319.4	319.2
147.5°	328.9	329.2	329.5	329.8	330.1	330.2	330.0	329.9	329.8	329.6	329.5
150°	335.6	335.8	336.0	336.2	336.4	336.4	336.3	336.2	336.0	335.9	335.8
152.5°	341.0	341.3	341.6	341.9	342.1	342.2	342.0	341.7	341.5	341.3	341.2
155°	348.5	348.9	349.3	349.7	350.0	350.1	349.7	349.4	349.1	348.8	348.7
157.5°	354.8	355.3	355.8	356.3	356.8	356.9	356.5	356.1	355.7	355.4	355.4
160°	358.9	359.3	359.7	360.2	360.6	360.7	360.3	359.9	359.5	359.2	359.3
162.5°	362.7	363.1	363.5	363.8	364.2	364.2	363.8	363.4	362.9	362.5	362.6
165°	367.3	367.7	368.1	368.6	369.0	369.0	368.5	368.0	367.5	367.0	367.0
167.5°	370.6	371.1	371.5	372.1	372.6	372.6	372.1	371.5	371.1	370.6	370.6
170°	372.6	373.1	373.6	374.1	374.5	374.5	374.1	373.6	373.1	372.6	372.6
172.5°	373.7	374.2	374.8	375.3	375.9	375.9	375.4	374.9	374.5	373.9	373.9
175°	375.4	375.9	376.4	376.9	377.4	377.4	377.0	376.5	376.1	375.7	375.6
177.5°	375.9	376.4	376.9	377.4	377.9	378.0	377.6	377.2	376.8	376.4	376.3
180°	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8



TEST NUMBER: P332000-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1147.2	1143.7	1140.3	1134.2	1129.0	1121.7	1119.5	1117.0	1109.2	1102.3	1097.1
5°	1217.2	1204.3	1185.4	1168.2	1154.1	1135.3	1124.5	1113.2	1097.0	1082.4	1070.6
7.5°	1290.5	1265.1	1235.8	1204.0	1174.6	1146.1	1123.1	1102.6	1080.0	1058.5	1041.8
10°	1348.8	1312.1	1271.1	1226.9	1189.2	1152.5	1121.8	1094.9	1065.7	1040.4	1019.4
12.5°	1415.2	1360.8	1304.3	1250.6	1206.0	1155.2	1117.9	1083.6	1050.7	1020.2	996.6
15°	1493.7	1424.7	1358.0	1284.0	1216.2	1152.5	1108.3	1065.2	1026.9	995.7	965.5
17.5°	1565.4	1487.2	1399.1	1309.3	1227.3	1151.9	1090.0	1041.2	993.4	955.1	925.0
20°	1605.9	1516.9	1417.2	1324.0	1233.4	1149.3	1081.4	1023.2	971.4	931.0	897.0
22.5°	1640.8	1536.8	1433.6	1333.9	1233.0	1142.4	1065.4	1005.5	949.4	909.8	873.7
25°	1677.0	1552.5	1449.1	1332.1	1219.4	1125.6	1039.3	971.4	915.4	869.0	831.8
27.5°	1708.1	1551.5	1428.6	1302.8	1198.0	1104.0	1011.9	939.1	879.6	829.2	791.5
30°	1728.8	1553.6	1407.5	1283.0	1177.3	1080.3	990.8	917.5	855.0	803.7	768.2
32.5°	1741.8	1552.3	1388.1	1255.4	1144.5	1058.8	968.0	892.1	827.8	777.4	743.1
35°	1749.3	1542.9	1354.7	1198.3	1091.6	1008.1	932.1	853.3	786.0	739.1	700.3
37.5°	1734.2	1522.9	1315.9	1143.4	1026.5	944.2	880.3	813.3	748.8	697.1	663.7
40°	1710.5	1510.0	1285.7	1104.5	981.7	902.4	848.0	782.2	718.6	669.6	638.3
42.5°	1665.2	1483.6	1252.5	1061.4	935.1	855.8	805.7	750.8	690.5	644.5	613.2
45°	1554.7	1426.4	1202.7	996.7	866.3	784.3	740.1	700.3	645.8	601.0	574.1
47.5°	1401.4	1340.2	1130.7	928.5	794.5	715.7	669.7	637.6	597.9	561.7	535.8
50°	1294.8	1269.6	1081.9	881.9	746.6	669.6	625.3	596.2	567.7	531.6	507.8
52.5°	1172.0	1187.6	1025.0	833.6	697.9	622.1	580.5	557.4	531.4	501.8	481.1
55°	998.9	1055.5	926.7	752.6	625.3	553.1	513.7	493.2	478.2	456.1	438.2
57.5°	836.9	908.9	820.4	669.0	554.1	491.7	454.0	431.7	422.0	410.4	396.4
60°	740.7	811.8	744.5	612.9	506.2	446.9	413.4	394.6	384.9	376.8	365.0
62.5°	654.9	726.9	670.3	556.0	459.1	404.2	375.1	356.6	349.1	344.9	334.8
65°	536.9	598.9	561.2	467.4	391.9	343.4	317.0	304.0	297.1	295.4	288.9
67.5°	437.0	484.2	456.7	387.7	328.3	286.4	264.0	252.9	247.6	247.0	242.2
70°	371.5	415.7	394.6	332.1	280.8	248.0	228.5	218.9	215.6	215.1	212.4
72.5°	320.5	351.3	334.6	282.5	242.9	213.0	198.8	188.7	185.0	185.8	183.9
75°	237.2	260.4	250.6	214.5	182.8	163.3	151.5	145.0	141.8	143.4	141.2
77.5°	170.6	185.4	176.6	151.6	132.0	118.0	109.2	105.2	102.3	102.2	101.2
80°	128.8	137.4	132.6	117.5	101.3	89.5	82.5	79.8	78.2	77.6	77.1
82.5°	91.7	99.1	93.4	83.0	72.0	64.9	60.9	57.4	56.2	56.5	55.9
85°	46.3	49.0	46.9	40.4	36.1	32.9	30.7	29.1	28.0	28.6	27.5
87.5°	17.0	17.3	15.8	13.9	12.9	11.5	11.4	10.4	9.7	9.8	9.5
90°	5.1	4.3	3.5	2.8	2.1	1.5	0.9	0.3	0.9	1.5	2.1
92.5°	5.9	5.3	4.8	4.5	4.7	4.8	5.1	5.2	5.1	4.8	4.7
95°	7.3	6.7	5.9	6.9	9.4	12.0	14.5	17.1	14.5	12.0	9.4
97.5°	18.0	22.4	26.9	29.7	30.9	32.0	33.2	34.3	33.2	32.0	30.9
100°	28.7	38.3	48.1	52.3	51.0	49.8	48.6	47.3	48.6	49.8	51.0
102.5°	39.6	50.2	60.8	65.7	64.8	63.8	63.0	62.1	63.0	63.8	64.8
105°	72.5	78.1	83.7	86.2	85.5	84.8	84.1	83.4	84.1	84.8	85.5
107.5°	110.6	109.7	108.8	108.1	107.6	107.0	106.5	105.9	106.5	107.0	107.6
110°	124.8	124.2	123.5	122.9	122.4	121.9	121.4	121.0	121.4	121.9	122.4





TEST NUMBER: P332000-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	139.0	138.3	137.6	137.0	136.6	136.2	135.7	135.2	135.7	136.2	136.6
115°	159.5	159.0	158.4	158.0	157.6	157.2	156.9	156.5	156.9	157.2	157.6
117.5°	179.8	179.5	179.3	178.9	178.4	177.9	177.5	177.1	177.5	177.9	178.4
120°	192.8	192.6	192.4	192.0	191.5	190.9	190.4	189.8	190.4	190.9	191.5
122.5°	205.4	205.2	204.9	204.6	204.1	203.7	203.3	202.8	203.3	203.7	204.1
125°	223.5	223.2	222.9	222.6	222.0	221.6	221.1	220.6	221.1	221.6	222.0
127.5°	240.8	240.5	240.2	239.8	239.3	238.8	238.4	237.8	238.4	238.8	239.3
130°	251.4	251.2	251.0	250.6	250.1	249.5	249.1	248.6	249.1	249.5	250.1
132.5°	261.7	261.4	261.2	260.9	260.4	259.9	259.4	258.9	259.4	259.9	260.4
135°	276.9	276.6	276.4	276.1	275.8	275.4	275.0	274.6	275.0	275.4	275.8
137.5°	290.5	290.4	290.3	289.9	289.5	289.0	288.5	288.0	288.5	289.0	289.5
140°	299.1	299.0	298.8	298.5	298.1	297.8	297.4	297.0	297.4	297.8	298.1
142.5°	307.4	307.3	307.0	306.8	306.4	306.0	305.7	305.3	305.7	306.0	306.4
145°	319.2	319.0	318.9	318.6	318.2	317.7	317.3	316.9	317.3	317.7	318.2
147.5°	329.4	329.3	329.2	328.9	328.7	328.4	328.1	327.8	328.1	328.4	328.7
150°	335.6	335.6	335.4	335.3	335.1	334.9	334.7	334.5	334.7	334.9	335.1
152.5°	341.1	341.0	341.0	340.9	340.8	340.7	340.6	340.6	340.6	340.7	340.8
155°	348.6	348.6	348.6	348.6	348.7	348.8	349.0	349.1	349.0	348.8	348.7
157.5°	355.5	355.5	355.6	355.6	355.6	355.7	355.7	355.7	355.7	355.7	355.6
160°	359.3	359.3	359.4	359.5	359.5	359.6	359.7	359.7	359.7	359.6	359.5
162.5°	362.7	362.7	362.7	362.9	363.1	363.2	363.4	363.5	363.4	363.2	363.1
165°	367.1	367.2	367.3	367.3	367.6	367.7	367.9	368.1	367.9	367.7	367.6
167.5°	370.6	370.6	370.6	370.7	371.0	371.2	371.5	371.7	371.5	371.2	371.0
170°	372.6	372.6	372.6	372.7	373.0	373.2	373.4	373.7	373.4	373.2	373.0
172.5°	373.8	373.8	373.8	373.8	374.1	374.5	374.8	375.0	374.8	374.5	374.1
175°	375.6	375.5	375.4	375.6	375.9	376.1	376.4	376.8	376.4	376.1	375.9
177.5°	376.2	376.2	376.1	376.2	376.5	376.8	377.0	377.2	377.0	376.8	376.5
180°	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8



TEST NUMBER: P332000-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1094.1	1091.1	1086.8	1080.3	1075.1	1066.9	1066.9	1068.3	1068.3	1067.8	1066.9
5°	1060.9	1052.8	1043.1	1031.8	1019.9	1008.1	1005.9	1001.6	998.4	996.2	993.5
7.5°	1025.9	1011.5	997.4	981.5	967.1	955.1	946.8	939.9	935.5	930.7	927.3
10°	1002.1	984.4	967.7	950.9	932.6	918.1	908.9	902.4	897.5	893.3	891.1
12.5°	974.1	953.7	935.3	919.4	899.4	884.4	875.7	872.7	867.0	857.9	853.1
15°	933.1	914.3	892.2	867.9	858.2	839.9	829.7	824.8	821.6	814.5	812.4
17.5°	898.1	873.4	848.6	830.5	812.5	797.6	791.9	785.8	781.6	775.9	774.1
20°	870.1	848.0	825.3	805.9	787.0	770.9	766.0	761.7	757.4	754.7	752.6
22.5°	841.6	819.5	800.7	782.6	762.5	751.9	746.6	741.9	738.9	737.0	734.8
25°	801.6	782.2	761.2	745.0	728.8	721.8	718.6	715.9	713.8	711.1	710.5
27.5°	765.8	744.7	727.6	712.6	700.9	695.1	692.0	690.6	691.1	692.1	692.7
30°	739.1	719.7	705.7	692.7	681.9	676.5	676.0	676.0	678.2	678.7	679.8
32.5°	714.5	698.5	684.5	672.0	663.8	660.1	662.2	662.2	663.9	665.4	667.3
35°	678.7	664.6	653.9	643.1	636.1	637.7	638.8	639.8	642.5	645.8	648.0
37.5°	644.5	632.3	621.2	612.7	609.5	612.4	615.0	617.3	620.4	622.8	625.0
40°	620.0	610.8	600.0	592.5	593.5	595.2	597.3	600.0	602.7	604.3	606.5
42.5°	597.1	587.5	579.3	573.1	574.6	576.6	577.9	579.3	582.4	585.3	586.6
45°	562.3	554.7	547.2	543.4	544.5	545.6	546.6	548.3	551.0	553.1	553.7
47.5°	523.1	517.8	512.8	509.1	510.8	510.4	511.8	515.2	516.1	517.4	520.4
50°	498.1	493.2	487.4	486.2	486.2	486.2	486.8	491.1	491.1	493.2	495.4
52.5°	470.5	467.4	463.6	461.7	460.8	460.8	463.0	465.2	466.1	469.1	471.3
55°	429.7	426.4	423.2	421.5	420.5	421.5	425.9	426.9	429.7	431.3	432.8
57.5°	387.1	384.6	382.0	381.1	380.9	382.3	384.7	387.9	388.6	393.6	396.0
60°	359.0	355.2	353.1	353.1	352.0	356.9	355.8	361.2	362.3	365.5	369.2
62.5°	330.1	325.0	324.2	324.2	325.7	327.1	328.6	331.0	333.8	337.9	340.8
65°	283.5	280.8	284.6	284.1	283.0	286.2	286.2	288.9	292.2	296.0	301.9
67.5°	239.5	238.1	238.4	238.4	240.0	241.9	243.4	245.7	249.6	253.6	257.5
70°	209.7	211.4	208.7	210.8	212.4	212.9	214.0	217.2	221.6	224.3	228.5
72.5°	180.8	180.7	181.0	181.9	183.5	184.5	185.5	189.3	193.9	196.2	199.7
75°	139.1	138.6	140.1	140.1	142.8	143.9	145.0	146.6	150.9	154.2	156.9
77.5°	101.6	102.2	101.9	103.7	103.0	103.1	106.5	108.1	108.6	114.9	116.4
80°	76.5	77.6	78.2	78.7	79.2	78.2	81.9	83.6	83.6	87.3	90.0
82.5°	55.0	55.6	57.0	57.6	57.7	58.8	59.1	60.3	61.6	63.2	66.7
85°	27.5	29.1	29.6	29.1	29.6	28.6	30.2	30.7	31.3	31.3	31.3
87.5°	9.2	9.7	9.5	10.1	9.8	10.4	10.5	9.7	9.7	11.0	9.3
90°	2.8	3.5	4.3	5.1	5.9	6.7	7.0	7.2	7.4	7.7	7.9
92.5°	4.5	4.8	5.3	5.9	6.6	7.1	7.5	8.0	8.4	8.8	9.0
95°	6.9	5.9	6.7	7.3	8.0	8.7	9.1	9.6	10.0	10.5	10.6
97.5°	29.7	26.9	22.4	18.0	13.5	9.0	9.5	10.0	10.5	11.0	11.2
100°	52.3	48.1	38.3	28.7	18.9	9.3	9.7	10.2	10.7	11.2	11.5
102.5°	65.7	60.8	50.2	39.6	29.0	18.5	16.9	15.4	13.8	12.3	11.6
105°	86.2	83.7	78.1	72.5	66.9	61.3	50.3	39.3	28.3	17.3	11.8
107.5°	108.1	108.8	109.7	110.6	111.5	112.3	104.3	96.3	88.2	80.1	71.9
110°	122.9	123.5	124.2	124.8	125.6	126.3	124.2	122.2	120.1	118.0	112.6



TEST NUMBER: P332000-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	137.0	137.6	138.3	139.0	139.7	140.4	140.4	140.5	140.5	140.5	139.6
115°	158.0	158.4	159.0	159.5	160.1	160.7	161.3	161.9	162.6	163.2	163.6
117.5°	178.9	179.3	179.5	179.8	180.1	180.4	180.9	181.4	181.9	182.4	182.7
120°	192.0	192.4	192.6	192.8	193.0	193.1	193.7	194.2	194.6	195.1	195.4
122.5°	204.6	204.9	205.2	205.4	205.7	205.9	206.3	206.6	207.0	207.3	207.5
125°	222.6	222.9	223.2	223.5	223.7	223.9	224.1	224.2	224.3	224.4	224.6
127.5°	239.8	240.2	240.5	240.8	241.1	241.4	241.6	241.8	242.0	242.2	242.2
130°	250.6	251.0	251.2	251.4	251.7	251.9	252.2	252.5	252.7	252.9	253.0
132.5°	260.9	261.2	261.4	261.7	261.8	262.1	262.3	262.5	262.8	263.0	263.1
135°	276.1	276.4	276.6	276.9	277.2	277.4	277.6	277.8	278.0	278.1	278.1
137.5°	289.9	290.3	290.4	290.5	290.7	290.8	291.1	291.4	291.7	292.0	292.1
140°	298.5	298.8	299.0	299.1	299.4	299.5	299.8	300.0	300.2	300.6	300.6
142.5°	306.8	307.0	307.3	307.4	307.6	307.8	308.0	308.2	308.4	308.6	308.6
145°	318.6	318.9	319.0	319.2	319.2	319.4	319.6	319.6	319.8	319.9	320.0
147.5°	328.9	329.2	329.3	329.4	329.5	329.6	329.8	329.9	330.0	330.2	330.1
150°	335.3	335.4	335.6	335.6	335.8	335.9	336.0	336.2	336.3	336.4	336.4
152.5°	340.9	341.0	341.0	341.1	341.2	341.3	341.5	341.7	342.0	342.2	342.1
155°	348.6	348.6	348.6	348.6	348.7	348.8	349.1	349.4	349.7	350.1	350.0
157.5°	355.6	355.6	355.5	355.5	355.4	355.4	355.7	356.1	356.5	356.9	356.8
160°	359.5	359.4	359.3	359.3	359.3	359.2	359.5	359.9	360.3	360.7	360.6
162.5°	362.9	362.7	362.7	362.7	362.6	362.5	362.9	363.4	363.8	364.2	364.2
165°	367.3	367.3	367.2	367.1	367.0	367.0	367.5	368.0	368.5	369.0	369.0
167.5°	370.7	370.6	370.6	370.6	370.6	370.6	371.1	371.5	372.1	372.6	372.6
170°	372.7	372.6	372.6	372.6	372.6	372.6	373.1	373.6	374.1	374.5	374.5
172.5°	373.8	373.8	373.8	373.8	373.9	373.9	374.5	374.9	375.4	375.9	375.9
175°	375.6	375.4	375.5	375.6	375.6	375.7	376.1	376.5	377.0	377.4	377.4
177.5°	376.2	376.1	376.2	376.2	376.3	376.4	376.8	377.2	377.6	378.0	377.9
180°	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8



TEST NUMBER: P332000-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1063.9	1063.5	1066.5	1064.4	1066.5	1063.5	1063.9	1066.9	1067.8	1068.3	1068.3
5°	990.3	991.9	986.5	986.5	986.5	991.9	990.3	993.5	996.2	998.4	1001.6
7.5°	924.7	922.3	922.6	919.6	922.6	922.3	924.7	927.3	930.7	935.5	939.9
10°	884.6	881.4	880.3	880.8	880.3	881.4	884.6	891.1	893.3	897.5	902.4
12.5°	851.4	850.8	843.7	843.8	843.7	850.8	851.4	853.1	857.9	867.0	872.7
15°	812.4	802.2	801.1	804.3	801.1	802.2	812.4	812.4	814.5	821.6	824.8
17.5°	773.2	767.9	768.2	766.6	768.2	767.9	773.2	774.1	775.9	781.6	785.8
20°	752.6	749.3	748.8	745.0	748.8	749.3	752.6	752.6	754.7	757.4	761.7
22.5°	733.6	732.5	732.8	728.6	732.8	732.5	733.6	734.8	737.0	738.9	741.9
25°	710.0	712.6	710.5	710.5	710.5	712.6	710.0	710.5	711.1	713.8	715.9
27.5°	694.0	693.9	692.8	692.8	692.8	693.9	694.0	692.7	692.1	691.1	690.6
30°	681.9	681.4	682.5	682.5	682.5	681.4	681.9	679.8	678.7	678.2	676.0
32.5°	669.9	670.6	670.8	671.2	670.8	670.6	669.9	667.3	665.4	663.9	662.2
35°	651.2	651.7	653.4	652.3	653.4	651.7	651.2	648.0	645.8	642.5	639.8
37.5°	626.0	628.4	627.9	628.8	627.9	628.4	626.0	625.0	622.8	620.4	617.3
40°	607.0	608.6	608.1	608.1	608.1	608.6	607.0	606.5	604.3	602.7	600.0
42.5°	587.6	588.7	587.4	586.5	587.4	588.7	587.6	586.6	585.3	582.4	579.3
45°	555.8	554.7	556.3	554.1	556.3	554.7	555.8	553.7	553.1	551.0	548.3
47.5°	520.2	521.3	521.7	523.3	521.7	521.3	520.2	520.4	517.4	516.1	515.2
50°	496.5	499.7	499.7	499.2	499.7	499.7	496.5	495.4	493.2	491.1	491.1
52.5°	473.2	474.7	476.9	476.7	476.9	474.7	473.2	471.3	469.1	466.1	465.2
55°	437.2	438.2	439.3	439.9	439.3	438.2	437.2	432.8	431.3	429.7	426.9
57.5°	399.9	399.4	402.0	402.8	402.0	399.4	399.9	396.0	393.6	388.6	387.9
60°	373.6	373.6	377.9	379.5	377.9	373.6	373.6	369.2	365.5	362.3	361.2
62.5°	345.5	347.3	351.6	349.4	351.6	347.3	345.5	340.8	337.9	333.8	331.0
65°	304.6	308.9	308.3	310.5	308.3	308.9	304.6	301.9	296.0	292.2	288.9
67.5°	261.7	264.4	268.3	268.7	268.3	264.4	261.7	257.5	253.6	249.6	245.7
70°	232.9	235.6	237.7	239.3	237.7	235.6	232.9	228.5	224.3	221.6	217.2
72.5°	204.9	206.3	211.4	209.1	211.4	206.3	204.9	199.7	196.2	193.9	189.3
75°	160.7	164.4	167.6	166.0	167.6	164.4	160.7	156.9	154.2	150.9	146.6
77.5°	118.8	122.6	124.1	122.7	124.1	122.6	118.8	116.4	114.9	108.6	108.1
80°	93.8	93.2	96.5	95.9	96.5	93.2	93.8	90.0	87.3	83.6	83.6
82.5°	68.8	68.3	69.8	70.1	69.8	68.3	68.8	66.7	63.2	61.6	60.3
85°	33.4	35.0	32.9	32.3	32.9	35.0	33.4	31.3	31.3	31.3	30.7
87.5°	9.3	9.4	9.0	8.6	9.0	9.4	9.3	9.3	11.0	9.7	9.7
90°	8.0	8.2	8.2	8.4	8.2	8.2	8.0	7.9	7.7	7.4	7.2
92.5°	9.0	9.1	9.2	9.3	9.2	9.1	9.0	9.0	8.8	8.4	8.0
95°	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.5	10.0	9.6
97.5°	11.3	11.4	11.5	11.6	11.5	11.4	11.3	11.2	11.0	10.5	10.0
100°	11.6	11.6	11.7	11.7	11.7	11.6	11.6	11.5	11.2	10.7	10.2
102.5°	11.6	11.7	11.9	12.0	11.9	11.7	11.6	11.6	12.3	13.8	15.4
105°	12.0	12.0	12.2	12.3	12.2	12.0	12.0	11.8	17.3	28.3	39.3
107.5°	63.6	55.3	47.0	38.7	47.0	55.3	63.6	71.9	80.1	88.2	96.3
110°	103.7	94.7	85.9	77.0	85.9	94.7	103.7	112.6	118.0	120.1	122.2



TEST NUMBER: P332000-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	137.7	135.9	134.0	132.1	134.0	135.9	137.7	139.6	140.5	140.5	140.5
115°	163.8	164.1	164.4	164.6	164.4	164.1	163.8	163.6	163.2	162.6	161.9
117.5°	182.7	182.8	182.8	182.8	182.8	182.8	182.7	182.7	182.4	181.9	181.4
120°	195.4	195.4	195.4	195.4	195.4	195.4	195.4	195.4	195.1	194.6	194.2
122.5°	207.6	207.6	207.6	207.7	207.6	207.6	207.6	207.5	207.3	207.0	206.6
125°	224.7	224.8	225.0	225.1	225.0	224.8	224.7	224.6	224.4	224.3	224.2
127.5°	242.1	242.0	241.9	241.8	241.9	242.0	242.1	242.2	242.2	242.0	241.8
130°	252.9	252.8	252.6	252.5	252.6	252.8	252.9	253.0	252.9	252.7	252.5
132.5°	262.8	262.7	262.5	262.4	262.5	262.7	262.8	263.1	263.0	262.8	262.5
135°	278.0	277.8	277.6	277.4	277.6	277.8	278.0	278.1	278.1	278.0	277.8
137.5°	291.9	291.8	291.7	291.6	291.7	291.8	291.9	292.1	292.0	291.7	291.4
140°	300.5	300.3	300.2	300.1	300.2	300.3	300.5	300.6	300.6	300.2	300.0
142.5°	308.5	308.2	308.1	307.9	308.1	308.2	308.5	308.6	308.6	308.4	308.2
145°	320.0	320.0	320.0	320.0	320.0	320.0	320.0	320.0	319.9	319.8	319.6
147.5°	329.8	329.5	329.2	328.9	329.2	329.5	329.8	330.1	330.2	330.0	329.9
150°	336.2	336.0	335.8	335.6	335.8	336.0	336.2	336.4	336.4	336.3	336.2
152.5°	341.9	341.6	341.3	341.0	341.3	341.6	341.9	342.1	342.2	342.0	341.7
155°	349.7	349.3	348.9	348.5	348.9	349.3	349.7	350.0	350.1	349.7	349.4
157.5°	356.3	355.8	355.3	354.8	355.3	355.8	356.3	356.8	356.9	356.5	356.1
160°	360.2	359.7	359.3	358.9	359.3	359.7	360.2	360.6	360.7	360.3	359.9
162.5°	363.8	363.5	363.1	362.7	363.1	363.5	363.8	364.2	364.2	363.8	363.4
165°	368.6	368.1	367.7	367.3	367.7	368.1	368.6	369.0	369.0	368.5	368.0
167.5°	372.1	371.5	371.1	370.6	371.1	371.5	372.1	372.6	372.6	372.1	371.5
170°	374.1	373.6	373.1	372.6	373.1	373.6	374.1	374.5	374.5	374.1	373.6
172.5°	375.3	374.8	374.2	373.7	374.2	374.8	375.3	375.9	375.9	375.4	374.9
175°	376.9	376.4	375.9	375.4	375.9	376.4	376.9	377.4	377.4	377.0	376.5
177.5°	377.4	376.9	376.4	375.9	376.4	376.9	377.4	377.9	378.0	377.6	377.2
180°	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8



TEST NUMBER: P332000-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1066.9	1066.9	1075.1	1080.3	1086.8	1091.1	1094.1	1097.1	1102.3	1109.2	1117.0
5°	1005.9	1008.1	1019.9	1031.8	1043.1	1052.8	1060.9	1070.6	1082.4	1097.0	1113.2
7.5°	946.8	955.1	967.1	981.5	997.4	1011.5	1025.9	1041.8	1058.5	1080.0	1102.6
10°	908.9	918.1	932.6	950.9	967.7	984.4	1002.1	1019.4	1040.4	1065.7	1094.9
12.5°	875.7	884.4	899.4	919.4	935.3	953.7	974.1	996.6	1020.2	1050.7	1083.6
15°	829.7	839.9	858.2	867.9	892.2	914.3	933.1	965.5	995.7	1026.9	1065.2
17.5°	791.9	797.6	812.5	830.5	848.6	873.4	898.1	925.0	955.1	993.4	1041.2
20°	766.0	770.9	787.0	805.9	825.3	848.0	870.1	897.0	931.0	971.4	1023.2
22.5°	746.6	751.9	762.5	782.6	800.7	819.5	841.6	873.7	909.8	949.4	1005.5
25°	718.6	721.8	728.8	745.0	761.2	782.2	801.6	831.8	869.0	915.4	971.4
27.5°	692.0	695.1	700.9	712.6	727.6	744.7	765.8	791.5	829.2	879.6	939.1
30°	676.0	676.5	681.9	692.7	705.7	719.7	739.1	768.2	803.7	855.0	917.5
32.5°	662.2	660.1	663.8	672.0	684.5	698.5	714.5	743.1	777.4	827.8	892.1
35°	638.8	637.7	636.1	643.1	653.9	664.6	678.7	700.3	739.1	786.0	853.3
37.5°	615.0	612.4	609.5	612.7	621.2	632.3	644.5	663.7	697.1	748.8	813.3
40°	597.3	595.2	593.5	592.5	600.0	610.8	620.0	638.3	669.6	718.6	782.2
42.5°	577.9	576.6	574.6	573.1	579.3	587.5	597.1	613.2	644.5	690.5	750.8
45°	546.6	545.6	544.5	543.4	547.2	554.7	562.3	574.1	601.0	645.8	700.3
47.5°	511.8	510.4	510.8	509.1	512.8	517.8	523.1	535.8	561.7	597.9	637.6
50°	486.8	486.2	486.2	486.2	487.4	493.2	498.1	507.8	531.6	567.7	596.2
52.5°	463.0	460.8	460.8	461.7	463.6	467.4	470.5	481.1	501.8	531.4	557.4
55°	425.9	421.5	420.5	421.5	423.2	426.4	429.7	438.2	456.1	478.2	493.2
57.5°	384.7	382.3	380.9	381.1	382.0	384.6	387.1	396.4	410.4	422.0	431.7
60°	355.8	356.9	352.0	353.1	353.1	355.2	359.0	365.0	376.8	384.9	394.6
62.5°	328.6	327.1	325.7	324.2	324.2	325.0	330.1	334.8	344.9	349.1	356.6
65°	286.2	286.2	283.0	284.1	284.6	280.8	283.5	288.9	295.4	297.1	304.0
67.5°	243.4	241.9	240.0	238.4	238.4	238.1	239.5	242.2	247.0	247.6	252.9
70°	214.0	212.9	212.4	210.8	208.7	211.4	209.7	212.4	215.1	215.6	218.9
72.5°	185.5	184.5	183.5	181.9	181.0	180.7	180.8	183.9	185.8	185.0	188.7
75°	145.0	143.9	142.8	140.1	140.1	138.6	139.1	141.2	143.4	141.8	145.0
77.5°	106.5	103.1	103.0	103.7	101.9	102.2	101.6	101.2	102.2	102.3	105.2
80°	81.9	78.2	79.2	78.7	78.2	77.6	76.5	77.1	77.6	78.2	79.8
82.5°	59.1	58.8	57.7	57.6	57.0	55.6	55.0	55.9	56.5	56.2	57.4
85°	30.2	28.6	29.6	29.1	29.6	29.1	27.5	27.5	28.6	28.0	29.1
87.5°	10.5	10.4	9.8	10.1	9.5	9.7	9.2	9.5	9.8	9.7	10.4
90°	7.0	6.7	5.9	5.1	4.3	3.5	2.8	2.1	1.5	0.9	0.3
92.5°	7.5	7.1	6.6	5.9	5.3	4.8	4.5	4.7	4.8	5.1	5.2
95°	9.1	8.7	8.0	7.3	6.7	5.9	6.9	9.4	12.0	14.5	17.1
97.5°	9.5	9.0	13.5	18.0	22.4	26.9	29.7	30.9	32.0	33.2	34.3
100°	9.7	9.3	18.9	28.7	38.3	48.1	52.3	51.0	49.8	48.6	47.3
102.5°	16.9	18.5	29.0	39.6	50.2	60.8	65.7	64.8	63.8	63.0	62.1
105°	50.3	61.3	66.9	72.5	78.1	83.7	86.2	85.5	84.8	84.1	83.4
107.5°	104.3	112.3	111.5	110.6	109.7	108.8	108.1	107.6	107.0	106.5	105.9
110°	124.2	126.3	125.6	124.8	124.2	123.5	122.9	122.4	121.9	121.4	121.0



TEST NUMBER: P332000-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	140.4	140.4	139.7	139.0	138.3	137.6	137.0	136.6	136.2	135.7	135.2
115°	161.3	160.7	160.1	159.5	159.0	158.4	158.0	157.6	157.2	156.9	156.5
117.5°	180.9	180.4	180.1	179.8	179.5	179.3	178.9	178.4	177.9	177.5	177.1
120°	193.7	193.1	193.0	192.8	192.6	192.4	192.0	191.5	190.9	190.4	189.8
122.5°	206.3	205.9	205.7	205.4	205.2	204.9	204.6	204.1	203.7	203.3	202.8
125°	224.1	223.9	223.7	223.5	223.2	222.9	222.6	222.0	221.6	221.1	220.6
127.5°	241.6	241.4	241.1	240.8	240.5	240.2	239.8	239.3	238.8	238.4	237.8
130°	252.2	251.9	251.7	251.4	251.2	251.0	250.6	250.1	249.5	249.1	248.6
132.5°	262.3	262.1	261.8	261.7	261.4	261.2	260.9	260.4	259.9	259.4	258.9
135°	277.6	277.4	277.2	276.9	276.6	276.4	276.1	275.8	275.4	275.0	274.6
137.5°	291.1	290.8	290.7	290.5	290.4	290.3	289.9	289.5	289.0	288.5	288.0
140°	299.8	299.5	299.4	299.1	299.0	298.8	298.5	298.1	297.8	297.4	297.0
142.5°	308.0	307.8	307.6	307.4	307.3	307.0	306.8	306.4	306.0	305.7	305.3
145°	319.6	319.4	319.2	319.2	319.0	318.9	318.6	318.2	317.7	317.3	316.9
147.5°	329.8	329.6	329.5	329.4	329.3	329.2	328.9	328.7	328.4	328.1	327.8
150°	336.0	335.9	335.8	335.6	335.6	335.4	335.3	335.1	334.9	334.7	334.5
152.5°	341.5	341.3	341.2	341.1	341.0	341.0	340.9	340.8	340.7	340.6	340.6
155°	349.1	348.8	348.7	348.6	348.6	348.6	348.6	348.7	348.8	349.0	349.1
157.5°	355.7	355.4	355.4	355.5	355.5	355.6	355.6	355.6	355.7	355.7	355.7
160°	359.5	359.2	359.3	359.3	359.3	359.4	359.5	359.5	359.6	359.7	359.7
162.5°	362.9	362.5	362.6	362.7	362.7	362.7	362.9	363.1	363.2	363.4	363.5
165°	367.5	367.0	367.0	367.1	367.2	367.3	367.3	367.6	367.7	367.9	368.1
167.5°	371.1	370.6	370.6	370.6	370.6	370.6	370.7	371.0	371.2	371.5	371.7
170°	373.1	372.6	372.6	372.6	372.6	372.6	372.7	373.0	373.2	373.4	373.7
172.5°	374.5	373.9	373.9	373.8	373.8	373.8	373.8	374.1	374.5	374.8	375.0
175°	376.1	375.7	375.6	375.6	375.5	375.4	375.6	375.9	376.1	376.4	376.8
177.5°	376.8	376.4	376.3	376.2	376.2	376.1	376.2	376.5	376.8	377.0	377.2
180°	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8



TEST NUMBER: P332000-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1119.5	1121.7	1129.0	1134.2	1140.3	1143.7	1147.2	1149.8	1153.2	1154.1	1166.6
5°	1124.5	1135.3	1154.1	1168.2	1185.4	1204.3	1217.2	1223.1	1238.8	1251.7	1277.6
7.5°	1123.1	1146.1	1174.6	1204.0	1235.8	1265.1	1290.5	1320.7	1342.2	1374.4	1406.2
10°	1121.8	1152.5	1189.2	1226.9	1271.1	1312.1	1348.8	1389.7	1423.7	1468.5	1506.7
12.5°	1117.9	1155.2	1206.0	1250.6	1304.3	1360.8	1415.2	1467.8	1497.9	1572.4	1607.7
15°	1108.3	1152.5	1216.2	1284.0	1358.0	1424.7	1493.7	1548.8	1637.7	1703.0	1744.5
17.5°	1090.0	1151.9	1227.3	1309.3	1399.1	1487.2	1565.4	1648.8	1743.1	1822.1	1906.1
20°	1081.4	1149.3	1233.4	1324.0	1417.2	1516.9	1605.9	1706.2	1809.1	1886.7	1994.6
22.5°	1065.4	1142.4	1233.0	1333.9	1433.6	1536.8	1640.8	1741.9	1860.9	1967.9	2070.4
25°	1039.3	1125.6	1219.4	1332.1	1449.1	1552.5	1677.0	1811.3	1935.3	2072.7	2175.2
27.5°	1011.9	1104.0	1198.0	1302.8	1428.6	1551.5	1708.1	1859.8	2011.4	2130.1	2205.9
30°	990.8	1080.3	1177.3	1283.0	1407.5	1553.6	1728.8	1894.3	2042.0	2143.9	2186.5
32.5°	968.0	1058.8	1144.5	1255.4	1388.1	1552.3	1741.8	1914.5	2043.8	2111.6	2103.2
35°	932.1	1008.1	1091.6	1198.3	1354.7	1542.9	1749.3	1916.4	1995.7	1981.1	1871.1
37.5°	880.3	944.2	1026.5	1143.4	1315.9	1522.9	1734.2	1859.6	1854.4	1735.9	1576.6
40°	848.0	902.4	981.7	1104.5	1285.7	1510.0	1710.5	1791.9	1722.9	1557.4	1366.5
42.5°	805.7	855.8	935.1	1061.4	1252.5	1483.6	1665.2	1688.8	1553.8	1363.3	1188.4
45°	740.1	784.3	866.3	996.7	1202.7	1426.4	1554.7	1497.0	1315.3	1118.6	985.4
47.5°	669.7	715.7	794.5	928.5	1130.7	1340.2	1401.4	1278.7	1092.2	932.6	810.3
50°	625.3	669.6	746.6	881.9	1081.9	1269.6	1294.8	1136.4	965.0	824.8	724.5
52.5°	580.5	622.1	697.9	833.6	1025.0	1187.6	1172.0	1010.4	852.8	733.3	654.7
55°	513.7	553.1	625.3	752.6	926.7	1055.5	998.9	844.7	714.3	621.5	561.7
57.5°	454.0	491.7	554.1	669.0	820.4	908.9	836.9	706.9	603.2	531.9	487.2
60°	413.4	446.9	506.2	612.9	744.5	811.8	740.7	625.9	538.5	481.4	441.5
62.5°	375.1	404.2	459.1	556.0	670.3	726.9	654.9	557.7	483.3	432.7	398.8
65°	317.0	343.4	391.9	467.4	561.2	598.9	536.9	458.2	400.5	362.8	340.2
67.5°	264.0	286.4	328.3	387.7	456.7	484.2	437.0	376.0	332.6	302.3	284.3
70°	228.5	248.0	280.8	332.1	394.6	415.7	371.5	321.3	289.5	265.2	248.5
72.5°	198.8	213.0	242.9	282.5	334.6	351.3	320.5	276.5	246.8	228.5	215.3
75°	151.5	163.3	182.8	214.5	250.6	260.4	237.2	209.7	189.7	176.8	166.6
77.5°	109.2	118.0	132.0	151.6	176.6	185.4	170.6	152.3	137.8	129.0	123.3
80°	82.5	89.5	101.3	117.5	132.6	137.4	128.8	114.8	104.6	99.7	94.9
82.5°	60.9	64.9	72.0	83.0	93.4	99.1	91.7	83.3	77.9	73.4	71.6
85°	30.7	32.9	36.1	40.4	46.9	49.0	46.3	44.2	41.0	38.3	38.3
87.5°	11.4	11.5	12.9	13.9	15.8	17.3	17.0	16.2	16.0	15.6	15.2
90°	0.9	1.5	2.1	2.8	3.5	4.3	5.1	5.9	6.7	7.0	7.2
92.5°	5.1	4.8	4.7	4.5	4.8	5.3	5.9	6.6	7.1	7.5	8.0
95°	14.5	12.0	9.4	6.9	5.9	6.7	7.3	8.0	8.7	9.1	9.6
97.5°	33.2	32.0	30.9	29.7	26.9	22.4	18.0	13.5	9.0	9.5	10.0
100°	48.6	49.8	51.0	52.3	48.1	38.3	28.7	18.9	9.3	9.7	10.2
102.5°	63.0	63.8	64.8	65.7	60.8	50.2	39.6	29.0	18.5	16.9	15.4
105°	84.1	84.8	85.5	86.2	83.7	78.1	72.5	66.9	61.3	50.3	39.3
107.5°	106.5	107.0	107.6	108.1	108.8	109.7	110.6	111.5	112.3	104.3	96.3
110°	121.4	121.9	122.4	122.9	123.5	124.2	124.8	125.6	126.3	124.2	122.2





TEST NUMBER: P332000-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	135.7	136.2	136.6	137.0	137.6	138.3	139.0	139.7	140.4	140.4	140.5
115°	156.9	157.2	157.6	158.0	158.4	159.0	159.5	160.1	160.7	161.3	161.9
117.5°	177.5	177.9	178.4	178.9	179.3	179.5	179.8	180.1	180.4	180.9	181.4
120°	190.4	190.9	191.5	192.0	192.4	192.6	192.8	193.0	193.1	193.7	194.2
122.5°	203.3	203.7	204.1	204.6	204.9	205.2	205.4	205.7	205.9	206.3	206.6
125°	221.1	221.6	222.0	222.6	222.9	223.2	223.5	223.7	223.9	224.1	224.2
127.5°	238.4	238.8	239.3	239.8	240.2	240.5	240.8	241.1	241.4	241.6	241.8
130°	249.1	249.5	250.1	250.6	251.0	251.2	251.4	251.7	251.9	252.2	252.5
132.5°	259.4	259.9	260.4	260.9	261.2	261.4	261.7	261.8	262.1	262.3	262.5
135°	275.0	275.4	275.8	276.1	276.4	276.6	276.9	277.2	277.4	277.6	277.8
137.5°	288.5	289.0	289.5	289.9	290.3	290.4	290.5	290.7	290.8	291.1	291.4
140°	297.4	297.8	298.1	298.5	298.8	299.0	299.1	299.4	299.5	299.8	300.0
142.5°	305.7	306.0	306.4	306.8	307.0	307.3	307.4	307.6	307.8	308.0	308.2
145°	317.3	317.7	318.2	318.6	318.9	319.0	319.2	319.2	319.4	319.6	319.6
147.5°	328.1	328.4	328.7	328.9	329.2	329.3	329.4	329.5	329.6	329.8	329.9
150°	334.7	334.9	335.1	335.3	335.4	335.6	335.6	335.8	335.9	336.0	336.2
152.5°	340.6	340.7	340.8	340.9	341.0	341.0	341.1	341.2	341.3	341.5	341.7
155°	349.0	348.8	348.7	348.6	348.6	348.6	348.6	348.7	348.8	349.1	349.4
157.5°	355.7	355.7	355.6	355.6	355.6	355.5	355.5	355.4	355.4	355.7	356.1
160°	359.7	359.6	359.5	359.5	359.4	359.3	359.3	359.3	359.2	359.5	359.9
162.5°	363.4	363.2	363.1	362.9	362.7	362.7	362.7	362.6	362.5	362.9	363.4
165°	367.9	367.7	367.6	367.3	367.3	367.2	367.1	367.0	367.0	367.5	368.0
167.5°	371.5	371.2	371.0	370.7	370.6	370.6	370.6	370.6	370.6	371.1	371.5
170°	373.4	373.2	373.0	372.7	372.6	372.6	372.6	372.6	372.6	373.1	373.6
172.5°	374.8	374.5	374.1	373.8	373.8	373.8	373.8	373.9	373.9	374.5	374.9
175°	376.4	376.1	375.9	375.6	375.4	375.5	375.6	375.6	375.7	376.1	376.5
177.5°	377.0	376.8	376.5	376.2	376.1	376.2	376.2	376.3	376.4	376.8	377.2
180°	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8



TEST NUMBER: P332000-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1170.8	1171.3	1176.1	1179.5	1177.7	1180.0	1180.7
5°	1279.2	1298.6	1308.8	1316.4	1316.9	1317.5	1321.8
7.5°	1432.8	1453.7	1468.9	1491.9	1498.8	1506.7	1504.4
10°	1545.0	1575.7	1602.1	1616.1	1631.3	1653.4	1635.5
12.5°	1649.8	1704.2	1744.5	1766.2	1780.4	1784.9	1776.2
15°	1822.6	1893.8	1932.1	1930.9	1979.5	2000.5	1967.6
17.5°	1981.1	2046.8	2099.4	2126.3	2166.8	2175.7	2171.6
20°	2078.1	2149.8	2190.8	2237.1	2258.2	2277.0	2280.3
22.5°	2161.8	2226.2	2270.2	2308.7	2326.3	2335.3	2340.7
25°	2247.9	2298.6	2325.1	2338.5	2343.4	2342.2	2335.3
27.5°	2242.0	2245.9	2216.8	2188.2	2162.7	2133.9	2123.9
30°	2183.8	2138.5	2057.6	2011.8	1944.4	1891.1	1912.6
32.5°	2030.7	1940.5	1849.7	1749.6	1666.7	1643.1	1619.4
35°	1733.1	1574.6	1481.9	1374.1	1330.9	1287.9	1258.2
37.5°	1402.2	1279.5	1169.6	1099.1	1055.8	1028.6	1013.9
40°	1212.4	1101.8	1011.3	954.2	921.3	890.6	886.2
42.5°	1061.0	958.2	890.1	844.6	813.0	799.9	790.5
45°	869.0	797.3	751.5	719.1	698.1	690.0	679.2
47.5°	735.5	684.8	650.5	628.4	612.6	606.6	605.7
50°	660.9	618.9	593.5	576.2	563.9	561.7	553.1
52.5°	604.8	568.4	548.7	533.6	524.7	518.6	516.0
55°	525.1	500.8	483.0	474.4	467.4	461.4	461.4
57.5°	459.4	439.1	427.4	420.0	417.9	413.7	411.0
60°	418.8	401.6	392.4	386.0	381.7	382.2	377.3
62.5°	379.2	368.0	359.3	352.8	347.6	347.7	348.0
65°	322.9	314.3	307.8	305.6	302.5	298.7	299.8
67.5°	273.6	265.5	260.5	256.8	255.7	253.7	256.8
70°	238.3	232.3	228.5	225.3	224.3	224.8	227.5
72.5°	205.9	201.7	199.2	197.7	195.4	195.4	197.3
75°	161.7	158.5	156.3	154.7	154.2	154.2	154.2
77.5°	118.8	118.0	117.1	114.7	114.8	115.5	115.6
80°	93.8	92.2	91.7	90.5	89.0	87.9	90.5
82.5°	70.1	68.4	67.9	67.7	65.2	65.0	67.3
85°	37.7	36.1	36.7	36.1	36.1	35.6	35.6
87.5°	14.9	14.5	14.1	14.6	14.1	13.7	14.7
90°	7.4	7.7	7.9	8.0	8.2	8.2	8.4
92.5°	8.4	8.8	9.0	9.0	9.1	9.2	9.3
95°	10.0	10.5	10.6	10.6	10.6	10.6	10.6
97.5°	10.5	11.0	11.2	11.3	11.4	11.5	11.6
100°	10.7	11.2	11.5	11.6	11.6	11.7	11.7
102.5°	13.8	12.3	11.6	11.6	11.7	11.9	12.0
105°	28.3	17.3	11.8	12.0	12.0	12.2	12.3
107.5°	88.2	80.1	71.9	63.6	55.3	47.0	38.7
110°	120.1	118.0	112.6	103.7	94.7	85.9	77.0



TEST NUMBER: P332000-927

CATALOG NUMBER: S123DIP-S1000D365U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	140.5	140.5	139.6	137.7	135.9	134.0	132.1
115°	162.6	163.2	163.6	163.8	164.1	164.4	164.6
117.5°	181.9	182.4	182.7	182.7	182.8	182.8	182.8
120°	194.6	195.1	195.4	195.4	195.4	195.4	195.4
122.5°	207.0	207.3	207.5	207.6	207.6	207.6	207.7
125°	224.3	224.4	224.6	224.7	224.8	225.0	225.1
127.5°	242.0	242.2	242.2	242.1	242.0	241.9	241.8
130°	252.7	252.9	253.0	252.9	252.8	252.6	252.5
132.5°	262.8	263.0	263.1	262.8	262.7	262.5	262.4
135°	278.0	278.1	278.1	278.0	277.8	277.6	277.4
137.5°	291.7	292.0	292.1	291.9	291.8	291.7	291.6
140°	300.2	300.6	300.6	300.5	300.3	300.2	300.1
142.5°	308.4	308.6	308.6	308.5	308.2	308.1	307.9
145°	319.8	319.9	320.0	320.0	320.0	320.0	320.0
147.5°	330.0	330.2	330.1	329.8	329.5	329.2	328.9
150°	336.3	336.4	336.4	336.2	336.0	335.8	335.6
152.5°	342.0	342.2	342.1	341.9	341.6	341.3	341.0
155°	349.7	350.1	350.0	349.7	349.3	348.9	348.5
157.5°	356.5	356.9	356.8	356.3	355.8	355.3	354.8
160°	360.3	360.7	360.6	360.2	359.7	359.3	358.9
162.5°	363.8	364.2	364.2	363.8	363.5	363.1	362.7
165°	368.5	369.0	369.0	368.6	368.1	367.7	367.3
167.5°	372.1	372.6	372.6	372.1	371.5	371.1	370.6
170°	374.1	374.5	374.5	374.1	373.6	373.1	372.6
172.5°	375.4	375.9	375.9	375.3	374.8	374.2	373.7
175°	377.0	377.4	377.4	376.9	376.4	375.9	375.4
177.5°	377.6	378.0	377.9	377.4	376.9	376.4	375.9
180°	376.8	376.8	376.8	376.8	376.8	376.8	376.8

(END OF REPORT)