

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331618-930

Luminaire Tested: **S122RDIP-S290D330U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331618-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S290D330U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1910.2 lumens
Efficiency: N/A
Efficacy: 94.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331618-930

CATALOG NUMBER: S122RDIP-S290D330U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331618-930

CATALOG NUMBER: S122RDIP-S290D330U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	45	44	44	38
2	89	81	76	71	81	75	70	66	62	59	56	51	49	46	41	39	37	32
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	36	34	32	28
4	74	64	56	51	68	59	52	47	50	45	41	41	37	34	33	30	28	24
5	68	57	49	44	62	53	46	41	45	39	35	37	33	30	30	27	25	21
6	63	51	44	38	58	48	41	36	40	35	31	33	29	26	27	24	22	19
7	58	46	39	33	53	43	36	31	37	31	27	31	27	24	25	22	20	17
8	54	42	35	30	50	39	33	28	33	28	24	28	24	21	23	20	18	15
9	51	39	31	26	46	36	29	25	31	26	22	26	22	19	21	18	16	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6608	6608	6608
5°	6634	6525	6561
10°	6583	6419	6365
15°	6506	6228	6048
20°	6402	5957	5658
25°	6296	5649	5279
30°	6145	5330	4793
35°	6000	4987	4366
40°	5855	4628	3872
45°	5683	4229	3425
50°	5506	3823	2987
55°	5326	3386	2567
60°	5118	2929	2131
65°	4883	2460	1937
70°	4598	2030	1780
75°	4255	1847	1666
80°	3756	1655	1516
85°	2946	1297	1297



TEST NUMBER: P331618-930

CATALOG NUMBER: S122RDIP-S290D330U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	2.0
10°-20°	105.2	5.5
20°-30°	147.7	7.7
30°-40°	161.1	8.4
40°-50°	148.1	7.8
50°-60°	116.3	6.1
60°-70°	75.8	4.0
70°-80°	39.1	2.0
80°-90°	11.0	0.6
90°-100°	12.1	0.6
100°-110°	44.6	2.3
110°-120°	119.1	6.2
120°-130°	196.6	10.3
130°-140°	209.1	10.9
140°-150°	194.4	10.2
150°-160°	156.3	8.2
160°-170°	100.7	5.3
170°-180°	34.7	1.8
0°-30°	291.2	15.2
0°-40°	452.3	23.7
0°-60°	716.7	37.5
0°-90°	842.6	44.1
90°-120°	175.8	9.2
90°-150°	776.0	40.6
90°-180°	1068.0	55.9
0°-180°	1910.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	409	407	403	406	405	39
15°	389	385	373	366	362	110
25°	353	341	317	302	296	162
35°	304	285	253	230	222	190
45°	249	223	185	160	150	192
55°	189	160	120	99	91	169
65°	128	98	64	52	51	127
75°	68	43	30	27	27	72
85°	16	8	7	7	7	19
90°	0	3	5	7	7	1
95°	17	9	10	12	11	21
105°	80	84	16	19	20	86
115°	152	156	163	46	22	149
125°	214	218	223	225	225	191
135°	265	269	272	274	274	205
145°	308	308	312	314	312	192
155°	339	337	340	341	339	156
165°	357	356	356	358	356	101
175°	365	363	364	365	363	35
180°	364	364	364	364	364	



TEST NUMBER: P331618-930

CATALOG NUMBER: S122RDIP-S290D330U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	410.7	410.4	410.1	409.8	409.4	408.9	408.1	407.5	406.8	406.0	406.7
5°	409.3	408.9	408.5	408.1	407.6	406.8	405.8	404.7	403.7	402.6	403.3
7.5°	405.0	404.6	404.0	403.5	403.0	402.1	400.9	399.6	398.4	397.1	397.3
10°	401.5	400.9	400.3	399.7	399.2	398.0	396.4	394.8	393.1	391.5	391.3
12.5°	397.1	396.3	395.6	394.9	394.2	392.8	390.7	388.6	386.5	384.3	383.9
15°	389.2	388.3	387.4	386.5	385.6	383.8	381.0	378.2	375.4	372.6	371.0
17.5°	379.7	378.3	376.9	375.5	374.1	371.7	368.1	364.5	360.9	357.3	355.5
20°	372.6	371.0	369.3	367.6	366.0	363.1	359.0	354.9	350.8	346.7	344.6
22.5°	364.9	363.1	361.2	359.4	357.5	354.2	349.6	345.0	340.4	335.7	333.0
25°	353.4	350.7	348.1	345.4	342.8	338.8	333.3	327.9	322.5	317.1	313.6
27.5°	339.4	336.6	333.7	330.8	327.9	323.4	317.3	311.2	305.1	299.0	295.1
30°	329.6	326.5	323.3	320.2	317.2	312.3	305.7	299.1	292.5	285.9	281.8
32.5°	320.2	316.5	312.8	309.2	305.5	300.4	293.7	286.9	280.2	273.5	268.7
35°	304.4	300.3	296.0	291.9	287.6	281.9	274.7	267.4	260.2	253.0	247.8
37.5°	288.8	284.1	279.5	274.9	270.3	264.2	256.4	248.7	241.0	233.3	227.6
40°	277.8	272.9	267.9	262.9	258.0	251.6	243.6	235.6	227.6	219.6	213.8
42.5°	266.5	261.3	256.1	250.9	245.7	239.0	230.7	222.5	214.3	206.0	200.0
45°	248.9	243.4	237.8	232.4	226.8	219.7	211.1	202.4	193.8	185.2	179.4
47.5°	231.7	225.8	220.0	214.2	208.3	201.0	192.0	183.1	174.1	165.3	159.5
50°	219.2	213.4	207.6	201.7	195.9	188.4	179.4	170.3	161.3	152.2	146.5
52.5°	207.1	201.0	194.9	188.8	182.7	175.2	166.3	157.5	148.6	139.7	134.3
55°	189.2	182.9	176.4	170.0	163.5	156.0	147.0	138.1	129.2	120.3	115.4
57.5°	171.0	164.4	157.8	151.2	144.6	137.1	128.5	120.0	111.5	102.9	98.3
60°	158.5	152.0	145.4	138.8	132.2	124.7	116.2	107.7	99.2	90.7	86.5
62.5°	146.3	139.8	133.2	126.6	120.0	112.7	104.6	96.5	88.5	80.4	76.4
65°	127.8	121.1	114.5	107.8	101.1	94.1	86.7	79.2	71.8	64.4	61.6
67.5°	109.8	103.2	96.6	90.0	83.4	76.7	70.0	63.4	56.7	50.1	48.8
70°	97.4	91.0	84.5	78.2	71.7	65.7	60.0	54.3	48.7	43.0	42.2
72.5°	85.5	79.4	73.2	67.1	60.9	55.6	51.0	46.5	41.9	37.3	36.6
75°	68.2	62.4	56.7	50.9	45.1	40.8	38.0	35.2	32.4	29.6	29.0
77.5°	51.0	46.0	40.9	35.9	30.8	27.6	26.3	24.9	23.6	22.3	21.9
80°	40.4	36.2	32.0	27.8	23.6	21.0	20.2	19.4	18.6	17.8	17.4
82.5°	30.6	27.3	24.1	20.8	17.5	15.6	15.0	14.4	13.9	13.4	13.1
85°	15.9	14.2	12.5	10.8	9.0	8.0	7.7	7.5	7.3	7.0	7.0
87.5°	4.8	4.4	4.0	3.6	3.2	3.0	3.2	3.3	3.3	3.4	3.4
90°	0.2	0.9	1.5	2.2	2.9	3.4	3.8	4.3	4.8	5.3	5.5
92.5°	5.3	5.3	5.2	5.1	5.1	5.2	5.4	5.6	5.9	6.1	6.3
95°	17.1	15.2	13.3	11.3	9.4	8.6	9.0	9.5	9.9	10.3	10.6
97.5°	34.0	28.5	23.1	17.7	12.2	9.9	10.9	11.8	12.8	13.8	14.0
100°	46.6	38.6	30.6	22.6	14.6	11.0	12.1	13.0	14.0	15.0	15.5
102.5°	60.6	58.9	57.2	55.5	53.8	48.8	40.4	32.1	23.8	15.4	16.1
105°	80.1	81.9	83.6	85.4	87.2	80.1	64.1	48.1	32.0	16.1	16.7
107.5°	102.4	103.9	105.3	106.7	108.1	99.2	80.1	60.9	41.7	22.5	21.9
110°	116.8	118.0	119.3	120.5	121.7	113.8	96.9	80.0	63.0	46.1	40.3



TEST NUMBER: P331618-930

CATALOG NUMBER: S122RDIP-S290D330U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	130.3	131.3	132.5	133.5	134.6	133.1	128.9	124.7	120.5	116.3	95.0
115°	151.6	152.5	153.6	154.6	155.6	156.8	158.2	159.7	161.2	162.7	135.5
117.5°	170.6	171.7	172.8	174.0	175.0	176.1	177.2	178.1	179.1	180.2	173.6
120°	184.5	185.4	186.3	187.2	188.0	189.0	190.0	191.1	192.2	193.2	194.0
122.5°	196.3	197.3	198.2	199.1	200.1	201.1	202.2	203.3	204.6	205.7	206.1
125°	214.3	215.1	215.8	216.6	217.4	218.3	219.4	220.5	221.6	222.7	223.1
127.5°	230.6	231.5	232.3	233.2	234.0	234.8	235.6	236.5	237.3	238.1	238.7
130°	240.9	241.9	242.8	243.8	244.7	245.5	246.1	246.8	247.4	248.1	248.7
132.5°	251.5	252.3	253.1	253.9	254.7	255.4	256.0	256.7	257.3	258.0	258.5
135°	265.2	266.1	267.1	268.0	269.0	269.7	270.2	270.8	271.3	271.8	272.4
137.5°	279.1	279.7	280.4	281.0	281.7	282.3	282.9	283.5	284.1	284.7	285.3
140°	288.1	288.6	289.0	289.5	290.0	290.6	291.2	291.9	292.5	293.1	293.7
142.5°	295.7	296.1	296.5	297.0	297.4	298.0	298.7	299.5	300.2	300.9	301.4
145°	307.6	307.6	307.5	307.4	307.4	307.9	308.8	309.9	310.9	311.9	312.3
147.5°	318.0	317.8	317.6	317.3	317.2	317.5	318.5	319.5	320.5	321.5	321.7
150°	324.7	324.3	323.9	323.5	323.1	323.4	324.3	325.3	326.2	327.2	327.5
152.5°	330.4	330.0	329.5	329.1	328.6	328.8	329.7	330.6	331.5	332.4	332.7
155°	338.8	338.2	337.7	337.1	336.6	336.7	337.5	338.1	338.8	339.5	339.9
157.5°	345.2	344.8	344.3	343.9	343.4	343.5	344.0	344.5	345.0	345.4	345.8
160°	349.0	348.7	348.3	348.0	347.6	347.6	348.0	348.3	348.7	349.0	349.4
162.5°	352.4	352.0	351.7	351.3	351.0	351.0	351.2	351.6	351.9	352.2	352.6
165°	356.9	356.6	356.2	355.9	355.6	355.5	355.6	355.8	356.0	356.1	356.5
167.5°	360.3	360.0	359.6	359.2	358.9	358.8	359.0	359.1	359.3	359.5	359.9
170°	362.2	361.8	361.5	361.2	360.8	360.7	360.8	360.9	361.0	361.2	361.6
172.5°	363.5	363.1	362.7	362.4	362.1	361.9	362.1	362.2	362.3	362.4	362.8
175°	365.1	364.7	364.3	363.9	363.5	363.3	363.5	363.5	363.7	363.8	364.2
177.5°	365.3	365.0	364.7	364.4	364.0	363.9	363.9	364.0	364.0	364.1	364.4
180°	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3



TEST NUMBER: P331618-930

CATALOG NUMBER: S122RDIP-S290D330U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	407.3	408.0	408.6	408.9	408.8	408.6	408.5	408.4
5°	404.1	404.8	405.5	405.8	405.5	405.3	405.0	404.8
7.5°	397.5	397.8	397.9	397.9	397.5	397.0	396.6	396.2
10°	391.0	390.8	390.5	390.1	389.6	389.1	388.7	388.2
12.5°	383.5	383.0	382.6	382.0	381.2	380.3	379.5	378.7
15°	369.5	367.9	366.3	365.2	364.4	363.5	362.6	361.8
17.5°	353.6	351.7	349.9	348.3	346.8	345.4	344.0	342.6
20°	342.6	340.5	338.4	336.5	334.7	332.9	331.1	329.3
22.5°	330.4	327.8	325.1	323.1	321.7	320.4	319.0	317.7
25°	310.3	306.9	303.5	301.3	300.0	298.7	297.5	296.3
27.5°	291.1	287.1	283.2	280.3	278.3	276.4	274.4	272.5
30°	277.5	273.4	269.1	266.0	263.7	261.5	259.3	257.1
32.5°	263.9	259.1	254.3	250.9	248.8	246.7	244.6	242.6
35°	242.6	237.4	232.2	228.7	226.9	225.1	223.3	221.5
37.5°	221.8	216.1	210.4	206.5	204.5	202.4	200.3	198.2
40°	208.0	202.1	196.2	192.2	190.1	188.0	185.8	183.7
42.5°	193.9	187.8	181.8	177.8	175.7	173.7	171.5	169.5
45°	173.5	167.6	161.8	157.9	156.0	153.9	152.0	150.0
47.5°	153.6	147.8	142.0	138.2	136.4	134.6	132.8	131.0
50°	140.9	135.2	129.5	125.8	124.1	122.4	120.6	118.9
52.5°	128.8	123.4	117.9	114.3	112.8	111.1	109.5	107.9
55°	110.5	105.6	100.6	97.3	95.8	94.2	92.7	91.2
57.5°	93.8	89.3	84.8	81.9	80.6	79.2	77.9	76.6
60°	82.3	78.2	73.9	71.2	69.9	68.6	67.3	66.0
62.5°	72.4	68.4	64.4	62.0	61.1	60.4	59.6	58.8
65°	58.9	56.0	53.2	51.7	51.4	51.2	51.0	50.7
67.5°	47.5	46.2	44.9	44.2	43.9	43.6	43.4	43.1
70°	41.3	40.5	39.7	39.1	38.7	38.4	38.1	37.7
72.5°	36.0	35.2	34.6	34.2	33.9	33.8	33.5	33.3
75°	28.5	27.9	27.3	27.0	26.9	26.8	26.7	26.7
77.5°	21.5	21.2	20.9	20.7	20.5	20.4	20.3	20.1
80°	17.1	16.8	16.5	16.3	16.3	16.3	16.3	16.3
82.5°	13.0	12.7	12.6	12.5	12.5	12.5	12.5	12.5
85°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
87.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.5	3.5
90°	5.9	6.1	6.4	6.7	6.8	6.8	7.0	7.1
92.5°	6.4	6.6	6.7	6.8	6.9	7.0	7.0	7.1
95°	10.8	11.2	11.4	11.6	11.5	11.4	11.4	11.3
97.5°	14.3	14.4	14.7	14.8	14.9	15.0	15.1	15.2
100°	16.0	16.5	16.9	17.2	17.3	17.4	17.5	17.7
102.5°	16.6	17.3	17.9	18.3	18.4	18.6	18.8	18.9
105°	17.4	18.0	18.7	19.1	19.3	19.6	19.8	20.1
107.5°	21.2	20.5	19.9	19.6	19.9	20.1	20.4	20.6
110°	34.4	28.5	22.7	19.9	20.1	20.4	20.6	20.8



TEST NUMBER: P331618-930

CATALOG NUMBER: S122RDIP-S290D330U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	73.6	52.3	30.9	20.3	20.5	20.6	20.9	21.0
115°	108.4	81.3	54.1	38.5	34.2	30.1	25.8	21.6
117.5°	167.1	160.5	153.9	143.7	129.9	116.0	102.2	88.3
120°	194.6	195.3	196.0	192.4	184.5	176.6	168.7	160.8
122.5°	206.5	206.9	207.3	206.8	205.3	203.7	202.2	200.6
125°	223.6	224.0	224.4	224.7	224.9	225.0	225.2	225.3
127.5°	239.4	239.9	240.5	240.8	240.9	240.9	240.9	241.0
130°	249.3	250.0	250.6	250.9	250.9	250.8	250.8	250.7
132.5°	259.1	259.6	260.2	260.4	260.3	260.3	260.2	260.2
135°	273.0	273.5	274.1	274.3	274.3	274.1	274.0	273.9
137.5°	285.8	286.4	287.0	287.1	287.0	286.8	286.6	286.4
140°	294.2	294.7	295.2	295.4	295.1	294.8	294.5	294.2
142.5°	301.9	302.4	302.9	303.0	302.6	302.4	302.1	301.7
145°	312.7	313.1	313.5	313.6	313.2	313.0	312.7	312.3
147.5°	322.0	322.4	322.7	322.7	322.5	322.2	322.0	321.7
150°	327.8	328.2	328.6	328.6	328.3	328.0	327.7	327.4
152.5°	333.1	333.5	333.8	333.8	333.4	333.0	332.6	332.2
155°	340.2	340.6	341.0	340.9	340.4	340.0	339.5	339.0
157.5°	346.3	346.7	347.0	347.0	346.5	346.1	345.6	345.2
160°	349.8	350.1	350.4	350.4	350.0	349.6	349.2	348.8
162.5°	352.9	353.4	353.8	353.8	353.2	352.7	352.2	351.7
165°	356.9	357.3	357.8	357.8	357.3	356.9	356.5	356.1
167.5°	360.3	360.7	361.1	361.0	360.5	360.0	359.5	358.9
170°	362.0	362.4	362.8	362.7	362.2	361.7	361.2	360.6
172.5°	363.2	363.6	364.0	364.0	363.5	363.0	362.4	361.9
175°	364.6	365.0	365.4	365.3	364.8	364.2	363.5	363.0
177.5°	364.8	365.1	365.4	365.3	364.9	364.5	364.1	363.7
180°	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3

(END OF REPORT)