

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332016-927

Luminaire Tested: **S123DIP-S1000D585U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332016-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D585U927-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4858.2 lumens  
Efficiency: N/A  
Efficacy: 99.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332016-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332016-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	97	93	89	96	92	88	85	81	79	76	72	70	68	63	62	61	56
2	92	85	78	73	87	80	74	70	71	67	63	63	60	57	56	53	51	47
3	84	75	67	61	79	70	64	58	63	58	53	56	52	48	49	46	43	40
4	77	66	58	52	72	63	55	49	56	50	45	50	45	41	44	40	37	34
5	71	59	50	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30
6	65	53	45	39	61	50	43	37	45	39	34	41	35	31	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23	21
9	53	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	19
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13497	13497	13497
5°	13560	13374	13467
10°	13470	13258	13340
15°	13312	13108	13133
20°	13128	12893	12906
25°	12883	12638	12613
30°	12609	12356	12261
35°	12326	12056	11901
40°	12029	11726	11545
45°	11702	11423	11144
50°	11375	11050	10742
55°	10946	10663	10340
60°	10514	10213	9888
65°	10132	9722	9419
70°	9567	9161	8752
75°	8742	8430	8072
80°	7885	7550	7482
85°	6928	6657	6385



TEST NUMBER: P332016-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.1	2.4
10°-20°	333.5	6.9
20°-30°	492.7	10.1
30°-40°	575.5	11.8
40°-50°	578.6	11.9
50°-60°	508.2	10.5
60°-70°	378.6	7.8
70°-80°	215.7	4.4
80°-90°	63.6	1.3
90°-100°	37.5	0.8
100°-110°	112.2	2.3
110°-120°	190.8	3.9
120°-130°	250.9	5.2
130°-140°	282.0	5.8
140°-150°	277.2	5.7
150°-160°	233.4	4.8
160°-170°	155.4	3.2
170°-180°	54.4	1.1
0°-30°	944.3	19.4
0°-40°	1519.8	31.3
0°-60°	2606.6	53.7
0°-90°	3264.5	67.2
90°-120°	340.4	7.0
90°-150°	1150.6	23.7
90°-180°	1594.0	32.8
0°-180°	4858.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1254	1254	1254	1254	1254	
5°	1255	1249	1238	1248	1246	119
15°	1195	1190	1176	1184	1178	337
25°	1085	1078	1064	1065	1062	499
35°	938	931	918	911	906	587
45°	769	764	750	738	732	593
55°	583	582	568	557	551	522
65°	398	392	382	373	370	392
75°	210	206	203	197	194	225
85°	56	54	54	52	52	62
90°	0	5	11	13	14	5
95°	27	30	33	35	35	30
105°	102	103	107	107	108	109
115°	192	193	192	193	192	190
125°	281	282	282	280	278	251
135°	365	367	367	365	364	281
145°	442	443	445	444	442	276
155°	506	507	507	508	506	233
165°	552	550	550	553	550	155
175°	574	572	572	574	572	54
180°	575	575	575	575	575	



TEST NUMBER: P332016-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1258.2	1257.5	1256.7	1255.9	1255.2	1253.7	1251.6	1249.5	1247.4	1245.3	1247.2
5°	1255.0	1253.8	1252.6	1251.4	1250.2	1248.3	1245.7	1243.0	1240.4	1237.8	1240.2
7.5°	1242.7	1241.5	1240.3	1239.1	1237.9	1236.0	1233.3	1230.5	1227.8	1225.0	1227.2
10°	1232.4	1231.2	1229.9	1228.8	1227.6	1225.4	1222.3	1219.2	1216.1	1213.0	1215.1
12.5°	1218.5	1217.6	1216.6	1215.5	1214.6	1212.6	1209.7	1206.7	1203.8	1200.9	1202.5
15°	1194.6	1193.7	1192.7	1191.8	1190.8	1188.7	1185.7	1182.6	1179.4	1176.3	1178.2
17.5°	1166.8	1165.5	1164.3	1163.1	1161.8	1159.7	1156.5	1153.4	1150.3	1147.2	1148.5
20°	1146.1	1144.7	1143.3	1141.8	1140.3	1138.0	1135.0	1131.9	1128.8	1125.6	1126.6
22.5°	1122.8	1121.4	1120.0	1118.5	1117.1	1114.8	1111.7	1108.6	1105.5	1102.3	1103.1
25°	1084.7	1083.2	1081.8	1080.4	1078.9	1076.7	1073.5	1070.4	1067.3	1064.1	1064.4
27.5°	1043.9	1042.5	1041.1	1039.7	1038.3	1035.9	1032.6	1029.3	1025.9	1022.5	1022.7
30°	1014.5	1013.4	1012.2	1011.0	1009.8	1007.5	1004.2	1000.8	997.4	994.1	994.1
32.5°	985.2	983.7	982.1	980.5	978.9	976.8	974.2	971.7	969.1	966.5	965.1
35°	938.0	936.6	935.2	933.7	932.2	930.0	926.9	923.8	920.7	917.5	916.1
37.5°	889.7	887.9	886.1	884.2	882.4	880.0	876.8	873.6	870.4	867.3	865.5
40°	856.1	854.6	853.2	851.8	850.3	848.0	844.5	841.2	837.9	834.5	832.6
42.5°	822.4	820.8	819.2	817.5	815.9	813.4	810.1	806.8	803.4	800.0	798.1
45°	768.7	767.8	766.8	765.9	764.9	762.9	759.8	756.6	753.5	750.4	747.6
47.5°	715.5	714.1	712.7	711.3	710.0	707.7	704.9	702.0	699.0	696.1	693.2
50°	679.3	678.0	676.8	675.7	674.5	672.3	669.2	666.1	663.0	659.9	657.2
52.5°	641.3	640.5	639.7	638.9	638.0	636.0	632.7	629.4	626.1	622.7	620.5
55°	583.3	583.0	582.8	582.6	582.3	580.7	577.6	574.4	571.3	568.2	565.5
57.5°	528.1	527.3	526.5	525.7	524.8	523.2	520.7	518.2	515.7	513.3	510.9
60°	488.4	488.1	487.9	487.7	487.4	485.9	483.0	480.1	477.3	474.4	472.2
62.5°	453.0	452.4	451.8	451.1	450.6	448.9	445.9	443.1	440.2	437.3	435.1
65°	397.8	396.6	395.5	394.3	393.1	391.3	388.9	386.5	384.0	381.7	379.8
67.5°	339.5	338.3	337.3	336.3	335.2	333.7	331.9	330.1	328.3	326.5	324.8
70°	304.0	302.6	301.2	299.8	298.3	296.8	295.4	294.0	292.6	291.1	289.5
72.5°	267.0	265.9	264.8	263.8	262.8	261.4	259.8	258.2	256.5	254.8	253.4
75°	210.2	209.3	208.3	207.4	206.4	205.6	204.9	204.1	203.4	202.7	201.5
77.5°	160.0	159.5	158.9	158.4	157.9	157.2	156.4	155.5	154.6	153.8	153.0
80°	127.2	126.5	125.8	125.1	124.4	123.7	123.3	122.8	122.3	121.8	121.6
82.5°	95.3	95.1	95.1	94.9	94.7	94.6	94.5	94.4	94.3	94.3	93.8
85°	56.1	55.6	55.1	54.7	54.2	53.9	53.9	53.9	53.9	53.9	53.4
87.5°	22.5	22.2	21.8	21.4	21.0	20.8	20.9	21.0	21.1	21.2	21.1
90°	0.5	1.4	2.5	3.5	4.4	5.6	6.9	8.2	9.5	10.9	11.2
92.5°	10.9	11.6	12.3	13.0	13.7	14.4	15.1	15.8	16.6	17.3	17.7
95°	26.7	27.3	28.0	28.8	29.5	30.3	31.1	31.8	32.6	33.4	33.8
97.5°	47.4	47.8	48.4	49.0	49.4	50.0	50.5	51.2	51.7	52.4	52.8
100°	61.5	62.0	62.7	63.3	63.8	64.4	64.9	65.4	65.9	66.4	66.7
102.5°	77.7	78.1	78.4	78.8	79.1	79.7	80.3	81.0	81.7	82.3	82.6
105°	101.6	101.9	102.0	102.3	102.5	103.0	103.9	104.8	105.8	106.6	106.6
107.5°	129.5	129.6	129.8	129.8	130.0	130.2	130.6	130.9	131.3	131.7	132.0
110°	146.9	147.0	147.3	147.4	147.7	147.8	148.1	148.3	148.5	148.7	149.1



TEST NUMBER: P332016-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	164.9	165.0	165.2	165.2	165.4	165.5	165.6	165.6	165.6	165.6	166.1
115°	192.0	192.3	192.7	193.0	193.2	193.3	193.1	192.9	192.7	192.5	192.6
117.5°	219.4	219.5	219.8	219.9	220.1	220.1	219.8	219.6	219.4	219.0	219.0
120°	236.3	236.9	237.5	238.1	238.8	238.8	238.3	237.8	237.3	236.8	236.7
122.5°	254.1	254.4	254.9	255.3	255.8	255.9	255.6	255.4	255.1	254.8	254.6
125°	281.1	281.4	281.6	281.9	282.3	282.3	282.1	281.9	281.7	281.5	281.1
127.5°	306.0	306.7	307.3	307.9	308.6	308.8	308.6	308.3	308.1	307.9	307.4
130°	322.7	323.4	324.2	325.0	325.8	326.1	325.8	325.5	325.2	324.9	324.5
132.5°	339.2	340.1	340.9	341.7	342.5	342.8	342.5	342.3	342.1	341.9	341.4
135°	364.6	365.3	365.8	366.5	367.0	367.3	367.2	367.1	367.0	366.9	366.5
137.5°	388.2	388.6	389.1	389.7	390.1	390.5	390.8	391.0	391.3	391.6	391.2
140°	404.4	404.9	405.4	405.9	406.4	406.7	406.8	406.9	407.0	407.1	407.0
142.5°	419.2	419.7	420.3	420.7	421.2	421.6	421.8	421.9	422.2	422.3	422.2
145°	442.4	442.6	442.8	443.0	443.1	443.4	443.7	444.0	444.3	444.7	444.5
147.5°	462.6	463.0	463.3	463.7	464.1	464.4	464.7	464.9	465.2	465.5	465.5
150°	476.7	476.9	477.1	477.3	477.5	477.7	477.9	478.1	478.3	478.5	478.5
152.5°	488.3	488.5	488.9	489.1	489.4	489.6	489.7	489.8	490.0	490.0	490.2
155°	506.5	506.5	506.5	506.5	506.5	506.6	506.7	506.8	506.9	507.0	507.4
157.5°	522.0	522.0	521.8	521.7	521.6	521.6	521.7	521.7	521.8	521.9	522.3
160°	531.8	531.6	531.4	531.2	531.0	530.9	530.9	530.9	530.9	530.9	531.4
162.5°	540.5	540.2	540.0	539.6	539.4	539.3	539.4	539.5	539.6	539.6	540.1
165°	551.7	551.4	551.1	550.8	550.5	550.3	550.3	550.3	550.3	550.3	551.0
167.5°	560.6	560.2	559.8	559.4	559.0	558.9	559.0	559.0	559.1	559.2	559.8
170°	565.7	565.3	564.9	564.5	564.1	563.9	563.9	563.9	563.9	563.9	564.6
172.5°	569.7	569.3	568.9	568.5	568.1	567.9	567.9	567.9	567.9	567.9	568.5
175°	573.9	573.5	573.1	572.7	572.3	572.0	572.0	572.0	572.0	572.0	572.7
177.5°	575.6	575.3	575.0	574.6	574.3	574.1	574.1	574.1	574.1	574.1	574.6
180°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2



TEST NUMBER: P332016-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1249.1	1251.1	1253.0	1253.9	1253.6	1253.5	1253.2	1253.1
5°	1242.5	1244.9	1247.4	1248.3	1247.8	1247.4	1246.9	1246.4
7.5°	1229.4	1231.5	1233.7	1234.6	1234.3	1234.1	1233.7	1233.4
10°	1217.3	1219.4	1221.6	1222.4	1221.9	1221.5	1221.0	1220.5
12.5°	1204.0	1205.6	1207.2	1207.8	1207.6	1207.3	1207.0	1206.7
15°	1180.1	1182.0	1184.0	1184.2	1182.8	1181.3	1179.9	1178.5
17.5°	1149.9	1151.2	1152.5	1152.9	1152.5	1151.9	1151.4	1150.9
20°	1127.5	1128.5	1129.5	1129.6	1128.9	1128.1	1127.4	1126.7
22.5°	1103.9	1104.6	1105.4	1105.3	1104.5	1103.5	1102.6	1101.7
25°	1064.6	1064.9	1065.2	1064.9	1064.1	1063.4	1062.7	1062.0
27.5°	1022.9	1023.1	1023.3	1022.9	1022.1	1021.1	1020.3	1019.3
30°	994.1	994.1	994.1	993.2	991.6	989.9	988.2	986.5
32.5°	963.8	962.5	961.2	960.0	959.1	958.1	957.3	956.3
35°	914.7	913.2	911.8	910.5	909.3	908.1	906.9	905.7
37.5°	863.9	862.1	860.4	859.1	858.4	857.6	856.8	856.1
40°	830.7	828.8	826.9	825.4	824.4	823.5	822.5	821.6
42.5°	796.1	794.2	792.3	790.9	790.0	789.0	788.1	787.1
45°	744.7	741.8	738.9	736.9	735.7	734.5	733.3	732.1
47.5°	690.4	687.6	684.8	682.9	681.8	680.7	679.7	678.6
50°	654.6	652.0	649.3	647.3	645.9	644.4	642.9	641.5
52.5°	618.2	616.0	613.8	611.9	610.5	609.0	607.6	606.2
55°	562.9	560.3	557.7	555.7	554.5	553.3	552.2	551.0
57.5°	508.5	506.2	503.8	501.9	500.6	499.2	497.8	496.4
60°	470.1	467.9	465.8	464.1	462.9	461.7	460.5	459.3
62.5°	433.0	430.9	428.6	427.2	426.4	425.6	424.8	424.0
65°	377.9	375.9	374.0	372.7	372.0	371.3	370.5	369.8
67.5°	323.1	321.5	319.8	318.5	317.4	316.4	315.4	314.4
70°	287.7	286.1	284.4	283.0	281.8	280.6	279.4	278.1
72.5°	251.9	250.4	248.9	247.9	247.2	246.6	246.1	245.4
75°	200.3	199.1	197.9	196.9	196.2	195.5	194.8	194.1
77.5°	152.1	151.3	150.5	150.1	150.1	150.1	150.1	150.1
80°	121.4	121.1	120.9	120.7	120.7	120.7	120.7	120.7
82.5°	93.4	92.9	92.5	92.2	92.0	91.8	91.7	91.4
85°	52.9	52.4	52.0	51.7	51.7	51.7	51.7	51.7
87.5°	20.9	20.8	20.7	20.7	20.7	20.8	20.8	20.8
90°	11.6	12.0	12.4	12.8	13.0	13.2	13.4	13.5
92.5°	18.0	18.3	18.6	18.8	18.6	18.5	18.4	18.2
95°	34.2	34.6	35.0	35.3	35.3	35.3	35.3	35.3
97.5°	53.2	53.7	54.2	54.3	54.3	54.3	54.3	54.2
100°	67.0	67.3	67.7	67.9	68.0	68.3	68.4	68.7
102.5°	82.9	83.3	83.5	83.7	83.7	83.6	83.6	83.5
105°	106.6	106.6	106.6	106.7	106.9	107.1	107.3	107.6
107.5°	132.3	132.6	132.9	133.1	132.9	132.8	132.7	132.6
110°	149.5	149.9	150.3	150.4	150.2	150.0	149.8	149.6





TEST NUMBER: P332016-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	166.6	167.1	167.5	167.8	167.8	167.7	167.7	167.6
115°	192.7	192.8	192.9	192.9	192.8	192.7	192.6	192.5
117.5°	219.0	219.0	219.0	218.8	218.6	218.2	218.0	217.7
120°	236.5	236.5	236.4	236.2	236.0	235.8	235.6	235.4
122.5°	254.3	254.1	253.8	253.5	253.3	252.9	252.7	252.4
125°	280.7	280.3	279.9	279.5	279.1	278.7	278.3	277.9
127.5°	306.7	306.2	305.6	305.1	304.7	304.2	303.7	303.2
130°	324.1	323.7	323.3	322.7	322.0	321.3	320.6	319.9
132.5°	340.9	340.4	339.9	339.5	338.9	338.3	337.8	337.2
135°	366.1	365.7	365.3	365.0	364.8	364.6	364.4	364.2
137.5°	390.7	390.3	389.9	389.5	389.1	388.7	388.3	387.9
140°	406.9	406.8	406.7	406.3	405.6	404.9	404.2	403.5
142.5°	422.1	422.0	421.9	421.6	421.0	420.5	419.9	419.4
145°	444.4	444.3	444.3	443.9	443.5	443.1	442.8	442.4
147.5°	465.5	465.5	465.5	465.2	464.6	464.0	463.4	462.8
150°	478.5	478.5	478.5	478.2	477.6	477.0	476.4	475.8
152.5°	490.4	490.6	490.8	490.5	490.0	489.5	489.0	488.5
155°	507.8	508.2	508.6	508.4	507.7	507.0	506.4	505.6
157.5°	522.8	523.2	523.6	523.5	522.9	522.4	521.8	521.3
160°	532.0	532.4	532.9	533.0	532.6	532.2	531.8	531.4
162.5°	540.6	541.1	541.6	541.5	540.9	540.3	539.6	539.0
165°	551.6	552.2	552.8	552.7	552.0	551.3	550.6	549.9
167.5°	560.5	561.1	561.7	561.7	561.1	560.5	559.8	559.2
170°	565.3	566.0	566.7	566.7	566.0	565.3	564.6	563.9
172.5°	569.1	569.7	570.4	570.4	569.7	568.9	568.2	567.5
175°	573.2	573.9	574.5	574.4	573.7	573.0	572.3	571.6
177.5°	575.1	575.6	576.1	576.0	575.4	574.9	574.3	573.8
180°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2

(END OF REPORT)