

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332017-927

Luminaire Tested: **S123DIP-S1000D585U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332017-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D585U927-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4943.9 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332017-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332017-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	101	97	93	89	95	91	88	85	81	78	76	71	69	67	63	61	60	55
2	92	85	78	73	87	80	74	69	71	66	63	63	59	56	55	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	48	49	45	43	39
4	77	66	58	51	72	62	55	49	56	50	45	49	45	41	44	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	36	31	28	26
7	60	48	40	34	57	45	38	33	41	35	30	37	31	28	33	28	25	23
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	23	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20	18
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13497	13497	13497
5°	13560	13374	13467
10°	13470	13258	13340
15°	13312	13108	13133
20°	13128	12893	12906
25°	12883	12638	12613
30°	12609	12356	12261
35°	12326	12056	11901
40°	12029	11726	11545
45°	11702	11423	11144
50°	11375	11050	10742
55°	10946	10663	10340
60°	10514	10213	9888
65°	10132	9722	9419
70°	9567	9161	8752
75°	8742	8430	8072
80°	7885	7550	7482
85°	6928	6657	6385



TEST NUMBER: P332017-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.1	2.4
10°-20°	333.5	6.7
20°-30°	492.7	10.0
30°-40°	575.5	11.6
40°-50°	578.6	11.7
50°-60°	508.2	10.3
60°-70°	378.6	7.7
70°-80°	215.7	4.4
80°-90°	63.6	1.3
90°-100°	124.2	2.5
100°-110°	351.7	7.1
110°-120°	346.0	7.0
120°-130°	276.0	5.6
130°-140°	217.6	4.4
140°-150°	162.4	3.3
150°-160°	113.2	2.3
160°-170°	66.5	1.3
170°-180°	21.6	0.4
0°-30°	944.3	19.1
0°-40°	1519.8	30.7
0°-60°	2606.6	52.7
0°-90°	3264.6	66.0
90°-120°	822.0	16.6
90°-150°	1478.0	29.9
90°-180°	1679.0	34.0
0°-180°	4943.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1254	1254	1254	1254	1254	
5°	1255	1249	1238	1248	1246	119
15°	1195	1190	1176	1184	1178	337
25°	1085	1078	1064	1065	1062	499
35°	938	931	918	911	906	587
45°	769	764	750	738	732	593
55°	583	582	568	557	551	522
65°	398	392	382	373	370	392
75°	210	206	203	197	194	225
85°	56	54	54	52	52	62
90°	1	5	11	13	13	4
95°	15	50	268	78	52	17
105°	52	78	363	635	575	56
115°	93	115	278	609	699	92
125°	129	152	259	470	551	114
135°	151	180	256	387	447	117
145°	172	197	252	317	349	108
155°	196	211	244	278	290	90
165°	214	220	234	248	252	60
175°	223	223	225	228	227	21
180°	223	223	223	223	223	



TEST NUMBER: P332017-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1258.2	1257.5	1256.7	1255.9	1255.2	1253.7	1251.6	1249.5	1247.4	1245.3	1247.2
5°	1255.0	1253.8	1252.6	1251.4	1250.2	1248.3	1245.7	1243.0	1240.4	1237.8	1240.2
7.5°	1242.7	1241.5	1240.3	1239.1	1237.9	1236.0	1233.3	1230.5	1227.8	1225.0	1227.2
10°	1232.4	1231.2	1229.9	1228.8	1227.6	1225.4	1222.3	1219.2	1216.1	1213.0	1215.1
12.5°	1218.5	1217.6	1216.6	1215.5	1214.6	1212.6	1209.7	1206.7	1203.8	1200.9	1202.5
15°	1194.6	1193.7	1192.7	1191.8	1190.8	1188.7	1185.7	1182.6	1179.4	1176.3	1178.2
17.5°	1166.8	1165.5	1164.3	1163.1	1161.8	1159.7	1156.5	1153.4	1150.3	1147.2	1148.5
20°	1146.1	1144.7	1143.3	1141.8	1140.3	1138.0	1135.0	1131.9	1128.8	1125.6	1126.6
22.5°	1122.8	1121.4	1120.0	1118.5	1117.1	1114.8	1111.7	1108.6	1105.5	1102.3	1103.1
25°	1084.7	1083.2	1081.8	1080.4	1078.9	1076.7	1073.5	1070.4	1067.3	1064.1	1064.4
27.5°	1043.9	1042.5	1041.1	1039.7	1038.3	1035.9	1032.6	1029.3	1025.9	1022.5	1022.7
30°	1014.5	1013.4	1012.2	1011.0	1009.8	1007.5	1004.2	1000.8	997.4	994.1	994.1
32.5°	985.2	983.7	982.1	980.5	978.9	976.8	974.2	971.7	969.1	966.5	965.1
35°	938.0	936.6	935.2	933.7	932.2	930.0	926.9	923.8	920.7	917.5	916.1
37.5°	889.7	887.9	886.1	884.2	882.4	880.0	876.8	873.6	870.4	867.3	865.5
40°	856.1	854.6	853.2	851.8	850.3	848.0	844.5	841.2	837.9	834.5	832.6
42.5°	822.4	820.8	819.2	817.5	815.9	813.4	810.1	806.8	803.4	800.0	798.1
45°	768.7	767.8	766.8	765.9	764.9	762.9	759.8	756.6	753.5	750.4	747.6
47.5°	715.5	714.1	712.7	711.3	710.0	707.7	704.9	702.0	699.0	696.1	693.2
50°	679.3	678.0	676.8	675.7	674.5	672.3	669.2	666.1	663.0	659.9	657.2
52.5°	641.3	640.5	639.7	638.9	638.0	636.0	632.7	629.4	626.1	622.7	620.5
55°	583.3	583.0	582.8	582.6	582.3	580.7	577.6	574.4	571.3	568.2	565.5
57.5°	528.1	527.3	526.5	525.7	524.8	523.2	520.7	518.2	515.7	513.3	510.9
60°	488.4	488.1	487.9	487.7	487.4	485.9	483.0	480.1	477.3	474.4	472.2
62.5°	453.0	452.4	451.8	451.1	450.6	448.9	445.9	443.1	440.2	437.3	435.1
65°	397.8	396.6	395.5	394.3	393.1	391.3	388.9	386.5	384.0	381.7	379.8
67.5°	339.5	338.3	337.3	336.3	335.2	333.7	331.9	330.1	328.3	326.5	324.8
70°	304.0	302.6	301.2	299.8	298.3	296.8	295.4	294.0	292.6	291.1	289.5
72.5°	267.0	265.9	264.8	263.8	262.8	261.4	259.8	258.2	256.5	254.8	253.4
75°	210.2	209.3	208.3	207.4	206.4	205.6	204.9	204.1	203.4	202.7	201.5
77.5°	160.0	159.5	158.9	158.4	157.9	157.2	156.4	155.5	154.6	153.8	153.0
80°	127.2	126.5	125.8	125.1	124.4	123.7	123.3	122.8	122.3	121.8	121.6
82.5°	95.3	95.1	95.1	94.9	94.7	94.6	94.5	94.4	94.3	94.3	93.8
85°	56.1	55.6	55.1	54.7	54.2	53.9	53.9	53.9	53.9	53.9	53.4
87.5°	22.6	22.2	21.8	21.5	21.2	20.9	21.0	21.1	21.2	21.2	21.0
90°	0.9	1.8	2.7	4.0	5.0	5.9	7.2	8.6	9.9	11.3	10.9
92.5°	5.6	8.3	12.1	15.6	19.4	26.1	37.9	57.4	76.4	69.5	52.4
95°	15.4	16.7	21.7	29.4	41.1	58.7	97.1	164.5	238.6	267.9	217.3
97.5°	26.2	26.7	30.6	37.2	48.8	67.9	104.6	180.5	304.0	415.3	444.3
100°	33.4	33.9	37.1	43.4	54.2	71.9	103.5	170.3	289.1	427.9	516.9
102.5°	41.0	41.8	44.7	50.6	60.4	76.5	104.9	161.7	267.5	404.4	520.5
105°	52.4	53.8	56.5	61.9	70.5	84.5	108.9	155.4	240.8	363.3	493.0
107.5°	64.5	65.9	68.5	73.8	81.9	94.9	116.3	155.0	223.9	326.9	444.7
110°	73.2	74.5	76.8	81.8	89.4	102.1	122.5	156.8	217.3	306.3	414.3



TEST NUMBER: P332017-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	81.1	82.5	84.8	89.8	97.4	109.7	128.6	160.4	213.7	292.6	387.9
115°	92.6	94.4	97.1	101.6	109.3	121.5	138.7	166.3	212.4	277.9	356.1
117.5°	104.1	106.2	108.4	112.6	121.2	132.5	149.5	174.0	213.2	269.2	336.8
120°	112.1	113.4	115.7	120.2	128.8	140.1	156.3	179.8	214.6	265.2	326.7
122.5°	118.9	120.3	122.6	127.4	135.6	147.7	163.6	185.3	217.1	262.7	318.4
125°	128.8	129.7	132.4	137.4	145.9	158.1	174.0	193.8	220.9	259.4	307.7
127.5°	136.3	137.6	141.0	146.0	155.5	167.7	183.0	200.9	225.3	257.7	298.3
130°	141.0	142.4	146.4	151.8	161.3	173.5	188.4	205.6	228.1	256.7	293.3
132.5°	144.6	146.3	150.8	157.2	166.8	178.6	193.1	209.9	230.4	256.3	288.5
135°	150.9	152.7	157.7	164.5	174.0	186.2	200.2	215.6	233.6	255.7	282.4
137.5°	156.9	158.8	163.7	170.9	180.3	191.5	205.0	219.7	235.8	254.8	277.1
140°	160.9	163.1	167.6	174.8	183.9	195.2	208.3	221.9	237.2	254.4	273.8
142.5°	165.2	167.1	172.0	178.5	187.5	198.1	210.8	224.0	238.3	253.7	270.9
145°	172.1	173.5	177.6	184.3	192.0	202.4	214.2	226.4	239.0	252.5	267.0
147.5°	179.2	180.0	184.0	189.9	197.3	206.1	216.9	227.8	239.0	250.9	263.2
150°	183.9	184.3	188.0	193.8	200.2	208.3	218.7	228.1	239.0	249.4	260.7
152.5°	188.6	188.7	192.3	197.5	203.0	210.8	219.8	228.9	238.0	247.6	257.9
155°	195.7	195.7	198.4	202.9	207.9	214.2	221.9	229.1	236.8	244.5	253.5
157.5°	201.2	201.6	203.7	207.8	212.0	216.9	223.0	229.6	235.2	241.6	248.6
160°	205.6	205.6	207.4	211.0	214.2	218.7	224.1	229.6	234.5	239.5	245.3
162.5°	208.8	208.8	210.3	213.2	215.9	219.8	224.5	229.2	233.1	237.3	242.1
165°	213.7	213.3	214.2	216.4	218.2	221.4	225.0	228.1	230.9	234.1	237.7
167.5°	217.5	216.9	217.3	219.0	220.3	222.3	224.9	227.4	228.7	230.8	233.5
170°	219.6	218.7	219.1	220.5	221.4	222.3	224.6	226.4	227.3	228.6	230.9
172.5°	221.0	220.5	220.6	221.6	222.1	222.7	224.6	226.0	226.2	226.8	228.4
175°	222.8	222.3	221.9	222.8	222.8	223.2	224.1	225.0	224.6	224.6	225.5
177.5°	223.6	223.2	222.8	223.2	223.2	223.2	223.6	224.3	223.6	223.2	223.6
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P332017-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1249.1	1251.1	1253.0	1253.9	1253.6	1253.5	1253.2	1253.1
5°	1242.5	1244.9	1247.4	1248.3	1247.8	1247.4	1246.9	1246.4
7.5°	1229.4	1231.5	1233.7	1234.6	1234.3	1234.1	1233.7	1233.4
10°	1217.3	1219.4	1221.6	1222.4	1221.9	1221.5	1221.0	1220.5
12.5°	1204.0	1205.6	1207.2	1207.8	1207.6	1207.3	1207.0	1206.7
15°	1180.1	1182.0	1184.0	1184.2	1182.8	1181.3	1179.9	1178.5
17.5°	1149.9	1151.2	1152.5	1152.9	1152.5	1151.9	1151.4	1150.9
20°	1127.5	1128.5	1129.5	1129.6	1128.9	1128.1	1127.4	1126.7
22.5°	1103.9	1104.6	1105.4	1105.3	1104.5	1103.5	1102.6	1101.7
25°	1064.6	1064.9	1065.2	1064.9	1064.1	1063.4	1062.7	1062.0
27.5°	1022.9	1023.1	1023.3	1022.9	1022.1	1021.1	1020.3	1019.3
30°	994.1	994.1	994.1	993.2	991.6	989.9	988.2	986.5
32.5°	963.8	962.5	961.2	960.0	959.1	958.1	957.3	956.3
35°	914.7	913.2	911.8	910.5	909.3	908.1	906.9	905.7
37.5°	863.9	862.1	860.4	859.1	858.4	857.6	856.8	856.1
40°	830.7	828.8	826.9	825.4	824.4	823.5	822.5	821.6
42.5°	796.1	794.2	792.3	790.9	790.0	789.0	788.1	787.1
45°	744.7	741.8	738.9	736.9	735.7	734.5	733.3	732.1
47.5°	690.4	687.6	684.8	682.9	681.8	680.7	679.7	678.6
50°	654.6	652.0	649.3	647.3	645.9	644.4	642.9	641.5
52.5°	618.2	616.0	613.8	611.9	610.5	609.0	607.6	606.2
55°	562.9	560.3	557.7	555.7	554.5	553.3	552.2	551.0
57.5°	508.5	506.2	503.8	501.9	500.6	499.2	497.8	496.4
60°	470.1	467.9	465.8	464.1	462.9	461.7	460.5	459.3
62.5°	433.0	430.9	428.6	427.2	426.4	425.6	424.8	424.0
65°	377.9	375.9	374.0	372.7	372.0	371.3	370.5	369.8
67.5°	323.1	321.5	319.8	318.5	317.4	316.4	315.4	314.4
70°	287.7	286.1	284.4	283.0	281.8	280.6	279.4	278.1
72.5°	251.9	250.4	248.9	247.9	247.2	246.6	246.1	245.4
75°	200.3	199.1	197.9	196.9	196.2	195.5	194.8	194.1
77.5°	152.1	151.3	150.5	150.1	150.1	150.1	150.1	150.1
80°	121.4	121.1	120.9	120.7	120.7	120.7	120.7	120.7
82.5°	93.4	92.9	92.5	92.2	92.0	91.8	91.7	91.4
85°	52.9	52.4	52.0	51.7	51.7	51.7	51.7	51.7
87.5°	20.8	20.8	20.7	20.8	20.7	20.8	20.8	20.8
90°	11.3	11.7	12.2	13.1	12.7	13.1	13.5	13.1
92.5°	38.0	30.2	26.7	24.3	23.5	22.1	22.6	21.8
95°	162.6	110.3	86.3	70.0	61.5	57.4	54.2	52.4
97.5°	405.5	324.8	266.5	212.5	179.1	158.8	146.6	142.7
100°	532.7	496.1	443.2	379.1	333.4	300.5	282.9	283.3
102.5°	575.0	573.9	543.0	502.3	466.8	440.7	426.0	415.6
105°	587.4	632.6	641.2	629.4	608.6	591.4	577.0	574.7
107.5°	551.8	625.2	664.7	680.8	681.2	675.4	670.5	666.4
110°	517.8	600.9	657.9	689.5	702.2	705.8	704.9	703.9



TEST NUMBER: P332017-927

CATALOG NUMBER: S123DIP-S1000D585U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	484.2	569.1	633.0	673.6	696.7	708.0	711.4	711.5
115°	439.7	518.2	584.7	633.9	667.8	687.7	696.7	699.0
117.5°	407.3	475.2	534.9	584.9	620.2	642.9	656.0	659.0
120°	390.4	451.4	505.6	551.3	586.9	612.3	623.1	625.8
122.5°	377.0	432.2	482.4	524.8	556.6	579.3	591.3	594.7
125°	359.2	408.4	451.9	488.0	516.9	536.8	548.1	551.3
127.5°	343.6	387.6	426.7	459.6	485.4	502.3	512.5	515.5
130°	333.9	374.5	411.1	441.9	465.9	482.1	491.6	495.2
132.5°	324.9	362.3	396.3	425.6	448.1	464.4	472.8	475.3
135°	312.7	344.8	374.1	399.9	422.0	435.5	443.7	446.9
137.5°	301.6	327.9	353.2	375.5	394.1	407.8	414.7	416.8
140°	295.1	318.1	339.8	359.2	376.4	389.0	396.2	395.8
142.5°	288.9	308.7	327.5	344.4	359.0	370.3	376.8	376.3
145°	281.5	296.4	310.9	324.0	335.3	344.8	348.4	349.3
147.5°	275.4	287.2	299.0	308.2	316.8	323.2	326.7	327.0
150°	271.1	281.5	291.0	299.6	306.3	311.3	314.0	314.0
152.5°	267.1	276.1	284.5	291.6	296.9	301.6	303.2	303.2
155°	261.2	268.4	275.2	280.6	284.6	288.3	289.1	289.6
157.5°	254.8	260.9	266.2	270.4	273.9	276.6	277.3	277.3
160°	251.2	256.2	260.7	263.9	267.0	269.7	269.7	269.3
162.5°	246.9	251.1	255.3	258.1	260.2	262.5	262.5	262.1
165°	241.3	244.0	247.2	249.4	251.2	253.0	252.5	252.5
167.5°	236.4	238.4	240.3	241.9	242.7	244.0	243.5	243.5
170°	233.1	234.5	236.3	237.2	237.7	238.6	238.1	238.1
172.5°	230.3	231.2	232.7	233.2	233.3	234.2	233.5	233.1
175°	226.4	226.8	227.8	227.8	227.8	228.1	227.8	227.3
177.5°	223.9	224.3	224.7	224.7	224.3	224.7	223.9	223.9
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2

(END OF REPORT)