

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331638-930

Luminaire Tested: **S122RDIP-S290D925U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331638-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S290D925U930-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3789.9 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331638-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331638-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	22
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26	19
2	84	77	71	66	74	68	64	59	52	49	47	38	36	34	24	23	22	16
3	76	68	61	55	68	60	54	50	46	42	39	34	31	29	22	20	19	14
4	70	60	52	47	62	53	47	42	41	37	34	30	27	25	20	18	17	12
5	64	53	46	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11
6	59	48	40	35	52	43	36	31	33	29	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	29	24	27	23	19	20	17	15	13	12	10	8
9	47	35	28	23	42	32	26	21	25	20	17	19	16	13	12	11	9	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6608	6608	6608
5°	6634	6525	6561
10°	6583	6419	6365
15°	6506	6228	6048
20°	6402	5957	5658
25°	6296	5649	5279
30°	6145	5330	4793
35°	6000	4987	4366
40°	5855	4628	3872
45°	5683	4229	3425
50°	5506	3823	2987
55°	5326	3386	2567
60°	5118	2929	2131
65°	4883	2460	1937
70°	4598	2030	1780
75°	4255	1847	1666
80°	3756	1655	1516
85°	2946	1297	1297



TEST NUMBER: P331638-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	1.0
10°-20°	105.2	2.8
20°-30°	147.7	3.9
30°-40°	161.1	4.2
40°-50°	148.1	3.9
50°-60°	116.3	3.1
60°-70°	75.8	2.0
70°-80°	39.1	1.0
80°-90°	13.9	0.4
90°-100°	169.2	4.5
100°-110°	574.1	15.1
110°-120°	609.9	16.1
120°-130°	502.1	13.2
130°-140°	403.2	10.6
140°-150°	304.7	8.0
150°-160°	214.1	5.6
160°-170°	126.0	3.3
170°-180°	41.0	1.1
0°-30°	291.2	7.7
0°-40°	452.3	11.9
0°-60°	716.7	18.9
0°-90°	845.5	22.3
90°-120°	1353.2	35.7
90°-150°	2563.1	67.6
90°-180°	2944.0	77.7
0°-180°	3789.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	409	407	403	406	405	39
15°	389	385	373	366	362	110
25°	353	341	317	302	296	162
35°	304	285	253	230	222	190
45°	249	223	185	160	150	192
55°	189	160	120	99	91	169
65°	128	98	64	52	51	127
75°	68	43	30	27	27	72
85°	16	8	7	7	7	19
90°	1	11	28	26	27	2
95°	28	70	319	120	93	30
105°	99	150	603	1078	917	106
115°	175	221	504	1041	1207	173
125°	244	289	485	843	979	217
135°	286	342	479	709	811	221
145°	327	376	477	592	648	205
155°	372	402	463	524	544	171
165°	405	417	443	470	478	114
175°	422	423	426	432	430	40
180°	423	423	423	423	423	



TEST NUMBER: P331638-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	410.7	410.4	410.1	409.8	409.4	408.9	408.1	407.5	406.8	406.0	406.7
5°	409.3	408.9	408.5	408.1	407.6	406.8	405.8	404.7	403.7	402.6	403.3
7.5°	405.0	404.6	404.0	403.5	403.0	402.1	400.9	399.6	398.4	397.1	397.3
10°	401.5	400.9	400.3	399.7	399.2	398.0	396.4	394.8	393.1	391.5	391.3
12.5°	397.1	396.3	395.6	394.9	394.2	392.8	390.7	388.6	386.5	384.3	383.9
15°	389.2	388.3	387.4	386.5	385.6	383.8	381.0	378.2	375.4	372.6	371.0
17.5°	379.7	378.3	376.9	375.5	374.1	371.7	368.1	364.5	360.9	357.3	355.5
20°	372.6	371.0	369.3	367.6	366.0	363.1	359.0	354.9	350.8	346.7	344.6
22.5°	364.9	363.1	361.2	359.4	357.5	354.2	349.6	345.0	340.4	335.7	333.0
25°	353.4	350.7	348.1	345.4	342.8	338.8	333.3	327.9	322.5	317.1	313.6
27.5°	339.4	336.6	333.7	330.8	327.9	323.4	317.3	311.2	305.1	299.0	295.1
30°	329.6	326.5	323.3	320.2	317.2	312.3	305.7	299.1	292.5	285.9	281.8
32.5°	320.2	316.5	312.8	309.2	305.5	300.4	293.7	286.9	280.2	273.5	268.7
35°	304.4	300.3	296.0	291.9	287.6	281.9	274.7	267.4	260.2	253.0	247.8
37.5°	288.8	284.1	279.5	274.9	270.3	264.2	256.4	248.7	241.0	233.3	227.6
40°	277.8	272.9	267.9	262.9	258.0	251.6	243.6	235.6	227.6	219.6	213.8
42.5°	266.5	261.3	256.1	250.9	245.7	239.0	230.7	222.5	214.3	206.0	200.0
45°	248.9	243.4	237.8	232.4	226.8	219.7	211.1	202.4	193.8	185.2	179.4
47.5°	231.7	225.8	220.0	214.2	208.3	201.0	192.0	183.1	174.1	165.3	159.5
50°	219.2	213.4	207.6	201.7	195.9	188.4	179.4	170.3	161.3	152.2	146.5
52.5°	207.1	201.0	194.9	188.8	182.7	175.2	166.3	157.5	148.6	139.7	134.3
55°	189.2	182.9	176.4	170.0	163.5	156.0	147.0	138.1	129.2	120.3	115.4
57.5°	171.0	164.4	157.8	151.2	144.6	137.1	128.5	120.0	111.5	102.9	98.3
60°	158.5	152.0	145.4	138.8	132.2	124.7	116.2	107.7	99.2	90.7	86.5
62.5°	146.3	139.8	133.2	126.6	120.0	112.7	104.6	96.5	88.5	80.4	76.4
65°	127.8	121.1	114.5	107.8	101.1	94.1	86.7	79.2	71.8	64.4	61.6
67.5°	109.8	103.2	96.6	90.0	83.4	76.7	70.0	63.4	56.7	50.1	48.8
70°	97.4	91.0	84.5	78.2	71.7	65.7	60.0	54.3	48.7	43.0	42.2
72.5°	85.5	79.4	73.2	67.1	60.9	55.6	51.0	46.5	41.9	37.3	36.6
75°	68.2	62.4	56.7	50.9	45.1	40.8	38.0	35.2	32.4	29.6	29.0
77.5°	51.0	46.0	40.9	35.9	30.8	27.6	26.3	24.9	23.6	22.3	21.9
80°	40.4	36.2	32.0	27.8	23.6	21.0	20.2	19.4	18.6	17.8	17.4
82.5°	30.6	27.3	24.1	20.8	17.5	15.6	15.0	14.4	13.9	13.4	13.1
85°	15.9	14.2	12.5	10.8	9.0	8.0	7.7	7.5	7.3	7.0	7.0
87.5°	4.9	4.9	5.0	4.8	4.6	4.8	5.6	6.8	7.7	7.9	7.7
90°	0.8	3.3	6.5	8.2	9.8	12.2	16.3	21.9	26.8	27.6	26.8
92.5°	9.9	14.3	20.2	23.7	29.3	36.9	55.4	81.2	104.3	105.7	89.4
95°	28.5	31.7	39.9	47.2	60.3	79.7	117.2	187.9	282.3	318.9	279.1
97.5°	46.4	50.8	59.4	70.4	85.4	107.5	154.6	253.2	410.1	544.5	571.2
100°	62.6	65.1	72.4	85.4	101.7	124.5	167.6	266.9	442.6	642.8	760.0
102.5°	77.6	79.4	86.7	99.8	116.7	139.5	179.4	267.6	430.3	646.0	830.3
105°	99.3	102.6	108.2	120.4	138.4	161.1	199.3	271.7	406.0	602.9	819.4
107.5°	122.7	125.3	130.9	142.1	159.8	182.8	219.9	283.0	394.0	556.8	748.0
110°	138.4	141.6	146.4	157.0	174.1	197.7	233.5	292.1	391.4	534.6	703.0



TEST NUMBER: P331638-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	152.6	155.9	161.4	171.4	187.8	212.1	246.5	301.9	392.0	520.2	671.8
115°	175.0	179.0	183.9	193.6	209.9	231.9	266.9	316.5	395.4	504.5	633.1
117.5°	198.0	201.3	206.2	214.8	230.4	253.2	285.6	332.2	401.3	496.8	608.6
120°	212.4	215.6	220.5	227.8	244.1	266.9	298.6	342.6	405.2	492.3	595.7
122.5°	226.1	228.6	233.5	241.5	257.8	281.2	311.0	351.6	409.8	489.7	584.6
125°	244.1	246.5	251.4	261.2	277.4	300.3	329.5	366.2	416.6	484.9	568.8
127.5°	258.4	261.7	268.5	279.2	294.9	318.3	346.8	379.7	423.6	482.2	554.2
130°	266.9	270.1	278.3	289.7	306.0	328.7	357.2	388.2	428.8	480.9	544.4
132.5°	274.7	278.6	287.4	299.5	316.3	339.2	366.3	396.6	434.0	480.2	536.5
135°	286.4	289.7	299.5	311.6	330.4	353.1	379.2	407.6	440.2	479.2	525.6
137.5°	297.5	301.4	311.1	324.2	342.8	363.9	389.6	416.1	445.7	479.1	518.0
140°	306.0	309.2	318.9	332.0	349.9	371.0	395.4	420.7	448.3	478.4	513.5
142.5°	314.4	317.0	326.1	339.2	356.4	376.3	400.0	424.6	450.3	478.4	508.9
145°	327.1	330.4	338.5	350.7	367.0	384.9	406.8	429.7	452.4	476.8	502.9
147.5°	340.8	343.2	351.0	362.2	375.8	391.8	412.4	432.4	453.1	473.9	496.7
150°	349.9	352.3	358.8	369.4	381.6	396.2	415.0	433.7	452.4	472.0	491.5
152.5°	359.0	360.1	366.6	375.9	387.5	400.8	417.6	434.3	451.1	468.7	486.9
155°	371.9	372.7	377.6	386.5	395.4	407.6	421.5	435.3	449.1	463.0	478.4
157.5°	382.6	383.4	387.3	395.1	402.3	412.5	424.3	435.3	445.4	457.1	470.5
160°	389.8	390.6	393.8	400.3	406.8	415.8	425.6	435.3	443.4	453.2	464.6
162.5°	396.9	396.4	399.7	404.9	410.7	417.8	426.2	434.6	441.5	450.0	459.4
165°	405.2	404.4	406.0	410.9	415.0	419.9	427.2	432.9	437.7	443.4	450.8
167.5°	412.1	411.1	412.5	415.6	418.6	421.7	427.1	431.8	434.0	437.7	442.3
170°	416.6	415.0	415.8	418.2	419.9	422.3	426.4	430.5	432.1	434.5	437.7
172.5°	419.2	418.2	417.8	420.2	421.2	423.0	425.7	428.5	429.5	430.6	433.3
175°	422.3	421.5	420.7	422.3	422.3	423.1	424.8	426.4	425.6	426.4	427.2
177.5°	423.8	422.5	421.8	423.1	423.1	423.1	423.8	425.1	423.8	423.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331638-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	407.3	408.0	408.6	408.9	408.8	408.6	408.5	408.4
5°	404.1	404.8	405.5	405.8	405.5	405.3	405.0	404.8
7.5°	397.5	397.8	397.9	397.9	397.5	397.0	396.6	396.2
10°	391.0	390.8	390.5	390.1	389.6	389.1	388.7	388.2
12.5°	383.5	383.0	382.6	382.0	381.2	380.3	379.5	378.7
15°	369.5	367.9	366.3	365.2	364.4	363.5	362.6	361.8
17.5°	353.6	351.7	349.9	348.3	346.8	345.4	344.0	342.6
20°	342.6	340.5	338.4	336.5	334.7	332.9	331.1	329.3
22.5°	330.4	327.8	325.1	323.1	321.7	320.4	319.0	317.7
25°	310.3	306.9	303.5	301.3	300.0	298.7	297.5	296.3
27.5°	291.1	287.1	283.2	280.3	278.3	276.4	274.4	272.5
30°	277.5	273.4	269.1	266.0	263.7	261.5	259.3	257.1
32.5°	263.9	259.1	254.3	250.9	248.8	246.7	244.6	242.6
35°	242.6	237.4	232.2	228.7	226.9	225.1	223.3	221.5
37.5°	221.8	216.1	210.4	206.5	204.5	202.4	200.3	198.2
40°	208.0	202.1	196.2	192.2	190.1	188.0	185.8	183.7
42.5°	193.9	187.8	181.8	177.8	175.7	173.7	171.5	169.5
45°	173.5	167.6	161.8	157.9	156.0	153.9	152.0	150.0
47.5°	153.6	147.8	142.0	138.2	136.4	134.6	132.8	131.0
50°	140.9	135.2	129.5	125.8	124.1	122.4	120.6	118.9
52.5°	128.8	123.4	117.9	114.3	112.8	111.1	109.5	107.9
55°	110.5	105.6	100.6	97.3	95.8	94.2	92.7	91.2
57.5°	93.8	89.3	84.8	81.9	80.6	79.2	77.9	76.6
60°	82.3	78.2	73.9	71.2	69.9	68.6	67.3	66.0
62.5°	72.4	68.4	64.4	62.0	61.1	60.4	59.6	58.8
65°	58.9	56.0	53.2	51.7	51.4	51.2	51.0	50.7
67.5°	47.5	46.2	44.9	44.2	43.9	43.6	43.4	43.1
70°	41.3	40.5	39.7	39.1	38.7	38.4	38.1	37.7
72.5°	36.0	35.2	34.6	34.2	33.9	33.8	33.5	33.3
75°	28.5	27.9	27.3	27.0	26.9	26.8	26.7	26.7
77.5°	21.5	21.2	20.9	20.7	20.5	20.4	20.3	20.1
80°	17.1	16.8	16.5	16.3	16.3	16.3	16.3	16.3
82.5°	13.0	12.7	12.6	12.5	12.5	12.5	12.5	12.5
85°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
87.5°	7.4	7.1	7.3	7.4	7.4	7.4	7.4	7.4
90°	26.0	24.4	26.0	26.8	26.8	26.8	26.8	26.8
92.5°	70.9	60.9	54.1	49.0	48.3	45.7	46.4	45.1
95°	213.2	163.5	129.4	111.5	100.9	94.4	92.0	92.8
97.5°	497.5	407.0	318.9	260.2	221.4	201.3	189.4	182.6
100°	742.9	642.0	530.5	432.1	364.5	329.5	306.0	291.3
102.5°	903.7	880.9	799.4	695.0	621.7	561.9	532.5	512.7
105°	988.6	1080.6	1091.2	1064.3	1013.8	963.4	928.4	917.0
107.5°	927.5	1065.9	1150.6	1189.9	1196.3	1193.5	1186.5	1171.4
110°	874.7	1020.3	1124.5	1191.2	1226.2	1241.7	1249.0	1248.2



TEST NUMBER: P331638-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	826.6	966.4	1077.7	1154.1	1202.8	1228.7	1242.5	1246.9
115°	767.3	892.6	999.2	1083.0	1140.8	1178.2	1199.4	1206.7
117.5°	722.7	832.7	929.4	1008.0	1066.9	1106.4	1128.8	1134.9
120°	700.6	801.5	887.7	961.8	1018.7	1057.0	1080.6	1088.8
122.5°	683.0	775.4	857.1	924.1	975.1	1012.7	1033.7	1040.6
125°	657.5	741.3	812.9	873.9	921.1	952.0	972.3	978.8
127.5°	632.3	708.1	775.6	831.9	873.1	902.0	919.7	924.9
130°	616.0	685.9	750.2	804.0	843.8	871.5	887.7	894.2
132.5°	600.3	665.1	724.1	774.6	813.8	841.6	856.5	862.3
135°	578.5	632.3	685.9	731.5	766.5	793.4	808.0	811.2
137.5°	561.1	606.0	648.7	688.4	720.3	743.4	756.3	761.2
140°	550.1	589.1	626.6	662.3	688.4	709.6	721.8	726.6
142.5°	541.0	574.1	606.3	636.3	661.0	680.3	691.1	692.1
145°	528.1	555.0	580.2	603.7	623.3	637.2	645.2	647.7
147.5°	518.1	539.3	559.0	576.3	592.4	603.4	608.9	610.4
150°	511.0	528.9	546.0	560.6	572.8	582.6	587.5	588.3
152.5°	503.9	520.4	534.9	547.6	557.2	565.7	569.2	569.4
155°	493.9	507.0	519.1	528.1	537.0	542.7	546.0	544.4
157.5°	482.3	493.3	503.5	510.5	516.8	521.5	523.0	523.0
160°	475.2	484.1	493.1	498.8	504.5	508.6	509.4	509.4
162.5°	468.1	475.6	483.3	487.7	493.4	496.2	497.0	496.4
165°	457.3	463.0	468.7	472.0	475.2	478.4	478.4	477.6
167.5°	447.0	451.4	455.3	458.3	459.7	461.5	461.4	460.4
170°	441.8	444.3	447.5	449.1	450.0	452.4	451.6	450.0
172.5°	435.9	437.7	440.3	441.3	442.1	443.3	442.5	441.5
175°	429.7	430.5	431.3	432.1	432.1	432.9	432.1	430.5
177.5°	425.1	425.1	425.7	425.7	425.7	425.7	425.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1

(END OF REPORT)