

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332025-927

Luminaire Tested: **S123DIP-S1000D805U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332025-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D805U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5449.7 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332025-927

CATALOG NUMBER: S123DIP-S1000D805U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332025-927

CATALOG NUMBER: S123DIP-S1000D805U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	110	110	110	110	102	102	102	102	89	89	89		77	77	77		65	65	65	60
1	100	95	92	88	93	89	86	83	78	75	73		67	65	64		58	56	55	50
2	91	83	77	72	85	78	73	68	68	64	60		59	56	53		51	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51		52	48	45		45	42	39	36
4	76	65	57	51	71	61	54	48	53	48	43		47	42	38		40	37	34	31
5	70	58	50	43	65	54	47	41	48	42	37		42	37	33		36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33		38	33	29		33	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29		34	30	26		30	26	23	21
8	55	43	35	29	52	40	33	28	36	30	26		31	27	23		27	24	21	18
9	51	39	31	26	48	37	30	25	33	27	23		29	24	21		25	22	19	17
10	48	36	28	24	45	34	27	23	30	25	21		27	22	19		24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13497	13497	13497
5°	13560	13374	13467
10°	13470	13258	13340
15°	13312	13108	13133
20°	13128	12893	12906
25°	12883	12638	12613
30°	12609	12356	12261
35°	12326	12056	11901
40°	12029	11726	11545
45°	11702	11423	11144
50°	11375	11050	10742
55°	10946	10663	10340
60°	10514	10213	9888
65°	10132	9722	9419
70°	9567	9161	8752
75°	8742	8430	8072
80°	7885	7550	7482
85°	6928	6657	6385



TEST NUMBER: P332025-927

CATALOG NUMBER: S123DIP-S1000D805U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.1	2.2
10°-20°	333.5	6.1
20°-30°	492.7	9.0
30°-40°	575.5	10.6
40°-50°	578.6	10.6
50°-60°	508.2	9.3
60°-70°	378.6	6.9
70°-80°	215.7	4.0
80°-90°	64.2	1.2
90°-100°	51.4	0.9
100°-110°	153.7	2.8
110°-120°	261.5	4.8
120°-130°	343.9	6.3
130°-140°	386.6	7.1
140°-150°	380.0	7.0
150°-160°	319.9	5.9
160°-170°	212.9	3.9
170°-180°	74.6	1.4
0°-30°	944.3	17.3
0°-40°	1519.8	27.9
0°-60°	2606.6	47.8
0°-90°	3265.2	59.9
90°-120°	466.6	8.6
90°-150°	1577.1	28.9
90°-180°	2185.0	40.1
0°-180°	5449.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1254	1254	1254	1254	1254	
5°	1255	1249	1238	1248	1246	119
15°	1195	1190	1176	1184	1178	337
25°	1085	1078	1064	1065	1062	499
35°	938	931	918	911	906	587
45°	769	764	750	738	732	593
55°	583	582	568	557	551	522
65°	398	392	382	373	370	392
75°	210	206	203	197	194	225
85°	56	54	54	52	52	62
90°	1	7	15	17	19	5
95°	36	41	46	48	48	41
105°	139	141	146	146	147	149
115°	263	265	264	264	264	260
125°	385	387	386	383	381	343
135°	500	503	503	500	499	385
145°	606	608	609	609	606	379
155°	694	694	695	697	693	319
165°	756	754	754	758	754	213
175°	787	784	784	787	784	75
180°	788	788	788	788	788	



TEST NUMBER: P332025-927

CATALOG NUMBER: S123DIP-S1000D805U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1258.2	1257.5	1256.7	1255.9	1255.2	1253.7	1251.6	1249.5	1247.4	1245.3	1247.2
5°	1255.0	1253.8	1252.6	1251.4	1250.2	1248.3	1245.7	1243.0	1240.4	1237.8	1240.2
7.5°	1242.7	1241.5	1240.3	1239.1	1237.9	1236.0	1233.3	1230.5	1227.8	1225.0	1227.2
10°	1232.4	1231.2	1229.9	1228.8	1227.6	1225.4	1222.3	1219.2	1216.1	1213.0	1215.1
12.5°	1218.5	1217.6	1216.6	1215.5	1214.6	1212.6	1209.7	1206.7	1203.8	1200.9	1202.5
15°	1194.6	1193.7	1192.7	1191.8	1190.8	1188.7	1185.7	1182.6	1179.4	1176.3	1178.2
17.5°	1166.8	1165.5	1164.3	1163.1	1161.8	1159.7	1156.5	1153.4	1150.3	1147.2	1148.5
20°	1146.1	1144.7	1143.3	1141.8	1140.3	1138.0	1135.0	1131.9	1128.8	1125.6	1126.6
22.5°	1122.8	1121.4	1120.0	1118.5	1117.1	1114.8	1111.7	1108.6	1105.5	1102.3	1103.1
25°	1084.7	1083.2	1081.8	1080.4	1078.9	1076.7	1073.5	1070.4	1067.3	1064.1	1064.4
27.5°	1043.9	1042.5	1041.1	1039.7	1038.3	1035.9	1032.6	1029.3	1025.9	1022.5	1022.7
30°	1014.5	1013.4	1012.2	1011.0	1009.8	1007.5	1004.2	1000.8	997.4	994.1	994.1
32.5°	985.2	983.7	982.1	980.5	978.9	976.8	974.2	971.7	969.1	966.5	965.1
35°	938.0	936.6	935.2	933.7	932.2	930.0	926.9	923.8	920.7	917.5	916.1
37.5°	889.7	887.9	886.1	884.2	882.4	880.0	876.8	873.6	870.4	867.3	865.5
40°	856.1	854.6	853.2	851.8	850.3	848.0	844.5	841.2	837.9	834.5	832.6
42.5°	822.4	820.8	819.2	817.5	815.9	813.4	810.1	806.8	803.4	800.0	798.1
45°	768.7	767.8	766.8	765.9	764.9	762.9	759.8	756.6	753.5	750.4	747.6
47.5°	715.5	714.1	712.7	711.3	710.0	707.7	704.9	702.0	699.0	696.1	693.2
50°	679.3	678.0	676.8	675.7	674.5	672.3	669.2	666.1	663.0	659.9	657.2
52.5°	641.3	640.5	639.7	638.9	638.0	636.0	632.7	629.4	626.1	622.7	620.5
55°	583.3	583.0	582.8	582.6	582.3	580.7	577.6	574.4	571.3	568.2	565.5
57.5°	528.1	527.3	526.5	525.7	524.8	523.2	520.7	518.2	515.7	513.3	510.9
60°	488.4	488.1	487.9	487.7	487.4	485.9	483.0	480.1	477.3	474.4	472.2
62.5°	453.0	452.4	451.8	451.1	450.6	448.9	445.9	443.1	440.2	437.3	435.1
65°	397.8	396.6	395.5	394.3	393.1	391.3	388.9	386.5	384.0	381.7	379.8
67.5°	339.5	338.3	337.3	336.3	335.2	333.7	331.9	330.1	328.3	326.5	324.8
70°	304.0	302.6	301.2	299.8	298.3	296.8	295.4	294.0	292.6	291.1	289.5
72.5°	267.0	265.9	264.8	263.8	262.8	261.4	259.8	258.2	256.5	254.8	253.4
75°	210.2	209.3	208.3	207.4	206.4	205.6	204.9	204.1	203.4	202.7	201.5
77.5°	160.0	159.5	158.9	158.4	157.9	157.2	156.4	155.5	154.6	153.8	153.0
80°	127.2	126.5	125.8	125.1	124.4	123.7	123.3	122.8	122.3	121.8	121.6
82.5°	95.3	95.1	95.1	94.9	94.7	94.6	94.5	94.4	94.3	94.3	93.8
85°	56.1	55.6	55.1	54.7	54.2	53.9	53.9	53.9	53.9	53.9	53.4
87.5°	22.6	22.3	21.9	21.6	21.4	21.3	21.5	21.6	21.8	21.9	21.9
90°	0.6	2.0	3.4	4.8	6.1	7.7	9.5	11.2	13.1	14.9	15.4
92.5°	15.0	15.9	16.9	17.8	18.7	19.7	20.8	21.8	22.7	23.8	24.2
95°	36.5	37.5	38.5	39.5	40.4	41.4	42.5	43.6	44.8	45.9	46.4
97.5°	64.9	65.6	66.3	67.0	67.8	68.5	69.3	70.1	70.9	71.7	72.3
100°	84.2	85.1	85.9	86.7	87.5	88.3	89.0	89.7	90.4	91.0	91.5
102.5°	106.5	107.0	107.5	108.1	108.5	109.2	110.1	111.1	111.9	112.9	113.3
105°	139.3	139.7	139.9	140.2	140.5	141.2	142.4	143.7	145.0	146.2	146.2
107.5°	177.5	177.7	177.8	178.0	178.2	178.5	179.0	179.5	180.0	180.5	180.9
110°	201.3	201.5	201.8	202.1	202.4	202.6	203.0	203.2	203.5	203.7	204.3



TEST NUMBER: P332025-927

CATALOG NUMBER: S123DIP-S1000D805U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	226.1	226.2	226.4	226.6	226.7	226.8	226.9	227.0	227.0	227.0	227.8
115°	263.2	263.6	264.0	264.4	264.9	265.0	264.7	264.4	264.1	263.9	264.0
117.5°	300.6	301.0	301.2	301.4	301.7	301.7	301.3	301.0	300.6	300.2	300.2
120°	323.9	324.7	325.6	326.4	327.3	327.3	326.6	325.9	325.3	324.6	324.4
122.5°	348.2	348.8	349.4	350.0	350.6	350.8	350.4	350.1	349.7	349.4	349.0
125°	385.2	385.6	386.0	386.5	386.9	387.0	386.7	386.4	386.1	385.9	385.3
127.5°	419.5	420.3	421.2	422.1	422.9	423.3	422.9	422.6	422.3	422.0	421.3
130°	442.2	443.3	444.4	445.5	446.6	446.9	446.6	446.2	445.8	445.3	444.7
132.5°	465.0	466.1	467.2	468.3	469.4	469.8	469.5	469.2	468.9	468.6	467.9
135°	499.8	500.7	501.5	502.3	503.1	503.5	503.4	503.2	503.0	503.0	502.4
137.5°	532.0	532.7	533.4	534.1	534.8	535.3	535.7	536.0	536.4	536.7	536.1
140°	554.3	555.0	555.7	556.4	557.1	557.5	557.6	557.8	557.9	558.0	557.9
142.5°	574.6	575.4	576.0	576.7	577.4	577.9	578.1	578.4	578.6	578.8	578.7
145°	606.3	606.7	606.9	607.2	607.4	607.8	608.2	608.6	609.0	609.4	609.3
147.5°	634.1	634.6	635.1	635.6	636.1	636.5	636.9	637.3	637.7	638.1	638.1
150°	653.4	653.7	653.9	654.3	654.5	654.8	655.1	655.4	655.6	655.9	655.9
152.5°	669.3	669.6	670.0	670.4	670.8	671.1	671.3	671.5	671.6	671.8	672.0
155°	694.3	694.3	694.3	694.3	694.3	694.3	694.5	694.7	694.8	694.9	695.5
157.5°	715.6	715.4	715.3	715.1	714.9	714.9	715.0	715.2	715.3	715.3	716.0
160°	729.0	728.7	728.4	728.2	727.9	727.8	727.8	727.8	727.8	727.8	728.4
162.5°	740.8	740.5	740.1	739.7	739.3	739.2	739.3	739.4	739.5	739.7	740.3
165°	756.2	755.8	755.4	755.0	754.6	754.4	754.4	754.4	754.4	754.4	755.2
167.5°	768.5	767.9	767.4	766.8	766.3	766.1	766.2	766.3	766.4	766.5	767.4
170°	775.5	774.9	774.4	773.8	773.2	772.9	772.9	772.9	772.9	772.9	774.0
172.5°	780.9	780.4	779.8	779.3	778.7	778.4	778.4	778.4	778.4	778.4	779.3
175°	786.6	786.0	785.5	785.0	784.4	784.1	784.1	784.1	784.1	784.1	785.0
177.5°	788.9	788.5	788.1	787.6	787.2	787.0	787.0	787.0	787.0	787.0	787.6
180°	788.5	788.5	788.5	788.5	788.5	788.5	788.5	788.5	788.5	788.5	788.5



TEST NUMBER: P332025-927

CATALOG NUMBER: S123DIP-S1000D805U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1249.1	1251.1	1253.0	1253.9	1253.6	1253.5	1253.2	1253.1
5°	1242.5	1244.9	1247.4	1248.3	1247.8	1247.4	1246.9	1246.4
7.5°	1229.4	1231.5	1233.7	1234.6	1234.3	1234.1	1233.7	1233.4
10°	1217.3	1219.4	1221.6	1222.4	1221.9	1221.5	1221.0	1220.5
12.5°	1204.0	1205.6	1207.2	1207.8	1207.6	1207.3	1207.0	1206.7
15°	1180.1	1182.0	1184.0	1184.2	1182.8	1181.3	1179.9	1178.5
17.5°	1149.9	1151.2	1152.5	1152.9	1152.5	1151.9	1151.4	1150.9
20°	1127.5	1128.5	1129.5	1129.6	1128.9	1128.1	1127.4	1126.7
22.5°	1103.9	1104.6	1105.4	1105.3	1104.5	1103.5	1102.6	1101.7
25°	1064.6	1064.9	1065.2	1064.9	1064.1	1063.4	1062.7	1062.0
27.5°	1022.9	1023.1	1023.3	1022.9	1022.1	1021.1	1020.3	1019.3
30°	994.1	994.1	994.1	993.2	991.6	989.9	988.2	986.5
32.5°	963.8	962.5	961.2	960.0	959.1	958.1	957.3	956.3
35°	914.7	913.2	911.8	910.5	909.3	908.1	906.9	905.7
37.5°	863.9	862.1	860.4	859.1	858.4	857.6	856.8	856.1
40°	830.7	828.8	826.9	825.4	824.4	823.5	822.5	821.6
42.5°	796.1	794.2	792.3	790.9	790.0	789.0	788.1	787.1
45°	744.7	741.8	738.9	736.9	735.7	734.5	733.3	732.1
47.5°	690.4	687.6	684.8	682.9	681.8	680.7	679.7	678.6
50°	654.6	652.0	649.3	647.3	645.9	644.4	642.9	641.5
52.5°	618.2	616.0	613.8	611.9	610.5	609.0	607.6	606.2
55°	562.9	560.3	557.7	555.7	554.5	553.3	552.2	551.0
57.5°	508.5	506.2	503.8	501.9	500.6	499.2	497.8	496.4
60°	470.1	467.9	465.8	464.1	462.9	461.7	460.5	459.3
62.5°	433.0	430.9	428.6	427.2	426.4	425.6	424.8	424.0
65°	377.9	375.9	374.0	372.7	372.0	371.3	370.5	369.8
67.5°	323.1	321.5	319.8	318.5	317.4	316.4	315.4	314.4
70°	287.7	286.1	284.4	283.0	281.8	280.6	279.4	278.1
72.5°	251.9	250.4	248.9	247.9	247.2	246.6	246.1	245.4
75°	200.3	199.1	197.9	196.9	196.2	195.5	194.8	194.1
77.5°	152.1	151.3	150.5	150.1	150.1	150.1	150.1	150.1
80°	121.4	121.1	120.9	120.7	120.7	120.7	120.7	120.7
82.5°	93.4	92.9	92.5	92.2	92.0	91.8	91.7	91.4
85°	52.9	52.4	52.0	51.7	51.7	51.7	51.7	51.7
87.5°	21.8	21.7	21.6	21.6	21.6	21.7	21.8	21.9
90°	16.0	16.5	17.0	17.5	17.7	18.1	18.3	18.6
92.5°	24.6	25.1	25.5	25.7	25.5	25.3	25.2	25.0
95°	46.9	47.5	48.0	48.3	48.3	48.3	48.3	48.3
97.5°	73.0	73.6	74.2	74.5	74.5	74.5	74.4	74.3
100°	91.9	92.3	92.7	93.1	93.3	93.6	93.9	94.1
102.5°	113.7	114.1	114.5	114.7	114.6	114.5	114.5	114.5
105°	146.2	146.2	146.2	146.3	146.6	146.9	147.1	147.4
107.5°	181.3	181.8	182.3	182.4	182.2	182.0	181.9	181.7
110°	204.9	205.4	206.0	206.1	205.8	205.6	205.3	205.0



TEST NUMBER: P332025-927

CATALOG NUMBER: S123DIP-S1000D805U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	228.4	229.0	229.7	230.0	230.0	229.9	229.8	229.8
115°	264.1	264.3	264.4	264.4	264.3	264.1	264.0	263.9
117.5°	300.2	300.2	300.2	299.9	299.6	299.2	298.8	298.4
120°	324.2	324.2	324.0	323.8	323.5	323.2	323.0	322.7
122.5°	348.6	348.2	347.9	347.5	347.1	346.7	346.3	345.9
125°	384.8	384.2	383.7	383.1	382.5	382.0	381.4	380.9
127.5°	420.5	419.7	419.0	418.3	417.6	417.0	416.4	415.7
130°	444.3	443.7	443.1	442.4	441.4	440.5	439.5	438.5
132.5°	467.3	466.6	466.0	465.2	464.5	463.7	463.0	462.3
135°	501.8	501.3	500.7	500.3	500.0	499.8	499.5	499.2
137.5°	535.6	535.0	534.4	533.9	533.4	532.8	532.3	531.8
140°	557.8	557.6	557.5	557.0	556.0	555.0	554.1	553.1
142.5°	578.6	578.5	578.3	577.9	577.1	576.4	575.6	574.9
145°	609.2	609.0	608.9	608.6	608.0	607.4	606.9	606.3
147.5°	638.1	638.1	638.1	637.6	636.8	636.0	635.2	634.4
150°	655.9	655.9	655.9	655.5	654.7	653.9	653.0	652.2
152.5°	672.2	672.4	672.6	672.4	671.7	671.0	670.3	669.6
155°	696.0	696.6	697.1	696.9	695.9	695.0	694.0	693.1
157.5°	716.5	717.1	717.6	717.6	716.8	716.1	715.3	714.5
160°	729.1	729.8	730.5	730.6	730.0	729.4	728.9	728.3
162.5°	741.0	741.7	742.4	742.3	741.4	740.5	739.7	738.8
165°	756.1	756.9	757.7	757.6	756.7	755.7	754.7	753.8
167.5°	768.3	769.1	769.9	769.9	769.1	768.3	767.4	766.5
170°	774.9	775.9	776.8	776.8	775.9	774.9	774.0	772.9
172.5°	780.1	781.0	781.8	781.8	780.8	779.8	778.9	777.9
175°	785.8	786.6	787.4	787.3	786.4	785.4	784.4	783.5
177.5°	788.3	788.9	789.6	789.6	788.8	788.0	787.3	786.5
180°	788.5	788.5	788.5	788.5	788.5	788.5	788.5	788.5

(END OF REPORT)