

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331715-930

Luminaire Tested: **S122RDIP-S865D530U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331715-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S865D530U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4001.4 lumens
Efficiency: N/A
Efficacy: 82.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331715-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331715-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	90	94	91	88	85	80	77	75	69	68	66	60	59	57	53
2	92	85	79	74	86	80	75	70	70	66	63	62	59	56	53	51	49	45
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43	39
4	78	67	59	54	73	63	56	51	56	51	46	49	45	42	43	40	37	34
5	72	60	52	46	67	57	50	44	51	45	40	45	40	37	39	36	33	30
6	66	54	46	41	62	51	44	39	46	40	36	41	36	32	36	32	29	27
7	62	49	41	36	58	47	40	35	42	36	32	37	32	29	33	29	26	24
8	57	45	37	32	54	43	36	31	38	33	28	34	30	26	30	27	24	22
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	24	22	20
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19302	19302	19302
5°	19376	19060	19164
10°	19226	18748	18589
15°	19005	18191	17668
20°	18699	17399	16526
25°	18387	16498	15419
30°	17952	15571	13998
35°	17527	14564	12751
40°	17102	13523	11310
45°	16600	12353	10003
50°	16088	11170	8721
55°	15564	9897	7491
60°	14951	8561	6219
65°	14258	7194	5662
70°	13430	5925	5207
75°	12420	5402	4860
80°	10962	4826	4426
85°	8633	3798	3798



TEST NUMBER: P331715-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.9	2.8
10°-20°	307.2	7.7
20°-30°	431.5	10.8
30°-40°	470.5	11.8
40°-50°	432.6	10.8
50°-60°	339.7	8.5
60°-70°	221.5	5.5
70°-80°	114.2	2.9
80°-90°	31.8	0.8
90°-100°	34.9	0.9
100°-110°	108.4	2.7
110°-120°	185.3	4.6
120°-130°	243.7	6.1
130°-140°	273.5	6.8
140°-150°	268.2	6.7
150°-160°	225.0	5.6
160°-170°	149.2	3.7
170°-180°	52.2	1.3
0°-30°	850.6	21.3
0°-40°	1321.1	33.0
0°-60°	2093.4	52.3
0°-90°	2460.9	61.5
90°-120°	328.7	8.2
90°-150°	1114.2	27.8
90°-180°	1540.0	38.5
0°-180°	4001.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1196	1190	1176	1185	1182	113
15°	1137	1124	1088	1068	1057	320
25°	1032	995	926	883	866	474
35°	889	832	739	673	647	556
45°	727	652	541	467	438	561
55°	553	467	352	289	266	494
65°	373	285	188	153	148	370
75°	199	126	87	79	78	211
85°	47	25	20	20	20	55
90°	0	6	16	15	16	3
95°	24	29	30	30	29	28
105°	100	101	102	103	103	106
115°	186	189	188	187	186	184
125°	271	274	273	272	272	242
135°	350	355	356	356	354	270
145°	425	428	431	431	430	265
155°	486	487	489	491	490	224
165°	529	528	528	531	529	149
175°	550	549	548	551	548	52
180°	551	551	551	551	551	



TEST NUMBER: P331715-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5
2.5°	1199.8	1198.8	1197.8	1196.9	1196.0	1194.4	1192.3	1190.2	1188.1	1185.9	1187.9
5°	1195.5	1194.3	1193.0	1191.8	1190.7	1188.5	1185.4	1182.3	1179.1	1176.0	1178.1
7.5°	1183.1	1181.6	1180.1	1178.7	1177.1	1174.6	1170.9	1167.3	1163.6	1159.9	1160.6
10°	1172.7	1171.0	1169.4	1167.7	1166.0	1162.8	1158.0	1153.2	1148.3	1143.5	1142.8
12.5°	1159.8	1157.6	1155.6	1153.6	1151.4	1147.4	1141.2	1135.1	1128.9	1122.7	1121.4
15°	1137.0	1134.4	1131.7	1129.1	1126.4	1121.0	1112.9	1104.7	1096.5	1088.3	1083.8
17.5°	1109.1	1105.1	1101.1	1097.0	1093.0	1085.7	1075.2	1064.7	1054.3	1043.7	1038.4
20°	1088.3	1083.5	1078.7	1073.9	1069.1	1060.7	1048.6	1036.7	1024.7	1012.6	1006.6
22.5°	1065.8	1060.5	1055.1	1049.7	1044.3	1034.9	1021.2	1007.7	994.2	980.6	972.8
25°	1032.1	1024.4	1016.7	1009.0	1001.4	989.5	973.6	957.8	941.9	926.1	916.2
27.5°	991.4	983.0	974.7	966.3	958.0	944.9	926.9	909.1	891.1	873.3	861.8
30°	962.9	953.7	944.6	935.5	926.3	912.2	892.9	873.7	854.4	835.2	823.0
32.5°	935.1	924.5	913.8	903.1	892.4	877.3	857.7	838.0	818.5	798.8	784.9
35°	889.2	877.0	864.8	852.5	840.2	823.5	802.3	781.2	760.1	738.9	723.7
37.5°	843.4	830.0	816.5	803.0	789.5	771.5	749.0	726.4	703.9	681.3	664.6
40°	811.4	797.0	782.5	768.1	753.7	734.8	711.5	688.2	664.9	641.6	624.4
42.5°	778.5	763.3	748.1	733.0	717.7	698.1	674.0	649.9	625.8	601.7	584.1
45°	727.0	710.9	694.8	678.7	662.6	641.9	616.7	591.4	566.1	541.0	523.8
47.5°	676.8	659.7	642.7	625.6	608.5	586.9	560.9	534.8	508.7	482.7	465.8
50°	640.5	623.4	606.3	589.2	572.2	550.4	524.0	497.5	471.1	444.7	428.0
52.5°	605.0	587.1	569.3	551.5	533.6	511.8	485.9	460.0	434.1	408.3	392.2
55°	552.9	534.1	515.4	496.6	477.8	455.4	429.5	403.5	377.6	351.6	337.2
57.5°	499.4	480.1	460.9	441.6	422.5	400.4	375.4	350.4	325.5	300.5	287.3
60°	463.0	443.8	424.6	405.4	386.1	364.1	339.3	314.5	289.8	265.1	252.8
62.5°	427.5	408.3	389.1	369.8	350.6	329.2	305.6	282.0	258.4	234.7	223.1
65°	373.2	353.8	334.3	314.8	295.4	274.8	253.2	231.5	209.9	188.3	180.1
67.5°	320.9	301.6	282.3	262.9	243.5	224.1	204.7	185.2	165.8	146.3	142.5
70°	284.5	265.8	247.0	228.3	209.5	191.8	175.3	158.7	142.1	125.5	123.1
72.5°	249.9	232.0	213.9	196.0	178.0	162.3	149.0	135.7	122.4	109.1	107.0
75°	199.1	182.2	165.4	148.5	131.8	119.3	111.0	102.9	94.7	86.6	84.9
77.5°	149.1	134.3	119.5	104.8	90.0	80.7	76.7	72.8	68.9	64.9	63.9
80°	117.9	105.7	93.4	81.1	68.9	61.6	59.1	56.7	54.3	51.9	51.0
82.5°	89.4	79.8	70.2	60.7	51.1	45.5	43.9	42.2	40.6	39.0	38.4
85°	46.6	41.5	36.4	31.4	26.3	23.5	22.7	22.0	21.3	20.5	20.5
87.5°	13.9	12.6	11.3	10.0	8.8	8.4	8.8	9.3	9.7	10.2	9.9
90°	0.5	1.7	2.9	4.2	5.5	7.2	9.5	11.7	14.0	16.3	16.1
92.5°	8.3	9.2	10.1	11.0	11.9	12.6	13.2	13.7	14.3	14.8	14.8
95°	24.2	25.2	26.3	27.3	28.3	28.9	29.1	29.4	29.5	29.8	29.8
97.5°	44.2	45.1	46.0	46.9	47.8	48.4	48.8	49.2	49.7	50.1	50.1
100°	59.0	59.8	60.7	61.6	62.4	62.9	63.3	63.5	63.8	64.2	64.2
102.5°	74.7	75.3	76.0	76.6	77.3	77.9	78.3	78.6	79.0	79.4	79.5
105°	100.0	100.3	100.6	100.9	101.2	101.4	101.7	101.8	102.1	102.3	102.5
107.5°	125.5	125.9	126.4	126.8	127.3	127.5	127.5	127.5	127.5	127.5	127.6
110°	141.8	142.4	143.0	143.7	144.3	144.6	144.6	144.6	144.6	144.6	144.6



TEST NUMBER: P331715-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	159.6	160.3	160.9	161.5	162.2	162.4	162.3	162.2	162.2	162.1	161.8
115°	186.0	186.6	187.2	187.8	188.4	188.7	188.4	188.3	188.0	187.8	187.8
117.5°	212.2	213.0	213.9	214.7	215.5	215.6	215.1	214.4	213.9	213.3	213.0
120°	229.7	230.5	231.3	232.1	233.0	233.0	232.1	231.3	230.5	229.7	229.7
122.5°	245.6	246.6	247.7	248.7	249.6	249.8	249.2	248.7	248.1	247.5	247.3
125°	270.6	271.5	272.5	273.4	274.3	274.6	274.3	274.0	273.7	273.4	273.0
127.5°	294.8	296.0	297.2	298.4	299.5	299.9	299.6	299.2	298.9	298.5	298.1
130°	310.1	311.4	312.7	314.1	315.4	316.0	315.8	315.6	315.4	315.2	315.0
132.5°	327.2	328.3	329.4	330.5	331.6	332.2	332.2	332.2	332.3	332.3	331.9
135°	350.1	351.2	352.4	353.5	354.7	355.3	355.5	355.7	356.0	356.1	356.0
137.5°	374.1	375.1	376.0	377.0	377.9	378.5	378.8	379.0	379.3	379.5	379.4
140°	388.7	389.6	390.5	391.4	392.4	393.1	393.6	394.1	394.7	395.2	395.2
142.5°	403.6	404.5	405.4	406.3	407.2	407.9	408.3	408.6	409.0	409.3	409.4
145°	424.9	425.7	426.4	427.1	427.9	428.5	429.1	429.7	430.4	431.0	431.0
147.5°	444.0	444.8	445.7	446.6	447.4	448.1	448.5	448.9	449.3	449.8	450.0
150°	457.1	457.6	458.3	458.9	459.5	460.0	460.4	460.8	461.2	461.7	461.9
152.5°	468.6	469.2	469.8	470.4	471.0	471.6	472.1	472.5	473.0	473.6	473.9
155°	485.8	486.2	486.5	486.7	487.1	487.4	487.7	488.0	488.3	488.6	489.2
157.5°	500.6	500.8	501.0	501.2	501.5	501.7	501.8	502.1	502.2	502.4	503.1
160°	509.6	509.7	510.0	510.1	510.4	510.5	510.6	510.7	510.9	510.9	511.6
162.5°	517.7	517.8	517.8	517.9	517.9	518.0	518.0	518.2	518.3	518.4	519.1
165°	528.6	528.5	528.4	528.3	528.2	528.2	528.2	528.2	528.2	528.2	528.9
167.5°	537.7	537.4	537.1	536.8	536.5	536.3	536.3	536.3	536.2	536.2	537.0
170°	542.6	542.3	541.9	541.6	541.4	541.1	541.0	540.9	540.8	540.7	541.4
172.5°	545.9	545.6	545.3	544.9	544.7	544.5	544.4	544.3	544.1	544.0	544.8
175°	550.0	549.7	549.3	549.1	548.8	548.5	548.3	548.1	547.9	547.6	548.4
177.5°	551.7	551.4	551.1	550.9	550.7	550.5	550.3	550.2	550.0	549.8	550.3
180°	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9



TEST NUMBER: P331715-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5
2.5°	1189.8	1191.7	1193.6	1194.4	1194.0	1193.6	1193.3	1192.9
5°	1180.3	1182.4	1184.6	1185.4	1184.6	1183.9	1183.2	1182.4
7.5°	1161.2	1161.8	1162.5	1162.1	1160.9	1159.7	1158.4	1157.2
10°	1142.1	1141.3	1140.6	1139.5	1138.1	1136.7	1135.2	1133.8
12.5°	1120.1	1118.8	1117.5	1115.7	1113.3	1110.9	1108.5	1106.1
15°	1079.2	1074.6	1070.1	1066.6	1064.2	1061.8	1059.4	1057.0
17.5°	1032.9	1027.4	1022.1	1017.2	1013.1	1009.0	1004.9	1000.7
20°	1000.6	994.6	988.6	982.9	977.6	972.3	967.0	961.8
22.5°	965.2	957.4	949.7	943.8	939.9	935.9	932.0	928.1
25°	906.4	896.5	886.6	879.9	876.3	872.7	869.1	865.5
27.5°	850.3	838.8	827.3	818.7	813.0	807.2	801.5	795.8
30°	810.7	798.4	786.1	776.7	770.3	763.8	757.3	750.8
32.5°	770.9	756.8	742.9	732.8	726.8	720.6	714.5	708.4
35°	708.6	693.5	678.3	668.1	662.8	657.5	652.2	646.9
37.5°	648.0	631.3	614.7	603.2	597.2	591.1	585.1	579.0
40°	607.4	590.4	573.2	561.6	555.4	549.1	542.8	536.6
42.5°	566.5	548.8	531.2	519.3	513.2	507.2	501.1	495.0
45°	506.8	489.8	472.6	461.2	455.4	449.7	443.9	438.1
47.5°	448.7	431.8	414.8	403.7	398.5	393.2	388.0	382.8
50°	411.5	394.8	378.3	367.5	362.4	357.3	352.3	347.2
52.5°	376.3	360.3	344.2	333.9	329.2	324.6	319.9	315.3
55°	322.8	308.3	293.9	284.4	279.8	275.2	270.7	266.1
57.5°	274.1	260.9	247.7	239.1	235.3	231.4	227.6	223.7
60°	240.5	228.3	216.0	208.0	204.1	200.2	196.4	192.6
62.5°	211.4	199.7	188.0	181.0	178.7	176.4	174.1	171.8
65°	171.9	163.7	155.6	151.1	150.3	149.7	149.0	148.2
67.5°	138.8	135.0	131.3	129.0	128.2	127.4	126.7	126.0
70°	120.7	118.3	115.9	114.2	113.2	112.3	111.3	110.3
72.5°	105.0	103.0	100.9	99.7	99.1	98.5	97.9	97.3
75°	83.2	81.5	79.8	78.8	78.6	78.4	78.1	77.9
77.5°	63.0	62.0	61.1	60.4	60.0	59.6	59.3	58.9
80°	50.0	49.1	48.1	47.6	47.6	47.6	47.6	47.6
82.5°	37.8	37.2	36.6	36.4	36.4	36.4	36.4	36.4
85°	20.5	20.5	20.5	20.5	20.5	20.5	20.5	20.5
87.5°	9.7	9.5	9.2	9.1	9.1	9.2	9.2	9.2
90°	15.9	15.7	15.4	15.4	15.5	15.6	15.7	15.8
92.5°	14.8	14.9	14.9	15.0	15.0	15.0	15.1	15.1
95°	29.8	29.8	29.8	29.7	29.4	29.3	29.0	28.9
97.5°	50.1	50.1	50.1	50.0	50.0	50.0	50.0	49.9
100°	64.2	64.2	64.2	64.1	64.0	63.9	63.8	63.7
102.5°	79.6	79.7	79.7	79.7	79.7	79.5	79.4	79.3
105°	102.7	102.9	103.1	103.2	103.2	103.2	103.2	103.2
107.5°	127.7	127.8	127.8	127.6	127.1	126.7	126.2	125.7
110°	144.6	144.6	144.6	144.5	144.1	143.8	143.5	143.2



TEST NUMBER: P331715-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	161.6	161.3	161.1	160.9	160.6	160.4	160.1	160.0
115°	187.6	187.5	187.4	187.2	186.9	186.6	186.3	186.0
117.5°	212.8	212.5	212.3	212.1	211.7	211.4	211.1	210.8
120°	229.7	229.7	229.7	229.5	229.2	228.9	228.6	228.3
122.5°	247.0	246.8	246.5	246.3	246.1	245.8	245.6	245.4
125°	272.7	272.5	272.1	271.9	271.8	271.7	271.6	271.5
127.5°	297.7	297.3	297.0	296.6	296.3	296.0	295.6	295.3
130°	314.8	314.6	314.4	314.1	313.6	313.2	312.8	312.4
132.5°	331.4	330.9	330.5	330.1	329.8	329.5	329.1	328.8
135°	356.0	355.8	355.7	355.5	355.2	354.9	354.6	354.2
137.5°	379.4	379.3	379.2	379.0	378.5	378.1	377.7	377.3
140°	395.2	395.2	395.2	395.0	394.5	394.1	393.7	393.3
142.5°	409.4	409.5	409.6	409.4	409.0	408.6	408.2	407.8
145°	431.2	431.3	431.4	431.2	430.8	430.4	430.0	429.6
147.5°	450.2	450.5	450.7	450.6	450.2	449.8	449.4	449.0
150°	462.3	462.6	462.9	462.9	462.6	462.3	461.9	461.7
152.5°	474.3	474.7	475.2	475.2	474.7	474.3	473.9	473.6
155°	489.7	490.2	490.7	490.8	490.5	490.2	489.8	489.6
157.5°	503.8	504.5	505.2	505.3	504.8	504.3	503.9	503.3
160°	512.2	512.8	513.4	513.6	513.1	512.7	512.3	511.8
162.5°	519.8	520.5	521.2	521.3	520.8	520.3	519.8	519.3
165°	529.6	530.4	531.0	531.2	530.6	530.1	529.6	529.0
167.5°	537.7	538.4	539.2	539.2	538.7	538.2	537.6	537.0
170°	542.2	542.9	543.6	543.6	543.0	542.4	541.8	541.2
172.5°	545.5	546.3	546.9	547.0	546.4	545.8	545.1	544.5
175°	549.1	549.8	550.6	550.7	550.0	549.3	548.8	548.1
177.5°	550.8	551.3	551.8	551.8	551.3	550.8	550.3	549.8
180°	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9

(END OF REPORT)