

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831194

Luminaire Tested: S123DIP-S1165D1025U927-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831194
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1025U927-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7158.5 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831194
CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831194

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59				
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51				
2	92	85	79	74	86	79	74	70	69	66	62	60	57	55	52	50	48	44				
3	84	75	68	63	79	71	64	59	62	57	53	54	50	47	46	44	42	38				
4	78	67	60	54	72	63	56	51	56	50	46	49	45	41	42	39	36	33				
5	72	60	52	47	67	57	50	45	50	45	40	44	40	36	38	35	32	29				
6	66	55	47	41	62	52	44	39	46	40	36	40	36	32	35	32	29	26				
7	62	50	42	37	58	47	40	35	42	36	32	37	32	29	32	29	26	24				
8	58	45	38	33	54	43	36	31	38	33	29	34	30	26	30	27	24	22				
9	54	42	35	30	50	40	33	28	36	30	26	32	27	24	28	24	22	20				
10	50	39	32	27	47	37	30	26	33	28	24	30	25	22	26	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	28243	28243	28243	28243	28243
5°	35718	33713	28496	22964	21102
10°	36066	37156	28306	18306	15996
15°	27164	34497	28113	15502	13527
20°	18927	27915	27755	13557	12287
25°	14433	21467	27143	12473	11525
30°	12485	17055	26166	11706	10912
35°	11583	14399	25039	11152	10479
40°	10967	12917	23456	10624	10333
45°	10602	11954	21444	10213	10268
50°	10419	11194	19063	9838	10215
55°	10031	10637	16726	9483	10260
60°	9672	10038	14417	9147	10092
65°	9088	9475	12437	8792	9892
70°	8393	8755	10578	8201	9312
75°	7594	7848	9062	7619	8509
80°	6267	6868	7172	6639	7172
85°	4965	5570	5261	5644	5718

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 24484 cd/sqm



TEST NUMBER: P831194

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.1	3.5
10°-20°	617.1	8.6
20°-30°	730.7	10.2
30°-40°	734.7	10.3
40°-50°	674.1	9.4
50°-60°	556.4	7.8
60°-70°	393.6	5.5
70°-80°	210.1	2.9
80°-90°	55.5	0.8
90°-100°	212.0	3.0
100°-110°	620.6	8.7
110°-120°	606.0	8.5
120°-130°	482.6	6.7
130°-140°	380.8	5.3
140°-150°	284.1	4.0
150°-160°	198.1	2.8
160°-170°	116.4	1.6
170°-180°	37.8	0.5
0°-30°	1595.9	22.3
0°-40°	2330.6	32.6
0°-60°	3561.0	49.7
0°-90°	4220.2	59.0
90°-120°	1438.6	20.1
90°-150°	2586.1	36.1
90°-180°	2938.0	41.0
0°-180°	7158.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2624	2624	2624	2624	2624	
5°	3306	3120	2637	2125	1953	315
15°	2438	3096	2523	1391	1214	673
25°	1215	1808	2285	1050	970	573
35°	882	1096	1906	849	798	554
45°	696	785	1409	671	674	539
55°	534	567	891	505	547	478
65°	357	372	488	345	388	355
75°	183	189	218	183	205	192
85°	40	45	43	46	46	45
90°	23	20	2	20	23	15
95°	92	469	27	469	92	149
105°	1006	636	92	636	1006	1003
115°	1223	486	162	486	1223	1193
125°	965	454	225	454	965	873
135°	782	448	264	448	782	607
145°	611	442	301	442	611	388
155°	507	428	342	428	507	236
165°	442	410	374	410	442	126
175°	398	393	390	393	398	39
180°	391	391	391	391	391	



TEST NUMBER: P831194

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9
2.5°	2957.5	2954.5	2951.4	2936.2	2921.0	2913.7	2906.4	2884.5	2862.5	2838.2	2813.8
5°	3305.7	3314.3	3322.8	3313.0	3303.3	3273.5	3243.6	3204.1	3164.5	3120.1	3075.6
7.5°	3466.5	3471.3	3476.2	3470.1	3464.0	3456.1	3448.2	3412.9	3377.6	3331.9	3286.3
10°	3299.7	3310.6	3321.6	3345.3	3369.1	3395.8	3422.6	3417.8	3412.9	3399.5	3386.1
12.5°	2933.2	2946.6	2959.9	3007.4	3054.9	3115.8	3176.7	3229.0	3281.4	3317.9	3354.4
15°	2437.6	2474.7	2511.9	2555.1	2598.3	2687.8	2777.3	2887.5	2997.7	3095.7	3193.7
17.5°	2007.8	2021.8	2035.8	2082.1	2128.3	2241.0	2353.6	2480.8	2608.1	2770.6	2933.2
20°	1652.3	1665.0	1677.8	1738.7	1799.6	1887.9	1976.1	2119.2	2262.3	2437.0	2611.7
22.5°	1388.0	1408.1	1428.2	1462.3	1496.4	1581.0	1665.7	1792.9	1920.1	2113.1	2306.1
25°	1215.2	1229.8	1244.4	1265.1	1285.8	1353.3	1420.9	1525.6	1630.3	1807.5	1984.7
27.5°	1097.0	1103.1	1109.2	1129.9	1150.6	1194.5	1238.3	1328.4	1418.5	1568.9	1719.2
30°	1004.5	1008.8	1013.0	1031.3	1049.6	1079.4	1109.2	1174.4	1239.5	1372.2	1504.9
32.5°	940.0	943.0	946.1	960.1	974.1	995.4	1016.7	1064.2	1111.7	1221.2	1330.8
35°	881.5	883.4	885.2	895.5	905.9	921.7	937.5	973.5	1009.4	1095.8	1182.3
37.5°	830.4	832.8	835.3	841.4	847.4	861.4	875.4	904.1	932.7	999.0	1065.4
40°	780.5	784.7	789.0	793.3	797.5	809.1	820.7	842.6	864.5	919.3	974.1
42.5°	737.9	742.1	746.4	748.2	750.0	756.7	763.4	783.5	803.6	844.4	885.2
45°	696.5	698.3	700.1	701.9	703.8	709.2	714.7	732.4	750.0	785.3	820.7
47.5°	658.7	658.7	658.7	659.9	661.1	666.0	670.9	683.7	696.5	723.9	751.3
50°	622.2	622.2	622.2	620.4	618.5	621.6	624.6	634.4	644.1	668.5	692.8
52.5°	578.4	578.4	578.4	579.0	579.6	579.6	579.6	588.1	596.6	618.5	640.4
55°	534.5	537.0	539.4	537.6	535.7	537.0	538.2	543.7	549.1	566.8	584.4
57.5°	490.7	491.9	493.1	492.5	491.9	492.5	493.1	498.0	502.9	516.3	529.6
60°	449.3	449.3	449.3	448.1	446.9	448.1	449.3	451.7	454.2	466.3	478.5
62.5°	403.0	403.6	404.2	404.8	405.5	404.2	403.0	406.1	409.1	418.2	427.4
65°	356.8	357.4	358.0	359.8	361.6	360.4	359.2	362.2	365.3	372.0	378.7
67.5°	315.4	314.1	312.9	313.5	314.1	316.0	317.8	318.4	319.0	326.3	333.6
70°	266.7	267.9	269.1	268.5	267.9	268.5	269.1	270.9	272.7	278.2	283.7
72.5°	222.8	223.4	224.0	224.0	224.0	225.3	226.5	228.3	230.1	233.2	236.2
75°	182.6	182.6	182.6	183.9	185.1	185.7	186.3	186.3	186.3	188.7	191.2
77.5°	138.8	141.8	144.9	144.3	143.7	144.9	146.1	147.9	149.8	151.0	152.2
80°	101.1	101.1	101.1	101.7	102.3	104.1	105.9	107.1	108.4	110.8	113.2
82.5°	64.5	65.1	65.7	67.6	69.4	70.6	71.8	73.7	75.5	75.5	75.5
85°	40.2	39.0	37.7	39.0	40.2	41.4	42.6	43.2	43.8	45.1	46.3
87.5°	19.5	19.5	19.5	19.5	19.5	20.1	20.7	20.7	20.7	20.7	20.7
90°	22.9	23.7	22.9	22.1	22.9	21.3	20.6	19.8	19.0	19.8	17.4
92.5°	41.9	43.5	42.7	45.9	47.4	53.0	60.9	78.3	109.9	147.1	162.9
95°	91.7	94.9	100.4	107.5	122.6	151.0	192.9	284.7	380.3	468.9	417.5
97.5°	188.2	196.9	215.9	245.9	298.9	389.0	493.4	653.9	745.7	721.2	538.5
100°	495.8	495.0	525.8	583.6	663.4	775.7	868.2	932.3	904.6	748.8	506.1
102.5°	785.2	808.1	832.6	875.3	933.1	994.0	1038.2	1024.8	912.5	697.4	458.6
105°	1005.8	1009.8	1035.1	1065.1	1101.5	1122.1	1107.0	1028.0	862.7	635.8	421.5
107.5°	1149.7	1158.4	1168.7	1182.9	1187.7	1166.3	1104.7	980.5	791.5	581.2	394.6
110°	1232.0	1233.6	1235.1	1228.8	1206.7	1151.3	1051.7	906.2	725.1	536.1	380.3



TEST NUMBER: P831194

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1248.6	1247.8	1239.9	1216.9	1171.9	1096.8	982.1	832.6	667.4	506.1	372.4
115°	1223.3	1219.3	1203.5	1168.7	1109.4	1023.2	907.0	769.4	623.1	486.3	371.6
117.5°	1167.9	1162.4	1138.7	1099.9	1038.2	948.9	842.1	720.4	593.8	472.9	372.4
120°	1095.2	1090.4	1071.5	1027.2	964.7	884.8	789.9	683.2	571.7	464.2	375.6
122.5°	1027.2	1020.8	999.5	960.7	907.0	834.2	748.0	653.9	553.5	458.6	381.1
125°	964.7	959.2	939.4	904.6	854.0	790.7	714.8	628.6	538.5	453.9	386.7
127.5°	910.9	906.2	888.0	858.0	812.1	753.6	684.0	605.7	524.3	451.5	393.0
130°	866.6	860.3	843.7	815.3	773.3	719.6	655.5	584.4	513.2	449.1	399.3
132.5°	823.2	819.2	805.0	776.5	737.8	687.2	628.6	564.6	502.9	448.3	404.1
135°	782.0	776.5	762.3	738.5	699.8	654.7	603.3	547.2	494.2	447.6	408.8
137.5°	738.5	733.8	721.9	697.4	664.2	623.9	578.0	530.6	486.3	446.0	412.0
140°	692.7	693.5	680.8	658.7	628.6	594.6	556.7	516.4	479.2	445.2	415.1
142.5°	650.0	650.8	639.7	620.7	596.2	567.8	536.1	502.9	472.9	443.6	417.5
145°	611.2	609.7	603.3	586.7	567.0	544.0	518.7	492.6	467.3	442.0	418.3
147.5°	578.0	577.2	570.9	559.1	543.2	526.6	505.3	483.9	461.8	439.7	418.3
150°	549.6	549.6	544.8	536.1	524.3	509.2	492.6	474.4	456.3	436.5	418.3
152.5°	525.8	525.8	523.5	515.6	506.9	495.0	480.8	465.7	449.9	432.5	415.9
155°	506.9	506.1	504.5	498.2	491.0	481.6	469.7	457.0	443.6	427.8	414.3
157.5°	488.7	488.7	487.1	482.4	476.0	468.1	458.6	447.6	436.5	423.8	412.0
160°	471.3	472.1	472.1	467.3	461.8	456.3	448.3	439.7	429.4	419.1	410.4
162.5°	455.5	456.3	456.3	452.3	449.1	444.4	437.3	430.2	422.3	414.3	407.2
165°	442.0	442.0	442.8	439.7	436.5	432.5	427.0	422.3	415.9	409.6	404.1
167.5°	428.6	428.6	429.4	427.0	425.4	422.3	419.1	415.1	409.6	404.9	400.9
170°	416.7	416.7	417.5	415.9	415.1	413.6	410.4	408.0	404.1	400.1	397.7
172.5°	405.6	406.4	408.0	406.4	406.4	405.6	403.3	401.7	398.5	396.2	395.4
175°	397.7	398.5	399.3	398.5	398.5	398.5	397.0	396.2	394.6	393.0	393.0
177.5°	392.2	392.2	393.8	393.0	393.8	393.8	393.0	392.2	391.4	390.6	391.4
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P831194

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9
2.5°	2806.5	2799.2	2772.4	2745.7	2715.2	2684.8	2662.3	2639.7	2606.2	2572.8	2545.4
5°	3041.5	3007.4	2950.8	2894.2	2817.5	2740.8	2689.0	2637.3	2567.9	2498.5	2443.1
7.5°	3227.8	3169.4	3090.2	3011.1	2910.6	2810.2	2715.2	2620.2	2514.3	2408.4	2321.9
10°	3346.5	3307.0	3215.6	3124.3	2989.8	2855.2	2722.5	2589.8	2453.4	2317.1	2202.6
12.5°	3358.1	3361.8	3277.7	3193.7	3041.5	2889.3	2728.0	2566.7	2395.0	2223.3	2090.0
15°	3256.4	3319.1	3272.9	3226.6	3073.2	2919.8	2721.3	2522.8	2325.0	2127.1	1973.1
17.5°	3067.7	3202.2	3208.9	3215.6	3062.2	2908.8	2689.0	2469.3	2245.2	2021.2	1859.3
20°	2810.2	3008.7	3076.8	3145.0	3020.2	2895.4	2659.2	2423.0	2172.2	1921.3	1751.5
22.5°	2547.2	2788.3	2913.1	3037.9	2945.3	2852.8	2601.4	2349.9	2085.1	1820.3	1648.0
25°	2247.7	2510.7	2702.4	2894.2	2837.6	2781.0	2533.2	2285.4	2003.5	1721.7	1545.7
27.5°	1986.5	2253.8	2485.1	2716.4	2704.3	2692.1	2446.1	2200.2	1911.6	1623.0	1453.2
30°	1753.9	2002.9	2261.7	2520.4	2550.2	2580.1	2342.6	2105.2	1816.0	1526.9	1363.1
32.5°	1548.2	1765.5	2043.1	2320.7	2379.2	2437.6	2223.3	2009.0	1722.9	1436.8	1279.1
35°	1379.5	1576.8	1854.4	2132.0	2205.0	2278.1	2091.8	1905.5	1626.7	1347.9	1197.5
37.5°	1230.4	1395.4	1666.3	1937.2	2026.7	2116.2	1949.4	1782.5	1521.4	1260.2	1122.0
40°	1106.8	1239.5	1488.5	1737.5	1841.0	1944.5	1806.9	1669.3	1421.5	1173.8	1046.5
42.5°	1003.3	1121.4	1347.3	1573.1	1672.4	1771.6	1655.3	1539.0	1318.6	1098.3	982.0
45°	915.0	1009.4	1214.5	1419.7	1514.1	1608.4	1508.6	1408.7	1214.5	1020.3	912.0
47.5°	832.2	913.2	1088.5	1263.9	1347.9	1431.9	1354.0	1276.0	1111.7	947.3	849.3
50°	757.9	823.1	976.5	1129.9	1203.0	1276.0	1207.2	1138.4	1003.3	868.1	782.9
52.5°	693.4	746.4	874.8	1003.3	1066.0	1128.7	1069.6	1010.6	903.4	796.3	722.0
55°	629.5	674.5	786.0	897.4	940.0	982.6	936.9	891.3	804.8	718.4	655.7
57.5°	569.8	610.0	701.3	792.6	825.5	858.4	817.0	775.6	710.5	645.3	593.0
60°	511.4	544.3	620.4	696.5	716.5	736.6	703.2	669.7	624.0	578.4	531.5
62.5°	457.2	487.0	543.7	600.3	613.7	627.1	601.5	575.9	541.2	506.5	470.0
65°	401.2	423.7	470.0	516.3	524.8	533.3	510.8	488.3	462.1	435.9	409.1
67.5°	349.4	365.3	403.0	440.8	441.4	442.0	423.7	405.5	390.8	376.2	354.9
70°	298.9	314.1	339.1	364.1	364.7	365.3	350.7	336.1	325.1	314.1	298.3
72.5°	247.2	258.1	277.0	295.9	294.7	293.4	284.3	275.2	266.7	258.1	246.6
75°	200.3	209.4	222.2	235.0	231.3	227.7	222.8	217.9	210.6	203.3	196.0
77.5°	157.7	163.2	170.5	177.8	175.3	172.9	168.6	164.4	158.9	153.4	150.4
80°	115.7	118.1	123.0	127.8	126.6	125.4	120.5	115.7	114.5	113.2	109.0
82.5°	78.5	81.6	82.8	84.0	83.4	82.8	79.1	75.5	74.3	73.1	72.4
85°	46.9	47.5	48.1	48.7	46.9	45.1	43.8	42.6	42.6	42.6	42.0
87.5°	21.3	21.9	21.9	21.9	21.3	20.7	19.5	18.3	18.9	19.5	19.5
90°	15.0	12.7	10.3	8.7	7.1	4.7	3.2	1.6	3.2	4.7	7.1
92.5°	121.8	79.9	54.6	40.3	32.4	25.3	17.4	11.9	17.4	25.3	32.4
95°	287.8	170.0	102.8	72.0	51.4	38.0	29.3	26.9	29.3	38.0	51.4
97.5°	320.2	183.5	117.0	83.0	62.5	50.6	43.5	42.7	43.5	50.6	62.5
100°	298.1	181.1	125.7	94.9	75.9	64.8	59.3	58.5	59.3	64.8	75.9
102.5°	279.1	184.2	136.0	108.3	91.7	81.4	76.7	75.1	76.7	81.4	91.7
105°	272.0	190.6	147.9	123.4	108.3	98.8	94.1	91.7	94.1	98.8	108.3
107.5°	270.4	200.8	162.9	140.0	125.7	116.2	111.5	109.1	111.5	116.2	125.7
110°	274.4	214.3	178.7	156.6	143.1	134.4	130.5	128.1	130.5	134.4	143.1



TEST NUMBER: P831194

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	282.3	227.7	195.3	174.0	160.5	151.8	147.9	145.5	147.9	151.8	160.5
115°	291.0	242.8	212.7	191.4	177.9	170.0	165.3	162.1	165.3	170.0	177.9
117.5°	302.1	258.6	228.5	208.8	193.7	186.6	182.7	178.7	182.7	186.6	193.7
120°	314.7	273.6	245.1	225.4	210.3	202.4	198.5	196.1	198.5	202.4	210.3
122.5°	326.6	289.4	261.7	240.4	226.2	217.5	213.5	211.1	213.5	217.5	226.2
125°	339.2	304.4	276.8	255.4	240.4	231.7	226.9	225.4	226.9	231.7	240.4
127.5°	349.5	317.9	291.0	269.6	253.0	244.3	238.8	236.4	238.8	244.3	253.0
130°	359.8	329.7	303.6	282.3	265.7	256.2	249.1	246.7	249.1	256.2	265.7
132.5°	369.3	340.0	314.7	294.2	277.5	265.7	257.8	254.6	257.8	265.7	277.5
135°	377.2	350.3	325.8	304.4	287.8	276.0	267.3	264.1	267.3	276.0	287.8
137.5°	383.5	357.4	333.7	313.9	297.3	284.7	276.0	272.8	276.0	284.7	297.3
140°	388.3	364.5	341.6	321.8	306.0	293.4	285.5	281.5	285.5	293.4	306.0
142.5°	393.0	370.1	347.9	329.7	313.9	302.9	294.2	291.0	294.2	302.9	313.9
145°	396.2	374.8	354.3	336.1	322.6	310.8	303.6	301.3	303.6	310.8	322.6
147.5°	398.5	378.8	359.8	344.0	330.5	320.2	313.1	311.6	313.1	320.2	330.5
150°	399.3	382.7	364.5	350.3	339.2	328.9	322.6	321.8	322.6	328.9	339.2
152.5°	400.9	385.1	370.1	356.6	347.1	338.4	332.1	332.1	332.1	338.4	347.1
155°	400.9	388.3	374.8	363.7	355.0	347.1	342.4	342.4	342.4	347.1	355.0
157.5°	401.7	389.8	378.8	370.1	362.2	355.0	351.1	350.3	351.1	355.0	362.2
160°	401.7	392.2	382.7	374.8	369.3	362.9	359.8	359.8	359.8	362.9	369.3
162.5°	400.9	393.0	385.1	378.8	374.0	369.3	366.9	366.9	366.9	369.3	374.0
165°	399.3	393.8	387.5	381.9	378.8	374.8	373.2	374.0	373.2	374.8	378.8
167.5°	398.5	393.8	389.0	385.1	382.7	379.6	378.8	379.6	378.8	379.6	382.7
170°	396.2	393.0	389.0	387.5	385.9	383.5	382.7	384.3	382.7	383.5	385.9
172.5°	395.4	393.0	389.8	389.0	388.3	386.7	386.7	387.5	386.7	386.7	388.3
175°	393.8	392.2	390.6	389.8	389.8	388.3	389.0	389.8	389.0	388.3	389.8
177.5°	393.0	391.4	390.6	390.6	390.6	389.8	390.6	391.4	390.6	389.8	390.6
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P831194

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9	2623.9
2.5°	2518.0	2494.2	2470.5	2452.2	2434.0	2402.9	2371.9	2364.6	2357.2	2346.9	2336.5
5°	2387.7	2329.2	2270.8	2218.4	2166.1	2125.3	2084.5	2057.7	2030.9	2011.5	1992.0
7.5°	2235.5	2147.8	2060.2	1998.1	1936.0	1876.9	1817.9	1799.0	1780.1	1754.5	1729.0
10°	2088.2	1991.4	1894.6	1813.6	1732.6	1674.8	1617.0	1593.8	1570.7	1538.4	1506.2
12.5°	1956.7	1850.7	1744.8	1663.2	1581.6	1525.6	1469.6	1436.1	1402.7	1384.4	1366.1
15°	1819.1	1705.8	1592.6	1517.1	1441.6	1391.1	1340.6	1311.3	1282.1	1264.5	1246.8
17.5°	1697.3	1585.3	1473.3	1400.8	1328.4	1282.1	1235.8	1210.3	1184.7	1171.3	1157.9
20°	1581.6	1472.1	1362.5	1291.9	1221.2	1183.5	1145.7	1129.3	1112.9	1101.9	1091.0
22.5°	1475.7	1368.0	1260.2	1199.9	1139.7	1109.2	1078.8	1067.2	1055.6	1046.5	1037.4
25°	1369.8	1273.6	1177.4	1126.3	1075.1	1050.2	1025.2	1013.6	1002.1	992.9	983.8
27.5°	1283.3	1191.4	1099.5	1055.6	1011.8	992.3	972.9	963.7	954.6	946.1	937.5
30°	1199.3	1117.1	1034.9	997.2	959.5	941.8	924.1	915.0	905.9	898.0	890.1
32.5°	1121.4	1050.8	980.2	945.5	910.8	896.1	881.5	870.6	859.6	853.5	847.4
35°	1047.1	983.8	920.5	891.9	863.3	848.7	834.0	824.9	815.8	810.9	806.0
37.5°	983.8	927.2	870.6	843.2	815.8	801.8	787.8	779.9	771.9	770.1	768.3
40°	919.3	870.6	821.9	795.1	768.3	756.1	743.9	739.1	734.2	733.0	731.8
42.5°	865.7	818.2	770.7	746.4	722.0	711.7	701.3	698.9	696.5	698.3	700.1
45°	803.6	764.0	724.5	701.9	679.4	670.9	662.4	660.5	658.7	662.4	666.0
47.5°	751.3	714.7	678.2	656.9	635.6	629.5	623.4	622.8	622.2	627.1	631.9
50°	697.7	662.4	627.1	610.0	593.0	587.5	582.0	583.8	585.7	593.6	601.5
52.5°	647.8	614.9	582.0	566.2	550.3	546.7	543.0	547.3	551.6	560.1	568.6
55°	593.0	563.1	533.3	521.1	509.0	505.3	501.6	510.2	518.7	526.6	534.5
57.5°	540.6	514.4	488.3	477.3	466.3	465.7	465.1	473.0	480.9	489.5	498.0
60°	484.6	462.7	440.8	432.2	423.7	424.9	426.2	435.3	444.4	451.1	457.8
62.5°	433.5	415.2	396.9	389.0	381.1	384.1	387.2	396.3	405.5	413.4	421.3
65°	382.3	367.1	351.9	346.4	340.9	345.2	349.4	357.4	365.3	370.8	376.2
67.5°	333.6	320.8	308.0	303.8	299.5	303.8	308.0	316.0	323.9	329.4	334.8
70°	282.5	272.1	261.8	258.7	255.7	260.6	265.4	272.1	278.8	284.3	289.8
72.5°	235.0	227.1	219.2	218.6	217.9	222.2	226.5	233.2	239.9	243.5	247.2
75°	188.7	184.5	180.2	179.6	179.0	183.2	187.5	191.2	194.8	197.9	200.9
77.5°	147.3	143.7	140.0	140.6	141.2	144.3	147.3	151.0	154.6	156.5	158.3
80°	104.7	103.5	102.3	103.5	104.7	107.1	109.6	112.0	114.5	115.7	116.9
82.5°	71.8	70.6	69.4	71.2	73.1	74.9	76.7	78.5	80.4	81.0	81.6
85°	41.4	43.2	45.1	45.1	45.1	45.7	46.3	46.9	47.5	46.9	46.3
87.5°	19.5	20.1	20.7	20.7	20.7	21.3	21.9	21.9	21.9	21.3	20.7
90°	8.7	10.3	12.7	15.0	17.4	19.8	19.0	19.8	20.6	21.3	22.9
92.5°	40.3	54.6	79.9	121.8	162.9	147.1	109.9	78.3	60.9	53.0	47.4
95°	72.0	102.8	170.0	287.8	417.5	468.9	380.3	284.7	192.9	151.0	122.6
97.5°	83.0	117.0	183.5	320.2	538.5	721.2	745.7	653.9	493.4	389.0	298.9
100°	94.9	125.7	181.1	298.1	506.1	748.8	904.6	932.3	868.2	775.7	663.4
102.5°	108.3	136.0	184.2	279.1	458.6	697.4	912.5	1024.8	1038.2	994.0	933.1
105°	123.4	147.9	190.6	272.0	421.5	635.8	862.7	1028.0	1107.0	1122.1	1101.5
107.5°	140.0	162.9	200.8	270.4	394.6	581.2	791.5	980.5	1104.7	1166.3	1187.7
110°	156.6	178.7	214.3	274.4	380.3	536.1	725.1	906.2	1051.7	1151.3	1206.7



TEST NUMBER: P831194

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	174.0	195.3	227.7	282.3	372.4	506.1	667.4	832.6	982.1	1096.8	1171.9
115°	191.4	212.7	242.8	291.0	371.6	486.3	623.1	769.4	907.0	1023.2	1109.4
117.5°	208.8	228.5	258.6	302.1	372.4	472.9	593.8	720.4	842.1	948.9	1038.2
120°	225.4	245.1	273.6	314.7	375.6	464.2	571.7	683.2	789.9	884.8	964.7
122.5°	240.4	261.7	289.4	326.6	381.1	458.6	553.5	653.9	748.0	834.2	907.0
125°	255.4	276.8	304.4	339.2	386.7	453.9	538.5	628.6	714.8	790.7	854.0
127.5°	269.6	291.0	317.9	349.5	393.0	451.5	524.3	605.7	684.0	753.6	812.1
130°	282.3	303.6	329.7	359.8	399.3	449.1	513.2	584.4	655.5	719.6	773.3
132.5°	294.2	314.7	340.0	369.3	404.1	448.3	502.9	564.6	628.6	687.2	737.8
135°	304.4	325.8	350.3	377.2	408.8	447.6	494.2	547.2	603.3	654.7	699.8
137.5°	313.9	333.7	357.4	383.5	412.0	446.0	486.3	530.6	578.0	623.9	664.2
140°	321.8	341.6	364.5	388.3	415.1	445.2	479.2	516.4	556.7	594.6	628.6
142.5°	329.7	347.9	370.1	393.0	417.5	443.6	472.9	502.9	536.1	567.8	596.2
145°	336.1	354.3	374.8	396.2	418.3	442.0	467.3	492.6	518.7	544.0	567.0
147.5°	344.0	359.8	378.8	398.5	418.3	439.7	461.8	483.9	505.3	526.6	543.2
150°	350.3	364.5	382.7	399.3	418.3	436.5	456.3	474.4	492.6	509.2	524.3
152.5°	356.6	370.1	385.1	400.9	415.9	432.5	449.9	465.7	480.8	495.0	506.9
155°	363.7	374.8	388.3	400.9	414.3	427.8	443.6	457.0	469.7	481.6	491.0
157.5°	370.1	378.8	389.8	401.7	412.0	423.8	436.5	447.6	458.6	468.1	476.0
160°	374.8	382.7	392.2	401.7	410.4	419.1	429.4	439.7	448.3	456.3	461.8
162.5°	378.8	385.1	393.0	400.9	407.2	414.3	422.3	430.2	437.3	444.4	449.1
165°	381.9	387.5	393.8	399.3	404.1	409.6	415.9	422.3	427.0	432.5	436.5
167.5°	385.1	389.0	393.8	398.5	400.9	404.9	409.6	415.1	419.1	422.3	425.4
170°	387.5	389.0	393.0	396.2	397.7	400.1	404.1	408.0	410.4	413.6	415.1
172.5°	389.0	389.8	393.0	395.4	395.4	396.2	398.5	401.7	403.3	405.6	406.4
175°	389.8	390.6	392.2	393.8	393.0	393.0	394.6	396.2	397.0	398.5	398.5
177.5°	390.6	390.6	391.4	393.0	391.4	390.6	391.4	392.2	393.0	393.8	393.8
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P831194

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2623.9	2623.9	2623.9	2623.9
2.5°	2332.3	2328.0	2311.0	2293.9
5°	1977.4	1962.7	1957.9	1953.0
7.5°	1727.8	1726.5	1701.0	1675.4
10°	1508.0	1509.8	1486.7	1463.5
12.5°	1350.9	1335.7	1333.9	1332.0
15°	1232.8	1218.8	1216.4	1213.9
17.5°	1149.4	1140.9	1138.4	1136.0
20°	1086.1	1081.2	1077.0	1072.7
22.5°	1031.3	1025.2	1021.6	1017.9
25°	978.3	972.9	971.6	970.4
27.5°	930.8	924.1	924.1	924.1
30°	885.8	881.5	879.7	877.9
32.5°	843.8	840.1	840.1	840.1
35°	804.2	802.4	800.0	797.5
37.5°	768.3	768.3	767.1	765.9
40°	733.6	735.4	735.4	735.4
42.5°	701.9	703.8	703.8	703.8
45°	669.1	672.1	673.3	674.5
47.5°	636.8	641.7	642.9	644.1
50°	605.1	608.8	609.4	610.0
52.5°	572.9	577.1	580.2	583.2
55°	538.8	543.0	544.9	546.7
57.5°	502.3	506.5	507.1	507.7
60°	462.1	466.3	467.6	468.8
62.5°	423.7	426.2	427.4	428.6
65°	379.9	383.5	386.0	388.4
67.5°	337.9	340.9	340.9	340.9
70°	291.0	292.2	294.0	295.9
72.5°	247.8	248.4	248.4	248.4
75°	202.1	203.3	203.9	204.6
77.5°	158.9	159.5	159.5	159.5
80°	116.3	115.7	115.7	115.7
82.5°	79.8	77.9	77.9	77.9
85°	45.7	45.1	45.7	46.3
87.5°	20.7	20.7	20.7	20.7
90°	22.1	22.9	23.7	22.9
92.5°	45.9	42.7	43.5	41.9
95°	107.5	100.4	94.9	91.7
97.5°	245.9	215.9	196.9	188.2
100°	583.6	525.8	495.0	495.8
102.5°	875.3	832.6	808.1	785.2
105°	1065.1	1035.1	1009.8	1005.8
107.5°	1182.9	1168.7	1158.4	1149.7
110°	1228.8	1235.1	1233.6	1232.0



TEST NUMBER: P831194

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	1216.9	1239.9	1247.8	1248.6
115°	1168.7	1203.5	1219.3	1223.3
117.5°	1099.9	1138.7	1162.4	1167.9
120°	1027.2	1071.5	1090.4	1095.2
122.5°	960.7	999.5	1020.8	1027.2
125°	904.6	939.4	959.2	964.7
127.5°	858.0	888.0	906.2	910.9
130°	815.3	843.7	860.3	866.6
132.5°	776.5	805.0	819.2	823.2
135°	738.5	762.3	776.5	782.0
137.5°	697.4	721.9	733.8	738.5
140°	658.7	680.8	693.5	692.7
142.5°	620.7	639.7	650.8	650.0
145°	586.7	603.3	609.7	611.2
147.5°	559.1	570.9	577.2	578.0
150°	536.1	544.8	549.6	549.6
152.5°	515.6	523.5	525.8	525.8
155°	498.2	504.5	506.1	506.9
157.5°	482.4	487.1	488.7	488.7
160°	467.3	472.1	472.1	471.3
162.5°	452.3	456.3	456.3	455.5
165°	439.7	442.8	442.0	442.0
167.5°	427.0	429.4	428.6	428.6
170°	415.9	417.5	416.7	416.7
172.5°	406.4	408.0	406.4	405.6
175°	398.5	399.3	398.5	397.7
177.5°	393.0	393.8	392.2	392.2
180°	390.6	390.6	390.6	390.6



TEST NUMBER: P831194

CATALOG NUMBER: S123DIP-S1165D1025U927-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.97	16.88	16.86	17.78	18.92	18.21	19.11	19.09	20.01	21.15
	3H	17.62	18.43	18.52	19.34	20.51	19.64	20.45	20.53	21.36	22.52
	4H	18.20	18.97	19.12	19.88	21.06	20.09	20.85	21.00	21.77	22.94
	6H	18.58	19.28	19.50	20.20	21.39	20.37	21.07	21.29	21.99	23.18
	8H	18.67	19.34	19.61	20.28	21.47	20.43	21.10	21.36	22.04	23.23
	12H	18.72	19.36	19.66	20.29	21.50	20.45	21.09	21.39	22.02	23.23
4H	2H	16.55	17.32	17.47	18.23	19.41	18.38	19.14	19.30	20.06	21.23
	3H	18.39	19.02	19.31	19.97	21.16	20.00	20.64	20.93	21.58	22.77
	4H	19.09	19.67	20.02	20.61	21.82	20.59	21.17	21.52	22.11	23.32
	6H	19.56	20.06	20.51	21.03	22.24	20.99	21.49	21.94	22.46	23.67
	8H	19.70	20.17	20.65	21.12	22.35	21.11	21.57	22.06	22.53	23.76
	12H	19.77	20.19	20.74	21.17	22.40	21.15	21.57	22.12	22.55	23.78
8H	4H	19.36	19.82	20.31	20.78	22.01	20.70	21.16	21.65	22.12	23.35
	6H	19.95	20.33	20.92	21.33	22.56	21.20	21.58	22.18	22.58	23.81
	8H	20.15	20.49	21.14	21.48	22.73	21.38	21.72	22.37	22.71	23.95
	12H	20.28	20.58	21.27	21.56	22.85	21.48	21.78	22.47	22.76	24.06
12H	4H	19.36	19.78	20.33	20.75	21.99	20.67	21.09	21.64	22.07	23.30
	6H	20.00	20.34	20.98	21.32	22.57	21.21	21.55	22.20	22.54	23.79
	8H	20.23	20.53	21.22	21.51	22.81	21.42	21.71	22.41	22.70	23.99