

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331426

Luminaire Tested: **S122DIP-S1005D330U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331426
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S1005D330U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5365.5 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331426

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331426

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	113	113	113	113	108	108	108	108	98	98	98	88	88	88	80	80	80	80	80	80	80	80	80	76														
1	104	99	95	91	98	94	91	88	86	83	80	78	76	74	70	69	67	67	67	67	67	67	67	64														
2	94	87	80	75	89	83	77	72	75	71	67	68	65	62	62	59	57	57	57	57	57	57	57	53														
3	86	76	68	62	82	73	66	60	66	61	56	60	56	52	55	51	48	48	48	48	48	48	48	45														
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42	42	42	42	42	42	42	39														
5	73	60	52	46	69	58	50	44	53	47	42	49	43	39	44	40	36	36	36	36	36	36	36	34														
6	67	54	46	40	64	52	44	39	48	41	36	44	38	34	40	36	32	32	32	32	32	32	32	30														
7	62	49	41	35	59	47	40	34	44	37	32	40	35	30	37	32	29	29	29	29	29	29	29	26														
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	26	26	26	26	26	26	24														
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23	23	23	23	23	23	23	21														
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21	21	21	21	21	21	21	19														

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25733	25733	25733
5°	25832	25459	25608
10°	25678	25201	25327
15°	25361	24874	24849
20°	24911	24383	24357
25°	24464	23779	23779
30°	23886	23228	23029
35°	23349	22565	22231
40°	22675	21901	21479
45°	22012	21240	20717
50°	21288	20557	19826
55°	20535	19758	19023
60°	19695	18807	18112
65°	18793	17857	17039
70°	17651	16711	15918
75°	16064	15390	15009
80°	14254	13826	13110
85°	11634	11078	9930



TEST NUMBER: P331426

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.9	2.8
10°-20°	421.7	7.9
20°-30°	619.8	11.6
30°-40°	720.0	13.4
40°-50°	719.2	13.4
50°-60°	627.2	11.7
60°-70°	463.8	8.6
70°-80°	262.7	4.9
80°-90°	71.7	1.3
90°-100°	14.9	0.3
100°-110°	54.7	1.0
110°-120°	146.1	2.7
120°-130°	241.2	4.5
130°-140°	256.5	4.8
140°-150°	238.4	4.4
150°-160°	191.7	3.6
160°-170°	123.5	2.3
170°-180°	42.5	0.8
0°-30°	1191.4	22.2
0°-40°	1911.4	35.6
0°-60°	3257.9	60.7
0°-90°	4056.0	75.6
90°-120°	215.7	4.0
90°-150°	951.8	17.7
90°-180°	1309.0	24.4
0°-180°	5365.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1594	1587	1571	1582	1580	151
15°	1517	1507	1488	1493	1487	427
25°	1373	1360	1335	1338	1335	631
35°	1185	1169	1145	1136	1128	739
45°	964	953	930	914	907	744
55°	730	720	702	684	676	652
65°	492	482	467	454	446	486
75°	258	254	247	238	241	275
85°	63	61	60	55	54	72
90°	0	4	6	8	9	4
95°	21	11	13	14	14	26
105°	98	103	20	23	25	105
115°	186	192	200	57	26	183
125°	263	267	273	275	276	234
135°	325	330	333	336	336	251
145°	377	377	382	385	383	236
155°	416	413	416	418	416	191
165°	438	436	437	439	437	124
175°	448	446	446	448	445	43
180°	447	447	447	447	447	



TEST NUMBER: P331426

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1601.2	1599.8	1598.5	1597.1	1595.7	1593.6	1590.6	1587.6	1584.6	1581.6	1584.3
5°	1593.8	1592.5	1591.1	1589.7	1588.4	1585.8	1582.1	1578.3	1574.6	1570.8	1573.6
7.5°	1579.7	1577.6	1575.5	1573.4	1571.3	1568.3	1564.5	1560.7	1556.9	1553.1	1555.8
10°	1566.2	1563.9	1561.5	1559.1	1556.7	1553.5	1549.4	1545.3	1541.2	1537.1	1539.9
12.5°	1547.9	1545.7	1543.6	1541.5	1539.4	1536.3	1532.2	1528.1	1524.1	1520.0	1521.9
15°	1517.2	1515.2	1513.1	1511.1	1509.0	1505.8	1501.4	1496.9	1492.5	1488.1	1489.5
17.5°	1478.0	1475.9	1473.9	1471.8	1469.8	1466.5	1462.0	1457.5	1453.0	1448.6	1450.1
20°	1449.8	1447.7	1445.7	1443.6	1441.6	1438.2	1433.4	1428.7	1423.9	1419.1	1420.1
22.5°	1421.6	1418.7	1415.9	1413.0	1410.1	1406.5	1402.0	1397.5	1393.0	1388.5	1388.7
25°	1373.2	1370.4	1367.7	1365.0	1362.3	1358.0	1352.2	1346.4	1340.6	1334.8	1335.5
27.5°	1318.0	1315.5	1313.1	1310.6	1308.2	1304.7	1300.1	1295.5	1291.0	1286.4	1285.4
30°	1281.2	1278.5	1275.7	1273.0	1270.3	1266.4	1261.3	1256.2	1251.1	1245.9	1244.9
32.5°	1242.0	1239.8	1237.6	1235.4	1233.2	1229.5	1224.1	1218.7	1213.3	1207.9	1206.1
35°	1184.6	1181.2	1177.8	1174.4	1171.0	1166.6	1161.1	1155.7	1150.3	1144.8	1142.8
37.5°	1120.0	1117.0	1114.0	1111.0	1108.0	1103.8	1098.3	1092.9	1087.4	1082.0	1079.4
40°	1075.8	1073.1	1070.4	1067.7	1064.9	1060.9	1055.4	1050.0	1044.5	1039.1	1036.0
42.5°	1032.9	1030.2	1027.5	1024.8	1022.0	1017.9	1012.5	1007.0	1001.6	996.1	992.8
45°	964.0	961.6	959.2	956.8	954.4	950.7	945.6	940.5	935.4	930.2	926.5
47.5°	895.3	893.1	890.8	888.6	886.3	882.5	877.2	871.9	866.6	861.3	857.3
50°	847.5	845.8	844.1	842.4	840.7	837.4	832.7	827.9	823.1	818.4	813.6
52.5°	800.9	798.7	796.4	794.2	791.9	788.5	784.0	779.5	775.1	770.6	766.6
55°	729.5	727.4	725.4	723.4	721.3	718.2	714.2	710.1	706.0	701.9	697.8
57.5°	657.8	656.1	654.5	652.9	651.2	648.2	643.7	639.2	634.7	630.2	626.2
60°	609.9	608.6	607.2	605.9	604.5	601.4	596.7	591.9	587.1	582.4	578.6
62.5°	563.4	561.2	559.0	556.8	554.6	551.7	548.0	544.4	540.7	537.0	533.5
65°	491.9	489.9	487.9	485.8	483.8	481.0	477.6	474.2	470.8	467.4	464.4
67.5°	419.3	417.7	416.0	414.4	412.8	410.4	407.3	404.3	401.2	398.2	395.8
70°	373.9	372.6	371.2	369.9	368.5	366.3	363.2	360.1	357.1	354.0	351.6
72.5°	327.3	326.0	324.6	323.3	321.9	320.2	318.3	316.3	314.3	312.3	309.9
75°	257.5	256.8	256.1	255.4	254.7	253.5	251.8	250.1	248.4	246.7	244.7
77.5°	194.9	193.8	192.6	191.5	190.3	189.4	188.7	188.0	187.3	186.7	185.6
80°	153.3	152.9	152.6	152.2	151.9	151.4	150.7	150.0	149.3	148.7	147.6
82.5°	114.0	114.0	113.9	113.8	113.7	113.5	113.1	112.7	112.3	111.9	110.6
85°	62.8	62.5	62.2	61.8	61.5	61.1	60.8	60.4	60.1	59.8	58.7
87.5°	22.1	21.7	21.4	21.0	20.6	20.2	19.7	19.3	18.9	18.5	17.7
90°	0.3	1.1	1.9	2.7	3.5	4.2	4.7	5.3	5.9	6.5	6.8
92.5°	6.5	6.5	6.4	6.3	6.2	6.4	6.6	6.9	7.2	7.5	7.7
95°	21.0	18.6	16.3	13.9	11.5	10.6	11.1	11.6	12.1	12.6	13.0
97.5°	41.7	35.0	28.3	21.7	15.0	12.2	13.4	14.5	15.7	16.9	17.2
100°	57.2	47.4	37.5	27.7	17.9	13.5	14.8	16.0	17.2	18.4	19.0
102.5°	74.3	72.2	70.1	68.1	66.0	59.8	49.6	39.4	29.2	18.9	19.7
105°	98.3	100.4	102.6	104.8	106.9	98.2	78.6	59.0	39.3	19.7	20.5
107.5°	125.6	127.4	129.1	130.9	132.6	121.7	98.2	74.7	51.1	27.6	26.8
110°	143.2	144.7	146.3	147.8	149.3	139.6	118.9	98.1	77.3	56.6	49.4



TEST NUMBER: P331426

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	159.8	161.1	162.5	163.8	165.1	163.2	158.1	153.0	147.8	142.7	116.5
115°	185.9	187.1	188.4	189.6	190.8	192.3	194.1	195.9	197.7	199.5	166.2
117.5°	209.3	210.6	212.0	213.4	214.7	216.0	217.3	218.5	219.7	221.0	212.9
120°	226.3	227.4	228.5	229.6	230.6	231.8	233.1	234.4	235.7	237.0	237.9
122.5°	240.8	242.0	243.1	244.2	245.4	246.6	248.0	249.4	250.9	252.3	252.8
125°	262.9	263.8	264.7	265.7	266.6	267.8	269.1	270.5	271.8	273.2	273.7
127.5°	282.8	283.9	284.9	286.0	287.0	288.0	289.0	290.1	291.1	292.1	292.8
130°	295.5	296.7	297.8	299.0	300.1	301.1	301.9	302.7	303.5	304.3	305.0
132.5°	308.5	309.4	310.4	311.4	312.4	313.2	314.0	314.8	315.6	316.4	317.1
135°	325.3	326.4	327.6	328.7	329.9	330.8	331.4	332.1	332.7	333.4	334.1
137.5°	342.3	343.1	343.9	344.7	345.5	346.3	347.0	347.7	348.5	349.2	349.9
140°	353.4	354.0	354.5	355.1	355.7	356.4	357.2	358.0	358.8	359.5	360.2
142.5°	362.7	363.2	363.7	364.3	364.8	365.5	366.4	367.3	368.2	369.1	369.7
145°	377.3	377.3	377.2	377.1	377.0	377.6	378.8	380.1	381.3	382.5	383.0
147.5°	390.1	389.8	389.5	389.2	389.0	389.4	390.6	391.9	393.1	394.3	394.6
150°	398.3	397.8	397.3	396.8	396.3	396.7	397.8	399.0	400.1	401.3	401.7
152.5°	405.3	404.8	404.2	403.6	403.1	403.3	404.4	405.5	406.6	407.7	408.1
155°	415.5	414.8	414.2	413.5	412.9	413.0	413.9	414.7	415.6	416.4	416.9
157.5°	423.4	422.9	422.3	421.8	421.2	421.3	421.9	422.5	423.1	423.7	424.2
160°	428.1	427.7	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1	428.5
162.5°	432.2	431.8	431.4	430.9	430.5	430.5	430.8	431.2	431.6	432.0	432.5
165°	437.8	437.4	436.9	436.5	436.1	436.0	436.2	436.4	436.6	436.8	437.3
167.5°	441.9	441.5	441.1	440.6	440.2	440.1	440.3	440.5	440.7	440.9	441.4
170°	444.3	443.8	443.4	443.0	442.5	442.4	442.5	442.7	442.8	443.0	443.5
172.5°	445.8	445.4	444.9	444.5	444.1	443.9	444.1	444.2	444.4	444.5	445.0
175°	447.8	447.3	446.8	446.3	445.8	445.6	445.8	445.9	446.1	446.2	446.7
177.5°	448.1	447.7	447.3	446.9	446.5	446.4	446.4	446.5	446.5	446.6	447.0
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331426

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1587.0	1589.7	1592.5	1593.6	1593.0	1592.5	1591.9	1591.4
5°	1576.3	1579.0	1581.7	1582.8	1582.1	1581.4	1580.7	1580.0
7.5°	1558.5	1561.2	1564.0	1565.0	1564.2	1563.5	1562.7	1562.0
10°	1542.6	1545.3	1548.0	1548.9	1547.9	1546.8	1545.8	1544.8
12.5°	1523.8	1525.7	1527.6	1528.2	1527.4	1526.7	1525.9	1525.2
15°	1490.8	1492.2	1493.5	1493.4	1491.7	1490.0	1488.3	1486.6
17.5°	1451.7	1453.3	1454.8	1454.8	1453.1	1451.5	1449.9	1448.2
20°	1421.2	1422.2	1423.2	1423.0	1421.7	1420.3	1419.0	1417.6
22.5°	1388.9	1389.1	1389.3	1389.0	1388.2	1387.4	1386.5	1385.7
25°	1336.2	1336.9	1337.6	1337.6	1336.9	1336.2	1335.5	1334.8
27.5°	1284.4	1283.3	1282.3	1281.0	1279.4	1277.7	1276.1	1274.5
30°	1243.9	1242.9	1241.9	1240.7	1239.3	1237.9	1236.6	1235.2
32.5°	1204.3	1202.4	1200.6	1199.0	1197.6	1196.3	1194.9	1193.5
35°	1140.7	1138.7	1136.6	1134.8	1133.1	1131.4	1129.6	1127.9
37.5°	1076.9	1074.4	1071.9	1069.8	1068.2	1066.5	1064.9	1063.3
40°	1032.9	1029.9	1026.8	1024.6	1023.2	1021.9	1020.5	1019.1
42.5°	989.5	986.1	982.8	980.2	978.3	976.4	974.5	972.5
45°	922.8	919.0	915.3	912.7	911.3	910.0	908.6	907.3
47.5°	853.4	849.4	845.5	842.5	840.5	838.6	836.6	834.6
50°	808.8	804.1	799.3	796.1	794.4	792.7	791.0	789.3
52.5°	762.7	758.7	754.8	751.7	749.4	747.2	744.9	742.7
55°	693.7	689.6	685.6	682.7	681.0	679.3	677.6	675.8
57.5°	622.1	618.1	614.1	611.4	610.2	608.9	607.6	606.3
60°	574.9	571.1	567.4	565.0	564.0	563.0	561.9	560.9
62.5°	530.1	526.6	523.1	520.7	519.4	518.1	516.8	515.5
65°	461.3	458.2	455.2	452.8	451.1	449.4	447.7	446.0
67.5°	393.4	391.0	388.6	386.7	385.4	384.0	382.7	381.3
70°	349.2	346.9	344.5	342.6	341.2	339.9	338.5	337.2
72.5°	307.6	305.2	302.8	301.1	300.0	298.9	297.8	296.7
75°	242.7	240.6	238.6	237.9	238.6	239.2	239.9	240.6
77.5°	184.6	183.6	182.6	181.6	180.6	179.7	178.7	177.8
80°	146.6	145.6	144.6	143.7	143.0	142.4	141.7	141.0
82.5°	109.3	108.0	106.7	106.0	105.8	105.7	105.6	105.4
85°	57.7	56.7	55.7	55.0	54.7	54.3	54.0	53.6
87.5°	17.0	16.2	15.5	15.0	14.7	14.5	14.2	14.0
90°	7.2	7.5	7.9	8.2	8.3	8.4	8.6	8.7
92.5°	7.9	8.1	8.2	8.4	8.5	8.6	8.6	8.7
95°	13.3	13.7	14.0	14.2	14.1	14.0	14.0	13.9
97.5°	17.5	17.7	18.0	18.2	18.3	18.4	18.5	18.6
100°	19.6	20.2	20.7	21.1	21.2	21.4	21.5	21.7
102.5°	20.4	21.2	21.9	22.4	22.6	22.8	23.0	23.2
105°	21.3	22.1	22.9	23.4	23.7	24.0	24.3	24.6
107.5°	26.0	25.2	24.4	24.1	24.4	24.7	25.0	25.3
110°	42.2	35.0	27.8	24.4	24.7	25.0	25.3	25.5



TEST NUMBER: P331426

CATALOG NUMBER: S122DIP-S1005D330U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	90.3	64.1	37.9	24.9	25.1	25.3	25.6	25.8
115°	133.0	99.7	66.4	47.2	42.0	36.9	31.7	26.5
117.5°	204.9	196.8	188.8	176.3	159.3	142.3	125.3	108.3
120°	238.7	239.6	240.4	236.0	226.3	216.6	206.9	197.2
122.5°	253.3	253.8	254.3	253.6	251.8	249.9	248.0	246.1
125°	274.2	274.7	275.2	275.6	275.8	276.0	276.2	276.4
127.5°	293.6	294.3	295.0	295.4	295.5	295.5	295.5	295.6
130°	305.8	306.6	307.4	307.8	307.7	307.6	307.6	307.5
132.5°	317.8	318.4	319.1	319.4	319.3	319.3	319.2	319.1
135°	334.8	335.5	336.2	336.5	336.4	336.2	336.1	335.9
137.5°	350.6	351.3	352.0	352.2	352.0	351.8	351.5	351.3
140°	360.8	361.5	362.1	362.3	361.9	361.6	361.2	360.8
142.5°	370.3	370.9	371.5	371.6	371.2	370.9	370.5	370.1
145°	383.5	384.0	384.5	384.6	384.2	383.9	383.5	383.1
147.5°	395.0	395.4	395.8	395.8	395.5	395.2	394.9	394.6
150°	402.1	402.5	403.0	403.0	402.7	402.3	401.9	401.6
152.5°	408.6	409.0	409.4	409.4	408.9	408.5	408.0	407.5
155°	417.3	417.7	418.2	418.1	417.5	417.0	416.4	415.8
157.5°	424.7	425.2	425.6	425.6	425.0	424.5	423.9	423.4
160°	429.0	429.4	429.8	429.8	429.3	428.8	428.3	427.8
162.5°	432.9	433.4	433.9	433.9	433.2	432.6	432.0	431.4
165°	437.8	438.3	438.8	438.8	438.3	437.8	437.3	436.8
167.5°	441.9	442.4	442.9	442.8	442.2	441.5	440.9	440.2
170°	444.0	444.5	445.0	444.9	444.3	443.6	443.0	442.3
172.5°	445.5	446.0	446.5	446.5	445.8	445.2	444.5	443.9
175°	447.2	447.7	448.2	448.1	447.4	446.7	445.9	445.2
177.5°	447.4	447.8	448.2	448.1	447.6	447.1	446.6	446.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8

(END OF REPORT)