

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332082-927

Luminaire Tested: **S123DIP-S1165D1195U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332082-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1195U927-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7128.3 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332082-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332082-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	64	54	47	42	47	42	37	41	36	33	34	31	28	25
6	64	52	44	38	59	49	42	36	43	37	33	37	32	29	31	28	25	22
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	29	25	22	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13832	13832	13832	13832
5°	16495	13891	12310	13891
10°	20647	13821	11119	13821
15°	25324	13710	10351	13710
20°	30166	13536	9856	13536
25°	32033	13324	9745	13324
30°	27455	13170	9797	13170
35°	19094	12951	9900	12951
40°	14383	12694	9868	12694
45°	11942	12310	9742	12310
50°	10697	11531	9656	11531
55°	10001	10691	9533	10691
60°	9382	9810	9436	9810
65°	8818	8945	9133	8945
70°	8271	7956	8699	7956
75°	7407	6966	7977	6966
80°	6484	5709	6868	5709
85°	5076	4150	4619	4150



TEST NUMBER: P332082-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.6	1.8
10°-20°	405.9	5.7
20°-30°	681.2	9.6
30°-40°	771.4	10.8
40°-50°	691.7	9.7
50°-60°	558.2	7.8
60°-70°	389.0	5.5
70°-80°	204.5	2.9
80°-90°	53.5	0.8
90°-100°	76.3	1.1
100°-110°	228.5	3.2
110°-120°	388.6	5.5
120°-130°	511.1	7.2
130°-140°	574.5	8.1
140°-150°	564.7	7.9
150°-160°	475.4	6.7
160°-170°	316.5	4.4
170°-180°	110.8	1.6
0°-30°	1213.7	17.0
0°-40°	1985.1	27.8
0°-60°	3235.0	45.4
0°-90°	3882.0	54.5
90°-120°	693.4	9.7
90°-150°	2343.7	32.9
90°-180°	3246.0	45.5
0°-180°	7128.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1285	1285	1285	1285	1285	
5°	1527	1286	1139	1286	1527	158
15°	2272	1230	929	1230	2272	656
25°	2697	1122	820	1122	2697	1183
35°	1453	986	753	986	1453	944
45°	784	809	640	809	784	621
55°	533	570	508	570	533	478
65°	346	351	359	351	346	345
75°	178	168	192	168	178	191
85°	41	34	37	34	41	49
90°	28	1	28	1	28	15
95°	72	54	72	54	72	74
105°	219	207	219	207	219	232
115°	392	391	392	391	392	388
125°	566	572	566	572	566	506
135°	742	743	742	743	742	570
145°	901	901	901	901	901	562
155°	1030	1032	1030	1032	1030	474
165°	1120	1124	1120	1124	1120	316
175°	1164	1169	1164	1169	1164	111
180°	1172	1172	1172	1172	1172	



TEST NUMBER: P332082-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1363.7	1362.7	1360.3	1362.2	1358.3	1352.7	1352.3	1347.3	1332.8	1331.8	1327.9
5°	1526.6	1521.6	1521.0	1520.4	1511.6	1499.8	1477.4	1475.5	1445.7	1430.7	1412.7
7.5°	1737.5	1740.1	1731.1	1723.1	1696.5	1678.9	1654.9	1624.1	1587.4	1550.1	1525.3
10°	1889.0	1909.5	1884.0	1866.5	1850.4	1819.8	1784.4	1740.1	1695.9	1644.3	1605.0
12.5°	2051.4	2061.4	2056.3	2039.9	2014.7	1968.3	1905.4	1856.7	1816.0	1730.0	1695.2
15°	2272.5	2310.5	2286.2	2230.2	2231.3	2187.1	2105.0	2014.7	1966.8	1891.4	1788.7
17.5°	2508.0	2512.8	2502.4	2455.8	2424.6	2363.9	2288.1	2201.5	2104.4	2013.3	1904.2
20°	2633.5	2629.8	2608.0	2583.8	2530.2	2482.9	2400.1	2303.6	2179.1	2089.5	1970.5
22.5°	2703.3	2697.1	2686.8	2666.4	2621.9	2571.0	2496.7	2391.3	2272.7	2149.2	2011.8
25°	2697.1	2705.1	2706.4	2700.8	2685.3	2654.8	2596.2	2512.2	2393.9	2235.1	2091.9
27.5°	2453.0	2464.5	2497.8	2527.2	2560.3	2593.8	2589.3	2547.7	2460.1	2323.0	2147.9
30°	2208.9	2184.0	2245.7	2323.5	2376.5	2469.8	2522.1	2525.2	2476.0	2358.4	2187.8
32.5°	1870.3	1897.7	1924.9	2020.7	2136.4	2241.2	2345.3	2429.1	2438.7	2360.4	2211.2
35°	1453.1	1487.4	1537.2	1587.0	1711.5	1818.6	2001.6	2161.0	2288.1	2304.9	2213.3
37.5°	1171.0	1187.9	1219.4	1269.3	1350.8	1477.8	1619.4	1820.8	2004.9	2141.7	2147.7
40°	1023.6	1028.5	1064.0	1102.0	1168.0	1272.6	1400.2	1578.3	1798.6	1989.8	2069.5
42.5°	913.0	923.9	939.0	975.5	1028.0	1106.8	1225.4	1372.5	1574.5	1794.5	1950.4
45°	784.5	796.9	806.3	830.5	867.9	920.8	1003.6	1138.1	1291.9	1519.1	1728.9
47.5°	699.6	700.5	707.5	725.8	751.2	790.9	849.5	935.9	1077.1	1261.4	1476.8
50°	638.8	648.7	651.3	665.5	685.5	714.7	763.3	836.8	952.6	1114.4	1312.4
52.5°	596.0	599.0	605.9	616.2	633.7	656.5	698.5	756.1	847.0	984.9	1167.0
55°	532.9	532.9	539.8	547.9	557.9	578.4	606.4	648.7	717.9	824.9	975.6
57.5°	474.7	477.8	482.6	485.1	493.6	507.2	530.6	562.7	614.3	696.6	816.5
60°	435.8	441.4	440.8	445.8	453.3	463.8	483.8	509.9	556.0	621.9	722.9
62.5°	402.0	401.6	401.5	407.4	414.9	425.0	437.9	460.6	499.7	558.3	644.1
65°	346.2	344.9	349.3	353.0	355.5	363.0	373.0	392.8	419.0	462.6	529.2
67.5°	296.6	293.0	295.3	296.6	300.9	306.7	316.0	328.4	349.1	384.1	434.4
70°	262.8	259.6	259.0	260.2	264.0	268.3	275.2	287.0	306.3	334.3	371.1
72.5°	227.8	225.8	225.6	228.4	230.1	233.0	237.8	248.7	264.0	285.0	319.2
75°	178.1	178.1	178.1	178.7	180.5	183.1	186.8	192.3	204.2	219.1	242.2
77.5°	133.5	133.3	132.6	132.5	135.2	136.3	137.2	142.4	149.0	159.1	175.9
80°	104.6	101.5	102.7	104.6	105.8	106.5	108.4	109.6	115.2	120.8	132.6
82.5°	77.7	75.1	75.3	78.2	78.4	79.1	81.0	82.7	84.8	89.9	96.3
85°	41.1	41.1	41.7	41.7	42.3	41.7	43.6	44.2	44.2	47.3	51.0
87.5°	20.4	19.4	19.8	20.2	19.6	20.0	20.4	20.7	21.0	21.4	21.3
90°	27.6	27.2	26.8	26.4	26.0	25.3	24.6	23.8	22.9	22.1	19.4
92.5°	37.2	37.4	37.7	37.9	38.2	37.9	37.3	36.7	36.0	35.3	33.8
95°	71.8	71.8	71.8	71.8	71.8	71.4	70.6	69.7	68.9	68.1	66.5
97.5°	110.4	110.5	110.6	110.7	110.7	110.4	109.4	108.4	107.5	106.5	105.4
100°	139.9	139.5	139.1	138.7	138.2	137.8	137.1	136.5	135.9	135.3	134.3
102.5°	170.1	170.2	170.2	170.3	170.4	170.2	169.5	168.9	168.3	167.7	166.4
105°	219.0	218.6	218.2	217.9	217.5	217.2	217.2	217.2	217.2	217.2	215.4
107.5°	270.1	270.3	270.5	270.8	271.0	270.8	270.2	269.5	268.9	268.2	267.4
110°	304.7	305.1	305.5	305.9	306.3	306.1	305.3	304.4	303.6	302.9	302.4



TEST NUMBER: P332082-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	341.5	341.6	341.7	341.7	341.8	341.4	340.4	339.4	338.4	337.4	337.3
115°	392.1	392.3	392.5	392.7	392.9	392.9	392.7	392.5	392.3	392.1	392.5
117.5°	443.5	444.0	444.6	445.2	445.8	446.1	446.1	446.2	446.2	446.2	446.8
120°	479.5	480.0	480.4	480.8	481.2	481.5	481.7	481.9	482.1	482.3	483.3
122.5°	514.1	514.7	515.3	515.9	516.4	517.0	517.5	518.1	518.6	519.1	519.7
125°	566.1	566.9	567.7	568.5	569.3	570.1	571.0	571.8	572.6	573.5	573.9
127.5°	617.8	618.7	619.6	620.6	621.5	622.6	623.8	624.9	626.1	627.2	627.6
130°	651.6	653.1	654.5	655.9	657.4	658.5	659.3	660.1	661.0	661.8	662.4
132.5°	687.0	688.1	689.2	690.3	691.4	692.4	693.5	694.4	695.4	696.4	696.8
135°	741.9	742.3	742.7	743.1	743.5	744.1	744.9	745.8	746.6	747.3	747.6
137.5°	790.3	791.1	791.9	792.6	793.4	794.2	795.0	795.9	796.8	797.6	797.1
140°	822.0	823.4	824.8	826.2	827.7	828.5	828.7	828.9	829.1	829.3	829.1
142.5°	854.4	855.5	856.5	857.6	858.7	859.4	859.6	859.8	860.0	860.2	859.8
145°	901.1	901.9	902.7	903.6	904.4	904.9	905.1	905.3	905.5	905.7	905.1
147.5°	942.7	943.9	945.2	946.3	947.6	948.2	948.2	948.2	948.2	948.2	947.6
150°	969.2	970.4	971.7	972.9	974.1	974.7	974.7	974.7	974.7	974.7	974.3
152.5°	995.0	996.0	997.1	998.1	999.3	999.6	999.3	998.9	998.6	998.3	998.1
155°	1029.9	1031.4	1032.8	1034.3	1035.7	1036.0	1035.1	1034.4	1033.6	1032.7	1032.5
157.5°	1061.8	1063.0	1064.1	1065.2	1066.4	1066.5	1065.6	1064.8	1064.0	1063.1	1063.0
160°	1082.4	1083.2	1084.0	1084.9	1085.7	1085.6	1084.6	1083.5	1082.5	1081.5	1081.5
162.5°	1097.9	1099.2	1100.5	1101.8	1103.1	1103.3	1102.2	1101.2	1100.2	1099.2	1099.0
165°	1120.1	1121.6	1123.0	1124.4	1125.8	1126.0	1124.7	1123.6	1122.3	1121.1	1121.1
167.5°	1139.1	1140.3	1141.6	1142.9	1144.1	1144.1	1142.9	1141.6	1140.3	1139.1	1138.9
170°	1148.7	1150.1	1151.5	1153.0	1154.4	1154.4	1153.0	1151.5	1150.1	1148.7	1148.7
172.5°	1156.0	1157.5	1158.9	1160.3	1161.8	1161.9	1160.6	1159.4	1158.1	1156.8	1156.8
175°	1164.3	1165.8	1167.2	1168.6	1170.1	1170.1	1168.9	1167.7	1166.5	1165.2	1165.2
177.5°	1168.8	1169.9	1171.0	1172.2	1173.3	1173.4	1172.4	1171.5	1170.4	1169.5	1169.5
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332082-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1324.8	1320.9	1316.9	1310.0	1303.9	1295.5	1293.0	1290.0	1281.0	1273.1	1267.1
5°	1405.8	1390.8	1369.0	1349.2	1333.0	1311.2	1298.7	1285.6	1266.9	1250.1	1236.4
7.5°	1490.5	1461.1	1427.2	1390.6	1356.5	1323.7	1297.1	1273.4	1247.3	1222.5	1203.2
10°	1557.7	1515.4	1468.1	1417.1	1373.4	1331.1	1295.6	1264.5	1230.9	1201.6	1177.3
12.5°	1634.4	1571.7	1506.4	1444.4	1392.9	1334.1	1291.1	1251.6	1213.5	1178.2	1151.0
15°	1725.2	1645.5	1568.3	1483.0	1404.5	1331.1	1280.1	1230.3	1186.1	1149.9	1115.1
17.5°	1807.9	1717.6	1615.9	1512.1	1417.5	1330.4	1258.9	1202.6	1147.3	1103.1	1068.3
20°	1854.7	1752.0	1636.8	1529.1	1424.5	1327.4	1249.0	1181.7	1121.9	1075.2	1036.0
22.5°	1895.1	1774.9	1655.7	1540.6	1424.0	1319.4	1230.5	1161.3	1096.5	1050.8	1009.1
25°	1936.9	1793.1	1673.6	1538.4	1408.3	1300.0	1200.4	1121.9	1057.2	1003.6	960.7
27.5°	1972.8	1791.8	1650.0	1504.7	1383.6	1275.1	1168.7	1084.6	1015.8	957.7	914.1
30°	1996.6	1794.3	1625.6	1481.8	1359.8	1247.7	1144.3	1059.6	987.5	928.3	887.2
32.5°	2011.6	1792.8	1603.1	1449.9	1321.9	1222.7	1117.9	1030.2	956.1	897.9	858.3
35°	2020.3	1781.9	1564.6	1384.0	1260.8	1164.3	1076.5	985.6	907.8	853.6	808.7
37.5°	2002.9	1758.8	1519.7	1320.5	1185.6	1090.5	1016.7	939.2	864.7	805.2	766.5
40°	1975.5	1743.9	1484.9	1275.7	1133.8	1042.2	979.4	903.4	829.9	773.2	737.1
42.5°	1923.2	1713.5	1446.5	1225.9	1080.0	988.4	930.5	867.0	797.6	744.3	708.3
45°	1795.6	1647.3	1389.0	1151.2	1000.5	905.9	854.8	808.7	745.8	694.2	663.1
47.5°	1618.5	1547.9	1305.8	1072.4	917.6	826.6	773.5	736.4	690.5	648.7	618.9
50°	1495.5	1466.2	1249.5	1018.6	862.3	773.2	722.2	688.6	655.6	613.9	586.5
52.5°	1353.5	1371.6	1183.8	962.7	806.0	718.5	670.4	643.7	613.8	579.5	555.6
55°	1153.7	1219.0	1070.2	869.1	722.2	638.8	593.3	569.7	552.2	526.7	506.2
57.5°	966.5	1049.7	947.5	772.6	639.9	567.9	524.3	498.6	487.4	474.0	457.9
60°	855.5	937.6	859.8	707.9	584.6	516.1	477.5	455.7	444.5	435.2	421.5
62.5°	756.3	839.5	774.1	642.1	530.3	466.8	433.2	411.9	403.2	398.3	386.7
65°	620.1	691.7	648.1	539.8	452.7	396.6	366.1	351.2	343.0	341.2	333.7
67.5°	504.7	559.2	527.4	447.7	379.1	330.7	304.8	292.2	285.9	285.3	279.6
70°	429.0	480.0	455.7	383.5	324.4	286.4	264.0	252.8	249.1	248.4	245.3
72.5°	370.2	405.8	386.5	326.2	280.5	246.1	229.6	217.9	213.7	214.5	212.5
75°	273.9	300.7	289.5	247.8	211.0	188.6	174.9	167.5	163.7	165.6	163.1
77.5°	197.1	214.0	204.0	175.1	152.4	136.3	126.1	121.5	118.2	118.0	116.9
80°	148.8	158.8	153.1	135.7	117.1	103.4	95.2	92.1	90.3	89.7	89.0
82.5°	106.0	114.5	107.8	95.9	83.2	74.9	70.3	66.2	64.9	65.3	64.6
85°	53.6	56.6	54.2	46.7	41.7	37.9	35.5	33.6	32.4	33.0	31.8
87.5°	21.8	21.8	19.7	17.3	15.8	13.9	13.5	12.1	11.6	12.0	11.9
90°	16.8	14.1	11.5	9.1	7.1	5.0	2.9	1.0	2.9	5.0	7.1
92.5°	32.3	30.8	29.3	27.8	26.5	25.0	23.7	22.3	23.7	25.0	26.5
95°	64.8	63.2	61.6	60.0	58.6	57.2	55.8	54.3	55.8	57.2	58.6
97.5°	104.3	103.1	101.9	100.7	99.7	98.6	97.5	96.5	97.5	98.6	99.7
100°	133.2	132.2	131.2	130.1	128.9	127.6	126.4	125.2	126.4	127.6	128.9
102.5°	165.0	163.7	162.3	161.3	160.5	159.8	159.1	158.3	159.1	159.8	160.5
105°	213.6	211.7	209.8	208.7	208.3	207.9	207.5	207.1	207.5	207.9	208.3
107.5°	266.7	266.0	265.3	264.7	264.5	264.3	264.0	263.8	264.0	264.3	264.5
110°	302.0	301.6	301.2	300.8	300.4	299.9	299.5	299.1	299.5	299.9	300.4



TEST NUMBER: P332082-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	337.2	337.2	337.1	336.9	336.7	336.4	336.2	336.0	336.2	336.4	336.7
115°	392.9	393.3	393.7	393.6	393.0	392.4	391.8	391.2	391.8	392.4	393.0
117.5°	447.3	447.8	448.4	448.4	448.0	447.6	447.2	446.8	447.2	447.6	448.0
120°	484.3	485.4	486.4	486.3	485.1	483.9	482.6	481.4	482.6	483.9	485.1
122.5°	520.1	520.7	521.3	521.1	520.1	519.3	518.3	517.5	518.3	519.3	520.1
125°	574.3	574.6	575.0	575.0	574.3	573.7	573.1	572.5	573.1	573.7	574.3
127.5°	628.0	628.5	629.0	628.5	627.2	625.9	624.6	623.3	624.6	625.9	627.2
130°	663.0	663.6	664.2	663.7	662.1	660.4	658.8	657.2	658.8	660.4	662.1
132.5°	697.3	697.8	698.2	697.6	695.9	694.3	692.7	691.0	692.7	694.3	695.9
135°	747.8	748.0	748.2	747.7	746.5	745.2	744.0	742.8	744.0	745.2	746.5
137.5°	796.5	796.1	795.5	794.7	793.7	792.7	791.6	790.7	791.6	792.7	793.7
140°	828.9	828.7	828.5	827.8	826.9	825.9	824.8	823.8	824.8	825.9	826.9
142.5°	859.5	859.1	858.7	858.1	857.1	856.0	855.0	854.0	855.0	856.0	857.1
145°	904.4	903.9	903.2	902.7	902.3	901.9	901.5	901.1	901.5	901.9	902.3
147.5°	947.1	946.5	945.9	945.3	944.5	943.8	943.1	942.3	943.1	943.8	944.5
150°	973.9	973.5	973.1	972.7	972.2	971.8	971.5	971.1	971.5	971.8	972.2
152.5°	997.8	997.5	997.3	996.9	996.3	995.8	995.2	994.6	995.2	995.8	996.3
155°	1032.3	1032.1	1031.9	1031.8	1031.8	1031.8	1031.8	1031.8	1031.8	1031.8	1031.8
157.5°	1062.8	1062.6	1062.4	1062.5	1062.7	1063.0	1063.2	1063.4	1063.2	1063.0	1062.7
160°	1081.5	1081.5	1081.5	1081.7	1082.1	1082.5	1082.9	1083.3	1082.9	1082.5	1082.1
162.5°	1098.8	1098.7	1098.5	1098.8	1099.3	1099.9	1100.4	1101.0	1100.4	1099.9	1099.3
165°	1121.1	1121.1	1121.1	1121.4	1122.0	1122.6	1123.2	1123.9	1123.2	1122.6	1122.0
167.5°	1138.8	1138.6	1138.4	1138.8	1139.6	1140.4	1141.2	1142.1	1141.2	1140.4	1139.6
170°	1148.7	1148.7	1148.7	1149.1	1149.9	1150.7	1151.5	1152.4	1151.5	1150.7	1149.9
172.5°	1156.8	1156.8	1156.8	1157.2	1158.0	1158.8	1159.7	1160.5	1159.7	1158.8	1158.0
175°	1165.2	1165.2	1165.2	1165.7	1166.5	1167.3	1168.2	1168.9	1168.2	1167.3	1166.5
177.5°	1169.5	1169.5	1169.5	1169.8	1170.4	1171.2	1171.8	1172.4	1171.8	1171.2	1170.4
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332082-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1263.6	1260.1	1255.1	1247.7	1241.7	1232.2	1232.2	1233.7	1233.7	1233.3	1232.2
5°	1225.3	1215.9	1204.8	1191.7	1178.0	1164.3	1161.7	1156.7	1153.0	1150.6	1147.5
7.5°	1184.8	1168.2	1151.9	1133.6	1116.9	1103.1	1093.5	1085.5	1080.5	1075.0	1071.0
10°	1157.4	1136.9	1117.5	1098.3	1077.1	1060.3	1049.7	1042.2	1036.6	1031.7	1029.1
12.5°	1125.1	1101.5	1080.2	1061.9	1038.7	1021.4	1011.4	1007.8	1001.2	990.8	985.3
15°	1077.7	1055.9	1030.4	1002.3	991.2	970.0	958.1	952.6	948.8	940.7	938.3
17.5°	1037.2	1008.7	980.1	959.2	938.3	921.1	914.6	907.6	902.6	896.0	894.1
20°	1004.9	979.4	953.2	930.8	908.9	890.3	884.7	879.7	874.7	871.6	869.1
22.5°	972.0	946.5	924.8	903.9	880.6	868.4	862.3	856.8	853.3	851.2	848.7
25°	925.8	903.4	879.1	860.4	841.8	833.6	829.9	826.8	824.3	821.2	820.5
27.5°	884.5	860.1	840.3	822.9	809.5	802.8	799.2	797.6	798.2	799.3	800.0
30°	853.6	831.2	815.0	800.0	787.6	781.3	780.7	780.7	783.2	783.9	785.1
32.5°	825.2	806.8	790.6	776.1	766.7	762.4	764.8	764.8	766.8	768.4	770.6
35°	783.9	767.6	755.2	742.8	734.7	736.5	737.8	739.0	742.1	745.8	748.4
37.5°	744.3	730.3	717.3	707.7	703.9	707.3	710.3	712.9	716.4	719.4	721.8
40°	716.0	705.4	692.9	684.2	685.5	687.4	689.8	692.9	696.1	697.9	700.4
42.5°	689.6	678.5	669.1	661.8	663.5	665.9	667.4	669.1	672.6	676.0	677.5
45°	649.4	640.6	631.9	627.6	628.8	630.1	631.3	633.2	636.3	638.8	639.4
47.5°	604.2	598.1	592.2	588.0	589.9	589.5	591.1	595.1	596.0	597.5	601.0
50°	575.3	569.7	562.8	561.6	561.6	561.6	562.2	567.2	567.2	569.7	572.2
52.5°	543.4	539.8	535.4	533.2	532.2	532.2	534.8	537.3	538.3	541.8	544.3
55°	496.2	492.5	488.7	486.9	485.6	486.9	491.9	493.1	496.2	498.0	499.9
57.5°	447.0	444.2	441.2	440.1	439.9	441.6	444.3	448.0	448.8	454.5	457.3
60°	414.6	410.3	407.8	407.8	406.5	412.2	410.9	417.2	418.4	422.2	426.5
62.5°	381.3	375.4	374.5	374.5	376.2	377.8	379.5	382.3	385.5	390.2	393.6
65°	327.5	324.4	328.8	328.1	326.9	330.6	330.6	333.7	337.5	341.8	348.6
67.5°	276.6	275.0	275.3	275.3	277.2	279.3	281.1	283.8	288.3	292.9	297.4
70°	242.2	244.1	241.0	243.4	245.3	245.9	247.2	250.9	255.9	259.0	264.0
72.5°	208.8	208.7	209.1	210.1	211.9	213.0	214.3	218.6	224.0	226.6	230.6
75°	160.7	160.0	161.8	161.8	165.0	166.2	167.5	169.4	174.4	178.1	181.2
77.5°	117.3	118.0	117.6	119.8	118.9	119.1	123.0	124.9	125.4	132.8	134.4
80°	88.4	89.7	90.3	90.9	91.5	90.3	94.7	96.5	96.5	100.8	103.9
82.5°	63.5	64.2	65.9	66.5	66.6	67.9	68.2	69.6	71.1	73.0	77.1
85°	31.8	33.6	34.2	33.6	34.2	33.0	34.9	35.5	36.1	36.1	36.1
87.5°	11.8	12.8	12.8	13.8	13.9	14.9	15.1	14.2	14.3	16.0	14.2
90°	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.8	24.6	25.3	26.0
92.5°	27.8	29.3	30.8	32.3	33.8	35.3	36.0	36.7	37.3	37.9	38.2
95°	60.0	61.6	63.2	64.8	66.5	68.1	68.9	69.7	70.6	71.4	71.8
97.5°	100.7	101.9	103.1	104.3	105.4	106.5	107.5	108.4	109.4	110.4	110.7
100°	130.1	131.2	132.2	133.2	134.3	135.3	135.9	136.5	137.1	137.8	138.2
102.5°	161.3	162.3	163.7	165.0	166.4	167.7	168.3	168.9	169.5	170.2	170.4
105°	208.7	209.8	211.7	213.6	215.4	217.2	217.2	217.2	217.2	217.2	217.5
107.5°	264.7	265.3	266.0	266.7	267.4	268.2	268.9	269.5	270.2	270.8	271.0
110°	300.8	301.2	301.6	302.0	302.4	302.9	303.6	304.4	305.3	306.1	306.3



TEST NUMBER: P332082-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	336.9	337.1	337.2	337.2	337.3	337.4	338.4	339.4	340.4	341.4	341.8
115°	393.6	393.7	393.3	392.9	392.5	392.1	392.3	392.5	392.7	392.9	392.9
117.5°	448.4	448.4	447.8	447.3	446.8	446.2	446.2	446.2	446.1	446.1	445.8
120°	486.3	486.4	485.4	484.3	483.3	482.3	482.1	481.9	481.7	481.5	481.2
122.5°	521.1	521.3	520.7	520.1	519.7	519.1	518.6	518.1	517.5	517.0	516.4
125°	575.0	575.0	574.6	574.3	573.9	573.5	572.6	571.8	571.0	570.1	569.3
127.5°	628.5	629.0	628.5	628.0	627.6	627.2	626.1	624.9	623.8	622.6	621.5
130°	663.7	664.2	663.6	663.0	662.4	661.8	661.0	660.1	659.3	658.5	657.4
132.5°	697.6	698.2	697.8	697.3	696.8	696.4	695.4	694.4	693.5	692.4	691.4
135°	747.7	748.2	748.0	747.8	747.6	747.3	746.6	745.8	744.9	744.1	743.5
137.5°	794.7	795.5	796.1	796.5	797.1	797.6	796.8	795.9	795.0	794.2	793.4
140°	827.8	828.5	828.7	828.9	829.1	829.3	829.1	828.9	828.7	828.5	827.7
142.5°	858.1	858.7	859.1	859.5	859.8	860.2	860.0	859.8	859.6	859.4	858.7
145°	902.7	903.2	903.9	904.4	905.1	905.7	905.5	905.3	905.1	904.9	904.4
147.5°	945.3	945.9	946.5	947.1	947.6	948.2	948.2	948.2	948.2	948.2	947.6
150°	972.7	973.1	973.5	973.9	974.3	974.7	974.7	974.7	974.7	974.7	974.1
152.5°	996.9	997.3	997.5	997.8	998.1	998.3	998.6	998.9	999.3	999.6	999.3
155°	1031.8	1031.9	1032.1	1032.3	1032.5	1032.7	1033.6	1034.4	1035.1	1036.0	1035.7
157.5°	1062.5	1062.4	1062.6	1062.8	1063.0	1063.1	1064.0	1064.8	1065.6	1066.5	1066.4
160°	1081.7	1081.5	1081.5	1081.5	1081.5	1081.5	1082.5	1083.5	1084.6	1085.6	1085.7
162.5°	1098.8	1098.5	1098.7	1098.8	1099.0	1099.2	1100.2	1101.2	1102.2	1103.3	1103.1
165°	1121.4	1121.1	1121.1	1121.1	1121.1	1121.1	1122.3	1123.6	1124.7	1126.0	1125.8
167.5°	1138.8	1138.4	1138.6	1138.8	1138.9	1139.1	1140.3	1141.6	1142.9	1144.1	1144.1
170°	1149.1	1148.7	1148.7	1148.7	1148.7	1148.7	1150.1	1151.5	1153.0	1154.4	1154.4
172.5°	1157.2	1156.8	1156.8	1156.8	1156.8	1156.8	1158.1	1159.4	1160.6	1161.9	1161.8
175°	1165.7	1165.2	1165.2	1165.2	1165.2	1165.2	1166.5	1167.7	1168.9	1170.1	1170.1
177.5°	1169.8	1169.5	1169.5	1169.5	1169.5	1169.5	1170.4	1171.5	1172.4	1173.4	1173.3
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332082-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1228.8	1228.3	1231.8	1229.2	1231.8	1228.3	1228.8	1232.2	1233.3	1233.7	1233.7
5°	1143.7	1145.6	1139.3	1139.3	1139.3	1145.6	1143.7	1147.5	1150.6	1153.0	1156.7
7.5°	1068.0	1065.2	1065.5	1062.2	1065.5	1065.2	1068.0	1071.0	1075.0	1080.5	1085.5
10°	1021.7	1018.0	1016.7	1017.3	1016.7	1018.0	1021.7	1029.1	1031.7	1036.6	1042.2
12.5°	983.3	982.5	974.4	974.5	974.4	982.5	983.3	985.3	990.8	1001.2	1007.8
15°	938.3	926.5	925.2	928.9	925.2	926.5	938.3	938.3	940.7	948.8	952.6
17.5°	893.0	886.8	887.2	885.3	887.2	886.8	893.0	894.1	896.0	902.6	907.6
20°	869.1	865.4	864.7	860.4	864.7	865.4	869.1	869.1	871.6	874.7	879.7
22.5°	847.2	846.0	846.4	841.5	846.4	846.0	847.2	848.7	851.2	853.3	856.8
25°	820.0	823.1	820.5	820.5	820.5	823.1	820.0	820.5	821.2	824.3	826.8
27.5°	801.5	801.4	800.2	800.2	800.2	801.4	801.5	800.0	799.3	798.2	797.6
30°	787.6	787.0	788.2	788.2	788.2	787.0	787.6	785.1	783.9	783.2	780.7
32.5°	773.6	774.5	774.8	775.2	774.8	774.5	773.6	770.6	768.4	766.8	764.8
35°	752.1	752.7	754.6	753.4	754.6	752.7	752.1	748.4	745.8	742.1	739.0
37.5°	722.9	725.8	725.2	726.2	725.2	725.8	722.9	721.8	719.4	716.4	712.9
40°	701.0	702.9	702.3	702.3	702.3	702.9	701.0	700.4	697.9	696.1	692.9
42.5°	678.7	680.0	678.3	677.4	678.3	680.0	678.7	677.5	676.0	672.6	669.1
45°	641.9	640.6	642.5	640.0	642.5	640.6	641.9	639.4	638.8	636.3	633.2
47.5°	600.8	602.1	602.5	604.4	602.5	602.1	600.8	601.0	597.5	596.0	595.1
50°	573.4	577.1	577.1	576.6	577.1	577.1	573.4	572.2	569.7	567.2	567.2
52.5°	546.5	548.3	550.7	550.6	550.7	548.3	546.5	544.3	541.8	538.3	537.3
55°	504.9	506.2	507.4	508.0	507.4	506.2	504.9	499.9	498.0	496.2	493.1
57.5°	461.8	461.4	464.3	465.2	464.3	461.4	461.8	457.3	454.5	448.8	448.0
60°	431.4	431.4	436.4	438.3	436.4	431.4	431.4	426.5	422.2	418.4	417.2
62.5°	399.1	401.1	406.1	403.5	406.1	401.1	399.1	393.6	390.2	385.5	382.3
65°	351.7	356.7	356.1	358.6	356.1	356.7	351.7	348.6	341.8	337.5	333.7
67.5°	302.3	305.5	309.9	310.3	309.9	305.5	302.3	297.4	292.9	288.3	283.8
70°	268.9	272.0	274.6	276.4	274.6	272.0	268.9	264.0	259.0	255.9	250.9
72.5°	236.6	238.2	244.2	241.5	244.2	238.2	236.6	230.6	226.6	224.0	218.6
75°	185.5	189.9	193.6	191.8	193.6	189.9	185.5	181.2	178.1	174.4	169.4
77.5°	137.2	141.6	143.3	141.7	143.3	141.6	137.2	134.4	132.8	125.4	124.9
80°	108.4	107.7	111.5	110.8	111.5	107.7	108.4	103.9	100.8	96.5	96.5
82.5°	79.5	78.8	80.6	81.0	80.6	78.8	79.5	77.1	73.0	71.1	69.6
85°	38.6	40.5	37.9	37.4	37.9	40.5	38.6	36.1	36.1	36.1	35.5
87.5°	14.3	14.3	13.9	13.5	13.9	14.3	14.3	14.2	16.0	14.3	14.2
90°	26.4	26.8	27.2	27.6	27.2	26.8	26.4	26.0	25.3	24.6	23.8
92.5°	37.9	37.7	37.4	37.2	37.4	37.7	37.9	38.2	37.9	37.3	36.7
95°	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.4	70.6	69.7
97.5°	110.7	110.6	110.5	110.4	110.5	110.6	110.7	110.7	110.4	109.4	108.4
100°	138.7	139.1	139.5	139.9	139.5	139.1	138.7	138.2	137.8	137.1	136.5
102.5°	170.3	170.2	170.2	170.1	170.2	170.2	170.3	170.4	170.2	169.5	168.9
105°	217.9	218.2	218.6	219.0	218.6	218.2	217.9	217.5	217.2	217.2	217.2
107.5°	270.8	270.5	270.3	270.1	270.3	270.5	270.8	271.0	270.8	270.2	269.5
110°	305.9	305.5	305.1	304.7	305.1	305.5	305.9	306.3	306.1	305.3	304.4



TEST NUMBER: P332082-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	341.7	341.7	341.6	341.5	341.6	341.7	341.7	341.8	341.4	340.4	339.4
115°	392.7	392.5	392.3	392.1	392.3	392.5	392.7	392.9	392.9	392.7	392.5
117.5°	445.2	444.6	444.0	443.5	444.0	444.6	445.2	445.8	446.1	446.1	446.2
120°	480.8	480.4	480.0	479.5	480.0	480.4	480.8	481.2	481.5	481.7	481.9
122.5°	515.9	515.3	514.7	514.1	514.7	515.3	515.9	516.4	517.0	517.5	518.1
125°	568.5	567.7	566.9	566.1	566.9	567.7	568.5	569.3	570.1	571.0	571.8
127.5°	620.6	619.6	618.7	617.8	618.7	619.6	620.6	621.5	622.6	623.8	624.9
130°	655.9	654.5	653.1	651.6	653.1	654.5	655.9	657.4	658.5	659.3	660.1
132.5°	690.3	689.2	688.1	687.0	688.1	689.2	690.3	691.4	692.4	693.5	694.4
135°	743.1	742.7	742.3	741.9	742.3	742.7	743.1	743.5	744.1	744.9	745.8
137.5°	792.6	791.9	791.1	790.3	791.1	791.9	792.6	793.4	794.2	795.0	795.9
140°	826.2	824.8	823.4	822.0	823.4	824.8	826.2	827.7	828.5	828.7	828.9
142.5°	857.6	856.5	855.5	854.4	855.5	856.5	857.6	858.7	859.4	859.6	859.8
145°	903.6	902.7	901.9	901.1	901.9	902.7	903.6	904.4	904.9	905.1	905.3
147.5°	946.3	945.2	943.9	942.7	943.9	945.2	946.3	947.6	948.2	948.2	948.2
150°	972.9	971.7	970.4	969.2	970.4	971.7	972.9	974.1	974.7	974.7	974.7
152.5°	998.1	997.1	996.0	995.0	996.0	997.1	998.1	999.3	999.6	999.3	998.9
155°	1034.3	1032.8	1031.4	1029.9	1031.4	1032.8	1034.3	1035.7	1036.0	1035.1	1034.4
157.5°	1065.2	1064.1	1063.0	1061.8	1063.0	1064.1	1065.2	1066.4	1066.5	1065.6	1064.8
160°	1084.9	1084.0	1083.2	1082.4	1083.2	1084.0	1084.9	1085.7	1085.6	1084.6	1083.5
162.5°	1101.8	1100.5	1099.2	1097.9	1099.2	1100.5	1101.8	1103.1	1103.3	1102.2	1101.2
165°	1124.4	1123.0	1121.6	1120.1	1121.6	1123.0	1124.4	1125.8	1126.0	1124.7	1123.6
167.5°	1142.9	1141.6	1140.3	1139.1	1140.3	1141.6	1142.9	1144.1	1144.1	1142.9	1141.6
170°	1153.0	1151.5	1150.1	1148.7	1150.1	1151.5	1153.0	1154.4	1154.4	1153.0	1151.5
172.5°	1160.3	1158.9	1157.5	1156.0	1157.5	1158.9	1160.3	1161.8	1161.9	1160.6	1159.4
175°	1168.6	1167.2	1165.8	1164.3	1165.8	1167.2	1168.6	1170.1	1170.1	1168.9	1167.7
177.5°	1172.2	1171.0	1169.9	1168.8	1169.9	1171.0	1172.2	1173.3	1173.4	1172.4	1171.5
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332082-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1232.2	1232.2	1241.7	1247.7	1255.1	1260.1	1263.6	1267.1	1273.1	1281.0	1290.0
5°	1161.7	1164.3	1178.0	1191.7	1204.8	1215.9	1225.3	1236.4	1250.1	1266.9	1285.6
7.5°	1093.5	1103.1	1116.9	1133.6	1151.9	1168.2	1184.8	1203.2	1222.5	1247.3	1273.4
10°	1049.7	1060.3	1077.1	1098.3	1117.5	1136.9	1157.4	1177.3	1201.6	1230.9	1264.5
12.5°	1011.4	1021.4	1038.7	1061.9	1080.2	1101.5	1125.1	1151.0	1178.2	1213.5	1251.6
15°	958.1	970.0	991.2	1002.3	1030.4	1055.9	1077.7	1115.1	1149.9	1186.1	1230.3
17.5°	914.6	921.1	938.3	959.2	980.1	1008.7	1037.2	1068.3	1103.1	1147.3	1202.6
20°	884.7	890.3	908.9	930.8	953.2	979.4	1004.9	1036.0	1075.2	1121.9	1181.7
22.5°	862.3	868.4	880.6	903.9	924.8	946.5	972.0	1009.1	1050.8	1096.5	1161.3
25°	829.9	833.6	841.8	860.4	879.1	903.4	925.8	960.7	1003.6	1057.2	1121.9
27.5°	799.2	802.8	809.5	822.9	840.3	860.1	884.5	914.1	957.7	1015.8	1084.6
30°	780.7	781.3	787.6	800.0	815.0	831.2	853.6	887.2	928.3	987.5	1059.6
32.5°	764.8	762.4	766.7	776.1	790.6	806.8	825.2	858.3	897.9	956.1	1030.2
35°	737.8	736.5	734.7	742.8	755.2	767.6	783.9	808.7	853.6	907.8	985.6
37.5°	710.3	707.3	703.9	707.7	717.3	730.3	744.3	766.5	805.2	864.7	939.2
40°	689.8	687.4	685.5	684.2	692.9	705.4	716.0	737.1	773.2	829.9	903.4
42.5°	667.4	665.9	663.5	661.8	669.1	678.5	689.6	708.3	744.3	797.6	867.0
45°	631.3	630.1	628.8	627.6	631.9	640.6	649.4	663.1	694.2	745.8	808.7
47.5°	591.1	589.5	589.9	588.0	592.2	598.1	604.2	618.9	648.7	690.5	736.4
50°	562.2	561.6	561.6	561.6	562.8	569.7	575.3	586.5	613.9	655.6	688.6
52.5°	534.8	532.2	532.2	533.2	535.4	539.8	543.4	555.6	579.5	613.8	643.7
55°	491.9	486.9	485.6	486.9	488.7	492.5	496.2	506.2	526.7	552.2	569.7
57.5°	444.3	441.6	439.9	440.1	441.2	444.2	447.0	457.9	474.0	487.4	498.6
60°	410.9	412.2	406.5	407.8	407.8	410.3	414.6	421.5	435.2	444.5	455.7
62.5°	379.5	377.8	376.2	374.5	374.5	375.4	381.3	386.7	398.3	403.2	411.9
65°	330.6	330.6	326.9	328.1	328.8	324.4	327.5	333.7	341.2	343.0	351.2
67.5°	281.1	279.3	277.2	275.3	275.3	275.0	276.6	279.6	285.3	285.9	292.2
70°	247.2	245.9	245.3	243.4	241.0	244.1	242.2	245.3	248.4	249.1	252.8
72.5°	214.3	213.0	211.9	210.1	209.1	208.7	208.8	212.5	214.5	213.7	217.9
75°	167.5	166.2	165.0	161.8	161.8	160.0	160.7	163.1	165.6	163.7	167.5
77.5°	123.0	119.1	118.9	119.8	117.6	118.0	117.3	116.9	118.0	118.2	121.5
80°	94.7	90.3	91.5	90.9	90.3	89.7	88.4	89.0	89.7	90.3	92.1
82.5°	68.2	67.9	66.6	66.5	65.9	64.2	63.5	64.6	65.3	64.9	66.2
85°	34.9	33.0	34.2	33.6	34.2	33.6	31.8	31.8	33.0	32.4	33.6
87.5°	15.1	14.9	13.9	13.8	12.8	12.8	11.8	11.9	12.0	11.6	12.1
90°	22.9	22.1	19.4	16.8	14.1	11.5	9.1	7.1	5.0	2.9	1.0
92.5°	36.0	35.3	33.8	32.3	30.8	29.3	27.8	26.5	25.0	23.7	22.3
95°	68.9	68.1	66.5	64.8	63.2	61.6	60.0	58.6	57.2	55.8	54.3
97.5°	107.5	106.5	105.4	104.3	103.1	101.9	100.7	99.7	98.6	97.5	96.5
100°	135.9	135.3	134.3	133.2	132.2	131.2	130.1	128.9	127.6	126.4	125.2
102.5°	168.3	167.7	166.4	165.0	163.7	162.3	161.3	160.5	159.8	159.1	158.3
105°	217.2	217.2	215.4	213.6	211.7	209.8	208.7	208.3	207.9	207.5	207.1
107.5°	268.9	268.2	267.4	266.7	266.0	265.3	264.7	264.5	264.3	264.0	263.8
110°	303.6	302.9	302.4	302.0	301.6	301.2	300.8	300.4	299.9	299.5	299.1



TEST NUMBER: P332082-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	338.4	337.4	337.3	337.2	337.2	337.1	336.9	336.7	336.4	336.2	336.0
115°	392.3	392.1	392.5	392.9	393.3	393.7	393.6	393.0	392.4	391.8	391.2
117.5°	446.2	446.2	446.8	447.3	447.8	448.4	448.4	448.0	447.6	447.2	446.8
120°	482.1	482.3	483.3	484.3	485.4	486.4	486.3	485.1	483.9	482.6	481.4
122.5°	518.6	519.1	519.7	520.1	520.7	521.3	521.1	520.1	519.3	518.3	517.5
125°	572.6	573.5	573.9	574.3	574.6	575.0	575.0	574.3	573.7	573.1	572.5
127.5°	626.1	627.2	627.6	628.0	628.5	629.0	628.5	627.2	625.9	624.6	623.3
130°	661.0	661.8	662.4	663.0	663.6	664.2	663.7	662.1	660.4	658.8	657.2
132.5°	695.4	696.4	696.8	697.3	697.8	698.2	697.6	695.9	694.3	692.7	691.0
135°	746.6	747.3	747.6	747.8	748.0	748.2	747.7	746.5	745.2	744.0	742.8
137.5°	796.8	797.6	797.1	796.5	796.1	795.5	794.7	793.7	792.7	791.6	790.7
140°	829.1	829.3	829.1	828.9	828.7	828.5	827.8	826.9	825.9	824.8	823.8
142.5°	860.0	860.2	859.8	859.5	859.1	858.7	858.1	857.1	856.0	855.0	854.0
145°	905.5	905.7	905.1	904.4	903.9	903.2	902.7	902.3	901.9	901.5	901.1
147.5°	948.2	948.2	947.6	947.1	946.5	945.9	945.3	944.5	943.8	943.1	942.3
150°	974.7	974.7	974.3	973.9	973.5	973.1	972.7	972.2	971.8	971.5	971.1
152.5°	998.6	998.3	998.1	997.8	997.5	997.3	996.9	996.3	995.8	995.2	994.6
155°	1033.6	1032.7	1032.5	1032.3	1032.1	1031.9	1031.8	1031.8	1031.8	1031.8	1031.8
157.5°	1064.0	1063.1	1063.0	1062.8	1062.6	1062.4	1062.5	1062.7	1063.0	1063.2	1063.4
160°	1082.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.7	1082.1	1082.5	1082.9	1083.3
162.5°	1100.2	1099.2	1099.0	1098.8	1098.7	1098.5	1098.8	1099.3	1099.9	1100.4	1101.0
165°	1122.3	1121.1	1121.1	1121.1	1121.1	1121.1	1121.4	1122.0	1122.6	1123.2	1123.9
167.5°	1140.3	1139.1	1138.9	1138.8	1138.6	1138.4	1138.8	1139.6	1140.4	1141.2	1142.1
170°	1150.1	1148.7	1148.7	1148.7	1148.7	1148.7	1149.1	1149.9	1150.7	1151.5	1152.4
172.5°	1158.1	1156.8	1156.8	1156.8	1156.8	1156.8	1157.2	1158.0	1158.8	1159.7	1160.5
175°	1166.5	1165.2	1165.2	1165.2	1165.2	1165.2	1165.7	1166.5	1167.3	1168.2	1168.9
177.5°	1170.4	1169.5	1169.5	1169.5	1169.5	1169.5	1169.8	1170.4	1171.2	1171.8	1172.4
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332082-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1293.0	1295.5	1303.9	1310.0	1316.9	1320.9	1324.8	1327.9	1331.8	1332.8	1347.3
5°	1298.7	1311.2	1333.0	1349.2	1369.0	1390.8	1405.8	1412.7	1430.7	1445.7	1475.5
7.5°	1297.1	1323.7	1356.5	1390.6	1427.2	1461.1	1490.5	1525.3	1550.1	1587.4	1624.1
10°	1295.6	1331.1	1373.4	1417.1	1468.1	1515.4	1557.7	1605.0	1644.3	1695.9	1740.1
12.5°	1291.1	1334.1	1392.9	1444.4	1506.4	1571.7	1634.4	1695.2	1730.0	1816.0	1856.7
15°	1280.1	1331.1	1404.5	1483.0	1568.3	1645.5	1725.2	1788.7	1891.4	1966.8	2014.7
17.5°	1258.9	1330.4	1417.5	1512.1	1615.9	1717.6	1807.9	1904.2	2013.3	2104.4	2201.5
20°	1249.0	1327.4	1424.5	1529.1	1636.8	1752.0	1854.7	1970.5	2089.5	2179.1	2303.6
22.5°	1230.5	1319.4	1424.0	1540.6	1655.7	1774.9	1895.1	2011.8	2149.2	2272.7	2391.3
25°	1200.4	1300.0	1408.3	1538.4	1673.6	1793.1	1936.9	2091.9	2235.1	2393.9	2512.2
27.5°	1168.7	1275.1	1383.6	1504.7	1650.0	1791.8	1972.8	2147.9	2323.0	2460.1	2547.7
30°	1144.3	1247.7	1359.8	1481.8	1625.6	1794.3	1996.6	2187.8	2358.4	2476.0	2525.2
32.5°	1117.9	1222.7	1321.9	1449.9	1603.1	1792.8	2011.6	2211.2	2360.4	2438.7	2429.1
35°	1076.5	1164.3	1260.8	1384.0	1564.6	1781.9	2020.3	2213.3	2304.9	2288.1	2161.0
37.5°	1016.7	1090.5	1185.6	1320.5	1519.7	1758.8	2002.9	2147.7	2141.7	2004.9	1820.8
40°	979.4	1042.2	1133.8	1275.7	1484.9	1743.9	1975.5	2069.5	1989.8	1798.6	1578.3
42.5°	930.5	988.4	1080.0	1225.9	1446.5	1713.5	1923.2	1950.4	1794.5	1574.5	1372.5
45°	854.8	905.9	1000.5	1151.2	1389.0	1647.3	1795.6	1728.9	1519.1	1291.9	1138.1
47.5°	773.5	826.6	917.6	1072.4	1305.8	1547.9	1618.5	1476.8	1261.4	1077.1	935.9
50°	722.2	773.2	862.3	1018.6	1249.5	1466.2	1495.5	1312.4	1114.4	952.6	836.8
52.5°	670.4	718.5	806.0	962.7	1183.8	1371.6	1353.5	1167.0	984.9	847.0	756.1
55°	593.3	638.8	722.2	869.1	1070.2	1219.0	1153.7	975.6	824.9	717.9	648.7
57.5°	524.3	567.9	639.9	772.6	947.5	1049.7	966.5	816.5	696.6	614.3	562.7
60°	477.5	516.1	584.6	707.9	859.8	937.6	855.5	722.9	621.9	556.0	509.9
62.5°	433.2	466.8	530.3	642.1	774.1	839.5	756.3	644.1	558.3	499.7	460.6
65°	366.1	396.6	452.7	539.8	648.1	691.7	620.1	529.2	462.6	419.0	392.8
67.5°	304.8	330.7	379.1	447.7	527.4	559.2	504.7	434.4	384.1	349.1	328.4
70°	264.0	286.4	324.4	383.5	455.7	480.0	429.0	371.1	334.3	306.3	287.0
72.5°	229.6	246.1	280.5	326.2	386.5	405.8	370.2	319.2	285.0	264.0	248.7
75°	174.9	188.6	211.0	247.8	289.5	300.7	273.9	242.2	219.1	204.2	192.3
77.5°	126.1	136.3	152.4	175.1	204.0	214.0	197.1	175.9	159.1	149.0	142.4
80°	95.2	103.4	117.1	135.7	153.1	158.8	148.8	132.6	120.8	115.2	109.6
82.5°	70.3	74.9	83.2	95.9	107.8	114.5	106.0	96.3	89.9	84.8	82.7
85°	35.5	37.9	41.7	46.7	54.2	56.6	53.6	51.0	47.3	44.2	44.2
87.5°	13.5	13.9	15.8	17.3	19.7	21.8	21.8	21.3	21.4	21.0	20.7
90°	2.9	5.0	7.1	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.8
92.5°	23.7	25.0	26.5	27.8	29.3	30.8	32.3	33.8	35.3	36.0	36.7
95°	55.8	57.2	58.6	60.0	61.6	63.2	64.8	66.5	68.1	68.9	69.7
97.5°	97.5	98.6	99.7	100.7	101.9	103.1	104.3	105.4	106.5	107.5	108.4
100°	126.4	127.6	128.9	130.1	131.2	132.2	133.2	134.3	135.3	135.9	136.5
102.5°	159.1	159.8	160.5	161.3	162.3	163.7	165.0	166.4	167.7	168.3	168.9
105°	207.5	207.9	208.3	208.7	209.8	211.7	213.6	215.4	217.2	217.2	217.2
107.5°	264.0	264.3	264.5	264.7	265.3	266.0	266.7	267.4	268.2	268.9	269.5
110°	299.5	299.9	300.4	300.8	301.2	301.6	302.0	302.4	302.9	303.6	304.4



TEST NUMBER: P332082-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	336.2	336.4	336.7	336.9	337.1	337.2	337.2	337.3	337.4	338.4	339.4
115°	391.8	392.4	393.0	393.6	393.7	393.3	392.9	392.5	392.1	392.3	392.5
117.5°	447.2	447.6	448.0	448.4	448.4	447.8	447.3	446.8	446.2	446.2	446.2
120°	482.6	483.9	485.1	486.3	486.4	485.4	484.3	483.3	482.3	482.1	481.9
122.5°	518.3	519.3	520.1	521.1	521.3	520.7	520.1	519.7	519.1	518.6	518.1
125°	573.1	573.7	574.3	575.0	575.0	574.6	574.3	573.9	573.5	572.6	571.8
127.5°	624.6	625.9	627.2	628.5	629.0	628.5	628.0	627.6	627.2	626.1	624.9
130°	658.8	660.4	662.1	663.7	664.2	663.6	663.0	662.4	661.8	661.0	660.1
132.5°	692.7	694.3	695.9	697.6	698.2	697.8	697.3	696.8	696.4	695.4	694.4
135°	744.0	745.2	746.5	747.7	748.2	748.0	747.8	747.6	747.3	746.6	745.8
137.5°	791.6	792.7	793.7	794.7	795.5	796.1	796.5	797.1	797.6	796.8	795.9
140°	824.8	825.9	826.9	827.8	828.5	828.7	828.9	829.1	829.3	829.1	828.9
142.5°	855.0	856.0	857.1	858.1	858.7	859.1	859.5	859.8	860.2	860.0	859.8
145°	901.5	901.9	902.3	902.7	903.2	903.9	904.4	905.1	905.7	905.5	905.3
147.5°	943.1	943.8	944.5	945.3	945.9	946.5	947.1	947.6	948.2	948.2	948.2
150°	971.5	971.8	972.2	972.7	973.1	973.5	973.9	974.3	974.7	974.7	974.7
152.5°	995.2	995.8	996.3	996.9	997.3	997.5	997.8	998.1	998.3	998.6	998.9
155°	1031.8	1031.8	1031.8	1031.8	1031.9	1032.1	1032.3	1032.5	1032.7	1033.6	1034.4
157.5°	1063.2	1063.0	1062.7	1062.5	1062.4	1062.6	1062.8	1063.0	1063.1	1064.0	1064.8
160°	1082.9	1082.5	1082.1	1081.7	1081.5	1081.5	1081.5	1081.5	1081.5	1082.5	1083.5
162.5°	1100.4	1099.9	1099.3	1098.8	1098.5	1098.7	1098.8	1099.0	1099.2	1100.2	1101.2
165°	1123.2	1122.6	1122.0	1121.4	1121.1	1121.1	1121.1	1121.1	1121.1	1122.3	1123.6
167.5°	1141.2	1140.4	1139.6	1138.8	1138.4	1138.6	1138.8	1138.9	1139.1	1140.3	1141.6
170°	1151.5	1150.7	1149.9	1149.1	1148.7	1148.7	1148.7	1148.7	1148.7	1150.1	1151.5
172.5°	1159.7	1158.8	1158.0	1157.2	1156.8	1156.8	1156.8	1156.8	1156.8	1158.1	1159.4
175°	1168.2	1167.3	1166.5	1165.7	1165.2	1165.2	1165.2	1165.2	1165.2	1166.5	1167.7
177.5°	1171.8	1171.2	1170.4	1169.8	1169.5	1169.5	1169.5	1169.5	1169.5	1170.4	1171.5
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332082-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1352.3	1352.7	1358.3	1362.2	1360.3	1362.7	1363.7
5°	1477.4	1499.8	1511.6	1520.4	1521.0	1521.6	1526.6
7.5°	1654.9	1678.9	1696.5	1723.1	1731.1	1740.1	1737.5
10°	1784.4	1819.8	1850.4	1866.5	1884.0	1909.5	1889.0
12.5°	1905.4	1968.3	2014.7	2039.9	2056.3	2061.4	2051.4
15°	2105.0	2187.1	2231.3	2230.2	2286.2	2310.5	2272.5
17.5°	2288.1	2363.9	2424.6	2455.8	2502.4	2512.8	2508.0
20°	2400.1	2482.9	2530.2	2583.8	2608.0	2629.8	2633.5
22.5°	2496.7	2571.0	2621.9	2666.4	2686.8	2697.1	2703.3
25°	2596.2	2654.8	2685.3	2700.8	2706.4	2705.1	2697.1
27.5°	2589.3	2593.8	2560.3	2527.2	2497.8	2464.5	2453.0
30°	2522.1	2469.8	2376.5	2323.5	2245.7	2184.0	2208.9
32.5°	2345.3	2241.2	2136.4	2020.7	1924.9	1897.7	1870.3
35°	2001.6	1818.6	1711.5	1587.0	1537.2	1487.4	1453.1
37.5°	1619.4	1477.8	1350.8	1269.3	1219.4	1187.9	1171.0
40°	1400.2	1272.6	1168.0	1102.0	1064.0	1028.5	1023.6
42.5°	1225.4	1106.8	1028.0	975.5	939.0	923.9	913.0
45°	1003.6	920.8	867.9	830.5	806.3	796.9	784.5
47.5°	849.5	790.9	751.2	725.8	707.5	700.5	699.6
50°	763.3	714.7	685.5	665.5	651.3	648.7	638.8
52.5°	698.5	656.5	633.7	616.2	605.9	599.0	596.0
55°	606.4	578.4	557.9	547.9	539.8	532.9	532.9
57.5°	530.6	507.2	493.6	485.1	482.6	477.8	474.7
60°	483.8	463.8	453.3	445.8	440.8	441.4	435.8
62.5°	437.9	425.0	414.9	407.4	401.5	401.6	402.0
65°	373.0	363.0	355.5	353.0	349.3	344.9	346.2
67.5°	316.0	306.7	300.9	296.6	295.3	293.0	296.6
70°	275.2	268.3	264.0	260.2	259.0	259.6	262.8
72.5°	237.8	233.0	230.1	228.4	225.6	225.8	227.8
75°	186.8	183.1	180.5	178.7	178.1	178.1	178.1
77.5°	137.2	136.3	135.2	132.5	132.6	133.3	133.5
80°	108.4	106.5	105.8	104.6	102.7	101.5	104.6
82.5°	81.0	79.1	78.4	78.2	75.3	75.1	77.7
85°	43.6	41.7	42.3	41.7	41.7	41.1	41.1
87.5°	20.4	20.0	19.6	20.2	19.8	19.4	20.4
90°	24.6	25.3	26.0	26.4	26.8	27.2	27.6
92.5°	37.3	37.9	38.2	37.9	37.7	37.4	37.2
95°	70.6	71.4	71.8	71.8	71.8	71.8	71.8
97.5°	109.4	110.4	110.7	110.7	110.6	110.5	110.4
100°	137.1	137.8	138.2	138.7	139.1	139.5	139.9
102.5°	169.5	170.2	170.4	170.3	170.2	170.2	170.1
105°	217.2	217.2	217.5	217.9	218.2	218.6	219.0
107.5°	270.2	270.8	271.0	270.8	270.5	270.3	270.1
110°	305.3	306.1	306.3	305.9	305.5	305.1	304.7



TEST NUMBER: P332082-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	340.4	341.4	341.8	341.7	341.7	341.6	341.5
115°	392.7	392.9	392.9	392.7	392.5	392.3	392.1
117.5°	446.1	446.1	445.8	445.2	444.6	444.0	443.5
120°	481.7	481.5	481.2	480.8	480.4	480.0	479.5
122.5°	517.5	517.0	516.4	515.9	515.3	514.7	514.1
125°	571.0	570.1	569.3	568.5	567.7	566.9	566.1
127.5°	623.8	622.6	621.5	620.6	619.6	618.7	617.8
130°	659.3	658.5	657.4	655.9	654.5	653.1	651.6
132.5°	693.5	692.4	691.4	690.3	689.2	688.1	687.0
135°	744.9	744.1	743.5	743.1	742.7	742.3	741.9
137.5°	795.0	794.2	793.4	792.6	791.9	791.1	790.3
140°	828.7	828.5	827.7	826.2	824.8	823.4	822.0
142.5°	859.6	859.4	858.7	857.6	856.5	855.5	854.4
145°	905.1	904.9	904.4	903.6	902.7	901.9	901.1
147.5°	948.2	948.2	947.6	946.3	945.2	943.9	942.7
150°	974.7	974.7	974.1	972.9	971.7	970.4	969.2
152.5°	999.3	999.6	999.3	998.1	997.1	996.0	995.0
155°	1035.1	1036.0	1035.7	1034.3	1032.8	1031.4	1029.9
157.5°	1065.6	1066.5	1066.4	1065.2	1064.1	1063.0	1061.8
160°	1084.6	1085.6	1085.7	1084.9	1084.0	1083.2	1082.4
162.5°	1102.2	1103.3	1103.1	1101.8	1100.5	1099.2	1097.9
165°	1124.7	1126.0	1125.8	1124.4	1123.0	1121.6	1120.1
167.5°	1142.9	1144.1	1144.1	1142.9	1141.6	1140.3	1139.1
170°	1153.0	1154.4	1154.4	1153.0	1151.5	1150.1	1148.7
172.5°	1160.6	1161.9	1161.8	1160.3	1158.9	1157.5	1156.0
175°	1168.9	1170.1	1170.1	1168.6	1167.2	1165.8	1164.3
177.5°	1172.4	1173.4	1173.3	1172.2	1171.0	1169.9	1168.8
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7

(END OF REPORT)