

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332087-927

Luminaire Tested: **S123DIP-S1165D1195U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332087-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1195U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7549.6 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332087-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332087-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	89	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	40	35
3	81	72	64	58	75	66	60	55	56	51	47	47	43	40	39	36	34	30
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	31	29	25
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20	17
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18	15
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15588	15588	15588
5°	15662	15446	15554
10°	15557	15312	15407
15°	15375	15139	15166
20°	15163	14892	14905
25°	14878	14598	14567
30°	14564	14270	14162
35°	14236	13925	13745
40°	13893	13543	13333
45°	13516	13192	12871
50°	13137	12762	12407
55°	12643	12314	11941
60°	12144	11795	11418
65°	11703	11227	10878
70°	11053	10581	10112
75°	10098	9736	9320
80°	9106	8722	8647
85°	7991	7694	7385



TEST NUMBER: P332087-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.4	1.8
10°-20°	385.2	5.1
20°-30°	569.0	7.5
30°-40°	664.6	8.8
40°-50°	668.2	8.9
50°-60°	587.0	7.8
60°-70°	437.3	5.8
70°-80°	249.1	3.3
80°-90°	75.0	1.0
90°-100°	45.0	0.6
100°-110°	214.7	2.8
110°-120°	515.6	6.8
120°-130°	656.6	8.7
130°-140°	701.5	9.3
140°-150°	656.0	8.7
150°-160°	529.2	7.0
160°-170°	341.5	4.5
170°-180°	117.7	1.6
0°-30°	1090.6	14.4
0°-40°	1755.3	23.2
0°-60°	3010.4	39.9
0°-90°	3771.8	50.0
90°-120°	775.3	10.3
90°-150°	2789.4	36.9
90°-180°	3778.0	50.0
0°-180°	7549.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1448	1448	1448	1448	1448	
5°	1450	1443	1430	1441	1440	137
15°	1380	1374	1358	1368	1361	389
25°	1253	1245	1229	1230	1226	577
35°	1083	1075	1060	1052	1046	677
45°	888	882	867	852	846	685
55°	674	672	656	643	636	603
65°	460	453	441	431	427	453
75°	243	238	234	228	224	260
85°	65	62	62	60	60	71
90°	1	10	22	26	28	6
95°	56	21	28	35	35	69
105°	274	279	202	48	40	291
115°	514	520	528	537	541	508
125°	725	732	736	738	740	647
135°	903	908	912	915	912	695
145°	1042	1048	1050	1052	1052	652
155°	1148	1146	1147	1151	1146	529
165°	1210	1208	1207	1213	1208	342
175°	1239	1234	1235	1241	1234	118
180°	1239	1239	1239	1239	1239	



TEST NUMBER: P332087-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1453.2	1452.3	1451.4	1450.6	1449.6	1448.0	1445.6	1443.1	1440.7	1438.2	1440.4
5°	1449.5	1448.1	1446.7	1445.3	1443.9	1441.7	1438.7	1435.6	1432.6	1429.5	1432.3
7.5°	1435.3	1433.8	1432.5	1431.1	1429.7	1427.4	1424.3	1421.2	1418.0	1414.8	1417.3
10°	1423.3	1421.9	1420.5	1419.1	1417.8	1415.3	1411.7	1408.1	1404.5	1400.9	1403.4
12.5°	1407.4	1406.2	1405.0	1403.9	1402.7	1400.4	1397.1	1393.7	1390.3	1387.0	1388.8
15°	1379.7	1378.6	1377.5	1376.4	1375.3	1372.9	1369.4	1365.7	1362.2	1358.5	1360.7
17.5°	1347.6	1346.2	1344.7	1343.3	1341.8	1339.3	1335.7	1332.1	1328.5	1324.9	1326.5
20°	1323.7	1322.0	1320.3	1318.7	1317.1	1314.4	1310.8	1307.3	1303.6	1300.1	1301.2
22.5°	1296.8	1295.1	1293.5	1291.8	1290.1	1287.5	1283.9	1280.3	1276.8	1273.1	1274.0
25°	1252.7	1251.0	1249.4	1247.7	1246.1	1243.4	1239.8	1236.3	1232.6	1229.1	1229.3
27.5°	1205.6	1204.0	1202.5	1200.8	1199.2	1196.5	1192.6	1188.7	1184.9	1181.0	1181.2
30°	1171.8	1170.4	1169.0	1167.6	1166.3	1163.6	1159.8	1155.9	1152.0	1148.1	1148.1
32.5°	1137.9	1136.1	1134.2	1132.4	1130.6	1128.1	1125.2	1122.2	1119.2	1116.3	1114.7
35°	1083.4	1081.7	1080.1	1078.4	1076.7	1074.1	1070.5	1066.9	1063.3	1059.7	1058.0
37.5°	1027.5	1025.5	1023.3	1021.3	1019.1	1016.3	1012.6	1009.0	1005.4	1001.6	999.7
40°	988.7	987.1	985.4	983.7	982.1	979.3	975.4	971.5	967.7	963.8	961.6
42.5°	949.8	948.0	946.1	944.2	942.3	939.4	935.6	931.7	927.8	924.0	921.8
45°	887.9	886.8	885.7	884.6	883.4	881.1	877.5	873.9	870.3	866.6	863.4
47.5°	826.3	824.7	823.2	821.5	819.9	817.5	814.0	810.6	807.3	803.9	800.7
50°	784.5	783.2	781.7	780.4	779.0	776.5	772.9	769.3	765.6	762.1	759.1
52.5°	740.7	739.7	738.8	737.8	736.9	734.5	730.7	726.9	723.1	719.2	716.6
55°	673.7	673.4	673.1	672.9	672.6	670.7	667.0	663.5	659.8	656.2	653.2
57.5°	609.9	609.0	608.0	607.1	606.2	604.3	601.3	598.5	595.6	592.7	590.0
60°	564.1	563.8	563.6	563.2	563.0	561.2	557.9	554.5	551.2	547.9	545.4
62.5°	523.2	522.5	521.8	521.1	520.4	518.3	515.0	511.7	508.4	505.1	502.6
65°	459.5	458.1	456.7	455.3	453.9	451.9	449.1	446.3	443.5	440.8	438.6
67.5°	392.0	390.8	389.6	388.3	387.1	385.5	383.3	381.3	379.1	377.1	375.1
70°	351.2	349.5	347.8	346.2	344.5	342.9	341.2	339.5	337.9	336.2	334.3
72.5°	308.3	307.1	305.9	304.7	303.5	301.9	300.0	298.1	296.3	294.4	292.6
75°	242.8	241.7	240.6	239.5	238.4	237.4	236.6	235.8	235.0	234.1	232.7
77.5°	184.8	184.2	183.5	183.0	182.4	181.6	180.5	179.6	178.6	177.6	176.7
80°	146.9	146.1	145.3	144.4	143.6	142.9	142.4	141.8	141.2	140.7	140.5
82.5°	110.1	109.9	109.7	109.6	109.4	109.2	109.2	109.1	108.9	108.8	108.4
85°	64.7	64.2	63.6	63.1	62.5	62.3	62.3	62.3	62.3	62.3	61.7
87.5°	26.1	25.8	25.6	25.3	25.0	25.1	25.4	25.7	26.1	26.3	26.3
90°	1.0	2.9	5.0	7.1	9.1	11.5	14.1	16.8	19.4	22.1	22.9
92.5°	17.1	16.6	16.0	15.4	14.8	15.5	17.6	19.6	21.5	23.5	24.9
95°	56.2	47.8	39.4	31.0	22.6	19.6	21.8	24.0	26.3	28.5	29.9
97.5°	112.8	109.1	105.3	101.6	97.8	88.6	73.8	59.1	44.4	29.6	31.3
100°	155.5	159.6	163.7	167.8	171.9	158.0	126.1	94.2	62.3	30.3	32.0
102.5°	204.1	207.1	210.0	212.9	215.9	199.9	165.1	130.2	95.4	60.5	55.5
105°	274.3	276.6	278.8	281.0	283.3	275.2	256.7	238.4	220.0	201.5	165.3
107.5°	348.2	350.1	351.9	353.6	355.5	357.8	360.8	363.6	366.5	369.5	342.9
110°	397.6	399.3	400.8	402.5	404.2	406.1	408.4	410.6	412.8	415.1	408.4



TEST NUMBER: P332087-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	444.7	446.2	447.7	449.2	450.6	452.5	454.7	457.0	459.2	461.4	461.6
115°	514.5	515.7	516.9	518.2	519.4	520.9	522.8	524.6	526.5	528.3	530.4
117.5°	582.0	583.5	585.0	586.6	588.1	589.3	590.3	591.2	592.2	593.1	594.7
120°	624.0	625.8	627.7	629.5	631.4	632.6	633.2	633.8	634.5	635.0	636.7
122.5°	666.7	668.2	669.7	671.2	672.8	673.9	674.7	675.5	676.2	677.0	678.2
125°	725.2	726.9	728.5	730.2	731.8	733.0	733.8	734.7	735.5	736.3	736.7
127.5°	782.0	783.5	785.2	786.9	788.5	789.8	790.8	791.8	792.7	793.7	794.4
130°	817.3	819.0	820.5	822.2	823.8	825.1	825.9	826.7	827.5	828.3	829.2
132.5°	851.1	852.8	854.4	856.0	857.7	858.8	859.5	860.2	860.8	861.5	862.3
135°	902.9	904.1	905.3	906.6	907.8	908.8	909.7	910.5	911.2	912.1	912.7
137.5°	947.1	948.6	950.1	951.7	953.3	954.3	954.7	955.2	955.6	956.1	957.0
140°	976.5	977.7	979.0	980.2	981.4	982.3	982.9	983.6	984.2	984.8	985.6
142.5°	1003.8	1005.0	1006.2	1007.4	1008.7	1009.6	1010.2	1010.8	1011.5	1012.0	1012.7
145°	1041.9	1043.3	1044.7	1046.2	1047.6	1048.5	1048.9	1049.3	1049.7	1050.1	1050.5
147.5°	1077.8	1078.7	1079.7	1080.5	1081.5	1082.2	1082.6	1083.0	1083.4	1083.8	1084.3
150°	1099.9	1100.4	1101.1	1101.7	1102.3	1102.8	1103.2	1103.6	1104.1	1104.5	1104.9
152.5°	1119.7	1120.0	1120.3	1120.5	1120.9	1121.1	1121.3	1121.7	1121.9	1122.1	1122.8
155°	1147.7	1147.3	1146.8	1146.4	1146.1	1146.0	1146.1	1146.4	1146.6	1146.8	1147.8
157.5°	1169.4	1169.3	1169.3	1169.3	1169.3	1169.1	1168.9	1168.7	1168.5	1168.3	1169.6
160°	1182.6	1182.5	1182.3	1182.1	1181.9	1181.6	1181.5	1181.2	1181.1	1180.8	1182.1
162.5°	1195.2	1194.7	1194.1	1193.6	1193.0	1192.7	1192.5	1192.3	1192.1	1191.8	1193.3
165°	1210.3	1209.7	1209.0	1208.5	1207.8	1207.4	1207.2	1207.0	1206.8	1206.6	1208.2
167.5°	1222.1	1221.2	1220.4	1219.6	1218.8	1218.4	1218.4	1218.4	1218.4	1218.4	1220.0
170°	1228.7	1227.9	1227.1	1226.2	1225.4	1225.0	1225.0	1225.0	1225.0	1225.0	1226.6
172.5°	1233.1	1232.2	1231.1	1230.2	1229.2	1228.8	1228.9	1229.1	1229.2	1229.4	1231.1
175°	1238.8	1237.8	1236.8	1235.7	1234.7	1234.3	1234.5	1234.7	1234.9	1235.1	1236.6
177.5°	1240.3	1239.4	1238.7	1237.9	1237.0	1236.7	1236.8	1237.0	1237.2	1237.3	1238.7
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332087-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1442.6	1444.9	1447.1	1448.1	1447.9	1447.6	1447.4	1447.2
5°	1435.0	1437.8	1440.6	1441.7	1441.1	1440.6	1440.0	1439.5
7.5°	1419.8	1422.3	1424.8	1425.8	1425.5	1425.2	1424.9	1424.6
10°	1405.9	1408.3	1410.9	1411.8	1411.3	1410.7	1410.2	1409.6
12.5°	1390.6	1392.4	1394.2	1395.0	1394.6	1394.3	1394.0	1393.7
15°	1362.9	1365.2	1367.4	1367.7	1366.0	1364.4	1362.7	1361.0
17.5°	1328.0	1329.6	1331.1	1331.6	1331.0	1330.4	1329.8	1329.2
20°	1302.3	1303.4	1304.5	1304.6	1303.8	1302.9	1302.1	1301.2
22.5°	1274.9	1275.8	1276.7	1276.6	1275.6	1274.5	1273.4	1272.4
25°	1229.6	1229.9	1230.2	1229.9	1229.1	1228.2	1227.4	1226.5
27.5°	1181.5	1181.6	1181.9	1181.5	1180.4	1179.3	1178.3	1177.3
30°	1148.1	1148.1	1148.1	1147.2	1145.2	1143.3	1141.3	1139.4
32.5°	1113.1	1111.6	1110.0	1108.7	1107.7	1106.6	1105.6	1104.5
35°	1056.4	1054.7	1053.0	1051.5	1050.1	1048.8	1047.3	1046.0
37.5°	997.7	995.7	993.7	992.3	991.3	990.5	989.6	988.7
40°	959.4	957.2	955.0	953.3	952.2	951.1	950.0	948.9
42.5°	919.6	917.3	915.1	913.5	912.4	911.2	910.1	909.0
45°	860.1	856.7	853.4	851.0	849.7	848.3	846.9	845.5
47.5°	797.4	794.2	790.8	788.6	787.4	786.2	785.0	783.8
50°	756.0	753.0	749.9	747.6	745.9	744.3	742.6	740.9
52.5°	714.1	711.5	708.8	706.7	705.0	703.4	701.7	700.1
55°	650.1	647.1	644.0	641.8	640.5	639.1	637.7	636.3
57.5°	587.3	584.6	581.9	579.7	578.1	576.6	574.9	573.3
60°	543.0	540.4	538.0	536.0	534.6	533.2	531.9	530.4
62.5°	500.1	497.6	495.1	493.4	492.4	491.5	490.6	489.6
65°	436.4	434.2	432.0	430.5	429.6	428.8	427.9	427.1
67.5°	373.2	371.2	369.3	367.7	366.6	365.4	364.2	363.1
70°	332.3	330.4	328.4	326.8	325.4	324.0	322.7	321.3
72.5°	291.0	289.2	287.5	286.3	285.6	284.9	284.2	283.4
75°	231.3	230.0	228.5	227.4	226.6	225.8	225.0	224.1
77.5°	175.7	174.8	173.8	173.3	173.3	173.3	173.3	173.3
80°	140.1	139.9	139.6	139.5	139.5	139.5	139.5	139.5
82.5°	107.8	107.3	106.9	106.5	106.2	106.1	105.8	105.6
85°	61.2	60.6	60.0	59.8	59.8	59.8	59.8	59.8
87.5°	26.2	26.1	26.1	26.1	26.2	26.3	26.4	26.5
90°	23.7	24.6	25.3	26.0	26.4	26.8	27.2	27.6
92.5°	26.1	27.5	28.8	29.5	29.8	30.1	30.3	30.6
95°	31.4	32.8	34.2	34.9	34.9	34.9	34.9	34.9
97.5°	32.9	34.5	36.2	37.1	37.3	37.5	37.7	37.9
100°	33.7	35.3	36.9	37.9	38.0	38.3	38.4	38.7
102.5°	50.4	45.3	40.2	37.9	38.3	38.7	39.1	39.4
105°	129.1	92.9	56.7	38.9	39.3	39.7	40.1	40.5
107.5°	316.3	289.8	263.2	236.3	209.1	181.7	154.5	127.2
110°	401.6	394.8	388.1	370.1	340.9	311.6	282.3	253.1



TEST NUMBER: P332087-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	461.7	461.8	462.0	458.9	452.7	446.6	440.4	434.2
115°	532.3	534.4	536.5	537.9	538.7	539.6	540.3	541.1
117.5°	596.4	598.0	599.6	600.6	600.7	600.9	601.0	601.2
120°	638.3	639.9	641.6	642.4	642.4	642.4	642.4	642.4
122.5°	679.3	680.5	681.6	682.2	682.4	682.5	682.8	682.9
125°	737.1	737.5	737.9	738.3	738.7	739.2	739.6	740.0
127.5°	795.0	795.7	796.3	796.5	796.1	795.7	795.3	794.8
130°	830.0	830.8	831.6	831.8	831.4	831.0	830.6	830.2
132.5°	863.1	864.0	864.7	864.8	864.3	863.7	863.2	862.5
135°	913.3	913.9	914.6	914.6	913.9	913.3	912.7	912.1
137.5°	958.1	959.0	960.0	960.3	959.9	959.5	959.1	958.6
140°	986.4	987.2	988.1	988.2	987.9	987.5	987.1	986.7
142.5°	1013.4	1014.0	1014.6	1014.7	1014.2	1013.5	1013.0	1012.4
145°	1051.0	1051.4	1051.8	1051.9	1051.9	1051.9	1051.9	1051.9
147.5°	1084.7	1085.1	1085.4	1085.2	1084.3	1083.3	1082.4	1081.4
150°	1105.3	1105.6	1106.0	1106.0	1105.3	1104.8	1104.1	1103.5
152.5°	1123.6	1124.3	1125.1	1125.0	1124.0	1123.1	1122.1	1121.2
155°	1148.8	1149.9	1150.9	1150.7	1149.5	1148.3	1147.1	1145.9
157.5°	1170.8	1172.0	1173.2	1173.1	1171.5	1169.8	1168.2	1166.6
160°	1183.3	1184.5	1185.7	1185.7	1184.2	1182.8	1181.3	1179.9
162.5°	1194.7	1196.0	1197.5	1197.5	1196.2	1194.9	1193.7	1192.4
165°	1209.9	1211.5	1213.1	1213.2	1211.8	1210.4	1208.9	1207.5
167.5°	1221.6	1223.3	1225.0	1225.0	1223.3	1221.6	1220.0	1218.4
170°	1228.3	1229.9	1231.5	1231.5	1229.9	1228.3	1226.6	1225.0
172.5°	1232.7	1234.3	1236.0	1235.9	1234.1	1232.3	1230.5	1228.7
175°	1238.0	1239.4	1240.9	1240.7	1239.1	1237.5	1235.9	1234.2
177.5°	1239.9	1241.3	1242.5	1242.4	1240.8	1239.1	1237.5	1235.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

(END OF REPORT)