

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332088-927

Luminaire Tested: **S123DIP-S1165D1195U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332088-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1195U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7018.2 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332088-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332088-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	53	51	50	45
2	90	82	76	71	83	76	71	66	66	61	58	55	52	50	46	44	42	38
3	82	72	65	59	76	67	61	55	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	44	39	36	37	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	32	54	43	36	31	38	32	28	32	28	24	27	24	21	18
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	22	19	17
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15588	15588	15588
5°	15662	15446	15554
10°	15557	15312	15407
15°	15375	15139	15166
20°	15163	14892	14905
25°	14878	14598	14567
30°	14564	14270	14162
35°	14236	13925	13745
40°	13893	13543	13333
45°	13516	13192	12871
50°	13137	12762	12407
55°	12643	12314	11941
60°	12144	11795	11418
65°	11703	11227	10878
70°	11053	10581	10112
75°	10098	9736	9320
80°	9106	8722	8647
85°	7991	7694	7385



TEST NUMBER: P332088-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.4	1.9
10°-20°	385.2	5.5
20°-30°	569.0	8.1
30°-40°	664.6	9.5
40°-50°	668.2	9.5
50°-60°	587.0	8.4
60°-70°	437.3	6.2
70°-80°	249.1	3.5
80°-90°	75.0	1.1
90°-100°	76.3	1.1
100°-110°	228.5	3.3
110°-120°	388.6	5.5
120°-130°	511.1	7.3
130°-140°	574.5	8.2
140°-150°	564.7	8.0
150°-160°	475.4	6.8
160°-170°	316.5	4.5
170°-180°	110.8	1.6
0°-30°	1090.6	15.5
0°-40°	1755.3	25.0
0°-60°	3010.4	42.9
0°-90°	3771.8	53.7
90°-120°	693.4	9.9
90°-150°	2343.7	33.4
90°-180°	3246.0	46.3
0°-180°	7018.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1448	1448	1448	1448	1448	
5°	1450	1443	1430	1441	1440	137
15°	1380	1374	1358	1368	1361	389
25°	1253	1245	1229	1230	1226	577
35°	1083	1075	1060	1052	1046	677
45°	888	882	867	852	846	685
55°	674	672	656	643	636	603
65°	460	453	441	431	427	453
75°	243	238	234	228	224	260
85°	65	62	62	60	60	71
90°	1	10	22	26	28	7
95°	54	61	68	72	72	61
105°	207	209	217	217	219	222
115°	391	394	392	393	392	387
125°	572	575	574	570	566	510
135°	743	748	747	744	742	572
145°	901	903	906	905	901	563
155°	1032	1032	1033	1036	1030	475
165°	1124	1121	1121	1126	1120	317
175°	1169	1165	1165	1170	1164	111
180°	1172	1172	1172	1172	1172	



TEST NUMBER: P332088-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1453.2	1452.3	1451.4	1450.6	1449.6	1448.0	1445.6	1443.1	1440.7	1438.2	1440.4
5°	1449.5	1448.1	1446.7	1445.3	1443.9	1441.7	1438.7	1435.6	1432.6	1429.5	1432.3
7.5°	1435.3	1433.8	1432.5	1431.1	1429.7	1427.4	1424.3	1421.2	1418.0	1414.8	1417.3
10°	1423.3	1421.9	1420.5	1419.1	1417.8	1415.3	1411.7	1408.1	1404.5	1400.9	1403.4
12.5°	1407.4	1406.2	1405.0	1403.9	1402.7	1400.4	1397.1	1393.7	1390.3	1387.0	1388.8
15°	1379.7	1378.6	1377.5	1376.4	1375.3	1372.9	1369.4	1365.7	1362.2	1358.5	1360.7
17.5°	1347.6	1346.2	1344.7	1343.3	1341.8	1339.3	1335.7	1332.1	1328.5	1324.9	1326.5
20°	1323.7	1322.0	1320.3	1318.7	1317.1	1314.4	1310.8	1307.3	1303.6	1300.1	1301.2
22.5°	1296.8	1295.1	1293.5	1291.8	1290.1	1287.5	1283.9	1280.3	1276.8	1273.1	1274.0
25°	1252.7	1251.0	1249.4	1247.7	1246.1	1243.4	1239.8	1236.3	1232.6	1229.1	1229.3
27.5°	1205.6	1204.0	1202.5	1200.8	1199.2	1196.5	1192.6	1188.7	1184.9	1181.0	1181.2
30°	1171.8	1170.4	1169.0	1167.6	1166.3	1163.6	1159.8	1155.9	1152.0	1148.1	1148.1
32.5°	1137.9	1136.1	1134.2	1132.4	1130.6	1128.1	1125.2	1122.2	1119.2	1116.3	1114.7
35°	1083.4	1081.7	1080.1	1078.4	1076.7	1074.1	1070.5	1066.9	1063.3	1059.7	1058.0
37.5°	1027.5	1025.5	1023.3	1021.3	1019.1	1016.3	1012.6	1009.0	1005.4	1001.6	999.7
40°	988.7	987.1	985.4	983.7	982.1	979.3	975.4	971.5	967.7	963.8	961.6
42.5°	949.8	948.0	946.1	944.2	942.3	939.4	935.6	931.7	927.8	924.0	921.8
45°	887.9	886.8	885.7	884.6	883.4	881.1	877.5	873.9	870.3	866.6	863.4
47.5°	826.3	824.7	823.2	821.5	819.9	817.5	814.0	810.6	807.3	803.9	800.7
50°	784.5	783.2	781.7	780.4	779.0	776.5	772.9	769.3	765.6	762.1	759.1
52.5°	740.7	739.7	738.8	737.8	736.9	734.5	730.7	726.9	723.1	719.2	716.6
55°	673.7	673.4	673.1	672.9	672.6	670.7	667.0	663.5	659.8	656.2	653.2
57.5°	609.9	609.0	608.0	607.1	606.2	604.3	601.3	598.5	595.6	592.7	590.0
60°	564.1	563.8	563.6	563.2	563.0	561.2	557.9	554.5	551.2	547.9	545.4
62.5°	523.2	522.5	521.8	521.1	520.4	518.3	515.0	511.7	508.4	505.1	502.6
65°	459.5	458.1	456.7	455.3	453.9	451.9	449.1	446.3	443.5	440.8	438.6
67.5°	392.0	390.8	389.6	388.3	387.1	385.5	383.3	381.3	379.1	377.1	375.1
70°	351.2	349.5	347.8	346.2	344.5	342.9	341.2	339.5	337.9	336.2	334.3
72.5°	308.3	307.1	305.9	304.7	303.5	301.9	300.0	298.1	296.3	294.4	292.6
75°	242.8	241.7	240.6	239.5	238.4	237.4	236.6	235.8	235.0	234.1	232.7
77.5°	184.8	184.2	183.5	183.0	182.4	181.6	180.5	179.6	178.6	177.6	176.7
80°	146.9	146.1	145.3	144.4	143.6	142.9	142.4	141.8	141.2	140.7	140.5
82.5°	110.1	109.9	109.7	109.6	109.4	109.2	109.2	109.1	108.9	108.8	108.4
85°	64.7	64.2	63.6	63.1	62.5	62.3	62.3	62.3	62.3	62.3	61.7
87.5°	26.1	25.8	25.6	25.3	25.0	25.1	25.4	25.7	26.1	26.3	26.3
90°	1.0	2.9	5.0	7.1	9.1	11.5	14.1	16.8	19.4	22.1	22.9
92.5°	22.3	23.7	25.0	26.5	27.8	29.3	30.8	32.3	33.8	35.3	36.0
95°	54.3	55.8	57.2	58.6	60.0	61.6	63.2	64.8	66.5	68.1	68.9
97.5°	96.5	97.5	98.6	99.7	100.7	101.9	103.1	104.3	105.4	106.5	107.5
100°	125.2	126.4	127.6	128.9	130.1	131.2	132.2	133.2	134.3	135.3	135.9
102.5°	158.3	159.1	159.8	160.5	161.3	162.3	163.7	165.0	166.4	167.7	168.3
105°	207.1	207.5	207.9	208.3	208.7	209.8	211.7	213.6	215.4	217.2	217.2
107.5°	263.8	264.0	264.3	264.5	264.7	265.3	266.0	266.7	267.4	268.2	268.9
110°	299.1	299.5	299.9	300.4	300.8	301.2	301.6	302.0	302.4	302.9	303.6



TEST NUMBER: P332088-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	336.0	336.2	336.4	336.7	336.9	337.1	337.2	337.2	337.3	337.4	338.4
115°	391.2	391.8	392.4	393.0	393.6	393.7	393.3	392.9	392.5	392.1	392.3
117.5°	446.8	447.2	447.6	448.0	448.4	448.4	447.8	447.3	446.8	446.2	446.2
120°	481.4	482.6	483.9	485.1	486.3	486.4	485.4	484.3	483.3	482.3	482.1
122.5°	517.5	518.3	519.3	520.1	521.1	521.3	520.7	520.1	519.7	519.1	518.6
125°	572.5	573.1	573.7	574.3	575.0	575.0	574.6	574.3	573.9	573.5	572.6
127.5°	623.3	624.6	625.9	627.2	628.5	629.0	628.5	628.0	627.6	627.2	626.1
130°	657.2	658.8	660.4	662.1	663.7	664.2	663.6	663.0	662.4	661.8	661.0
132.5°	691.0	692.7	694.3	695.9	697.6	698.2	697.8	697.3	696.8	696.4	695.4
135°	742.8	744.0	745.2	746.5	747.7	748.2	748.0	747.8	747.6	747.3	746.6
137.5°	790.7	791.6	792.7	793.7	794.7	795.5	796.1	796.5	797.1	797.6	796.8
140°	823.8	824.8	825.9	826.9	827.8	828.5	828.7	828.9	829.1	829.3	829.1
142.5°	854.0	855.0	856.0	857.1	858.1	858.7	859.1	859.5	859.8	860.2	860.0
145°	901.1	901.5	901.9	902.3	902.7	903.2	903.9	904.4	905.1	905.7	905.5
147.5°	942.3	943.1	943.8	944.5	945.3	945.9	946.5	947.1	947.6	948.2	948.2
150°	971.1	971.5	971.8	972.2	972.7	973.1	973.5	973.9	974.3	974.7	974.7
152.5°	994.6	995.2	995.8	996.3	996.9	997.3	997.5	997.8	998.1	998.3	998.6
155°	1031.8	1031.8	1031.8	1031.8	1031.8	1031.9	1032.1	1032.3	1032.5	1032.7	1033.6
157.5°	1063.4	1063.2	1063.0	1062.7	1062.5	1062.4	1062.6	1062.8	1063.0	1063.1	1064.0
160°	1083.3	1082.9	1082.5	1082.1	1081.7	1081.5	1081.5	1081.5	1081.5	1081.5	1082.5
162.5°	1101.0	1100.4	1099.9	1099.3	1098.8	1098.5	1098.7	1098.8	1099.0	1099.2	1100.2
165°	1123.9	1123.2	1122.6	1122.0	1121.4	1121.1	1121.1	1121.1	1121.1	1121.1	1122.3
167.5°	1142.1	1141.2	1140.4	1139.6	1138.8	1138.4	1138.6	1138.8	1138.9	1139.1	1140.3
170°	1152.4	1151.5	1150.7	1149.9	1149.1	1148.7	1148.7	1148.7	1148.7	1148.7	1150.1
172.5°	1160.5	1159.7	1158.8	1158.0	1157.2	1156.8	1156.8	1156.8	1156.8	1156.8	1158.1
175°	1168.9	1168.2	1167.3	1166.5	1165.7	1165.2	1165.2	1165.2	1165.2	1165.2	1166.5
177.5°	1172.4	1171.8	1171.2	1170.4	1169.8	1169.5	1169.5	1169.5	1169.5	1169.5	1170.4
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332088-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1442.6	1444.9	1447.1	1448.1	1447.9	1447.6	1447.4	1447.2
5°	1435.0	1437.8	1440.6	1441.7	1441.1	1440.6	1440.0	1439.5
7.5°	1419.8	1422.3	1424.8	1425.8	1425.5	1425.2	1424.9	1424.6
10°	1405.9	1408.3	1410.9	1411.8	1411.3	1410.7	1410.2	1409.6
12.5°	1390.6	1392.4	1394.2	1395.0	1394.6	1394.3	1394.0	1393.7
15°	1362.9	1365.2	1367.4	1367.7	1366.0	1364.4	1362.7	1361.0
17.5°	1328.0	1329.6	1331.1	1331.6	1331.0	1330.4	1329.8	1329.2
20°	1302.3	1303.4	1304.5	1304.6	1303.8	1302.9	1302.1	1301.2
22.5°	1274.9	1275.8	1276.7	1276.6	1275.6	1274.5	1273.4	1272.4
25°	1229.6	1229.9	1230.2	1229.9	1229.1	1228.2	1227.4	1226.5
27.5°	1181.5	1181.6	1181.9	1181.5	1180.4	1179.3	1178.3	1177.3
30°	1148.1	1148.1	1148.1	1147.2	1145.2	1143.3	1141.3	1139.4
32.5°	1113.1	1111.6	1110.0	1108.7	1107.7	1106.6	1105.6	1104.5
35°	1056.4	1054.7	1053.0	1051.5	1050.1	1048.8	1047.3	1046.0
37.5°	997.7	995.7	993.7	992.3	991.3	990.5	989.6	988.7
40°	959.4	957.2	955.0	953.3	952.2	951.1	950.0	948.9
42.5°	919.6	917.3	915.1	913.5	912.4	911.2	910.1	909.0
45°	860.1	856.7	853.4	851.0	849.7	848.3	846.9	845.5
47.5°	797.4	794.2	790.8	788.6	787.4	786.2	785.0	783.8
50°	756.0	753.0	749.9	747.6	745.9	744.3	742.6	740.9
52.5°	714.1	711.5	708.8	706.7	705.0	703.4	701.7	700.1
55°	650.1	647.1	644.0	641.8	640.5	639.1	637.7	636.3
57.5°	587.3	584.6	581.9	579.7	578.1	576.6	574.9	573.3
60°	543.0	540.4	538.0	536.0	534.6	533.2	531.9	530.4
62.5°	500.1	497.6	495.1	493.4	492.4	491.5	490.6	489.6
65°	436.4	434.2	432.0	430.5	429.6	428.8	427.9	427.1
67.5°	373.2	371.2	369.3	367.7	366.6	365.4	364.2	363.1
70°	332.3	330.4	328.4	326.8	325.4	324.0	322.7	321.3
72.5°	291.0	289.2	287.5	286.3	285.6	284.9	284.2	283.4
75°	231.3	230.0	228.5	227.4	226.6	225.8	225.0	224.1
77.5°	175.7	174.8	173.8	173.3	173.3	173.3	173.3	173.3
80°	140.1	139.9	139.6	139.5	139.5	139.5	139.5	139.5
82.5°	107.8	107.3	106.9	106.5	106.2	106.1	105.8	105.6
85°	61.2	60.6	60.0	59.8	59.8	59.8	59.8	59.8
87.5°	26.2	26.1	26.1	26.1	26.2	26.3	26.4	26.5
90°	23.8	24.6	25.3	26.0	26.4	26.8	27.2	27.6
92.5°	36.7	37.3	37.9	38.2	37.9	37.7	37.4	37.2
95°	69.7	70.6	71.4	71.8	71.8	71.8	71.8	71.8
97.5°	108.4	109.4	110.4	110.7	110.7	110.6	110.5	110.4
100°	136.5	137.1	137.8	138.2	138.7	139.1	139.5	139.9
102.5°	168.9	169.5	170.2	170.4	170.3	170.2	170.2	170.1
105°	217.2	217.2	217.2	217.5	217.9	218.2	218.6	219.0
107.5°	269.5	270.2	270.8	271.0	270.8	270.5	270.3	270.1
110°	304.4	305.3	306.1	306.3	305.9	305.5	305.1	304.7



TEST NUMBER: P332088-927

CATALOG NUMBER: S123DIP-S1165D1195U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	339.4	340.4	341.4	341.8	341.7	341.7	341.6	341.5
115°	392.5	392.7	392.9	392.9	392.7	392.5	392.3	392.1
117.5°	446.2	446.1	446.1	445.8	445.2	444.6	444.0	443.5
120°	481.9	481.7	481.5	481.2	480.8	480.4	480.0	479.5
122.5°	518.1	517.5	517.0	516.4	515.9	515.3	514.7	514.1
125°	571.8	571.0	570.1	569.3	568.5	567.7	566.9	566.1
127.5°	624.9	623.8	622.6	621.5	620.6	619.6	618.7	617.8
130°	660.1	659.3	658.5	657.4	655.9	654.5	653.1	651.6
132.5°	694.4	693.5	692.4	691.4	690.3	689.2	688.1	687.0
135°	745.8	744.9	744.1	743.5	743.1	742.7	742.3	741.9
137.5°	795.9	795.0	794.2	793.4	792.6	791.9	791.1	790.3
140°	828.9	828.7	828.5	827.7	826.2	824.8	823.4	822.0
142.5°	859.8	859.6	859.4	858.7	857.6	856.5	855.5	854.4
145°	905.3	905.1	904.9	904.4	903.6	902.7	901.9	901.1
147.5°	948.2	948.2	948.2	947.6	946.3	945.2	943.9	942.7
150°	974.7	974.7	974.7	974.1	972.9	971.7	970.4	969.2
152.5°	998.9	999.3	999.6	999.3	998.1	997.1	996.0	995.0
155°	1034.4	1035.1	1036.0	1035.7	1034.3	1032.8	1031.4	1029.9
157.5°	1064.8	1065.6	1066.5	1066.4	1065.2	1064.1	1063.0	1061.8
160°	1083.5	1084.6	1085.6	1085.7	1084.9	1084.0	1083.2	1082.4
162.5°	1101.2	1102.2	1103.3	1103.1	1101.8	1100.5	1099.2	1097.9
165°	1123.6	1124.7	1126.0	1125.8	1124.4	1123.0	1121.6	1120.1
167.5°	1141.6	1142.9	1144.1	1144.1	1142.9	1141.6	1140.3	1139.1
170°	1151.5	1153.0	1154.4	1154.4	1153.0	1151.5	1150.1	1148.7
172.5°	1159.4	1160.6	1161.9	1161.8	1160.3	1158.9	1157.5	1156.0
175°	1167.7	1168.9	1170.1	1170.1	1168.6	1167.2	1165.8	1164.3
177.5°	1171.5	1172.4	1173.4	1173.3	1172.2	1171.0	1169.9	1168.8
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7

(END OF REPORT)