

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331430

Luminaire Tested: **S122DIP-S1005D530U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331430
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S1005D530U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6291.5 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331430

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331430

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74	74	74	74	70		
1	103	99	95	92	97	94	90	87	84	81	79	75	73	71	67	66	64	64	64	64	64	64	64	60		
2	94	87	81	76	89	83	77	73	74	70	67	67	64	61	60	57	55	55	55	55	55	55	55	52		
3	86	77	70	64	82	73	67	62	66	61	57	60	56	52	54	50	48	48	48	48	48	48	48	44		
4	80	69	61	55	75	66	58	53	59	54	49	54	49	45	48	45	42	42	42	42	42	42	42	39		
5	73	62	54	48	69	59	52	46	54	48	43	49	44	40	44	40	37	37	37	37	37	37	37	34		
6	68	56	48	42	64	53	46	41	49	43	38	44	39	35	40	36	33	33	33	33	33	33	33	30		
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	37	33	29	29	29	29	29	29	29	27		
8	59	46	39	33	56	44	37	32	41	35	30	37	32	29	34	30	27	27	27	27	27	27	27	25		
9	55	43	35	30	52	41	34	29	38	32	28	34	29	26	32	27	24	24	24	24	24	24	24	22		
10	51	39	32	27	49	38	31	27	35	29	25	32	27	24	29	25	22	22	22	22	22	22	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	32195	32195	32195	32195
5°	36094	32405	28716	32405
10°	41361	32139	24851	32139
15°	45757	31550	21956	31550
20°	45060	30917	20015	30917
25°	40631	30077	18786	30077
30°	33575	28732	17889	28732
35°	24471	27325	17251	27325
40°	19545	25665	16895	25665
45°	17080	23745	16413	23745
50°	16053	21886	16093	21886
55°	14798	19997	15662	19997
60°	13563	17990	14996	17990
65°	12355	16191	14346	16191
70°	11216	14436	13388	14436
75°	9944	12477	11859	12477
80°	8554	10330	9549	10330
85°	7669	7669	5687	7669



TEST NUMBER: P331430

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.9	3.0
10°-20°	552.1	8.8
20°-30°	801.2	12.7
30°-40°	845.5	13.4
40°-50°	748.6	11.9
50°-60°	597.4	9.5
60°-70°	406.1	6.5
70°-80°	208.2	3.3
80°-90°	52.9	0.8
90°-100°	42.8	0.7
100°-110°	133.0	2.1
110°-120°	227.3	3.6
120°-130°	298.9	4.8
130°-140°	335.5	5.3
140°-150°	329.0	5.2
150°-160°	275.9	4.4
160°-170°	183.0	2.9
170°-180°	64.0	1.0
0°-30°	1543.2	24.5
0°-40°	2388.7	38.0
0°-60°	3734.8	59.4
0°-90°	4402.0	70.0
90°-120°	403.1	6.4
90°-150°	1366.6	21.7
90°-180°	1889.0	30.0
0°-180°	6291.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1994	1994	1994	1994	1994	
5°	2227	1999	1772	1999	2227	222
15°	2737	1888	1314	1888	2737	755
25°	2281	1688	1054	1688	2281	1031
35°	1242	1386	875	1386	1242	807
45°	748	1040	719	1040	748	588
55°	526	710	556	710	526	471
65°	323	424	376	424	323	322
75°	159	200	190	200	159	170
85°	41	41	31	41	41	46
90°	19	1	19	1	19	11
95°	35	30	35	30	35	39
105°	127	123	127	123	127	133
115°	228	228	228	228	228	225
125°	333	332	333	332	333	297
135°	434	429	434	429	434	334
145°	527	521	527	521	527	329
155°	600	596	600	596	600	276
165°	649	648	649	648	649	183
175°	672	675	672	675	672	64
180°	676	676	676	676	676	



TEST NUMBER: P331430

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2086.0	2086.6	2087.8	2078.0	2076.8	2076.8	2068.2	2060.9	2052.3	2040.6	2041.9
5°	2227.0	2235.4	2238.5	2229.3	2215.5	2214.0	2201.0	2179.5	2159.6	2143.5	2132.0
7.5°	2395.3	2398.7	2391.2	2379.1	2368.8	2350.4	2326.2	2302.4	2269.2	2238.7	2216.0
10°	2522.8	2527.4	2514.4	2496.8	2482.2	2460.8	2425.5	2389.5	2345.8	2303.7	2269.9
12.5°	2619.7	2631.0	2614.3	2612.0	2587.1	2557.6	2515.6	2497.4	2435.9	2377.2	2341.1
15°	2737.4	2736.6	2738.2	2723.6	2705.2	2700.6	2656.2	2607.9	2521.3	2486.8	2427.0
17.5°	2703.4	2715.0	2720.4	2720.2	2719.8	2716.9	2702.6	2672.1	2628.7	2572.8	2503.8
20°	2622.5	2637.8	2640.1	2657.7	2667.7	2680.7	2686.1	2677.6	2650.8	2604.1	2544.3
22.5°	2497.4	2501.7	2508.9	2536.3	2557.9	2590.6	2607.6	2635.9	2625.7	2602.8	2552.9
25°	2280.7	2273.0	2299.8	2313.6	2363.4	2415.5	2453.1	2494.5	2531.3	2553.5	2538.9
27.5°	2020.4	2008.9	2049.1	2085.7	2126.2	2182.6	2241.1	2310.2	2367.7	2439.6	2464.3
30°	1800.9	1807.8	1846.1	1885.2	1946.5	2026.2	2092.1	2168.0	2250.0	2330.5	2386.4
32.5°	1564.3	1590.8	1615.0	1674.9	1728.9	1817.8	1914.3	2009.2	2111.5	2203.0	2289.6
35°	1241.5	1272.1	1305.9	1349.5	1425.4	1513.5	1607.8	1735.8	1875.3	2000.2	2102.9
37.5°	1045.0	1040.1	1059.4	1091.0	1152.4	1223.6	1332.1	1458.5	1622.7	1769.5	1914.3
40°	927.3	924.2	938.0	967.1	1013.9	1066.0	1161.0	1272.1	1424.6	1604.0	1776.4
42.5°	846.4	848.2	855.9	876.4	908.4	951.3	1022.5	1117.0	1256.7	1425.6	1610.9
45°	748.0	753.3	761.8	771.7	790.1	825.4	865.2	932.7	1043.0	1184.0	1366.4
47.5°	677.1	677.3	685.9	694.6	705.5	725.4	757.9	800.2	878.1	992.9	1149.7
50°	639.1	633.8	639.9	646.8	658.3	672.1	693.5	733.4	785.5	878.2	1009.3
52.5°	592.5	592.7	598.2	600.8	611.1	624.9	644.5	672.1	719.3	791.8	899.5
55°	525.7	529.5	532.6	537.2	546.4	556.4	571.7	590.1	626.9	681.3	761.0
57.5°	462.9	464.1	467.2	475.9	481.7	490.9	505.5	522.2	546.1	586.4	646.3
60°	420.0	420.0	426.1	429.9	437.6	446.8	458.3	474.4	495.8	528.8	577.1
62.5°	380.7	380.1	382.6	388.8	394.7	403.3	414.7	428.4	448.6	477.9	517.6
65°	323.4	321.9	326.5	328.0	334.1	342.6	351.8	366.3	382.4	403.9	439.1
67.5°	268.2	270.1	272.5	275.4	278.8	287.7	293.8	304.1	317.7	335.5	359.4
70°	237.6	237.6	237.6	239.9	244.5	249.1	255.2	263.6	276.7	292.0	313.4
72.5°	203.2	205.7	208.1	206.8	212.6	215.3	222.7	227.5	239.9	249.7	268.7
75°	159.4	159.4	159.4	163.2	165.5	167.8	172.4	177.0	183.2	195.4	205.4
77.5°	118.9	118.6	119.4	120.3	122.8	125.5	126.9	131.0	136.7	142.4	150.8
80°	92.0	93.5	94.3	95.8	95.8	97.3	98.1	103.5	107.3	111.1	116.5
82.5°	71.1	71.4	71.6	71.9	72.5	73.4	75.4	77.1	78.5	81.7	85.8
85°	41.4	40.6	40.6	42.1	41.4	41.4	42.9	44.4	44.4	45.2	47.5
87.5°	19.8	19.8	20.4	19.7	19.7	20.3	20.4	19.8	20.5	21.2	21.2
90°	19.4	19.3	19.1	19.0	18.9	18.9	19.2	19.5	19.7	20.0	17.2
92.5°	18.5	18.5	18.4	18.4	18.4	18.3	18.3	18.2	18.2	18.1	17.5
95°	35.4	35.6	35.9	36.1	36.4	36.5	36.5	36.5	36.5	36.5	36.2
97.5°	61.2	61.3	61.3	61.3	61.3	61.4	61.4	61.4	61.4	61.4	60.9
100°	78.1	78.3	78.4	78.5	78.6	78.7	78.7	78.7	78.7	78.7	78.3
102.5°	97.3	97.4	97.5	97.7	97.8	97.8	97.7	97.6	97.5	97.4	96.9
105°	126.6	126.6	126.6	126.6	126.6	126.5	126.2	126.0	125.7	125.5	125.2
107.5°	154.2	154.8	155.4	155.9	156.5	156.8	156.7	156.6	156.5	156.4	156.4
110°	175.6	176.0	176.4	176.8	177.2	177.3	177.3	177.3	177.3	177.3	177.3



TEST NUMBER: P331430

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	196.2	196.4	196.7	197.0	197.3	197.6	197.9	198.2	198.5	198.8	198.9
115°	228.1	228.5	228.9	229.2	229.6	229.9	230.0	230.1	230.3	230.4	230.6
117.5°	258.5	258.9	259.3	259.7	260.1	260.4	260.7	261.0	261.3	261.6	262.3
120°	280.0	280.4	280.8	281.1	281.5	281.7	281.7	281.7	281.7	281.7	282.7
122.5°	301.0	301.3	301.5	301.8	302.1	302.4	302.7	303.0	303.3	303.6	304.3
125°	333.0	333.1	333.3	333.4	333.5	333.8	334.2	334.5	334.9	335.3	335.7
127.5°	362.2	362.6	363.0	363.4	363.8	364.3	364.7	365.2	365.6	366.1	366.6
130°	383.2	383.7	384.2	384.7	385.2	385.6	385.9	386.1	386.4	386.6	386.9
132.5°	403.3	403.7	404.1	404.5	404.9	405.4	405.9	406.5	407.1	407.6	407.6
135°	434.5	434.9	435.3	435.7	436.0	436.3	436.4	436.6	436.7	436.8	436.6
137.5°	462.8	463.3	463.8	464.3	464.8	465.1	465.2	465.3	465.4	465.5	465.2
140°	482.4	482.9	483.4	483.9	484.5	484.7	484.7	484.7	484.7	484.7	484.1
142.5°	500.2	500.7	501.2	501.7	502.2	502.4	502.3	502.2	502.1	502.0	501.6
145°	526.9	527.4	527.9	528.4	528.9	529.1	529.0	528.9	528.7	528.6	527.9
147.5°	550.7	551.2	551.7	552.2	552.7	552.8	552.5	552.2	551.9	551.7	551.1
150°	566.3	566.6	567.0	567.4	567.8	567.8	567.4	567.0	566.6	566.3	565.7
152.5°	580.9	581.3	581.8	582.3	582.8	582.8	582.3	581.8	581.3	580.9	580.2
155°	600.5	600.8	601.2	601.6	602.0	601.9	601.2	600.6	600.0	599.3	598.9
157.5°	617.3	618.0	618.6	619.2	619.8	619.7	618.8	617.9	617.1	616.2	616.0
160°	627.8	628.3	628.9	629.4	629.9	629.7	629.0	628.2	627.5	626.7	626.6
162.5°	637.0	637.6	638.2	638.8	639.4	639.3	638.4	637.5	636.7	635.8	635.7
165°	648.9	649.6	650.2	650.8	651.5	651.3	650.5	649.6	648.7	647.8	647.8
167.5°	658.7	659.4	660.1	660.7	661.4	661.3	660.4	659.5	658.6	657.7	657.7
170°	663.8	664.5	665.3	666.0	666.8	666.7	665.9	665.0	664.1	663.2	663.3
172.5°	667.9	668.6	669.4	670.2	670.9	670.8	670.0	669.1	668.2	667.3	667.4
175°	672.3	673.1	673.8	674.6	675.4	675.3	674.4	673.5	672.6	671.7	672.0
177.5°	674.4	675.0	675.6	676.2	676.8	676.8	676.2	675.6	675.0	674.4	674.6
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331430

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2046.2	2041.3	2038.2	2027.2	2017.3	2007.5	2004.5	2005.7	1992.2	1979.3	1973.8
5°	2125.9	2110.5	2096.0	2075.3	2050.8	2023.9	2010.1	1999.4	1972.6	1943.5	1926.6
7.5°	2197.3	2175.4	2147.3	2108.4	2072.7	2030.5	2003.7	1979.9	1940.7	1899.6	1874.5
10°	2240.8	2210.9	2174.9	2127.4	2083.7	2032.4	1996.3	1960.3	1914.3	1865.3	1834.6
12.5°	2278.2	2237.9	2202.5	2141.5	2089.8	2025.6	1982.9	1932.1	1883.7	1825.4	1795.4
15°	2367.3	2292.9	2225.5	2156.5	2092.9	2003.2	1955.7	1887.5	1823.9	1751.9	1717.4
17.5°	2436.1	2352.5	2246.3	2158.7	2084.5	1985.2	1915.4	1833.7	1758.5	1676.2	1629.3
20°	2475.3	2379.5	2265.3	2161.1	2072.2	1958.8	1882.9	1799.4	1711.3	1618.5	1568.0
22.5°	2498.6	2397.9	2285.0	2151.9	2047.7	1937.3	1841.8	1750.3	1661.0	1560.9	1507.9
25°	2506.0	2414.0	2294.5	2144.3	2017.0	1892.1	1777.2	1688.3	1580.2	1486.7	1409.3
27.5°	2469.5	2403.6	2288.6	2129.8	1981.6	1835.6	1707.4	1606.7	1492.7	1391.2	1313.4
30°	2424.7	2386.4	2274.5	2115.1	1953.4	1796.3	1655.3	1541.1	1427.7	1325.0	1245.3
32.5°	2355.5	2347.2	2248.8	2094.3	1923.4	1746.7	1600.8	1485.3	1359.7	1258.8	1182.8
35°	2219.4	2256.1	2194.1	2047.7	1866.8	1676.0	1518.1	1386.3	1256.1	1159.5	1088.2
37.5°	2037.0	2128.3	2112.1	1979.5	1790.5	1599.1	1424.8	1287.0	1162.9	1065.4	995.5
40°	1911.3	2027.8	2044.6	1927.4	1736.6	1539.6	1354.9	1217.7	1096.6	1007.8	937.2
42.5°	1776.4	1912.5	1958.8	1864.8	1677.7	1477.1	1292.4	1150.3	1030.4	944.0	881.5
45°	1550.3	1730.4	1814.0	1760.3	1579.5	1374.1	1184.0	1039.9	931.1	849.9	801.6
47.5°	1339.0	1535.8	1648.1	1629.1	1470.2	1266.8	1078.9	940.6	834.7	769.9	726.7
50°	1189.4	1391.7	1527.3	1533.5	1391.7	1190.1	1001.6	871.3	774.0	713.5	678.2
52.5°	1059.4	1252.5	1400.4	1432.9	1304.0	1110.4	932.3	802.7	717.0	661.4	629.8
55°	889.7	1053.0	1217.0	1276.7	1173.3	989.4	824.6	710.4	629.9	591.6	564.0
57.5°	739.7	875.8	1027.2	1093.3	1029.5	872.1	717.6	618.4	553.2	519.6	498.4
60°	660.6	767.9	902.8	981.7	926.5	786.3	651.4	557.1	503.5	473.6	453.7
62.5°	587.0	682.1	796.1	868.3	838.2	706.0	585.2	502.0	455.7	427.6	413.2
65°	484.3	559.4	647.6	714.2	694.3	593.9	495.1	423.8	387.0	364.8	353.3
67.5°	398.8	453.1	514.2	572.6	556.5	485.4	406.0	350.5	323.1	303.9	297.0
70°	344.9	386.2	440.7	487.4	474.4	416.1	353.3	305.8	282.0	265.9	259.0
72.5°	293.4	327.4	368.9	407.1	398.3	349.9	297.5	261.6	243.4	228.5	222.9
75°	221.5	247.5	272.8	298.1	295.8	258.3	227.6	200.0	185.5	174.0	171.7
77.5°	163.5	178.1	195.3	210.3	206.1	184.7	160.6	144.8	134.1	126.4	125.2
80°	124.9	133.3	145.6	156.3	151.0	141.8	122.6	111.1	103.5	95.8	92.7
82.5°	90.6	99.0	106.4	112.2	108.1	99.5	87.7	79.9	75.3	70.0	68.8
85°	47.5	52.1	55.2	56.7	55.2	49.8	44.4	41.4	37.6	35.3	34.5
87.5°	21.3	20.7	20.2	20.9	18.8	18.5	15.7	13.6	13.3	13.0	12.1
90°	14.4	11.6	8.8	6.7	5.1	3.6	2.1	0.6	2.1	3.6	5.1
92.5°	16.8	16.2	15.5	14.6	13.5	12.4	11.3	10.2	11.3	12.4	13.5
95°	36.0	35.7	35.5	34.7	33.5	32.2	30.9	29.7	30.9	32.2	33.5
97.5°	60.4	59.9	59.4	58.6	57.5	56.4	55.3	54.2	55.3	56.4	57.5
100°	77.9	77.6	77.2	76.5	75.5	74.4	73.4	72.4	73.4	74.4	75.5
102.5°	96.4	96.0	95.5	94.8	94.0	93.2	92.4	91.6	92.4	93.2	94.0
105°	124.9	124.7	124.4	124.1	123.7	123.4	123.0	122.6	123.0	123.4	123.7
107.5°	156.4	156.4	156.4	156.1	155.5	155.0	154.4	153.9	154.4	155.0	155.5
110°	177.3	177.3	177.3	177.0	176.2	175.4	174.7	173.9	174.7	175.4	176.2



TEST NUMBER: P331430

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	199.0	199.1	199.2	198.9	198.1	197.3	196.6	195.8	196.6	197.3	198.1
115°	230.9	231.1	231.4	231.1	230.4	229.6	228.9	228.1	228.9	229.6	230.4
117.5°	263.0	263.8	264.5	264.3	263.3	262.3	261.3	260.3	261.3	262.3	263.3
120°	283.7	284.7	285.8	285.8	284.7	283.7	282.7	281.7	282.7	283.7	284.7
122.5°	305.0	305.7	306.4	306.2	305.0	303.8	302.5	301.3	302.5	303.8	305.0
125°	336.1	336.4	336.8	336.4	335.3	334.2	333.0	331.9	333.0	334.2	335.3
127.5°	367.0	367.5	367.9	367.4	366.0	364.5	363.1	361.6	363.1	364.5	366.0
130°	387.1	387.4	387.6	386.9	385.3	383.6	382.0	380.4	382.0	383.6	385.3
132.5°	407.5	407.5	407.4	406.7	405.4	404.0	402.7	401.3	402.7	404.0	405.4
135°	436.3	436.0	435.8	435.0	433.6	432.2	430.8	429.4	430.8	432.2	433.6
137.5°	464.9	464.6	464.2	463.5	462.4	461.2	460.1	458.9	460.1	461.2	462.4
140°	483.4	482.8	482.2	481.3	480.1	479.0	477.9	476.7	477.9	479.0	480.1
142.5°	501.2	500.8	500.3	499.5	498.4	497.3	496.1	495.0	496.1	497.3	498.4
145°	527.1	526.3	525.6	524.8	523.9	523.0	522.1	521.2	522.1	523.0	523.9
147.5°	550.6	550.1	549.6	548.8	547.8	546.7	545.6	544.6	545.6	546.7	547.8
150°	565.2	564.7	564.2	563.6	562.8	562.1	561.3	560.6	561.3	562.1	562.8
152.5°	579.6	579.0	578.4	577.7	577.0	576.2	575.5	574.7	575.5	576.2	577.0
155°	598.6	598.2	597.8	597.4	597.0	596.7	596.3	595.9	596.3	596.7	597.0
157.5°	615.8	615.5	615.3	615.1	614.8	614.5	614.3	614.0	614.3	614.5	614.8
160°	626.4	626.3	626.2	626.0	625.7	625.5	625.2	625.0	625.2	625.5	625.7
162.5°	635.6	635.4	635.3	635.2	635.2	635.1	635.1	635.0	635.1	635.1	635.2
165°	647.8	647.8	647.8	647.9	648.0	648.1	648.2	648.4	648.2	648.1	648.0
167.5°	657.8	657.8	657.8	658.0	658.4	658.8	659.2	659.5	659.2	658.8	658.4
170°	663.4	663.6	663.7	664.0	664.3	664.7	665.1	665.5	665.1	664.7	664.3
172.5°	667.6	667.7	667.8	668.1	668.4	668.8	669.2	669.6	669.2	668.8	668.4
175°	672.3	672.5	672.8	673.1	673.5	673.8	674.2	674.6	674.2	673.8	673.5
177.5°	674.8	675.0	675.2	675.4	675.7	676.0	676.3	676.7	676.3	676.0	675.7
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331430

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1967.7	1964.0	1951.1	1944.4	1933.4	1922.9	1916.2	1919.3	1921.7	1920.5	1918.6
5°	1911.3	1896.7	1874.5	1855.3	1841.5	1816.3	1805.5	1800.2	1795.6	1790.2	1784.8
7.5°	1844.1	1821.2	1789.3	1762.0	1736.2	1704.8	1686.9	1676.2	1665.1	1653.0	1642.3
10°	1796.3	1764.1	1730.4	1692.1	1661.5	1633.1	1607.8	1590.9	1575.6	1561.1	1550.3
12.5°	1746.1	1709.0	1667.3	1614.9	1581.1	1540.5	1536.7	1507.0	1483.0	1474.0	1461.4
15°	1666.0	1613.9	1561.1	1499.0	1472.2	1435.4	1412.4	1389.4	1368.7	1354.1	1350.3
17.5°	1575.2	1507.7	1455.1	1410.5	1366.6	1328.9	1307.7	1289.3	1272.3	1252.8	1250.2
20°	1505.9	1447.6	1390.2	1351.1	1305.9	1267.5	1241.5	1223.1	1208.5	1197.0	1187.1
22.5°	1440.3	1376.5	1323.9	1281.2	1236.6	1205.6	1185.1	1167.3	1155.2	1142.5	1133.1
25°	1335.0	1285.2	1227.7	1179.4	1142.6	1122.7	1105.8	1090.5	1082.9	1074.4	1063.7
27.5°	1242.9	1187.5	1133.7	1096.3	1064.0	1046.4	1034.4	1024.0	1016.8	1011.9	1005.8
30°	1177.9	1121.9	1079.8	1043.0	1016.2	998.6	990.9	984.8	976.3	973.3	970.2
32.5°	1115.3	1064.9	1028.9	997.0	971.4	959.9	952.9	947.4	940.8	937.7	931.6
35°	1026.9	984.8	949.5	931.9	911.2	901.2	895.9	888.2	882.1	879.0	878.2
37.5°	943.7	907.1	883.9	861.2	852.5	846.4	839.0	833.8	832.0	831.5	830.7
40°	889.7	859.8	839.2	820.8	816.9	807.7	801.6	797.0	797.0	797.8	797.0
42.5°	840.7	813.9	795.6	779.7	775.2	769.7	763.6	763.3	764.5	767.1	764.5
45°	766.4	747.2	734.2	726.5	718.1	712.7	711.9	714.2	715.0	715.8	718.1
47.5°	698.0	685.3	673.5	665.0	661.4	660.4	659.5	663.5	667.2	668.6	672.1
50°	657.5	643.0	633.0	627.6	624.6	623.0	624.6	629.2	632.2	636.1	638.4
52.5°	612.2	601.9	595.0	590.9	589.6	590.6	590.9	596.1	601.0	602.4	603.4
55°	549.5	541.8	540.3	533.4	536.4	535.7	539.5	542.6	547.2	551.8	552.5
57.5°	486.9	480.8	476.7	477.3	478.2	481.6	484.8	490.2	495.1	500.0	500.4
60°	445.3	442.2	439.9	439.9	441.4	446.0	449.8	455.2	458.3	461.3	463.6
62.5°	407.2	404.2	401.9	403.1	407.1	409.8	414.3	417.2	420.3	423.3	424.4
65°	347.2	345.6	347.9	349.5	350.2	354.1	359.4	361.7	364.8	366.3	371.7
67.5°	291.8	292.1	291.8	294.0	298.4	299.3	304.4	309.8	310.4	313.3	316.8
70°	254.4	256.0	257.5	259.0	262.9	264.4	268.2	270.5	273.6	275.9	278.2
72.5°	220.1	220.4	221.9	221.6	224.8	228.2	231.4	233.7	236.8	239.7	242.0
75°	169.4	169.4	170.9	171.7	175.5	179.3	178.6	180.1	183.2	186.2	187.8
77.5°	123.7	122.0	123.7	124.5	125.7	128.9	129.5	131.7	135.2	134.1	135.8
80°	94.3	92.0	94.3	95.0	95.0	98.9	98.9	100.4	102.7	100.4	102.7
82.5°	67.3	66.2	67.9	68.1	69.3	69.4	70.7	71.0	73.3	72.2	73.3
85°	33.7	33.0	33.7	33.0	33.7	34.5	34.5	33.7	33.7	35.3	33.0
87.5°	11.8	11.6	11.5	12.1	12.0	12.0	11.3	11.2	11.2	9.9	9.9
90°	6.7	8.8	11.6	14.4	17.2	20.0	19.7	19.5	19.2	18.9	18.9
92.5°	14.6	15.5	16.2	16.8	17.5	18.1	18.2	18.2	18.3	18.3	18.4
95°	34.7	35.5	35.7	36.0	36.2	36.5	36.5	36.5	36.5	36.5	36.4
97.5°	58.6	59.4	59.9	60.4	60.9	61.4	61.4	61.4	61.4	61.4	61.3
100°	76.5	77.2	77.6	77.9	78.3	78.7	78.7	78.7	78.7	78.7	78.6
102.5°	94.8	95.5	96.0	96.4	96.9	97.4	97.5	97.6	97.7	97.8	97.8
105°	124.1	124.4	124.7	124.9	125.2	125.5	125.7	126.0	126.2	126.5	126.6
107.5°	156.1	156.4	156.4	156.4	156.4	156.4	156.5	156.6	156.7	156.8	156.5
110°	177.0	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.2



TEST NUMBER: P331430

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	198.9	199.2	199.1	199.0	198.9	198.8	198.5	198.2	197.9	197.6	197.3
115°	231.1	231.4	231.1	230.9	230.6	230.4	230.3	230.1	230.0	229.9	229.6
117.5°	264.3	264.5	263.8	263.0	262.3	261.6	261.3	261.0	260.7	260.4	260.1
120°	285.8	285.8	284.7	283.7	282.7	281.7	281.7	281.7	281.7	281.7	281.5
122.5°	306.2	306.4	305.7	305.0	304.3	303.6	303.3	303.0	302.7	302.4	302.1
125°	336.4	336.8	336.4	336.1	335.7	335.3	334.9	334.5	334.2	333.8	333.5
127.5°	367.4	367.9	367.5	367.0	366.6	366.1	365.6	365.2	364.7	364.3	363.8
130°	386.9	387.6	387.4	387.1	386.9	386.6	386.4	386.1	385.9	385.6	385.2
132.5°	406.7	407.4	407.5	407.5	407.6	407.6	407.1	406.5	405.9	405.4	404.9
135°	435.0	435.8	436.0	436.3	436.6	436.8	436.7	436.6	436.4	436.3	436.0
137.5°	463.5	464.2	464.6	464.9	465.2	465.5	465.4	465.3	465.2	465.1	464.8
140°	481.3	482.2	482.8	483.4	484.1	484.7	484.7	484.7	484.7	484.7	484.5
142.5°	499.5	500.3	500.8	501.2	501.6	502.0	502.1	502.2	502.3	502.4	502.2
145°	524.8	525.6	526.3	527.1	527.9	528.6	528.7	528.9	529.0	529.1	528.9
147.5°	548.8	549.6	550.1	550.6	551.1	551.7	551.9	552.2	552.5	552.8	552.7
150°	563.6	564.2	564.7	565.2	565.7	566.3	566.6	567.0	567.4	567.8	567.8
152.5°	577.7	578.4	579.0	579.6	580.2	580.9	581.3	581.8	582.3	582.8	582.8
155°	597.4	597.8	598.2	598.6	598.9	599.3	600.0	600.6	601.2	601.9	602.0
157.5°	615.1	615.3	615.5	615.8	616.0	616.2	617.1	617.9	618.8	619.7	619.8
160°	626.0	626.2	626.3	626.4	626.6	626.7	627.5	628.2	629.0	629.7	629.9
162.5°	635.2	635.3	635.4	635.6	635.7	635.8	636.7	637.5	638.4	639.3	639.4
165°	647.9	647.8	647.8	647.8	647.8	647.8	648.7	649.6	650.5	651.3	651.5
167.5°	658.0	657.8	657.8	657.8	657.7	657.7	658.6	659.5	660.4	661.3	661.4
170°	664.0	663.7	663.6	663.4	663.3	663.2	664.1	665.0	665.9	666.7	666.8
172.5°	668.1	667.8	667.7	667.6	667.4	667.3	668.2	669.1	670.0	670.8	670.9
175°	673.1	672.8	672.5	672.3	672.0	671.7	672.6	673.5	674.4	675.3	675.4
177.5°	675.4	675.2	675.0	674.8	674.6	674.4	675.0	675.6	676.2	676.8	676.8
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331430

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1912.5	1911.3	1911.3	1905.8	1911.3	1911.3	1912.5	1918.6	1920.5	1921.7	1919.3
5°	1774.1	1771.8	1768.0	1771.8	1768.0	1771.8	1774.1	1784.8	1790.2	1795.6	1800.2
7.5°	1637.2	1628.0	1626.7	1617.6	1626.7	1628.0	1637.2	1642.3	1653.0	1665.1	1676.2
10°	1537.3	1531.2	1530.4	1515.8	1530.4	1531.2	1537.3	1550.3	1561.1	1575.6	1590.9
12.5°	1461.3	1446.6	1449.5	1441.0	1449.5	1446.6	1461.3	1461.4	1474.0	1483.0	1507.0
15°	1329.6	1329.6	1326.6	1313.5	1326.6	1329.6	1329.6	1350.3	1354.1	1368.7	1389.4
17.5°	1235.1	1233.5	1226.2	1229.8	1226.2	1233.5	1235.1	1250.2	1252.8	1272.3	1289.3
20°	1178.6	1174.1	1164.9	1164.9	1164.9	1174.1	1178.6	1187.1	1197.0	1208.5	1223.1
22.5°	1125.3	1125.0	1115.2	1118.3	1115.2	1125.0	1125.3	1133.1	1142.5	1155.2	1167.3
25°	1062.9	1056.8	1052.2	1054.5	1052.2	1056.8	1062.9	1063.7	1074.4	1082.9	1090.5
27.5°	1003.8	1000.4	1000.1	993.8	1000.1	1000.4	1003.8	1005.8	1011.9	1016.8	1024.0
30°	969.4	961.8	963.3	959.5	963.3	961.8	969.4	970.2	973.3	976.3	984.8
32.5°	930.2	927.4	925.9	922.7	925.9	927.4	930.2	931.6	937.7	940.8	947.4
35°	876.7	877.5	873.6	875.2	873.6	877.5	876.7	878.2	879.0	882.1	888.2
37.5°	830.0	832.4	830.6	831.0	830.6	832.4	830.0	830.7	831.5	832.0	833.8
40°	799.3	799.3	799.3	801.6	799.3	799.3	799.3	797.0	797.8	797.0	797.0
42.5°	769.9	768.7	767.4	767.3	767.4	768.7	769.9	764.5	767.1	764.5	763.3
45°	719.6	721.9	722.7	718.8	722.7	721.9	719.6	718.1	715.8	715.0	714.2
47.5°	674.1	674.4	674.1	677.5	674.1	674.4	674.1	672.1	668.6	667.2	663.5
50°	642.2	640.7	642.2	640.7	642.2	640.7	642.2	638.4	636.1	632.2	629.2
52.5°	608.5	608.8	607.9	607.6	607.9	608.8	608.5	603.4	602.4	601.0	596.1
55°	555.6	557.1	556.4	556.4	556.4	557.1	555.6	552.5	551.8	547.2	542.6
57.5°	500.9	502.3	503.3	500.0	503.3	502.3	500.9	500.4	500.0	495.1	490.2
60°	462.9	466.7	465.9	464.4	465.9	466.7	462.9	463.6	461.3	458.3	455.2
62.5°	427.9	429.3	429.2	428.9	429.2	429.3	427.9	424.4	423.3	420.3	417.2
65°	374.0	375.5	373.2	375.5	373.2	375.5	374.0	371.7	366.3	364.8	361.7
67.5°	315.9	316.4	318.0	319.1	318.0	316.4	315.9	316.8	313.3	310.4	309.8
70°	279.7	279.0	281.3	283.6	281.3	279.0	279.7	278.2	275.9	273.6	270.5
72.5°	241.7	243.4	242.6	244.3	242.6	243.4	241.7	242.0	239.7	236.8	233.7
75°	186.2	188.5	187.8	190.1	187.8	188.5	186.2	187.8	186.2	183.2	180.1
77.5°	134.6	134.9	134.6	135.8	134.6	134.9	134.6	135.8	134.1	135.2	131.7
80°	102.7	101.2	99.6	102.7	99.6	101.2	102.7	102.7	100.4	102.7	100.4
82.5°	71.4	72.3	70.8	70.8	70.8	72.3	71.4	73.3	72.2	73.3	71.0
85°	33.0	32.2	30.7	30.7	30.7	32.2	33.0	33.0	35.3	33.7	33.7
87.5°	9.9	9.3	9.4	8.8	9.4	9.3	9.9	9.9	9.9	11.2	11.2
90°	19.0	19.1	19.3	19.4	19.3	19.1	19.0	18.9	18.9	19.2	19.5
92.5°	18.4	18.4	18.5	18.5	18.5	18.4	18.4	18.4	18.3	18.3	18.2
95°	36.1	35.9	35.6	35.4	35.6	35.9	36.1	36.4	36.5	36.5	36.5
97.5°	61.3	61.3	61.3	61.2	61.3	61.3	61.3	61.3	61.4	61.4	61.4
100°	78.5	78.4	78.3	78.1	78.3	78.4	78.5	78.6	78.7	78.7	78.7
102.5°	97.7	97.5	97.4	97.3	97.4	97.5	97.7	97.8	97.8	97.7	97.6
105°	126.6	126.6	126.6	126.6	126.6	126.6	126.6	126.6	126.5	126.2	126.0
107.5°	155.9	155.4	154.8	154.2	154.8	155.4	155.9	156.5	156.8	156.7	156.6
110°	176.8	176.4	176.0	175.6	176.0	176.4	176.8	177.2	177.3	177.3	177.3



TEST NUMBER: P331430

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	197.0	196.7	196.4	196.2	196.4	196.7	197.0	197.3	197.6	197.9	198.2
115°	229.2	228.9	228.5	228.1	228.5	228.9	229.2	229.6	229.9	230.0	230.1
117.5°	259.7	259.3	258.9	258.5	258.9	259.3	259.7	260.1	260.4	260.7	261.0
120°	281.1	280.8	280.4	280.0	280.4	280.8	281.1	281.5	281.7	281.7	281.7
122.5°	301.8	301.5	301.3	301.0	301.3	301.5	301.8	302.1	302.4	302.7	303.0
125°	333.4	333.3	333.1	333.0	333.1	333.3	333.4	333.5	333.8	334.2	334.5
127.5°	363.4	363.0	362.6	362.2	362.6	363.0	363.4	363.8	364.3	364.7	365.2
130°	384.7	384.2	383.7	383.2	383.7	384.2	384.7	385.2	385.6	385.9	386.1
132.5°	404.5	404.1	403.7	403.3	403.7	404.1	404.5	404.9	405.4	405.9	406.5
135°	435.7	435.3	434.9	434.5	434.9	435.3	435.7	436.0	436.3	436.4	436.6
137.5°	464.3	463.8	463.3	462.8	463.3	463.8	464.3	464.8	465.1	465.2	465.3
140°	483.9	483.4	482.9	482.4	482.9	483.4	483.9	484.5	484.7	484.7	484.7
142.5°	501.7	501.2	500.7	500.2	500.7	501.2	501.7	502.2	502.4	502.3	502.2
145°	528.4	527.9	527.4	526.9	527.4	527.9	528.4	528.9	529.1	529.0	528.9
147.5°	552.2	551.7	551.2	550.7	551.2	551.7	552.2	552.7	552.8	552.5	552.2
150°	567.4	567.0	566.6	566.3	566.6	567.0	567.4	567.8	567.8	567.4	567.0
152.5°	582.3	581.8	581.3	580.9	581.3	581.8	582.3	582.8	582.8	582.3	581.8
155°	601.6	601.2	600.8	600.5	600.8	601.2	601.6	602.0	601.9	601.2	600.6
157.5°	619.2	618.6	618.0	617.3	618.0	618.6	619.2	619.8	619.7	618.8	617.9
160°	629.4	628.9	628.3	627.8	628.3	628.9	629.4	629.9	629.7	629.0	628.2
162.5°	638.8	638.2	637.6	637.0	637.6	638.2	638.8	639.4	639.3	638.4	637.5
165°	650.8	650.2	649.6	648.9	649.6	650.2	650.8	651.5	651.3	650.5	649.6
167.5°	660.7	660.1	659.4	658.7	659.4	660.1	660.7	661.4	661.3	660.4	659.5
170°	666.0	665.3	664.5	663.8	664.5	665.3	666.0	666.8	666.7	665.9	665.0
172.5°	670.2	669.4	668.6	667.9	668.6	669.4	670.2	670.9	670.8	670.0	669.1
175°	674.6	673.8	673.1	672.3	673.1	673.8	674.6	675.4	675.3	674.4	673.5
177.5°	676.2	675.6	675.0	674.4	675.0	675.6	676.2	676.8	676.8	676.2	675.6
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331430

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1916.2	1922.9	1933.4	1944.4	1951.1	1964.0	1967.7	1973.8	1979.3	1992.2	2005.7
5°	1805.5	1816.3	1841.5	1855.3	1874.5	1896.7	1911.3	1926.6	1943.5	1972.6	1999.4
7.5°	1686.9	1704.8	1736.2	1762.0	1789.3	1821.2	1844.1	1874.5	1899.6	1940.7	1979.9
10°	1607.8	1633.1	1661.5	1692.1	1730.4	1764.1	1796.3	1834.6	1865.3	1914.3	1960.3
12.5°	1536.7	1540.5	1581.1	1614.9	1667.3	1709.0	1746.1	1795.4	1825.4	1883.7	1932.1
15°	1412.4	1435.4	1472.2	1499.0	1561.1	1613.9	1666.0	1717.4	1751.9	1823.9	1887.5
17.5°	1307.7	1328.9	1366.6	1410.5	1455.1	1507.7	1575.2	1629.3	1676.2	1758.5	1833.7
20°	1241.5	1267.5	1305.9	1351.1	1390.2	1447.6	1505.9	1568.0	1618.5	1711.3	1799.4
22.5°	1185.1	1205.6	1236.6	1281.2	1323.9	1376.5	1440.3	1507.9	1560.9	1661.0	1750.3
25°	1105.8	1122.7	1142.6	1179.4	1227.7	1285.2	1335.0	1409.3	1486.7	1580.2	1688.3
27.5°	1034.4	1046.4	1064.0	1096.3	1133.7	1187.5	1242.9	1313.4	1391.2	1492.7	1606.7
30°	990.9	998.6	1016.2	1043.0	1079.8	1121.9	1177.9	1245.3	1325.0	1427.7	1541.1
32.5°	952.9	959.9	971.4	997.0	1028.9	1064.9	1115.3	1182.8	1258.8	1359.7	1485.3
35°	895.9	901.2	911.2	931.9	949.5	984.8	1026.9	1088.2	1159.5	1256.1	1386.3
37.5°	839.0	846.4	852.5	861.2	883.9	907.1	943.7	995.5	1065.4	1162.9	1287.0
40°	801.6	807.7	816.9	820.8	839.2	859.8	889.7	937.2	1007.8	1096.6	1217.7
42.5°	763.6	769.7	775.2	779.7	795.6	813.9	840.7	881.5	944.0	1030.4	1150.3
45°	711.9	712.7	718.1	726.5	734.2	747.2	766.4	801.6	849.9	931.1	1039.9
47.5°	659.5	660.4	661.4	665.0	673.5	685.3	698.0	726.7	769.9	834.7	940.6
50°	624.6	623.0	624.6	627.6	633.0	643.0	657.5	678.2	713.5	774.0	871.3
52.5°	590.9	590.6	589.6	590.9	595.0	601.9	612.2	629.8	661.4	717.0	802.7
55°	539.5	535.7	536.4	533.4	540.3	541.8	549.5	564.0	591.6	629.9	710.4
57.5°	484.8	481.6	478.2	477.3	476.7	480.8	486.9	498.4	519.6	553.2	618.4
60°	449.8	446.0	441.4	439.9	439.9	442.2	445.3	453.7	473.6	503.5	557.1
62.5°	414.3	409.8	407.1	403.1	401.9	404.2	407.2	413.2	427.6	455.7	502.0
65°	359.4	354.1	350.2	349.5	347.9	345.6	347.2	353.3	364.8	387.0	423.8
67.5°	304.4	299.3	298.4	294.0	291.8	292.1	291.8	297.0	303.9	323.1	350.5
70°	268.2	264.4	262.9	259.0	257.5	256.0	254.4	259.0	265.9	282.0	305.8
72.5°	231.4	228.2	224.8	221.6	221.9	220.4	220.1	222.9	228.5	243.4	261.6
75°	178.6	179.3	175.5	171.7	170.9	169.4	169.4	171.7	174.0	185.5	200.0
77.5°	129.5	128.9	125.7	124.5	123.7	122.0	123.7	125.2	126.4	134.1	144.8
80°	98.9	98.9	95.0	95.0	94.3	92.0	94.3	92.7	95.8	103.5	111.1
82.5°	70.7	69.4	69.3	68.1	67.9	66.2	67.3	68.8	70.0	75.3	79.9
85°	34.5	34.5	33.7	33.0	33.7	33.0	33.7	34.5	35.3	37.6	41.4
87.5°	11.3	12.0	12.0	12.1	11.5	11.6	11.8	12.1	13.0	13.3	13.6
90°	19.7	20.0	17.2	14.4	11.6	8.8	6.7	5.1	3.6	2.1	0.6
92.5°	18.2	18.1	17.5	16.8	16.2	15.5	14.6	13.5	12.4	11.3	10.2
95°	36.5	36.5	36.2	36.0	35.7	35.5	34.7	33.5	32.2	30.9	29.7
97.5°	61.4	61.4	60.9	60.4	59.9	59.4	58.6	57.5	56.4	55.3	54.2
100°	78.7	78.7	78.3	77.9	77.6	77.2	76.5	75.5	74.4	73.4	72.4
102.5°	97.5	97.4	96.9	96.4	96.0	95.5	94.8	94.0	93.2	92.4	91.6
105°	125.7	125.5	125.2	124.9	124.7	124.4	124.1	123.7	123.4	123.0	122.6
107.5°	156.5	156.4	156.4	156.4	156.4	156.4	156.1	155.5	155.0	154.4	153.9
110°	177.3	177.3	177.3	177.3	177.3	177.3	177.0	176.2	175.4	174.7	173.9



TEST NUMBER: P331430

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	198.5	198.8	198.9	199.0	199.1	199.2	198.9	198.1	197.3	196.6	195.8
115°	230.3	230.4	230.6	230.9	231.1	231.4	231.1	230.4	229.6	228.9	228.1
117.5°	261.3	261.6	262.3	263.0	263.8	264.5	264.3	263.3	262.3	261.3	260.3
120°	281.7	281.7	282.7	283.7	284.7	285.8	285.8	284.7	283.7	282.7	281.7
122.5°	303.3	303.6	304.3	305.0	305.7	306.4	306.2	305.0	303.8	302.5	301.3
125°	334.9	335.3	335.7	336.1	336.4	336.8	336.4	335.3	334.2	333.0	331.9
127.5°	365.6	366.1	366.6	367.0	367.5	367.9	367.4	366.0	364.5	363.1	361.6
130°	386.4	386.6	386.9	387.1	387.4	387.6	386.9	385.3	383.6	382.0	380.4
132.5°	407.1	407.6	407.6	407.5	407.5	407.4	406.7	405.4	404.0	402.7	401.3
135°	436.7	436.8	436.6	436.3	436.0	435.8	435.0	433.6	432.2	430.8	429.4
137.5°	465.4	465.5	465.2	464.9	464.6	464.2	463.5	462.4	461.2	460.1	458.9
140°	484.7	484.7	484.1	483.4	482.8	482.2	481.3	480.1	479.0	477.9	476.7
142.5°	502.1	502.0	501.6	501.2	500.8	500.3	499.5	498.4	497.3	496.1	495.0
145°	528.7	528.6	527.9	527.1	526.3	525.6	524.8	523.9	523.0	522.1	521.2
147.5°	551.9	551.7	551.1	550.6	550.1	549.6	548.8	547.8	546.7	545.6	544.6
150°	566.6	566.3	565.7	565.2	564.7	564.2	563.6	562.8	562.1	561.3	560.6
152.5°	581.3	580.9	580.2	579.6	579.0	578.4	577.7	577.0	576.2	575.5	574.7
155°	600.0	599.3	598.9	598.6	598.2	597.8	597.4	597.0	596.7	596.3	595.9
157.5°	617.1	616.2	616.0	615.8	615.5	615.3	615.1	614.8	614.5	614.3	614.0
160°	627.5	626.7	626.6	626.4	626.3	626.2	626.0	625.7	625.5	625.2	625.0
162.5°	636.7	635.8	635.7	635.6	635.4	635.3	635.2	635.2	635.1	635.1	635.0
165°	648.7	647.8	647.8	647.8	647.8	647.8	647.9	648.0	648.1	648.2	648.4
167.5°	658.6	657.7	657.7	657.8	657.8	657.8	658.0	658.4	658.8	659.2	659.5
170°	664.1	663.2	663.3	663.4	663.6	663.7	664.0	664.3	664.7	665.1	665.5
172.5°	668.2	667.3	667.4	667.6	667.7	667.8	668.1	668.4	668.8	669.2	669.6
175°	672.6	671.7	672.0	672.3	672.5	672.8	673.1	673.5	673.8	674.2	674.6
177.5°	675.0	674.4	674.6	674.8	675.0	675.2	675.4	675.7	676.0	676.3	676.7
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331430

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2004.5	2007.5	2017.3	2027.2	2038.2	2041.3	2046.2	2041.9	2040.6	2052.3	2060.9
5°	2010.1	2023.9	2050.8	2075.3	2096.0	2110.5	2125.9	2132.0	2143.5	2159.6	2179.5
7.5°	2003.7	2030.5	2072.7	2108.4	2147.3	2175.4	2197.3	2216.0	2238.7	2269.2	2302.4
10°	1996.3	2032.4	2083.7	2127.4	2174.9	2210.9	2240.8	2269.9	2303.7	2345.8	2389.5
12.5°	1982.9	2025.6	2089.8	2141.5	2202.5	2237.9	2278.2	2341.1	2377.2	2435.9	2497.4
15°	1955.7	2003.2	2092.9	2156.5	2225.5	2292.9	2367.3	2427.0	2486.8	2521.3	2607.9
17.5°	1915.4	1985.2	2084.5	2158.7	2246.3	2352.5	2436.1	2503.8	2572.8	2628.7	2672.1
20°	1882.9	1958.8	2072.2	2161.1	2265.3	2379.5	2475.3	2544.3	2604.1	2650.8	2677.6
22.5°	1841.8	1937.3	2047.7	2151.9	2285.0	2397.9	2498.6	2552.9	2602.8	2625.7	2635.9
25°	1777.2	1892.1	2017.0	2144.3	2294.5	2414.0	2506.0	2538.9	2553.5	2531.3	2494.5
27.5°	1707.4	1835.6	1981.6	2129.8	2288.6	2403.6	2469.5	2464.3	2439.6	2367.7	2310.2
30°	1655.3	1796.3	1953.4	2115.1	2274.5	2386.4	2424.7	2386.4	2330.5	2250.0	2168.0
32.5°	1600.8	1746.7	1923.4	2094.3	2248.8	2347.2	2355.5	2289.6	2203.0	2111.5	2009.2
35°	1518.1	1676.0	1866.8	2047.7	2194.1	2256.1	2219.4	2102.9	2000.2	1875.3	1735.8
37.5°	1424.8	1599.1	1790.5	1979.5	2112.1	2128.3	2037.0	1914.3	1769.5	1622.7	1458.5
40°	1354.9	1539.6	1736.6	1927.4	2044.6	2027.8	1911.3	1776.4	1604.0	1424.6	1272.1
42.5°	1292.4	1477.1	1677.7	1864.8	1958.8	1912.5	1776.4	1610.9	1425.6	1256.7	1117.0
45°	1184.0	1374.1	1579.5	1760.3	1814.0	1730.4	1550.3	1366.4	1184.0	1043.0	932.7
47.5°	1078.9	1266.8	1470.2	1629.1	1648.1	1535.8	1339.0	1149.7	992.9	878.1	800.2
50°	1001.6	1190.1	1391.7	1533.5	1527.3	1391.7	1189.4	1009.3	878.2	785.5	733.4
52.5°	932.3	1110.4	1304.0	1432.9	1400.4	1252.5	1059.4	899.5	791.8	719.3	672.1
55°	824.6	989.4	1173.3	1276.7	1217.0	1053.0	889.7	761.0	681.3	626.9	590.1
57.5°	717.6	872.1	1029.5	1093.3	1027.2	875.8	739.7	646.3	586.4	546.1	522.2
60°	651.4	786.3	926.5	981.7	902.8	767.9	660.6	577.1	528.8	495.8	474.4
62.5°	585.2	706.0	838.2	868.3	796.1	682.1	587.0	517.6	477.9	448.6	428.4
65°	495.1	593.9	694.3	714.2	647.6	559.4	484.3	439.1	403.9	382.4	366.3
67.5°	406.0	485.4	556.5	572.6	514.2	453.1	398.8	359.4	335.5	317.7	304.1
70°	353.3	416.1	474.4	487.4	440.7	386.2	344.9	313.4	292.0	276.7	263.6
72.5°	297.5	349.9	398.3	407.1	368.9	327.4	293.4	268.7	249.7	239.9	227.5
75°	227.6	258.3	295.8	298.1	272.8	247.5	221.5	205.4	195.4	183.2	177.0
77.5°	160.6	184.7	206.1	210.3	195.3	178.1	163.5	150.8	142.4	136.7	131.0
80°	122.6	141.8	151.0	156.3	145.6	133.3	124.9	116.5	111.1	107.3	103.5
82.5°	87.7	99.5	108.1	112.2	106.4	99.0	90.6	85.8	81.7	78.5	77.1
85°	44.4	49.8	55.2	56.7	55.2	52.1	47.5	47.5	45.2	44.4	44.4
87.5°	15.7	18.5	18.8	20.9	20.2	20.7	21.3	21.2	21.2	20.5	19.8
90°	2.1	3.6	5.1	6.7	8.8	11.6	14.4	17.2	20.0	19.7	19.5
92.5°	11.3	12.4	13.5	14.6	15.5	16.2	16.8	17.5	18.1	18.2	18.2
95°	30.9	32.2	33.5	34.7	35.5	35.7	36.0	36.2	36.5	36.5	36.5
97.5°	55.3	56.4	57.5	58.6	59.4	59.9	60.4	60.9	61.4	61.4	61.4
100°	73.4	74.4	75.5	76.5	77.2	77.6	77.9	78.3	78.7	78.7	78.7
102.5°	92.4	93.2	94.0	94.8	95.5	96.0	96.4	96.9	97.4	97.5	97.6
105°	123.0	123.4	123.7	124.1	124.4	124.7	124.9	125.2	125.5	125.7	126.0
107.5°	154.4	155.0	155.5	156.1	156.4	156.4	156.4	156.4	156.4	156.5	156.6
110°	174.7	175.4	176.2	177.0	177.3	177.3	177.3	177.3	177.3	177.3	177.3



TEST NUMBER: P331430

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	196.6	197.3	198.1	198.9	199.2	199.1	199.0	198.9	198.8	198.5	198.2
115°	228.9	229.6	230.4	231.1	231.4	231.1	230.9	230.6	230.4	230.3	230.1
117.5°	261.3	262.3	263.3	264.3	264.5	263.8	263.0	262.3	261.6	261.3	261.0
120°	282.7	283.7	284.7	285.8	285.8	284.7	283.7	282.7	281.7	281.7	281.7
122.5°	302.5	303.8	305.0	306.2	306.4	305.7	305.0	304.3	303.6	303.3	303.0
125°	333.0	334.2	335.3	336.4	336.8	336.4	336.1	335.7	335.3	334.9	334.5
127.5°	363.1	364.5	366.0	367.4	367.9	367.5	367.0	366.6	366.1	365.6	365.2
130°	382.0	383.6	385.3	386.9	387.6	387.4	387.1	386.9	386.6	386.4	386.1
132.5°	402.7	404.0	405.4	406.7	407.4	407.5	407.5	407.6	407.6	407.1	406.5
135°	430.8	432.2	433.6	435.0	435.8	436.0	436.3	436.6	436.8	436.7	436.6
137.5°	460.1	461.2	462.4	463.5	464.2	464.6	464.9	465.2	465.5	465.4	465.3
140°	477.9	479.0	480.1	481.3	482.2	482.8	483.4	484.1	484.7	484.7	484.7
142.5°	496.1	497.3	498.4	499.5	500.3	500.8	501.2	501.6	502.0	502.1	502.2
145°	522.1	523.0	523.9	524.8	525.6	526.3	527.1	527.9	528.6	528.7	528.9
147.5°	545.6	546.7	547.8	548.8	549.6	550.1	550.6	551.1	551.7	551.9	552.2
150°	561.3	562.1	562.8	563.6	564.2	564.7	565.2	565.7	566.3	566.6	567.0
152.5°	575.5	576.2	577.0	577.7	578.4	579.0	579.6	580.2	580.9	581.3	581.8
155°	596.3	596.7	597.0	597.4	597.8	598.2	598.6	598.9	599.3	600.0	600.6
157.5°	614.3	614.5	614.8	615.1	615.3	615.5	615.8	616.0	616.2	617.1	617.9
160°	625.2	625.5	625.7	626.0	626.2	626.3	626.4	626.6	626.7	627.5	628.2
162.5°	635.1	635.1	635.2	635.2	635.3	635.4	635.6	635.7	635.8	636.7	637.5
165°	648.2	648.1	648.0	647.9	647.8	647.8	647.8	647.8	647.8	648.7	649.6
167.5°	659.2	658.8	658.4	658.0	657.8	657.8	657.8	657.7	657.7	658.6	659.5
170°	665.1	664.7	664.3	664.0	663.7	663.6	663.4	663.3	663.2	664.1	665.0
172.5°	669.2	668.8	668.4	668.1	667.8	667.7	667.6	667.4	667.3	668.2	669.1
175°	674.2	673.8	673.5	673.1	672.8	672.5	672.3	672.0	671.7	672.6	673.5
177.5°	676.3	676.0	675.7	675.4	675.2	675.0	674.8	674.6	674.4	675.0	675.6
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331430

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2068.2	2076.8	2076.8	2078.0	2087.8	2086.6	2086.0
5°	2201.0	2214.0	2215.5	2229.3	2238.5	2235.4	2227.0
7.5°	2326.2	2350.4	2368.8	2379.1	2391.2	2398.7	2395.3
10°	2425.5	2460.8	2482.2	2496.8	2514.4	2527.4	2522.8
12.5°	2515.6	2557.6	2587.1	2612.0	2614.3	2631.0	2619.7
15°	2656.2	2700.6	2705.2	2723.6	2738.2	2736.6	2737.4
17.5°	2702.6	2716.9	2719.8	2720.2	2720.4	2715.0	2703.4
20°	2686.1	2680.7	2667.7	2657.7	2640.1	2637.8	2622.5
22.5°	2607.6	2590.6	2557.9	2536.3	2508.9	2501.7	2497.4
25°	2453.1	2415.5	2363.4	2313.6	2299.8	2273.0	2280.7
27.5°	2241.1	2182.6	2126.2	2085.7	2049.1	2008.9	2020.4
30°	2092.1	2026.2	1946.5	1885.2	1846.1	1807.8	1800.9
32.5°	1914.3	1817.8	1728.9	1674.9	1615.0	1590.8	1564.3
35°	1607.8	1513.5	1425.4	1349.5	1305.9	1272.1	1241.5
37.5°	1332.1	1223.6	1152.4	1091.0	1059.4	1040.1	1045.0
40°	1161.0	1066.0	1013.9	967.1	938.0	924.2	927.3
42.5°	1022.5	951.3	908.4	876.4	855.9	848.2	846.4
45°	865.2	825.4	790.1	771.7	761.8	753.3	748.0
47.5°	757.9	725.4	705.5	694.6	685.9	677.3	677.1
50°	693.5	672.1	658.3	646.8	639.9	633.8	639.1
52.5°	644.5	624.9	611.1	600.8	598.2	592.7	592.5
55°	571.7	556.4	546.4	537.2	532.6	529.5	525.7
57.5°	505.5	490.9	481.7	475.9	467.2	464.1	462.9
60°	458.3	446.8	437.6	429.9	426.1	420.0	420.0
62.5°	414.7	403.3	394.7	388.8	382.6	380.1	380.7
65°	351.8	342.6	334.1	328.0	326.5	321.9	323.4
67.5°	293.8	287.7	278.8	275.4	272.5	270.1	268.2
70°	255.2	249.1	244.5	239.9	237.6	237.6	237.6
72.5°	222.7	215.3	212.6	206.8	208.1	205.7	203.2
75°	172.4	167.8	165.5	163.2	159.4	159.4	159.4
77.5°	126.9	125.5	122.8	120.3	119.4	118.6	118.9
80°	98.1	97.3	95.8	95.8	94.3	93.5	92.0
82.5°	75.4	73.4	72.5	71.9	71.6	71.4	71.1
85°	42.9	41.4	41.4	42.1	40.6	40.6	41.4
87.5°	20.4	20.3	19.7	19.7	20.4	19.8	19.8
90°	19.2	18.9	18.9	19.0	19.1	19.3	19.4
92.5°	18.3	18.3	18.4	18.4	18.4	18.5	18.5
95°	36.5	36.5	36.4	36.1	35.9	35.6	35.4
97.5°	61.4	61.4	61.3	61.3	61.3	61.3	61.2
100°	78.7	78.7	78.6	78.5	78.4	78.3	78.1
102.5°	97.7	97.8	97.8	97.7	97.5	97.4	97.3
105°	126.2	126.5	126.6	126.6	126.6	126.6	126.6
107.5°	156.7	156.8	156.5	155.9	155.4	154.8	154.2
110°	177.3	177.3	177.2	176.8	176.4	176.0	175.6



TEST NUMBER: P331430

CATALOG NUMBER: S122DIP-S1005D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	197.9	197.6	197.3	197.0	196.7	196.4	196.2
115°	230.0	229.9	229.6	229.2	228.9	228.5	228.1
117.5°	260.7	260.4	260.1	259.7	259.3	258.9	258.5
120°	281.7	281.7	281.5	281.1	280.8	280.4	280.0
122.5°	302.7	302.4	302.1	301.8	301.5	301.3	301.0
125°	334.2	333.8	333.5	333.4	333.3	333.1	333.0
127.5°	364.7	364.3	363.8	363.4	363.0	362.6	362.2
130°	385.9	385.6	385.2	384.7	384.2	383.7	383.2
132.5°	405.9	405.4	404.9	404.5	404.1	403.7	403.3
135°	436.4	436.3	436.0	435.7	435.3	434.9	434.5
137.5°	465.2	465.1	464.8	464.3	463.8	463.3	462.8
140°	484.7	484.7	484.5	483.9	483.4	482.9	482.4
142.5°	502.3	502.4	502.2	501.7	501.2	500.7	500.2
145°	529.0	529.1	528.9	528.4	527.9	527.4	526.9
147.5°	552.5	552.8	552.7	552.2	551.7	551.2	550.7
150°	567.4	567.8	567.8	567.4	567.0	566.6	566.3
152.5°	582.3	582.8	582.8	582.3	581.8	581.3	580.9
155°	601.2	601.9	602.0	601.6	601.2	600.8	600.5
157.5°	618.8	619.7	619.8	619.2	618.6	618.0	617.3
160°	629.0	629.7	629.9	629.4	628.9	628.3	627.8
162.5°	638.4	639.3	639.4	638.8	638.2	637.6	637.0
165°	650.5	651.3	651.5	650.8	650.2	649.6	648.9
167.5°	660.4	661.3	661.4	660.7	660.1	659.4	658.7
170°	665.9	666.7	666.8	666.0	665.3	664.5	663.8
172.5°	670.0	670.8	670.9	670.2	669.4	668.6	667.9
175°	674.4	675.3	675.4	674.6	673.8	673.1	672.3
177.5°	676.2	676.8	676.8	676.2	675.6	675.0	674.4
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7

(END OF REPORT)