

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331901-927

Luminaire Tested: **S123DIP-S340D1195U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331901-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D1195U927-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1195 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4930.9 lumens  
Efficiency: N/A  
Efficacy: 116.8 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331901-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331901-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	23
1	92	88	84	81	82	78	75	72	60	58	56	43	42	41	28	27	27	20
2	84	77	71	66	74	68	64	59	53	49	47	38	36	34	25	24	23	17
3	76	67	61	55	68	60	54	50	47	43	39	34	31	29	22	21	20	14
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	12
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11	8
8	50	39	31	26	45	35	28	24	27	22	19	20	17	15	13	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	11	10	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4100	4100	4100	4100
5°	4889	4118	3649	4118
10°	6120	4098	3296	4098
15°	7506	4063	3069	4063
20°	8942	4013	2922	4013
25°	9495	3950	2888	3950
30°	8139	3904	2903	3904
35°	5660	3840	2934	3840
40°	4263	3763	2925	3763
45°	3539	3649	2888	3649
50°	3170	3418	2862	3418
55°	2965	3170	2826	3170
60°	2781	2908	2796	2908
65°	2613	2651	2707	2651
70°	2452	2357	2578	2357
75°	2196	2067	2366	2067
80°	1922	1692	2039	1692
85°	1507	1235	1371	1235



TEST NUMBER: P331901-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.5	0.8
10°-20°	120.3	2.4
20°-30°	201.9	4.1
30°-40°	228.6	4.6
40°-50°	205.0	4.2
50°-60°	165.5	3.4
60°-70°	115.3	2.3
70°-80°	60.6	1.2
80°-90°	18.3	0.4
90°-100°	45.0	0.9
100°-110°	214.7	4.4
110°-120°	515.6	10.5
120°-130°	656.6	13.3
130°-140°	701.5	14.2
140°-150°	656.0	13.3
150°-160°	529.2	10.7
160°-170°	341.5	6.9
170°-180°	117.7	2.4
0°-30°	359.8	7.3
0°-40°	588.4	11.9
0°-60°	958.9	19.4
0°-90°	1153.1	23.4
90°-120°	775.3	15.7
90°-150°	2789.4	56.6
90°-180°	3778.0	76.6
0°-180°	4930.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	381	381	381	381	381	
5°	452	381	338	381	452	47
15°	674	365	275	365	674	194
25°	800	333	243	333	800	351
35°	431	292	223	292	431	280
45°	232	240	190	240	232	184
55°	158	169	151	169	158	142
65°	103	104	106	104	103	102
75°	53	50	57	50	53	56
85°	12	10	11	10	12	15
90°	28	1	28	1	28	13
95°	35	56	35	56	35	29
105°	40	274	40	274	40	93
115°	541	514	541	514	541	500
125°	740	725	740	725	740	661
135°	912	903	912	903	912	703
145°	1052	1042	1052	1042	1052	657
155°	1146	1148	1146	1148	1146	528
165°	1208	1210	1208	1210	1208	341
175°	1234	1239	1234	1239	1234	117
180°	1239	1239	1239	1239	1239	



TEST NUMBER: P331901-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	404.3	403.9	403.2	403.8	402.6	401.0	400.8	399.3	395.1	394.8	393.6
5°	452.5	451.1	450.8	450.7	448.1	444.6	437.9	437.4	428.5	424.1	418.7
7.5°	515.1	515.8	513.1	510.8	502.9	497.6	490.5	481.4	470.6	459.5	452.2
10°	559.9	566.0	558.5	553.3	548.5	539.5	528.9	515.8	502.7	487.4	475.8
12.5°	608.1	611.0	609.5	604.7	597.2	583.4	564.8	550.3	538.3	512.8	502.5
15°	673.6	684.8	677.6	661.1	661.4	648.3	624.0	597.2	583.0	560.6	530.2
17.5°	743.5	744.8	741.8	727.9	718.7	700.7	678.2	652.6	623.8	596.8	564.4
20°	780.6	779.5	773.1	765.9	750.0	736.0	711.5	682.9	645.9	619.3	584.1
22.5°	801.3	799.5	796.4	790.4	777.2	762.2	740.1	708.8	673.7	637.1	596.4
25°	799.5	801.8	802.2	800.6	796.0	787.0	769.6	744.7	709.6	662.5	620.1
27.5°	727.1	730.6	740.4	749.2	758.9	768.9	767.5	755.2	729.2	688.6	636.7
30°	654.8	647.4	665.7	688.7	704.4	732.1	747.6	748.5	734.0	699.1	648.5
32.5°	554.4	562.5	570.6	599.0	633.3	664.3	695.2	720.0	722.9	699.7	655.5
35°	430.7	440.9	455.7	470.4	507.3	539.1	593.3	640.6	678.2	683.2	656.1
37.5°	347.1	352.1	361.5	376.3	400.4	438.1	480.0	539.7	594.3	634.9	636.6
40°	303.4	304.9	315.4	326.6	346.2	377.2	415.0	467.9	533.1	589.9	613.5
42.5°	270.6	273.9	278.4	289.1	304.8	328.0	363.2	406.9	466.8	532.0	578.1
45°	232.5	236.2	239.0	246.2	257.3	273.0	297.5	337.4	382.9	450.3	512.5
47.5°	207.4	207.6	209.7	215.2	222.7	234.5	251.8	277.4	319.2	373.9	437.8
50°	189.3	192.3	193.1	197.3	203.2	211.8	226.2	248.0	282.3	330.3	389.0
52.5°	176.7	177.5	179.6	182.7	187.8	194.6	207.1	224.1	251.0	292.0	345.9
55°	158.0	158.0	160.0	162.4	165.3	171.4	179.7	192.3	212.8	244.5	289.2
57.5°	140.7	141.6	143.1	143.8	146.3	150.4	157.2	166.8	182.0	206.5	242.0
60°	129.2	130.9	130.6	132.1	134.4	137.5	143.4	151.1	164.8	184.3	214.3
62.5°	119.1	119.1	119.0	120.8	122.9	126.0	129.8	136.5	148.1	165.5	190.9
65°	102.6	102.3	103.5	104.6	105.4	107.6	110.5	116.5	124.2	137.1	156.9
67.5°	87.9	86.8	87.5	87.9	89.2	90.9	93.7	97.4	103.5	113.8	128.7
70°	77.9	76.9	76.8	77.2	78.3	79.5	81.6	85.1	90.8	99.1	110.0
72.5°	67.6	66.9	66.9	67.7	68.2	69.1	70.5	73.7	78.3	84.5	94.7
75°	52.8	52.8	52.8	53.0	53.6	54.3	55.4	57.0	60.5	65.0	71.8
77.5°	39.5	39.5	39.3	39.3	40.1	40.4	40.6	42.2	44.2	47.1	52.1
80°	31.0	30.1	30.4	31.0	31.4	31.5	32.1	32.5	34.1	35.8	39.3
82.5°	23.1	22.3	22.3	23.2	23.3	23.4	24.0	24.5	25.1	26.6	28.5
85°	12.2	12.2	12.4	12.4	12.5	12.4	12.9	13.1	13.1	14.0	15.1
87.5°	10.0	9.6	9.7	9.7	9.5	9.5	9.5	9.5	9.4	9.4	9.0
90°	27.6	27.2	26.8	26.4	26.0	25.3	24.6	23.7	22.9	22.1	19.4
92.5°	30.6	30.3	30.1	29.8	29.5	28.8	27.5	26.1	24.9	23.5	21.5
95°	34.9	34.9	34.9	34.9	34.9	34.2	32.8	31.4	29.9	28.5	26.3
97.5°	37.9	37.7	37.5	37.3	37.1	36.2	34.5	32.9	31.3	29.6	44.4
100°	38.7	38.4	38.3	38.0	37.9	36.9	35.3	33.7	32.0	30.3	62.3
102.5°	39.4	39.1	38.7	38.3	37.9	40.2	45.3	50.4	55.5	60.5	95.4
105°	40.5	40.1	39.7	39.3	38.9	56.7	92.9	129.1	165.3	201.5	220.0
107.5°	127.2	154.5	181.7	209.1	236.3	263.2	289.8	316.3	342.9	369.5	366.5
110°	253.1	282.3	311.6	340.9	370.1	388.1	394.8	401.6	408.4	415.1	412.8



TEST NUMBER: P331901-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	434.2	440.4	446.6	452.7	458.9	462.0	461.8	461.7	461.6	461.4	459.2
115°	541.1	540.3	539.6	538.7	537.9	536.5	534.4	532.3	530.4	528.3	526.5
117.5°	601.2	601.0	600.9	600.7	600.6	599.6	598.0	596.4	594.7	593.1	592.2
120°	642.4	642.4	642.4	642.4	642.4	641.6	639.9	638.3	636.7	635.0	634.5
122.5°	682.9	682.8	682.5	682.4	682.2	681.6	680.5	679.3	678.2	677.0	676.2
125°	740.0	739.6	739.2	738.7	738.3	737.9	737.5	737.1	736.7	736.3	735.5
127.5°	794.8	795.3	795.7	796.1	796.5	796.3	795.7	795.0	794.4	793.7	792.7
130°	830.2	830.6	831.0	831.4	831.8	831.6	830.8	830.0	829.2	828.3	827.5
132.5°	862.5	863.2	863.7	864.3	864.8	864.7	864.0	863.1	862.3	861.5	860.8
135°	912.1	912.7	913.3	913.9	914.6	914.6	913.9	913.3	912.7	912.1	911.2
137.5°	958.6	959.1	959.5	959.9	960.3	960.0	959.0	958.1	957.0	956.1	955.6
140°	986.7	987.1	987.5	987.9	988.2	988.1	987.2	986.4	985.6	984.8	984.2
142.5°	1012.4	1013.0	1013.5	1014.2	1014.7	1014.6	1014.0	1013.4	1012.7	1012.0	1011.5
145°	1051.9	1051.9	1051.9	1051.9	1051.9	1051.8	1051.4	1051.0	1050.5	1050.1	1049.7
147.5°	1081.4	1082.4	1083.3	1084.3	1085.2	1085.4	1085.1	1084.7	1084.3	1083.8	1083.4
150°	1103.5	1104.1	1104.8	1105.3	1106.0	1106.0	1105.6	1105.3	1104.9	1104.5	1104.1
152.5°	1121.2	1122.1	1123.1	1124.0	1125.0	1125.1	1124.3	1123.6	1122.8	1122.1	1121.9
155°	1145.9	1147.1	1148.3	1149.5	1150.7	1150.9	1149.9	1148.8	1147.8	1146.8	1146.6
157.5°	1166.6	1168.2	1169.8	1171.5	1173.1	1173.2	1172.0	1170.8	1169.6	1168.3	1168.5
160°	1179.9	1181.3	1182.8	1184.2	1185.7	1185.7	1184.5	1183.3	1182.1	1180.8	1181.1
162.5°	1192.4	1193.7	1194.9	1196.2	1197.5	1197.5	1196.0	1194.7	1193.3	1191.8	1192.1
165°	1207.5	1208.9	1210.4	1211.8	1213.2	1213.1	1211.5	1209.9	1208.2	1206.6	1206.8
167.5°	1218.4	1220.0	1221.6	1223.3	1225.0	1225.0	1223.3	1221.6	1220.0	1218.4	1218.4
170°	1225.0	1226.6	1228.3	1229.9	1231.5	1231.5	1229.9	1228.3	1226.6	1225.0	1225.0
172.5°	1228.7	1230.5	1232.3	1234.1	1235.9	1236.0	1234.3	1232.7	1231.1	1229.4	1229.2
175°	1234.2	1235.9	1237.5	1239.1	1240.7	1240.9	1239.4	1238.0	1236.6	1235.1	1234.9
177.5°	1235.9	1237.5	1239.1	1240.8	1242.4	1242.5	1241.3	1239.9	1238.7	1237.3	1237.2
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P331901-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	392.7	391.6	390.4	388.3	386.5	384.0	383.3	382.4	379.7	377.4	375.6
5°	416.7	412.3	405.8	399.9	395.1	388.6	385.0	381.1	375.6	370.6	366.5
7.5°	441.8	433.1	423.0	412.3	402.1	392.4	384.5	377.5	369.7	362.4	356.6
10°	461.8	449.2	435.1	420.0	407.1	394.6	384.0	374.9	364.9	356.2	349.0
12.5°	484.5	465.9	446.6	428.2	412.9	395.5	382.7	371.0	359.7	349.3	341.2
15°	511.4	487.7	464.9	439.6	416.4	394.6	379.5	364.6	351.6	340.9	330.5
17.5°	535.9	509.1	479.0	448.2	420.2	394.3	373.2	356.5	340.1	327.0	316.7
20°	549.8	519.4	485.2	453.3	422.2	393.5	370.2	350.3	332.6	318.7	307.1
22.5°	561.7	526.1	490.8	456.6	422.1	391.1	364.7	344.2	325.0	311.5	299.1
25°	574.2	531.5	496.1	456.1	417.5	385.3	355.8	332.6	313.4	297.5	284.8
27.5°	584.8	531.2	489.1	446.0	410.1	378.0	346.4	321.5	301.1	283.8	270.9
30°	591.8	531.9	481.9	439.3	403.1	369.9	339.2	314.1	292.7	275.2	263.0
32.5°	596.3	531.4	475.2	429.8	391.8	362.4	331.4	305.4	283.4	266.2	254.4
35°	598.9	528.1	463.7	410.3	373.8	345.1	319.1	292.2	269.1	253.0	239.7
37.5°	593.7	521.3	450.5	391.4	351.4	323.3	301.3	278.5	256.4	238.7	227.2
40°	585.6	516.9	440.1	378.1	336.0	309.0	290.3	267.8	246.0	229.2	218.5
42.5°	570.1	507.9	428.8	363.4	320.1	293.0	275.8	257.0	236.4	220.6	209.9
45°	532.3	488.3	411.7	341.3	296.6	268.5	253.4	239.7	221.1	205.8	196.5
47.5°	479.7	458.8	387.1	317.9	272.0	245.0	229.3	218.3	204.7	192.3	183.5
50°	443.3	434.6	370.4	301.9	255.6	229.2	214.0	204.1	194.3	182.0	173.9
52.5°	401.2	406.5	350.9	285.4	238.9	212.9	198.8	190.8	182.0	171.7	164.7
55°	342.0	361.3	317.3	257.6	214.0	189.3	175.9	168.9	163.7	156.1	150.0
57.5°	286.5	311.2	280.8	229.0	189.6	168.3	155.4	147.8	144.5	140.5	135.7
60°	253.6	277.9	254.8	209.8	173.3	153.0	141.6	135.1	131.7	129.0	124.9
62.5°	224.2	248.8	229.5	190.4	157.2	138.4	128.4	122.1	119.5	118.1	114.6
65°	183.8	205.0	192.1	160.0	134.2	117.6	108.5	104.1	101.7	101.2	98.9
67.5°	149.6	165.7	156.4	132.7	112.4	98.1	90.4	86.6	84.8	84.5	82.9
70°	127.1	142.3	135.1	113.7	96.2	84.9	78.3	74.9	73.8	73.7	72.7
72.5°	109.7	120.3	114.5	96.7	83.2	73.0	68.0	64.6	63.4	63.6	63.0
75°	81.2	89.1	85.8	73.4	62.6	55.9	51.9	49.7	48.6	49.1	48.3
77.5°	58.5	63.5	60.4	51.9	45.2	40.4	37.4	36.0	35.0	35.0	34.7
80°	44.1	47.1	45.4	40.2	34.7	30.7	28.2	27.3	26.8	26.5	26.4
82.5°	31.4	33.9	31.9	28.4	24.6	22.2	20.8	19.6	19.3	19.3	19.2
85°	15.8	16.8	16.1	13.9	12.4	11.2	10.5	10.0	9.6	9.7	9.4
87.5°	8.8	8.4	7.4	6.4	5.7	4.8	4.4	3.7	3.8	4.3	4.5
90°	16.8	14.1	11.5	9.1	7.1	5.0	2.9	1.0	2.9	5.0	7.1
92.5°	19.6	17.6	15.5	14.8	15.4	16.0	16.6	17.1	16.6	16.0	15.4
95°	24.0	21.8	19.6	22.6	31.0	39.4	47.8	56.2	47.8	39.4	31.0
97.5°	59.1	73.8	88.6	97.8	101.6	105.3	109.1	112.8	109.1	105.3	101.6
100°	94.2	126.1	158.0	171.9	167.8	163.7	159.6	155.5	159.6	163.7	167.8
102.5°	130.2	165.1	199.9	215.9	212.9	210.0	207.1	204.1	207.1	210.0	212.9
105°	238.4	256.7	275.2	283.3	281.0	278.8	276.6	274.3	276.6	278.8	281.0
107.5°	363.6	360.8	357.8	355.5	353.6	351.9	350.1	348.2	350.1	351.9	353.6
110°	410.6	408.4	406.1	404.2	402.5	400.8	399.3	397.6	399.3	400.8	402.5





TEST NUMBER: P331901-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	457.0	454.7	452.5	450.6	449.2	447.7	446.2	444.7	446.2	447.7	449.2
115°	524.6	522.8	520.9	519.4	518.2	516.9	515.7	514.5	515.7	516.9	518.2
117.5°	591.2	590.3	589.3	588.1	586.6	585.0	583.5	582.0	583.5	585.0	586.6
120°	633.8	633.2	632.6	631.4	629.5	627.7	625.8	624.0	625.8	627.7	629.5
122.5°	675.5	674.7	673.9	672.8	671.2	669.7	668.2	666.7	668.2	669.7	671.2
125°	734.7	733.8	733.0	731.8	730.2	728.5	726.9	725.2	726.9	728.5	730.2
127.5°	791.8	790.8	789.8	788.5	786.9	785.2	783.5	782.0	783.5	785.2	786.9
130°	826.7	825.9	825.1	823.8	822.2	820.5	819.0	817.3	819.0	820.5	822.2
132.5°	860.2	859.5	858.8	857.7	856.0	854.4	852.8	851.1	852.8	854.4	856.0
135°	910.5	909.7	908.8	907.8	906.6	905.3	904.1	902.9	904.1	905.3	906.6
137.5°	955.2	954.7	954.3	953.3	951.7	950.1	948.6	947.1	948.6	950.1	951.7
140°	983.6	982.9	982.3	981.4	980.2	979.0	977.7	976.5	977.7	979.0	980.2
142.5°	1010.8	1010.2	1009.6	1008.7	1007.4	1006.2	1005.0	1003.8	1005.0	1006.2	1007.4
145°	1049.3	1048.9	1048.5	1047.6	1046.2	1044.7	1043.3	1041.9	1043.3	1044.7	1046.2
147.5°	1083.0	1082.6	1082.2	1081.5	1080.5	1079.7	1078.7	1077.8	1078.7	1079.7	1080.5
150°	1103.6	1103.2	1102.8	1102.3	1101.7	1101.1	1100.4	1099.9	1100.4	1101.1	1101.7
152.5°	1121.7	1121.3	1121.1	1120.9	1120.5	1120.3	1120.0	1119.7	1120.0	1120.3	1120.5
155°	1146.4	1146.1	1146.0	1146.1	1146.4	1146.8	1147.3	1147.7	1147.3	1146.8	1146.4
157.5°	1168.7	1168.9	1169.1	1169.3	1169.3	1169.3	1169.3	1169.4	1169.3	1169.3	1169.3
160°	1181.2	1181.5	1181.6	1181.9	1182.1	1182.3	1182.5	1182.6	1182.5	1182.3	1182.1
162.5°	1192.3	1192.5	1192.7	1193.0	1193.6	1194.1	1194.7	1195.2	1194.7	1194.1	1193.6
165°	1207.0	1207.2	1207.4	1207.8	1208.5	1209.0	1209.7	1210.3	1209.7	1209.0	1208.5
167.5°	1218.4	1218.4	1218.4	1218.8	1219.6	1220.4	1221.2	1222.1	1221.2	1220.4	1219.6
170°	1225.0	1225.0	1225.0	1225.4	1226.2	1227.1	1227.9	1228.7	1227.9	1227.1	1226.2
172.5°	1229.1	1228.9	1228.8	1229.2	1230.2	1231.1	1232.2	1233.1	1232.2	1231.1	1230.2
175°	1234.7	1234.5	1234.3	1234.7	1235.7	1236.8	1237.8	1238.8	1237.8	1236.8	1235.7
177.5°	1237.0	1236.8	1236.7	1237.0	1237.9	1238.7	1239.4	1240.3	1239.4	1238.7	1237.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P331901-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	374.5	373.5	372.1	369.9	368.0	365.3	365.3	365.7	365.7	365.6	365.3
5°	363.2	360.4	357.1	353.2	349.2	345.1	344.4	342.9	341.8	341.0	340.2
7.5°	351.2	346.3	341.4	336.0	331.1	327.0	324.2	321.8	320.3	318.6	317.4
10°	343.1	337.0	331.3	325.6	319.2	314.3	311.2	309.0	307.3	305.8	305.1
12.5°	333.5	326.5	320.2	314.7	307.9	302.8	299.8	298.7	296.8	293.7	292.1
15°	319.5	313.0	305.5	297.1	293.8	287.6	284.0	282.3	281.2	278.8	278.1
17.5°	307.4	299.0	290.5	284.3	278.1	273.1	271.1	269.0	267.6	265.6	265.0
20°	297.9	290.3	282.6	275.9	269.4	263.9	262.2	260.8	259.3	258.4	257.6
22.5°	288.1	280.6	274.1	267.9	261.0	257.4	255.6	254.0	252.9	252.3	251.6
25°	274.4	267.8	260.5	255.1	249.5	247.1	246.0	245.1	244.3	243.4	243.2
27.5°	262.2	254.9	249.1	243.9	240.0	238.0	236.9	236.5	236.6	236.9	237.2
30°	253.0	246.4	241.6	237.2	233.5	231.6	231.4	231.4	232.2	232.3	232.7
32.5°	244.6	239.2	234.3	230.0	227.3	226.0	226.7	226.7	227.3	227.8	228.5
35°	232.3	227.5	223.9	220.1	217.8	218.3	218.7	219.0	220.0	221.1	221.8
37.5°	220.6	216.5	212.6	209.8	208.7	209.6	210.6	211.3	212.4	213.3	214.0
40°	212.2	209.1	205.4	202.8	203.2	203.7	204.5	205.4	206.4	206.9	207.6
42.5°	204.4	201.1	198.3	196.1	196.7	197.4	197.8	198.3	199.4	200.4	200.8
45°	192.5	189.9	187.4	186.0	186.4	186.8	187.1	187.7	188.6	189.3	189.6
47.5°	179.1	177.3	175.5	174.3	174.9	174.8	175.2	176.4	176.7	177.1	178.2
50°	170.6	168.9	166.8	166.4	166.4	166.4	166.7	168.1	168.1	168.9	169.6
52.5°	161.1	160.0	158.8	158.0	157.7	157.7	158.5	159.2	159.5	160.6	161.4
55°	147.1	146.0	144.9	144.3	143.9	144.3	145.8	146.2	147.1	147.7	148.2
57.5°	132.5	131.7	130.8	130.5	130.4	130.9	131.7	132.8	133.0	134.8	135.5
60°	122.9	121.6	120.9	120.9	120.5	122.2	121.8	123.7	124.1	125.2	126.4
62.5°	113.0	111.3	111.0	111.0	111.5	112.0	112.5	113.3	114.3	115.7	116.7
65°	97.0	96.2	97.4	97.3	96.9	98.0	98.0	98.9	100.1	101.3	103.4
67.5°	82.0	81.5	81.6	81.6	82.1	82.8	83.3	84.1	85.5	86.8	88.2
70°	71.8	72.3	71.5	72.2	72.7	72.9	73.3	74.4	75.8	76.8	78.3
72.5°	61.9	61.9	61.9	62.3	62.8	63.1	63.5	64.8	66.4	67.2	68.4
75°	47.6	47.5	48.0	48.0	48.9	49.3	49.7	50.2	51.7	52.8	53.7
77.5°	34.8	35.0	34.9	35.5	35.3	35.3	36.4	37.0	37.2	39.4	39.8
80°	26.2	26.5	26.8	26.9	27.1	26.8	28.0	28.6	28.6	29.9	30.8
82.5°	18.9	19.0	19.5	19.7	19.7	20.1	20.2	20.6	21.1	21.6	22.8
85°	9.4	10.0	10.1	10.0	10.1	9.7	10.3	10.5	10.7	10.7	10.7
87.5°	4.8	5.4	5.8	6.4	6.8	7.5	7.7	7.5	7.7	8.3	7.8
90°	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.7	24.6	25.3	26.0
92.5°	14.8	15.5	17.6	19.6	21.5	23.5	24.9	26.1	27.5	28.8	29.5
95°	22.6	19.6	21.8	24.0	26.3	28.5	29.9	31.4	32.8	34.2	34.9
97.5°	97.8	88.6	73.8	59.1	44.4	29.6	31.3	32.9	34.5	36.2	37.1
100°	171.9	158.0	126.1	94.2	62.3	30.3	32.0	33.7	35.3	36.9	37.9
102.5°	215.9	199.9	165.1	130.2	95.4	60.5	55.5	50.4	45.3	40.2	37.9
105°	283.3	275.2	256.7	238.4	220.0	201.5	165.3	129.1	92.9	56.7	38.9
107.5°	355.5	357.8	360.8	363.6	366.5	369.5	342.9	316.3	289.8	263.2	236.3
110°	404.2	406.1	408.4	410.6	412.8	415.1	408.4	401.6	394.8	388.1	370.1



TEST NUMBER: P331901-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	450.6	452.5	454.7	457.0	459.2	461.4	461.6	461.7	461.8	462.0	458.9
115°	519.4	520.9	522.8	524.6	526.5	528.3	530.4	532.3	534.4	536.5	537.9
117.5°	588.1	589.3	590.3	591.2	592.2	593.1	594.7	596.4	598.0	599.6	600.6
120°	631.4	632.6	633.2	633.8	634.5	635.0	636.7	638.3	639.9	641.6	642.4
122.5°	672.8	673.9	674.7	675.5	676.2	677.0	678.2	679.3	680.5	681.6	682.2
125°	731.8	733.0	733.8	734.7	735.5	736.3	736.7	737.1	737.5	737.9	738.3
127.5°	788.5	789.8	790.8	791.8	792.7	793.7	794.4	795.0	795.7	796.3	796.5
130°	823.8	825.1	825.9	826.7	827.5	828.3	829.2	830.0	830.8	831.6	831.8
132.5°	857.7	858.8	859.5	860.2	860.8	861.5	862.3	863.1	864.0	864.7	864.8
135°	907.8	908.8	909.7	910.5	911.2	912.1	912.7	913.3	913.9	914.6	914.6
137.5°	953.3	954.3	954.7	955.2	955.6	956.1	957.0	958.1	959.0	960.0	960.3
140°	981.4	982.3	982.9	983.6	984.2	984.8	985.6	986.4	987.2	988.1	988.2
142.5°	1008.7	1009.6	1010.2	1010.8	1011.5	1012.0	1012.7	1013.4	1014.0	1014.6	1014.7
145°	1047.6	1048.5	1048.9	1049.3	1049.7	1050.1	1050.5	1051.0	1051.4	1051.8	1051.9
147.5°	1081.5	1082.2	1082.6	1083.0	1083.4	1083.8	1084.3	1084.7	1085.1	1085.4	1085.2
150°	1102.3	1102.8	1103.2	1103.6	1104.1	1104.5	1104.9	1105.3	1105.6	1106.0	1106.0
152.5°	1120.9	1121.1	1121.3	1121.7	1121.9	1122.1	1122.8	1123.6	1124.3	1125.1	1125.0
155°	1146.1	1146.0	1146.1	1146.4	1146.6	1146.8	1147.8	1148.8	1149.9	1150.9	1150.7
157.5°	1169.3	1169.1	1168.9	1168.7	1168.5	1168.3	1169.6	1170.8	1172.0	1173.2	1173.1
160°	1181.9	1181.6	1181.5	1181.2	1181.1	1180.8	1182.1	1183.3	1184.5	1185.7	1185.7
162.5°	1193.0	1192.7	1192.5	1192.3	1192.1	1191.8	1193.3	1194.7	1196.0	1197.5	1197.5
165°	1207.8	1207.4	1207.2	1207.0	1206.8	1206.6	1208.2	1209.9	1211.5	1213.1	1213.2
167.5°	1218.8	1218.4	1218.4	1218.4	1218.4	1218.4	1220.0	1221.6	1223.3	1225.0	1225.0
170°	1225.4	1225.0	1225.0	1225.0	1225.0	1225.0	1226.6	1228.3	1229.9	1231.5	1231.5
172.5°	1229.2	1228.8	1228.9	1229.1	1229.2	1229.4	1231.1	1232.7	1234.3	1236.0	1235.9
175°	1234.7	1234.3	1234.5	1234.7	1234.9	1235.1	1236.6	1238.0	1239.4	1240.9	1240.7
177.5°	1237.0	1236.7	1236.8	1237.0	1237.2	1237.3	1238.7	1239.9	1241.3	1242.5	1242.4
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P331901-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	364.2	364.1	365.1	364.4	365.1	364.1	364.2	365.3	365.6	365.7	365.7
5°	339.1	339.6	337.7	337.7	337.7	339.6	339.1	340.2	341.0	341.8	342.9
7.5°	316.6	315.8	315.8	314.8	315.8	315.8	316.6	317.4	318.6	320.3	321.8
10°	302.9	301.7	301.3	301.6	301.3	301.7	302.9	305.1	305.8	307.3	309.0
12.5°	291.4	291.3	288.8	288.8	288.8	291.3	291.4	292.1	293.7	296.8	298.7
15°	278.1	274.6	274.3	275.4	274.3	274.6	278.1	278.1	278.8	281.2	282.3
17.5°	264.7	262.8	263.0	262.4	263.0	262.8	264.7	265.0	265.6	267.6	269.0
20°	257.6	256.5	256.4	255.1	256.4	256.5	257.6	257.6	258.4	259.3	260.8
22.5°	251.1	250.8	250.9	249.5	250.9	250.8	251.1	251.6	252.3	252.9	254.0
25°	243.0	244.0	243.2	243.2	243.2	244.0	243.0	243.2	243.4	244.3	245.1
27.5°	237.6	237.6	237.2	237.2	237.2	237.6	237.6	237.2	236.9	236.6	236.5
30°	233.5	233.3	233.6	233.6	233.6	233.3	233.5	232.7	232.3	232.2	231.4
32.5°	229.3	229.6	229.7	229.8	229.7	229.6	229.3	228.5	227.8	227.3	226.7
35°	222.9	223.2	223.7	223.3	223.7	223.2	222.9	221.8	221.1	220.0	219.0
37.5°	214.3	215.2	215.0	215.2	215.0	215.2	214.3	214.0	213.3	212.4	211.3
40°	207.8	208.3	208.2	208.2	208.2	208.3	207.8	207.6	206.9	206.4	205.4
42.5°	201.1	201.5	201.1	200.8	201.1	201.5	201.1	200.8	200.4	199.4	198.3
45°	190.3	189.9	190.4	189.7	190.4	189.9	190.3	189.6	189.3	188.6	187.7
47.5°	178.1	178.5	178.6	179.2	178.6	178.5	178.1	178.2	177.1	176.7	176.4
50°	170.0	171.1	171.1	170.9	171.1	171.1	170.0	169.6	168.9	168.1	168.1
52.5°	162.0	162.5	163.3	163.2	163.3	162.5	162.0	161.4	160.6	159.5	159.2
55°	149.6	150.0	150.4	150.6	150.4	150.0	149.6	148.2	147.7	147.1	146.2
57.5°	136.9	136.7	137.6	137.9	137.6	136.7	136.9	135.5	134.8	133.0	132.8
60°	127.9	127.9	129.4	129.9	129.4	127.9	127.9	126.4	125.2	124.1	123.7
62.5°	118.3	118.9	120.3	119.6	120.3	118.9	118.3	116.7	115.7	114.3	113.3
65°	104.3	105.8	105.6	106.3	105.6	105.8	104.3	103.4	101.3	100.1	98.9
67.5°	89.6	90.5	91.9	92.0	91.9	90.5	89.6	88.2	86.8	85.5	84.1
70°	79.7	80.6	81.4	81.9	81.4	80.6	79.7	78.3	76.8	75.8	74.4
72.5°	70.1	70.6	72.4	71.6	72.4	70.6	70.1	68.4	67.2	66.4	64.8
75°	55.0	56.3	57.4	56.9	57.4	56.3	55.0	53.7	52.8	51.7	50.2
77.5°	40.6	42.0	42.5	42.0	42.5	42.0	40.6	39.8	39.4	37.2	37.0
80°	32.1	31.9	33.0	32.9	33.0	31.9	32.1	30.8	29.9	28.6	28.6
82.5°	23.5	23.4	23.8	24.0	23.8	23.4	23.5	22.8	21.6	21.1	20.6
85°	11.4	12.0	11.2	11.1	11.2	12.0	11.4	10.7	10.7	10.7	10.5
87.5°	7.9	8.0	7.9	7.9	7.9	8.0	7.9	7.8	8.3	7.7	7.5
90°	26.4	26.8	27.2	27.6	27.2	26.8	26.4	26.0	25.3	24.6	23.7
92.5°	29.8	30.1	30.3	30.6	30.3	30.1	29.8	29.5	28.8	27.5	26.1
95°	34.9	34.9	34.9	34.9	34.9	34.9	34.9	34.9	34.2	32.8	31.4
97.5°	37.3	37.5	37.7	37.9	37.7	37.5	37.3	37.1	36.2	34.5	32.9
100°	38.0	38.3	38.4	38.7	38.4	38.3	38.0	37.9	36.9	35.3	33.7
102.5°	38.3	38.7	39.1	39.4	39.1	38.7	38.3	37.9	40.2	45.3	50.4
105°	39.3	39.7	40.1	40.5	40.1	39.7	39.3	38.9	56.7	92.9	129.1
107.5°	209.1	181.7	154.5	127.2	154.5	181.7	209.1	236.3	263.2	289.8	316.3
110°	340.9	311.6	282.3	253.1	282.3	311.6	340.9	370.1	388.1	394.8	401.6



TEST NUMBER: P331901-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	452.7	446.6	440.4	434.2	440.4	446.6	452.7	458.9	462.0	461.8	461.7
115°	538.7	539.6	540.3	541.1	540.3	539.6	538.7	537.9	536.5	534.4	532.3
117.5°	600.7	600.9	601.0	601.2	601.0	600.9	600.7	600.6	599.6	598.0	596.4
120°	642.4	642.4	642.4	642.4	642.4	642.4	642.4	642.4	641.6	639.9	638.3
122.5°	682.4	682.5	682.8	682.9	682.8	682.5	682.4	682.2	681.6	680.5	679.3
125°	738.7	739.2	739.6	740.0	739.6	739.2	738.7	738.3	737.9	737.5	737.1
127.5°	796.1	795.7	795.3	794.8	795.3	795.7	796.1	796.5	796.3	795.7	795.0
130°	831.4	831.0	830.6	830.2	830.6	831.0	831.4	831.8	831.6	830.8	830.0
132.5°	864.3	863.7	863.2	862.5	863.2	863.7	864.3	864.8	864.7	864.0	863.1
135°	913.9	913.3	912.7	912.1	912.7	913.3	913.9	914.6	914.6	913.9	913.3
137.5°	959.9	959.5	959.1	958.6	959.1	959.5	959.9	960.3	960.0	959.0	958.1
140°	987.9	987.5	987.1	986.7	987.1	987.5	987.9	988.2	988.1	987.2	986.4
142.5°	1014.2	1013.5	1013.0	1012.4	1013.0	1013.5	1014.2	1014.7	1014.6	1014.0	1013.4
145°	1051.9	1051.9	1051.9	1051.9	1051.9	1051.9	1051.9	1051.9	1051.8	1051.4	1051.0
147.5°	1084.3	1083.3	1082.4	1081.4	1082.4	1083.3	1084.3	1085.2	1085.4	1085.1	1084.7
150°	1105.3	1104.8	1104.1	1103.5	1104.1	1104.8	1105.3	1106.0	1106.0	1105.6	1105.3
152.5°	1124.0	1123.1	1122.1	1121.2	1122.1	1123.1	1124.0	1125.0	1125.1	1124.3	1123.6
155°	1149.5	1148.3	1147.1	1145.9	1147.1	1148.3	1149.5	1150.7	1150.9	1149.9	1148.8
157.5°	1171.5	1169.8	1168.2	1166.6	1168.2	1169.8	1171.5	1173.1	1173.2	1172.0	1170.8
160°	1184.2	1182.8	1181.3	1179.9	1181.3	1182.8	1184.2	1185.7	1185.7	1184.5	1183.3
162.5°	1196.2	1194.9	1193.7	1192.4	1193.7	1194.9	1196.2	1197.5	1197.5	1196.0	1194.7
165°	1211.8	1210.4	1208.9	1207.5	1208.9	1210.4	1211.8	1213.2	1213.1	1211.5	1209.9
167.5°	1223.3	1221.6	1220.0	1218.4	1220.0	1221.6	1223.3	1225.0	1225.0	1223.3	1221.6
170°	1229.9	1228.3	1226.6	1225.0	1226.6	1228.3	1229.9	1231.5	1231.5	1229.9	1228.3
172.5°	1234.1	1232.3	1230.5	1228.7	1230.5	1232.3	1234.1	1235.9	1236.0	1234.3	1232.7
175°	1239.1	1237.5	1235.9	1234.2	1235.9	1237.5	1239.1	1240.7	1240.9	1239.4	1238.0
177.5°	1240.8	1239.1	1237.5	1235.9	1237.5	1239.1	1240.8	1242.4	1242.5	1241.3	1239.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P331901-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	365.3	365.3	368.0	369.9	372.1	373.5	374.5	375.6	377.4	379.7	382.4
5°	344.4	345.1	349.2	353.2	357.1	360.4	363.2	366.5	370.6	375.6	381.1
7.5°	324.2	327.0	331.1	336.0	341.4	346.3	351.2	356.6	362.4	369.7	377.5
10°	311.2	314.3	319.2	325.6	331.3	337.0	343.1	349.0	356.2	364.9	374.9
12.5°	299.8	302.8	307.9	314.7	320.2	326.5	333.5	341.2	349.3	359.7	371.0
15°	284.0	287.6	293.8	297.1	305.5	313.0	319.5	330.5	340.9	351.6	364.6
17.5°	271.1	273.1	278.1	284.3	290.5	299.0	307.4	316.7	327.0	340.1	356.5
20°	262.2	263.9	269.4	275.9	282.6	290.3	297.9	307.1	318.7	332.6	350.3
22.5°	255.6	257.4	261.0	267.9	274.1	280.6	288.1	299.1	311.5	325.0	344.2
25°	246.0	247.1	249.5	255.1	260.5	267.8	274.4	284.8	297.5	313.4	332.6
27.5°	236.9	238.0	240.0	243.9	249.1	254.9	262.2	270.9	283.8	301.1	321.5
30°	231.4	231.6	233.5	237.2	241.6	246.4	253.0	263.0	275.2	292.7	314.1
32.5°	226.7	226.0	227.3	230.0	234.3	239.2	244.6	254.4	266.2	283.4	305.4
35°	218.7	218.3	217.8	220.1	223.9	227.5	232.3	239.7	253.0	269.1	292.2
37.5°	210.6	209.6	208.7	209.8	212.6	216.5	220.6	227.2	238.7	256.4	278.5
40°	204.5	203.7	203.2	202.8	205.4	209.1	212.2	218.5	229.2	246.0	267.8
42.5°	197.8	197.4	196.7	196.1	198.3	201.1	204.4	209.9	220.6	236.4	257.0
45°	187.1	186.8	186.4	186.0	187.4	189.9	192.5	196.5	205.8	221.1	239.7
47.5°	175.2	174.8	174.9	174.3	175.5	177.3	179.1	183.5	192.3	204.7	218.3
50°	166.7	166.4	166.4	166.4	166.8	168.9	170.6	173.9	182.0	194.3	204.1
52.5°	158.5	157.7	157.7	158.0	158.8	160.0	161.1	164.7	171.7	182.0	190.8
55°	145.8	144.3	143.9	144.3	144.9	146.0	147.1	150.0	156.1	163.7	168.9
57.5°	131.7	130.9	130.4	130.5	130.8	131.7	132.5	135.7	140.5	144.5	147.8
60°	121.8	122.2	120.5	120.9	120.9	121.6	122.9	124.9	129.0	131.7	135.1
62.5°	112.5	112.0	111.5	111.0	111.0	111.3	113.0	114.6	118.1	119.5	122.1
65°	98.0	98.0	96.9	97.3	97.4	96.2	97.0	98.9	101.2	101.7	104.1
67.5°	83.3	82.8	82.1	81.6	81.6	81.5	82.0	82.9	84.5	84.8	86.6
70°	73.3	72.9	72.7	72.2	71.5	72.3	71.8	72.7	73.7	73.8	74.9
72.5°	63.5	63.1	62.8	62.3	61.9	61.9	61.9	63.0	63.6	63.4	64.6
75°	49.7	49.3	48.9	48.0	48.0	47.5	47.6	48.3	49.1	48.6	49.7
77.5°	36.4	35.3	35.3	35.5	34.9	35.0	34.8	34.7	35.0	35.0	36.0
80°	28.0	26.8	27.1	26.9	26.8	26.5	26.2	26.4	26.5	26.8	27.3
82.5°	20.2	20.1	19.7	19.7	19.5	19.0	18.9	19.2	19.3	19.3	19.6
85°	10.3	9.7	10.1	10.0	10.1	10.0	9.4	9.4	9.7	9.6	10.0
87.5°	7.7	7.5	6.8	6.4	5.8	5.4	4.8	4.5	4.3	3.8	3.7
90°	22.9	22.1	19.4	16.8	14.1	11.5	9.1	7.1	5.0	2.9	1.0
92.5°	24.9	23.5	21.5	19.6	17.6	15.5	14.8	15.4	16.0	16.6	17.1
95°	29.9	28.5	26.3	24.0	21.8	19.6	22.6	31.0	39.4	47.8	56.2
97.5°	31.3	29.6	44.4	59.1	73.8	88.6	97.8	101.6	105.3	109.1	112.8
100°	32.0	30.3	62.3	94.2	126.1	158.0	171.9	167.8	163.7	159.6	155.5
102.5°	55.5	60.5	95.4	130.2	165.1	199.9	215.9	212.9	210.0	207.1	204.1
105°	165.3	201.5	220.0	238.4	256.7	275.2	283.3	281.0	278.8	276.6	274.3
107.5°	342.9	369.5	366.5	363.6	360.8	357.8	355.5	353.6	351.9	350.1	348.2
110°	408.4	415.1	412.8	410.6	408.4	406.1	404.2	402.5	400.8	399.3	397.6



TEST NUMBER: P331901-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	461.6	461.4	459.2	457.0	454.7	452.5	450.6	449.2	447.7	446.2	444.7
115°	530.4	528.3	526.5	524.6	522.8	520.9	519.4	518.2	516.9	515.7	514.5
117.5°	594.7	593.1	592.2	591.2	590.3	589.3	588.1	586.6	585.0	583.5	582.0
120°	636.7	635.0	634.5	633.8	633.2	632.6	631.4	629.5	627.7	625.8	624.0
122.5°	678.2	677.0	676.2	675.5	674.7	673.9	672.8	671.2	669.7	668.2	666.7
125°	736.7	736.3	735.5	734.7	733.8	733.0	731.8	730.2	728.5	726.9	725.2
127.5°	794.4	793.7	792.7	791.8	790.8	789.8	788.5	786.9	785.2	783.5	782.0
130°	829.2	828.3	827.5	826.7	825.9	825.1	823.8	822.2	820.5	819.0	817.3
132.5°	862.3	861.5	860.8	860.2	859.5	858.8	857.7	856.0	854.4	852.8	851.1
135°	912.7	912.1	911.2	910.5	909.7	908.8	907.8	906.6	905.3	904.1	902.9
137.5°	957.0	956.1	955.6	955.2	954.7	954.3	953.3	951.7	950.1	948.6	947.1
140°	985.6	984.8	984.2	983.6	982.9	982.3	981.4	980.2	979.0	977.7	976.5
142.5°	1012.7	1012.0	1011.5	1010.8	1010.2	1009.6	1008.7	1007.4	1006.2	1005.0	1003.8
145°	1050.5	1050.1	1049.7	1049.3	1048.9	1048.5	1047.6	1046.2	1044.7	1043.3	1041.9
147.5°	1084.3	1083.8	1083.4	1083.0	1082.6	1082.2	1081.5	1080.5	1079.7	1078.7	1077.8
150°	1104.9	1104.5	1104.1	1103.6	1103.2	1102.8	1102.3	1101.7	1101.1	1100.4	1099.9
152.5°	1122.8	1122.1	1121.9	1121.7	1121.3	1121.1	1120.9	1120.5	1120.3	1120.0	1119.7
155°	1147.8	1146.8	1146.6	1146.4	1146.1	1146.0	1146.1	1146.4	1146.8	1147.3	1147.7
157.5°	1169.6	1168.3	1168.5	1168.7	1168.9	1169.1	1169.3	1169.3	1169.3	1169.3	1169.4
160°	1182.1	1180.8	1181.1	1181.2	1181.5	1181.6	1181.9	1182.1	1182.3	1182.5	1182.6
162.5°	1193.3	1191.8	1192.1	1192.3	1192.5	1192.7	1193.0	1193.6	1194.1	1194.7	1195.2
165°	1208.2	1206.6	1206.8	1207.0	1207.2	1207.4	1207.8	1208.5	1209.0	1209.7	1210.3
167.5°	1220.0	1218.4	1218.4	1218.4	1218.4	1218.4	1218.8	1219.6	1220.4	1221.2	1222.1
170°	1226.6	1225.0	1225.0	1225.0	1225.0	1225.0	1225.4	1226.2	1227.1	1227.9	1228.7
172.5°	1231.1	1229.4	1229.2	1229.1	1228.9	1228.8	1229.2	1230.2	1231.1	1232.2	1233.1
175°	1236.6	1235.1	1234.9	1234.7	1234.5	1234.3	1234.7	1235.7	1236.8	1237.8	1238.8
177.5°	1238.7	1237.3	1237.2	1237.0	1236.8	1236.7	1237.0	1237.9	1238.7	1239.4	1240.3
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P331901-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	383.3	384.0	386.5	388.3	390.4	391.6	392.7	393.6	394.8	395.1	399.3
5°	385.0	388.6	395.1	399.9	405.8	412.3	416.7	418.7	424.1	428.5	437.4
7.5°	384.5	392.4	402.1	412.3	423.0	433.1	441.8	452.2	459.5	470.6	481.4
10°	384.0	394.6	407.1	420.0	435.1	449.2	461.8	475.8	487.4	502.7	515.8
12.5°	382.7	395.5	412.9	428.2	446.6	465.9	484.5	502.5	512.8	538.3	550.3
15°	379.5	394.6	416.4	439.6	464.9	487.7	511.4	530.2	560.6	583.0	597.2
17.5°	373.2	394.3	420.2	448.2	479.0	509.1	535.9	564.4	596.8	623.8	652.6
20°	370.2	393.5	422.2	453.3	485.2	519.4	549.8	584.1	619.3	645.9	682.9
22.5°	364.7	391.1	422.1	456.6	490.8	526.1	561.7	596.4	637.1	673.7	708.8
25°	355.8	385.3	417.5	456.1	496.1	531.5	574.2	620.1	662.5	709.6	744.7
27.5°	346.4	378.0	410.1	446.0	489.1	531.2	584.8	636.7	688.6	729.2	755.2
30°	339.2	369.9	403.1	439.3	481.9	531.9	591.8	648.5	699.1	734.0	748.5
32.5°	331.4	362.4	391.8	429.8	475.2	531.4	596.3	655.5	699.7	722.9	720.0
35°	319.1	345.1	373.8	410.3	463.7	528.1	598.9	656.1	683.2	678.2	640.6
37.5°	301.3	323.3	351.4	391.4	450.5	521.3	593.7	636.6	634.9	594.3	539.7
40°	290.3	309.0	336.0	378.1	440.1	516.9	585.6	613.5	589.9	533.1	467.9
42.5°	275.8	293.0	320.1	363.4	428.8	507.9	570.1	578.1	532.0	466.8	406.9
45°	253.4	268.5	296.6	341.3	411.7	488.3	532.3	512.5	450.3	382.9	337.4
47.5°	229.3	245.0	272.0	317.9	387.1	458.8	479.7	437.8	373.9	319.2	277.4
50°	214.0	229.2	255.6	301.9	370.4	434.6	443.3	389.0	330.3	282.3	248.0
52.5°	198.8	212.9	238.9	285.4	350.9	406.5	401.2	345.9	292.0	251.0	224.1
55°	175.9	189.3	214.0	257.6	317.3	361.3	342.0	289.2	244.5	212.8	192.3
57.5°	155.4	168.3	189.6	229.0	280.8	311.2	286.5	242.0	206.5	182.0	166.8
60°	141.6	153.0	173.3	209.8	254.8	277.9	253.6	214.3	184.3	164.8	151.1
62.5°	128.4	138.4	157.2	190.4	229.5	248.8	224.2	190.9	165.5	148.1	136.5
65°	108.5	117.6	134.2	160.0	192.1	205.0	183.8	156.9	137.1	124.2	116.5
67.5°	90.4	98.1	112.4	132.7	156.4	165.7	149.6	128.7	113.8	103.5	97.4
70°	78.3	84.9	96.2	113.7	135.1	142.3	127.1	110.0	99.1	90.8	85.1
72.5°	68.0	73.0	83.2	96.7	114.5	120.3	109.7	94.7	84.5	78.3	73.7
75°	51.9	55.9	62.6	73.4	85.8	89.1	81.2	71.8	65.0	60.5	57.0
77.5°	37.4	40.4	45.2	51.9	60.4	63.5	58.5	52.1	47.1	44.2	42.2
80°	28.2	30.7	34.7	40.2	45.4	47.1	44.1	39.3	35.8	34.1	32.5
82.5°	20.8	22.2	24.6	28.4	31.9	33.9	31.4	28.5	26.6	25.1	24.5
85°	10.5	11.2	12.4	13.9	16.1	16.8	15.8	15.1	14.0	13.1	13.1
87.5°	4.4	4.8	5.7	6.4	7.4	8.4	8.8	9.0	9.4	9.4	9.5
90°	2.9	5.0	7.1	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.7
92.5°	16.6	16.0	15.4	14.8	15.5	17.6	19.6	21.5	23.5	24.9	26.1
95°	47.8	39.4	31.0	22.6	19.6	21.8	24.0	26.3	28.5	29.9	31.4
97.5°	109.1	105.3	101.6	97.8	88.6	73.8	59.1	44.4	29.6	31.3	32.9
100°	159.6	163.7	167.8	171.9	158.0	126.1	94.2	62.3	30.3	32.0	33.7
102.5°	207.1	210.0	212.9	215.9	199.9	165.1	130.2	95.4	60.5	55.5	50.4
105°	276.6	278.8	281.0	283.3	275.2	256.7	238.4	220.0	201.5	165.3	129.1
107.5°	350.1	351.9	353.6	355.5	357.8	360.8	363.6	366.5	369.5	342.9	316.3
110°	399.3	400.8	402.5	404.2	406.1	408.4	410.6	412.8	415.1	408.4	401.6





TEST NUMBER: P331901-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	446.2	447.7	449.2	450.6	452.5	454.7	457.0	459.2	461.4	461.6	461.7
115°	515.7	516.9	518.2	519.4	520.9	522.8	524.6	526.5	528.3	530.4	532.3
117.5°	583.5	585.0	586.6	588.1	589.3	590.3	591.2	592.2	593.1	594.7	596.4
120°	625.8	627.7	629.5	631.4	632.6	633.2	633.8	634.5	635.0	636.7	638.3
122.5°	668.2	669.7	671.2	672.8	673.9	674.7	675.5	676.2	677.0	678.2	679.3
125°	726.9	728.5	730.2	731.8	733.0	733.8	734.7	735.5	736.3	736.7	737.1
127.5°	783.5	785.2	786.9	788.5	789.8	790.8	791.8	792.7	793.7	794.4	795.0
130°	819.0	820.5	822.2	823.8	825.1	825.9	826.7	827.5	828.3	829.2	830.0
132.5°	852.8	854.4	856.0	857.7	858.8	859.5	860.2	860.8	861.5	862.3	863.1
135°	904.1	905.3	906.6	907.8	908.8	909.7	910.5	911.2	912.1	912.7	913.3
137.5°	948.6	950.1	951.7	953.3	954.3	954.7	955.2	955.6	956.1	957.0	958.1
140°	977.7	979.0	980.2	981.4	982.3	982.9	983.6	984.2	984.8	985.6	986.4
142.5°	1005.0	1006.2	1007.4	1008.7	1009.6	1010.2	1010.8	1011.5	1012.0	1012.7	1013.4
145°	1043.3	1044.7	1046.2	1047.6	1048.5	1048.9	1049.3	1049.7	1050.1	1050.5	1051.0
147.5°	1078.7	1079.7	1080.5	1081.5	1082.2	1082.6	1083.0	1083.4	1083.8	1084.3	1084.7
150°	1100.4	1101.1	1101.7	1102.3	1102.8	1103.2	1103.6	1104.1	1104.5	1104.9	1105.3
152.5°	1120.0	1120.3	1120.5	1120.9	1121.1	1121.3	1121.7	1121.9	1122.1	1122.8	1123.6
155°	1147.3	1146.8	1146.4	1146.1	1146.0	1146.1	1146.4	1146.6	1146.8	1147.8	1148.8
157.5°	1169.3	1169.3	1169.3	1169.3	1169.1	1168.9	1168.7	1168.5	1168.3	1169.6	1170.8
160°	1182.5	1182.3	1182.1	1181.9	1181.6	1181.5	1181.2	1181.1	1180.8	1182.1	1183.3
162.5°	1194.7	1194.1	1193.6	1193.0	1192.7	1192.5	1192.3	1192.1	1191.8	1193.3	1194.7
165°	1209.7	1209.0	1208.5	1207.8	1207.4	1207.2	1207.0	1206.8	1206.6	1208.2	1209.9
167.5°	1221.2	1220.4	1219.6	1218.8	1218.4	1218.4	1218.4	1218.4	1218.4	1220.0	1221.6
170°	1227.9	1227.1	1226.2	1225.4	1225.0	1225.0	1225.0	1225.0	1225.0	1226.6	1228.3
172.5°	1232.2	1231.1	1230.2	1229.2	1228.8	1228.9	1229.1	1229.2	1229.4	1231.1	1232.7
175°	1237.8	1236.8	1235.7	1234.7	1234.3	1234.5	1234.7	1234.9	1235.1	1236.6	1238.0
177.5°	1239.4	1238.7	1237.9	1237.0	1236.7	1236.8	1237.0	1237.2	1237.3	1238.7	1239.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P331901-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	400.8	401.0	402.6	403.8	403.2	403.9	404.3
5°	437.9	444.6	448.1	450.7	450.8	451.1	452.5
7.5°	490.5	497.6	502.9	510.8	513.1	515.8	515.1
10°	528.9	539.5	548.5	553.3	558.5	566.0	559.9
12.5°	564.8	583.4	597.2	604.7	609.5	611.0	608.1
15°	624.0	648.3	661.4	661.1	677.6	684.8	673.6
17.5°	678.2	700.7	718.7	727.9	741.8	744.8	743.5
20°	711.5	736.0	750.0	765.9	773.1	779.5	780.6
22.5°	740.1	762.2	777.2	790.4	796.4	799.5	801.3
25°	769.6	787.0	796.0	800.6	802.2	801.8	799.5
27.5°	767.5	768.9	758.9	749.2	740.4	730.6	727.1
30°	747.6	732.1	704.4	688.7	665.7	647.4	654.8
32.5°	695.2	664.3	633.3	599.0	570.6	562.5	554.4
35°	593.3	539.1	507.3	470.4	455.7	440.9	430.7
37.5°	480.0	438.1	400.4	376.3	361.5	352.1	347.1
40°	415.0	377.2	346.2	326.6	315.4	304.9	303.4
42.5°	363.2	328.0	304.8	289.1	278.4	273.9	270.6
45°	297.5	273.0	257.3	246.2	239.0	236.2	232.5
47.5°	251.8	234.5	222.7	215.2	209.7	207.6	207.4
50°	226.2	211.8	203.2	197.3	193.1	192.3	189.3
52.5°	207.1	194.6	187.8	182.7	179.6	177.5	176.7
55°	179.7	171.4	165.3	162.4	160.0	158.0	158.0
57.5°	157.2	150.4	146.3	143.8	143.1	141.6	140.7
60°	143.4	137.5	134.4	132.1	130.6	130.9	129.2
62.5°	129.8	126.0	122.9	120.8	119.0	119.1	119.1
65°	110.5	107.6	105.4	104.6	103.5	102.3	102.6
67.5°	93.7	90.9	89.2	87.9	87.5	86.8	87.9
70°	81.6	79.5	78.3	77.2	76.8	76.9	77.9
72.5°	70.5	69.1	68.2	67.7	66.9	66.9	67.6
75°	55.4	54.3	53.6	53.0	52.8	52.8	52.8
77.5°	40.6	40.4	40.1	39.3	39.3	39.5	39.5
80°	32.1	31.5	31.4	31.0	30.4	30.1	31.0
82.5°	24.0	23.4	23.3	23.2	22.3	22.3	23.1
85°	12.9	12.4	12.5	12.4	12.4	12.2	12.2
87.5°	9.5	9.5	9.5	9.7	9.7	9.6	10.0
90°	24.6	25.3	26.0	26.4	26.8	27.2	27.6
92.5°	27.5	28.8	29.5	29.8	30.1	30.3	30.6
95°	32.8	34.2	34.9	34.9	34.9	34.9	34.9
97.5°	34.5	36.2	37.1	37.3	37.5	37.7	37.9
100°	35.3	36.9	37.9	38.0	38.3	38.4	38.7
102.5°	45.3	40.2	37.9	38.3	38.7	39.1	39.4
105°	92.9	56.7	38.9	39.3	39.7	40.1	40.5
107.5°	289.8	263.2	236.3	209.1	181.7	154.5	127.2
110°	394.8	388.1	370.1	340.9	311.6	282.3	253.1



TEST NUMBER: P331901-927

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	461.8	462.0	458.9	452.7	446.6	440.4	434.2
115°	534.4	536.5	537.9	538.7	539.6	540.3	541.1
117.5°	598.0	599.6	600.6	600.7	600.9	601.0	601.2
120°	639.9	641.6	642.4	642.4	642.4	642.4	642.4
122.5°	680.5	681.6	682.2	682.4	682.5	682.8	682.9
125°	737.5	737.9	738.3	738.7	739.2	739.6	740.0
127.5°	795.7	796.3	796.5	796.1	795.7	795.3	794.8
130°	830.8	831.6	831.8	831.4	831.0	830.6	830.2
132.5°	864.0	864.7	864.8	864.3	863.7	863.2	862.5
135°	913.9	914.6	914.6	913.9	913.3	912.7	912.1
137.5°	959.0	960.0	960.3	959.9	959.5	959.1	958.6
140°	987.2	988.1	988.2	987.9	987.5	987.1	986.7
142.5°	1014.0	1014.6	1014.7	1014.2	1013.5	1013.0	1012.4
145°	1051.4	1051.8	1051.9	1051.9	1051.9	1051.9	1051.9
147.5°	1085.1	1085.4	1085.2	1084.3	1083.3	1082.4	1081.4
150°	1105.6	1106.0	1106.0	1105.3	1104.8	1104.1	1103.5
152.5°	1124.3	1125.1	1125.0	1124.0	1123.1	1122.1	1121.2
155°	1149.9	1150.9	1150.7	1149.5	1148.3	1147.1	1145.9
157.5°	1172.0	1173.2	1173.1	1171.5	1169.8	1168.2	1166.6
160°	1184.5	1185.7	1185.7	1184.2	1182.8	1181.3	1179.9
162.5°	1196.0	1197.5	1197.5	1196.2	1194.9	1193.7	1192.4
165°	1211.5	1213.1	1213.2	1211.8	1210.4	1208.9	1207.5
167.5°	1223.3	1225.0	1225.0	1223.3	1221.6	1220.0	1218.4
170°	1229.9	1231.5	1231.5	1229.9	1228.3	1226.6	1225.0
172.5°	1234.3	1236.0	1235.9	1234.1	1232.3	1230.5	1228.7
175°	1239.4	1240.9	1240.7	1239.1	1237.5	1235.9	1234.2
177.5°	1241.3	1242.5	1242.4	1240.8	1239.1	1237.5	1235.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

(END OF REPORT)