

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831356

Luminaire Tested: S123DIP-S340D1195U927-4F0-1E-UDD-G4

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831356  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D1195U927-4F0-1E-UDD-G4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4672.9 lumens  
Efficiency: N/A  
Efficacy: 107.7 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 43.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831356

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-G4

### Luminous Intensity Polar Plot





TEST NUMBER: P831356

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-G4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27				
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	31	30	30	23				
2	85	78	72	67	75	70	65	61	55	51	49	41	39	37	28	27	26	20				
3	77	69	62	56	69	62	56	51	48	44	41	36	34	31	25	23	22	17				
4	71	61	53	48	63	55	48	44	43	39	35	32	30	27	22	21	19	15				
5	65	54	47	41	58	49	42	37	39	34	31	29	26	24	20	19	17	13				
6	60	49	41	36	54	44	37	33	35	30	27	27	23	21	19	17	15	12				
7	56	44	36	31	50	40	33	29	32	27	24	24	21	19	17	15	14	11				
8	52	40	33	28	46	36	30	25	29	24	21	22	19	17	16	14	12	10				
9	48	36	29	25	43	33	27	23	27	22	19	20	17	15	15	13	11	9				
10	45	33	27	22	40	30	24	20	24	20	17	19	16	14	14	12	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	8372	8372	8372	8372	8372
5°	10588	9994	8447	6807	6255
10°	10691	11014	8391	5426	4741
15°	8052	10225	8333	4596	4009
20°	5611	8275	8227	4018	3643
25°	4278	6364	8045	3697	3417
30°	3701	5056	7756	3470	3234
35°	3434	4268	7422	3306	3106
40°	3250	3829	6953	3149	3063
45°	3142	3544	6357	3028	3043
50°	3088	3317	5652	2915	3028
55°	2973	3153	4958	2811	3042
60°	2868	2975	4273	2713	2992
65°	2692	2809	3685	2606	2932
70°	2486	2596	3135	2430	2760
75°	2250	2325	2687	2258	2520
80°	1860	2033	2126	1971	2126
85°	1470	1655	1556	1667	1692

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 7258 cd/sqm

TEST NUMBER: P831356

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-G4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.5	1.6
10°-20°	182.9	3.9
20°-30°	216.6	4.6
30°-40°	217.8	4.7
40°-50°	199.8	4.3
50°-60°	164.9	3.5
60°-70°	116.7	2.5
70°-80°	62.3	1.3
80°-90°	18.3	0.4
90°-100°	246.7	5.3
100°-110°	722.3	15.5
110°-120°	705.4	15.1
120°-130°	561.8	12.0
130°-140°	443.2	9.5
140°-150°	330.6	7.1
150°-160°	230.5	4.9
160°-170°	135.4	2.9
170°-180°	44.1	0.9
0°-30°	473.1	10.1
0°-40°	690.8	14.8
0°-60°	1055.6	22.6
0°-90°	1252.8	26.8
90°-120°	1674.5	35.8
90°-150°	3010.1	64.4
90°-180°	3420.0	73.2
0°-180°	4672.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	778	778	778	778	778	
5°	980	925	782	630	579	93
15°	723	918	748	412	360	200
25°	360	536	677	311	288	170
35°	261	325	565	252	236	164
45°	206	233	418	199	200	160
55°	158	168	264	150	162	142
65°	106	110	145	102	115	105
75°	54	56	65	54	61	57
85°	12	13	13	14	14	13
90°	27	23	2	23	27	15
95°	107	546	31	546	107	174
105°	1171	740	107	740	1171	1168
115°	1424	566	189	566	1424	1388
125°	1123	528	262	528	1123	1016
135°	910	521	307	521	910	706
145°	712	514	351	514	712	452
155°	590	498	398	498	590	275
165°	514	477	435	477	514	147
175°	463	457	454	457	463	45
180°	455	455	455	455	455	



TEST NUMBER: P831356

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	876.7	875.8	874.9	870.4	865.8	863.7	861.5	855.0	848.5	841.3	834.1
5°	979.9	982.4	985.0	982.1	979.2	970.3	961.5	949.8	938.0	924.9	911.7
7.5°	1027.5	1029.0	1030.4	1028.6	1026.8	1024.5	1022.1	1011.7	1001.2	987.7	974.1
10°	978.1	981.3	984.6	991.6	998.7	1006.6	1014.5	1013.1	1011.7	1007.7	1003.7
12.5°	869.5	873.4	877.4	891.5	905.5	923.6	941.6	957.2	972.7	983.5	994.3
15°	722.6	733.6	744.6	757.4	770.2	796.7	823.3	855.9	888.6	917.6	946.7
17.5°	595.2	599.3	603.5	617.2	630.9	664.3	697.7	735.4	773.1	821.3	869.5
20°	489.8	493.6	497.3	515.4	533.4	559.6	585.8	628.2	670.6	722.4	774.2
22.5°	411.4	417.4	423.4	433.5	443.6	468.7	493.7	531.5	569.2	626.4	683.6
25°	360.2	364.5	368.9	375.0	381.1	401.2	421.2	452.2	483.3	535.8	588.3
27.5°	325.2	327.0	328.8	334.9	341.1	354.1	367.1	393.8	420.5	465.0	509.6
30°	297.8	299.0	300.3	305.7	311.1	320.0	328.8	348.1	367.4	406.8	446.1
32.5°	278.6	279.5	280.4	284.6	288.7	295.1	301.4	315.4	329.5	362.0	394.5
35°	261.3	261.8	262.4	265.5	268.5	273.2	277.9	288.6	299.2	324.8	350.5
37.5°	246.1	246.9	247.6	249.4	251.2	255.4	259.5	268.0	276.5	296.1	315.8
40°	231.3	232.6	233.9	235.1	236.4	239.8	243.3	249.8	256.3	272.5	288.7
42.5°	218.7	220.0	221.2	221.8	222.3	224.3	226.3	232.3	238.2	250.3	262.4
45°	206.4	207.0	207.5	208.1	208.6	210.2	211.9	217.1	222.3	232.8	243.3
47.5°	195.3	195.3	195.3	195.6	196.0	197.4	198.9	202.7	206.4	214.6	222.7
50°	184.4	184.4	184.4	183.9	183.3	184.2	185.2	188.0	190.9	198.1	205.4
52.5°	171.4	171.4	171.4	171.6	171.8	171.8	171.8	174.3	176.9	183.3	189.8
55°	158.4	159.2	159.9	159.3	158.8	159.2	159.5	161.2	162.8	168.0	173.2
57.5°	145.5	145.8	146.2	146.0	145.8	146.0	146.2	147.6	149.1	153.0	157.0
60°	133.2	133.2	133.2	132.8	132.5	132.8	133.2	133.9	134.6	138.2	141.8
62.5°	119.5	119.6	119.8	120.0	120.2	119.8	119.5	120.4	121.3	124.0	126.7
65°	105.7	105.9	106.1	106.7	107.2	106.8	106.5	107.4	108.3	110.3	112.2
67.5°	93.5	93.1	92.8	92.9	93.1	93.7	94.2	94.4	94.6	96.7	98.9
70°	79.0	79.4	79.8	79.6	79.4	79.6	79.8	80.3	80.8	82.5	84.1
72.5°	66.0	66.2	66.4	66.4	66.4	66.8	67.1	67.7	68.2	69.1	70.0
75°	54.1	54.1	54.1	54.5	54.9	55.0	55.2	55.2	55.2	55.9	56.7
77.5°	41.1	42.0	42.9	42.8	42.6	42.9	43.3	43.9	44.4	44.8	45.1
80°	30.0	30.0	30.0	30.1	30.3	30.9	31.4	31.8	32.1	32.8	33.6
82.5°	19.1	19.3	19.5	20.0	20.6	20.9	21.3	21.8	22.4	22.4	22.4
85°	11.9	11.5	11.2	11.5	11.9	12.3	12.6	12.8	13.0	13.4	13.7
87.5°	5.8	5.8	5.8	5.8	5.8	6.0	6.1	6.1	6.1	6.1	6.1
90°	26.7	27.6	26.7	25.8	26.7	24.9	23.9	23.0	22.1	23.0	20.2
92.5°	48.8	50.6	49.7	53.4	55.2	61.7	70.9	91.1	127.9	171.2	189.6
95°	106.8	110.4	116.9	125.2	142.7	175.8	224.6	331.3	442.7	545.8	486.0
97.5°	219.1	229.2	251.3	286.2	347.9	452.8	574.3	761.2	867.9	839.4	626.8
100°	577.1	576.2	612.1	679.3	772.2	902.9	1010.6	1085.1	1052.9	871.6	589.1
102.5°	914.0	940.6	969.2	1018.9	1086.1	1156.9	1208.5	1192.8	1062.1	811.8	533.8
105°	1170.7	1175.3	1204.8	1239.8	1282.1	1306.0	1288.6	1196.5	1004.1	740.0	490.6
107.5°	1338.3	1348.4	1360.3	1376.9	1382.4	1357.6	1285.8	1141.3	921.3	676.5	459.3
110°	1434.0	1435.8	1437.7	1430.3	1404.5	1340.1	1224.1	1054.8	844.0	624.0	442.7



TEST NUMBER: P831356

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1453.3	1452.4	1443.2	1416.5	1364.0	1276.6	1143.1	969.2	776.8	589.1	433.5
115°	1423.8	1419.2	1400.8	1360.3	1291.3	1191.0	1055.7	895.5	725.3	566.0	432.6
117.5°	1359.4	1353.0	1325.4	1280.3	1208.5	1104.5	980.2	838.5	691.2	550.4	433.5
120°	1274.7	1269.2	1247.1	1195.6	1122.9	1029.9	919.5	795.2	665.4	540.3	437.2
122.5°	1195.6	1188.2	1163.4	1118.3	1055.7	971.0	870.7	761.2	644.3	533.8	443.6
125°	1122.9	1116.4	1093.4	1052.9	994.0	920.4	832.0	731.7	626.8	528.3	450.1
127.5°	1060.3	1054.8	1033.6	998.6	945.2	877.1	796.1	705.0	610.2	525.5	457.4
130°	1008.8	1001.4	982.1	948.9	900.1	837.6	763.0	680.2	597.3	522.8	464.8
132.5°	958.1	953.5	937.0	903.8	858.7	799.8	731.7	657.2	585.4	521.9	470.3
135°	910.3	903.8	887.3	859.6	814.5	762.1	702.3	636.9	575.2	520.9	475.8
137.5°	859.6	854.1	840.3	811.8	773.1	726.2	672.8	617.6	566.0	519.1	479.5
140°	806.3	807.2	792.5	766.7	731.7	692.1	648.0	601.0	557.8	518.2	483.2
142.5°	756.6	757.5	744.6	722.5	694.0	660.8	624.0	585.4	550.4	516.3	486.0
145°	711.5	709.6	702.3	682.9	659.9	633.2	603.8	573.4	544.0	514.5	486.9
147.5°	672.8	671.9	664.5	650.7	632.3	613.0	588.1	563.3	537.5	511.7	486.9
150°	639.7	639.7	634.2	624.0	610.2	592.7	573.4	552.2	531.1	508.1	486.9
152.5°	612.1	612.1	609.3	600.1	590.0	576.2	559.6	542.1	523.7	503.5	484.1
155°	590.0	589.1	587.2	579.8	571.6	560.5	546.7	532.0	516.3	497.9	482.3
157.5°	568.8	568.8	567.0	561.4	554.1	544.9	533.8	520.9	508.1	493.3	479.5
160°	548.6	549.5	549.5	544.0	537.5	531.1	521.9	511.7	499.8	487.8	477.7
162.5°	530.1	531.1	531.1	526.5	522.8	517.3	509.0	500.7	491.5	482.3	474.0
165°	514.5	514.5	515.4	511.7	508.1	503.5	497.0	491.5	484.1	476.8	470.3
167.5°	498.9	498.9	499.8	497.0	495.2	491.5	487.8	483.2	476.8	471.2	466.6
170°	485.0	485.0	486.0	484.1	483.2	481.4	477.7	474.9	470.3	465.7	463.0
172.5°	472.2	473.1	474.9	473.1	473.1	472.2	469.4	467.6	463.9	461.1	460.2
175°	463.0	463.9	464.8	463.9	463.9	463.9	462.0	461.1	459.3	457.4	457.4
177.5°	456.5	456.5	458.4	457.4	458.4	458.4	457.4	456.5	455.6	454.7	455.6
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P831356

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	831.9	829.8	821.8	813.9	804.9	795.8	789.2	782.5	772.6	762.6	754.5
5°	901.6	891.5	874.7	857.9	835.2	812.4	797.1	781.8	761.2	740.6	724.2
7.5°	956.8	939.5	916.0	892.6	862.8	833.0	804.9	776.7	745.3	713.9	688.3
10°	992.0	980.3	953.2	926.1	886.2	846.4	807.0	767.7	727.3	686.8	652.9
12.5°	995.4	996.5	971.6	946.7	901.6	856.5	808.6	760.8	709.9	659.0	619.5
15°	965.3	983.9	970.2	956.4	911.0	865.5	806.7	747.8	689.2	630.5	584.9
17.5°	909.3	949.2	951.2	953.2	907.7	862.2	797.1	731.9	665.5	599.1	551.1
20°	833.0	891.8	912.0	932.3	895.3	858.3	788.3	718.2	643.9	569.5	519.2
22.5°	755.0	826.5	863.5	900.5	873.1	845.6	771.1	696.6	618.1	539.6	488.5
25°	666.3	744.2	801.1	857.9	841.1	824.3	750.9	677.4	593.9	510.3	458.2
27.5°	588.8	668.1	736.6	805.2	801.6	798.0	725.1	652.2	566.6	481.1	430.8
30°	519.9	593.7	670.4	747.1	755.9	764.8	694.4	624.0	538.3	452.6	404.1
32.5°	458.9	523.3	605.6	687.9	705.2	722.6	659.0	595.5	510.7	425.9	379.1
35°	408.9	467.4	549.7	632.0	653.6	675.3	620.1	564.8	482.2	399.5	355.0
37.5°	364.7	413.6	493.9	574.2	600.8	627.3	577.8	528.4	451.0	373.6	332.6
40°	328.1	367.4	441.2	515.0	545.7	576.4	535.6	494.8	421.4	347.9	310.2
42.5°	297.4	332.4	399.4	466.3	495.7	525.1	490.7	456.2	390.9	325.6	291.1
45°	271.2	299.2	360.0	420.8	448.8	476.8	447.2	417.6	360.0	302.5	270.3
47.5°	246.7	270.7	322.7	374.6	399.5	424.4	401.3	378.2	329.5	280.8	251.7
50°	224.7	244.0	289.5	334.9	356.6	378.2	357.9	337.5	297.4	257.3	232.1
52.5°	205.5	221.2	259.3	297.4	316.0	334.6	317.1	299.6	267.8	236.0	214.0
55°	186.6	199.9	233.0	266.0	278.6	291.3	277.7	264.2	238.6	212.9	194.4
57.5°	168.9	180.8	207.9	235.0	244.7	254.4	242.2	229.9	210.6	191.3	175.8
60°	151.6	161.3	183.9	206.4	212.4	218.4	208.4	198.5	185.0	171.4	157.5
62.5°	135.5	144.4	161.2	177.9	181.9	185.9	178.3	170.7	160.4	150.1	139.3
65°	118.9	125.6	139.3	153.0	155.6	158.1	151.4	144.7	137.0	129.2	121.3
67.5°	103.6	108.3	119.5	130.7	130.8	131.0	125.6	120.2	115.9	111.5	105.2
70°	88.6	93.1	100.5	107.9	108.1	108.3	103.9	99.6	96.4	93.1	88.4
72.5°	73.3	76.5	82.1	87.7	87.3	87.0	84.3	81.6	79.0	76.5	73.1
75°	59.4	62.1	65.9	69.7	68.6	67.5	66.0	64.6	62.4	60.3	58.1
77.5°	46.7	48.4	50.5	52.7	52.0	51.3	50.0	48.7	47.1	45.5	44.6
80°	34.3	35.0	36.5	37.9	37.5	37.2	35.7	34.3	33.9	33.6	32.3
82.5°	23.3	24.2	24.5	24.9	24.7	24.5	23.5	22.4	22.0	21.7	21.5
85°	13.9	14.1	14.3	14.4	13.9	13.4	13.0	12.6	12.6	12.6	12.5
87.5°	6.3	6.5	6.5	6.5	6.3	6.1	5.8	5.4	5.6	5.8	5.8
90°	17.5	14.7	12.0	10.1	8.3	5.5	3.7	1.8	3.7	5.5	8.3
92.5°	141.7	93.0	63.5	46.9	37.7	29.5	20.2	13.8	20.2	29.5	37.7
95°	335.0	197.9	119.7	83.8	59.8	44.2	34.1	31.3	34.1	44.2	59.8
97.5°	372.8	213.5	136.2	96.6	72.7	58.9	50.6	49.7	50.6	58.9	72.7
100°	347.0	210.8	146.3	110.4	88.4	75.5	69.0	68.1	69.0	75.5	88.4
102.5°	324.9	214.5	158.3	126.1	106.8	94.8	89.3	87.4	89.3	94.8	106.8
105°	316.6	221.8	172.1	143.6	126.1	115.0	109.5	106.8	109.5	115.0	126.1
107.5°	314.8	233.8	189.6	162.9	146.3	135.3	129.8	127.0	129.8	135.3	146.3
110°	319.4	249.4	208.0	182.2	166.6	156.5	151.9	149.1	151.9	156.5	166.6





TEST NUMBER: P831356

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	328.6	265.1	227.3	202.5	186.8	176.7	172.1	169.4	172.1	176.7	186.8
115°	338.7	282.6	247.6	222.7	207.1	197.9	192.4	188.7	192.4	197.9	207.1
117.5°	351.6	301.0	266.0	243.0	225.5	217.2	212.6	208.0	212.6	217.2	225.5
120°	366.3	318.5	285.3	262.3	244.8	235.6	231.0	228.3	231.0	235.6	244.8
122.5°	380.1	336.9	304.7	279.8	263.2	253.1	248.5	245.7	248.5	253.1	263.2
125°	394.8	354.4	322.1	297.3	279.8	269.7	264.2	262.3	264.2	269.7	279.8
127.5°	406.8	370.0	338.7	313.9	294.5	284.4	278.0	275.2	278.0	284.4	294.5
130°	418.8	383.8	353.4	328.6	309.3	298.2	289.9	287.2	289.9	298.2	309.3
132.5°	429.8	395.8	366.3	342.4	323.1	309.3	300.0	296.4	300.0	309.3	323.1
135°	439.0	407.7	379.2	354.4	335.0	321.2	311.1	307.4	311.1	321.2	335.0
137.5°	446.4	416.0	388.4	365.4	346.1	331.3	321.2	317.5	321.2	331.3	346.1
140°	451.9	424.3	397.6	374.6	356.2	341.5	332.3	327.7	332.3	341.5	356.2
142.5°	457.4	430.7	405.0	383.8	365.4	352.5	342.4	338.7	342.4	352.5	365.4
145°	461.1	436.3	412.3	391.2	375.5	361.7	353.4	350.7	353.4	361.7	375.5
147.5°	463.9	440.9	418.8	400.4	384.7	372.8	364.5	362.6	364.5	372.8	384.7
150°	464.8	445.5	424.3	407.7	394.8	382.9	375.5	374.6	375.5	382.9	394.8
152.5°	466.6	448.2	430.7	415.1	404.1	393.9	386.6	386.6	386.6	393.9	404.1
155°	466.6	451.9	436.3	423.4	413.3	404.1	398.5	398.5	398.5	404.1	413.3
157.5°	467.6	453.8	440.9	430.7	421.5	413.3	408.7	407.7	408.7	413.3	421.5
160°	467.6	456.5	445.5	436.3	429.8	422.5	418.8	418.8	418.8	422.5	429.8
162.5°	466.6	457.4	448.2	440.9	435.3	429.8	427.1	427.1	427.1	429.8	435.3
165°	464.8	458.4	451.0	444.6	440.9	436.3	434.4	435.3	434.4	436.3	440.9
167.5°	463.9	458.4	452.8	448.2	445.5	441.8	440.9	441.8	440.9	441.8	445.5
170°	461.1	457.4	452.8	451.0	449.2	446.4	445.5	447.3	445.5	446.4	449.2
172.5°	460.2	457.4	453.8	452.8	451.9	450.1	450.1	451.0	450.1	450.1	451.9
175°	458.4	456.5	454.7	453.8	453.8	451.9	452.8	453.8	452.8	451.9	453.8
177.5°	457.4	455.6	454.7	454.7	454.7	453.8	454.7	455.6	454.7	453.8	454.7
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P831356

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	746.4	739.3	732.3	726.9	721.5	712.3	703.1	700.9	698.7	695.7	692.6
5°	707.8	690.4	673.1	657.6	642.1	630.0	617.9	610.0	602.0	596.2	590.5
7.5°	662.6	636.7	610.7	592.3	573.9	556.4	538.9	533.3	527.7	520.1	512.5
10°	619.0	590.3	561.6	537.6	513.6	496.4	479.3	472.4	465.6	456.0	446.5
12.5°	580.0	548.6	517.2	493.0	468.8	452.2	435.6	425.7	415.8	410.4	405.0
15°	539.2	505.6	472.1	449.7	427.3	412.4	397.4	388.7	380.0	374.8	369.6
17.5°	503.1	469.9	436.7	415.2	393.8	380.0	366.3	358.8	351.2	347.2	343.2
20°	468.8	436.4	403.9	382.9	362.0	350.8	339.6	334.8	329.9	326.6	323.4
22.5°	437.4	405.5	373.6	355.7	337.8	328.8	319.8	316.3	312.9	310.2	307.5
25°	406.0	377.5	349.0	333.9	318.7	311.3	303.9	300.5	297.0	294.3	291.6
27.5°	380.4	353.2	325.9	312.9	299.9	294.2	288.4	285.7	283.0	280.4	277.9
30°	355.5	331.1	306.8	295.6	284.4	279.2	273.9	271.2	268.5	266.2	263.8
32.5°	332.4	311.5	290.5	280.3	270.0	265.6	261.3	258.1	254.8	253.0	251.2
35°	310.4	291.6	272.9	264.4	255.9	251.6	247.2	244.5	241.8	240.4	238.9
37.5°	291.6	274.8	258.1	249.9	241.8	237.7	233.5	231.2	228.8	228.3	227.7
40°	272.5	258.1	243.6	235.7	227.7	224.1	220.5	219.1	217.6	217.3	216.9
42.5°	256.6	242.5	228.5	221.2	214.0	211.0	207.9	207.2	206.4	207.0	207.5
45°	238.2	226.5	214.7	208.1	201.4	198.9	196.3	195.8	195.3	196.3	197.4
47.5°	222.7	211.9	201.0	194.7	188.4	186.6	184.8	184.6	184.4	185.9	187.3
50°	206.8	196.3	185.9	180.8	175.8	174.1	172.5	173.1	173.6	175.9	178.3
52.5°	192.0	182.3	172.5	167.8	163.1	162.1	161.0	162.2	163.5	166.0	168.5
55°	175.8	166.9	158.1	154.5	150.9	149.8	148.7	151.2	153.8	156.1	158.4
57.5°	160.2	152.5	144.7	141.5	138.2	138.1	137.9	140.2	142.6	145.1	147.6
60°	143.6	137.1	130.7	128.1	125.6	126.0	126.3	129.0	131.7	133.7	135.7
62.5°	128.5	123.1	117.7	115.3	113.0	113.9	114.8	117.5	120.2	122.5	124.9
65°	113.3	108.8	104.3	102.7	101.1	102.3	103.6	105.9	108.3	109.9	111.5
67.5°	98.9	95.1	91.3	90.0	88.8	90.0	91.3	93.7	96.0	97.6	99.3
70°	83.7	80.7	77.6	76.7	75.8	77.2	78.7	80.7	82.7	84.3	85.9
72.5°	69.7	67.3	65.0	64.8	64.6	65.9	67.1	69.1	71.1	72.2	73.3
75°	55.9	54.7	53.4	53.2	53.1	54.3	55.6	56.7	57.7	58.6	59.6
77.5°	43.7	42.6	41.5	41.7	41.9	42.8	43.7	44.8	45.8	46.4	46.9
80°	31.0	30.7	30.3	30.7	31.0	31.8	32.5	33.2	33.9	34.3	34.6
82.5°	21.3	20.9	20.6	21.1	21.7	22.2	22.7	23.3	23.8	24.0	24.2
85°	12.3	12.8	13.4	13.4	13.4	13.5	13.7	13.9	14.1	13.9	13.7
87.5°	5.8	6.0	6.1	6.1	6.1	6.3	6.5	6.5	6.5	6.3	6.1
90°	10.1	12.0	14.7	17.5	20.2	23.0	22.1	23.0	23.9	24.9	26.7
92.5°	46.9	63.5	93.0	141.7	189.6	171.2	127.9	91.1	70.9	61.7	55.2
95°	83.8	119.7	197.9	335.0	486.0	545.8	442.7	331.3	224.6	175.8	142.7
97.5°	96.6	136.2	213.5	372.8	626.8	839.4	867.9	761.2	574.3	452.8	347.9
100°	110.4	146.3	210.8	347.0	589.1	871.6	1052.9	1085.1	1010.6	902.9	772.2
102.5°	126.1	158.3	214.5	324.9	533.8	811.8	1062.1	1192.8	1208.5	1156.9	1086.1
105°	143.6	172.1	221.8	316.6	490.6	740.0	1004.1	1196.5	1288.6	1306.0	1282.1
107.5°	162.9	189.6	233.8	314.8	459.3	676.5	921.3	1141.3	1285.8	1357.6	1382.4
110°	182.2	208.0	249.4	319.4	442.7	624.0	844.0	1054.8	1224.1	1340.1	1404.5

TEST NUMBER: P831356

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	202.5	227.3	265.1	328.6	433.5	589.1	776.8	969.2	1143.1	1276.6	1364.0
115°	222.7	247.6	282.6	338.7	432.6	566.0	725.3	895.5	1055.7	1191.0	1291.3
117.5°	243.0	266.0	301.0	351.6	433.5	550.4	691.2	838.5	980.2	1104.5	1208.5
120°	262.3	285.3	318.5	366.3	437.2	540.3	665.4	795.2	919.5	1029.9	1122.9
122.5°	279.8	304.7	336.9	380.1	443.6	533.8	644.3	761.2	870.7	971.0	1055.7
125°	297.3	322.1	354.4	394.8	450.1	528.3	626.8	731.7	832.0	920.4	994.0
127.5°	313.9	338.7	370.0	406.8	457.4	525.5	610.2	705.0	796.1	877.1	945.2
130°	328.6	353.4	383.8	418.8	464.8	522.8	597.3	680.2	763.0	837.6	900.1
132.5°	342.4	366.3	395.8	429.8	470.3	521.9	585.4	657.2	731.7	799.8	858.7
135°	354.4	379.2	407.7	439.0	475.8	520.9	575.2	636.9	702.3	762.1	814.5
137.5°	365.4	388.4	416.0	446.4	479.5	519.1	566.0	617.6	672.8	726.2	773.1
140°	374.6	397.6	424.3	451.9	483.2	518.2	557.8	601.0	648.0	692.1	731.7
142.5°	383.8	405.0	430.7	457.4	486.0	516.3	550.4	585.4	624.0	660.8	694.0
145°	391.2	412.3	436.3	461.1	486.9	514.5	544.0	573.4	603.8	633.2	659.9
147.5°	400.4	418.8	440.9	463.9	486.9	511.7	537.5	563.3	588.1	613.0	632.3
150°	407.7	424.3	445.5	464.8	486.9	508.1	531.1	552.2	573.4	592.7	610.2
152.5°	415.1	430.7	448.2	466.6	484.1	503.5	523.7	542.1	559.6	576.2	590.0
155°	423.4	436.3	451.9	466.6	482.3	497.9	516.3	532.0	546.7	560.5	571.6
157.5°	430.7	440.9	453.8	467.6	479.5	493.3	508.1	520.9	533.8	544.9	554.1
160°	436.3	445.5	456.5	467.6	477.7	487.8	499.8	511.7	521.9	531.1	537.5
162.5°	440.9	448.2	457.4	466.6	474.0	482.3	491.5	500.7	509.0	517.3	522.8
165°	444.6	451.0	458.4	464.8	470.3	476.8	484.1	491.5	497.0	503.5	508.1
167.5°	448.2	452.8	458.4	463.9	466.6	471.2	476.8	483.2	487.8	491.5	495.2
170°	451.0	452.8	457.4	461.1	463.0	465.7	470.3	474.9	477.7	481.4	483.2
172.5°	452.8	453.8	457.4	460.2	460.2	461.1	463.9	467.6	469.4	472.2	473.1
175°	453.8	454.7	456.5	458.4	457.4	457.4	459.3	461.1	462.0	463.9	463.9
177.5°	454.7	454.7	455.6	457.4	455.6	454.7	455.6	456.5	457.4	458.4	458.4
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P831356

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	777.8	777.8	777.8	777.8
2.5°	691.3	690.1	685.0	680.0
5°	586.1	581.8	580.4	578.9
7.5°	512.1	511.8	504.2	496.6
10°	447.0	447.5	440.7	433.8
12.5°	400.4	395.9	395.4	394.8
15°	365.4	361.3	360.6	359.8
17.5°	340.7	338.2	337.5	336.7
20°	321.9	320.5	319.2	318.0
22.5°	305.7	303.9	302.8	301.7
25°	290.0	288.4	288.0	287.7
27.5°	275.9	273.9	273.9	273.9
30°	262.6	261.3	260.8	260.2
32.5°	250.1	249.0	249.0	249.0
35°	238.4	237.8	237.1	236.4
37.5°	227.7	227.7	227.4	227.0
40°	217.5	218.0	218.0	218.0
42.5°	208.1	208.6	208.6	208.6
45°	198.3	199.2	199.6	199.9
47.5°	188.8	190.2	190.6	190.9
50°	179.4	180.5	180.6	180.8
52.5°	169.8	171.1	172.0	172.9
55°	159.7	161.0	161.5	162.1
57.5°	148.9	150.1	150.3	150.5
60°	137.0	138.2	138.6	139.0
62.5°	125.6	126.3	126.7	127.0
65°	112.6	113.7	114.4	115.1
67.5°	100.2	101.1	101.1	101.1
70°	86.3	86.6	87.2	87.7
72.5°	73.4	73.6	73.6	73.6
75°	59.9	60.3	60.5	60.6
77.5°	47.1	47.3	47.3	47.3
80°	34.5	34.3	34.3	34.3
82.5°	23.6	23.1	23.1	23.1
85°	13.5	13.4	13.5	13.7
87.5°	6.1	6.1	6.1	6.1
90°	25.8	26.7	27.6	26.7
92.5°	53.4	49.7	50.6	48.8
95°	125.2	116.9	110.4	106.8
97.5°	286.2	251.3	229.2	219.1
100°	679.3	612.1	576.2	577.1
102.5°	1018.9	969.2	940.6	914.0
105°	1239.8	1204.8	1175.3	1170.7
107.5°	1376.9	1360.3	1348.4	1338.3
110°	1430.3	1437.7	1435.8	1434.0



TEST NUMBER: P831356

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	<i>1416.5</i>	<i>1443.2</i>	<i>1452.4</i>	<i>1453.3</i>
115°	1360.3	1400.8	1419.2	1423.8
117.5°	1280.3	1325.4	1353.0	1359.4
120°	1195.6	1247.1	1269.2	1274.7
122.5°	1118.3	1163.4	1188.2	1195.6
125°	1052.9	1093.4	1116.4	1122.9
127.5°	998.6	1033.6	1054.8	1060.3
130°	948.9	982.1	1001.4	1008.8
132.5°	903.8	937.0	953.5	958.1
135°	859.6	887.3	903.8	910.3
137.5°	811.8	840.3	854.1	859.6
140°	766.7	792.5	807.2	806.3
142.5°	722.5	744.6	757.5	756.6
145°	682.9	702.3	709.6	711.5
147.5°	650.7	664.5	671.9	672.8
150°	624.0	634.2	639.7	639.7
152.5°	600.1	609.3	612.1	612.1
155°	579.8	587.2	589.1	590.0
157.5°	561.4	567.0	568.8	568.8
160°	544.0	549.5	549.5	548.6
162.5°	526.5	531.1	531.1	530.1
165°	511.7	515.4	514.5	514.5
167.5°	497.0	499.8	498.9	498.9
170°	484.1	486.0	485.0	485.0
172.5°	473.1	474.9	473.1	472.2
175°	463.9	464.8	463.9	463.0
177.5°	457.4	458.4	456.5	456.5
180°	454.7	454.7	454.7	454.7



TEST NUMBER: P831356

CATALOG NUMBER: S123DIP-S340D1195U927-4F0-1E-UDD-G4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.25	8.92	9.39	10.05	11.62	10.49	11.16	11.63	12.29	13.86
	3H	9.89	10.49	11.03	11.62	13.21	11.90	12.50	13.05	13.63	15.22
	4H	10.46	11.02	11.61	12.16	13.75	12.34	12.91	13.50	14.05	15.64
	6H	10.82	11.34	11.98	12.48	14.08	12.61	13.13	13.77	14.27	15.87
	8H	10.91	11.41	12.07	12.56	14.15	12.67	13.16	13.83	14.32	15.91
	12H	10.95	11.42	12.12	12.56	14.18	12.68	13.15	13.85	14.30	15.91
4H	2H	8.81	9.38	9.97	10.51	12.10	10.63	11.20	11.80	12.34	13.93
	3H	10.62	11.09	11.79	12.25	13.86	12.23	12.71	13.40	13.87	15.47
	4H	11.31	11.75	12.48	12.89	14.52	12.81	13.25	13.98	14.40	16.02
	6H	11.77	12.15	12.95	13.32	14.93	13.21	13.58	14.38	14.75	16.36
	8H	11.91	12.26	13.08	13.42	15.05	13.31	13.66	14.49	14.82	16.45
	12H	11.97	12.28	13.15	13.45	15.09	13.35	13.66	14.54	14.84	16.47
8H	4H	11.56	11.91	12.73	13.07	14.70	12.90	13.25	14.08	14.41	16.04
	6H	12.14	12.43	13.34	13.63	15.26	13.40	13.68	14.59	14.89	16.51
	8H	12.35	12.60	13.55	13.78	15.43	13.58	13.83	14.77	15.01	16.65
	12H	12.47	12.68	13.67	13.86	15.54	13.67	13.89	14.87	15.07	16.75
12H	4H	11.55	11.87	12.74	13.04	14.68	12.87	13.18	14.06	14.36	15.99
	6H	12.19	12.44	13.39	13.63	15.27	13.41	13.66	14.61	14.84	16.49
	8H	12.42	12.64	13.62	13.82	15.49	13.60	13.82	14.80	15.00	16.68